



Philips GreenPower LED Flowering Lamp

Length 12.7 cm • 5.0 in
 Width 12.7 cm • 5.0 in
 Height 16.4 cm • 6.5 in
 Weight 0.2 kg • 0.4 lb
 Input voltage 100V – 120V
 Beam angle: 110°

L90
 Warranty 25,000 hrs
 UL/CSA rated 3 year standard
 IP rating Damp/dry
 Ambient operating temp IP44
 0° C Min. • 40° C Max
 32° F Min. • 104° F Max

Frequency 50/60 Hz
 Power factor > 0.90
 Total harmonic distortion < 20%

*Medium Base E26

Flowering Lamp	12 NC	Power (W)	Amps 120V	Amps 208V	Amp 277V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GPL FL 25 DRW 120-240V 2.1S E26	9290 021 00284	10	0.08	0.05	0.04	25	2.5
GPL FL 20 DRWFR 120-240V 2.1S E26	9290 021 00285	9.3	0.08	0.04	0.03	20	2.2