



Philips GreenPower LED Flowering Lamp

Length 12.7 cm • 5.0 in
Width 12.7 cm • 5.0 in
Height 16.4 cm • 6.5 in
Weight 0.2 kg • 0.4 lb
Input voltage 100V – 120V
Beam angle: 110°

L90 25,000 hrs
Warranty 3 year standard
UL/CSA rated Damp/dry
IP rating IP44
Ambient operating temp 0° C Min. • 40° C Max
32° F Min. • 104° F Max

Frequency 50/60 Hz
Power factor > 0.90
Total harmonic distortion < 20%

*Medium Base E26

Philips GreenPower LED Flowering Lamp Gen. 2.1

Description	12 NC	Power (W)	Amps 120V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GPL FL 25 DRW 120-240V 2.1S E26	9290 021 00284	10	0.08	25	2.5
GPL FL 20 DRWFR 120-240V 2.1S E26	9290 021 00285	9.3	0.08	20	2.2

Philips GreenPower LED Flowering Lamp Gen. 2.0

Description	12 NC	Power (W)	Amps 120V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GP LED flowering DR/W E26	9290 015 45906	13	0.11	25	1.9