

PHILIPS

Public lighting

TrueForce



Miss the change or **lead the game?**

Real professionals count on **Philips TrueForce LED SOX** –
the perfect switch from SOX to LED

New!



**REAL
PROs**
**REAL
QUALITY**

Philips TrueForce LED SOX

Keep existing fixture,
save energy and improve
your light quality

Philips TrueForce LED SOX is the cost effective way to upgrade existing luminaires in road and area applications. It has exactly the same size as traditional SOX lamps and the rotational cap enables light adjustments to where it is needed on the ground. The energy efficiency, long lifetime and reduced maintenance bring more savings.

Save on road and area lighting

TrueForce LED SOX lamps are high quality alternatives for conventional SOX lamps used in existing road and highway lighting. The low initial investment – lower than other LED solutions – and energy saving add up to a payback typically within two years. The 36 watt system save up to 35% in energy.

Right light distribution

With a rotational cap and an output of total of up to 5000 lumen, Philips TrueForce LED SOX lamps distribute light where it's needed. The CRI 80 and a 4000K color temperature give a crispy white light to enhance comfort and safety. It combines the right lumen package with high system efficacy to provide the simplest LED solution for instant savings.

Low investment, long lifetime

With a low initial investment and fast payback time, TrueForce LED SOX is the number one choice for anyone looking to upgrade to LED. The TrueForce LED SOX range also offers a reliable lifetime of up to 50,000 hours. It ensures low maintenance needs and has a five-year warranty. So you can look forward to long-term savings too.

Calculate your energy savings





Before

After

Powerful reasons to **switch to LED**



Energy saving
up to 35%



Pleasant white light
with **CRI 80**



Reliable lifetime up
to 50,000 hours



Optically efficient,
emits light towards
usage direction



TrueForce LED SOX (Road/Area – SOX)



| Product type | Lumen Output | Power Wattage | Replacement Wattage | Color Temp | Voltage | Cap | Lifetime | CRI | Dimmable |
|-------------------------------|--------------|---------------|---------------------|------------|---------|-----|----------|-----|----------|
| | lm | W | W | K | VAC | | hrs | | |
| TForce LED SOX 18W B22 840 FR | 2500 | 18 | SOX-E 26W/SOX 35W | 4000 | 100-240 | B22 | 50000 | 80 | No |
| TForce LED SOX 28W B22 840 FR | 4000 | 28 | SOX-E 36W | 4000 | 100-240 | B22 | 50000 | 80 | No |
| TForce LED SOX 36W B22 840 FR | 5000 | 36 | SOX 55W | 4000 | 100-240 | B22 | 50000 | 80 | No |



©2021 Philips Lighting Holding B.V. All rights reserved. This document contains information relating to Philips Lighting product portfolio. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract. Trademarks are the property of Koninklijke Philips N.V., Philips Lighting Holding B.V. or their respective owners.

philips.com/trueforce-led-lamps