



Type A



PAR



BR



Candle



**G25 / ST19
Miscellaneous**

Contents

Type A lamps 1 – 8

PAR lamps 9 – 14

BR lamps 14 – 17

Candles 18 – 21

Misc (G25,ST19) 22 – 23

A Type lamps

Number of bulbs

			 3.8A15/PER/927-922/ CL/G/E12/WGX1FB T20			 3.8A15/PER/927-922/ CL/G/E26/WGX1FB T20			 12A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20			 9.5A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20			 8A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20			 5A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20			 T20 Bulb A19 120V 16-100W 1600lm 2700-2200K E26 D			 12.2A19 WG & DIM T20		
			9290022081 (549378)			9290022083 (549386)			9290034982 (578617) 9290034983 (578625) 9290034984 (578633)			9290034979 (578583) 9290034980 (578591) 9290034981 (578609)			9290034976 (578567) 9290034977 (578575) 9290034978 (578641)			9290034973 (578534) 9290034974 (578542) 9290034975 (578559)			9290022855 (815163)			9290022854 (561000), 9290023852 (561035), 9290023853 (561043), 9290023854 (561050), 9290022852 (560994)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora	6161																								
Leviton	SureSlide	6613																								
Leviton	SureSlide	6615P			1-10			1-10	1-6			1-8					1-9			1-10	1-5			1-8		
Leviton	SureSlide	6631	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	SureSlide	6633	2-10			2-10			1-10			1-10			2-10			1-10			1-10			1-15		
Leviton	SureSlide	6672	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	SureSlide	6674	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	Trimatron	6602	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	Trimatron	6681	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	IllumaTech	IPI06	2-10			2-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	Decora Slide	DSL06	1-10			1-10			1-10			1-10			1-10			1-10			1-20			1-20		
Leviton	IllumaTech	IPL06	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Leviton	IllumaTech	IPM10																								
Philips	Sunrise	SR1000VA120																								
Philips	Sunrise	SR150LED120	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Lightolier	Vega	V600VAU																								
Lightolier	Sunrise	ZP600VA ²																								
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																								
Lightolier	Onset	OS1000VA																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W	1-10			1-10			1-10			1-10			1-10						1-10			1-15		
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD																								
Lutron	Diva	DVCL-153P v2 ²																								
Lutron	Diva	DVCL-153P v3	1-10			1-10			1-10			1-10									1-10			1-15		
Lutron	Diva	DVCL-153P v3.03													1-10			1-10								
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P	1-10			1-10			1-10			1-10			1-10						1-10			1-15		
Lutron	Diva	DV-603PG																								
Lutron	DIVA	DVELV-300P	1-10			1-10									1-9						1-5			1-8		
Lutron	Glyder	GL-600P																								
Lutron	Maestro	MACL-153M v2.2	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-10			1-10			1-10			1-10			1-10						1-10			1-15		
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²							1-10			1-10			1-10			1-10			1-8			1-10		
Lutron	Grafik Eye	QSGR-3P ²							1-10			1-10			1-10			1-10			1-10			1-15		
Lutron	Qoto	Q-600P																								
Lutron	RADIO RA	RRD-6NA ²							1-10			1-10			1-10			1-10			1-10			1-15		
Lutron	Skylark	S-600P																								
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P	1-10			1-10			1-10			1-10			1-10			1-10			1-8			1-10		
Lutron	Skylark	SCL153P v2 ²																								
Lutron	Toggle	TG-600P																								
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)	1-10			1-10			1-10			1-10			1-10			1-10			1-10			1-15		X
Lutron	Maestro	MSCL-OP153MH	1-10			1-10															1-10			1-15		
Lutron	Maestro	MS-OPS2H																								
Leviton	Decora	IPS02	1-10			1-10															1-10			1-15		
Leviton	Decora	IPS05	1-10			1-10															1-10			1-15		
Leviton	Decora	IPS15	1-10			1-10															1-10			1-15		
Leviton	Decora	IPS06	1-10			1-10															1-10			1-15		
Lutron	Panel Module	GP (Harrier) Card																								
Lutron	Panel Module	HW/LP-RPM-4U-120																								

1. InstantFit Ballast Compatibility Guide

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

																							
			3.8A15/PER/927-922/ CL/G/E12/WGX1FB T20	3.8A15/PER/927-922/ CL/G/E26/WGX1FB T20	12A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	9.5A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	8A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	5A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	T20 Bulb A19 120V 16-100W 1600lm 2700-2200K E26 D	12.2A19 WG & DIM T20													
Number of bulbs			9290022855 (561027), 9290023855 (561068), 9290023856 (561076), 9290023857 (561456), 9290022853 (561019)	9290023430 (558221), 9290023431 (558239)	9290023278 (557595)	9290020007 (543116)	9290023276 (557678)	9290023275 (557660)	9290018377, 9290018377A (479485,479402,479535)	9290019413 9290020073 9290019413A 9290020073A													
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																					
Leviton	Decora	6161																					
Leviton	SureSlide	6613																					
Leviton	SureSlide	6615P	1-5			1-3						2-5	8-10	X	1-5			1-9			1-3		
Leviton	SureSlide	6631	1-10			1-5			1-27						1-9			1-17					
Leviton	SureSlide	6633	1-10			1-5			1-27			2-3	1, 5-10		1-9			1-17			1-3		
Leviton	SureSlide	6672	1-10			1-5			1-27			1-5	8-10		1-9			1-17			1-3		
Leviton	SureSlide	6674	1-10			1-5			1-27						1-9			1-17					
Leviton	Trimatron	6602	1-10			1-5						1-3	5-10		1-9			1-17			1-3		
Leviton	Trimatron	6681	1-10			1-5			1-27			2-5	1, 8-10		1-9			1-17			1-3		
Leviton	IllumaTech	IPI06	1-10			1-5			1-27				1-10		1-9			1-17			1-3		
Leviton	Decora Slide	DSL06	1-20			1-10			1-30						1-19			1-20					
Leviton	IllumaTech	IPL06	1-10			1-5			1-27						1-9			1-17					
Leviton	IllumaTech	IPM10										2	3-10	X							1-3		
Philips	Sunrise	SR1000VA120																					
Philips	Sunrise	SR150LED120	1-10			1-5			1-27						1-9			1-17			1-3		
Lightolier	Vega	V600VAU																					
Lightolier	Sunrise	ZP600VA ²																					
Lightolier	Onset	OS600																					
Lightolier	Onset	OS600VA																					
Lightolier	Onset	OS1000VA																					
Lightolier	MultiSet	MHP600VA																					
Lightolier	Momentum	MP2000VAI																					
WattStopper	Micro Decorator	DCD267-W	1-10			1-5							1-2, 8-10	X	1-9			1-17			1-3		
WattStopper	Paddle	PDMLV-703-W																					
WattStopper	Slide	SDMLV-603-W																					
WattStopper	Slide	SD-603-W																					
Lutron	Skylark	CTCL-153P																					
Lutron	Diva	DVCL-153PD																					
Lutron	Diva	DVCL-153P v2 ²												X							1-3		
Lutron	Diva	DVCL-153P v3	1-10			1-5			1-27					X	1-9			1-17					
Lutron	Diva	DVCL-153P v3.03																					
Lutron	Diva	DVPDC-203																					
Lutron	Diva	DV-600P	1-10			1-5							1-10		1-9			1-17			1-3		
Lutron	Diva	DV-603PG																					
Lutron	DIVA	DVELV-300P	1-5			1-3			1-27			1-10			1-9			1-9			1-3		
Lutron	Glyder	GL-600P																					
Lutron	Maestro	MACL-153M v2.2	1-10			1-5			1-27				1-10		1-9			1-17			1-3		
Lutron	Maestro	MAELV-600																					
Lutron	Maestro	MALV-600																					
Lutron	Maestro	MRF2-6ND-120	1-10			1-5							1-10		1-9			1-17			1-3		
Lutron	Nova	NLV600 ²																					
Lutron	Nova	NLV1000 ²	1-8			1-4						1-5	8-10		1-7			1-13			1-3		
Lutron	Grafik Eye	QSGR-3P ²	1-10			1-5			1-30				1-10		1-9			1-17					
Lutron	Qoto	Q-600P																					
Lutron	RADIO RA	RRD-6NA ²	1-10			1-5							1-10		1-9			1-17			1-3		
Lutron	Skylark	S-600P																					
Lutron	Skylark	SELV-300P																					
Lutron	Skylark	SLV-600P	1-8			1-4			1-20			1-2	3-10		1-7			1-13			1-3		
Lutron	Skylark	SCL153P v2 ²																					
Lutron	Toggle	TG-600P																					
Lutron	Power Module	PPHM-WBX																					
Lutron	Caseta	PD-6WCL (SD11)	1-10			X	1-5		1-27					X	1-9			1-17			1-3		
Lutron	Maestro	MSCL-OP153MH	1--10			1-5			1-27					X	1-9			1-17					
Lutron	Maestro	MS-OPS2H										1-10											
Leviton	Decora	IPS02	1-10			1-5			1-27			1-10			1-9			1-17					
Leviton	Decora	IPS05	1-10			1-5			1-27						1-9			1-17					
Leviton	Decora	IPS15	1-10			1-5			1-30			1-10			1-9			1-17					
Leviton	Decora	IPS06	1-10			1-5			1-27						1-9			1-17					
Lutron	Panel Module	GP (Harrier) Card										1-10											
Lutron	Panel Module	HW/LP-RPM-4U-120										1-10											

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

A Type lamps Number of bulbs																										
			8.8w Dimmable A19 Filament T20			8.5w(60w Eq) WG A19 Filament T20			4.5w(40w Eq) WG A19 Filament T20			8w WG A19 Filament			4.5w(40w) A19 Filament Dimmable			5w A19 WG & CG, P0022267, 2019Q1			8.8w (60w Eq) A21 WG & CG, P0022267, 2019Q1			12w (75w Eq) WG & CG T20, P0022267, 2019Q1 WG, 2019Q2 CG		
			9290022079 (549238), 9290022078 (549220)			9290019696 (549493), 9290019695 (549485)			9290019509 (537563)			9290019334 (536920)			9290012101 (461665)			9290019407 (479428), 9290020070			9290019409 (479444), 9290020071			9290019411 (479469), 9290020072		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora	6161																								
Leviton	SureSlide	6613	1-15						1-2,4-20		X		2-10	X	1-2,4-20		X	1-20			1-16			1-10		
Leviton	SureSlide	6615P	1-9						1-20				1-9		1-20				1-14			1-8			3-6	
Leviton	SureSlide	6631				1-18																				
Leviton	SureSlide	6633	1-15			1-18			2-20		X		1-10		2-20		X	1-20			1-16			1-10		
Leviton	SureSlide	6672	1-15			1-18				1-20			1-10			1-20			1-20			1-16			1-10	
Leviton	SureSlide	6674				1-18																				
Leviton	Trimatron	6602	1-15						1,3-20		X		1-10		1,3-20		X	1-20			1-16			1-10		
Leviton	Trimatron	6681	2-15		X	1-18			1,3-20	2			1-10		1,3-20	2		1-20			1-16			1-10		
Leviton	IllumaTech	IPI06	1-15			1-18			1-2,4-20		X		1-10		1-2,4-20		X	1-20			1-16			1-10		
Leviton	Decora Slide	DSL06				1-30																				
Leviton	IllumaTech	IPL06				1-18																				
Leviton	IllumaTech	IPM10	2-15		X								2-10	X				1-20			1-20			1-10		
Philips	Sunrise	SR1000VA120							1-20							1-20										
Philips	Sunrise	SR150LED120				1-20			1-20				1-10			1-20		1-20			1-16			1-10		
Lightolier	Vega	V600VAU																								
Lightolier	Sunrise	ZP600VA ²																								
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																								
Lightolier	Onset	OS1000VA																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W	1-15						1-20			1-3	5-10			1-20		2-20		X	1-16			1-10		
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD	1-15						1-20				1-10			1-20					1-16			1-10		
Lutron	Diva	DVCL-153P v2 ²	1-15						1-20				1-10			1-20		1-20			1-16			1-10		
Lutron	Diva	DVCL-153P v3				1-18																				
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P	1-15						1-20				1-10			1-20		1-20			1-16			1-10		
Lutron	Diva	DV-603PG																								
Lutron	DIVA	DVELV-300P	1-9			1-9			1-20			1-10			1-20			1-14			1-8			1-6		
Lutron	Glyder	GL-600P																								
Lutron	Maestro	MACL-153M v2.2	1-15			1-18			1-20				1-10			1-20		1-20			1-16			1-10		
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-15						1-10	15-20		1-3	5-10		1-10	15-20		1-20			1-16			1-10		
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²	1-15			1-24			1-20			1-10			1-20			1-20			1-20			1-10		
Lutron	Grafik Eye	QSGR-3P ²	8-15	1-5		1-30			1-20			1-3	5-10		1-20									1-10		
Lutron	Qoto	Q-600P																								
Lutron	RADIO RA	RRD-6NA ²	1-15						1-20			1-10			1-20			1-20			1-16			1-10		
Lutron	Skylark	S-600P																								
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P	1-15			1-13			1-20				1-10		1-20			1-20			1-12			1-9		
Lutron	Skylark	SCL153P v2 ²																								
Lutron	Toggler	TG-600P																								
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)	1-15			1-18			3-20		X		1-10		3-20		X	1-20			1-16			1-10		
Lutron	Maestro	MSCL-OP153MH	2-15	1		1-18				1-20			1-10			1-20										
Lutron	Maestro	MS-OPS2H	1-15						1-20			1-10			1-20											
Leviton	Decora	IPSO2	1-15			1-18			1-20			1-10			1-20											
Leviton	Decora	IPSO5				1-18																				
Leviton	Decora	IPSI5	1-15			1-18			1-20			1-10			1-20											
Leviton	Decora	IPSO6				1-30																				
Lutron	Panel Module	GP (Harrier) Card	1-10	15					1-20			1-10			1-20											
Lutron	Panel Module	HW/LP-RPM-4U-120																								

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

																										
			9290020357 (550400), 9290020358 (550418), 9290020359 (547042), 9290020360 (550426)			9290020361 (550434), 9290020362 (550442), 9290020363 (545897), 9290020363 (550459)			9290020364 (550475), 9290020365 (550483), 9290020366 (547091), 9290020367 (550491)			9290020368 (550509), 9290020369 (550517), 9290020370 (547125), 9290020371 (550525)			9290018368 (479881), 9290018369 (479899), 9290018370 (479493)			9290018873 (479873), 9290018668 (532993), 9290018367 (479477)			9290018363 (479857), 9290018364 (479865), 9290018365 (479451)			9290018373 (479444)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora	6161																								
Leviton	SureSlide	6613	1-20			1-17			1-12			1-9			1-9			1-13			1-15			1-15		
Leviton	SureSlide	6615P		2-15	X	1-9			1-6			1-5			1-5			1-6			X	1-8				
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633	1-20			1-17			1-12			1-9			1-9			1-13			1-15			1-15		
Leviton	SureSlide	6672		1-20		1-17			1-12			1-9			1-9			1-13			1-15			1-15		
Leviton	SureSlide	6674																								
Leviton	Trimatron	6602	1-20			1-17			1-12			1-9			1-9			1-13			1-15			1-15		
Leviton	Trimatron	6681	1-20			1-17			1-12			1-9			1-9		1	2-13			1-15			1-15		
Leviton	IllumaTech	IPI06	1-20			1-17			1-12			1-9			1-9			1-13			X	1-15				
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10		1-20		1-17			1-12			1-9						-15								
Philips	Sunrise	SR1000VA120													1-9						1-15		2-15	1		
Philips	Sunrise	SR150LED120	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lightolier	Vega	V600VAU																								
Lightolier	Sunrise	ZP600VA ²																								
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																								
Lightolier	Onset	OS1000VA																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W	1-20			1-17			1-12			1-9			1-9			1013			1-15		1-15			
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD	1-20			1-17				X	1-9				1-9			1-13					1-15			
Lutron	Diva	DVCL-153P v2 ²	1-20			1-17				X	1-9				1-9			1-13			1-15		1-15			
Lutron	Diva	DVCL-153P v3																								
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lutron	Diva	DV-603PG																								
Lutron	DIVA	DVELV-300P	1-15			1-9			1-6			1-5			1-9			1-6			1-15		1-8			
Lutron	Glyder	GL-600P																								
Lutron	Maestro	MACL-153M v2.2	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²	1-20			1-17			1-12			1-9			1-10			1-15			1-16		1-15			
Lutron	Grafik Eye	QSGR-3P ²																1-15			1-15			1-15		
Lutron	Qoto	Q-600P																								
Lutron	RADIO RA	RRD-6NA ²	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lutron	Skylark	S-600P																								
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P	1-20			1-13			1-9			1-7			1-7			1-9			1-8		1-15			
Lutron	Skylark	SCL153P v2 ²																								
Lutron	Toggle	TG-600P																								
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)	1-20			1-17			1-12			1-9			1-9			1-13			1-15		1-15			
Lutron	Maestro	MSCL-OP153MH													1-9			1-13			1-15		1-15			
Lutron	Maestro	MS-OPS2H													1-9			1-13			1-15		1-15			
Leviton	Decora	IPS02													1-9			1-13			1-15		1-15			
Leviton	Decora	IPS05																								
Leviton	Decora	IPS15												1-9			1-13			1-15		1-15		1-15		
Leviton	Decora	IPS06																								
Lutron	Panel Module	GP (Harrier) Card													1-15			1-15			1-15		1-15		1-15	
Lutron	Panel Module	HW/LP-RPM-4U-120													1-15			1-15			1-15		1-15		1-15	

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

			 5.5W(40W Eq)A19			 5.5W(40W Eq)A15 Clear WG			 7W(40W Eq) A15 CC WG			 4.5W(60W Eq) A19			 4.5W A19 Filament			 6W(40 Eq) A19			 6.5W(40W Eq) A19 WG			 7W(40W Eq) A19 CC WG		
			9290018371 (479428), 9290018361 (479840), 9290018669 (532985), 9290018362 (479436)			929001215004 (462529)			9290011818 (458760,458786,458778)			929001210103 (461632), 929001210135 (465542), 929001273935 (466227), 929001274135 (466243)			9290012101 (461665)			9290011348 (455808), 9290011348 (455782), 9290011178 (453209), 9290011178 (453274), 9290011178 (454058), 9290011348 (455790)			9290011347 (455774), 9290011347 (455766), 9290011347 (455741), 9290011176 (453316), 9290011176 (453183)			9290011815 (458737,458752,458745)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora	6161																								
Leviton	SureSlide	6613		1-15		1-25			1-21			1-33			1-33			1-12*			1-23				1-21	
Leviton	SureSlide	6615P	1-14				1-13		1-11			1-17			1-17			1-12*				1-7*		1-11		
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633		1-15		1-25			1-21			1-33			1-33			1-12*			1-23				1-21	
Leviton	SureSlide	6672	1-15			1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	SureSlide	6674							1-21			1-10	11-33		1-10	11-33		1-12*			1-23			1-21		
Leviton	Trimatron	6602	1-15			1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	Trimatron	6681		1-15		1-25			1-21			1-33			1-33			1-12*			1-23			1-21		1-21
Leviton	IllumaTech	IPI06		1-15		1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10				2-25	1	2-21		1		2-33	1		2-33	1		1-12*			2-23		1	2-21		1
Philips	Sunrise	SR1000VA120		2-15	X	2-25	1	2-21		1		2-33	1		2-33	1		1-12*			2-23		1	2-21		1
Philips	Sunrise	SR150LED120		1-15		1-3	4-25	1-21				1-10	11-33		1-10	11-33		1-12*			1-23			1-21		
Lightolier	Vega	V600VAU																								
Lightolier	Sunrise	ZP600VA ²																								
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																								
Lightolier	Onset	OS1000VA																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W		10-15	X	1-25			2-21		1	1-33			1-33			1-12*			1-23			2-21		1
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD		1-15		1-3	4-25			X							X									X
Lutron	Diva	DVCL-153P v2 ²		1-15		1-3	4-25	1-15	16-21			X			1-8	9-33		1-12*			X		1-15	16-21		
Lutron	Diva	DVCL-153P v3																								
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203										1-8	9-33													
Lutron	Diva	DV-600P		1-15		1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Lutron	Diva	DV-603PG																								
Lutron	DIVA	DVELV-300P	1-15			1-13			1-11			1-17			1-17			1-12*			1-7*			1-11		
Lutron	Glyder	GL-600P																								
Lutron	Maestro	MACL-153M v2.2		1-15		1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120		1-15		1-25			1-15	16-21		1-33			1-33			1-12*			1-23			1-15	16-21	
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²	2-15	1		1-25			1-21*			1-33			1-33			1-12*			1-23*			1-21*		
Lutron	Grafik Eye	QSGR-3P ²		1-15		1-25			1-21*			1-10	11-33		1-10	11-33		1-12*			1-23*			1-21*		
Lutron	Qoto	Q-600P																								
Lutron	RADIO RA	RRD-6NA ²		1-15		1-3	4-25		X	1-15	16-33			1-15	16-33			1-12*			1-23					X
Lutron	Skylark	S-600P																								
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P	1-5	8-15		1-19			1-16			1-25			1-25			1-12*			1-10*			1-16		
Lutron	Skylark	SCL153P v2 ²																								
Lutron	Toggler	TG-600P																								
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)		1-15		1-3	4-25	1-21				X				X		1-12*			1-23			1-21		
Lutron	Maestro	MSCL-OP153MH		1-15		1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Lutron	Maestro	MS-OPS2H	1-15			1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	Decora	IPS02	1-15			1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	Decora	IPS05																								
Leviton	Decora	IPS15	1-15			1-25			1-21			1-33			1-33			1-12*			1-23			1-21		
Leviton	Decora	IPS06																								
Lutron	Panel Module	GP (Harrier) Card	1-15			1-25			1-21*			1-33			1-33									1-21*		
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15			1-25			1-21*			1-33			1-33									1-21*		

A Type lamps

Number of bulbs

			 8W A19			 8W (40W Eq) A19			 8W (40W Eq) A19 Sultan			 8W A19 Slim Style			 9W (60W) A19 3000K Core			 9W (60W Eq) A19 5000K			 9W (60W Eq) A19 5000K			 9W A19 3000k Core		
			409938			417048, 414839			9290002267 (423483), 9290002267 (424374), 9290002295 (425256), 9290002267 (429266)			9290002706 (433219), 9290002706 (433136), 9290002704 (433201), 9290002704 (433128)			929001196904 (459057), 929001196905 (462234), 929001196995 (462242)			9290011970 (461327), 9290011970 (455881), 9290011970 (461368), 9290011970 (461335), 9290011970 (461350), 9290011970 (462259)			9290011346 (455881), 9290011346 (455899), 9290011346 (455873), 929001177 (453282), 929001177 (453241),			9290011969(459057), 9290011969(462234), 9290011969(462242)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2	1-16				1-4	>4																		
Leviton	Decora	6161			X																					
Leviton	SureSlide	6613			X			X		1-12	>12	1-18			1-15			1-17			1-15			1-15		
Leviton	SureSlide	6615P			X			X	1-9			1-8			1-8			1-8			1-8				1-8	
Leviton	SureSlide	6631			X																					
Leviton	SureSlide	6633													1-15			1-17			1-15			1-15		
Leviton	SureSlide	6672													1-15			1-17			1-15			1-15		
Leviton	SureSlide	6674	1-14				1-7				X	1-18			1-15	1-15		1-3		4-17	1-15				1-15	
Leviton	Trimatron	6602													1-15			1-17			1-15			1-15		
Leviton	Trimatron	6681			X	1-4	5-6	>6			X	1-18			1-15			1-17			1-15			1-15		
Leviton	IllumaTech	IPI06		1-16				X		1-9	>9	1-18			1-15			1-17			1-15			1-15		
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10													1-15			1-17			1-15				1-15	
Philips	Sunrise	SR1000VAI20													1-15			1-17			1-15				1-15	
Philips	Sunrise	SR150LED120													1-15			1-3		4-17	1-15				1-15	
Lightolier	Vega	V600VAU	1-2	3-16		1-8			1-13																	
Lightolier	Sunrise	ZP600VA ²			X	1-8					X															
Lightolier	Onset	OS600	3-16		1 or 2																					
Lightolier	Onset	OS600VA	1-4		>4			X	1-13																	
Lightolier	Onset	OS1000VA	1-4		>4																					
Lightolier	MultiSet	MHP600VA	1-8	9-16			1-16				X															
Lightolier	Momentum	MP2000VAI	1-16			1-7																				
WattStopper	Micro Decorator	DCD267-W	1-16					X	2-131		1	1-18			1-15			1-17			1-15				1-15	
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P	1-4																							
Lutron	Diva	DVCL-153PD		1-12		1-8													X							X
Lutron	Diva	DVCL-153P v2 ²	1-16				1-8		1-18			1-18			X			1-3	4-17		1-15			1-15		
Lutron	Diva	DVCL-153P v3																								
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203		1-4											1-15											
Lutron	Diva	DV-600P	1-16					X	1-6		>6	1-18			1-15			1-17			1-15			1-15		
Lutron	Diva	DV-603PG			X			X																		
Lutron	DIVA	DVELV-300P	1-9			1-18				1-9		1-8			1-8			1-8				1-8			1-8	
Lutron	Glyder	GL-600P			X			X																		
Lutron	Maestro	MACL-153M v2.2			X			X	1-12		>12	1-18			1-15			1-3	4-17		1-15				1-15	
Lutron	Maestro	MAELV-600	1-16																							
Lutron	Maestro	MALV-600			X																					
Lutron	Maestro	MRF2-6ND-120			X			X	1-12		>12	1-18			1-15			1-17			1-15				1-15	
Lutron	Nova	NLV600 ²	1-16			1-18			1-8	8-11	>11															
Lutron	Nova	NLV1000 ²	1-16*			1-24*			1-8	8-11	>11		1-18*		1-15			1-17			1-15*			1-15		
Lutron	Grafik Eye	QSGR-3P ²			X			X	1-17				1-18*		1-15			1-3		4-17		1-15*			1-15	
Lutron	Qoto	Q-600P			X			X																		
Lutron	RADIO RA	RRD-6NA ²	1-16				1-16		1-13			1-18			1-15			1-3		4-17	1-15				1-15	
Lutron	Skylark	S-600P						X																		
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P	1-16					X		1-12	>12	1-11			1-15			1-13			1-15			1-15		
Lutron	Skylark	SCL153P v2 ²				1-8			1-18				1-18													
Lutron	Toggler	TG-600P																								
Lutron	Power Module	PHPM-WBX	1-32																							
Lutron	Caseta	PD-6WCL (SD11)													1-15			1-17			1-15				1-15	
Lutron	Maestro	MSCL-OP153MH							1-18						1-15	1-15		1-17	1-17		1-15	1-15			1-15	1-15
Lutron	Maestro	MS-OPS2H							1-18						1-15			1-17			1-15			1-15		
Leviton	Decora	IPS02													1-15			1-17			1-15			1-15		
Leviton	Decora	IPS05													1-15			1-17			1-15			1-15		
Leviton	Decora	IPS15													1-15			1-17			1-15			1-15		
Leviton	Decora	IPS06																								
Lutron	Panel Module	GP (Harrier) Card													1-15			1-17						1-15		
Lutron	Panel Module	HW/LP-RPM-4U-120													1-15			1-17						1-15		

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

																							
			9.5W A19 2700K Core			9.5W A19 WG			9.5W A19 2200K-2700K			10W (60W Eq) A19 Clear WG			10W A19 L Prize			10.5W (60W Eq) A19 Slim style			11W (60W Eq) A19 Sultan		
			9290012006 (461269), 9290012006 (461194), 9290012006 (461210), 9290012006 (461244), 9290012006 (461226), 9290012006 (461228), 9290012006 (461251), 9290012006 (461236)			9290011175 (453258), 9290011175 (453324), 9290011345 (455865), 9290011345 (455857), 9290011345 (455840), 9290011345 (455831), 9290011345 (455832), 9290011345 (455816), 9290011175 (453225), 9290011345(455824)			9290011840			9290012149 (462499)			420224, 420075			9290002709 (433235), 9290002709 (433151), 9290002707 (433227), 9290002707 (433144),			9290002268 (423491, 424382, 429258), 9290002296 (425264)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2															X					1-2 1	>3
Leviton	Decora	6161													1-4								
Leviton	SureSlide	6613	1-15			1-15			1-15			1-15				1-5	>5	1-14				1-13 1	
Leviton	SureSlide	6615P		1-8		1-8			1-5			1-8				1-4	>4	1-5				1-4 1	>4
Leviton	SureSlide	6631																					
Leviton	SureSlide	6633	1-15				1-15		1-15			1-15											
Leviton	SureSlide	6672	1-15			1-15			1-15			1-15											
Leviton	SureSlide	6674		1-15		1-15			1-15			1-15			1	2	>2	1-14				1-4 1	>4
Leviton	Trimatron	6602	1-15				1-15		1-15			1-15											
Leviton	Trimatron	6681	1-15			1-15			1-15			1-15				X		1-14					X
Leviton	IllumaTech	IPI06	1-15			1-15			1-15			1-15			1-2	>2	1-14						X
Leviton	Decora Slide	DSL06																					
Leviton	IllumaTech	IPL06																					
Leviton	IllumaTech	IPM10		1-15		1-15						1-15											
Philips	Sunrise	SRI000VA120		1-15		1-15			1-15			1-15											
Philips	Sunrise	SRI50LED120		1-15		1-15			1-15			1-15											
Lightolier	Vega	V600VAU														1-4						1-13 1	
Lightolier	Sunrise	ZP600VA ²													1-10*							1-2 1	>2
Lightolier	Onset	OS600																					
Lightolier	Onset	OS600VA													1-4	5-6	>6					1-13 1	
Lightolier	Onset	OS1000VA																					
Lightolier	MultiSet	MHP600VA													1-9*							1-2 1	>2
Lightolier	Momentum	MP2000VAI													3-8	1-2							
WattStopper	Micro Decorator	DCD267-W		1-15		1-15			1-15			1-15				1-11*		1-14				1-13 1	
WattStopper	Paddle	PDMLV-703-W																				1-12 1	
WattStopper	Slide	SDMLV-603-W																				1-8 1	>8
WattStopper	Slide	SD-603-W																				1-8 1	>8
Lutron	Skylark	CTCL-153P															X					1-5 1	>5
Lutron	Diva	DVCL-153PD			X							1-15				1	>1					1-13 1	
Lutron	Diva	DVCL-153P v2 ²		1-15		1-15			X			1-15			1-9*			1-14				1-13 1	
Lutron	Diva	DVCL-153P v3																					
Lutron	Diva	DVCL-153P v3.03																					
Lutron	Diva	DVPDC-203																					
Lutron	Diva	DV-600P	1-15			1-15			1-15			1-15			1-4	5	>5	1-14				1-4 1	>4
Lutron	Diva	DV-603PG													1-4	5	>5						
Lutron	DIVA	DVELV-300P	1-8			1-8			1-5			1-8			1-5			1-5				1-6 1	
Lutron	Glyder	GL-600P													1-4								
Lutron	Maestro	MACL-153M v2.2		1-15		1-15			X			1-15			1-9*			1-14				1-13 1	
Lutron	Maestro	MAELV-600														1-4							
Lutron	Maestro	MALV-600															X						
Lutron	Maestro	MRF2-6ND-120		1-15		1-15			1-15			1-15				1-11*		1-14				1-13 1	
Lutron	Nova	NLV600 ²													1-10*							1-13 1	
Lutron	Nova	NLV1000 ²	1-15			1-15*			1-15			1-15			1-10*			1-14*				1-13* 1	
Lutron	Grafik Eye	QSGR-3P ²		1-15		1-15*			1-15			1-15			1-9*			1-14*				1-13* 1	
Lutron	Qoto	Q-600P													1-8		>8						
Lutron	RADIO RA	RRD-6NA ²		1-15		1-15			1-15			1-15			1-9*			1-14				1-13* 1	
Lutron	Skylark	S-600P																					
Lutron	Skylark	SELV-300P																					
Lutron	Skylark	SLV-600P	1-15			1-15			1-11			1-11				1-4	>4	1-8				1-13 1	
Lutron	Skylark	SCL153P v2 ²																1-14				1-13* 1	
Lutron	Toggler	TG-600P															>6						
Lutron	Power Module	PPHM-WBX													1-8								
Lutron	Caseta	PD-6WCL (SD11)		1-15		1-15			1-15			1-15											
Lutron	Maestro	MSCL-OP153MH		1-15		1-15			1-15			1-15											
Lutron	Maestro	MS-OPS2H	1-15			1-15			1-15			1-15											
Leviton	Decora	IPS02	1-15			1-15			1-15			1-15											
Leviton	Decora	IPS05																					
Leviton	Decora	IPS15	1-15			1-15			1-15			1-15											
Leviton	Decora	IPS06																					
Lutron	Panel Module	GP (Harrier) Card	1-15			1-19			1-15			1-15											
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15						1-15			1-15											

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

A Type lamps

Number of bulbs

A Type lamps Number of bulbs			 12.5W (60W Eq) A19			 13W (75W Eq) A21 Slim style			 14W (75W Eq) A21 WG			 15W (75W Eq) A21			 17W (75W Eq) A21 Prince			 18W (100W Eq) A21 WG			 19W (100W Eq) A21			 22W (100W Eq) A21		
			409946 (12E26A60-1 and 9290001829 models only)			9290011120 (452771), 9290011120 (452805), 9290011120 (452789), 9290011120 (452755), 9290011120 (452748), 9290011120 (452730)			9290011839 (459065), 9290011839 (459073), 9290011839 (459081), 9290011839 (459099)			9290002595A (453159), 9290002595A (451898)			17E26A21D (418590), 9290002018 (422220)			9290011741 (459107), 9290011741 (459115), 9290011741 (459123), 9290011741 (459131)			9290002596A (451906)					
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								X
Leviton	Decora	6161																								
Leviton	SureSlide	6613	1-12			1-13			1-11			1-8*			1-8 1			1-8			1-6*					X
Leviton	SureSlide	6615P	1-12				1-8			1-5		1-4*			1-4 1			1-8			1-3					X
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633							1-11									1-8								
Leviton	SureSlide	6672								1-11								1-8								
Leviton	SureSlide	6674	1-12			1-13			1-11				X		1-8 1			1-8				X				X
Leviton	Trimatron	6602								1-11								1-8								
Leviton	Trimatron	6681		1-8	>8	1-13			1-11			1-8*			1-6 1	>6	1-8				1-6*					X
Leviton	IllumaTech	IPI06	1-12			1-13				1-11			1-8*		1-8 1			1-8				X		1-6 1		
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10							1-11									1-8								
Philips	Sunrise	SR1000VA120								1-11								1-8								
Philips	Sunrise	SR150LED120				1-13			1-11				X					1-8				X				
Lightolier	Vega	V600VAU	1-12												1-5 1											X
Lightolier	Sunrise	ZP600VA ²	1-12												1-8 1										1-6 1	
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA	1-12												1-8 1										1-6 1	
Lightolier	Onset	OS1000VA																								
Lightolier	MultiSet	MHP600VA	1-12												1-8 1										1-6 1	
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W	1-12			1-13			1-11			1-8*			1-8 1			1-8			1-6*			1-6 1		
WattStopper	Paddle	PDMLV-703-W		1-14																						
WattStopper	Slide	SDMLV-603-W	1-12																							
WattStopper	Slide	SD-603-W	1-12																							
Lutron	Skylark	CTCL-153P													1-8 1											
Lutron	Diva	DVCL-153PD								X					1-4 1				X						X	
Lutron	Diva	DVCL-153P v2 ²	1-12				X	1-11				X			1-8 1			1-8			1-7				X	
Lutron	Diva	DVCL-153P v3																								
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203													X											
Lutron	Diva	DV-600P	1-8	9-12		1-13			1-11			1-8*			1-8 1			1-8			1-6*				X	
Lutron	Diva	DV-603PG													1-8 1											
Lutron	DIVA	DVELV-300P	1-12			1-7			1-5			1-4*			1-4 1			1-8			1-3*				X	
Lutron	Glyder	GL-600P													1-8 1											
Lutron	Maestro	MACL-153M v2.2	1-12			1-13			1-11			1-8*			1-8 1			1-8			1-6*			1-6 1		
Lutron	Maestro	MAELV-600																							1-6 1	
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-12			1-13			1-11			1-8*			1-8 1			1-8			1-6*			1-6 1		
Lutron	Nova	NLV600 ²	1-12												1-8 1										1-6 1	
Lutron	Nova	NLV1000 ²	1-16*			1-13*			1-11*			1-8*			1-14 1			1-8*			1-6*				1-10 1	
Lutron	Grafik Eye	QSGR-3P ²	1-12*				X		1-11*				X		1-11* 1			1-8*				X			1-8* 1	
Lutron	Qoto	Q-600P																								X
Lutron	RADIO RA	RRD-6NA ²	1-12			1-13			1-11			1-8*			1-8 1			1-8			1-7				1-6 1	
Lutron	Skylark	S-600P													1-8 1											
Lutron	Skylark	SELV-300P													1-8 1										1-6	
Lutron	Skylark	SLV-600P			X	1-10			1-11			1-6*			1-4 1	>4		1-8			1-4*			1-6 1		
Lutron	Skylark	SCL153P v2 ²					X														1-7					
Lutron	Toggle	TG-600P													1-4 1	>4										
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)								1-11								1-8								
Lutron	Maestro	MSCL-OP153MH				1-13				11*	1-10							1-8*			1-7					
Lutron	Maestro	MS-OPS2H				1-13*			1-11*									1-8*								
Leviton	Decora	IPS02				1-13*			1-11*									1-8*								
Leviton	Decora	IPS05																								
Leviton	Decora	IPS15				1-13*			1-11*									1-8*								
Leviton	Decora	IPS06																								
Lutron	Panel Module	GP (Harrier) Card							1-23									1-22			1-12					
Lutron	Panel Module	HW/LP-RPM-4U-120							1-23									1-22			1-17					

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps

Number of bulbs

																											
			14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB			9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB			14PAR38/COR/935-940/F25/DIM/120V/T20 6/1FB			PAR20 5.5W JA8			PAR20 WG 5.5W JA8			PAR30S/L 8.5W JA8			PAR38 10W JA8			PAR38 13W JA8			
			9290031338 (576470)			9290034669 (577759)						9290030261 (568063), 9290030262 (568071), 9290030264 (568089), 9290030265 (568097)			9290030263 (568105), 9290030267 (568113)			9290030277 (568006), 9290030278 (568014), 9290030279 (568022), 9290030280 (568030), 9290030281 (568048), 9290030282 (568055), 9290030269 (567941), 9290030270 (567957), 9290030271 (567965), 9290030272 (567973), 9290030273 (567981), 9290030274 (567999)			9290030285 (567859), 9290030286 (567867), 9290030287 (567925), 9290030288 (567875), 9290030289 (567883), 9290030290 (567891), 9290030291 (567909), 9290030292 (567933), 9290030293 (567917)			9290030295 (567750), 9290030296 (567768), 9290030298 (567776), 9290030299 (567784), 9290030300 (567792), 9290030301 (567800), 9290030303 (567818), 9290030304 (567826), 9290030297 (567834), 9290030302 (567842)			
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	
Leviton	Decora Slide	DSL06				1-10			1-10			1-20			1-20			1-20				1-20			1-20		
Leviton	SureSlide	6613	1-5																								
Leviton	SureSlide	6615P		1-5				X			X																
Leviton	SureSlide	6631				1-10			1-10																		
Leviton	SureSlide	6633	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	SureSlide	6672	1-5			1-10			1-10																		
Leviton	SureSlide	6674				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Trimatron	6602	1-5			1-10			1-10																		
Leviton	Trimatron	6681	2-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	IllumaTech	IPI06		1-5				X			X	1-20			1-20			1-15			1-15			1-10			
Leviton	IllumaTech	IPL06				1-10			1-10																		
Leviton	IllumaTech	IPM10																									
Philips	Sunrise	SR1000VA120	1-5																								
Philips	Sunrise	SR150LED120	1-5																								
WattStopper	Micro Decorator	DCD267-W				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Diva	DVCL-153PD																									
Lutron	Diva	DVCL-153P v2 ²																									
Lutron	Diva	DVCL-153P v2.1																									
Lutron	Diva	DVCL-153P v2.2																									
Lutron	Diva	DVCL-153P v3.0				1-10			1-10				1-20			1-20		1-15			1-15			1-10			
Lutron	Diva	DVPDC-203																									
Lutron	Diva	DV-600P	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	DIVA	DVELV-300P	1-5									1-10			1-10			1-8			1-8			1-5			
Lutron	Maestro	MACL-153M v2 ²	1-5			1-10			1-10																		
Lutron	Maestro	MRF2-6ND-120	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Nova	NLV1000 ²	1-5			1-10			1-10																		
Lutron	Grafik Eye	QSGR-3P ²																									
Lutron	RADIO RA	RRD-6NA ²																									
Lutron	Skylark	S-600P																									
Lutron	Skylark	SLV-600P	1-5			1-10			1-8			1-15			1-15			1-10			1-10			1-8			
Lutron	Caseta	PD-6WCL (SD11)	1-5			1-10			1-10																		
Lutron	Maestro	MSCL-OP153MH				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Maestro	MS-OPS2H																									
Leviton	Decora	IPS02				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS05										1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS06				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS15				1-10			1-10			1-20			1-20			1-20			1-20			1-20			
Lutron	Panel Module	GP (Harrier) Card																									
Lutron	Panel Module	HW/LP-RPM-4U-120																									

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps

Number of bulbs



PAR38 TrueForce DIM
120-277V



7W PAR20 Glass



7W PAR20 WG Glass



120V Gen2 Glass
PAR30S 10-75W



120V Gen2 Glass
PAR30L 10-75W



12W Glass PAR30



120V Gen2 Glass
PAR38 12-90W



13.5W PAR38 GLASS

92900030635 (569723),
92900030636 (569731)

92900013165 (471110),
92900013169 (471144),
92900013167 (471128),
92900013170 (471151)

92900013172 (471102),
92900013173 (471136)

92900013204 (529768),
92900013205 (529776),
92900013207 (529784),
92900013209 (529792),
92900013210 (529800),
92900013212 (529818),
92900013213 (471334)

92900013215 (529701),
92900013216 (529719),
92900013218 (529727),
92900013220 (529735),
92900013221 (529743),
92900013223 (529750),
92900013224 (471359),
92900013224 (471318)

92900012940 (467811),
92900012941 (467829),
92900012942 (467837),
92900012944 (467845),
92900012945 (467852),
92900012946 (467860),
92900012948 (467878),
92900012949 (467886),
92900012950 (467894),
92900012952 (467902),
92900012953 (467910),
92900012954 (467928)

92900013194 (529628),
92900013195 (529636),
92900013196 (474692),
92900013197 (529644),
92900013198 (529651),
92900013199 (529669),
92900013200 (529677),
92900013201 (474700),
92900013202 (529685),
92900013203 (529693)

92900012920 (467753),
92900012921 (467761),
92900012922 (467779),
92900012923 (468199),
92900012924 (467787),
92900012925 (467795),
92900012925 (467992),
92900012925 (468017),
92900012926 (467803),
92900012927 (468009),
92900012927 (468025)

Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06			X																					
Leviton	SureSlide	6613				1-16			1-15				1-15			1-15			1-13			1-11				1-11
Leviton	SureSlide	6615P	1-3				1-10			1-10			1-8			1-8			2-5	1		1-5				1-5
Leviton	SureSlide	6631	1-6																							
Leviton	SureSlide	6633	1-6			1-16			1-15				1-15			1-15			1-13			1-11				X
Leviton	SureSlide	6672		1-6		1-16			1-15			1-15			1-15				X	1-11						1-11
Leviton	SureSlide	6674			X														X							X
Leviton	Trimatron	6602		1-6		1-16			1-15			1-15			1-15				X		1-11					X
Leviton	Trimatron	6681		1-6		1-16			1-15				1-15			1-15			X		1-11					X
Leviton	IllumaTech	IPI06	1-6				1-16		1-15			1-15			1-15				1-13			1-11				1-11
Leviton	IllumaTech	IPL06			X																					
Leviton	IllumaTech	IPM10					2-16	X		2-15	X								1-16							X
Philips	Sunrise	SR1000VA120										2-15	1		2-15	1			1-16			1-13				X
Philips	Sunrise	SR150LED120			X	1-16			1-15				1-15			1-15				X		1-11				X
WattStopper	Micro Decorator	DCD267-W		1-6			2-16	X	2-15		X	1-2	3-15		1-2	3-15				X		1-11				X
Lutron	Diva	DVCL-153PD																								
Lutron	Diva	DVCL-153P v2 ²																		X						X
Lutron	Diva	DVCL-153P v2.1																		X						X
Lutron	Diva	DVCL-153P v2.2					1-16			1-15				X			X					1-2	X			
Lutron	Diva	DVCL-153P v3.0			X	3	5-8	1-2/10-16		1-15				X			X					1-5	X			
Lutron	Diva	DVPDC-203																		X						
Lutron	Diva	DV-600P	1-6			1-16				1-15		1-15			1-15				1-13			1-11				1-11
Lutron	DIVA	DVELV-300P	1-3			1-10				1-15		1-8			1-8			1-5				1-5				1-5
Lutron	Maestro	MACL-153M v2 ²		1-6			1-16			1-15			1-15			1-15				X		1-11				X
Lutron	Maestro	MRF2-6ND-120			X	1-16			1-15				1-15			1-15				X		1-11				X
Lutron	Nova	NLV1000 ²	1-7			1-16			1-15			1-15			1-15				1-13		1	2-11				1-11
Lutron	Grafik Eye	QSGR-3P ²		1-6		1-16			1-15				1-2	X		1-2	X			X		1-14				X
Lutron	RADIO RA	RRD-6NA ²			X	1-16			1-15			1-2	3-15		1-2	3-15				X	1-3	5-11				X
Lutron	Skylark	S-600P																								
Lutron	Skylark	SLV-600P	1-4			1-16				1-15		1-11			1-11				1-9			1-8				1-8
Lutron	Caseta	PD-6WCL (SD11)			X		1-16			1-15			1-15			1-15				X		1-11				X
Lutron	Maestro	MSCL-OP153MH			X		1-16			1-15			1-15			1-15				X		1-11				X
Lutron	Maestro	MS-OPS2H				1-16			1-15			1-15			1-15			1-13			1-11			1-11		
Leviton	Decora	IPS02	1-6			1-16			1-15			1-15			1-15			1-13			1-11			1-11		
Leviton	Decora	IPS05	1-6																							
Leviton	Decora	IPS06	1-6																							
Leviton	Decora	IPS15	1-15			1-16			1-15			1-15			1-15			1-13			1-11			1-11		
Lutron	Panel Module	GP (Harrier) Card				1-16			1-15				1-15			1-15				X		1-14				X
Lutron	Panel Module	HW/LP-RPM-4U-120				1-16			1-15				1-15			1-15				X	1-2	3-14				X

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps

Number of bulbs

14PAR38/COR/930/F25/D/P/B/ULW/T20 6/1FB

9.4PAR30S/COR/935/F25/DIM/120V/T20 6/1FB

14PAR38/COR/935-940/F25/DIM/120V/T20 6/1FB

PAR20 5.5W JA8

PAR20 WG 5.5W JA8

PAR30S/L 8.5W JA8

PAR38 10W JA8

PAR38 13W JA8

9290031338 (576470)

9290034669 (577759)

9290030261 (568063),
9290030262 (568071),
9290030264 (568089),
9290030265 (568097)

9290030263 (568105),
9290030267 (568113)

9290030277 (568006),
9290030278 (568014),
9290030279 (568022),
9290030280 (568030),
9290030281 (568048),
9290030282 (568055),
9290030269 (567941),
9290030270 (567957),
9290030271 (567965),
9290030272 (567973),
9290030273 (567981),
9290030274 (567999)

9290030285 (567859),
9290030286 (567867),
9290030287 (567925),
9290030288 (567875),
9290030289 (567883),
9290030290 (567891),
9290030291 (567909),
9290030292 (567933),
9290030293 (567917)

9290030295 (567750),
9290030296 (567768),
9290030298 (567776),
9290030299 (567784),
9290030300 (567792),
9290030301 (567800),
9290030303 (567818),
9290030304 (567826),
9290030297 (567834),
9290030302 (567842)

Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	
Leviton	Decora Slide	DSL06				1-10			1-10			1-20			1-20			1-20				1-20			1-20		
Leviton	SureSlide	6613	1-5																								
Leviton	SureSlide	6615P		1-5				X			X																
Leviton	SureSlide	6631				1-10			1-10																		
Leviton	SureSlide	6633	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	SureSlide	6672	1-5			1-10			1-10																		
Leviton	SureSlide	6674				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Trimatron	6602	1-5			1-10			1-10																		
Leviton	Trimatron	6681	2-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	IllumaTech	IPI06		1-5				X			X	1-20			1-20			1-15			1-15			1-10			
Leviton	IllumaTech	IPL06				1-10			1-10																		
Leviton	IllumaTech	IPM10																									
Philips	Sunrise	SR1000VA120	1-5																								
Philips	Sunrise	SR150LED120	1-5																								
WattStopper	Micro Decorator	DCD267-W				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Diva	DVCL-153PD																									
Lutron	Diva	DVCL-153P v2 ²																									
Lutron	Diva	DVCL-153P v2.1																									
Lutron	Diva	DVCL-153P v2.2																									
Lutron	Diva	DVCL-153P v3.0				1-10			1-10				1-20			1-20		1-15			1-15			1-10			
Lutron	Diva	DVPDC-203																									
Lutron	Diva	DV-600P	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	DIVA	DVELV-300P	1-5									1-10			1-10			1-8			1-8			1-5			
Lutron	Maestro	MACL-153M v2 ²	1-5			1-10			1-10																		
Lutron	Maestro	MRF2-6ND-120	1-5			1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Nova	NLV1000 ²	1-5			1-10			1-10																		
Lutron	Grafik Eye	QSGR-3P ²																									
Lutron	RADIO RA	RRD-6NA ²																									
Lutron	Skylark	S-600P																									
Lutron	Skylark	SLV-600P	1-5			1-10			1-8			1-15			1-15			1-10			1-10			1-8			
Lutron	Caseta	PD-6WCL (SD11)	1-5			1-10			1-10																		
Lutron	Maestro	MSCL-OP153MH				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Lutron	Maestro	MS-OPS2H																									
Leviton	Decora	IPS02				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS05										1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS06				1-10			1-10			1-20			1-20			1-15			1-15			1-10			
Leviton	Decora	IPS15				1-10			1-10			1-20			1-20			1-20			1-20			1-20			
Lutron	Panel Module	GP (Harrier) Card																									
Lutron	Panel Module	HW/LP-RPM-4U-120																									

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs



120V Gen2 Glass
PAR38 14-120W



16W PAR38 Glass



120V Expert Color
PAR20 9W



12W PAR30L Expert color,
9.4w PAR30L & PAR30S T20



17W PAR38 SO/Expert color,
14w PAR38 T20, 10w PAR38 T20



120V High Lumen DIM
PAR38 33W (Prof)



120V High Lumen DIM
PAR38 33W (Cons)

9290013183 (529503),
9290013184 (529529),
9290013185 (474676),
9290013186 (529537),
9290013187 (529545),
9290013188 (529552),
9290013189 (529594),
9290013190 (474684),
9290013191 (529602),
9290013192 (529610)

9290012912 (467696),
9290012913 (467704),
9290012914 (467712),
9290012915 (468181),
9290012916 (467720),
9290012917 (467936),
9290012917 (467738),
9290012917 (467976),
9290012918 (467746),
9290012919 (467944),
9290012919 (467984)

9290019218 (535260),
9290019219 (535278),
9290019220 (535286),
9290019221 (535294),
9290019222 (535300),
9290019223 (535310),
9290019224 (535328),
9290019225 (535336)

9290012858 (533299),
9290012858 (471052),
9290012857 (533281),
9290012857 (471045),
9290012856 (471037),
9290013409 (470954),
9290013410 (470962),
9290013411 (470970),
9290013412 (470988),
9290020454 (546969),
9290020455 (546977),
9290020456 (546985),
9290020457 (546993)

9290012855 (471029), 9290012854 (471011),
9290012853 (471003), 9290012852 (470996),
9290011131 (435354), 9290011132 (435362),
9290011134 (435388), 9290011135 (435396),
9290011137 (435412), 9290011138 (435420),
9290013394 (470823), 9290013395 (471831),
9290013396 (470849), 9290013398 (470864),
9290013698 (471797), 9290013400 (470872),
9290013401 (470880), 9290020450 (546929),
9290020451 (546937), 9290020452 (546945),
9290020453 (546950), 9290022382 (551887),
9290022383 (551895), 9290019091 (546929),
9290019092 (546937), 9290018537 (546945),
9290018538 (546950)

9290019168 (534602),
9290019169 (534610),
9290019196 (534628),
9290019197 (534636),
9290019208

9290019168 (534602),
9290019169 (534610),
9290019196 (534628),
9290019197 (534636),
9290019208

Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06																					
Leviton	SureSlide	6613		1-10			1-9			1-15		1-8*			1-8*			1-5			1-5		
Leviton	SureSlide	6615P		1-5			2-5	1	1-8			1-5*			1-4				1-2		1-2		
Leviton	SureSlide	6631																					
Leviton	SureSlide	6633		1-10			1-9			1-15		1-8*			1-8*			1-5			1-5		
Leviton	SureSlide	6672	1-10			1-9			1-15			1-8*			1-8*				1-5		1-5		
Leviton	SureSlide	6674					1-9			1-15		1-8*						1-5			1-5		
Leviton	Trimatron	6602	1-10			1-9			2, 5-15	1, 3		1-8*			1-8*			3	1-2, 5		3	1-2, 5	
Leviton	Trimatron	6681		1-10		1-9				1-15		1-8*			1-8*			1-5			1-5		
Leviton	IllumaTech	IPI06	1-10			1-9				1-15		1-8*				1-8*		1-5			1-5		
Leviton	IllumaTech	IPL06																					
Leviton	IllumaTech	IPM10					1-12		1-2, 8-15	3-5		1-8*						1-6			1-6		
Philips	Sunrise	SRI000VA120		1-10			1-12					1-8*			1-8*								
Philips	Sunrise	SRI50LED120		1-10			1-9					1-8*			1-8*								
WattStopper	Micro Decorator	DCD267-W		1-10			1-9			1-15		1-8*			1-8*			1-5			1-5		
Lutron	Diva	DVCL-153PD																					
Lutron	Diva	DVCL-153P v2 ²						X				1-8*					X						
Lutron	Diva	DVCL-153P v2.1						X															
Lutron	Diva	DVCL-153P v2.2			X				2-3, 10-15	1, 5-8								2, 5	1, 3		2, 5	1, 3	
Lutron	Diva	DVCL-153P v3.0			X					1-3, 8-15								1-5			1-5		
Lutron	Diva	DVPDC-203																					
Lutron	Diva	DV-600P		1-10			1-9		1-15			1-8*			1-8*			1-5			1-5		
Lutron	DIVA	DVELV-300P	1-5			1-5			1-8			1-5*				1-4		1-2			1-2		
Lutron	Maestro	MACL-153M v2 ²		1-10				X	1-15			1-8*				1-8*		1-5			1-5		
Lutron	Maestro	MRF2-6ND-120		1-5	X			X		1-15		1-8*			1-8*			1-5			1-5		
Lutron	Nova	NLV1000 ²	1-10			1-10			2-15	1		1-8*			1-8*			1-6			1-6		
Lutron	Grafik Eye	QSGR-3P ²		1-2	X			X		1-15		1-8*			1-8*			1-10			1-10		
Lutron	RADIO RA	RRD-6NA ²		1-10			1-9			1-15		1-8*						1-5			1-5		
Lutron	Skylark	S-600P	1-8																				
Lutron	Skylark	SLV-600P				1-7			1-13			1-8*			1-5*			1-3			1-3		
Lutron	Caseta	PD-6WCL (SD11)		1-10				X		1-15		1-8*				1-8*		1-5			1-5		
Lutron	Maestro	MSCL-OP153MH		1-5	X			X	1-15			1-8*			1-8*			1-5			1-5		
Lutron	Maestro	MS-OPS2H	1-10			1-9			1-15			1-8*			1-8*			1-5			1-5		
Leviton	Decora	IPS02	1-10			1-9			1-15			1-8*			1-8*			1-5			1-5		
Leviton	Decora	IPS05																					
Leviton	Decora	IPS06																					
Leviton	Decora	IPS15	1-10			1-9			1-15			1-8*			1-8*			1-5			1-5		
Lutron	Panel Module	GP (Harrier) Card		1-10			1-10			1-15					1-8*			1-10			1-10		
Lutron	Panel Module	HW/LP-RPM-4U-120	1-10			1-10				1-15								1-10			1-10		

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps

Number of bulbs

















4.5W PAR16-GU10 WG

9290011565 (457267),
9290011565 (457648),
9290011565 (457655)

4.5W PAR16-GU10

9290011288 (454363),
9290011288 (454405),
9290011288 (454389),
9290011288 (455378),
9290011288 (458034)

7W PAR16-GU10

929001172505 (457663)

7W PAR16L ES

929001318126 (475434)

7W PAR16L ES (Prof)

929001318126 (475434)

7W PAR16S/PAR16L 500lm

929001245403 (464981),
929001245605 (464999),
929001245705 (465005),
929001245635 (465021),
929001245735 (465039)

6W PAR20 AF

9290011448 (458927),
9290011448 (458919),
9290011452 (456111),
9290011451 (456103),
9290011450 (456095),
9290011449 (458893),
458885, 458901, 458959),
9290011449 (456087),
9290011448 (456079),
9290011447 (456061),
9290011446(456053),
9290011445(456046),
9290011487(456269)

6W PAR20

929001225403 (463620),
929001225004 (463646),
929001225104 (463653),
929001225204 (463661),
929001225304 (463679),
929001225404 (463687),
929001225504 (463695),
929001225904 (463703),
929001226004 (463711),
929001224704(463729)

Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06																								
Leviton	SureSlide	6613	1-20*			1-15					X	1-15					X		1-20		1-20					X
Leviton	SureSlide	6615P	1-20*				1-12				X		1-10			1-10		1-10		1-10				1-15		
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633	1-20*			1-8		9-15		2-16		1-15					X		1-20		1-20			1-15		
Leviton	SureSlide	6672	1-20*			1-15				2-16		1-15				1-15		1-20			1-20				1-15	
Leviton	SureSlide	6674	1-20*			1-15				2-13	14-20								X		1-20				1-15	
Leviton	Trimatron	6602	1-20*				1-15				X	1-15			1-15				1-20		1-20				1-15	
Leviton	Trimatron	6681	1-20*					X			X	1-15					X		1-20		1-20				1-15	
Leviton	IllumaTech	IPI06	1-20*			1-15					X		1-15			1-15			1-20		1-20			1-15		
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10					2-15	1		2-20			2-15	X		2-15	X		1-20				X			X
Philips	Sunrise	SRI000VA120		1-20*				2-15	1		2-20								1-20				X			X
Philips	Sunrise	SRI50LED120	1-20*			1-15				2-13	14-20	1-15			8	1/5/10-15	X		X	1-20					1-15	
WattStopper	Micro Decorator	DCD267-W	1-20*				2-15	1		2-16		2-15		X			X		X	1-20				1-15		
Lutron	Diva	DVCL-153PD																								X
Lutron	Diva	DVCL-153P v2 ²			X				X		2-8	9-20								X			X			
Lutron	Diva	DVCL-153P v2.1																	X						1-15	
Lutron	Diva	DVCL-153P v2.2										1-2/5-15		X			X									
Lutron	Diva	DVCL-153P v3.0										8	2-5	X			X									
Lutron	Diva	DVPDC-203								2-20																
Lutron	Diva	DV-600P	1-20*			1-15				2-16		1-15			8	10-15	X		1-20		1-20				1-15	
Lutron	DIVA	DVELV-300P	1-20*			1-12			1-8			1-10				1-10		1-10			1-10					X
Lutron	Maestro	MACL-153M v2 ²			X			X		2-20		1-15			1-15		X		X		X	1-20			1-15	
Lutron	Maestro	MRF2-6ND-120			X		1-15			2-16		1-15					X		X		X		X		1-15	
Lutron	Nova	NLV1000 ²	1-20*				1-15				X	1-15					X		1-20		1-20*			1-15		
Lutron	Grafik Eye	QSGR-3P ²	1-20*					X		2-20				X			X		X		X	1-20*		1-15		
Lutron	RADIO RA	RRD-6NA ²	1-20*			1-15				2-16							X		X		X	1-20			1-15	
Lutron	Skylark	S-600P										1-15														
Lutron	Skylark	SLV-600P	1-20*			1-15				2-12		1-15				1-15		1-16			1-20					X
Lutron	Caseta	PD-6WCL (SD11)		1-20*			1-11			2-16		1-15					X						X		1-15	
Lutron	Maestro	MSCL-OP153MH		1-20*			1-15			2-20			1-15			1-15		X		X	1-20				1-15	
Lutron	Maestro	MS-OPS2H	1-20*			1-15			2-20			1-15			1-15			1-20			1-20*			1-15		
Leviton	Decora	IPS02	1-20*			1-15			2-20			1-15			1-15			1-20			1-20*			1-15		
Leviton	Decora	IPS05																								
Leviton	Decora	IPS06																								
Leviton	Decora	IPS15	1-20*			1-15			2-20			1-15			1-15			1-20			1-20*			1-15		
Lutron	Panel Module	GP (Harrier) Card	1-20*							2-20		1-15					X			X	1-20*					
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20*							2-20		1-15					X			X	1-20*					

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

PAR lamps

Number of bulbs



6W(50W Eq) PAR20 SO

929001224704 (463729),
 929001225004 (463646),
 929001225104 (463653),
 929001225204 (463661),
 929001225304 (463679),
 929001225305 (463604),
 929001225335 (463844),
 929001225403 (463620),
 929001225404 (463687),
 929001225405 (463612),
 929001225435 (463851),
 929001225465 (463794),
 929001225504 (463695),
 929001225605 (463638),
 929001225635 (463869),
 929001225904 (463703),
 929001226004 (463711),



12W PAR30S AF SO/
Expert color

929001286204 (471094),
 929001286104 (471086),
 929001286004 (471078),
 929001285904 (471060),
 929001112304 (435271),
 929001112204 (435263),
 929001112904 (435339),
 929001112804 (435321),
 929001112604 (435305),
 929001112504 (435297),
 929001340204 (4708989),
 929001340304 (470906),
 929001340404 (470914),
 929001340604 (470922),
 929001340704 (470930),
 929001340804 (470948),
 929001369704 (471789)



8W PAR30L

9290012391 (463737),
 9290012391 (463752)



10.5W PAR30L AF

9290011114 (452656),
 9290011114 (452623),
 9290011114 (434992),
 9290011113 (452615),
 9290011113 (434984)



12.5W PAR30L SO AF

9290011327 (454702),
 9290011326 (454694),
 9290011325 (454686),
 9290011324 (454678),
 9290011323 (454660)



12W PAR38 SO

9290011834 (460063),
 9290011834 (460055),
 9290011834 (460105),
 9290011834 (460071),
 9290011835 (460121),
 9290011835 (460089),
 9290011835 (461046),
 9290011835 (460097),



13W PAR38 SO

9290011322 (454751),
 9290011321 (454744),
 9290011320 (454736),
 9290011319 (454728)



15W PAR38

92900111104 (453431)

Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06																								
Leviton	SureSlide	6613			X	1-8*				1-15		2-7*		1	1-8*				X	1-8*				1-8*		
Leviton	SureSlide	6615P	1-15				1-4			1-8			1-6*		1-5*			1-7				1-5*			1-4*	
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633	1-15			1-8*				1-15						1-8*			X	1-8*				1-8*		
Leviton	SureSlide	6672		1-15			1-8*			1-15						1-8*			1-14			1-8*			1-8*	
Leviton	SureSlide	6674		1-15		1-8*				1-15		1-7*				1-8*						1-8*			1-8*	
Leviton	Trimatron	6602		1-15			1-12			1-15						1-8*			1-14			1-8*			1-8*	
Leviton	Trimatron	6681		1-15		1-12				1-15		1-7*				1-8*				X	1-8*			1-8*		
Leviton	IllumaTech	IPIO6	1-15				1-8*			1-15			1-7*			1-8*			1-14			1-8*			1-8*	
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10			X					1-15						1-8*			1-15			1-8*			1-8*	
Philips	Sunrise	SR1000VAI20			X	1-8*				1-15						1-8*						1-8*			1-8*	
Philips	Sunrise	SR150LEDI20		1-15		1-8*				1-15		1-7*				1-8*				X	1-8*			1-8*		
WattStopper	Micro Decorator	DCD267-W	1-15			1-2	3-12			2-15	1	1-7*				1-8*				X	1-8*			1-8*		
Lutron	Diva	DVCL-153PD																								
Lutron	Diva	DVCL-153P v2 ²			X			X		1-15				X	1-8*				X			1-8*				X
Lutron	Diva	DVCL-153P v2.1		1-15						1-15																
Lutron	Diva	DVCL-153P v2.2																								
Lutron	Diva	DVCL-153P v3.0																								
Lutron	Diva	DVPCD-203		1-15																						
Lutron	Diva	DV-600P		1-15		1-12				1-15		1-7*				1-8*			1-14			1-8*			1-8*	
Lutron	DIVA	DVELV-300P			X	1-4				1-8		1-6*				1-5*			1-7			1-5*			1-4*	
Lutron	Maestro	MACL-153M v2 ²		1-15			1-12			1-15		1-7*				1-8*				X		1-8*			1-8*	
Lutron	Maestro	MRF2-6ND-120		1-15		1-8*				1-15		1-7*				1-8*				X	1-8*			1-8*		
Lutron	Nova	NLV1000 ²	1-15			1-8*				1-15		1-7*				1-8*			1-15			1-8*			1-8*	
Lutron	Grafik Eye	QSGR-3P ²	1-15					X		1-5	6-15	1-7*				1-8*				X			X	1-8*		
Lutron	RADIO RA	RRD-6NA ²		1-15		1-8*				1-15		1-7*				1-8*				X	1-8*			1-8		
Lutron	Skylark	S-600P																								
Lutron	Skylark	SLV-600P			X	1-8*				1-10		1-7*				1-8*			1-10				X	1-8*		
Lutron	Caseta	PD-6WCL (SD11)		1-15			1-12			1-15						1-8*				X		1-8*				
Lutron	Maestro	MSCL-OP153MH		1-15		1-8*				1-15						1-8*				X		1-8*				
Lutron	Maestro	MS-OPS2H	1-15			1-8*				1-15						1-8*			1-15			1-4*				
Leviton	Decora	IPS02	1-15			1-8*				1-15						1-8*			1-15			1-8*				
Leviton	Decora	IPS05																								
Leviton	Decora	IPS06																								
Leviton	Decora	IPS15	1-15			1-8*				1-15						1-8*			1-15			1-8*				
Lutron	Panel Module	GP (Harrier) Card								1-15									1-15							
Lutron	Panel Module	HW/LP-RPM-4U-120								1-15									1-15							

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

BR lamps

Number of bulbs

																										
			13.3BR40/PER/ 927-930-940-950/P/E26/ DIM 6/1CT T20			13.3BR40/PER/927-22/P/ E26/WG 6/1CT T20			P0027894 BR30 T20			P0027894 BR40 T20			P0028208 BR20 T20			P0025038 BR40			BR40, P0025038, 2019Q2			BR30, P0025038, 2019Q2		
			9290034772 (577858) 9290034773 (577866) 9290034774 (577874) 9290034775 (577882)			9290034771 (577841)			9290023514 (558023), 9290023513 (558031)			9290023512 (558049), 9290023515 (558056)			9290020922 (553883)			9290020924 (553909)			9290020355 (547422), 9290020356 (547430), 9290022042 (548115)			9290020321 (545905), 9290020322 (545913), 9290020923 (553891), 9290022041 (457093)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	R1061-VW-K2							1-20			1-16			1-20									1-20		
Leviton	Decora Slide	DSL06																								
Leviton	SureSlide	6613																1-18					1-18			
Leviton	SureSlide	6615P	1-6			1-6			1-6			1-4					1-16	1-9					1-9			1-11
Leviton	SureSlide	6631	1-10			1-10			1-12			1-8			1-20									1-20		
Leviton	SureSlide	6633	1-10			1-10			1-12			1-8			1-20								1-18		1-20	
Leviton	SureSlide	6672	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Leviton	SureSlide	6674	1-10			1-10			1-12			1-8			1-20										1-20	
Leviton	Trimatron	6602	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Leviton	IllumaTech	IPE04-1LZ																								
Leviton	IllumaTech	IPI06	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Leviton	IllumaTech	IPL06	1-10			1-10			1-12			1-8			1-20										1-20	
Leviton	IllumaTech	IPM10																				1-20		1-20		
Philips	Sunrise	SR1000VA120																								
Philips	Sunrise	SR150LED120							1-12			1-8			1-20							1-18		1-18		1-20
Lightolier	Vega	V600VAU																								
Lightolier	Vega	V1000VAU																								
Lightolier	Sunrise	ZP600VA ²																								
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W							1-12			1-8			1-20							1-18				1-20
WattStopper	Architectural	ADMLV-703-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD																								
Lutron	Diva	DVCL-153P v2 ²																								
Lutron	Diva	DVCL-153P v3.03	1-10			1-10			1-12			1-8			1-20										1-20	
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Lutron	DIVA	DVELV-300P							1-6			1-4			1-16							1-9		1-9		1-11
Lutron	Maestro	MACL-153M v2 ²							1-12			1-8			1-20							1-18		1-18		1*-20
Lutron	Maestro	MACL-153M v2.2	1-10			1-10																				
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²	1-10			1-10			1-15			1-11			1-20							1-20		1-20		1-20
Lutron	Nova	NTELV-300																								
Lutron	Grafik Eye	QSGR-3P ²							1-20			1-20			1-20							1-20		1-20		1-20
Lutron	RADIO RA	RRD-6NA ²																								
Lutron	Skylark	SLV-600P	1-9			1-9			1-9			1-6			1-17							1-13		1-13		1-17
Lutron	Skylark	SCL153P v2 ²																								
Lutron	Caseta	PD-6WCL (SD11)	1-10			1-10			1-12			1-8			1-20							1-18		1-18		1-20
Sensors																										
Lutron	Maestro	MSCL-OP153MH							1-12			1-8			1-20										1-20	
Lutron	Maestro	MS-OPS2H																								
Leviton	Decora	IPS02	1-10			1-10			1-12			1-8			1-20										1-20	
Leviton	Decora	IPS05							1-12			1-8			1-20										1-20	
Leviton	Decora	IPS06	1-10			1-10			1-12			1-8			1-20										1-20	
Leviton	Decora	IPS15	1-10			1-10			1-20			1-20			1-20										1-20	
Panel Modules																										
Lutron	Panel Module	GP (Harrier) Card																								
Lutron	Panel Module	HW/LP-RPM-4U-120																								

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

BR lamps Number of bulbs																										
			BR20, P0025038, 2019Q2			8.8w BR40 WG & CG, P0020365, 2018Q4			7.2w BR30 WG & CG, P0020365, 2018Q4			5w BR20 WG & CG, P0020365, 2018Q4			6W(50W Eq) BR20 WG			8W BR20 AF			9W BR30			9W (65W Eq) BR30 WG		
			9290020353 (547406), 9290020354 (547414), 9290022040 (548123)			9290020091 (457010), 9290020092			9290018703 (457044), 9790020069			9290020089 (456979), 9290020090			9290011557 (456979), 9290011557 (456995), 9290011557 (456987)			9290002192 (420331), 9290002192 (423400), 9290002192 (428813)			92900119449 (464180), 929001213763 (461855)			9290011555 (465996), 9290011555 (457044), 9290011555 (457051), 9290011555 (457036), 9290011555 (457077), 9290011555 (457069)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora Slide	DSL06																								
Leviton	SureSlide	6613	1-20			1-18			1-20			1-20			1-25			1-18						1-16		
Leviton	SureSlide	6615P	1-16			1-9			1-13			1-16			1-12			1-9					1-8		1-8	
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633	1-20			1-18			1-20			1-20			1-25							X		1-16		
Leviton	SureSlide	6672	1-20			1-18			1-20			1-20			1-25					1-8				1-16		
Leviton	SureSlide	6674													1-25		1-14		>14			1-8		1-16		
Leviton	Trimatron	6602	1-20			1-18			1-20			1-20			1-25							X		1-16		
Leviton	IllumaTech	IPE04-1LZ																								
Leviton	IllumaTech	IPI06	1-20			1-18			1-20			1-20			1-25			1-18			1-5	6-8	1-16			
Leviton	IllumaTech	IPL06																								
Leviton	IllumaTech	IPM10	1-20			1-20			1-20			1-20			2-25	1					1-8			1-16		
Philips	Sunrise	SR1000VA120													2-25	1					1-8			1-16		
Philips	Sunrise	SR150LED120	1-20			1-18			1-20			1-20			1-25						1-8			1-16		
Lightolier	Vega	V600VAU															1-18									
Lightolier	Vega	V1000VAU																								
Lightolier	Sunrise	ZP600VA ²															1-18									
Lightolier	Onset	OS600																								
Lightolier	Onset	OS600VA																1-8		>8						
Lightolier	MultiSet	MHP600VA															1-10		>10							
Lightolier	Momentum	MP2000VAI				1-18			1-20																	
WattStopper	Micro Decorator	DCD267-W	1-20			1-18			1-20			1-20			2-25	1	1-18				1-8			1-16		
WattStopper	Architectural	ADMLV-703-W				1-9																				
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD														X						X				X
Lutron	Diva	DVCL-153P v2 ²													1-25		1-18					X		1-16		
Lutron	Diva	DVCL-153P v3.03																								
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P	1-20			1-18			1-20			1-20			1-25		1-8	9-10	>10		1-8			1-16		
Lutron	DIVA	DVELV-300P	1-16			1-9			1-13			1-16			1-12			X		1-8			1-8		1-8	
Lutron	Maestro	MACL-153M v2 ²	1-20			1-18			1-20			1-20			1-25			1-18	1		1-8			1-16		
Lutron	Maestro	MACL-153M v2.2																								
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-6ND-120	1-20			1-18			1-20			1-20			1-25		1-18				1-8			1-16		
Lutron	Nova	NLV600 ²															1-18									
Lutron	Nova	NLV1000 ²	1-20			1-20			1-20			1-20			1-25*		1-18				1-8			1-16*		
Lutron	Nova	NTELV-300																								
Lutron	Grafik Eye	QSGR-3P ²	1-20			1-20			1-20			1-20			1-15	16-25			X		1-8			1-16*		
Lutron	RADIO RA	RRD-6NA ²													1-25		1-18				1-8			1-16		
Lutron	Skylark	SLV-600P	1-20			1-13			1-19			1-20			1-15		1-8	9-18			1-8			1-12		
Lutron	Skylark	SCL153P v2 ²															1-18									
Lutron	Caseta	PD-6WCL (SD11)	1-20			1-18			1-20			1-20			1-15	16-25					1-8			1-16		
Sensors																										
Lutron	Maestro	MSCL-OP153MH													1-15	16-25	1-18				1-8			1-16		
Lutron	Maestro	MS-OPS2H													1-25		1-18				1-8			1-16		
Leviton	Decora	IPS02													1-25						1-8			1-16		
Leviton	Decora	IPS05													1-25						1-8			1-16		
Leviton	Decora	IPS06													1-25						1-8			1-16		
Leviton	Decora	IPS15													1-25						1-8			1-16		
Panel Modules																										
Lutron	Panel Module	GP (Harrier) Card													1-25*									1-16*		
Lutron	Panel Module	HW/LP-RPM-4U-120													1-25*									1-16*		

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

																							
			9W BR30	9.5W (65W Eq) BR30 WG	9.5W (65W Eq) Slim style BR30	13W BR30 AF	13W BR30 AF Dim Tone	9W (65WEq) BR40 WG	12W BR40 AF	14.5W BR40 AF													
			929001174966 (458109), 929001174988 (460352), 929001174989 (465286), 929001174993 (462143), 929001174995 (460345), 929001174997 (464198), 929001174999 (465229),	9290011117 (452243), 9290011117 (452235), 9290011117 (452268), 9290011117 (452284)	9290011118 (452359), 9290011118 (452383), 9290011118 (452391), 9290011118 (452417), 9290011119 (452441), 9290011119 (452466), 9290011119 (452482)	9290002197 (420554), 9290002198 (420281), 9290002197 (423798), 9290002197 (429282)	92900002344 (426445)	9290011558 (457010), 9290011558 (457002), 9290011558 (457028)	92900025803 (451914)	9290002199 (420562), 9290002199 (423756)													
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2												1-11									1-10
Leviton	Decora Slide	DSL06																					
Leviton	SureSlide	6613		1-8		1-12*			1-8*			1-11		1-11			1-16		1-10*			1-10	
Leviton	SureSlide	6615P		1-8		1-7			1-5			1-5		1-5	1		1-8		1-5*				X
Leviton	SureSlide	6631																					
Leviton	SureSlide	6633		1-4	5-8												1-16						
Leviton	SureSlide	6672		1-8					1-8*								1-16						
Leviton	SureSlide	6674		1-8		1-12*			1-8*			1-11		1-4	>4		1-16		1-10*			1-10	
Leviton	Trimatron	6602		1-5	6-8											1-16							
Leviton	IllumaTech	IPE04-1LZ							1-8*			1-11		1-8	1								
Leviton	IllumaTech	IPI06		1-5	6-8	1-6			1-8*			1-11		1-7	>7	1-16			1-10*			1-10	
Leviton	IllumaTech	IPL06																					
Leviton	IllumaTech	IPM10		1-8													1-16						
Philips	Sunrise	SR1000VA120		1-8													1-16						
Philips	Sunrise	SR150LED120		1-8		1-12*			1-8*								1-16		1-10*				
Lightolier	Vega	V600VAU										1-11		1-11	1							1-10	
Lightolier	Vega	V1000VAU										1-16*		1-16*	1								
Lightolier	Sunrise	ZP600VA ²										1-11		1-5	>5							1-10	
Lightolier	Onset	OS600									X					X							
Lightolier	Onset	OS600VA										1-11		1-11								1-10	
Lightolier	MultiSet	MHP600VA										1-11		1-6	>6							1-10	
Lightolier	Momentum	MP2000VAI																					
WattStopper	Micro Decorator	DCD267-W		1-8		1-12*			1-8*			1-11		1-11			1-16		1-10*			1-10	
WattStopper	Architectural	ADMLV-703-W																					
Lutron	Skylark	CTCL-153P										1-11											
Lutron	Diva	DVCL-153PD										1-11		1-11				X					
Lutron	Diva	DVCL-153P v2 ²			X	1-15				X	1-11			1-11			1-16		1-12			1-10	
Lutron	Diva	DVCL-153P v3.03																					
Lutron	Diva	DVPDC-203			X									1-11									
Lutron	Diva	DV-600P		1-8		1-12*			1-8*			1-11		1-5	>5		1-16		1-10*			1-10	
Lutron	DIVA	DVELV-300P	1-8			1-7			1-5			1-5		1-5		1-8			1-5*			1-5	
Lutron	Maestro	MACL-153M v2 ²		1-8		1-12*			1-8*			1-11		1-11			1-16		1-12			1-10	
Lutron	Maestro	MACL-153M v2.2																					
Lutron	Maestro	MAELV-600												1-11									
Lutron	Maestro	MALV-600										1-11											
Lutron	Maestro	MRF2-6ND-120		1-8		1-12*			1-8*			1-11		1-11			1-16		1-10*			1-10	
Lutron	Nova	NLV600 ²										1-11		1-11								1-10	
Lutron	Nova	NLV1000 ²		1-8		1-12*			1-8*			1-16*		1-16*	1		1-16*		1-13*			1-10*	
Lutron	Nova	NTELV-300												1-5									
Lutron	Grafik Eye	QSGR-3P ²		1-8		1-12*				X	1-11*			1-13*	1		1-16*		1-18*			1-10*	
Lutron	RADIO RA	RRD-6NA ²		1-8		1-12*			1-15			1-11		1-11			1-16		1-10*			1-10	
Lutron	Skylark	SLV-600P		1-8		1-7			1-7			1-11		1-11			1-12		1-8*			1-10	
Lutron	Skylark	SCL153P v2 ²										1-11	1	1-11					1-12				
Lutron	Caseta	PD-6WCL (SD11)		1-8		1-15			1-15								1-16		1-12				
Sensors																							
Lutron	Maestro	MSCL-OP153MH		1-8		1-12*			1-8*								1-16		1-12				
Lutron	Maestro	MS-OPS2H	1-6			1-12*			1-8*								1-16		1-12*				
Leviton	Decora	IPS02	1-8			1-12*			1-8*								1-16		1-12*				
Leviton	Decora	IPS05	1-8			1-12*			1-8*								1-16		1-12*				
Leviton	Decora	IPS06	1-8			1-12*			1-8*								1-16		1-12*				
Leviton	Decora	IPS15	1-8			1-12*			1-8*								1-16		1-12*				
Panel Modules																							
Lutron	Panel Module	GP (Harrier) Card				1-27			1-26								1-16*		1-18				
Lutron	Panel Module	HW/LP-RPM-4U-120				1 - 38			1 - 38								1-16*		1-25				

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

Candles

Number of bulbs

																							
			5.5B11/PER/927-922/CL/G/ E26/WGX 1FB T20	6.6BA11/PER/950/CL/G/ E26/DIM 1FB T20 / P0025721-B	6.6BA11/PER/950/CL/G/ E12/DIM 1FB T20 / P0025721-B	6.6BA11/PER/950/CL/G/ E12/DIM 1FB T20 / P0025721-B	3G16.5/MOD/840/ E12/CL/GL/DIM 4/BC	3BA11/MOD/840/ E12/CL/GL/DIM 8/1BC	929002990804 (575167), 929003082404 (575183), 929003082504 (575191), 929003094904 (575175)	6.6BA11 WG E12/E26 T20													
			9290022046 (549345)	9290022045 (549337)	9290022958 (557488)	9290022959 (557496)	9290020014 (543157)	9290020012 (543173)		9290022956 (557462), 9290022957 (557470)													
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	R1061-VW-K2																					
Leviton	Decora	6161																					
Leviton	SureSlide	6613							1-10			1-10			1.3-15		X	1.3-15					
Leviton	SureSlide	6615P			1-10			1-10		1-5	2-20		1-5	2-20	1-15			1-15				1-10	
Leviton	SureSlide	6631	1-10			1-10									2-15	1		2-15	1		1-10		1-23
Leviton	SureSlide	6633	2-10			2-10									2-15			2-15			1-10		1-23
Leviton	SureSlide	6672	1-10			1-10									1-15			1-15			1-10		1-23
Leviton	SureSlide	6674	1-10			1-10									1-15			1-15			1-10		1-23
Leviton	Trimatron	6602	1-10			1-10									3-15	2	X	3-15	2	X			
Leviton	Trimatron	6681	1-10			1-10			1-10			1-10			3-15		X	3-15		X	1-10		1-23
Leviton	Trimatron	6683																					
Leviton	IllumaTech	IPE04-1LZ																					
Leviton	IllumaTech	IPI06	2-10			2-10									1-15			1-15			1-10		1-23
Leviton	IllumaTech	IPL06	1-10			1-10															1-10		1-23
Leviton	Decora Slide	DSL06	1-10			1-10															1-10		1-30
Leviton	IllumaTech	IPM10													2-15		X	2-15		X			
Leviton	Monet	MNI06-1																					
Philips	Sunrise	SR1000VA120																					
Philips	Sunrise	SR150LED120	1-10			1-10															1-10		1-23
Lightolier	Vega	V600VAU																					
Lightolier	Sunrise	ZP600VA																					
Lightolier	Sunrise	ZP600																					
Lightolier	Vega	V600																					
Lightolier	Onset	OS600VA																					
Lightolier	Onset	OS1000VA																					
Lightolier	Astral Slider	A600																					
Lightolier	Astral Slider	AP600																					
Lightolier	MultiSet	MHP600VA																					
Lightolier	Momentum	MP2000VAI																					
WattStopper	Micro Decorator	DCD267-W	1-10			1-10									1-15			1-15					
WattStopper	Paddle	PDMLV-703-W																					
WattStopper	Slide	SDMLV-603-W																					
WattStopper	Slide	SD-603-W																					
Lutron	Skylark	CTCL-153P																					
Lutron	Diva	DVCL-153PD																					
Lutron	Diva	DVCL-153P v2 ²																					
Lutron	Diva	DVCL-153P v3.3																			1-10		1-23
Lutron	Diva	DVPDC-203																					
Lutron	Diva	DV-600P	1-10			1-10									1-15			1-15					
Lutron	Diva	DV-603PG																					
Lutron	DIVA	DVELV-300P	1-10			1-10			1-10			1-10			1-15			1-15					1-11
Lutron	Glyder	GL-600P																					

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

Number of bulbs

[illegible]

Candles

Number of bulbs

																										
			2.5-8w Dimmable Candle and Vintage			2.5W (25W Eq) DS			3W			3.5W Filament			3.5W DW			3.5W (25W Eq) WG DS			4W (40W Eq) WG			4.5W (40W Eq) 2700K		
			9290013148 (470757), 9290013149 (470765), 9290013150 (470773), 9290013151 (470781), 9290018423 (478677), 9290018424 (478685), 9290018425 (478693), 9290018426 (478701), 9290018427 (478719), 9290018428 (478727), 9290018429 (478735), 9290018430 (478743), 9290018431 (478750), 9290018432 (478768), 9290018433 (478776), 9290018435 (478891), 9290018436 (478909), 9290018437 (478917), 9290018438 (478925), 9290012687 (466524), 9290012096 (461111), 9290013355 (475822), 9290013357 (475848), 9290013356 (475830)			92900002799 (435149), 9290011151 (451831)+G8-X-9J8-X9			410209, 410217, 420414, 420422, 420430, 426916, 427237			9290012103 (461681)			92900002417 (427799), 92900002419 (427815), 92900002418 (427781), 92900002420 (427807), 92900002417 (427765), 92900002419 (427773),			9290011668 (457242), 9290011668 (457234), 9290011668 (457226)			469676			9290012137 (461855), 9290012137 (461863), 9290012137 (461871), 9290012137 (461889), 9290012137 (461897), 9290012137 (461905), 9290012138 (461913), 9290012138 (461921), 9290012138 (461939), 9290012138 (461947), 9290012138 (461953), 9290012138 (462358),		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2												X												
Leviton	Decora	6161												X												
Leviton	SureSlide	6613	1-2,4-20			X	1-7*1					X	1-33		1-35			1-35			1-2,4-20	X		2-30		
Leviton	SureSlide	6615P	1-20					X				X	1-17		1-17			1-17			1-20			2-16		
Leviton	SureSlide	6631										X														
Leviton	SureSlide	6633	2-20			X	1-7*1					1-33					1-25			2-20	X		2-30			
Leviton	SureSlide	6672		1-20			1-7*1					1-33					1-35			1-20			2-30			
Leviton	SureSlide	6674					1-7*1		1-6	7-10	>10	1-10	11-33		1-10 1	>10	1-20						2-30			
Leviton	Trimatron	6602	1,3-20			X						1-33					1-15*			1,3-20	X		2-30			
Leviton	Trimatron	6681	1,3-20	2				X				1-33				X	1-25			1,3-20	2		2-30			
Leviton	Trimatron	6683										X														
Leviton	IllumaTech	IPE04-1LZ									1-12															
Leviton	IllumaTech	IPI06	1-2,4-20			X		X				X	1-33			X	1-35			1-2,4-20	X		2-30			
Leviton	IllumaTech	IPL06																								
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPM10					1-7*1							2-33	1			2-25	1					2-30		
Leviton	Monet	MNI06-1										X														
Philips	Sunrise	SR1000VAI20	1-20				1-7*1							2-33	1			2-25*	1		1-20			2-30		
Philips	Sunrise	SR150LED120	1-20				1-7*1							1-10	11-33			1-20			1-20			2-30		
Lightolier	Vega	V600VAU							1-2	3-12							X									
Lightolier	Sunrise	ZP600VA										X					2-42 1	1								
Lightolier	Sunrise	ZP600										X														
Lightolier	Vega	V600										X														
Lightolier	Onset	OS600VA										1-4	>4				1-8 1	>8								
Lightolier	Onset	OS1000VA										1-4	>4													
Lightolier	Astral Slider	A600										X														
Lightolier	Astral Slider	AP600										X														
Lightolier	MultiSet	MHP600VA									1-12							X								
Lightolier	Momentum	MP2000VAI									1-16															
WattStopper	Micro Decorator	DCD267-W	1-20				1-7*1							1-33			X	1-25			1-20			2-30		
WattStopper	Paddle	PDMLV-703-W															X									
WattStopper	Slide	SDMLV-603-W															X									
WattStopper	Slide	SD-603-W									1-12															
Lutron	Skylark	CTCL-153P															X									
Lutron	Diva	DVCL-153PD	1-20														X									
Lutron	Diva	DVCL-153P v2.2	1-20				1-7*1				1-12			X		1-42 1			X		1-20			2-30		X
Lutron	Diva	DVCL-153P v3.3																			1-20					
Lutron	Diva	DVPDC-203										X		1-8	9-33											
Lutron	Diva	DV-600P	1-20				1-7*1		1-8			X	1-33				X	1-15*			1-20			2-30		
Lutron	Diva	DV-603PG										X														
Lutron	DIVA	DVELV-300P	1-20				1-7*1			1-2	>2	1-17			10-21	1-10		1-17			1-20			2-16		
Lutron	Glyder	GL-600P										X														
Lutron	Maestro	MACL-153M v2.2	1-20				1-7*1				1-12			1-33			1-42 1		1-35		1-20			2-30		
Lutron	Maestro	MAELV-600									1-12															
Lutron	Maestro	MALV-600										X														
Lutron	Maestro	MRF2-600M									1-12															
Lutron	Maestro	MRF2-6ND-120	1-10	15-20			1-7*1					X	1-33			1-42 1		1-35		1-10	15-20			2-30		
Lutron	Nova	NLV600.2																								
Lutron	Nova	NLV1000.2	1-20				1-7*1				1-20			1-33			1-47* 1		1-47		1-20			2-30		
Lutron	Grafik Eye	QSGR-3P.2	1-20				1-7*1				1-30			1-10	11-33		X	1-50			1-20					X
Lutron	Qoto	Q-600P										X														
Lutron	RADIO RA	RRD-6NA.2	1-20				1-7*1		1-12			X	1-15	16-33		1-42		1-35			1-20			2-30		
Lutron	Skylark	S-600P										X														
Lutron	Skylark	SELV-300P									1-12															
Lutron	Skylark	SLV-600P	1-20				1-7*1			1-12				1-25			X	1-15	16-26		1-20			2-30		
Lutron	Skylark	SCL153P v2.2															4-42 1	1-4								
Lutron	Toggle	TG-600P										X														
Lutron	Power Module	PHPM-WBX									1-30															
Lutron	Caseta	PD-6WCL (SD11)	3-20				X	1-7*1						X				1-35			3-20		X	2-30		
Sensors																										
Lutron	Maestro	MSCL-OP153MH		1-20										1-33				2-45	1		1-20			2-30		2-30
Lutron	Maestro	MS-OPS2H	1-20											1-33				1-45	</							

1. Audible noise may be observed when used with this

Candles

Number of bulbs

																										
			9290012130 (463901), 9290012130 (463919), 9290012130 (463943),			9290002797 (435172), 9290002889 (435156), 9290002798 (435164)			9290011673 (457200), 9290011673 (457192), 9290011673 (457184), 9290011674 (457150), 9290011674 (457143), 9290011672 (457176), 9290011672 (457168), 9290011671 (457218), 9290011670 (457135), 9290011670 (457127), 9290011670 (457119),			9290012103 (461681)			9290012687 (465567), 9290012687 (465583), 9290012740 (466235)			9290012127 (461822), 9290012127 (461848)			9290002886 (435180), 9290011121 (452813)			9290011820 (458695), 9290011821 (458661), 9290011822 (458638), 9290011820 (458687), 9290011821 (458653), 9290011822 (458620), 9290011820 (459321), 9290011820 (458703), 9290011821 (458679)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Cooper	REACT	RI061-VW-K2																								
Leviton	Decora	6161																								
Leviton	SureSlide	6613		2-30				X		1-26				1-33		1-33				1-25		1-10*			1-21	
Leviton	SureSlide	6615P		2-16				X		1-13				1-17		1-17				1-12			X			1-11
Leviton	SureSlide	6631																								
Leviton	SureSlide	6633		2-30				1-10*1		1-26				1-33		1-33				1-25		1-10*				1-21
Leviton	SureSlide	6672		2-30				1-10*1		1-26				1-33		1-33				1-25		1-10*				1-21
Leviton	SureSlide	6674		2-30				1-10*		1-10*				1-10	11-33	1-10	11-33			1-25		1-10*				1-21
Leviton	Trimatron	6602		2-30				X		1-26				1-33		1-33				1-25			X			1-21
Leviton	Trimatron	6681		2-30				X		1-26				1-33		1-33				1-25			X			1-21
Leviton	Trimatron	6683																								
Leviton	IllumaTech	IPE04-1LZ																								
Leviton	IllumaTech	IPI06	2-30					X		1-26				1-33		1-33				1-25			X			1-21
Leviton	IllumaTech	IPL06																								
Leviton	Decora Slide	DSL06																								
Leviton	IllumaTech	IPM10		2-30				1-10*1		2-32				1	2-33	1	2-33	1		1-25		1-10*				1-25
Leviton	Monet	MNI06-1																								
Philips	Sunrise	SR1000VA120		2-30				1-10*		2-32				1	2-33	1	2-33	1		1-25		1-10*				1-25
Philips	Sunrise	SR150LED120		2-30				1-10*		1-10*				1-10	11-33		1-10	11-33		1-25		1-10*				1-21
Lightolier	Vega	V600VAU																								
Lightolier	Sunrise	ZP600VA																								
Lightolier	Sunrise	ZP600																								
Lightolier	Vega	V600																								
Lightolier	Onset	OS600VA																								
Lightolier	Onset	OS1000VA																								
Lightolier	Astral Slider	A600																								
Lightolier	Astral Slider	AP600																								
Lightolier	MultiSet	MHP600VA																								
Lightolier	Momentum	MP2000VAI																								
WattStopper	Micro Decorator	DCD267-W		2-30				1-10*						1-33		1-33			1-25			1-10*				1-21
WattStopper	Paddle	PDMLV-703-W																								
WattStopper	Slide	SDMLV-603-W																								
WattStopper	Slide	SD-603-W																								
Lutron	Skylark	CTCL-153P																								
Lutron	Diva	DVCL-153PD			X									X	9-33											X
Lutron	Diva	DVCL-153P v2.2		2-30				X					X						X				X			1-10
Lutron	Diva	DVCL-153P v3.3																								11-21
Lutron	Diva	DVPDC-203																								
Lutron	Diva	DV-600P		2-30				X		1-26				1-33		1-33			1-8	9-33	1-25		1-10*			1-21
Lutron	Diva	DV-603PG																								
Lutron	DIVA	DVELY-300P		2-16				X		1-13				1-17		1-17				1-12			X			1-11
Lutron	Glyder	GL-600P																								
Lutron	Maestro	MACL-153M v2.2		2-30				1-10*		1-26				1-33		1-33				1-25			1-10*			1-21
Lutron	Maestro	MAELV-600																								
Lutron	Maestro	MALV-600																								
Lutron	Maestro	MRF2-600M																								
Lutron	Maestro	MRF2-6ND-120		2-30				1-10*		1-26				1-33		1-33				1-25		1-10*1				1-21
Lutron	Nova	NLV600 ²																								
Lutron	Nova	NLV1000 ²		2-30				1-10*1		1-35				1-33		1-33			1-10	11-33	1-25		1-10*1		1-23*	1-25*
Lutron	Grafik Eye	QSGR-3P ²			X			1-10*		1-50				1-10	11-33		1-10	11-33		1-25		1-10*				1-25*
Lutron	Qoto	Q-600P																								
Lutron	RADIO RA	RRD-6NA ²		2-30				1-10*					X	1-15	16-33		1-15	16-33		1-25			1-10*			1-25
Lutron	Skylark	S-600P																								
Lutron	Skylark	SELV-300P																								
Lutron	Skylark	SLV-600P		2-30				1-10*		1-19*				1-25		1-25				1-25		1-10*				1-16
Lutron	Skylark	SCL153P v2.2																								
Lutron	Toggler	TG-600P																								
Lutron	Power Module	PHPM-WBX																								
Lutron	Caseta	PD-6WCL (SD11)			X			1-10*					X			X			X		1-25		1-10*			X
Sensors																										
Lutron	Maestro	MSCL-OP153MH			X									1-33		1-33		1-33		1-25						X
Lutron	Maestro	MS-OPS2H		2-30						1-33				1-33		1-33				1-25					1-21	
Leviton	Decora	IPS02		2-30						1-33				1-33		1-33				1-25					1-21	
Leviton	Decora	IPS05																								
Leviton	Decora	IPS06																								
Leviton	Decora	IPS15		2-30						1-26				1-33		1-33				1-25						1-21
Panel Modules																										
Lutron	Panel Module	GP (Harrier) Card		2-30				TBD		1-40*				1-33		1-33				1-25		1-10*				1-25*
Lutron	Panel Module	HW/LP-RPM-4U-120		2-30				TBD		1-45*				1-33		1-33				1-25		1-10*				1-25*

Misc (G25,ST19)

Number of bulbs

																										
			9290019368 (536318)			9290019366 (536292)			9290019367 (536300)			9290020009 (543132)			9290020010 (543140)			9290020008 (543124)			9290022960 (556530), 9290022961 (556548), 9290023277 (557587)			9290019363 (536268), 9290019364 (536276), 9290019365 (536284)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06																			1-30			1-20		
Leviton	SureSlide	6613	1-3			1-3			1-3			1.3-15		X	1.3-15		X	1.3-15		X						
Leviton	SureSlide	6615P		1-3			1-3			1-3		1-15			1-15			1-15								
Leviton	SureSlide	6631																			1-18			1-20		
Leviton	SureSlide	6633	1, 3	2		1, 3	2		1, 3	2		2-15	1		2-15	1		2-15	1		1-18			1-20		
Leviton	SureSlide	6672	1-3			1-3			1-3			1-15			1-15			1-15			1-18			1-20		
Leviton	SureSlide	6674	1-3			1-3			1-3			1-15			1-15			1-15			1-18			1-20		
Leviton	Trimatron	6602	1-3			1-3			1-3			3-15	2	X	3-15	2	X	3-15	2	X						
Leviton	Trimatron	6681	1-3			1-3			1-3			3-15		X	3-15		X	3-15		X	1-18			1-20		
Leviton	IllumaTech	IPI06	1-3			1-3			1-3			1-15			1-15			1-15			1-18			2-20		
Leviton	IllumaTech	IPL06																			1-18			1-20		
Leviton	IllumaTech	IPM10	2-3		X	2-3		X	2-3		X	2-15		X	2-15		X	2-15		X						
Philips	Sunrise	SR1000VA120																								
Philips	Sunrise	SR150LED120																			1-20			1-20		
WattStopper	Micro Decorator	DCD267-W	2-3	1		2-3	1		2-3	1		1-15			1-15			1-15								
Lutron	Diva	DVCL-153PD																								
Lutron	Diva	DVCL-153P v2 ²																								
Lutron	Diva	DVCL-153P v3.0	1-3			1-3			1-3			1-15			1-15			1-15			1-18			1-20		
Lutron	Diva	DV-600P	1-3			1-3			1-3			1-15			1-15			1-15								
Lutron	DIVA	DVELV-300P	1-3			1-3			1-3			1-15			1-15			1-15			1-9					
Lutron	Maestro	MACL-153M v2 ²																			1-18			1-20		
Lutron	Maestro	MRF2-6ND-120	1-3			1-3			1-3			1-15			1-15			1-15								
Lutron	Nova	NLV1000 ²																			1-24			1-20		
Lutron	Grafik Eye	QSGR-3P ²																			1-30			1-20		
Lutron	RADIO RA	RRD-6NA ²																								
Lutron	Skylark	SLV-600P	1-3			1-3			1-3			1-15			1-15			1-15			1-13			1-20		
Lutron	Caseta	PD-6WCL (SD11)		1-3			1-3			1-3		2-15		X	2-15		X	2-15		X	1-18			1-15		
Sensors																										
Lutron	Maestro	MSCL-OP153MH		1-3			1-3			1-3		1-15			1-15			1-15			1-18			1-20		
Lutron	Maestro	MS-OPS2H	1-3			1-3			1-3			1-15			1-15			1-15								
Leviton	Decora	IPS02	1-3			1-3			1-3			1-15			1-15			1-15			1-18			1-20		
Leviton	Decora	IPS05																			1-18			1-20		
Leviton	Decora	IPS06																			1-18			1-20		
Leviton	Decora	IPS15	1-3			1-3			1-3			1-15			1-15			1-15			1-30			1-20		
Panel Modules																										
Lutron	Panel Module	GP (Harrier) Card	1-3			1-3			1-3			1-15			1-15			1-15								
Lutron	Panel Module	HW/LP-RPM-4U-120	1-3			1-3			1-3			1-15			1-15			1-15								

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

Misc (G25,ST19)

Number of bulbs

			 4.5w (40w) G16.5 Filament dimmable			 3.8w WG G25 Filament T20, P0023793			 3.8w Dimmable G25 Filament T20, P0025721			 2.7w WG G25 Filament T20			 7W (40W Eq) G25 WG CC Bulb			 10W (60W Eq) G25 WG CC Bulb			 5.5W (40W Eq) Filament ST19		
			9290018434 (478784), 9290012102 (461673), 9290013354 (475814)			9290019697 (549501), 9290019699 (549527), 9290019698 (549519), 9290019700 (549535)			9290022067 (549188), 9290022069 (549204), 9290022068 (549196), 9290022070 (549212)			9290022047 (549352), 9290022080 (549360)			9290011817 (458802, 458794, 458810)			9290011898 (459347), 9290011898 (459339), 9290011816 (458828), 9290011898 (459354), 9290011816 (458844), 9290011816 (458836)			9290012102 (461673)		
Company	Brand	Model No.	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR	Best	OK	NR
Leviton	Decora Slide	DSL06																					
Leviton	SureSlide	6613	1-2,4-20		X	2-5	8-10	X	1-5	8-20		3-20	2	X		1-21			1-15		1-15		
Leviton	SureSlide	6615P	1-20				1-10		1-2	3-5, 10-20	X	1-10		X	1-11			1-8				1-15	
Leviton	SureSlide	6631																					
Leviton	SureSlide	6633	2-20		X		1-10		1-5	8-20		2-15		X	1-21			1-15			1-15		
Leviton	SureSlide	6672		1-20		1-5	8-10		1-5	8-20		8-20		X	1-21			1-15				1-15	
Leviton	SureSlide	6674													1-21			1-15				1-10	
Leviton	Trimatron	6602	1,3-20		X	2	3-10	X	1-3	5-20		2-20		X	1-21			9-15	1-8			1-25	
Leviton	Trimatron	6681	1,3-20	2		2-5	8-10	X	1-3	5-20		2-20		X	1-21			1-15				1-15	
Leviton	IllumaTech	IPI06	1-2,4-20		X	2-3, 8-10	1, 5		1-5	8-20		1-20			1-21			1-15			1-25		
Leviton	IllumaTech	IPL06																					
Leviton	IllumaTech	IPM10				3-5	8-10	X	2-10	15-20	X	8-20	3-5	X	2-21		1	2-15	1			1-25	
Philips	Sunrise	SRI000VA120		1-20											2-21		1	2-15	1			1-25	
Philips	Sunrise	SRI50LED120		1-20											1-21			1-15				1-10	
WattStopper	Micro Decorator	DCD267-W		1-20			2-10	X	2-5	1, 8-20		5-10	15-20	X	2-21		1	1-15				1-15	
Lutron	Diva	DVCL-153PD		1-20		1-5	8-10		1-5	8-20		1-20					X			X			X
Lutron	Diva	DVCL-153P v2 ²		1-20			1-10		1-20			1-20			1-15	16-21		1-15					X
Lutron	Diva	DVCL-153P v3.0																					
Lutron	Diva	DV-600P	1-20			1-5	8-10		1-5	8-20		1-20			1-21			1-15			1-15		
Lutron	DIVA	DVELV-300P	1-20			1-10			1-20			1-20			1-11			1-8			1-15		
Lutron	Maestro	MACL-153M v2 ²	1-20			1-10			1-5	8-20		1-20			1-21			1-15				1-15	
Lutron	Maestro	MRF2-6ND-120	1-10	15-20			2-10	X	3-5	1-2, 8-20		2-20		X	1-15	16-21		1-15				1-15	
Lutron	Nova	NLV1000 ²	1-20				1-10		1-20			1-20			1-21*			1-15*			1-15		
Lutron	Grafik Eye	QSGR-3P ²	1-20				1-10		1-3	5-20		1-20			1-21*			1-15*				1-8	
Lutron	RADIO RA	RRD-6NA ²	1-20				1-10		1-3	5-20		1-20					X	1-15			1-15		
Lutron	Skylark	SLV-600P	1-20			1-10			1-10	15-20		1-20			1-16				1-11		1-15		
Lutron	Caseta	PD-6WCL (SD11)	3-20		X		1-10		1-5	8-20		2-20		X	1-21				1-15				X
Sensors																							
Lutron	Maestro	MSCL-OP153MH		1-20			1-10		1-8	10-20		1-20				1-21		11-15	1-10			1-25	
Lutron	Maestro	MS-OPS2H	1-20			1-10			1-20			1-20			1-21			1-15			1-25		
Leviton	Decora	IPS02	1-20			1-10			1-20			1-20			1-21			1-15			1-25		
Leviton	Decora	IPS05																					
Leviton	Decora	IPS06																					
Leviton	Decora	IPS15	1-20			1-10			1-20			1-20			1-21			1-15			1-25		
Panel Modules																							
Lutron	Panel Module	GP (Harrier) Card	1-20				1-10			1-20			1-20		1-21*			1-15*			1-15		
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20				1-10			1-5	X	1		X	1-21*			1-15*			1-15		

1. Audible noise may be observed when used with this dimmer, depending on the application.

2. This dimmer has low end trim adjustment that may be used for optimal performance.

[illegible]



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-21015CR 06/22 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.
All other trademarks are owned by Signify Holding or their respective owners.