

PHILIPS

LED lamps

Party bulbs



Colorful lighting that offers a festive touch

The LED A19 bulbs provide bright colorful light perfect for special occasions, parties and holidays. These Philips LED A19 lamps are available in up to six different colors with a durable plastic finish or a classic glass finish that provide a festive touch to your facility lighting. Brighten up your facility and celebrate with color using these energy saving LED bulbs.

Benefits

- Up to six A19 colors available:
Red, green, blue, yellow, orange, purple
- All models are wet location

Features

- **Long life** – With a lifetime of up to 10,000 hours, you can reduce the hassle of frequently replacing your light bulb
- **Ideal for any occasion** – get festive for any reason
- **A19 bulbs** – rated for indoor/outdoor use

Philips LED party bulbs



E26

Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Base	Volts (V)	Lifetime ¹ (hrs)	Material	Color	Legend
MasterClass A19 - Plastic Party Bulbs non-dimming											
D	463208	929001998303	BC8A19/LED/PURPLE/ND 120V	8	60	E26	120	10,000	Plastic	Purple	A
D	463240	929001998005	8A19/LED/BLUE/P/ND 120V 4/1FB	8	60	E26	120	10,000	Plastic	Blue	B
D	463281	929001997905	8A19/LED/GREEN/P/ND 120V 4/1FB	8	60	E26	120	10,000	Plastic	Green	C
D	463257	929001998105	8A19/LED/YELLOW/P/ND 120V 4/1FB	8	60	E26	120	10,000	Plastic	Yellow	D
D	463232	929001998203	8A19/LED/ORANGE/P/ND 120V 6/1BC	8	60	E26	120	10,000	Plastic	Orange	E
D	463273	929001997805	8A19/LED/RED/P/ND 120V 4/1FB	8	60	E26	120	10,000	Plastic	Red	F
MasterClass A19 - Glass Party Bulbs non-dimming											
W	538256	929001937503	4A19/LED/PURPLE/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Purple	G
W	538231	929001937303	4A19/LED/BLUE/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Blue	H
W	538249	929001937403	4A19/LED/GREEN/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Green	I
W	538223	929001937203	4A19/LED/YELLOW/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Yellow	J
W	538215	929001937103	4A19/LED/ORANGE/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Orange	K
W	538207	929001937003	4A19/LED/RED/G/E26/ND 6/1BC	4	40	E26	120	10,000	Glass	Red	L

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

D = Damp location **W** = Wet location **E** = Suitable for enclosed fixtures **■** = ENERGY STAR® qualified **■** = Title 20 compliant **■** = Not regulated by Title 20



RoHS
COMPLIANT

© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-18116BN 07/20 philips.com/lighting



Signify North America Corporation
 200 Franklin Square Drive,
 Somerset, NJ 08873
 Telephone 855-486-2216

Signify Canada Ltd.
 281 Hillmount Road,
 Markham, ON, Canada L6C 2S3
 Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.