

PHILIPS

LED lamps

A-shape family



No matter the application, **get the right light**

Philips A-shape lamps provide a wide variety of features such as dimming and 3-way. Filament style, omni-directional light and various color temperatures make sure you always have the right light. Ideal for decorative and ambient lighting in retail outlets, hotels, restaurants, government buildings, and multi-unit residences.

Philips A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)



	Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
A19 - 40W lamp equivalent non-dimming														
D E	565085	929003004504	5A19/LED/927/FR/P/ND 4/1FB	E26	5	450	120	90	2700	11,000	CP	Plastic	Frosted	A
D E	571588	929003019904	5A19/LED/927/P/E26/ND 6/1FB T20	E26	5	450	120	90	2700	11,000	CP	Plastic	Frosted	A
D E	565093	929003004604	5A19/LED/930/FR/P/ND 4/1FB	E26	5	450	120	90	3000	11,000	CP	Plastic	Frosted	A
D E	571596	929003020004	5A19/LED/930/P/E26/ND 6/1FB T20	E26	5	450	120	90	3000	11,000	CP	Plastic	Frosted	A
D E	565100	929003004704	5A19/LED/950/FR/P/ND 4/1FB	E26	5	450	120	90	5000	11,000	CP	Plastic	Frosted	A
D E	571604	929003020104	5A19/LED/950/P/E26/ND/T20 6/1FB	E26	5	450	120	90	5000	11,000	CP	Plastic	Frosted	A
A19 - 40W lamp equivalent dimming														
W	556795	929001950933	4.5A19/VIN/820/E26/CL/GL/DIM 4/FBH T20	E26	4.5	350	120	80	2000	15,000	CP	Glass	Amber	B
W	565788	929002988503	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	E26	5.5	500	120	90	2700	15,000	CP	Glass	Clear	C NEW
W E	549485	929001969504	5A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	5	450	120	90	2700-2200	15,000	MC	Glass	Clear	D
W E	557595	929002327803	5A19/PER/927-22/FR/G/WGD 4/2FB T20	E26	5	450	120	90	2700-2200	15,000	MC	Glass	Frosted	E
D E	479428	929001940704	5A19/PER/927-22/P/E26/WG 6/1FB T20	E26	5	450	120	90	2700-2200	15,000	MC	Plastic	Frosted	F
D E	550400	929002035704	5A19/PER/927/P/E26/DIM 6/1FB T20	E26	5	450	120	90	2700	15,000	CP	Plastic	Frosted	G
W E	578534	929003497304	5A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	5	450	120	90	2700	15,000	CP	Glass	Frosted	H NEW
D E	550418	929002035804	5A19/PER/930/P/E26/DIM 6/1FB T20	E26	5	450	120	90	3000	15,000	CP	Plastic	Frosted	G
W E	578542	929003497404	5A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	5	450	120	90	3000	15,000	CP	Glass	Frosted	H NEW
D E	547042	929002035904	5A19/PER/940/P/E26/DIM 6/1FB T20	E26	5	450	120	90	4000	15,000	CP	Plastic	Frosted	G
D E	550426	929002036004	5A19/PER/950/P/E26/DIM 6/1FB T20	E26	5	450	120	90	5000	15,000	CP	Plastic	Frosted	J
D E	549220	929002207804	5A19/PER/950/CL/G/E26/DIM 1FB T20	E26	5	450	120	90	5000	15,000	CP	Glass	Clear	I
W E	578559	929003497504	5A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	5	450	120	90	5000	15,000	CP	Glass	Frosted	H NEW
A19 - 60W lamp equivalent non-dimming														
D E	571612	929003020204	8.8A19/LED/927/P/E26/ND/T20 6/1FB	E26	8.8	800	120	90	2700	11,000	CP	Plastic	Frosted	A
D E	565119	929003004804	8.5A19/LED/927/FR/P/ND 4/1FB	E26	8.5	800	120	90	2700	11,000	CP	Plastic	Frosted	A
D E	565127	929003004904	8.5A19/LED/930/FR/P/ND 4/1FB	E26	8.5	800	120	90	3000	11,000	CP	Plastic	Frosted	A
D E	571620	929003020304	8.8A19/LED/930/P/E26/ND 6/1FB T20	E26	8.8	800	120	90	3000	11,000	CP	Plastic	Frosted	A
D E	565135	929003005004	8.5A19/LED/950/FR/P/ND 4/1FB	E26	8.5	800	120	90	5000	11,000	CP	Plastic	Frosted	A
D E	571638	929003020404	8.8A19/LED/950/P/E26/ND 6/1FB T20	E26	8.8	800	120	90	5000	11,000	CP	Plastic	Frosted	A
D	554444	929002227304	8.8A19/LED/950/P/E26/ND 6/1FB T20	E26	8.8	800	120	90	5000	11,000	CP	Plastic	Frosted	J
A19 - 60W lamp equivalent dimming														
W	549493	929001969604	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	E26	8	800	120	90	2700-2200	15,000	MC	Glass	Clear	K
W E	573436	929003083243	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	E26	8	800	120	95	2700-2200	15,000	MC	Glass	Frosted	H NEW
D E	479444	929001940904	8.8A19/PER/927-22/P/E26/WG 6/1FB T20	E26	8.8	800	120	90	2700-2200	15,000	MC	Plastic	Frosted	F
D E	550434	929002036104	8.8A19/PER/927/P/E26/DIM 6/1FB T20	E26	8.8	800	120	90	2700	15,000	CP	Plastic	Frosted	B
W E	578567	929003497604	8A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	8	800	120	90	2700	15,000	CP	Glass	Frosted	H NEW
D E	550442	929002036204	8.8A19/PER/930/P/E26/DIM 6/1FB T20	E26	8.8	800	120	90	3000	15,000	CP	Plastic	Frosted	B
W E	578575	929003497704	8A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	8	800	120	90	3000	15,000	CP	Glass	Frosted	H NEW
D E	557660	929002327504	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	GU24	8.8	800	120	90	3000	15,000	CP	Plastic	Frosted	L
D E	545897	929002032304	8.8A19/PER/940/P/E26/DIM 6/1FB T20	E26	8.8	800	120	90	4000	15,000	CP	Plastic	Frosted	G
D E	550459	929002036304	8.8A19/PER/950/P/E26/DIM 6/1FB T20	E26	8.8	800	120	90	5000	15,000	CP	Plastic	Frosted	J
W E	578641	929003497804	8A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	8	800	120	90	5000	15,000	CP	Glass	Frosted	H NEW

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures

■ = ENERGY STAR® qualified ■ = Title 24 (JA8) compliant ■ = Title 20 compliant ■ = Not regulated by Title 20

Philips A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)



	Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
A19 / A21 - 75W lamp equivalent non-dimming														
D E	565143	929003005104	10A19/LED/927/FR/P/ND 4/1FB	E26	10	1000	120	90	2700	11,000	CP	Plastic	Frosted	A
D E	571646	929003020504	12.2A19/LED/927/P/E26/ND/T20 6/1FB	E26	12.2	1100	120	90	2700	11,000	CP	Plastic	Frosted	B
D E	565150	929003005204	10A19/LED/930/FR/P/ND 4/1FB	E26	10	1000	120	90	3000	11,000	CP	Plastic	Frosted	A
D E	571653	929003020604	12.2A19/LED/930/P/E26/ND 6/1FB T20	E26	12.2	1100	120	90	3000	11,000	CP	Plastic	Frosted	B
D E	565168	929003005304	10A19/LED/950/FR/P/ND 4/1FB	E26	10	1000	120	90	5000	11,000	CP	Plastic	Frosted	A
D E	571661	929003020704	12.2A19/LED/950/P/E26/ND/T20 6/1FB	E26	12.2	1100	120	90	5000	11,000	CP	Plastic	Frosted	B
A19 75W lamp equivalent dimming														
D E	561000	929002285404	12.2A19/PER/927-22/P/E26/WG 6/1FB T20	E26	12.2	1100	120	90	2700-2200	15,000	MC	Plastic	Frosted	C
W E	578583	929003497904	9.5A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	9.5	1100	120	90	2700	15,000	CP	Glass	Frosted	D NEW
D E	561035	929002385204	12.2A19/PER/927/P/E26/DIM 6/1FB T20	E26	12.2	1100	120	90	2700	15,000	CP	Plastic	Frosted	C
W E	578591	929003498004	9.5A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	9.5	1100	120	90	3000	15,000	CP	Glass	Frosted	D NEW
D E	561043	929002385304	12.2A19/PER/930/P/E26/DIM 6/1FB T20	E26	12.2	1100	120	90	3000	15,000	CP	Plastic	Frosted	C
D E	561050	929002385404	12.2A19/PER/940/P/E26/DIM 6/1FB T20	E26	12.2	1100	120	90	4000	15,000	CP	Plastic	Frosted	C
D E	560994	929002285204	12.2A19/PER/950/P/E26/DIM 6/1FB T20	E26	12.2	1100	120	90	5000	15,000	CP	Plastic	Frosted	C
W E	578609	929003498104	9.5A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	9.5	1100	120	90	5000	15,000	CP	Glass	Frosted	D NEW
A19 / A21 - 100W lamp equivalent non-dimming														
D E	565176	929003005404	13.5A19/LED/927/FR/P/ND 4/1FB	E26	13.5	1500	120	90	2700	11,000	CP	Plastic	Frosted	B
D E	554469	929002227604	16.6A21/LED/927/P/E26/ND 6/1FB T20	E26	16.6	1500	120	90	2700	11,000	CP	Plastic	Frosted	E
D E	565184	929003005504	13.5A19/LED/930/FR/P/ND 4/1FB	E26	13.5	1500	120	90	3000	11,000	CP	Plastic	Frosted	C NEW
D E	571687	929003020904	16.6A19/LED/930/FR/P/E26/ND 6/1FB T20	E26	16.6	1500	120	90	3000	11,000	CP	Plastic	Frosted	C NEW
D E	565192	929003005604	13.5A19/LED/950/FR/P/ND 4/1FB	E26	13.5	1500	120	90	5000	11,000	CP	Plastic	Frosted	B
D E	571695	929003021004	16.6A19/LED/950/P/E26/ND 6/1FB T20	E26	16.6	1500	120	90	5000	11,000	CP	Plastic	Frosted	B
A19 / A21 - 100W lamp equivalent dimming														
D E	561027	929002285504	16A19/PER/927-22/P/E26/WG 6/1FB T20	E26	16	1600	120	90	2200-2700	15,000	CP	Plastic	Frosted	C
D E	561068	929002385504	16A19/PER/927/P/E26/DIM 6/1FB T20	E26	16	1600	120	90	2700	15,000	CP	Plastic	Frosted	C
W E	578617	929003498204	12A19/LED/927/FR/Glass/E26/DIM 1FB T20	E26	12	1600	120	90	2700	15,000	CP	Glass	Frosted	F NEW
D E	557678	929002327604	16A21/PER/930/P/GU24/DIM 6/1FB T20	GU24	16	1600	120	90	3000	15,000	CP	Plastic	Frosted	G
W E	578625	929003498304	12A19/LED/930/FR/Glass/E26/DIM 1FB T20	E26	12	1600	120	90	3000	15,000	CP	Glass	Frosted	F NEW
D E	561076	929002385604	16A19/PER/930/P/E26/DIM 6/1FB T20	E26	16	1600	120	90	3000	15,000	CP	Plastic	Frosted	C
D E	561456	929002385704	16A19/PER/940/P/E26/DIM 6/1FB T20	E26	16	1600	120	90	4000	15,000	CP	Plastic	Frosted	C
D E	561019	929002285304	16A19/PER/950/P/E26/DIM 6/1FB T20	E26	16	1600	120	90	5000	15,000	CP	Plastic	Frosted	C
W E	578633	929003498404	12A19/LED/950/FR/Glass/E26/DIM 1FB T20	E26	12	1600	120	90	5000	15,000	CP	Glass	Frosted	F NEW
A21 - 150W lamp equivalent dimming														
D E	558221	929002343003	29A21/PER/827-22/P/E26/WG/HO 4/1FB	E26	29	2610	120	80	2700-2200	15,000	MC	Plastic	Frosted	E
D E	571505	929002343133	29A21/PER/850/FR/P/E26/D/HO 4/1PF	E26	29	2610	120	80	5000	15,000	CP	Plastic	Frosted	E

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location E = Suitable for enclosed fixtures E = ENERGY STAR® qualified E = Title 24 (JA8) compliant E = Title 20 compliant E = Not regulated by Title 20

Philips LED A-shape and decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product Model No. (6nc) No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
Large A lamps - 160W-200W-300W equivalent													
●	479287 929001854715	20A30/LED/865/P/E26/ND 4/1FB	E26	20	2300	120	80	6500	25,000	MC	Plastic	Frosted	A
●	479295 929001854815	24A35/LED/865/P/E26E39/ND 4/1FB	E26/E39	24	3000	120	80	6500	25,000	MC	Plastic	Frosted	B
●	479303 929001854915	42A40/LED/865/P/E26E39/ND 4/1FB	E26/E39	42	5000	120	80	6500	25,000	MC	Plastic	Frosted	C
3-way switching lamps													
■	556928 929002285003	14A21/LED/927/P/E26/3WAY ND 4/1FB T20	E26	5/8/14	450/800/1600	120	90	2700	25,000	MC	Plastic	Frosted	D
■	571513 929002285033	14A21/PER/927/FR/P/E26/3WAY/T20 4/IPF	E26	5/8/14	450/800/1600	120	90	2700	25,000	MC	Plastic	Frosted	C
■	571521 929002285133	18.5A21/PER/927/FR/P/E26/3WAY/T20 4/IPF	E26	6/13/18.5	620/1600/2150	120	90	2700	15,000	MC	Plastic	Frosted	C
SceneSwitch lamps													
■	464883 929001261343	9A19/PER/827-25-22/FR/ND/SSWG 4/1BC	E26	9/4/2	800/320/80	120	80	2700/2500/2200	15,000	MC	Plastic	Frosted	E
Dusk to Dawn lamps													
■	557728 929002333603	8.8A19/AMB/927/ND D2D 4/1FB T20	E26	8.8	800	120	90	2700	15,000	MC	Plastic	Frosted	F

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
2. MC/CP = MasterClass or CorePro product.
- = Damp location ● = Suitable for enclosed fixtures ■ = ENERGY STAR® qualified ■ = Title 20 compliant



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-1530BN 09/22 page 4 of 4 philips.com/lighting



Signify North America Corporation
400 Crossing Boulevard,
Bridgewater, NJ 08807
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.