

PHILIPS

LED lamps

Reflector lamps



Traditional lamp with a smooth design solution **for a seamless look**

Philips LED reflector lamps are a great alternative to standard incandescent, halogen and CFL lamps. The unique design replicates traditional form factors while providing excellent dimming. These lamps are ideal for ambient lighting areas such as restaurants, offices, multi-unit residences and many more.

Benefits

- Up to 15,000 life hours¹
- Suitable for enclosed fixtures
- Incandescent emulation offered for select products
- Contains no mercury
- ENERGY STAR® certified
- Title 20 compliant for California applications

Philips Reflector lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product Number	Model Number (12nc)	Description	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Legend
R20 lamp 45W equivalent dimming											
D ■ E ■	456979	929002008904	5R20/PER/927-22/P/E26/WG 6/1FB T20	5	450	120	90	2700-2200	15,000	MasterClass	A
D ■ E ■	553883	929002092204	5R20/PER/927/P/E26/DIM 6/1FB T20	5	450	120	90	2700	15,000	CorePro	B
D ■ E ■	547406	929002035304	5R20/PER/930/P/E26/DIM 6/1FB T20	5	450	120	90	3000	15,000	CorePro	B
D ■ E ■	547414	929002035404	5R20/PER/940/P/E26/DIM 6/1FB T20	5	450	120	90	4000	15,000	CorePro	B
D ■ E ■	548123	929002204063	5R20/PER/950/P/E26/DIM 6/1FB T20	5	450	120	90	5000	15,000	CorePro	B
BR30 lamp 65W equivalent dimming											
D ■ E ■	457044	929001870334	7.2BR30/PER/922-27/P/E26/WG 6/1FB T20	7.2	650	120	90	2700-2200	15,000	MasterClass	C
D ■ E ■	553891	929002092304	7.2BR30/PER/927/P/E26/DIM 6/1FB T20	7.2	650	120	90	2700	15,000	CorePro	D
D ■ E ■	545905	929002032104	7.2BR30/PER/930/P/E26/DIM 6/1FB T20	7.2	650	120	90	3000	15,000	CorePro	D
D ■ E ■	545913	929002032204	7.2BR30/PER/940/P/E26/DIM 6/1FB T20	7.2	650	120	90	4000	15,000	CorePro	D
D ■ E ■	548107	929002204163	7.2BR30/PER/950/P/E26/DIM 6/1FB T20	7.2	650	120	90	5000	15,000	CorePro	D
BR30 lamp 100W equivalent dimming											
D ■ E ■	558023	929002351403	15BR30/PER/927-22/E26/WG/HO 4/1FB T20	15	1400	120	90	2700-2200	15,000	MasterClass	E
D ■ E ■	558031	929002351303	15BR30/PER/950/E26/DIM/HO 4/1FB T20	15	1400	120	90	5000	15,000	CorePro	E
BR40 lamp 65W equivalent dimming											
D ■ E ■	553909	929002092404	8.8BR40/PER/927/P/E26/DIM 6/1FB T20	8.8	800	120	90	2700	15,000	CorePro	F
D ■ E ■	547422	929002035504	8.8BR40/PER/930/P/E26/DIM 6/1FB T20	8.8	800	120	90	3000	15,000	CorePro	F
D ■ E ■	547430	929002035604	8.8BR40/PER/940/P/E26/DIM 6/1FB T20	8.8	800	120	90	4000	15,000	CorePro	F
D ■ E ■	548115	929002204263	8.8BR40/PER/950/P/E26/DIM 6/1FB T20	8.8	800	120	90	5000	15,000	CorePro	F
BR40 lamp 86W equivalent dimming											
D ■ E ■	577841	929003477104	13.3BR40/PER/927-22/P/E26/WG 6/1CT T20	13.3	1204	120	90	2700-2200	15,000	MasterClass	G NEW
D ■ E ■	577858	929003477204	13.3BR40/PER/927/P/E26/DIM 6/1CT T20	13.3	1204	120	90	2700	15,000	CorePro	G NEW
D ■ E ■	577866	929003477304	13.3BR40/PER/930/P/E26/DIM 6/1CT T20	13.3	1204	120	90	3000	15,000	CorePro	G NEW
D ■ E ■	577874	929003477404	13.3BR40/PER/940/P/E26/DIM 6/1CT T20	13.3	1204	120	90	4000	15,000	CorePro	G NEW
D ■ E ■	577882	929003477504	13.3BR40/PER/950/P/E26/DIM 6/1CT T20	13.3	1204	120	90	5000	15,000	CorePro	G NEW
BR40 lamp 150W equivalent dimming											
D ■ E ■	558049	929002351203	20BR40/PER/927-22/E26/WG/HO 4/1FB T20	20.0	2175	120	90	2700-2200	15,000	MasterClass	H
D ■ E ■	558056	929002351503	20BR40/PER/950/E26/DIM/HO 4/1FB T20	20.0	2175	120	90	5000	15,000	CorePro	H

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed.
Warranty is based off of 15,000 hour claim. Lamps rated at 25,000 hours is for an unenclosed fixture.
Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures

■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20



RoHS
COMPLIANT



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.