

PHILIPS

LED lamps

G25 lamps



Decorative globes to light up your world

Philips LED G25 globes are designed to radiate a brilliant light. Filament models offers a light quality that provides consistent color from any angle. Perfect for vanities, pendant and other decorative locations.


Benefits

- Up to 15,000 hours life
- Smooth dimming down to 10%
- Certain models dim to a warm glow similar to incandescent lamps
- Excellent color consistency and high color rendering

Features

- Long life, lowers maintenance costs by reducing re-lamp frequency
- Up to 80% energy savings compared to standard incandescent lamps
- Wet location models can be used outside

Philips LED G25 globes



E26

Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
25W equivalent lamps dimming													
W ■	549360	929002208004	2.7G25/PER/927-922/FR/G/E26/WGX1FB T20	2.7	250	120	90	2700-2200	15,000	MC	Glass	Frosted	A
W ■	549352	929002204704	2.7G25/PER/927-922/CL/G/E26/WGX1FB T20	2.7	250	120	90	2700-2200	15,000	MC	Glass	Clear	B
W ■	543124	929002000803	4G25/MOD/840/E26/CL/GL/DIM 4/1BC	4	150	120	80	4000	15,000	CP	Glass	Smokey	C
40W equivalent lamps dimming													
W ■	537589	929001951253	4.5G25/VIN/820/E26/CL/GL/DIM 4/1BC T20	4.5	300	120	80	2000	15,000	CP	Glass	Amber	D
W ■	556811	929001951233	5.5G25/VIN/820/E26/CL/GL/DIM 4/FBH T20	4.5	300	120	80	2000	15,000	CP	Glass	Amber	D
W ■	549501	929001969704	3.8G25/PER/927-922/CL/G/E26/WGX1FB T20	3.8	350	120	90	2700-2200	15,000	MC	Glass	Clear	B
W ■	549527	929001969904	3.8G25/PER/927-922/FR/G/E26/WGX1FB T20	3.8	350	120	90	2700-2200	15,000	MC	Glass	Frosted	A
W ■	573337	929003084903	3.5G25/PER/UD50/CL/G/E26/D 4/2PFT20	3.5	350	120	90	5000	15,000	CP	Glass	Clear	E
W ■	549204	929002206904	3.8G25/PER/950/FR/G/E26/DIM 1FBT20	3.8	350	120	90	5000	15,000	CP	Glass	Frosted	A
W ■	575217	929003099803	3.5G25/PER/UD50/E26/FR/G/D 4/2PFT20	3.5	350	120	90	5000	15,000	CP	Glass	Frosted	A
60W equivalent lamps dimming													
W ■	565887	929002989503	6.5G25/VIN/820/E26/Amber/G/SP D 4/1PFT20	6.5	400	120	80	2000	15,000	CP	Glass	Amber	F
W ■	549519	929001969804	5.5G25/PER/927-922/CL/G/E26/WGX1FB T20	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	G
W ■	549535	929001970004	5.5G25/PER/927-922/FR/G/E26/WGX1FB T20	5.5	500	120	90	2700-2200	15,000	MC	Glass	Frosted	A
W ■	564914	929002991403	5G25/PER/UD50/CL/G/E26/D 4/2PFT20	5	500	120	90	5000	15,000	CP	Glass	Clear	H
W ■	549212	929002207004	5.5G25/PER/950/FR/G/E26/DIM 1FBT20	5.5	500	120	90	5000	15,000	CP	Glass	Frosted	A

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

W = Wet location ■ = ENERGY STAR® qualified ■ = Title 20 compliant ■ = Not regulated by Title 20



© 2020 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-18138BN 04/22 philips.com/lighting



Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.