

PHILIPS

LED lamps

Candles and
decorative lamps



Breathtaking brilliance and **sparkling white light**

Philips LED candles and decorative shapes incorporate beautiful filament aesthetic with amazing light quality, the ability to be used in wet locations and superior energy savings when compared to incandescent lamps. These dimmable lamps can create an intimate atmosphere. Perfect for chandeliers, sconces and general lighting.

Benefits

- Lowers maintenance costs by reducing re-lamp frequency
- Contains no mercury

Features

- Installs into existing candelabra and medium base fixtures
- Up to a 15,000-hour life¹
- Select models feature incandescent emulation to offer a familiar feel
- UL Wet location rated

Philips LED Candles and Decorative lamps



Ordering, electrical and technical data (Subject to change without notice)


	Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
A15 - 25W equivalent lamps non-dimming														
W	556555	929002260203	3.5A15/VIN/820/E26/CL/GL/DIM 4/1BC T20	E26	3.3	200	120	80	2000	15,000	CP	Glass	Amber	A
W	565655	929002987203	3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20	E26	3.5	225	120	80	2000	15,000	CP	Glass	Amber	B NEW
A15 - 40W equivalent lamps dimming														
W	549378	929002208104	3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	E12	3.8	350	120	90	2700-2200	15,000	MC	Glass	Clear	C
W	549386	929002208304	3.8A15/PER/927-922/CL/G/E26/WGX1FB T20	E26	3.8	350	120	90	2700-2200	15,000	MC	Glass	Clear	D
W	548305	929002209004	5A15/PER/950/CL/G/E26/DIM 1FB T20	E26	5	450	120	90	5000	15,000	CP	Glass	Clear	D
A15 - 60W equivalent lamps dimming														
W	549394	929002208404	5.5A15/PER/927-922/CL/G/E12/WGX1FB T20	E12	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	C
W	564450	929002986803	5A15/PER/UD/CL/G/E12/WGD 6/2PF T20	E12	5	450	120	95	2700-2200	15,000	MC	Glass	Clear	E NEW
W	549402	929002208604	5.5A15/PER/927-922/CL/G/E26/WGX1FB T20	E26	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	D
W	564385	929002986503	5A15/PER/UD/CL/G/E26/WGD 6/2PF T20	E26	5	450	120	95	2700-2200	15,000	MC	Glass	Clear	F NEW
W	573402	929003084503	6.6A15/PER/UD50/CL/G/E26/DIM2PF T20	E26	6.6	750	120	95	5000	15,000	CP	Glass	Clear	G NEW
G16.5 - 25W equivalent lamps dimming														
	537597	929001951353	4.5G16.5/VIN/820/E12/CL/GL/DIM 4/BC T20	E12	4.5	300	120	80	2000	15,000	CP	Glass	Amber	H
W	543157	929002001403	3G16.5/MOD/840/E12/CL/GL/DIM 4/BC	E12	3	100	120	80	4000	15,000	CP	Glass	Smokey	I
W	549253	929002204804	2.7G16.5/PER/927-922/CL/G/E26/WGX1FBT20	E26	2.7	250	120	90	2700-2200	15,000	MC	Glass	Clear	J
W	549261	929002204904	2.7G16.5/PER/927-922/CL/G/E12/WGX1FBT20	E12	2.7	250	120	90	2700-2200	15,000	MC	Glass	Clear	K
W	543157	929002001403	3G16.5/MOD/840/E12/CL/GL/DIM 4/BC	E12	3	100	120	80	4000	15,000	CP	Glass	Smokey	I
W	556829	929001951333	4.5G16.5/VIN/820/E12/CL/GL/DIM FBH T20	E12	4.5	300	120	80	2000	15,000	CP	Glass	Amber	H
G16.5 - 40W equivalent lamps dimming														
W	549287	929002205104	3.8G16.5/PER/927-922/CL/G/E12/WGX1FBT20	E12	3.8	350	120	90	2700-2200	15,000	MC	Glass	Clear	L
W	573303	929003085203	3.5G16.5/PER/UD/CL/G/E12WGD6/2PFT20	E12	3.5	350	120	95	2700-2200	15,000	MC	Glass	Clear	M NEW
W	549279	929002205004	3.8G16.5/PER/927-922/CL/G/E26/WGX1FBT20	E26	3.8	350	120	90	2700-2200	15,000	MC	Glass	Clear	N
W	573295	929003085103	3.5G16.5/PER/UD/CL/G/E26/WGD 6/2PF	E26	3.5	350	120	95	2700-2200	15,000	MC	Glass	Clear	O NEW
W	549311	929002205404	3.8G16.5/PER/927-922/FR/G/E26/WGX1FBT20	E26	3.8	350	120	90	2700-2200	15,000	MC	Glass	Frosted	P
W	564591	929002205423	3.8G16.5PER927-922FRGE26WGX2PFT20	E26	3.8	350	120	95	2700-2200	15,000	MC	Glass	Frosted	P NEW
G16.5 - 60W equivalent lamps dimming														
W	549303	929002205304	5.5G16.5/PER/927-922/CL/G/E12/WGX1FBT20	E12	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	L
W	573329	929003085403	5G16.5/PE/UD/CL/G/E12WGD 6/2PFT20	E12	5	500	120	95	2700-2200	15,000	MC	Glass	Clear	Q NEW
W	549295	929002205204	5.5G16.5/PER/927-922/CL/G/E26/WGX1FBT20	E26	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	N
W	573311	929003085303	5G16.5/PER/UD/CL/G/E26WGD 6/2PFT20	E26	5	500	120	95	2700-2200	15,000	MC	Glass	Clear	R NEW

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures = ENERGY STAR® qualified = Title 20 compliant = Not regulated by Title 20

Philips LED Candles and Decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
Candles - 15W equivalent lamps dimming														
W	543181	929002001303	3B11/MOD/840/E12/CL/GL/DIM 8/1BC	E12	3	100	120	80	4000	15,000	CP	Glass	Smokey	A
Candles - 25W equivalent lamps dimming														
W	566653	929002991803	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20	E12	2.3	185	120	95	2700-2200	15,000	MC	Glass	Clear	B NEW
Candles - 40W equivalent lamps dimming														
W	537621	929001951453	4.5B11/VIN/820/E12/CL/GL/DIM 8/1BC T20	E12	4.5	300	120	80	2000	15,000	CP	Glass	Amber	C
W	556852	929001951433	4.5B11/VIN/820/E12/CL/GL/DIM FBH T20	E12	4.5	300	120	80	2000	15,000	CP	Glass	Amber	C NEW
W	565804	929002988703	3.5B11/VIN/820/E12/Amber/G/SP D 4/2PF T20	E12	3.5	225	120	95	2000	15,000	CP	Glass	Amber	D NEW
W	556845	929001951133	4.5BA11/VIN/820/E12/CL/GL/DIM 4/FBHT20	E12	4.5	300	120	80	2000	15,000	CP	Glass	Amber	E
W	549568	929001969404	3.3B11/PER/927-922/CL/G/E12/WGX1FB T20	E12	3.3	300	120	90	2700-2200	15,000	MC	Glass	Clear	F
W	574392	929003089903	3.5B11/PER/UD/CL/G/E26/WGD 6/3PF T20	E26	3.5	300	120	95	2700-2200	15,000	MC	Glass	Clear	G NEW
W	549584	929002047204	3.3B11/PER/927-922/CL/G/E26/WGX1FB T20	E26	3.3	300	120	90	2700-2200	15,000	MC	Glass	Clear	H
W	549543	929001969204	3.3BA11/PER/927-922/CL/G/E12/WGX1FB T20	E12	3.3	300	120	90	2700-2200	15,000	MC	Glass	Clear	I
W	566661	929002990703	3.5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	E12	3.5	300	120	95	2700-2200	15,000	MC	Glass	Clear	J NEW
W	566679	929002991703	3.5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	E26	3.5	300	120	95	2700-2200	15,000	MC	Glass	Clear	K NEW
W	549147	929002205904	3.3B11/PER/950/CL/G/E12/DIM 1FBT20	E12	3.3	300	120	90	5000	15,000	CP	Glass	Clear	L
W	549121	929002205704	3.3BA11/PER/950/CL/G/E12/DIM 1FB T20	E12	3.3	300	120	90	5000	15,000	CP	Glass	Clear	M
W	564930	929002991603	3.5BA11/PER/UD50/CL/G/E12/D 6/3PF T20	E12	3.5	300	120	95	5000	15,000	CP	Glass	Clear	N NEW
W	549139	929002205804	3.3BA11/PER/950/CL/G/E26/DIM 1FB T20	E26	3.3	300	120	90	5000	15,000	CP	Glass	Clear	O

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.

Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location **W** = Wet location **E** = Suitable for enclosed fixtures **■** = ENERGY STAR® qualified **■** = Title 20 compliant **■** = Not regulated by Title 20

Philips LED Candles and Decorative lamps



Ordering, electrical and technical data (Subject to change without notice)

	Product No. (6nc)	Model No. (12nc)	Description	Base	Watts (W)	Lumens (lm)	Volts (V)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	MC/CP ²	Material	Finish	Legend
Candles - 60W equivalent lamps dimming														
W	549337	929002204504	5.5B11/PER/927-922/CL/G/E12/WGX 1FB T20	E12	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	P
W	573378	929003085503	5B11/PER/UD/CL/G/E26/WGD 6/3PF T20	E26	5	500	120	95	2700-2200	15,000	MC	Glass	Clear	Q NEW
W	566687	929002991003	5BA11/PER/UD/CL/G/E12/WGD 6/3PF T20	E12	5	500	120	95	2700-2200	15,000	MC	Glass	Clear	R NEW
W	566695	929002991103	5BA11/PER/UD/CL/G/E26/WGD 6/3PF T20	E26	5.5	500	120	95	2700-2200	15,000	MC	Glass	Clear	S NEW
W	572669	929002091593	5.5F15/PER/927-922/CL/G/E26/WGX 1PF T20	E26	5.5	500	120	90	2700-2200	15,000	MC	Glass	Clear	T NEW
W	575167	929002990804	5BA11/PER/CRI95WG/FR/G/E12/WGD 1CT	E12	5	500	120	95	2700-2200	15,000	MC	Glass	Frosted	U
W	575183	929003082404	5BA11/PER/CRI95WG/FR/G/E26/WGD 1CT	E26	5	500	120	95	2700-2200	15,000	MC	Glass	Frosted	V
W	575191	929003082504	5B11/PER/CRI95WG/FR/G/E12/WGD 1CT	E12	5	500	120	95	2700-2200	15,000	MC	Glass	Frosted	W
W	575175	929003094904	5B11/PER/CRI95WG/FR/G/E26/WGD 1CT	E26	5	500	120	95	2700-2200	15,000	MC	Glass	Frosted	X
W	549410	929002206304	5.5B11/PER/950/CL/G/E12/DIM 1FBT20	E12	5.5	500	120	90	5000	15,000	CP	Glass	Clear	Y NEW
Candles - 75W equivalent lamps dimming														
W	557462	929002295604	6.6BA11/PER/927-922/CL/G/E26/WGX T20	E26	6.6	600	120	90	2700-2200	15,000	MC	Glass	Clear	Z
W	557470	929002295704	6.6BA11/PER/927-922/CL/G/E12/WGX T20	E12	6.6	600	120	90	2700-2200	15,000	MC	Glass	Clear	AA
W	564492	929002986603	6.6/BA11/PER/UD/CL/G/E12+E26/WGD 3PF T20	E12+E26	6.6	700	120	95	2700-2200	15,000	MC	Glass	Clear	BB NEW
W	557496	929002295904	6.6BA11/PER/950/CL/G/E12/DIM 1FB T20	E12	6.6	600	120	90	5000	15,000	CP	Glass	Clear	AA
W	564500	929002986703	5.5BA11/PER/UD50/CL/G/E12+E26/D 3PF T20	E12+E26	5.5	700	120	95	5000	15,000	CP	Glass	Clear	AA NEW

1. Lamps rated 15,000 hours is in an enclosed fixture. Life rating is 25,000 in an unenclosed. Warranty is based off of 15,000 hour claim.
Lamps rated at 25,000 hours is for an unenclosed fixture. Life rating is 15,000 hours for enclosed. Warranty is based off of 25,000 hour claim.

2. MC/CP = MasterClass or CorePro product.

D = Damp location W = Wet location E = Suitable for enclosed fixtures ENERGY STAR® qualified Title 20 compliant Not regulated by Title 20



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-1430BN 09/22 page 4 of 4 philips.com/lighting



Signify North America Corporation
400 Crossing Boulevard,
Bridgewater, NJ 08807
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.