

**PHILIPS**



LED lamps

Contractor-grade



**Real pros use**  
Philips LED lamps

# Every job, **done right**



You're no handyman, you're a real professional. Someone who can be relied on to get the job done. Someone who plans well, executes fast and works efficiently.

LED technologies are rapidly changing, creating plenty of new opportunities. As a trusted name in lighting, we understand your challenges and can help you build your business & reputation. We know the importance of installing the lowest cost options to maintain profitability while still ensuring that you offer your customers a reliable product that will stand the test of time.

When you need to get the job done right, you can count on Philips LED lamps. Now offering a dedicated, affordable contractor-grade portfolio of LED Lamps.

**Real professionals**  
choose Philips LED lamps

# The right light for the right price

The Contractor-grade line of LED lamps offers reliable, lighting that meets industry efficiency standards and delivers the most affordable solutions from a trust-worthy brand leader.



## **Philips quality** that meets your needs

- ✓ Focused product portfolio with attractive price points
- ✓ Easy 1:1 replacement of conventional lamps with fast ROI
- ✓ Product lifetimes fitting application and customer needs
- ✓ Multi-pack options to make installs faster

## Contractor-grade

### MainsFit (UL Type-B) TLED lamps



## Why choose MainsFit (UL Type-B) TLED lamps?

- Double-ended for faster installs
- Proven over 40% energy savings<sup>1</sup> over fluorescent lamps
- Average life rating of 50,000 hours<sup>2</sup>
- UL Type B ballast bypass
- Emergency capable with Philips PTB15D, Bodine ELI-S-20 or ELI-S-100 EM drivers
- Glass tube construction



### Contractor-grade MainsFit (UL Type-B) TLED lamps



Cat. No.	Model No.	Product Description	Volts (V)	Watts (W)	Base	CRI (min)	CCT (K)	Lifespan (hrs)	Lumens (lm)	DLC ID	C/P Qty
577767	9290034745	14.5T8/CNG/48-835/MF17/G 25/1	120-277	14.5	G13	80	3500	50,000	1750	PHBJTIQF	25
577775	9290034746	14.5T8/CNG/48-840/MF18/G 25/1	120-277	14.5	G13	80	4000	50,000	1800	PAL56OQ3	25
577783	9290034747	14.5T8/CNG/48-850/MF18/G 25/1	120-277	14.5	G13	80	5000	50,000	1800	PFHOVHZ7	25
577791	9290034748	14.5T8/CNG/48-865/MF18/G 25/1	120-277	14.5	G13	80	6500	50,000	1800	PS3GBS4Q	25
579045	9290035106	16.5T8/CNG/48-835/MF20/G 25/1	120-277	16.5	G13	80	3500	50,000	2000	PWH5DXIO	25
579052	9290035107	16.5T8/CNG/48-840/MF21/G 25/1	120-277	16.5	G13	80	4000	50,000	2100	PCJUDVTN	25
579060	9290035108	16.5T8/CNG/48-850/MF21/G 25/1	120-277	16.5	G13	80	5000	50,000	2100	PYDXK24N	25

6NC	SKU UPC	Case UPC	Case Qty	Case Wt	Case Cube	Layer	Pallet	layers	SKU Dim	Case Dim	Pallet Dim
577767	046677577766	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
577775	046677577773	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
577783	046677577780	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
577791	046677577797	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
579045	046677579043	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
579052	046677579050	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"
579060	046677579067	50046677462975	25	13.99	1.19	150	1050	10	47.8" x 1.1" x 1.1"	49.2" x 6.0" x 7.0"	51.8" x 40.0" x 55.1"

1. Savings based on comparison to F32T8 electronic instant start systems.

2. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70).



## Why choose Frosted BR30 LED lamps?

- Most cost-efficient option for basic lighting applications
- Dimmable & enclosed rated
- Average life rating of 15,000 hours<sup>1</sup>
- 2700K, 3000K, 4000K & 5000K CCT options
- Opportunity to expand into the Residential Market & Resi contractors

### Contractor-grade Frosted BR30 LED lamps (E26 base)



Cat. No.	Model No.	Product Description	Volts (V)	Watts (W)	Equivalent	CRI (min)	CCT (K)	Lifespan (hrs)	Lumens (lm)	Dimmable	T20 status
583583	929003619804	8.8BR30/CNG/827/FR/P/E26/DIM/120V 6/1CT	120	8.8	65	80	2700	15,000	650	Yes	No
583591	929003619904	8.8BR30/CNG/830/FR/P/E26/DIM/120V 6/1CT	120	8.8	65	80	3000	15,000	650	Yes	No
583609	929003620004	8.8BR30/CNG/840/FR/P/E26/DIM/120V 6/1CT	120	8.8	65	80	4000	15,000	650	Yes	No
583617	929003620104	8.8BR30/CNG/850/FR/P/E26/DIM/120V 6/1CT	120	8.8	65	80	5000	15,000	650	Yes	No
541010	929001947903	9BR30/LED/827/FR/P/ND 6/1FB	120	9	65	80	2700	11,000	650	No	No
576561	929001947993	9BR30/LED/827/FR/P/ND 4/3CT	120	9	65	80	2700	11,000	650	No	No

Cat. No.	SKU UPC	Case UPC	Case Qty	Case Wght	Layer	Pallet	Sku dimensions	Case dimensions	Pallet dimensions
583583	46677583583	50046677583588	6	1.4938	120	840	3.80" x 3.80" x 5.28"	11.81" x 7.95" x 5.95"	47.24" x 39.37" x 47.60"
583591	46677583590	50046677583595	6	1.4938	120	840	3.80" x 3.80" x 5.28"	11.81" x 7.95" x 5.95"	47.24" x 39.37" x 47.60"
583609	46677583606	50046677583601	6	1.4938	120	840	3.80" x 3.80" x 5.28"	11.81" x 7.95" x 5.95"	47.24" x 39.37" x 47.60"
583617	46677583613	50046677583618	6	1.4938	120	840	3.80" x 3.80" x 5.28"	11.81" x 7.95" x 5.95"	47.24" x 39.37" x 47.60"
541010	46677541019	50046677541014	6	1.903	120	960	3.58" x 3.58" x 5.16"	11.22" x 7.56" x 5.83"	47.24" x 39.37" x 52.76"
576561	46677576561	50046677576566	4	3.56	60	360	3.74" x 7.28" x 7.05"	15.67" x 7.76" x 7.72"	47.24" x 39.37" x 52.09"

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70).



## Why choose Frosted A-shape LED lamps?

- Up to 35% cost savings compared to Core Pro A-shape lamps
- Ideal for residential and multi-family applications
- Lamps suitable for enclosed fixtures
- Select lamps Title 20 qualified for California applications
- Dimmable/non-dim portfolio



### Contractor-grade Frosted A-shape LED lamps (E26 base)

Cat. No.	Model No.	Product Description	Volts (V)	Watts (W)	Equivalent	CRI (min)	CCT (K)	Lifespan (hrs)	Lumens (lm)	Dimmable	T20 status
581801	929003585004	14A19/CNG/827/FR/P/E26/D 4/4CT	120	14	100	80	2700	15,000	1600	Yes	No
581827	929003585104	14A19/CNG/830/FR/P/E26/D 4/4CT	120	14	100	80	3000	15,000	1600	Yes	No
581835	929003585204	14A19/CNG/840/FR/P/E26/D 4/4CT	120	14	100	80	4000	15,000	1600	Yes	No
581868	929003585304	14A19/CNG/850/FR/P/E26/D 4/4CT	120	14	100	80	5000	15,000	1600	Yes	No
571695	929003021004	16.6A19/LED/950/P/E26/ND 6/1FB T20	120	16.6	100	90	5000	11,000	1500	No	Yes
571687	929003020904	16.6A19/LED/930/FR/P/E26/ND 6/1FB T20	120	16.6	100	90	3000	11,000	1500	No	Yes
571679	929003020804	16.6A19/LED/927/P/E26/ND 6/1FB T20	120	16.6	100	90	2700	11,000	1500	No	Yes
581751	929003579504	8A19/CNG/827/FR/P/E26/D 4/4CT	120	8	60	80	2700	15,000	800	Yes	No
581785	929003579604	8A19/CNG/850/FR/P/E26/D 4/4CT	120	8	60	80	5000	15,000	800	Yes	No
581769	929003584804	8A19/CNG/830/FR/P/E26/D 4/4CT	120	8	60	80	3000	15,000	800	Yes	No
581777	929003584904	8A19/CNG/840/FR/P/E26/D 4/4CT	120	8	60	80	4000	15,000	800	Yes	No
571653	929003020604	12.2A19/LED/930/P/E26/ND 6/1FB T20	120	12.2	75	90	3000	11,000	1100	No	Yes
571646	929003020504	12.2A19/LED/927/P/E26/ND 6/1FB T20	120	12.2	75	90	2700	11,000	1100	No	Yes
565184	929003005504	13.5A19/LED/930/FR/P/ND 4/1FB	120	13.5	100	90	3000	11,000	1500	No	No
565192	929003005604	13.5A19/LED/950/FR/P/ND 4/1FB	120	13.5	100	90	5000	11,000	1500	No	No
565176	929003005404	13.5A19/LED/927/FR/P/ND 4/1FB	120	13.5	100	90	2700	11,000	1500	No	No
571612	929003020204	8.8A19/LED/927/P/E26/ND 6/1FB T20	120	8.8	60	90	2700	11,000	800	No	Yes
571620	929003020304	8.8A19/LED/930/P/E26/ND 6/1FB T20	120	8.8	60	90	3000	11,000	800	No	Yes
571638	929003020404	8.8A19/LED/950/P/E26/ND 6/1FB T20	120	8.8	60	90	5000	11,000	800	No	Yes
571588	929003019904	5A19/LED/927/P/E26/ND 6/1FB T20	120	5	40	90	2700	11,000	450	No	Yes
571596	929003020004	5A19/LED/930/P/E26/ND 6/1FB T20	120	5	40	90	3000	11,000	450	No	Yes
565150	929003005204	10A19/LED/930/FR/P/ND 4/1FB	120	10	75	90	3000	11,000	1000	No	No
565168	929003005304	10A19/LED/950/FR/P/ND 4/1FB	120	10	75	90	5000	11,000	1000	No	No
565143	929003005104	10A19/LED/927/FR/P/ND 4/1FB	120	10	75	90	2700	11,000	1000	No	No
565135	929003005004	8.5A19/LED/950/FR/P/ND 4/1FB	120	8.5	60	90	5000	11,000	800	No	No
565127	929003004904	8.5A19/LED/930/FR/P/ND 4/1FB	120	8.5	60	90	3000	11,000	800	No	No
565119	929003004804	8.5A19/LED/927/FR/P/ND 4/1FB	120	8.5	60	90	2700	11,000	800	No	No
565100	929003004704	5A19/LED/950/FR/P/ND 4/1FB	120	5	40	90	5000	11,000	450	No	No
565085	929003004504	5A19/LED/927/FR/P/ND 4/1FB	120	5	40	90	2700	11,000	450	No	No
565093	929003004604	5A19/LED/930/FR/P/ND 4/1FB	120	5	40	90	3000	11,000	450	No	No

# PHILIPS

Contractor-grade

Frosted A-shape LED lamps



## Why choose Frosted A-shape LED lamps?

- Up to 35% cost savings compared to Core Pro A-shape lamps
- Ideal for residential and multi-family applications
- Lamps suitable for enclosed fixtures
- Select lamps Title 20 qualified for California applications
- Dimmable/non-dim portfolio

### Contractor-grade Frosted A-shape LED lamps (E26 base)



Cat. No.	SKU UPC	Case UPC	Case Qty	Case Wght	Layer	Pallet	Sku dimensions	Case dimensions	Pallet dimensions
581801	46677581800	50046677581805	4	2.65	144	864	4.61" x 2.36"	9.92" x 5.19" x 7.56"	47.244" x 39.37" x 51.535"
581827	46677581824	50046677581829	4	2.65	144	864	4.61" x 2.36"	9.92" x 5.19" x 7.57"	47.244" x 39.37" x 51.535"
581835	46677581831	50046677581836	4	2.65	144	864	4.61" x 2.36"	9.92" x 5.19" x 7.58"	47.244" x 39.37" x 51.535"
581868	46677581862	50046677581867	4	2.65	144	864	4.61" x 2.36"	9.92" x 5.19" x 7.59"	47.244" x 39.37" x 51.535"
571695	46677571696	50046677571691	6	1.33	270	2430	4.61" x 2.36"	7.756" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
571687	46677571689	50046677571684	6	1.33	270	2430	4.61" x 2.36"	7.756" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
571679	46677571672	50046677571677	6	1.33	270	2430	4.61" x 2.36"	7.756" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
581751	46677581756	50046677581751	4	1.66	144	864	4.09" x 2.36"	9.921" x 5.197" x 7.559"	47.244" x 39.37" x 51.535"
581785	46677581787	50046677581782	4	1.66	144	864	4.09" x 2.36"	9.921" x 5.197" x 7.559"	47.244" x 39.37" x 51.535"
581769	46677581763	50046677581768	4	1.66	144	864	4.09" x 2.36"	9.921" x 5.197" x 7.559"	47.244" x 39.37" x 51.535"
581777	46677581770	50046677581775	4	1.66	144	864	4.09" x 2.36"	9.921" x 5.197" x 7.559"	47.244" x 39.37" x 51.535"
571653	46677571658	50046677571653	6	1.33	270	2430	4.61" x 2.36"	7.756" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
571646	46677571641	50046677571646	6	1.33	270	2430	4.61" x 2.36"	7.756" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
565184	46677565183	50046677565188	4	0.76	252	2268	4.61" x 2.36"	5.276" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
565192	46677565190	50046677565195	4	0.76	252	2268	4.61" x 2.36"	5.276" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
565176	46677565176	50046677565171	4	0.76	252	2268	4.61" x 2.36"	5.276" x 5.276" x 5.315"	47.244" x 39.37" x 53.622"
571612	46677571610	50046677571615	6	0.77	270	2430	4.09" x 2.36"	7.677" x 5.236" x 4.882"	47.244" x 39.37" x 49.724"
571620	46677571627	50046677571622	6	0.77	270	2430	4.09" x 2.36"	7.677" x 5.236" x 4.882"	47.244" x 39.37" x 49.724"
571638	46677571634	50046677571639	6	0.77	270	2430	4.09" x 2.36"	7.677" x 5.236" x 4.882"	47.244" x 39.37" x 49.724"
571588	46677571580	50046677571585	6	0.77	270	2430	4.09" x 2.36"	7.677" x 5.236" x 4.882"	47.244" x 39.37" x 49.724"
571596	46677571597	50046677571592	6	0.77	270	2430	4.09" x 2.36"	7.677" x 5.236" x 4.882"	47.244" x 39.37" x 49.724"
565150	46677565152	50046677565157	4	0.77	252	2520	4.17" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565168	46677565169	50046677565164	4	0.77	252	2520	4.17" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565143	46677565145	50046677565140	4	0.77	252	2520	4.17" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565135	46677565138	50046677565133	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565127	46677565121	50046677565126	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565119	46677565114	50046677565119	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565100	46677565107	50046677565102	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565085	46677565084	50046677565089	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"
565093	46677565091	50046677565096	4	0.77	252	2520	4.09" x 2.36"	5.236" x 5.236" x 4.803"	47.244" x 39.37" x 53.78"



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLt-230XBR 07/23 [philips.com/LEDlamps](https://philips.com/LEDlamps)

Signify North America Corporation  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.