

PHILIPS

LED lamps

InstantFit LED

Ballast/Driver Compatibility Guide



Contents

T8 Instant-Start

UL Type A ballasts

BAA, 2ft, 3ft & 4ft	1, 3, 5 & 7
Glass, UniversalFit, FlexFit & U-Bent	2, 4, 6 & 8

T8 Programmed-Start

UL Type A fixed output ballasts

BAA, 2ft, 3ft & 4ft	9 & 11
Glass & U-Bent	10 & 12

T8 Programmed-Start

Dimmable ballasts

BAA, 2ft, 3ft & 4ft	11
Glass & U-Bent	12

T5/T8 Emergency ballasts

BAA, 2ft, 3ft & 4ft	13
Glass & U-Bent	14
T5 HO & T5 HE	14

T8 InstantFit drivers

2ft, 3ft & 4ft & Glass	13
U-Bent	14

Non-T8 InstantFit drivers

4ft, 8ft Plastic & 8ft Glass	14
---------------------------------	----

PL ballasts

PL-L, PL-C & PL-S	15 & 16
-------------------	---------

T12 ballasts

T12 Electronic	17
T12 Magnetic	17

T5 ballasts

T5 HO ballasts	17
T5 HE ballasts	18

T8 / T12 ballasts

8' Slimline ballasts	19
----------------------	----

LATAM

FA8 ballasts	19
--------------	----

T8 Instant-Start

UL Type A ballasts

		11.5W 2100m (4ft. Glass)	16W 1800 lm (4 ft. Glass)	10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)
				BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469320, 469338 469346, 469353 469452, 469478 469460	565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model			Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-1P32-N											
Advance	ICN-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-3P32-N					● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-4P32-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-1P32-N		Inadvisable			Inadvisable						Inadvisable
Advance	IOPA-2P32-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-3P32-N		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-4P32-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-2P32-LW-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-3P32-LW-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-4P32-LW-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-1P32-HL-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-2P32-HL-N	● Certified				● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOPA-3P32-HL-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IOPA-4P32-HL-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-1P32-SC	● Certified	● Certified			● Certified		● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-2P32-SC					● Certified		● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-3P32-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-4P32-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-2P32-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-2P32-LW-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-1P32-LW-SC	● Certified				● Certified		● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-2P32-LW-SC	● Certified				● Certified		● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-3P32-LW-SC	● Certified				● Certified		● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GOPA-4P32-LW-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	RES-2P32-N	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	REB-2P32-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	REB-4P32-SC	● Certified	● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH3-120-L		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH3-277-L		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH5-120-L					● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Fulham Co., Inc	WH5-277-L		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WHSG1-UNV-T8-IS		● Certified			Inadvisable	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WHSG2-UNV-T8-IS		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WHSG2-UNV-T8-LB		● Certified				● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WHSG3-UNV-T8-IS			■ Certified	■ Certified	Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	
Fulham Co., Inc	WHSG3-UNV-T8-LB		● Certified			Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	● Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		13 W 2100 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	17W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	12.5 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²	
		473926, 473934 473942, 473958	541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	456566, 456574 472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	FlexFit 560193, 600189 600197	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882
Manufacturer	Ballast Model		Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	
Advance	ICN-1P32-N										● Certified		
Advance	ICN-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	
Advance	ICN-3P32-N	● Certified			● Certified		● Certified	● Certified	● Certified		● Certified		
Advance	ICN-4P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	IOPA-1P32-N	Inadvisable				Inadvisable	Inadvisable	Inadvisable	Inadvisable	Inadvisable	● Certified	Inadvisable	
Advance	IOPA-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOPA-3P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	IOPA-4P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	IOPA-2P32-LW-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOPA-3P32-LW-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Advance	IOPA-4P32-LW-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	IOPA-1P32-HL-N	● Certified				● Certified	● Certified						
Advance	IOPA-2P32-HL-N	● Certified	● Certified	● Certified	● Certified		● Certified	● Certified	● Certified			● Certified	
Advance	IOPA-3P32-HL-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Advance	IOPA-4P32-HL-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Advance	GOPA-1P32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	GOPA-2P32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	GOPA-3P32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	GOPA-4P32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	GOPA-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	GOPA-2P32-LW-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	
Advance	GOPA-1P32-LW-SC	● Certified	● Certified	● Certified	● Certified		● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	GOPA-2P32-LW-SC	● Certified	● Certified	● Certified	● Certified		● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	GOPA-3P32-LW-SC	● Certified	● Certified	● Certified	● Certified		● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	GOPA-4P32-LW-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	REB-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	
Advance	REB-2P32-SC		● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Advance	REB-4P32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Fulham Co., Inc	WH3-120-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Fulham Co., Inc	WH3-277-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Fulham Co., Inc	WH5-120-L												
Fulham Co., Inc	WH5-277-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Fulham Co., Inc	WHSG1-UNV-T8-IS	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	
Fulham Co., Inc	WHSG2-UNV-T8-IS	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	
Fulham Co., Inc	WHSG2-UNV-T8-LB	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			
Fulham Co., Inc	WHSG3-UNV-T8-IS												
Fulham Co., Inc	WHSG3-UNV-T8-LB	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified			

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		11.5W 2100m (4ft. Glass)	16W 1800 lm (4 ft. Glass)	10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)
				BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469320, 469338 469346, 469353 469452, 469478 469460	565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	580266, 580274	580233	576777, 576785, 576793	576801, 576819, 576827							
		Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Fulham Co., Inc	WH5G3-UNV-T8-HB		● Certified			Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH42-UNV-L		● Certified			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH43-UNV-L		● Certified			Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	WH44-UNV-L					Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	
Fulham Co., Inc / Leviton	Zipline (361RC-Z03)					Inadvisable	Inadvisable	Inadvisable	● Certified	● Certified	● Certified	
Universal Lighting Tech.	B132IUNVHP-N	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B232IUNVHP-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVHP-A	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432IUNVHP-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B132IUNVHE-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B232IUNVHE-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVHE-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432IUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B132IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B232IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVEL-A		■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432IUNVEL-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B232IUNVHEH-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVHEH-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432I277HEH	■ Certified	■ Certified			■ Certified			■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B232I347HP-A	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432I347HP	■ Certified	■ Certified			■ Certified		■ Certified	■ Certified	■ Certified		
General Electric	GE-132-MV-N	■ Certified										■ Certified
General Electric	GE-232-MV-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-332-MV-N	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-232-MV-N-DIY	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-332-MV-N-DIY	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-432-MV-N-DIY	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232MAX-N/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MAX-N/ULTRA			■ Certified	■ Certified	■ Certified		■ Certified				■ Certified
General Electric	GE432MAX-N/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	Inadvisable	Inadvisable	Inadvisable	■ Certified
General Electric	GE232MAX-L/ULTRA	■ Certified				■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MAX-L/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE432MAX-L/ULTRA			■ Certified	■ Certified	■ Certified	Inadvisable	Inadvisable				■ Certified
General Electric	GE132MAX-H/ULTRA	■ Certified							■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232MAX-H/ULTRA		Inadvisable			■ Certified	■ Certified	■ Certified			■ Certified	■ Certified
General Electric	GE332MAX-H/ULTRA	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	Inadvisable	Inadvisable	Inadvisable	■ Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		13 W 2100 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	17W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	12.5 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²
		473926, 473934 473942, 473958	541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	456566, 456574 472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	FlexFit 560193, 600189 600197	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Fulham Co., Inc	WH5G3-UNV-T8-HB	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified
Fulham Co., Inc	WH42-UNV-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified
Fulham Co., Inc	WH43-UNV-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified
Fulham Co., Inc	WH44-UNV-L											
Fulham Co., Inc/Leviton	Zipline (361RC-Z03)											
Universal Lighting Tech.	B132IUNVHP-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232IUNVHP-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVHP-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B432IUNVHP-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B132IUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232IUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B432IUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B132IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B332IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B432IUNVEL-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232IUNVHEH-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B332IUNVHEH-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B432I277HEH	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232I347HP-A		■ Certified	■ Certified	■ Certified	■ Certified		■ Certified		■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B432I347HP	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified		■ Certified	■ Certified	
General Electric	GE-132-MV-N	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-232-MV-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-332-MV-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-232-MV-N-DIY	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-332-MV-N-DIY	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-432-MV-N-DIY	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE232MAX-N/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	Inadvisable	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MAX-N/ULTRA	■ Certified	Inadvisable	Inadvisable	Inadvisable		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE432MAX-N/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified				■ Certified	■ Certified	
General Electric	GE232MAX-L/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MAX-L/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE432MAX-L/ULTRA	■ Certified	Inadvisable	Inadvisable	Inadvisable		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE132MAX-H/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified					■ Certified	■ Certified	
General Electric	GE232MAX-H/ULTRA	■ Certified				Inadvisable	Inadvisable	Inadvisable	Inadvisable	Inadvisable	■ Certified	■ Certified
General Electric	GE332MAX-H/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		11.5W 2100m (4ft. Glass)	16W 1800 lm (4 ft. Glass)	10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)
				BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469320, 469338 469346, 469353 469452, 469478 469460	565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	580266, 580274	580233	576777, 576785, 576793	576801, 576819, 576827							
		Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
General Electric	GE432MAX-H/ULTRA		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232MAX347-N	■ Certified				■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE432MAX347-N			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232-120RES-DIY	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE432-120RES-DIY	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 1x32T8/UNV ISN-SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 2x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 3x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 4x32T8/UNV ISN-SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 2X32T8/347 ISN-SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4X32T8/347 ISN-SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC	■ Certified		■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISH-SC	■ Certified		■ Certified	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISH-SC	■ Certified				■ Certified			■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3x32T8/UNV ISH-SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4x32T8/UNV ISH	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISH HT SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISH HT SC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4X32T8/UNV ISH-HT-1		■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISN-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISN-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3x32T8/UNV ISN-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4x32T8/UNV ISN-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 1x32T8/UNV ISL-SC-1	■ Certified				■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x32T8/UNV ISL-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4x32T8/UNV ISL-SC-1	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Ultrasave	UT232347	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Ultrasave	UT432347					■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Hatch	HL232AIS/UV/HE/W					■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Hatch	HL332AIS/UV/HE/W	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		13 W 2100 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	17W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	12.5 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²	
		473926, 473934 473942, 473958	541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	456566, 456574 472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	FlexFit 560193, 600189 600197	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	
General Electric	GE432MAX-H/ULTRA	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
General Electric	GE232MAX347-N	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE432MAX347-N	■ Certified					■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
General Electric	GE232-120RES-DIY	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE432-120RES-DIY	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 1x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 2x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QTP 3x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 4x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 2X32T8/347 ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 1x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 2x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHE 3x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 4x32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 4X32T8/347 ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 1x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 2x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHE 3x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 4x32T8/UNV ISL-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 1x32T8/UNV ISH-SC	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified			
Osram Sylvania	QHE 2x32T8/UNV ISH-SC	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified		■ Certified		■ Certified	
Osram Sylvania	QHE 3x32T8/UNV ISH-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Osram Sylvania	QHE 4x32T8/UNV ISH	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Osram Sylvania	QHE 1x32T8/UNV ISH HT SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 2x32T8/UNV ISH HT SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Osram Sylvania	QHE 4X32T8/UNV ISH-HT-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Osram Sylvania	QHE 1x32T8/UNV ISN-SC-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 2x32T8/UNV ISN-SC-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHE 3x32T8/UNV ISN-SC-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QHE 4x32T8/UNV ISN-SC-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	Inadvisable	■ Certified	■ Certified		
Osram Sylvania	QHE 1x32T8/UNV ISL-SC-1	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified		■ Certified	■ Certified		
Osram Sylvania	QHE 2x32T8/UNV ISL-SC-1	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHE 4x32T8/UNV ISL-SC-1	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Ultrasave	UT232347	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Ultrasave	UT432347						■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Hatch	HL232AIS/UV/HE/W	■ Certified	■ Certified	■ Certified				■ Certified		■ Certified		■ Certified	
Hatch	HL332AIS/UV/HE/W	■ Certified	■ Certified	■ Certified		■ Certified		■ Certified		■ Certified			

1. System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		11.5W 2100m (4ft. Glass)	16W 1800 lm (4 ft. Glass)	10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)
				BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539874 539882, 539866	469320, 469338 469346, 469353 469452, 469478 469460	565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686
Manufacturer	Ballast Model	580266, 580274	580233	576777, 576785, 576793	576801, 576819, 576827							
		Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Hatch	HL232BIS/UV/HE/W	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Hatch	HL432BIS/UV/HE/W	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Hatch	HL232AIS/34/HE/W		■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		
Hatch	HL432AIS/34/HE/W	■ Certified				■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Accupro	AK-RC-232IP-UNV	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Accupro	AP-232IP-UNV-M	■ Certified	■ Certified						■ Certified	■ Certified		
Accupro	AP-332IP-UNV	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Howard Industries	EP2/32IS/MV/MC/HE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Howard Industries	EP4/32IS/MV/MC	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Howard Industries	EP4/32IS/MV/MC/HE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Fusion	FB232347E-N					■ Certified	■ Certified	■ Certified				
Fusion	FB232MVE	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Fusion	FB432MVE-N	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-132-UV-IS-N-P	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-232RIS-1-TP-SL	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-232-UV-IS-L-P		■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-232-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-332-UV-IS-L-P	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-332-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-432RIS-1-TP-SL	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified				
Keystone	KTEB-432-UV-IS-N-P	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-432-UV-PS-N-P	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE232120HIP	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE232MVHIPE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE232MVHIPHE	■ Certified	■ Certified			■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE232MVHIPLE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE332120MIP	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE332MVHIPHE	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE432120MIP	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE432MVHIPE	■ Certified	■ Certified			■ Certified		■ Certified				
ESPEN	VE432MVHIPH	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE432MVHIPHE	■ Certified	■ Certified			■ Certified		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ESPEN	VE432MVHIPLE	■ Certified	■ Certified			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Instant-Start

UL Type A ballasts

		13 W 2100 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	16W 1800 lm (4 ft. Glass)	17W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	12.5 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²	
		473926, 473934 473942, 473958	541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	542084, 542092 542100, 545616 544502, 544510 544486, 544494 544759, 545624 544916	472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	456566, 456574 472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	FlexFit 560193, 600189 600197	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888 545814, 544874 544882
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	
Hatch	HL232BIS/UV/HE/W	■ Certified	■ Certified	■ Certified		■ Certified		■ Certified		■ Certified		■ Certified	
Hatch	HL432BIS/UV/HE/W	■ Certified	■ Certified	■ Certified		■ Certified		■ Certified		■ Certified			
Hatch	HL232AIS/34/HE/W					■ Certified				■ Certified		■ Certified	
Hatch	HL432AIS/34/HE/W	■ Certified	■ Certified	■ Certified				■ Certified		■ Certified			
Accupro	AK-RC-232IP-UNV	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Accupro	AP-232IP-UNV-M		■ Certified	■ Certified		■ Certified		■ Certified		■ Certified		■ Certified	
Accupro	AP-332IP-UNV	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	■ Certified		■ Certified	
Howard Industries	EP2/32IS/MV/MC/HE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Howard Industries	EP4/32IS/MV/MC	■ Certified				■ Certified		■ Certified	■ Certified	■ Certified			
Howard Industries	EP4/32IS/MV/MC/HE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Fusion	FB232347E-N												
Fusion	FB232MVE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Fusion	FB432MVE-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Keystone	KTEB-132-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Keystone	KTEB-232RIS-1-TP-SL	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Keystone	KTEB-232-UV-IS-L-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Keystone	KTEB-232-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
Keystone	KTEB-332-UV-IS-L-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Keystone	KTEB-332-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Keystone	KTEB-432RIS-1-TP-SL		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified			
Keystone	KTEB-432-UV-IS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
Keystone	KTEB-432-UV-PS-N-P	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
ESPEN	VE232120HIP	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
ESPEN	VE232MVHIPE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
ESPEN	VE232MVHIPHE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
ESPEN	VE232MVHIPLE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified		■ Certified	
ESPEN	VE332120MIP	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
ESPEN	VE332MVHIPHE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
ESPEN	VE432120MIP	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
ESPEN	VE432MVHIPE		■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			■ Certified			
ESPEN	VE432MVHIPH	■ Certified				■ Certified		■ Certified	■ Certified				
ESPEN	VE432MVHIPHE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			
ESPEN	VE432MVHIPLE	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified			

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start

UL Type A fixed output ballasts

		10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)	13 W 2100 lm (4 ft.)	
		BAA 576777, 576785 576793	BAA 576801, 576819 576827	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847		469320, 469338 469346, 469353 469452, 469478 469460		565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	473926, 473934 473942, 473958
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	
Advance	IOP-1PSP32-N										● Certified	
Advance	IOP-2PSP32-N									● Certified	● Certified	
Advance	IOP-3PSP32-SC			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOP-4PSP32-SC			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOP-1PSP32-LW-N										● Certified	
Advance	IOP-2PSP32-LW-N									● Certified	● Certified	
Advance	IOP-3PSP32-LW-SC			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOP-4PSP32-LW-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	HOP-2PSP32-HL-L									● Certified	● Certified	
Advance	HOP-4PSP32-HL-G									● Certified	● Certified	
Universal Lighting Tech.	B232PUNVHE-B	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B332PUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B432PUNVHE-A	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Universal Lighting Tech.	B232PUNVHEH-A									■ Certified	■ Certified	
Universal Lighting Tech.	B332PUNVHEH-A									■ Certified	■ Certified	
Universal Lighting Tech.	B232PUNVEL-B									■ Certified	■ Certified	
Universal Lighting Tech.	B332PUNVEL-A									■ Certified	■ Certified	
Universal Lighting Tech.	B432PUNVEL-A									■ Certified	■ Certified	
General Electric	GE-232MVPS-XL									■ Certified	■ Certified	
General Electric	GE-332MVPS-XL									■ Certified	■ Certified	
General Electric	GE-132MVPS-L									■ Certified	■ Certified	
General Electric	GE-232MVPS-L									■ Certified	■ Certified	
General Electric	GE-332MVPS-L									■ Certified	■ Certified	
General Electric	GE-432MVPS-L									■ Certified	■ Certified	
General Electric	GE-132MVPS-N									■ Certified	■ Certified	
General Electric	GE-232MVPS-N			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-332MVPS-N			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-432MVPS-N			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-132MVPS-H									■ Certified	■ Certified	
General Electric	GE-232MVPS-H									■ Certified	■ Certified	
General Electric	GE-332MVPS-H									■ Certified	■ Certified	
General Electric	GE-432MVPS-H									■ Certified	■ Certified	
Osram Sylvania	QHE 1X32T8/UNV PSX-MC										■ Certified	
Osram Sylvania	QHE 2X32T8/UNV PSX-MC										■ Certified	
Osram Sylvania	QHE 3X32T8/UNV PSX-SC									■ Certified	■ Certified	
Osram Sylvania	QHE 4X32T8/UNV PSX-SC									■ Certified	■ Certified	
Osram Sylvania	QHE 1X32T8/UNV PSN-MC									■ Certified	■ Certified	

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start

UL Type A fixed output ballasts

		10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²
		541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	IOP-1PSP32-N						● Certified	
Advance	IOP-2PSP32-N						● Certified	
Advance	IOP-3PSP32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOP-4PSP32-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	
Advance	IOP-1PSP32-LW-N						● Certified	
Advance	IOP-2PSP32-LW-N							
Advance	IOP-3PSP32-LW-SC	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	IOP-4PSP32-LW-SC	● Certified	● Certified	● Certified	● Certified	● Certified		
Advance	HOP-2PSP32-HL-L						● Certified	
Advance	HOP-4PSP32-HL-G						● Certified	
Universal Lighting Tech.	B232PUNVHE-B	■ Certified	■ Certified	■ Certified				
Universal Lighting Tech.	B332PUNVHE-A	■ Certified	■ Certified	■ Certified				
Universal Lighting Tech.	B432PUNVHE-A	■ Certified	■ Certified	■ Certified				
Universal Lighting Tech.	B232PUNVHEH-A						■ Certified	
Universal Lighting Tech.	B332PUNVHEH-A						■ Certified	
Universal Lighting Tech.	B232PUNVEL-B						■ Certified	
Universal Lighting Tech.	B332PUNVEL-A						■ Certified	
Universal Lighting Tech.	B432PUNVEL-A						■ Certified	
General Electric	GE-232MVPS-XL						■ Certified	
General Electric	GE-332MVPS-XL						■ Certified	
General Electric	GE-132MVPS-L						■ Certified	
General Electric	GE-232MVPS-L						■ Certified	
General Electric	GE-332MVPS-L						■ Certified	
General Electric	GE-432MVPS-L						■ Certified	
General Electric	GE-132MVPS-N						■ Certified	
General Electric	GE-232MVPS-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE-332MVPS-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-432MVPS-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
General Electric	GE-132MVPS-H						■ Certified	
General Electric	GE-232MVPS-H						■ Certified	
General Electric	GE-332MVPS-H						■ Certified	
General Electric	GE-432MVPS-H						■ Certified	
Osram Sylvania	QHE 1X32T8/UNV PSX-MC						■ Certified	
Osram Sylvania	QHE 2X32T8/UNV PSX-MC						■ Certified	
Osram Sylvania	QHE 3X32T8/UNV PSX-SC						■ Certified	
Osram Sylvania	QHE 4X32T8/UNV PSX-SC						■ Certified	
Osram Sylvania	QHE 1X32T8/UNV PSN-MC						■ Certified	

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.
 2. Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start

UL Type A fixed output ballasts

		10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)	13 W 2100 lm (4 ft.)	
		BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847		469320, 469338 469346, 469353 469452, 469478 469460		565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	473926, 473934 473942, 473958
		576777, 576785 576793	576801, 576819 576827		539858, 539874 539882, 539866							
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Osram Sylvania	QHE 2X32T8/UNV PSN-MC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3X32T8/UNV PSN-SC			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 4X32T8/UNV PSN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHES 2X32T8/UNV PSL-SC									■ Certified		
Osram Sylvania	QHE 2X32T8/UNV PSH-HT	■ Certified	■ Certified							■ Certified	■ Certified	
Osram Sylvania	QHE 3X32T8/UNV PSH-HT-SC									■ Certified	■ Certified	
Osram Sylvania	QHE 4X32T8/UNV PSH-HT									■ Certified	■ Certified	
Hatch	HL232APS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL332APS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL432APS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL232BPS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL332BPS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL432BPS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL232CPS/UV/HE/W									■ Certified	■ Certified	
Hatch	HL332CPS/UV/HE/W									■ Certified	■ Certified	

T8 Programmed-Start

Dimmable ballasts

		10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)	13 W 2100 lm (4 ft.)	15.5 W 2500 lm (4 ft.)
		BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847		565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	473926, 473934 473942, 473958	545178, 533372 545194, 545200
		576777, 576785 576793	576801, 576819 576827		539858, 539874 539882, 539866					
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	IZT-2S32-SC									
Advance	IZT-4S32									
Advance	REZ-132-SC						● Certified	● Certified		
Advance	REZ-2S32-SC						● Certified	● Certified		
Advance	REZ-3S32-SC						● Certified	● Certified		
General Electric	GE132MVPSN-V03	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232MVPSN-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MVPSN-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE432MVPSN-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE232MVPSH-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE332MVPSH-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
General Electric	GE432MVPSH-V03			■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified

- System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
System performance blank field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

T8 Programmed-Start

UL Type A fixed output ballasts

		10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	16 W 1800 lm (4 ft.)	13W 2100 lm (U-Bent) ²
		541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	470096, 470104 470112, 470120	545178, 533372 545194, 545200	463133, 463141 463158, 468892	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Osram Sylvania	QHE 2X32T8/UNV PSN-MC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 3X32T8/UNV PSN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHE 4X32T8/UNV PSN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QHES 2X32T8/UNV PSL-SC							
Osram Sylvania	QHE 2X32T8/UNV PSH-HT						■ Certified	
Osram Sylvania	QHE 3X32T8/UNV PSH-HT-SC						■ Certified	
Osram Sylvania	QHE 4X32T8/UNV PSH-HT						■ Certified	
Hatch	HL232APS/UV/HE/W						■ Certified	
Hatch	HL332APS/UV/HE/W						■ Certified	
Hatch	HL432APS/UV/HE/W						■ Certified	
Hatch	HL232BPS/UV/HE/W						■ Certified	
Hatch	HL332BPS/UV/HE/W						■ Certified	
Hatch	HL432BPS/UV/HE/W						■ Certified	
Hatch	HL232CPS/UV/HE/W						■ Certified	
Hatch	HL332CPS/UV/HE/W						■ Certified	

T8 Programmed-Start

Dimmable ballasts

		10 W 1800 lm (4 ft. Glass)	14 W 2100 lm (4 ft. Glass)	13W 2100 lm (U-Bent) ²		
		541986, 541994 553214, 553222 553230, 553248	470096, 470104 470112, 470120	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888		
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Dimmers	
Advance	IZT-2S32-SC				Use Compatible 0-10V dimmer	
Advance	IZT-4S32				Use Compatible 0-10V dimmer	
Advance	REZ-132-SC				Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Advance	REZ-2S32-SC				Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
Advance	REZ-3S32-SC				Philips Lightolier - V1500EBUW	Lutron - MRF2-6ND-120
General Electric	GE132MVPSN-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSN-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSN-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSN-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE232MVPSH-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE332MVPSH-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	
General Electric	GE432MVPSH-V03	■ Certified	■ Certified	■ Certified	Use Compatible 0-10V dimmer	

- System performance ● **Certified** means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
System performance ■ **Certified** means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
System performance blank field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

Emergency ballasts

(contact the emergency ballast manufacturer for wiring diagrams)

			10.5W 1650 lm (4 ft.)	14.5W 2200 lm (4 ft.)	7 W 1050 lm (2 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	14 W 2100 lm (4 ft.)	13 W 2100 lm (4 ft.)	
			BAA	BAA	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	469320, 469338 469346, 469353 469452, 469478 469460, 539858 539874, 539882 539866	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966 473974, 473982 565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	473926, 473934 473942, 473958	
576777, 576785 576793	576801, 576819 576827											
Manufacturer	Ballast Model	# of lamps in emergency	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Bodine	(new) B50 (12 NC: 913702456401)	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	B5OCT	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Philips	PTA50	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	PEL12	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	LP600	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	LP600STU	1			Inadvisable	Inadvisable	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Philips Chloride	DEB-6LP	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-320	1 or 2			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-1605	1 or 2			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-162	2			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	ISL-54	1 or 2			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	ISL-540	1 or 2			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH7-UNV-500L	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH11-UNV-750L-xx	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH12-UNV-1400K-xx	1			● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified

T8 InstantFit

UL/CSA classified
with listed drivers

		14W 2100lm VLC	7 W 1050 lm (2 ft.)	8.5 W 1200 lm (3 ft.)	9 W 1200 lm (3 ft.)	8.9 W 1600 lm (4 ft.)	9.5 W 1600 lm (4 ft.)	10 W 1600 lm (4 ft.)	10 W 1800 lm (4 ft. Glass)	10.5W 1600 lm (4ft. Glass)	11.5 W 2100 lm (4ft. Glass)	12 W 1800 lm (4 ft. Glass)	13 W 2100 lm (4 ft.)
		529981, 529999	469270, 469288 469296, 469304 469429, 469445 469437, 541813 541821, 541839 541847	539858, 539866, 539874, 539882,	469320, 469338 469346, 469353 469452, 469478 469460	565580, 565598 565606, 565614	473974, 473982 473990, 474007 540807	468264, 468272 468280, 468298 468694, 469569 469577, 469585 469593, 473966	541986, 541994 553214, 553222 553230, 553248	BAA 576777, 576785, 576793	580266, 580274 580381	530469, 530477 530485, 530493	473926, 473934 473942, 473958
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2P13-TLED-N					● Certified	● Certified		● Certified				● Certified
Advance	ICN-2P15-TLED-N		● Certified	● Certified							● Certified		
Advance	ICN-2P16-TLED-N		● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-2P16-TLED-EL-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified		● Certified	● Certified
Advance	ICN-2P16-TLED-HL-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-3P13-TLED-N					● Certified	● Certified		● Certified				● Certified
Advance	ICN-3P15-TLED-N		● Certified	● Certified									
Advance	ICN-3P16-TLED-N		● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-4P13-TLED-N					● Certified	● Certified		● Certified				● Certified
Advance	ICN-4P15-TLED-N		● Certified	● Certified							● Certified		
Advance	ICN-4P16-TLED-N		● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-4P16-TLED-HL-SC	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IZT-2P15-TLED-N		● Certified	● Certified		● Certified			● Certified		● Certified		● Certified
Advance	IZT-2P16-TLED-SC		● Certified	● Certified		● Certified			● Certified	● Certified*		● Certified	● Certified
Advance	IZT-3P15-TLED-N		● Certified	● Certified		● Certified			● Certified		● Certified		● Certified
Advance	IZT-4P15-TLED-N		● Certified	● Certified		● Certified			● Certified		● Certified		● Certified
Advance	IZT-4P16-TLED-SC		● Certified	● Certified		● Certified	● Certified		● Certified				● Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
System performance blank field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

* This Driver is compatible for two(2) lamp configuration only.

Emergency ballasts

(contact the emergency ballast manufacturer for wiring diagrams)

			14 W 2100 lm (4 ft. Glass)	10 W 1800 lm (4 ft. Glass)	12 W 1800 lm (4 ft. Glass)	17W 2100 lm (4 ft. Glass)	16.5 W 2500 lm (4 ft.)	13W 2100 lm (U-Bent) ²	T5 HO	T5 HE
			470096, 470104 470112, 470120	541986, 541994 553214, 553222 553230, 553248	530469, 530477 530485, 530493	456566, 456574 472878, 472886 472894, 472902 472910, 472928 472936, 472944 472968, 472976 479782, 479790	463133, 463141 463158, 468892	469379, 469387 469395, 469403 469411, 470625 541854, 541862 541870, 541888	467126, 467134 467142, 467159	476499, 476507 476515, 476523
Manufacturer	Ballast Model	# of lamps in emergency	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Bodine	(new) B50 (12 NC: 913702456401)	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	B50CT	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Philips	PTA50	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	PEL12	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	LP600	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Bodine	LP600STU	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Philips Chloride	DEB-6LP	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-320	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-1605	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	I-162	2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	ISL-54	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota Engineering	ISL-540	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH7-UNV-500L	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH11-UNV-750L-xx	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham Co., Inc	FH12-UNV-1400K-xx	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified

T8 InstantFit

UL/CSA classified
with listed drivers

		14 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft. Glass)	15.5 W 2500 lm (4 ft.)	16.5 W 2500 lm (4 ft.)	13W 2100 lm (U-Bent) ²	13W 2100 lm (U-Bent) ²
		468306, 468314 468322, 468330 469061, 469619 469627, 469635 468652, 468660 468678, 468686	470096, 470104 470112, 470120	545178, 533372 545194, 545200	463133, 463141 463158, 468892	469379, 469387 469395, 469403 469411, 470625	541854, 541862 541870, 541888
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2P13-TLED-N					● Certified	● Certified
Advance	ICN-2P15-TLED-N			● Certified		● Certified	● Certified
Advance	ICN-2P16-TLED-N	● Certified	● Certified	● Certified	● Certified		● Certified
Advance	ICN-2P16-TLED-EL-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-2P16-TLED-HL-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-3P13-TLED-N						
Advance	ICN-3P15-TLED-N			● Certified			
Advance	ICN-3P16-TLED-N	● Certified	● Certified	● Certified	● Certified		
Advance	ICN-4P13-TLED-N						
Advance	ICN-4P15-TLED-N			● Certified			
Advance	ICN-4P16-TLED-N	● Certified	● Certified	● Certified	● Certified		
Advance	ICN-4P16-TLED-HL-SC	● Certified	● Certified	● Certified	● Certified		
Advance	I2T-2P15-TLED-N		● Certified	● Certified			● Certified
Advance	I2T-2P16-TLED-SC	● Certified	● Certified	● Certified	● Certified		● Certified
Advance	I2T-3P15-TLED-N		● Certified	● Certified			
Advance	I2T-4P15-TLED-N		● Certified	● Certified			
Advance	I2T-4P16-TLED-SC	● Certified	● Certified	● Certified	● Certified		

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
System performance blank field means consult factory.
2. Typical application for U-Bent lamps is with 2-lamp ballasts.

Non-T8 InstantFit

UL/CSA classified
with listed drivers

		T5HO 3500 lm (4 ft.)	35W 4200 lm (8ft Plastic)	28W 4200 lm (8ft Glass)	30W 4200 lm (8ft Glass)
		467126, 467134, 467142, 467159	469239, 469247, 469254, 469262	580282, 580290	533000, 533018, 533026, 533034
Manufacturer	Ballast Model	Perform ¹	Perform ¹	Perform ¹	Perform ¹
Advance	ICN-2S24-TLED-90C-N	● Certified			
Advance	ICN-4S24-TLED-90C-2LS-G	● Certified			
Advance	ICN-2P35-TLED-N		● Certified	● Certified	● Certified

PL-L ballasts

		16.5 W 2100 lm (PL-L 2 ft.)	16.5 W 2300 lm (PL-L 2 ft.)
		456632, 456640, 456657	532895, 532903, 532911
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Advance	ICN-1TTP40-SC	● Certified	● Certified
Advance	ICN-2TTP40-SC	● Certified*	● Certified*
Advance	ICN-3TTP40-SC	● Certified	
Advance	ICN-2S24-N		● Certified
Advance	ICN-2S24-T		● Certified
Advance	ICN-2S39-N		● Certified
Advance	ICN-2S39-T		● Certified
Advance	ICF-2S42-M2-BS		● Certified
Advance	ICF-2S42-M2-LD		● Certified
Advance	ICF-2S42-90C-M2-BS		● Certified
Advance	ICF-2S42-90C-M2-LD		● Certified
Advance	IZT-2TTS40-SC		● Certified
General Electric	GE140MAX-A	■ Certified	■ Certified
General Electric	GE240MAX-A	■ Certified	■ Certified
General Electric	GE340MAX-A	■ Certified	■ Certified
General Electric	GEC242-MVPS		■ Certified
General Electric	GEC240MVPS-A		■ Certified
General Electric	GEC225MVPS-A		■ Certified
Osram Sylvania	QHE1X40DL/UNV ISN-SC	■ Certified	■ Certified
Osram Sylvania	QHE2X40DL/UNV ISN-SC	■ Certified	■ Certified
Osram Sylvania	QHE3X40DL/UNV ISN-SC	■ Certified	■ Certified
Osram Sylvania	QTP 1x40TT5/277 PSN-F		■ Certified
Osram Sylvania	QTP 2x40TT5/120 PSN-F		■ Certified
Osram Sylvania	QTP 2x40TT5/277 PSN-F		■ Certified
Osram Sylvania	QTP 3x40TT5/120 PSN-B		■ Certified
Osram Sylvania	QTP 3x40TT5/277 PSN-B		■ Certified
Osram Sylvania	QTP 2X26/32/42CF/UNV DM		■ Certified

* Not recommended for one(1) lamp 277V operation.

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer. System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only. System performance blank field means consult factory.

PL-C / T 4-pin ballasts

UL/CSA classified with listed drivers

		Vertical Lamp 10.5W	Horizontal Lamp 8.5W	Vertical Lamp 12W	Horizontal Lamp 12W	Vertical Lamp 5.5W	Horizontal Lamp 5.5W
		458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	532432, 532440 532457, 532465	532390, 532408 532416, 532424
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICF-2S13-M1-BS	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICF-2S13-H1-LD	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICF-2S13-M1-BS-QS	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICF-2S26-H1-LD	● Certified	● Certified*	● Certified	● Certified*		
Advance	ICF-2S26-M1-BS	● Certified	● Certified*	● Certified	● Certified*		
Advance	ICF-2S26-M1-BS-QS	● Certified	● Certified	● Certified	● Certified		
Advance	ICF-2S18-H1-LD	● Certified	● Certified	● Certified	● Certified		
Advance	ICF-2S18-M1-BS	● Certified	● Certified	● Certified	● Certified		
Advance	ICF-2S18-M1-BS-QS	● Certified	● Certified	● Certified	● Certified		
Advance	ICF-2S42-M2-LD	● Certified	● Certified	● Certified**	● Certified**		
Advance	ICF-2S42-M2-BS	● Certified	● Certified	● Certified**	● Certified**		
Advance	ICF-2S42-90C-M2-BS	● Certified	● Certified	● Certified**	● Certified**		
Advance	ICF-2S42-90C-M2-LD	● Certified	● Certified	● Certified**	● Certified**		
Advance	IZT-2S26-M5-LD	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	REB-113-M6-EL	● Certified	● Certified	● Certified	● Certified		
Advance	REB-113-M6-BLS					● Certified	● Certified
Advance	REB-118-M6-BLS	● Certified	● Certified	● Certified	● Certified		
Advance	REB-2S18-M6-EL	● Certified	● Certified	● Certified	● Certified		
Advance	REB-126-M6-BLS	● Certified	● Certified	● Certified	● Certified		
General Electric	GEC218-MVPS-SE	■ Certified	■ Certified	■ Certified	■ Certified		
General Electric	GEC226-MVPS-3W	■ Certified	■ Certified	■ Certified	■ Certified		
General Electric	GEC242-MVPS-SE	■ Certified	■ Certified	■ Certified	■ Certified		
Univ. Lighting Tech.	C213UNVME					■ Certified	■ Certified
Univ. Lighting Tech.	C218UNVME	■ Certified	■ Certified	■ Certified	■ Certified		

* This ballast is compatible for two(2) lamp horizontal configuration only.

** When used with one(1) lamp, can only be operated at 120V.

PL-S/C Ballasts 2-pin ballasts

(UL/CSA classified with the listed ballasts)

		Horizontal Lamp PLS 5W	Vertical Lamp PLC 5W	Horizontal Lamp PLC 5W
		529511, 529560 529578, 529586	532358, 532366 532374, 532382	532309, 532317 532333, 532341
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Advance	VH-1B13-TP-W	● Certified	● Certified	● Certified
Advance	H-1B13-TP-W	● Certified	● Certified	● Certified
Advance	VLO-13-TP	● Certified	● Certified	● Certified
Advance	H-2B13-TP-BLS	● Certified	● Certified	● Certified
Advance	LC-13-TP	● Certified	● Certified	● Certified
Robertson	S1P	■ Certified	■ Certified	■ Certified
Robertson	O1527P(3P10104)	■ Certified*	■ Certified*	■ Certified*
Robertson	HP213P(3P10073)	■ Certified	■ Certified	■ Certified

* This ballast is compatible for one(1) lamp configuration only.

** Lamps are only compatible when used with a parallel wiring configuration.

PL-C / T 4-pin ballasts

UL/CSA classified with listed drivers

		Vertical Lamp 10.5W	Horizontal Lamp 8.5W	Vertical Lamp 12W	Horizontal Lamp 12W	Vertical Lamp 5.5W	Horizontal Lamp 5.5W
		458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	532432, 532440 532457, 532465	532390, 532408 532416, 532424
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Univ. Lighting Tech.	C2642UNVME	■ Certified	■ Certified	■ Certified	■ Certified		
Univ. Lighting Tech.	C242UNVME	■ Certified	■ Certified	■ Certified	■ Certified		
Univ. Lighting Tech.	C218UNVBE	■ Certified	■ Certified	■ Certified	■ Certified		
Univ. Lighting Tech.	C2642UNVBE	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 1/2X18CF/UNV DM	■ Certified	■ Certified	■ Certified	■ Certified		
Osram Sylvania	QTP 2X26CF/UNV DM						
Osram Sylvania	QTP2x26CF/UNV	■ Certified	■ Certified	■ Certified	■ Certified		
Howard Industries	EP2/26CF/MV/2	■ Certified	■ Certified	■ Certified	■ Certified		
Howard Industries	EP2CF26PS/MV/DC/K	■ Certified	■ Certified	■ Certified	■ Certified		
Motorola	M2-CF-26-B-S-277	■ Certified	■ Certified	■ Certified	■ Certified		
Keystone	KTEB-226-UV-RS-DW	■ Certified	■ Certified	■ Certified	■ Certified		
Fulham	WH2-120-C					■ Certified	■ Certified
Fulham	WH2-120-L					■ Certified	■ Certified
Fulham	NPY-120-226-CFL	■ Certified	■ Certified	■ Certified	■ Certified		
Robertson	RED1L10-120H	■ Certified	■ Certified	■ Certified	■ Certified		
ACE	CSD-332PBM	■ Certified	■ Certified	■ Certified	■ Certified		
Hatch	HC226PS/UV/D	■ Certified	■ Certified	■ Certified	■ Certified		
Deltek	CFL226MVRSL	■ Certified	■ Certified	■ Certified	■ Certified		
Espen	VE226120MR-1						
Sunpark	LC 12010T					■ Certified	■ Certified
Sunpark	SL15T	■ Certified	■ Certified	■ Certified	■ Certified		
Topstar Premium	BB-PL/UNH-1/2X26-1X42	■ Certified	■ Certified	■ Certified	■ Certified		
Topstar Premium	BB-PL/UVH-1/2X13-18	■ Certified	■ Certified	■ Certified	■ Certified		
Antron	16X952 CSD-113PNPF	■ Certified	■ Certified	■ Certified	■ Certified		
Standard	E528-120V/STD/EOL	■ Certified	■ Certified	■ Certified	■ Certified		
Radionic	RPL26-42R-M	■ Certified	■ Certified	■ Certified	■ Certified		
DAMAR	23350D					■ Certified	■ Certified

Emergency PL-C / T 4-pin ballasts

UL/CSA classified with listed drivers

			Vertical Lamp 18W/26W	Horizontal Lamp 18W/26W	Vertical Lamp 32W	Horizontal Lamp 32W	Vertical Lamp 32W	Horizontal Lamp 32W
			458406, 458414 458422, 458430	458364, 458372 458380, 458398	476101, 476119 476127, 476135	476069, 476077 476085, 476093	476101, 476119 476127, 476135	476069, 476077 476085, 476093
Manufacturer	Ballast Model	# of lamps in emergency	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Iota	I-42	1 or 2		● Certified		● Certified		● Certified
Iota	I-420	1	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota	I-420	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Iota	I-160	1	● Certified		● Certified		● Certified	
Iota	I-160	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham	FH11-UNV-750L	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Fulham	FH12-UNV-1400L	1 or 2	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.

T12 Electronic ballasts

		13 W 2100 lm (4 ft.)	14 W 2100 lm (4 ft.)	16 W 1800 lm (4 ft.)
		473926, 473934 473942, 473958	468306, 468314 468322, 468330 469061, 469619 469627, 469635	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2S40-N	● Certified	● Certified	● Certified
Advance	RELB-2S40-N	● Certified	● Certified	● Certified

T12 Rapid-Start Magnetic ballasts

		20 W 2100 lm (4 ft.)	16 W 1800 lm (4 ft.)
		463117, 463125	UniversalFit 539972, 539980 539148, 539155 539163, 542688 542696, 542704 565572, 565564 565556
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Advance	R-140-1-TP	● Certified	● Certified
Advance	X-140-TP	● Certified	● Certified
Advance	R-2S40-1-TP	● Certified	● Certified
Advance	XQM-2S40-TP	● Certified	● Certified
Advance	V-2S40-1-TP	● Certified	● Certified
Advance	RQM-2S40-3-TP	● Certified	● Certified
Advance	R-2S34-TP-5	● Certified	● Certified
Advance	V-2S34-TP	● Certified	● Certified
Advance	RM-2S35-TP	● Certified	● Certified
General Electric	GEM240RS277	■ Certified	■ Certified
General Electric	GEM240RS120 -1	■ Certified	■ Certified
Howard Industries	M1/40RS-120	■ Certified	■ Certified
Howard Industries	M2/40RS-277	■ Certified	■ Certified
Howard Industries	M2/40RS-240 -1	■ Certified	■ Certified
Universal Lighting Tech.	412-L-SLH-TC-P	■ Certified	■ Certified
Universal Lighting Tech.	458-L-SLH-TC-P	■ Certified	■ Certified
Universal Lighting Tech.	540-L-TC-P	■ Certified	■ Certified
Universal Lighting Tech.	CAT.NO.446-L-LH-TC-P-7	■ Certified	■ Certified
Universal Lighting Tech.	443-L-SLH-TC-P	■ Certified	■ Certified
Universal Lighting Tech.	446-L-SLH-TC-P	■ Certified	■ Certified
Osram Sylvania	MB1x40/277 RS-1	■ Certified	■ Certified
Osram Sylvania	MB1x40/120RS-1	■ Certified	■ Certified
Osram Sylvania	MB2x40/120RS-1	■ Certified	■ Certified
Osram Sylvania	MB2x40/277RS-1	■ Certified	■ Certified
Industrias Sola Basics S A DE C V	E420-F-234 IC -1	■ Certified	■ Certified
Radionic Industries Inc.	CAT.NO.ES240HTP	■ Certified	■ Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer. System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only. System performance blank field means consult factory.

T5 HO ballasts

		580225	576710, 576736 576744	467126, 467134 467142, 467159
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2S54-N	● Certified	● Certified	● Certified
Advance	ICN-2S54-90C-N	● Certified	● Certified	● Certified
Advance	ICN-2S54-T	● Certified	● Certified	● Certified
Advance	ICN-2S54-90C-T	● Certified	● Certified	● Certified
Advance	ICN-2S54-N(L)	● Certified	● Certified	● Certified
Advance	ICN-4S54-90C-2LS-G	● Certified	● Certified	● Certified
Advance	HCN-2S54-90C-WL	● Certified	● Certified	● Certified
Advance	HCN-4S54-90C-2LS-G	● Certified	● Certified	● Certified
Advance	IZT-2S54-D	● Certified	● Certified	● Certified
Advance	IZT-1S4-D	● Certified	● Certified	● Certified
Advance	REZ-2S54	● Certified	● Certified	● Certified
General Electric	GE254MVPS-A	■ Certified	■ Certified	■ Certified
General Electric	GE254MVPS-D	■ Certified	■ Certified	■ Certified
General Electric	GE454MVPS90-E-S	■ Certified	■ Certified	■ Certified
General Electric	GE454MVPS90-F	■ Certified	■ Certified	■ Certified
General Electric	GE454MVPS90-G	■ Certified	■ Certified	■ Certified
General Electric	GE254MVPS90-A	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN HT	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2x54T5HO/UNV PSN(L)	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 2X54T5HO/UNV PSN HT	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B254PUNV-D	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B254PUNVHB-D	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B454PUNV-E	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B454PUNVHB-E	■ Certified	■ Certified	■ Certified
Hatch	HL454HO/PS/UV/W	■ Certified	■ Certified	■ Certified
Hatch	HL254HO/PS/UV/W	■ Certified	■ Certified	■ Certified
ESPEN	VE254MVHRP	■ Certified	■ Certified	■ Certified
ESPEN	VE454MVHRP	■ Certified	■ Certified	■ Certified
Fulham	RHA-UNV-254-LT5	■ Certified	■ Certified	■ Certified
Fulham	RHA-UNV-454-LT5	■ Certified	■ Certified	■ Certified
Keystone Inc.	KTEB-254HO-UV-PS-SL	■ Certified	■ Certified	■ Certified
Keystone Inc.	KTEB-454HO-UV-TP-PS	■ Certified	■ Certified	■ Certified
Sunpark	U-2/54T5HO	■ Certified	■ Certified	■ Certified
MAGG	2x54W LFL T5 AFP	■ Certified	■ Certified	■ Certified

T5 HE ballasts

		8 W 1050 lm (2 ft. Glass)	11 W 1500 lm (3 ft. Glass)	14 W 2100 lm (4 ft. Glass)	8 W 1050 lm (2 ft. Glass)	11 W 1500 lm (3 ft. Glass)	14 W 2100 lm (4 ft. Glass)
		476416, 476424 476432, 476440	476457, 476465 476473, 476481	476499, 476507 476515, 476523	476416, 476424 476432, 476440	476457, 476465 476473, 476481	476499, 476507 476515, 476523
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2S24-N	● Certified	● Certified		● Certified	● Certified	
Advance	ICN-2S24-T	● Certified	● Certified		● Certified	● Certified	
Advance	ICN-2S28-N	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	ICN-2S28-T	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	GCN-2S28-L	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	IZT-128-D	● Certified	● Certified	● Certified			
Advance	IZT-2S28-D	● Certified	● Certified	● Certified	● Certified	● Certified	● Certified
Osram Sylvania	QHE 2X39-24T5HO/UNV PSN	■ Certified	■ Certified		■ Certified	■ Certified	
Osram Sylvania	QTP 2X28T5/UNV PSN	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QHE 2X28T5/UNV PSN	■ Certified*	■ Certified*	■ Certified	■ Certified*	■ Certified*	■ Certified
General Electric	GE228MVPS-MC	■ Certified*	■ Certified*	■ Certified*	■ Certified*	■ Certified*	■ Certified*
General Electric	GE228MVPS-MC-H	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B224PUNV-C	■ Certified	■ Certified		■ Certified	■ Certified	
Universal Lighting Tech.	B228PUNV-C	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B228PUNV-N	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B228PUNV85-D	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Universal Lighting Tech.	B239PUNV-D	■ Certified*	■ Certified*		■ Certified*	■ Certified*	
Keystone	KTEB-228HE-UV-PS	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Keystone	KTEB-228HE-UV-PS-SL	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Fulham	RHA-UNV-228-LT5	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Robertson	PSA228T5MV	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified

1. System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer.
 System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only.
 System performance blank field means consult factory.

* This ballast is compatible for two(2) lamp configuration only.

LATAM T8 ballasts

		7W 1150 lm (2 ft.)	10W 1600lm (4 ft.)	13W 2100lm (4 ft.)	17W 2100lm (4 ft.)	13W 2100lm (U-Bent) ²
		929001311004 929001311104	929001397404 929001397504	929001397804 929001397904	929001343503	929001311804 929001311904 929001312004 929001312104
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹	Performance ¹	Performance ¹
Advance	ICN-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	RES-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified
Advance	REM-2P32-N	● Certified	● Certified	● Certified	● Certified	● Certified
ISB Sola Basic	758-232-MC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ISB Sola Basic	758-432-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ISB Sola Basic	758-U-432-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ISB Sola Basic	E-758-U-232-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
ISB Sola Basic	E18-232	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Magg	B04341	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 1X32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QTP 2X32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	■ Certified
Osram Sylvania	QTP 3X32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	
Osram Sylvania	QTP 4X32T8/UNV ISN-SC	■ Certified	■ Certified	■ Certified	■ Certified	

T8 /T12 8' Slimline ballasts

		28W 4200lm (8ft Glass)	35W 4200 lm (8ft Plastic)	30W 4200 lm (8ft Glass)
		580282, 580290	469239, 469247 469254, 469262	533000, 533018 533026, 533034
Manufacturer	Ballast Model	Performance ¹	Performance ¹	Performance ¹
Advance	IOP-2P59-N	● Certified	● Certified	● Certified
Advance	ICN-2P60-N	● Certified	● Certified	● Certified
General Electric	GE259MAX-L/ULTRA	■ Certified	■ Certified	■ Certified
General Electric	GE259MAXP-N/ULTRA	■ Certified	■ Certified	■ Certified
General Electric	GE-259-MV-N 30194		■ Certified	■ Certified
General Electric	GE259MAX-G-N 74469	■ Certified	■ Certified	■ Certified
General Electric	GE259MAXP-N-DIY 23954	■ Certified	■ Certified	■ Certified
Howard Industries	EP2/59IS/MV/MC/HE		■ Certified	■ Certified
Howard Industries	E2/75IS-120MC		■ Certified	■ Certified
Fulham	WH5-277-L		■ Certified	■ Certified
Universal Lighting Tech.	B260IUNVHP		■ Certified	■ Certified
Universal Lighting Tech.	B260I120M-A	■ Certified	■ Certified	■ Certified
Osram Sylvania	OSRAM QT 2X96/120 IS		■ Certified	■ Certified
Osram Sylvania	OSRAM QT 2X96/277 IS		■ Certified	■ Certified
Osram Sylvania	2X75W T12(96)		■ Certified	■ Certified
Industrias Sola Basics S A DE C V	EIO-260-MC	■ Certified	■ Certified	■ Certified
Industrias Sola Basics S A DE C V	EOI-230/32-MC	■ Certified	■ Certified	■ Certified

- System performance ● Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp and ballast manufacturer. System performance ■ Certified means Philips InstantFit LED T8 lamps and ballasts have been evaluated by the lamp manufacturer only. System performance blank field means consult factory.
- Typical application for U-Bent lamps is with 2-lamp ballasts.

LATAM FA8 ballasts

		13W 1600lm (4 ft.)	26W 3200lm (8 ft.)
		929001273412	929001273612
Manufacturer	Ballast Model	Performance ¹	Performance ¹
Advance	ICN-2P59-N	● Certified	● Certified
Advance	REL-275-N	● Certified	● Certified
Advance	REL-239-N	● Certified	● Certified
ISB Sola Basic	758-U-259-SC	■ Certified	■ Certified
ISB Sola Basic	12-EI-139	■ Certified	■ Certified
ISB Sola Basic	EIO-230/232-MC	■ Certified	■ Certified
ISB Sola Basic	758-259-SC	■ Certified	■ Certified
ISB Sola Basic	EIO-U-260-SC	■ Certified	■ Certified
ISB Sola Basic	EIO-260-MC	■ Certified	■ Certified



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-16118CR 08/23 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.