



**PHILIPS**

LED lamps


Field Selectable Products



Field selectable  
lamps price guide

July 2024





With the unique convenience of adjustable color temperatures and/or lumen outputs, our new field selectable product line makes it easy to always have the right product for the job.



**Flex Fit (Hor/Ver adj.) PLED lamps** with selectable CCT



**Flex Fit. TLED lamps** with selectable CCT



**MainsFit CorePro TLED lamps** with selectable CCT



**MainsFit CorePro PLED lamps** with selectable CCT



**MasterClass LED corn cob lamps** with selectable CCT & LMs



**MasterClass high wattage LED corn cob lamps** with selectable CCT

Field Selectable products give you the added benefit of carrying one SKU versus multiple SKUs, keeping your inventory low and turns high. These field selectable products are priced right and are all part of our Ready to go offering!

Learn more about additional Ready to go offerings at:  
[www.philips.com/LEDlamps](http://www.philips.com/LEDlamps)

# Philips field selectable products



## FlexFit (Type A+B) TLED and PLED lamps with selectable CCT

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Price
588624	929003794504	7.5T8/COR/24-5CCT/FF11/G/DIM 25/1	7.5	1100	82	3000/3500/4000/5000/6500	50,000	
588632	929003794604	10.5T8/COR/36-5CCT/FF15/G/DIM 25/1	10.5	1500	82	3000/3500/4000/5000/6500	50,000	
588640	929003794704	12T8/COR/48-5CCT/FF18/G/DIM 25/1	12	1800	82	3000/3500/4000/5000/6500	50,000	
589788	929003807304	16PL-C/T/COR/42HV-5CCT/FF18/4P 50/1	16	1850	82	2700/3000/3500/4000/5000	50,000	



## MainsFit CorePro (UL Type-B) TLED lamps with selectable CCT (120-277V) 240° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Wts (W)	Lumens (lm)	CRI (min)	CCT (K)	Life <sup>1</sup> (hrs)	Price
579672	929003540104	14.5T8/COR/48-5CCT/MF18/G/DIM 25/1	14.5	1800	82	3000/3500/4000/5000/6500	50,000	
589804	929003815504	43T8/COR/96-5CCT/MF52LS/G/FA8-R17D 10/1	43	3400/4300/5200	82	3000/3500/4000/5000/6500	50,000	



## MainsFit CorePro PLED lamps with selectable CCT (120-277V) 120° beam angle

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	MOL (in)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Price
577890	9290034776	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	8	5.9	975/1000/1050	83	3000/3500/4000	30,000	
577908	9290034777	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	8	4.7	975/1000/1050	83	3000/3500/4000	30,000	
577916	9290034778	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	11	5.9	1425/1450/1500	83	3000/3500/4000	30,000	
577924	9290034779	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	11	4.7	1425/1450/1500	83	3000/3500/4000	30,000	



## MasterClass LED corn cob HID replacement lamps with selectable CCT & Lumens

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Price
570465	929003065204	36CC/LED/3CCT/LS EX39 G3 BB 3/1	36	150 (100-150)	4800/5000/5000	80	3000/4000/5000	50,000	
570473	929003065304	45CC/LED/3CCT/LS EX39 G3 BB 3/1	45	175 (150-175)	5800/6200/6200	80	3000/4000/5000	50,000	
570481	929003065404	54CC/LED/3CCT/LS EX39 G3 BB 3/1	54	250 (150-250)	7000/7500/7500	80	3000/4000/5000	50,000	
570499	929003065504	63CC/LED/3CCT/LS EX39 G3 BB 3/1	63	250 (175-250)	7800/8500/8500	80	3000/4000/5000	50,000	



## MasterClass high wattage LED corn cob lamps with selectable CCT

Product No. (6nc)	Model No. (12nc)	Description	Watts (W)	Replace Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime <sup>1</sup> (hrs)	Price
583682	929003631404	80CC/LED/3CCT/LS EX39 BB 3/1	80	250	11500/12000/12000	80	3000/4000/5000	50,000	
583690	929003631504	115CC/LED/3CCT/LS EX39 BB 3/1	115	320	15800/17000/17000	80	3000/4000/5000	50,000	
583708	929003631604	145CC/LED/3CCT/LS EX39 BB 3/1	145	400	20500/22000/22000	80	3000/4000/5000	50,000	

1. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.

MasterClass corn cob LED HID replacement lamps are damp location rated and suitable for enclosed fixtures



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLt-2158BR 07/24 [philips.com/LEDlamps](https://philips.com/LEDlamps)

Signify North America Corp.  
400 Crossing Blvd, Suite 600  
Bridgewater, NJ 08807  
Telephone: 800-555-0050

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone: 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.