



Type A



PAR



BR



Candle



G25 / ST19
Miscellaneous

Contents

Type A lamps 1 – 8

PAR lamps 9 – 15

BR lamps 16 – 18

Candles 19 – 23

Misc. (G25,ST19) 24 – 26

Type A lamps

Number of bulbs

											
		14A19 CNG FR P D	8A19/PER/UD/FR/G/E26/WGD 4/2PFT20	16A19/PER/927-950/P/E26/DIM 6/1FB T20	8A19 CNG FR P E26 D	3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	5A15/PER/UD/CL/G/E12/WGD 6/2PF T20	3.8A15/PER/927-922/CL/G/E12/WGX1FB T20	3.8A15/PER/927-922/CL/G/E26/WGX1FB T20	12A19/LED/927-930-950/FR/Glass/E26/DIM 1FB T20	9.5A19/LED/927-930-950/FR/Glass/E26/DIM 1FB T20
		9290035850 (581801) 9290035851 (581827) 9290035852 (581835) 9290035853 (581868)	9290030832 (573436)	9290023855 (561068) 9290023856 (561076) 9290023857 (561456) 9290022853 (561019) 9290022855 (561027)	9290035795 (581751) 9290035796 (581785) 9290035848 (581785) 9290035849 (581777)	9290030845 (573402)	9290029868 (564450) 9290029865 (564385)	9290022081 (549378)	9290022083 (549386)	9290034982 (578617) 9290034983 (578625) 9290034984 (578633)	9290034979 (578583) 9290034980 (578591) 9290034981 (578609)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-10	1-10	1-9	1-18			1-10	1-10	1-10	1-10
Leviton	6631	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6633	1-10	2-10	1-9	1-18	1-10	1-10	2-10	2-10	1-10	1-10
Leviton	6672	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6674	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6615P	1-10	NR		NR	NR	NR	NR	NR	1-6	1-8
Leviton	DSE06										
Leviton	DSL06	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	DSM10										
Leviton	IPI06	1-10	1-10	NR	1-18	1-10	1-10	2-10	2-10	1-10	1-10
Leviton	IPL06	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	AYCL-153P		1-10	1-9							
Lutron	CTCL-153P		1-10	1-9							
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-10	1-10	1-9	1-18			1-10	1-10	1-10	1-10
Lutron	DV-600PR										
Lutron	DVCL-153P	1-10	1-10	1-9	1-18	1-10	1-10				
Lutron	DVCL-253P		1-10								
Lutron	DVELV-300P	1-10	1-10	1-9	1-18			1-10	1-10		
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-10	1-10	1-9	1-18			1-10	1-10	1-10	1-10
Lutron	NTCL-250		1-10	1-9							
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-10	1-10	1-9	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-10	1-10	1-9	1-18	1-10	1-10			1-10	1-10
Lutron	S-600P										
Lutron	SCL-153P		1-10	1-9							
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-10	1-10	1-7	1-18	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M			1-9		1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MSCL-OP153MH	1-10		1-9	1-18	1-10	1-10	1-10	1-10		
Lutron	MS-OPS2H										
Panel Modules											
Lutron	GP (Harrier) Card	1-10	1-10	1-9	NR						
Lutron	HW-RPM-4A-120										
Lutron	HW-RPM-4U-120										
Lutron	LP-RPM-4U-120										

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

											
		8A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	5A19/LED/927-930-950/ FR/Glass/E26/DIM 1FB T20	T20 Bulb A19 120V 16-100W 1600lm 2700-2200K E26 D	12.2A19 WG & DIM T20	16A19 WG & DIM T20	29W A21 DIM & WG Lamp	5A19/PER/927-22/FR/G/ WGX 4/2FB T20	4A19/MOD/840/E26/CL/ GL/DIM 4/1BC	16A21/PER/930/P/ GU24/DIM 6/1FB T20	8.8A19/PER/930/P/ GU24/DIM 6/1FB T20
		9290034976 (578567) 9290034977 (578575) 9290034978 (578641)	9290034973 (578534) 9290034974 (578542) 9290034975 (578559)	9290022855 (815163)	9290022854 (561000) 9290023852 (561035) 9290023853 (561043) 9290023854 (561050) 9290022852 (560994)	9290022855 (561027) 9290023855 (561068) 9290023856 (561076) 9290023857 (561456) 9290022853 (561019)	9290023430 (558221) 9290023431 (558239)	9290023278 (557595)	9290020007 (543116)	9290023276 (557678)	9290023275 (557660)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-10		1-10	1-15	1-10	1-5		1-3	1-9	1-17
Leviton	6631	1-10	1-10	1-10	1-15	1-10	1-5	1-27		1-9	1-17
Leviton	6633	2-10	1-10	1-10	1-15	1-10	1-5	1-27	2-3	1-9	1-17
Leviton	6672	1-10	1-10	1-10	1-15	1-10	1-5	1-27	1-5	1-9	1-17
Leviton	6674	1-10	1-10	1-10	1-15	1-10	1-5	1-27		1-9	1-17
Leviton	6615P	NR	NR	1-5	1-8	1-5	1-3		2-5	1-5	1-9
Leviton	DSE06										
Leviton	DSL06	1-10	1-10	1-20	1-20	1-20	1-10	1-30		1-19	1-20
Leviton	DSM10										
Leviton	IPI06	1-10	1-10	1-10	1-15	1-10	1-5	1-27	1-10	1-9	1-17
Leviton	IPL06	1-10	1-10	1-10	1-15	1-10	1-5	1-27		1-9	1-17
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-10		1-10	1-15	1-10	1-5		1-10	1-9	1-17
Lutron	DV-600PR										
Lutron	DVCL-153P	1-10	1-10								
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-9		1-5	1-8	1-5	1-3	1-27	1-10	1-9	1-9
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-10	1-10	1-10	1-15	1-10	1-5	1-27	1-10	1-9	1-17
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-10		1-10	1-15	1-10	1-5		1-10	1-9	1-17
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-10	1-10	1-10	1-15	1-10	1-5	1-27	NR	1-9	1-17
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-10	1-10	1-10	1-15	1-10	1-5		1-10	1-9	1-17
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-10	1-10	1-8	1-10	1-8	1-4	1-20	1-2	1-7	1-13
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-10	1-10	1-10	1-15	1-10	1-5	1-27	1-10	1-9	1-17
Lutron	MSCL-OP153MH			1-10	1-15	1-10	1-5	1-27	NR	1-9	1-17
Lutron	MS-OPS2H								1-10		
Panel Modules											
Lutron	GP (Harrier) Card								1-10		
Lutron	HW-RPM-4A-120								1-10		
Lutron	HW-RPM-4U-120								1-10		
Lutron	LP-RPM-4U-120								1-10		

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

											
		16A21/PER/827-22/P/E26/WG	16w A21 WG & CG bulb	8.8w Dimmable A19 Filament T20	8.5w(60w Eq) WG A19 Filament T20	4.5w(40w Eq) WG A19 Filament T20	8w WG A19 Filament	4.5w(40w) A19 Filament (dimmable)	5w A19 WG & CG, P0022267, 2019Q1	8.8w (60w Eq) A21 WG & CG, P0022267, 2019Q1	12w (75w Eq) WG & CG T20, P0022267, 2019Q1 WG, 2019Q2 CG
		9290018377 9290018377A (479485, 479402, 479535)	9290019413 9290020073 9290019413A 9290020073A	9290022079 (549238) 9290022078 (549220)	9290019696 (549493) 9290019695 (549485)	9290019509 (537563)	9290019334 (536920)	9290012101 (461665)	9290019407 (479428) 9290020070	9290019409 (479444) 9290020071	9290019411 (479469) 9290020072
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-3	1-9	1-15		3-20	1-10	3-20	1-20	1-16	1-10
Leviton	6631				1-18						
Leviton	6633	1-3	1-9	1-15	1-18	2-20	1-10	2-20	1-20	1-16	1-10
Leviton	6672	1-3	1-9	1-15	1-18	1-20	1-10	1-20	1-20	1-16	1-10
Leviton	6674				1-18						
Leviton	6615P	1-3	NR	1-9		1-20	1-9	1-20	1-14	1-8	3-6
Leviton	DSE06										
Leviton	DSL06				1-30						
Leviton	DSM10										
Leviton	IPI06	1-3	1-9	1-15	1-18	4-20	1-10	4-20	1-20	1-16	1-10
Leviton	IPL06				1-18						
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-3	1-9	1-15		1-20	1-10	1-20	1-20	1-16	1-10
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-3	1-5	1-9	1-9	1-20	1-10	1-20	1-14	1-8	1-6
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-3	1-9	1-15	1-18	1-20	1-10	1-20	1-20	1-16	1-10
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-3	1-9	1-15		1-10	1-3	1-10	1-20	1-16	1-10
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-3	1-9	1-15	1-18	3-20	1-10	3-20	1-20	1-16	1-10
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-3	1-9	1-15		1-20	1-10	1-20	1-20	1-16	1-10
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-3	1-7	1-15	1-13	1-20	1-10	1-20	1-20	1-12	1-9
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-3	1-9	1-15	1-18	1-20	1-10	1-20	1-20	1-16	1-10
Lutron	MSCL-OP153MH			2-15	1-18	1-20	1-10	1-20			
Lutron	MS-OPS2H			1-15		1-20	1-10	1-20			
Panel Modules											
Lutron	GP (Harrier) Card			1-10		1-20	1-10	1-20			
Lutron	HW-RPM-4A-120			1-5		1-20	1-10	1-20			
Lutron	HW-RPM-4U-120			1-5		1-20	1-10	1-20			
Lutron	LP-RPM-4U-120			1-5		1-20	1-10	1-20			

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

											
		5w (40w Eq) A19, T20, P0024994, 2019 Q2	8.8w (60w Eq) A19, T20, P0024994, 2019 Q2	12.2w (75w Eq) A21 T20, P0024994, 2019 Q2	16w (100w Eq) A21 T20, P024994, 2019 Q2	16w(100w Eq) A21	12w(75w Eq) A21	9.5w(60w Eq) A19	9.5w(60w Eq) A19 WG	5.5w(40w Eq) A19	5.5W(40W Eq) A15 Clear WG
		9290020357 (550400) 9290020358 (550418) 9290020359 (547042) 9290020360 (550426)	9290020361 (550434) 9290020362 (550442) 9290020323 (545897) 9290020363 (550459)	9290020364 (550475) 9290020365 (550483) 9290020366 (547091) 9290020367 (550491)	9290020368 (550509) 9290020369 (550517) 9290020370 (547125) 9290020371 (550525)	9290018368 (479881) 9290018369 (479899) 9290018370 (479493)	9290018873 (479873) 9290018668 (532993) 9290018367 (479477)	9290018363 (479857) 9290018364 (479865) 9290018365 (479451)	9290018371 (479428) 9290018361 (479840) 9290018669 (532985) 9290018362 (479436)	9290018373 (479444)	9290012150 (462529)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Leviton	6631										
Leviton	6633	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Leviton	6672	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Leviton	6674										
Leviton	6615P	2-15	1-9	1-6	1-5	1-5	1-6	NR	1-8	1-14	1-13
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	1-20	1-17	1-12	1-9	1-9	1-13	NR	1-15	1-15	1-25
Leviton	IPL06										
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-15	1-9	1-6	1-5	1-9	1-6	1-15	1-8	1-15	1-13
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	NR
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	NR
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-20	1-13	1-9	1-7	1-7	1-9	1-8	1-15	1-5	1-19
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-20	1-17	1-12	1-9	1-9	1-13	1-15	1-15	1-15	1-25
Lutron	MSCL-OP153MH					1-9	1-13	1-15	1-15	1-15	1-25
Lutron	MS-OPS2H					1-9	1-13	1-15	1-15	1-15	1-25
Panel Modules											
Lutron	GP (Harrier) Card					1-15	1-15	1-15	1-15	1-15	1-25
Lutron	HW-RPM-4A-120					1-15	1-15	1-15	1-15	1-15	
Lutron	HW-RPM-4U-120					1-15	1-15	1-15	1-15	1-15	
Lutron	LP-RPM-4U-120					1-15	1-15	1-15	1-15	1-15	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

											
		7W(40W Eq) A15 CC WG	4.5W(60W Eq) A19	4.5W A19 Filament	6W(40 Eq) A19	6.5W(40W Eq) A19 WG	7W(40W Eq) A19 CC WG	8W A19	8W(40W Eq) A19 Remote Phospur	8W(40W Eq) A19 Sultan	8W A19 Slim Style
		9290011818 (458760, 458786, 458778)	9290012101 (461632) 9290012101 (465542) 9290012739 (466227) 9290012741 (466243)	9290012101 (461665)	9290011348 (455782) 9290011178 (453209) 9290011178 (453274) 9290011178 (454058) 9290011348 (455790)	9290011347 (455774) 9290011347 (455766) 9290011347 (455741) 9290011176 (453316) 9290011176 (453183)	9290011348 (455808) 9290011815 (458737, 458752, 458745)	409938	417048 414839	9290002267 (423483) 9290002267 (424374) 9290002295 (425256) 9290002267 (429266)	9290002706 (433219) 9290002706 (433136) 9290002704 (433201) 9290002704 (433128)
Company	Model No.										
Cooper	RI061-VW-K2							1-16	1-4		
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-21	1-33	1-33	1-12	1-23	1-21				
Leviton	6631							NR			
Leviton	6633	1-21	1-33	1-33	1-12	1-23	1-21				
Leviton	6672	1-21	1-33	1-33	1-12	1-23	1-21				
Leviton	6674	1-21	1-10	1-10	1-12	1-23	1-21	1-14	1-4	NR	1-18
Leviton	6615P	1-11	1-17	1-17	1-12	1-7	1-11	NR	NR	1-9	1-8
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	1-21	1-33	1-33	1-12	1-23	1-21	1-16	NR	1-9	1-18
Leviton	IPL06										
Lutron	AYCL-153P							1-4			
Lutron	CTCL-153P							1-4			
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-21	1-33	1-33	1-12	1-23	1-21	1-16	NR	1-6	1-18
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P							1-4			
Lutron	DVELV-300P	1-11	1-17	1-17	1-12	1-7	1-11	1-9	1-18	1-9	1-8
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-21	1-33	1-33	1-12	1-23	1-21	NR	NR	1-12	1-18
Lutron	MAELV-600							1-16			
Lutron	MALV-600							NR			
Lutron	MRF2-6ND-120	1-15	1-33	1-33	1-12	1-23	1-15	NR	NR	1-12	1-18
Lutron	NTCL-250							1-4			
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-21	NR	NR	1-12	1-23	1-21				
Lutron	RRD-3LD										
Lutron	RRD-6NA	NR	1-15	1-15	1-12	1-23	NR	1-16	1-16	1-13	1-18
Lutron	S-600P								NR		
Lutron	SCL-153P								1-8	1-18	1-18
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-16	1-25	1-25	1-12	1-10	1-16	1-16	NR	1-12	1-11
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-21	1-33	1-33	1-12	1-23	1-21	NR	NR	1-12	1-18
Lutron	MSCL-OP153MH		1-33	1-33	1-12	1-23				1-18	
Lutron	MS-OPS2H	1-21	1-33	1-33	1-12	1-23	1-21			1-18	
Panel Modules											
Lutron	GP (Harrier) Card	1-21	1-33	1-33			1-21				
Lutron	HW-RPM-4A-120	1-21	1-33	1-33			1-21				
Lutron	HW-RPM-4U-120	1-21	1-33	1-33			1-21				
Lutron	LP-RPM-4U-120	1-21	1-33	1-33			1-21				

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

Type A lamps Number of bulbs											
		9W(60W Eq) A19 3000K	9W(60W Eq) A19 5000K Core		9W(60W Eq) A19 5000K	9W A19 3000k Core	9.5W A19 2700K Core		9290011175 (453258)	9290011345 (455831)	
		9290011969 (459057) 9290011969 (462234) 9290011969 (462242)	9290011970 (461327) 9290011970 (455881) 9290011970 (461368)	9290011970 (461335) 9290011970 (461350) 9290011970 (462259)	9290011346 (455881) 9290011346 (455907) 9290011346 (455899)	9290011346 (455873) 9290011177 (453282) 9290011177 (453241)	9290011969 (459057) 9290011969 (462234) 9290011969 (462242)	9290012006 (461269) 9290012006 (461194) 9290012006 (461210) 9290012006 (461244)	9290012006 (461226) 9290012006 (461228) 9290012006 (461251) 9290012006 (461236)	9290011175 (453324) 9290011345 (455865) 9290011345 (455857) 9290011345 (455840)	9290011345 (455832) 9290011345 (455816) 9290011175 (453225) 9290011345 (455824)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-15	1-17		1-15		1-15		1-15		1-15
Leviton	6631										
Leviton	6633	1-15	1-17		1-15		1-15		1-15		1-15
Leviton	6672	1-15	1-17		1-15		1-15		1-15		1-15
Leviton	6674	1-15	1-3		1-15		1-15		1-15		1-15
Leviton	6615P	1-8	1-8		1-8		1-8		1-8		1-8
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	1-15	1-17		1-15		1-15		1-15		1-15
Leviton	IPL06										
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-15	1-17		1-15		1-15		1-15		1-15
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-8	1-8		1-8		1-8		1-8		1-8
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-15	1-3		1-15		1-15		1-15		1-15
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-15	1-17		1-15		1-15		1-15		1-15
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-15	1-17		1-15		1-15		1-15		1-15
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-15	1-3		1-15		1-15		1-15		1-15
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-15	1-13		1-15		1-15		1-15		1-15
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-15	1-3		1-15		1-15		1-15		1-15
Lutron	MSCL-OP153MH	1-15	1-17		1-15		1-15		1-15		1-15
Lutron	MS-OPS2H	1-15	1-17		1-15		1-15		1-15		1-15
Panel Modules											
Lutron	GP (Harrier) Card	1-15	1-17				1-15		1-15		1-19
Lutron	HW-RPM-4A-120	1-15	1-17				1-15		1-15		
Lutron	HW-RPM-4U-120	1-15	1-17				1-15		1-15		
Lutron	LP-RPM-4U-120	1-15	1-17				1-15		1-15		

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

Type A lamps Number of bulbs										
		9.5W A19 2200K-2700K	10W(60W Eq) A19 Clear WG	10W A19 L-Prize	10.5W(60W Eq) A19 Slim style	11W(60W Eq) A19 Sultan	12.5W(60W Eq) A19 Remote Phosphur	13W(75W Eq) A21 Slim style	14W(75W Eq) A21 WG	15W(75W Eq) A21
		9290011840	9290012149 (462499)	420224 420075	9290002709 (433235) 9290002709 (433151) 9290002707 (433227) 9290002707 (433144)	9290002268 (423491, 424382, 429258) 9290002296 (425264)	409946 (12E26A60-1 & 9290001829 models only)	9290011120 (452771) 9290011120 (452805) 9290011120 (452789)	9290011120 (452755) 9290011120 (452748) 9290011120 (452730)	9290011839 (459065) 9290011839 (459073) 9290011839 (459081) 9290011839 (459099)
Company	Model No.									
Cooper	RI061-VW-K2			NR		1-2				
Cooper	SAL06P									
Eaton	DAL06P									
Legrand	HCL453P									
Leviton	6602	1-15	1-15						1-11	
Leviton	6631									
Leviton	6633	1-15	1-15						1-11	
Leviton	6672	1-15	1-15						1-11	
Leviton	6674	1-15	1-15	1	1-14	1-4	1-12	1-13	1-11	NR
Leviton	6615P	1-5	1-8	1-4	1-5	1-4	1-12	1-8	1-5	1-4
Leviton	DSE06									
Leviton	DSL06									
Leviton	DSM10									
Leviton	IPI06	1-15	1-15	1-2	1-14	NR	1-12	1-13	1-11	1-8
Leviton	IPL06									
Lutron	AYCL-153P					1-5				
Lutron	CTCL-153P					1-5				
Lutron	CTCL-153PDH									
Lutron	DV-600P	1-15	1-15	1-4	1-14	1-4	1-8	1-13	1-11	1-8
Lutron	DV-600PR									
Lutron	DVCL-153P									
Lutron	DVCL-253P					1-5				
Lutron	DVELV-300P	1-5	1-8	1-5	1-5	1-6	1-12	1-7	1-5	1-4
Lutron	DVRP-253P									
Lutron	LGCL-153P									
Lutron	MACL-153M	NR	1-15	1-9	1-14	1-13	1-12	1-13	1-11	1-8
Lutron	MAELV-600									
Lutron	MALV-600			NR						
Lutron	MRF2-6ND-120	1-15	1-15	1-11	1-14	1-13	1-12	1-13	1-11	1-8
Lutron	NTCL-250					1-5				
Lutron	NTELV-300			1-4						
Lutron	PD-5NE									
Lutron	PD-6WCL	1-15	1-15						1-11	
Lutron	RRD-3LD									
Lutron	RRD-6NA	1-15	1-15	1-9	1-14	1-13	1-12	1-13	1-11	1-8
Lutron	S-600P			NR						
Lutron	SCL-153P				1-14	1-13		NR		
Lutron	SCL-153PR									
Lutron	SELV-300P									
Lutron	SLV-600P	1-11	1-11	1-4	1-8	1-13	NR	1-10	1-11	1-6*
Lutron	TG-600PR									
Lutron	TGCL-153P									
Lutron	TGCL-153PH									
Lutron	TT-300									
Leviton	VPI06									
Sensors										
Lutron	MSCL-OP153M	NR	1-15	1-9	1-14	1-13	1-12	1-13	1-11	1-8
Lutron	MSCL-OP153MH	1-15	1-15					1-13	1-11	
Lutron	MS-OPS2H	1-15	1-15					1-13	1-11	
Panel Modules										
Lutron	GP (Harrier) Card	1-15	1-15						1-23	
Lutron	HW-RPM-4A-120	1-15	1-15						1-23	
Lutron	HW-RPM-4U-120	1-15	1-15						1-23	
Lutron	LP-RPM-4U-120	1-15	1-15						1-23	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Type A lamps

Number of bulbs

					
		17W(75W Eq) A21 Prince	18W(100W Eq) A21 WG	19W(100W Eq) A21	22W(100W Eq) A21
		17E26A21D (418590) 92900002018 (422220)	9290011741 (459107) 9290011741 (459115) 9290011741 (459123) 9290011741 (459131)	9290002596A (451906)	92900002290 (423525) 92900002290 (424432)
Company	Model No.				
Cooper	RI061-VW-K2				NR
Cooper	SAL06P				
Eaton	DAL06P				
Legrand	HCL453P				
Leviton	6602		1-8		
Leviton	6631				
Leviton	6633		1-8		
Leviton	6672		1-8		
Leviton	6674	1-8	1-8	NR	NR
Leviton	6615P	1-4	1-8	1-3	NR
Leviton	DSE06				
Leviton	DSL06				
Leviton	DSM10				
Leviton	IPI06	1-8	1-8	NR	1-6
Leviton	IPL06				
Lutron	AYCL-153P	1-8			
Lutron	CTCL-153P	1-8			
Lutron	CTCL-153PDH				
Lutron	DV-600P	1-8	1-8	1-6	NR
Lutron	DV-600PR				
Lutron	DVCL-153P				
Lutron	DVCL-253P	1-8			
Lutron	DVELV-300P	1-4	1-8	1-3	NR
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M	1-8	1-8	1-6	1-6
Lutron	MAELV-600				1-6
Lutron	MALV-600				
Lutron	MRF2-6ND-120	1-8	1-8	1-6	1-6
Lutron	NTCL-250	1-8			
Lutron	NTELV-300				
Lutron	PD-5NE				
Lutron	PD-6WCL		1-8		
Lutron	RRD-3LD				
Lutron	RRD-6NA	1-8	1-8	1-7	1-6
Lutron	S-600P	1-8			
Lutron	SCL-153P			1-6	
Lutron	SCL-153PR				
Lutron	SELV-300P	1-8			1-6
Lutron	SLV-600P	1-4	1-8	1-4	1-6
Lutron	TG-600PR				
Lutron	TGCL-153P				
Lutron	TGCL-153PH				
Lutron	TT-300				
Leviton	VPI06				
Sensors					
Lutron	MSCL-OP153M	1-8	1-8	1-6	1-6
Lutron	MSCL-OP153MH		1-8	1-6	
Lutron	MS-OPS2H		1-8		
Panel Modules					
Lutron	GP (Harrier) Card		1-22	1-12	
Lutron	HW-RPM-4A-120		1-22	1-17	
Lutron	HW-RPM-4U-120		1-22	1-17	
Lutron	LP-RPM-4U-120		1-22	1-17	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

PAR lamps Number of bulbs										
		4W GU10	4W GU10 WG T20	14PAR38/COR/930/F25/ D/P/B/ULW/T20 6/1FB	9.4PAR30S/COR/935/F25/ DIM/120V/T20 6/1FB	14PAR38/COR/935-940/F25/ DIM/120V/T20 6/1FB	PAR20 5.5W JA8	PAR20 WG 5.5W JA8	PAR30S/L 8.5W JA8	
		9290020555 (468140) 9290020557 (566539)	9290020553 (471565)	9290031338 (576470)	9290034669 (577759)	9290034667 (577734) 9290034668 (577742)	9290030261 (568063) 9290030262 (568071) 9290030264 (568089) 9290030265 (568097)	9290030263 (568105) 9290030267 (568113)	9290030277 (568006) 9290030278 (568014) 9290030279 (568022) 9290030280 (568030) 9290030281 (568048) 9290030282 (568055)	9290030269 (567941) 9290030270 (567957) 9290030271 (567965) 9290030272 (567973) 9290030273 (567981) 9290030274 (567999)
Company	Model No.									
Cooper	SAL06P									
Eaton	DAL06P									
Legrand	HCL453P									
Leviton	6602	1-5	1-5	1-5	1-10	1-10				
Leviton	6631				1-10	1-10				
Leviton	6633	1-5	1-5	1-5	1-10	1-10	1-20	1-20	1-15	
Leviton	6672	1-5	1-5	1-5	1-10	1-10				
Leviton	6674	1-5	1-5		1-10	1-10	1-20	1-20	1-15	
Leviton	6615P	1-5	1-5	1-5	NR	NR				
Leviton	DSE06									
Leviton	DSL06	1-5	1-5		1-10	1-10	1-20	1-20	1-15	
Leviton	DSM10									
Leviton	IPI06	1-5	1-5	1-5	NR	NR	1-20	1-20	1-15	
Leviton	IPL06				1-10	1-10				
Lutron	AYCL-153P				1-10	1-10	1-20	1-20	1-15	
Lutron	CTCL-153P				1-10	1-10	1-20	1-20	1-15	
Lutron	CTCL-153PDH									
Lutron	DV-600P	1-5	1-5	1-5	1-10	1-10	1-20	1-20	1-15	
Lutron	DV-600PR									
Lutron	DVCL-153P				1-10	1-10	1-20	1-20	1-15	
Lutron	DVCL-253P				1-10	1-10	1-20	1-20	1-15	
Lutron	DVELV-300P	1-5	1-5	1-5			1-10	1-10	1-8	
Lutron	DVRP-253P									
Lutron	LGCL-153P									
Lutron	MACL-153M	1-5	1-5	1-5	1-10	1-10				
Lutron	MAELV-600									
Lutron	MALV-600									
Lutron	MRF2-6ND-120	1-5	1-5	1-5	1-10	1-10	1-20	1-20	1-15	
Lutron	NTCL-250				1-10	1-10	1-20	1-20	1-15	
Lutron	NTELV-300									
Lutron	PD-5NE									
Lutron	PD-6WCL	1-5	1-5	1-5	1-10	1-10				
Lutron	RRD-3LD									
Lutron	RRD-6NA									
Lutron	S-600P									
Lutron	SCL-153P				1-10	1-10	1-20	1-20	1-15	
Lutron	SCL-153PR									
Lutron	SELV-300P									
Lutron	SLV-600P	1-5	1-5	1-5	1-10	1-8	1-15	1-15	1-10	
Lutron	TG-600PR									
Lutron	TGCL-153P									
Lutron	TGCL-153PH									
Lutron	TT-300									
Leviton	VPI06									
Sensors										
Lutron	MSCL-OP153M	1-5	1-5	1-5	1-10	1-10				
Lutron	MSCL-OP153MH				1-10	1-10	1-20	1-20	1-15	
Lutron	MS-OPS2H									
Panel Modules										
Lutron	GP (Harrier) Card									
Lutron	HW-RPM-4A-120									
Lutron	HW-RPM-4U-120									
Lutron	LP-RPM-4U-120									

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

		 PAR38 10W JA8		 PAR38 13W JA8		 PAR38 TrueForce DIM 120-277V		 PAR20 7W Glass		 PAR20 7W WG Glass		 PAR30S 10-75W 120V Gen2 Glass	
		9290030285 (567859) 9290030286 (567867) 9290030287 (567925) 9290030288 (567875) 9290030289 (567883)	9290030290 (567891) 9290030291 (567909) 9290030292 (567933) 9290030293 (567917)	9290030295 (567750) 9290030296 (567768) 9290030298 (567776) 9290030299 (567784) 9290030300 (567792)	9290030301 (567800) 9290030303 (567818) 9290030304 (567826) 9290030297 (567834) 9290030302 (567842)	9290030635 (569723) 9290030636 (569731)		9290013165 (471110) 9290013169 (471144) 9290013167 (471128) 9290013170 (471151)		9290013172 (471102) 9290013173 (471136)		9290013204 (529768) 9290013205 (529776) 9290013207 (529784) 9290013209 (529792)	9290013210 (529800) 9290013212 (529818) 9290013213 (471334)
Company	Model No.												
Cooper	SAL06P												
Eaton	DAL06P												
Legrand	HCL453P												
Leviton	6602												
Leviton	6631												
Leviton	6633	1-15		1-10				1-16		1-15		1-15	
Leviton	6672							1-16		1-15		1-15	
Leviton	6674	1-15		1-10				NR					
Leviton	6615P							1-10		1-10		1-8	
Leviton	DSE06												
Leviton	DSL06	1-15		1-10		NR							
Leviton	DSM10												
Leviton	IPI06	1-15		1-10		1-6		1-16		1-15		1-15	
Leviton	IPL06					NR							
Lutron	AYCL-153P	1-15		1-10		NR		3		1-15		NR	
Lutron	CTCL-153P	1-15		1-10		NR		3		1-15		NR	
Lutron	CTCL-153PDH												
Lutron	DV-600P	1-15		1-10		1-6		1-16		1-15		1-15	
Lutron	DV-600PR												
Lutron	DVCL-153P	1-15		1-10		NR		3		1-15		NR	
Lutron	DVCL-253P	1-15		1-10		NR		3		1-15		NR	
Lutron	DVELV-300P	1-8		1-5		1-3		1-10		1-15		1-8	
Lutron	DVRP-253P												
Lutron	LGCL-153P												
Lutron	MACL-153M					1-6		1-16		1-15		1-15	
Lutron	MAELV-600												
Lutron	MALV-600												
Lutron	MRF2-6ND-120	1-15		1-10		NR		1-16		1-15		1-15	
Lutron	NTCL-250	1-15		1-10		NR		3		1-15		NR	
Lutron	NTELV-300												
Lutron	PD-5NE												
Lutron	PD-6WCL					NR		1-16		1-15		1-15	
Lutron	RRD-3LD												
Lutron	RRD-6NA					NR		1-16		1-15		1-2	
Lutron	S-600P												
Lutron	SCL-153P	1-15		1-10		NR		3		1-15		NR	
Lutron	SCL-153PR												
Lutron	SELV-300P												
Lutron	SLV-600P	1-10		1-8		1-4		1-16		1-15		1-11	
Lutron	TG-600PR												
Lutron	TGCL-153P												
Lutron	TGCL-153PH												
Lutron	TT-300												
Leviton	VPI06												
Sensors													
Lutron	MSCL-OP153M					1-16		1-15		1-15		1-15	
Lutron	MSCL-OP153MH	1-15		1-10		NR		1-16		1-15		1-15	
Lutron	MS-OPS2H												
Panel Modules													
Lutron	GP (Harrier) Card												
Lutron	HW-RPM-4A-120							1-15		1-15		1-15	
Lutron	HW-RPM-4U-120							1-15		1-15		1-15	
Lutron	LP-RPM-4U-120							1-15		1-15		1-15	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

											
		PAR30L 10-75W 120V Gen2 Glass		PAR30 12W Glass		PAR38 12-90W 120V Gen2 Glass		PAR38 13.5W Glass		PAR38 14-120W 120V Gen2 Glass	
9290013215 (529701)		9290013221 (529743)		9290012940 (467811)		9290013194 (529628)		9290012920 (467753)		9290013183 (529503)	
9290013216 (529719)		9290013223 (529750)		9290012941 (467829)		9290013195 (529636)		9290012921 (467761)		9290013184 (529529)	
9290013218 (529727)		9290013224 (471359)		9290012942 (467837)		9290013196 (474692)		9290012922 (467779)		9290013185 (474676)	
9290013220 (529735)		9290013224 (471318)		9290012944 (467845)		9290013197 (529644)		9290012923 (468199)		9290013186 (529537)	
				9290012945 (467852)		9290013198 (529651)		9290012924 (467787)		9290013187 (529545)	
				9290012946 (467860)				9290012925 (468009)		9290013188 (529552)	
								9290012925 (468017)		9290013189 (529594)	
								9290012926 (467803)		9290013190 (474684)	
								9290012927 (468009)		9290013191 (529602)	
								9290012927 (468025)		9290013192 (529610)	
Company	Model No.										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-15		NR		1-11		NR		1-10	
Leviton	6631										
Leviton	6633	1-15		1-13		1-11		NR		1-10	
Leviton	6672	1-15		NR		1-11		1-11		1-10	
Leviton	6674			NR				NR			
Leviton	6615P	1-8		2-5		1-5		1-5		1-5	
Leviton	DSE06										
Leviton	DSL06			NR				NR			
Leviton	DSM10										
Leviton	IPI06	1-15		1-13		1-11		1-11		1-10	
Leviton	IPL06										
Lutron	AYCL-153P	NR				1-5				NR	
Lutron	CTCL-153P	NR				1-5				NR	
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-15		1-13		1-11		1-11		1-10	
Lutron	DV-600PR										
Lutron	DVCL-153P	NR				1-5				NR	
Lutron	DVCL-253P	NR				1-5				NR	
Lutron	DVELV-300P	1-8		1-5		1-5		1-5		1-5	
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-15		NR		1-11		NR		1-10	
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-15		NR		1-11		NR		1-5	
Lutron	NTCL-250	NR				1-5				NR	
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-15		NR		1-11		NR		1-10	
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-2		NR		1-3		NR		1-10	
Lutron	S-600P									1-8	
Lutron	SCL-153P	NR				1-5				NR	
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-11		1-9		1-8		1-8			
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-15		NR		1-11		NR		1-10	
Lutron	MSCL-OP153MH	1-15		NR		1-11		NR		1-5	
Lutron	MS-OPS2H	1-15		1-13		1-11		1-11		1-10	
Panel Modules											
Lutron	GP (Harrier) Card	1-15		NR		1-14		NR		1-10	
Lutron	HW-RPM-4A-120	1-15		NR		1-2		NR		1-10	
Lutron	HW-RPM-4U-120	1-15		NR		1-2		NR		1-10	
Lutron	LP-RPM-4U-120	1-15		NR		1-2		NR		1-10	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

PAR lamps													
Number of bulbs		PAR38 16W Glass		PAR20 9W 120V Expert Color		PAR30L 12W Expert color, PAR30L & PAR30S 9.4W T20		PAR38 17W SO/Expert color, PAR38 14W T20, PAR38 10W T20				PAR16-GU10 4.5W WG	
		9290012912 (467696)		9290019218 (535260)		9290012858 (533299)		9290012855 (471029)	9290011135 (435396)	9290013698 (471797)	9290022382 (551887)	9290019168 (534602)	
		9290012913 (467704)	9290012917 (467738)	9290019220 (535286)	9290019219 (535278)	9290012858 (471052)	9290013411 (470970)	9290012854 (471011)	9290011137 (435412)	9290013400 (470872)	9290022383 (551895)	9290019169 (534610)	
		9290012914 (467712)	9290012917 (467976)	9290019221 (535294)	9290019219 (535278)	9290012857 (533281)	9290013412 (470988)	9290012853 (471003)	9290011138 (435420)	9290013401 (470880)	9290019091 (546929)	9290019196 (534628)	
		9290012915 (468181)	9290012918 (467746)	9290019222 (535300)	9290019222 (535300)	9290012857 (471045)	9290020454 (546969)	9290012852 (470996)	9290013394 (470823)	9290020450 (546929)	9290019092 (546937)	9290019197 (534636)	
		9290012916 (467720)	9290012919 (467944)	9290019223 (535310)	9290019223 (535310)	9290012856 (471037)	9290020455 (546977)	9290011131 (435354)	9290013395 (471831)	9290020451 (546937)	9290018537 (546945)		
		9290012917 (467936)	9290012919 (467984)	9290019224 (535328)	9290019224 (535328)	9290013409 (470954)	9290020456 (546985)	9290011132 (435362)	9290013396 (470849)	9290020452 (546945)	9290018538 (546950)	9290019208	
				9290019225 (535336)	9290019225 (535336)	9290013410 (470962)	9290020457 (546993)	9290011134 (435388)	9290013398 (470864)	9290020453 (546950)			
Company	Model No.												
Cooper	SAL06P												
Eaton	DAL06P												
Legrand	HCL453P												
Leviton	6602	1-9		5-15		1-8		1-8				3	
Leviton	6631												
Leviton	6633	1-9		1-15		1-8		1-8				1-5	
Leviton	6672	1-9		1-15		1-8		1-8				1-5	
Leviton	6674	1-9		1-15		1-8						1-5	
Leviton	6615P	2-5		1-8		1-5				1-4		1-2	
Leviton	DSE06												
Leviton	DSL06	1-9		1-15		1-8						1-5	
Leviton	DSM10												
Leviton	IPI06	1-9		1-15		1-8		1-8				1-5	
Leviton	IPL06												
Lutron	AYCL-153P			1-3								1-5	
Lutron	CTCL-153P			1-3								1-5	
Lutron	CTCL-153PDH												
Lutron	DV-600P	1-9		1-15		1-8		1-8				1-5	
Lutron	DV-600PR												
Lutron	DVCL-153P			1-3								1-5	
Lutron	DVCL-253P			1-3								1-5	
Lutron	DVELV-300P	1-5		1-8		1-5				1-4		1-2	
Lutron	DVRP-253P												
Lutron	LGCL-153P												
Lutron	MACL-153M	NR		1-15		1-8		1-8				1-5	
Lutron	MAELV-600												
Lutron	MALV-600												
Lutron	MRF2-6ND-120	NR		1-15		1-8		1-8				1-5	
Lutron	NTCL-250			1-3								1-5	
Lutron	NTLV-300												
Lutron	PD-5NE												
Lutron	PD-6WCL	NR		1-15		1-8		1-8				1-5	
Lutron	RRD-3LD												
Lutron	RRD-6NA	1-9		1-15		1-8						1-5	
Lutron	S-600P												
Lutron	SCL-153P			1-3								1-5	
Lutron	SCL-153PR												
Lutron	SELV-300P												
Lutron	SLV-600P	1-7		1-13		1-8		1-5				1-3	
Lutron	TG-600PR												
Lutron	TGCL-153P												
Lutron	TGCL-153PH												
Lutron	TT-300												
Leviton	VPI06												
Sensors													
Lutron	MSCL-OP153M	NR		1-15		1-8		1-8				1-5	
Lutron	MSCL-OP153MH	NR		1-15		1-8		1-8				1-5	
Lutron	MS-OPS2H	1-9		1-15		1-8		1-8				1-5	
Panel Modules													
Lutron	GP (Harrier) Card	1-10		1-15				1-8				1-10	
Lutron	HW-RPM-4A-120	1-10		1-15								1-10	
Lutron	HW-RPM-4U-120	1-10		1-15								1-10	
Lutron	LP-RPM-4U-120	1-10		1-15								1-10	

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

PAR lamps									
Number of bulbs		PAR38 33W (Cons) 120V High Lumen DIM	PAR16-GU10 WG 4.5W	PAR16-GU10 4.5W	PAR16-GU10 7W	PAR16L ES 7W	PAR16L ES (Prof) 7W	PAR16S/PAR16L 7W 500lm	PAR20 AF 6W
		9290019168 (534602) 9290019169 (534610) 9290019196 (534628) 9290019197 (534636) 9290019208	9290011565 (457267) 9290011565 (457648) 9290011565 (457655)	9290011288 (454363) 9290011288 (454405) 9290011288 (454389) 9290011288 (455378) 9290011288 (458034)	929001172505 (457663)	929001318126 (475434)	929001318126 (475434)	9290012454 (464981) 9290012456 (464999) 9290012457 (465005) 9290012456 (465021) 9290012457 (465039)	9290011448 (458927) 9290011448 (458919) 9290011452 (456111) 9290011451 (456103) 9290011450 (456095) 9290011449 (458893, 458885, 458901, 458959) 9290011447 (456061) 9290011446 (456053) 9290011445 (456046) 9290011487 (456269)
Company	Model No.								
Cooper	SAL06P								
Eaton	DAL06P								
Legrand	HCL453P								
Leviton	6602	3	1-20	1-15	NR	1-15	1-15	1-20	1-20
Leviton	6631								
Leviton	6633	1-5	1-20	1-8	2-16	1-15	NR	1-20	1-20
Leviton	6672	1-5	1-20	1-15	2-16	1-15	1-15	1-20	1-20
Leviton	6674	1-5	1-20	1-15	2-13			NR	1-20
Leviton	6615P	1-2	1-20	1-12	NR	1-10	1-10	1-10	1-10
Leviton	DSE06								
Leviton	DSL06	1-5	1-20	1-15	2-13			NR	1-20
Leviton	DSM10								
Leviton	IPI06	1-5	1-20	1-15	NR	1-15	1-15	1-20	1-20
Leviton	IPL06								
Lutron	AYCL-153P	1-5				8G	NR		
Lutron	CTCL-153P	1-5				8G	NR		
Lutron	CTCL-153PDH								
Lutron	DV-600P	1-5	1-20	1-15	2-16	1-15	8G	1-20	1-20
Lutron	DV-600PR								
Lutron	DVCL-153P	1-5				8G	NR		
Lutron	DVCL-253P	1-5				8G	NR		
Lutron	DVELV-300P	1-2	1-20	1-12	1-8	1-10	1-10	1-10	1-10
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M	1-5	NR	NR	2-20	1-15	NR	NR	1-20
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120	1-5	NR	1-15	2-16	1-15	NR	NR	NR
Lutron	NTCL-250	1-5				8G	NR		
Lutron	NTELV-300								
Lutron	PD-5NE								
Lutron	PD-6WCL	1-5	1-20	1-11	2-16	1-15	NR		NR
Lutron	RRD-3LD								
Lutron	RRD-6NA	1-5	1-20	1-15	2-16		NR	NR	1-20
Lutron	S-600P					1-15			
Lutron	SCL-153P	1-5				8G	NR		
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P	1-3	1-20	1-15	2-12	1-15	1-15	1-16	1-20
Lutron	TG-600PR								
Lutron	TGCL-153P								
Lutron	TGCL-153PH								
Lutron	TT-300								
Leviton	VPI06								
Sensors									
Lutron	MSCL-OP153M	1-5	NR	NR	2-20	1-15	NR	NR	1-20
Lutron	MSCL-OP153MH	1-5	1-20	1-15	2-20	1-15	NR	NR	1-20
Lutron	MS-OPS2H	1-5	1-20	1-15	2-20	1-15	1-15	1-20	1-20
Panel Modules									
Lutron	GP (Harrier) Card	1-10	1-20		2-20	1-15	NR	NR	1-20
Lutron	HW-RPM-4A-120	1-10	1-20		2-20	1-15	NR	NR	1-20
Lutron	HW-RPM-4U-120	1-10	1-20		2-20	1-15	NR	NR	1-20
Lutron	LP-RPM-4U-120	1-10	1-20		2-20	1-15	NR	NR	1-20

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps

Number of bulbs

									
		PAR20 6W		PAR20 SO 6W (50W Eq)		PAR30S AF SO 12W Expert color		PAR30L 8W	PAR30L AF 10.5W
		9290012254 (463620)	9290012254 (463687)	9290012247 (463729)	9290012253 (463844)	9290012862 (471094)	9290011129 (435339)		9290011114 (452656)
		9290012250 (463646)	9290012255 (463695)	9290012250 (463646)	9290012254 (463620)	9290012861 (471086)	9290011128 (435321)		9290011114 (452623)
		9290012251 (463653)	9290012259 (463703)	9290012251 (463653)	9290012254 (463687)	9290012860 (471078)	9290011126 (435305)	9290013404 (470914)	9290011114 (434992)
		9290012252 (463661)	9290012260 (463711)	9290012252 (463661)	9290012254 (463612)	9290012859 (471060)	9290011125 (435297)	9290013407 (470930)	9290011113 (452615)
		9290012253 (463679)	9290012247 (463729)	9290012253 (463679)	9290012254 (463851)	9290011123 (435271)	9290013402 (478989)	9290013408 (470948)	9290011113 (434984)
				9290012253 (463604)	9290012254 (463794)	9290011122 (435263)	9290013403 (470906)	9290013697 (471789)	
Company	Model No.								
Cooper	SAL06P								
Eaton	DAL06P								
Legrand	HCL453P								
Leviton	6602	1-15		1-15		1-12		1-15	
Leviton	6631								
Leviton	6633	1-15		1-15		1-8		1-15	
Leviton	6672	1-15		1-15		1-8		1-15	
Leviton	6674	1-15		1-15		1-8		1-15	1-7
Leviton	6615P	1-15		1-15		1-4		1-8	1-6
Leviton	DSE06								
Leviton	DSL06	1-15		1-15		1-8		1-15	1-7
Leviton	DSM10								
Leviton	IPI06	1-15		1-15		1-8		1-15	1-7
Leviton	IPL06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P	1-15		1-15		1-12		1-15	1-7
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P	NR		NR		1-4		1-8	1-6
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M	1-15		1-15		1-12		1-15	1-7
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120	1-15		1-15		1-8		1-15	1-7
Lutron	NTCL-250								
Lutron	NTELV-300								
Lutron	PD-5NE								
Lutron	PD-6WCL	1-15		1-15		1-12		1-15	
Lutron	RRD-3LD								
Lutron	RRD-6NA	1-15		1-15		1-8		1-15	1-7
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P	NR		NR		1-8		1-10	1-7
Lutron	TG-600PR								
Lutron	TGCL-153P								
Lutron	TGCL-153PH								
Lutron	TT-300								
Leviton	VPI06								
Sensors									
Lutron	MSCL-OP153M	1-15		1-15		1-12		1-15	1-7
Lutron	MSCL-OP153MH	1-15		1-15		1-8		1-15	
Lutron	MS-OPS2H	1-15		1-15		1-8		1-15	
Panel Modules									
Lutron	GP (Harrier) Card					1-15			
Lutron	HW-RPM-4A-120					1-15			
Lutron	HW-RPM-4U-120					1-15			
Lutron	LP-RPM-4U-120					1-15			

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

PAR lamps


Number of bulbs

PAR lamps Number of bulbs						
		PAR30L SO AF 12.5W	PAR38 SO 12W		PAR38 SO 13W	PAR38 15W
		9290011327 (454702) 9290011326 (454694) 9290011325 (454686) 9290011324 (454678) 9290011323 (454660)	9290011834 (460063) 9290011834 (460055) 9290011834 (460105) 9290011834 (460071)	9290011835 (460121) 9290011835 (460089) 9290011835 (461046) 9290011835 (460097)	9290011322 (454751) 9290011321 (454744) 9290011320 (454736) 9290011319 (454728)	92900111104 (453431)
Company	Model No.					
Cooper	SAL06P					
Eaton	DAL06P					
Legrand	HCL453P					
Leviton	6602	1-8	1-14	1-8	1-8	
Leviton	6631					
Leviton	6633	1-8	NR	1-8	1-8	
Leviton	6672	1-8	1-14	1-8	1-8	
Leviton	6674	1-8		1-8	1-8	
Leviton	6615P	1-5	1-7	1-5	1-4	
Leviton	DSE06					
Leviton	DSL06	1-8		1-8	1-8	
Leviton	DSM10					
Leviton	IPI06	1-8	1-14	1-8	1-8	
Leviton	IPL06					
Lutron	AYCL-153P					
Lutron	CTCL-153P					
Lutron	CTCL-153PDH					
Lutron	DV-600P	1-8	1-14	1-8	1-8	
Lutron	DV-600PR					
Lutron	DVCL-153P					
Lutron	DVCL-253P					
Lutron	DVELV-300P	1-5	1-7	1-5	1-4	
Lutron	DVRP-253P					
Lutron	LGCL-153P					
Lutron	MACL-153M	1-8	NR	1-8	1-8	
Lutron	MAELV-600					
Lutron	MALV-600					
Lutron	MRF2-6ND-120	1-8	NR	1-8	1-8	
Lutron	NTCL-250					
Lutron	NTELV-300					
Lutron	PD-5NE					
Lutron	PD-6WCL	1-8	NR	1-8		
Lutron	RRD-3LD					
Lutron	RRD-6NA	1-8	NR	1-8	1-8	
Lutron	S-600P					
Lutron	SCL-153P					
Lutron	SCL-153PR					
Lutron	SELV-300P					
Lutron	SLV-600P	1-8	1-10	NR	1-8	
Lutron	TG-600PR					
Lutron	TGCL-153P					
Lutron	TGCL-153PH					
Lutron	TT-300					
Leviton	VPI06					
Sensors						
Lutron	MSCL-OP153M	1-8	NR	1-8	1-8	
Lutron	MSCL-OP153MH	1-8	NR	1-8		
Lutron	MS-OPS2H	1-8	1-15	1-4		
Panel Modules						
Lutron	GP (Harrier) Card		1-15			
Lutron	HW-RPM-4A-120		1-15			
Lutron	HW-RPM-4U-120		1-15			
Lutron	LP-RPM-4U-120		1-15			
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.					
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.					
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).					
	Lamp not yet tested with this dimmer, compatibility unknown.					

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

											
		8.8W BR30 CNG FR P D 9290036198 (583583) 9290036199 (583591) 9290036200 (583609) 9290036201 (583617)	15BR30/PER/927/P/E26/ WG/HO/T20 4/1PF 9290023514 (571471)	4.5BR30/UE/930-950/P/ E26/D/T20 1PF/3 SRP 9290035854 (581678) 9290035855 (581686)	13.3BR40/PER/ 927-930-940-950/P/ E26/DIM 6/1CT T20 9290034772 (577858) 9290034773 (577866) 9290034774 (577874) 9290034775 (577882)	13.3BR40/PER/927-22/P/ E26/WG 6/1CT T20 9290034771 (577841)	BR30 P0027894 T20 9290023514 (558023, 571471) 9290023513 (571463, 558031)	BR40 P0027894 T20 9290023512 (558049) 9290023515 (558056)	BR20 P0028208 T20 9290020922 (553883)	BR40 P0025038 9290020924 (553909)	BR40, P0025038, 2019Q2 9290020355 (547422) 9290020356 (547430) 9290022042 (548115)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SALO6P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Leviton	6631	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20		
Leviton	6633	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Leviton	6672	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Leviton	6674	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20		
Leviton	6615P		1-6	NR	1-6	1-6	1-6	1-4	NR	1-9	1-9
Leviton	DSE06										
Leviton	DSL06	1-18	1-20	1-20			1-20	1-16	1-20		
Leviton	DSM10										
Leviton	IPI06	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Leviton	IPL06	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20		
Lutron	AYCL-153P			1-20							
Lutron	CTCL-153P			1-20							
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Lutron	DV-600PR										
Lutron	DVCL-153P	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20		
Lutron	DVCL-253P			1-20							
Lutron	DVELV-300P	1-18	1-6				1-6	1-4	1-16	1-9	1-9
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-18	1-12	1-20			1-12	1-8	1-20	1-18	1-18
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-18	1-12	1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Lutron	NTCL-250			1-20							
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-18		1-20	1-10	1-10	1-12	1-8	1-20	1-18	1-18
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-18									
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-18	1-9	1-20	1-9	1-9	1-9	1-6	1-17	1-13	1-13
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M			1-20			1-12	1-8	1-20	1-18	1-18
Lutron	MSCL-OP153MH	1-18	1-12	1-20			1-12	1-8	1-20		
Lutron	MS-OPS2H										
Panel Modules											
Lutron	GP (Harrier) Card	NR		1-20							
Lutron	HW-RPM-4A-120										
Lutron	HW-RPM-4U-120										
Lutron	LP-RPM-4U-120										

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

BR lamps

Number of bulbs

BR lamps Number of bulbs											
		BR30 P0025038, 2019Q2	BR20 P0025038, 2019Q2	BR40 8.8W WG & CG, P0020365, 2018Q4	BR30 7.2W WG & CG, P0020365, 2018Q4	BR20 5W WG & CG, P0020365, 2018Q4	BR20 6W(50W Eq) WG	BR20 8W AF	BR30 9W	BR30 9W(65W Eq) WG	
		9290020321 (545905) 9290020322 (545913) 9290020923 (553891) 9290022041 (457093)	9290020353 (547406) 9290020354 (547414) 9290022040 (548123)	9290020091 (457010) 9290020092	9290018703 (457044) 9790020069	9290020089 (456979) 9290020090	9290011557 (456979) 9290011557 (456995) 9290011557 (456987)	9290002192 (420331) 9290002192 (423400) 9290002192 (428813)	92900119449 (464180) 929001213763 (461855)	9290011555 (465996) 9290011555 (457044) 9290011555 (457051)	9290011555 (457036) 9290011555 (457077) 9290011555 (457069)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-20	1-20	1-18	1-20	1-20	1-25		NR	1-16	
Leviton	6631	1-20									
Leviton	6633	1-20	1-20	1-18	1-20	1-20	1-25		NR	1-16	
Leviton	6672	1-20	1-20	1-18	1-20	1-20	1-25		1-8	1-16	
Leviton	6674	1-20					1-25	1-14	1-8	1-16	
Leviton	6615P	NR	1-16	1-9	1-13	1-16	1-12	1-9	1-8	1-8	
Leviton	DSE06										
Leviton	DSL06	1-20									
Leviton	DSM10										
Leviton	IPI06	1-20	1-20	1-18	1-20	1-20	1-25	1-18	1-5	1-16	
Leviton	IPL06	1-20									
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-20	1-20	1-18	1-20	1-20	1-25	1-8	1-8	1-16	
Lutron	DV-600PR										
Lutron	DVCL-153P	1-20									
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-11	1-16	1-9	1-13	1-16	1-12	NR	1-8	1-8	
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-20	1-20	1-18	1-20	1-20	1-25	1-18	1-8	1-16	
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-20	1-20	1-18	1-20	1-20	1-25	1-18	1-8	1-16	
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-20	1-20	1-18	1-20	1-20	1-15		1-8	1-16	
Lutron	RRD-3LD										
Lutron	RRD-6NA						1-25	1-18	1-8	1-16	
Lutron	S-600P										
Lutron	SCL-153P							1-18			
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-17	1-20	1-13	1-19	1-20	1-15	1-8	1-8	1-12	
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-20	1-20	1-18	1-20	1-20	1-25	1-18	1-8	1-16	
Lutron	MSCL-OP153MH	1-20					1-15	1-18	1-8	1-16	
Lutron	MS-OPS2H						1-25	1-18	1-8	1-16	
Panel Modules											
Lutron	GP (Harrier) Card						1-25			1-16	
Lutron	HW-RPM-4A-120						1-25			1-16	
Lutron	HW-RPM-4U-120						1-25			1-16	
Lutron	LP-RPM-4U-120						1-25			1-16	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.										
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.										
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).										
	Lamp not vet tested with this dimmer, compatibility unknown.										

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

BR lamps Number of bulbs											
		BR30 9W	BR30 9.5W (65W Eq) WG	BR30 9.5W (65W Eq) Slim style	BR30 13W AF	BR30 13W AF Dim Tone	BR40 9W (65WEq) WG	BR40 12W AF	BR40 14.5W AF		
		929001174966 (458109) 929001174988 (460352) 929001174989 (465286) 929001174993 (462143)	929001174995 (460345) 929001174997 (464198) 929001174999 (465229)	9290011117 (452243) 9290011117 (452235) 9290011117 (452268) 9290011117 (452284)	9290011118 (452359) 9290011118 (452383) 9290011118 (452391) 9290011118 (452417)	9290011119 (452441) 9290011119 (452466) 9290011119 (452482)	9290002197 (420554) 9290002198 (420281) 9290002197 (423798) 9290002197 (429282)	9290002344 (426445)	9290011558 (457010) 9290011558 (457002) 9290011558 (457028)	92900025803 (451914)	9290002199 (420562) 9290002199 (423756)
Company	Model No.										
Cooper	RI061-VW-K2					1-11			1-10		
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-5					1-16				
Leviton	6631										
Leviton	6633	1-4					1-16				
Leviton	6672	1-8		1-8			1-16				
Leviton	6674	1-8	1-12	1-8	1-11	1-4	1-16	1-10	1-10		
Leviton	6615P	1-8	1-7	1-5	1-5	1-5	1-8	1-5	NR		
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	1-5	1-6	1-8	1-11	1-7	1-16	1-10	1-10		
Leviton	IPL06										
Lutron	AYCL-153P				1-11						
Lutron	CTCL-153P				1-11						
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-8	1-12	1-8	1-11	1-5	1-16	1-10	1-10		
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P				1-11						
Lutron	DVELV-300P	1-8	1-7	1-5	1-5	1-5	1-8	1-5	1-5		
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-8	1-12	1-8	1-11	1-11	1-16	1-12	1-10		
Lutron	MAELV-600					1-11					
Lutron	MALV-600				1-11						
Lutron	MRF2-6ND-120	1-8	1-12	1-8	1-11	1-11	1-16	1-10	1-10		
Lutron	NTCL-250				1-11						
Lutron	NTELV-300					1-5					
Lutron	PD-5NE										
Lutron	PD-6WCL	1-8	1-15	1-15			1-16	1-12			
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-8	1-12	1-15	1-11	1-11	1-16	1-10	1-10		
Lutron	S-600P										
Lutron	SCL-153P				1-11	1-11		1-12			
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-8	1-7	1-7	1-11	1-11	1-12	1-8	1-10		
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-8	1-12	1-8	1-11	1-11	1-16	1-12	1-10		
Lutron	MSCL-OP153MH	1-8	1-12	1-8			1-16	1-12			
Lutron	MS-OPS2H	1-6	1-12	1-8			1-16	1-12			
Panel Modules											
Lutron	GP (Harrier) Card		1-27	1-26			1-16	1-18			
Lutron	HW-RPM-4A-120		1-38	1-38			1-16	1-25			
Lutron	HW-RPM-4U-120		1-38	1-38			1-16	1-25			
Lutron	LP-RPM-4U-120		1-38	1-38			1-16	1-25			
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.										
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.										
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).										
	Lamp not yet tested with this dimmer, compatibility unknown.										

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

											
		5BA11/PER/UD50/CL/ G/E26/D 6/3PF T20	5B11/PER/UD/CL/ G/E26/WGD 6/3PF T20	3.5BA11/PER/UD50/ CL/G/E12/D 6/3PF T20	3.5B11/PER/UD/CL/ G/E26/WGD 6/3PF T20	3.5B11/VIN/820/E12/ Amber/G/SP D 4/2PF T20	5.5B11/PER/927-922/ CL/G/E26/WGX 1FB T20	6.6BA11/PER/950/CL/ G/E26/DIM 1FB T20/ P0025721-B	6.6BA11/PER/950/CL/ G/E12/DIM 1FB T20 /P0025721-B	6.6BA11/PER/950/CL/ G/E12/DIM 1FB T20/ P0025721-B	6.6BA11/PER/950/CL/ G/E12/DIM 1FB T20/ P0025721-B
		9290029915 (564922)	9290030855 (573378) 9290029910 (566687) 9290029911 (566695)	9290029916 (564930) 9290029919 (564948)	9290029918 (566653) 9290030899 (574392) 9290029917 (566679)	9290029887 (565804)	9290022046 (549345)	9290022045 (549337)	9290022958 (557488)	9290022959 (557496)	9290022959 (557496)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602					1-10	1-10	1-10			3-15
Leviton	6631	1-10	1-10	1-10	1-10	1-10	1-10	1-10			
Leviton	6633	1-10	1-10	1-10	1-10	1-10	2-10	2-10			2-15
Leviton	6672	1-10	1-10	1-10	1-10	1-10	1-10	1-10			1-15
Leviton	6674	1-10	1-10	1-10	1-10	1-10	1-10	1-10			1-15
Leviton	6615P	1-10	1-10	1-10	1-10	1-10	NR	NR	1-5	1-5	1-15
Leviton	DSE06										
Leviton	DSL06	1-10	1-10	1-10	1-10	1-10	1-10	1-10			
Leviton	DSM10										
Leviton	IPI06	1-10	1-10	1-10	1-10	1-10	2-10	2-10			1-15
Leviton	IPL06	1-10	1-10	1-10	1-10	2-20	1-10	1-10			
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P					1-10	1-10	1-10			1-15
Lutron	DV-600PR										
Lutron	DVCL-153P	1-10	1-10	1-10	1-10						
Lutron	DVCL-253P										
Lutron	DVELV-300P					1-10	1-10	1-10	1-10	1-10	1-15
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-10	1-10	1-10	1-10	1-10					
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120					1-10	1-10	1-10			1-15
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-10	1-10	1-10	1-10	1-10	1-10	1-10	1-10	1-10	2-15
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-10	1-10	1-10	1-10	1-10					
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-10	1-10	1-10	1-10	1-10	1-10	1-10			1-15
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-10	1-10	1-10	1-10	1-10					
Lutron	MSCL-OP153MH	1-10	1-10	1-10	1-10	1-10	1-10	1-10			1-15
Lutron	MS-OPS2H										1-15
Panel Modules											
Lutron	GP (Harrier) Card										1-15
Lutron	HW-RPM-4A-120										1-15
Lutron	HW-RPM-4U-120										1-15
Lutron	LP-RPM-4U-120										1-15
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.										
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.										
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).										
	Lamp not yet tested with this dimmer, compatibility unknown.										

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

Candles Number of bulbs									
		3BA11/Mod/840/ E12/CL/GL/DIM 8/1BC	6.6BA11 WG E12/E26 T20	A15 8W Filament T20	B11 3.3W Dimmable Filament T20, P0025721	BA11 2W (25 Eq) WG Filament T20, P0023793	BA11 4.5W (40w Eq) WG Filament T20, P0023793		

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs



3.8W (40w Eq) WG Candle, P0020414, P0023247



3-5.5W WG Filament



5.5W BA11/G16.5 Candle



2.5-8W Dimmable Candle & Vintage

		3.8W (40w Eq) WG Candle, P0020414, P0023247			3-5.5W WG Filament		5.5W BA11/G16.5 Candle	2.5-8W Dimmable Candle & Vintage			
		9290019514 (537621)	9290019511 (537613)	9290019512 (556811)	9290019333 (536524)	9290019323 (536854)	9290018413 (478792)	9290013148 (470757)	9290018425 (478693)	9290018431 (478750)	9290018438 (478925)
		9290019509 (537563)	9290019514 (556852)	9290019510 (556803)	9290019335 (536938)	9290019324 (536862)	9290018414 (478800)	9290013149 (470765)	9290018426 (478701)	9290018432 (478768)	9290012687 (466524)
		9290019513 (537597)	9290019511 (556845)	9290019510 (556803)	9290019336 (536746)	9290019325 (536870)	9290018415 (478818)	9290013150 (470773)	9290018427 (478719)	9290018433 (478776)	9290012096 (461111)
		9290018431 (478750)	9290019513 (556829)	9290019515 (537605)	9290019337 (536950)	9290019325 (536870)	9290018416 (478826)	9290013151 (470781)	9290018428 (478727)	9290018435 (478891)	9290013355 (475822)
		9290018432 (478768)	9290019512 (537589)	9290019515 (556837)	9290019321 (536839)	9290019326 (536888)	9290018417 (478834)	9290018423 (478677)	9290018429 (478735)	9290018436 (478909)	9290013357 (475848)
					9290019322 (536847)	9290020915 (547959)	9290018418 (478842)	9290018424 (478685)	9290018430 (478743)	9290018437 (478917)	9290013356 (475830)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	3-20			2-10		1-5	3-20			
Leviton	6631										
Leviton	6633	2-20			1-10		1-10	2-20			
Leviton	6672	1-20			1-10		1-10	1-20			
Leviton	6674										
Leviton	6615P	1-20			1-10		1-5	1-20			
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	4-20			1-10		1-10	4-20			
Leviton	IPL06										
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-20			2-10		1-10	1-20			
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-20			1-10		1-3	1-20			
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-20			1-10		1-10	1-20			
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-10			2-10		1-10	1-10			
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	3-20			NR		1-10	3-20			
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-20			1-3		1-10	1-20			
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-20			2-10		1-10	1-20			
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-20			1-10		1-10	1-20			
Lutron	MSCL-OP153MH	1-20			1-10		1-10	1-20			
Lutron	MS-OPS2H	1-20			1-10		1-10	1-20			
Panel Modules											
Lutron	GP (Harrier) Card	1-20			1-10		1-8	1-20			
Lutron	HW-RPM-4A-120	1-20			1-10		1-10	1-20			
Lutron	HW-RPM-4U-120	1-20			1-10		1-10	1-20			
Lutron	LP-RPM-4U-120	1-20			1-10		1-10	1-20			

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Candles

Number of bulbs

Candles Number of bulbs											
		2.5W (25W Eq) DS	3W	3.5W Filament	3.5W DW	3.5W (25W Eq) WG DS	4W (40W Eq) WG	4.5W (40W Eq) 2700K		4.5W (40W Eq) 5000K	4.5W (40W Eq) DS
		9290002799 (435149) 9290011151 (451831)	410209, 410217, 420414, 420422, 420430, 426916, 427237	9290012103 (461681)	9290002417 (427799) 9290002419 (427815) 9290002418 (427781) 9290002420 (427807) 9290002417 (427765) 9290002419 (427773)	9290011668 (457242) 9290011668 (457234) 9290011668 (457226)	469676	9290012137 (461855) 9290012137 (461863) 9290012137 (461871) 9290012137 (461889) 9290012137 (461897) 9290012137 (461905)	9290012138 (461913) 9290012138 (461921) 9290012138 (461939) 9290012138 (461947) 9290012138 (461953) 9290012138 (462358)	9290012130 (463901) 9290012130 (463919) 9290012130 (463943)	9290002797 (435172) 9290002889 (435156) 9290002798 (435164)
Company	Model No.										
Cooper	RI061-VW-K2		NR								
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	NR		1-33		1-15	3-20	2-30	2-30	NR	
Leviton	6631		NR								
Leviton	6633	1-7		1-33		1-25	2-20	2-30	2-30	1-10	
Leviton	6672	1-7		1-33		1-35	1-20	2-30	2-30	1-10	
Leviton	6674	1-7	1-6	1-10	1-10	1-20		2-30	2-30	1-10	
Leviton	6615P	NR	NR	1-17	1-17	1-17	1-20	2-16	2-16	NR	
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	NR	NR	1-33	NR	1-35	4-20	2-30	2-30	NR	
Leviton	IPL06										
Lutron	AYCL-153P		NR								
Lutron	CTCL-153P		NR								
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-7	1-8	1-33	NR	1-15	1-20	2-30	2-30	NR	
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P		NR								
Lutron	DVELV-300P	1-7	1-2	1-17	10-21	1-17	1-20	2-16	2-16	NR	
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-7	1-12	1-33	1-42	1-35	1-20	2-30	2-30	1-10	
Lutron	MAELV-600		1-12								
Lutron	MALV-600		NR								
Lutron	MRF2-6ND-120	1-7	NR	1-33	1-42	1-35	1-10	2-30	2-30	1-10	
Lutron	NTCL-250		NR								
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-7		NR		1-35	3-20	2-30	NR	1-10	
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-7	1-12	1-15	1-42	1-35	1-20	2-30	2-30	1-10	
Lutron	S-600P		NR								
Lutron	SCL-153P				4-42						
Lutron	SCL-153PR										
Lutron	SELV-300P		1-12								
Lutron	SLV-600P	1-7	1-12	1-25	NR	1-15	1-20	2-30	2-30	1-10	
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-7	1-12	1-33	1-42	1-35	1-20	2-30	2-30	1-10	
Lutron	MSCL-OP153MH			1-33		2-45	1-20	2-30	NR		
Lutron	MS-OPS2H			1-33		1-45	1-20	2-30	2-30		
Panel Modules											
Lutron	GP (Harrier) Card			1-33		1-50	1-20	2-30	2-30		
Lutron	HW-RPM-4A-120			1-33		1-50	1-20	2-30	2-30		
Lutron	HW-RPM-4U-120			1-33		1-50	1-20	2-30	2-30		
Lutron	LP-RPM-4U-120			1-33		1-50	1-20	2-30	2-30		

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Candles

Number of bulbs

Candles Number of bulbs											
		4.5W (40Eq) DS WG	4.5W (40W Eq) Filament	4.5W (60W Eq) Filament	6W (60W Eq) 5000K	6.5W (60W Eq) DS	7W (60W Eq) DS WG				
		9290011673 (457200) 9290011673 (457192) 9290011673 (457184) 9290011674 (457150)	9290011674 (457143) 9290011672 (457176) 9290011672 (457168)	9290011671 (457218) 9290011670 (457135) 9290011670 (457127) 9290011670 (457119)	9290012103 (461681)	9290012687 (465567) 9290012687 (465583) 9290012740 (466235)	9290012127 (461822) 9290012127 (461848)	9290002886 (435180) 9290011121 (452813)	9290011820 (458695) 9290011821 (458661) 9290011822 (458638) 9290011820 (458687) 9290011821 (458653)	9290011822 (458620) 9290011820 (459321) 9290011820 (458703) 9290011821 (458679)	
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-26	1-33	1-33	1-25	NR	1-21				
Leviton	6631										
Leviton	6633	1-26	1-33	1-33	1-25	1-10	1-21				
Leviton	6672	1-26	1-33	1-33	1-25	1-10	1-21				
Leviton	6674	1-10	1-10	1-10	1-25	1-10	1-21				
Leviton	6615P	1-13	1-17	1-17	1-12	NR	1-11				
Leviton	DSE06										
Leviton	DSL06										
Leviton	DSM10										
Leviton	IPI06	1-26	1-33	1-33	1-25	NR	1-21				
Leviton	IPL06										
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-26	1-33	1-33	1-25	1-10	1-21				
Lutron	DV-600PR										
Lutron	DVCL-153P										
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-13	1-17	1-17	1-12	NR	1-11				
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-26	1-33	1-33	1-25	1-10	1-21				
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-26	1-33	1-33	1-25	1-10	1-21				
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	NR	NR	NR	1-25	1-10	NR				
Lutron	RRD-3LD										
Lutron	RRD-6NA	NR	1-15	1-15	1-25	1-10	1-25				
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-19	1-25	1-25	1-25	1-10	1-16				
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-26	1-33	1-33	1-25	1-10	1-21				
Lutron	MSCL-OP153MH	1-33	1-33	1-33	1-25		NR				
Lutron	MS-OPS2H	1-33	1-33	1-33	1-25		1-21				
Panel Modules											
Lutron	GP (Harrier) Card	1-40	1-33	1-33	1-25	1-10	1-25				
Lutron	HW-RPM-4A-120	1-45	1-33	1-33	1-25	1-10	1-25				
Lutron	HW-RPM-4U-120	1-45	1-33	1-33	1-25	1-10	1-25				
Lutron	LP-RPM-4U-120	1-45	1-33	1-33	1-25	1-10	1-25				
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.										
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.										
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).										
	Lamp not yet tested with this dimmer, compatibility unknown.										

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

										
		5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	5G25/PER/UD50/CL/G/E26/D 4/2PFT20	3.5W G25 G16.5 CL G T20	2.5G25/PER/UD/CL/G/E26/WGD 4/2PF T20	6.5ST19/VIN/820/E26/Amber/G/SP/D 1PFT20	6.5G25/VIN/820/E26/Amber/G/SP D 4/1PFT20	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	3.5T10/VIN/820/E26/Amber/G/SP D 4/1PFT20	3.5A15/VIN/820/E26/Amber/G/SP D 4/1PFT20
		9290029885 (565788)	9290029914 (564914)	9290030848 (573345) 9290030850 (573352) 9290030851 (573295)	9290030852 (573303) 9290030849 (573337) 9290030998 (575217)	9290030847 (573360)	9290029869 (565622)	9290029895 (565887)	9290029888 (565812)	9290029874 (565671) 9290029872 (565655)
Company	Model No.									
Cooper	RI061-VW-K2									
Cooper	SAL06P									
Eaton	DAL06P									
Legrand	HCL453P									
Leviton	6602	NR					5-20	5-20	5-20	1-10
Leviton	6631		1-10	1-10	1-10				1-10	1-10
Leviton	6633	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Leviton	6672	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Leviton	6674	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Leviton	6615P	1-14	NR	NR	NR		1-10	1-10	1-15	1-10
Leviton	DSE06									
Leviton	DSL06		1-10	1-10	1-10				1-10	1-10
Leviton	DSM10									
Leviton	IPI06	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Leviton	IPL06	1-20	1-10	1-10	1-10		1-20	1-20	1-20	2-20
Lutron	AYCL-153P									
Lutron	CTCL-153P									
Lutron	CTCL-153PDH									
Lutron	DV-600P								1-10	1-10
Lutron	DV-600PR									
Lutron	DVCL-153P	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Lutron	DVCL-253P									
Lutron	DVELV-300P								1-10	1-10
Lutron	DVRP-253P									
Lutron	LGCL-153P									
Lutron	MACL-153M	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Lutron	MAELV-600									
Lutron	MALV-600									
Lutron	MRF2-6ND-120	1-20					1-20	1-20	1-20	1-10
Lutron	NTCL-250									
Lutron	NTELV-300									
Lutron	PD-5NE									
Lutron	PD-6WCL	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Lutron	RRD-3LD									
Lutron	RRD-6NA		1-10	1-10	1-10				1-10	1-10
Lutron	S-600P									
Lutron	SCL-153P									
Lutron	SCL-153PR									
Lutron	SELV-300P									
Lutron	SLV-600P	1-20	1-10	1-10	1-10		1-15	1-15	1-20	1-10
Lutron	TG-600PR									
Lutron	TGCL-153P									
Lutron	TGCL-153PH									
Lutron	TT-300									
Leviton	VPI06									
Sensors										
Lutron	MSCL-OP153M		1-10	1-10	1-10		1-20	1-20	1-20	1-10
Lutron	MSCL-OP153MH	1-20	1-10	1-10	1-10		1-20	1-20	1-20	1-10
Lutron	MS-OPS2H									
Panel Modules										
Lutron	GP (Harrier) Card									
Lutron	HW-RPM-4A-120									
Lutron	HW-RPM-4U-120									
Lutron	LP-RPM-4U-120									

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

Misc. (G25,ST19)

Number of bulbs

											
		7.5T20/VIN/820/Amber/G/E26/SP/DIM 2/1CT	7.5A50/VIN/820/CL/G/E26/amber/SP/DIM 2/1CT	7.5G63/VIN/820/Amber/G/E26/SP/DIM 2/1CT	7.5T20/modern/840/CL/G/DIM 2/1CT	7.5G63/modern/840/CL/G/DIM 2/1CT	7.5A50/modern/840/CL/G/DIM 2/1CT	4T10/MOD/840/E26/CL/GL/DIM 4/1BC	4ST19/MOD/840/E26/CL/GL/DIM 4/1BC	4G25/MOD/840/E26/CL/GL/DIM 4/1BC	8.8ST19 DIM, 8ST19WG, 8.5A19 WG T20
		9290019365 (575241)	9290019364 (575233)	9290019363 (575225)	9290019368 (536318)	9290019366 (536292)	9290019367 (536300)	9290020009 (543132)	9290020010 (543140)	9290020008 (543124)	9290022960 (556530), 9290022961 (556548), 9290023277 (557587)
Company	Model No.										
Cooper	RI061-VW-K2										
Cooper	SAL06P										
Eaton	DAL06P										
Legrand	HCL453P										
Leviton	6602	1-3	1-3	1-3	1-3	1-3	1-3	3-15	3-15	3-15	
Leviton	6631										1-18
Leviton	6633	NR	NR	NR	NR	NR	NR	2-15	2-15	2-15	1-18
Leviton	6672	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-18
Leviton	6674	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-18
Leviton	6615P	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Leviton	DSE06										
Leviton	DSL06										1-30
Leviton	DSM10										
Leviton	IPI06	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-18
Leviton	IPL06										1-18
Lutron	AYCL-153P										
Lutron	CTCL-153P										
Lutron	CTCL-153PDH										
Lutron	DV-600P	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Lutron	DV-600PR										
Lutron	DVCL-153P	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-18
Lutron	DVCL-253P										
Lutron	DVELV-300P	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-9
Lutron	DVRP-253P										
Lutron	LGCL-153P										
Lutron	MACL-153M	1-3	1-3	1-3							1-18
Lutron	MAELV-600										
Lutron	MALV-600										
Lutron	MRF2-6ND-120	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Lutron	NTCL-250										
Lutron	NTELV-300										
Lutron	PD-5NE										
Lutron	PD-6WCL	1-3	1-3	1-3	1-3	1-3	1-3	2-15	2-15	2-15	1-18
Lutron	RRD-3LD										
Lutron	RRD-6NA	1-3	1-3	1-3							
Lutron	S-600P										
Lutron	SCL-153P										
Lutron	SCL-153PR										
Lutron	SELV-300P										
Lutron	SLV-600P	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-13
Lutron	TG-600PR										
Lutron	TGCL-153P										
Lutron	TGCL-153PH										
Lutron	TT-300										
Leviton	VPI06										
Sensors											
Lutron	MSCL-OP153M	1-3	1-3	1-3							1-18
Lutron	MSCL-OP153MH	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	1-18
Lutron	MS-OPS2H	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Panel Modules											
Lutron	GP (Harrier) Card	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Lutron	HW-RPM-4A-120	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Lutron	HW-RPM-4U-120	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Lutron	LP-RPM-4U-120	1-3	1-3	1-3	1-3	1-3	1-3	1-15	1-15	1-15	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.										
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.										
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).										
	Lamp not yet tested with this dimmer, compatibility unknown.										

Misc. (G25,ST19)

Number of bulbs

		 A50, G63 Filament T20	 4.5W (40W) G16.5 Filament dimmable	 3.8W WG G25 Filament T20, P0023793	 3.8W Dimmable G25 Filament T20, P0025721	 2.7W WG G25 Filament T20	 7W (40W Eq) G25 WG CC Bulb	 10W (60W Eq) G25 WG CC Bulb	 5.5W (40W Eq) Filament ST19
		9290019363 (536268), 9290019364 (536276), 9290019365 (536284)	9290018434 (478784), 9290012102 (461673), 9290013354 (475814)	9290019697 (549501), 9290019699 (549527), 9290019698 (549519), 9290019700 (549535)	9290022067 (549188), 9290022069 (549204), 9290022068 (549196), 9290022070 (549212)	9290022047 (549352), 9290022080 (549360)	9290011817 (458802, 458794, 458810)	9290011898 (459347), 9290011898 (459339), 9290011816 (458828), 9290011816 (458836)	9290012102 (461673)
Company	Model No.								
Cooper	RI061-VW-K2								
Cooper	SAL06P								
Eaton	DAL06P								
Legrand	HCL453P								
Leviton	6602		3-20	2	1-3	2-20	1-21	9-15	1-25
Leviton	6631	1-20							
Leviton	6633	1-20	2-20	1-10	1-5	2-15	1-21	1-15	1-15
Leviton	6672	1-20	1-20	1-5	1-5	8-20	1-21	1-15	1-15
Leviton	6674	1-20					1-21	1-15	1-10
Leviton	6615P		1-20	1-10	1-2	1-10	1-11	1-8	1-15
Leviton	DSE06								
Leviton	DSL06	1-20							
Leviton	DSM10								
Leviton	IPI06	2-20	4-20	2-3	1-5	1-20	1-21	1-15	1-25
Leviton	IPL06	1-20							
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-20	1-5	1-5	1-20	1-21	1-15	1-15
Lutron	DV-600PR								
Lutron	DVCL-153P	1-20							
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-20	1-10	1-20	1-20	1-11	1-8	1-15
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M	1-20	1-20	1-10	1-5	1-20	1-21	1-15	1-15
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-10	2-10	3-5	2-20	1-15	1-15	1-15
Lutron	NTCL-250								
Lutron	NTELV-300								
Lutron	PD-5NE								
Lutron	PD-6WCL	1-15	3-20	1-10	1-5	2-20	1-21	1-15	NR
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-20	1-10	1-3	1-20	NR	1-15	1-15
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P	1-20	1-20	1-10	1-10	1-20	1-16	1-11	1-15
Lutron	TG-600PR								
Lutron	TGCL-153P								
Lutron	TGCL-153PH								
Lutron	TT-300								
Leviton	VPI06								
Sensors									
Lutron	MSCL-OP153M	1-20	1-20	1-10	1-5	1-20	1-21	1-15	1-15
Lutron	MSCL-OP153MH	1-20	1-20	1-10	1-8	1-20	1-21	11-15	1-25
Lutron	MS-OPS2H		1-20	1-10	1-20	1-20	1-21	1-15	1-25
Panel Modules									
Lutron	GP (Harrier) Card		1-20	1-10	1-20	1-20	1-21	1-15	1-15
Lutron	HW-RPM-4A-120		1-20	1-10	1-5	1	1-21	1-15	1-15
Lutron	HW-RPM-4U-120		1-20	1-10	1-5	1	1-21	1-15	1-15
Lutron	LP-RPM-4U-120		1-20	1-10	1-5	1	1-21	1-15	1-15
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.								
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.								
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).								
	Lamp not yet tested with this dimmer, compatibility unknown.								

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Consumer Luminaires

Number of bulbs

		9290032595	9290032596	9290031754	9290031764
Company	Model No.				
Cooper	RI061-VW-K2				
Cooper	SAL06P				
Eaton	DAL06P				
Legrand	HCL453P				
Leviton	6602	1-3	1-3	1-3	1-3
Leviton	6631	1-3	1-3	1-3	1-3
Leviton	6633	1-3	1-3	1-3	1-3
Leviton	6672	1-3	1-3	1-3	1-3
Leviton	6674	1-3	1-3	1-3	1-3
Leviton	6615P	1-3	1-3	1-3	1-3
Leviton	DSE06				
Leviton	DSL06	1-3	1-3	1-3	1-3
Leviton	DSM10				
Leviton	IPI06	1-3	1-3	NR	NR
Leviton	IPL06	1-3	1-3	1-3	1-3
Lutron	AYCL-153P	1-3	1-3	1-3	1-3
Lutron	CTCL-153P	1-3	1-3	1-3	1-3
Lutron	CTCL-153PDH				
Lutron	DV-600P	1-3	1-3	1-3	1-3
Leviton	DV-600PR				
Lutron	DVCL-153P	1-3	1-3	1-3	1-3
Lutron	DVCL-253P	1-3	1-3	1-3	1-3
Lutron	DVELV-300P	1-3	1-3	1-3	1-3
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M	1-3	1-3	1-3	1-3
Lutron	MAELV-600				
Lutron	MALV-600				
Lutron	MRF2-6ND-120	1-3	1-3	1-3	1-3
Lutron	NTCL-250				
Lutron	NTELV-300				
Lutron	PD-5NE				
Lutron	PD-6WCL	1-3	1-3	1-3	1-3
Lutron	RRD-3LD				
Lutron	RRD-6NA	1-3	1-3	1-3	1-3
Lutron	S-600P				
Lutron	SCL-153P				
Lutron	SCL-153PR				
Lutron	SELV-300P				
Lutron	SLV-600P	1-3	1-3	1-3	1-3
Lutron	TG-600PR				
Lutron	TGCL-153P				
Lutron	TGCL-153PH				
Lutron	TT-300				
Leviton	VPI06				
Sensors					
Lutron	MSCL-OP153M	1-3	1-3	1-3	1-3
Lutron	MSCL-OP153MH	1-3	1-3	1-3	1-3
Lutron	MS-OPS2H				
Panel Modules					
Lutron	GP (Harrier) Card				
Lutron	HW-RPM-4A-120				
Lutron	HW-RPM-4U-120				
Lutron	LP-RPM-4U-120				

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.	WG = Warm Glow	AF = Air Flux	DS = Diamond Spark	CC = Clear Classic	DC = Die Cast	DW = Direct White	SO = Single Optic
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.							
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).							
	Lamp not yet tested with this dimmer, compatibility unknown.							

This image shows a full page of white paper with horizontal blue lines. The lines are evenly spaced and run across the width of the page, typical of notebook paper or a document template. There are no margins, text, or other markings present.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-21015CR 09/23 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.
All other trademarks are owned by Signify Holding or their respective owners.