

投光燈



150W / 200W新上市

沛亮 LED 投光燈特色

- 超薄一體式設計
- 高品質鑄鋁外殼，防水防塵防衝擊
- 適用於戶外招牌投光



LED



亮麗柔和
舒適感受



輕巧靈活
美觀簡潔



設計精良
安全可靠



經久耐用
經濟節能



無藍光
危害認證

產品型號	電壓	耗電	色溫	光通量(流明)	演色性	壽命	尺寸	防水防塵等級
PILA-BVP01040	110-240V	10W	4000K	900	80	10,000小時	103x137x34mm	IP65/IK06mm
PILA-BVP01065			6500K					
PILA-BVP03040		30W	4000K	2700				
PILA-BVP03065			6500K					
PILA-BVP05040		50W	4000K	4500				
PILA-BVP05065			6500K					
PILA-BVP10040		100W	4000K	9000				
PILA-BVP10065			6500K					
PILA-BVP15030		150W	3000K	12000			375x292x38mm	
PILA-BVP15065			6500K	12570				
PILA-BVP20030	200W	3000K	16000	429x334x38mm				
PILA-BVP20065		6500K	17000					

