



Lámpara LED Alta Potencia

Mayores beneficios,
al menor costo.



Especificaciones

80   
CRI 220-240V 10,000 h No dimerizable

Nombre comercial	PILA LED HB 2700lm 25W 865 E27	PILA LED HB 3600lm 35W 865 E27	PILA LED HB 4500lm 45W 865 E27
12NC	929003000612	929003000812	929003001012
Potencia (W)	25	35	45
Flujo luminoso (lm)	2.700	3.600	4.500
Eficiencia (lm/W)	108	102	100
Temperatura de color (K)	6.500	6.500	6.500
IP	IP20	IP20	IP20
Factor de potencia	> 0.5	> 0.5	> 0.5
Formato	T80	T100	T120
Reemplazo (W)	55W CFLi	65W CFLi	82W CFLi
Base	E27	E27	E27

Beneficios:

- ▶ Confiabilidad
- ▶ Ahorro de energía
- ▶ Amplio rango de aplicación
- ▶ 1 año de garantía

Aplicaciones:

- ▶ Talleres
- ▶ Industrias
- ▶ Depósitos
- ▶ Áreas cerradas de gran altura

Datos comerciales

Nombre comercial	Altura / largo total (mm)	Ancho / diámetro (mm)	EAN	Cant x caja
PILA LED HB 2700lm 25W 865 E27	141	82	8727900972054	6
PILA LED HB 3600lm 35W 865 E27	174	102	8727900972092	6
PILA LED HB 4500lm 45W 865 E27	199	121	8727900972139	6