




# Luminaire Panel



Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_

Notes: \_\_\_\_\_

The Pila BP is a backlit LED flat panel that provides a uniformly lit lens for a clean aesthetic appeal, and even distribution of light to the space to minimize the number of light points needed. Shallow depth and light weight make the BP flat panel a versatile and easy to use product in applications such as schools, office, and retail.

## Product offering

Catalog Code	Description	UPC Code	Case Qty. (pc/carton)	Pallet Qty. (pc/pallet)
BP2230L40KU	2x2 Panel, 30W, 3000 LUMENS, 4000K, 120-277V, 0-10V DIM	190096130788	2	28
BP2448L40KU	2x4 Panel, 48W, 4800 LUMENS, 4000K, 120-277V, 0-10V DIM	190096130795	2	14
BP2230L35KU	2x2 Panel, 30W, 3000 LUMENS, 3500K, 120-277V, 0-10V DIM	190096130801	2	28
BP2448L35KU	2x4 Panel, 48W, 4800 LUMENS, 3500K, 120-277V, 0-10V DIM	190096130818	2	14

## Technical specifications

<b>Nominal power</b>	2x2: 38W, 2x4: 48W
<b>Nominal lumens</b>	2x2: 3000 lumens, 2x4: 4800 lumens
<b>Input voltage</b>	120-277V, 50/60Hz
<b>Dimming</b>	0-10V to 10%
<b>CCT</b>	3500, 4000K
<b>CRI</b>	≥80
<b>Power Factor (system)</b>	>0.9
<b>System Efficacy</b>	>100 lm/W
<b>Material and finishing</b>	White painted finish, steel housing and driver box, extruded aluminum frame, acrylic diffuser
<b>Mounting</b>	Recessed T-Bar NEMA G 15/16", NFG 9/16", T-bar clips provided (4)
<b>Weight</b>	2x2: 5.3lb (2.4kg), 2x4: 10.1lb (4.6kg)
<b>IP/IK rating</b>	IP20 / IK03




<b>Operating temperature range</b>	14°F to 95°F (-10°C to 35°C)
<b>Lifetime</b>	50K hrs @ L70 B50 @Ta 25°C
<b>Compliance</b>	cETLus listed for use in damp locations
<b>Warranty</b>	5-year limited warranty





## Dimensions

2x2



2x4

47.72 in  
1212 mm

