



PILA Wall mounted

PILA WL007C LED10S/840 PSU RND WH G2

PILA Wall mounted – LED Module, system flux 1000 lm – 840 neutral white – Power supply unit – Round – White

Benefits

- Available with motion sensor
- Supports energy saving
- Available in round and oval
- For wall and ceiling mounted



Product data

General information

Lamp family code	LED10S [LED Module, system flux 960 lm]
Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	Beam angle 110°
Control interface	No
Connection	Screw terminal
Protection class IEC	Safety class II
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
Service tag	-
Product family code	WL007C [PILA Wall mounted]

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.5

Surge Protection (KV)	-
-----------------------	---

Controls and Dimming

Dimmable	No
Motion sensor	No

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover/lens material	-
Optical cover/lens finish	-
Overall height	76 mm
Overall diameter	170 mm
Color	White
Accessory	-

Approval and Application

Ingress protection code	IP54
Mech. impact protection code	IK06

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1000 lm
Initial LED luminaire efficacy	83 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	12 W



PILA LED Wall mounted

Over Time Performance (IEC Compliant)

Lifetime L70B50	35,000 h
-----------------	----------


Application Conditions

Performance ambient temperature Tq	-
------------------------------------	---

Product Data

Full product code	-
Order product name	PILA WL007C LED10S/840 PSU RND WH G2
EAN/UPC - Product	8710163364421
Order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401774752
Net Weight (Piece)	-

Dimensional drawing





PILA Wall mounted

PILA WL007C LED13S/840 PSU RND MDU WH

PILA Wall mounted – LED Module, system flux 1300 lm – 840 neutral white – Power supply unit – Round – Motion Detection Unit – White

Benefits

- Available with motion sensor
- Available in round and oval
- Supports energy saving
- For wall and ceiling mounted



Product data

General information

Lamp family code	LED13S [LED Module, system flux 1300 lm]
Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Screw terminal
Protection class IEC	Safety class II
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
Service tag	-
Product family code	WL007C [PILA Wall mounted]

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.9

Surge Protection (KV)	-
-----------------------	---

Controls and Dimming

Dimmable	No
Motion sensor	Yes

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover/lens material	-
Optical cover/lens finish	-
Overall height	66 mm
Overall diameter	182 mm
Color	White
Accessory	-

Approval and Application

Ingress protection code	IP54
Mech. impact protection code	IK06

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1300 lm
Initial LED luminaire efficacy	86,7 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 70
Initial chromaticity	-
Initial input power	15 W



PILA LED Wall mounted

Over Time Performance (IEC Compliant)

Lifetime L70B50	20,000 h
-----------------	----------


Application Conditions

Performance ambient temperature Tq	-
------------------------------------	---

Product Data

Full product code	-
Order product name	PILA WL007C LED13S/840 PSU RND MDU WH
EAN/UPC - Product	8710163335117
Order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401735142
Net Weight (Piece)	-

Dimensional drawing





PILA Wall mounted

PILA WL007C LED16S/840 PSU RND WH G2

PILA Wall mounted – LED Module, system flux 1600 lm – 840 neutral white – Power supply unit – Round – White

Benefits

- Available with motion sensor
- Supports energy saving
- Available in round and oval
- For wall and ceiling mounted



Product data

General information

Lamp family code	LED16S [LED Module, system flux 1600 lm]
Light source color	840 neutral white
Light source replaceable	-
Number of gear units	1 unit
Driver/power unit/transformer	PSU [Power supply unit]
Driver included	Yes
Emergency Lighting	-
Optic type	-
Control interface	No
Connection	Screw terminal
Protection class IEC	Safety class II
Mounting	-
CE mark	Yes
EU RoHS compliant	Yes
Constant light output	No
Number of products on MCB of 16 A type B	-
Service tag	-
Product family code	WL007C [PILA Wall mounted]

Operating and Electrical

Input Voltage	220-240 V
Input Frequency	50 to 60 Hz
Inrush current	-
Inrush time	-
Power Factor (Min)	> 0.5

Surge Protection (KV)	-
-----------------------	---

Controls and Dimming

Dimmable	No
Motion sensor	No

Mechanical and Housing

Housing Material	Polycarbonate
Optical cover/lens material	-
Optical cover/lens finish	-
Overall height	88 mm
Overall diameter	220 mm
Color	White
Accessory	-

Approval and Application

Ingress protection code	IP54
Mech. impact protection code	IK06

Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	1600 lm
Initial LED luminaire efficacy	80 lm/W
Init. Corr. Color Temperature	4000 K
Init. Color Rendering Index	> 80
Initial chromaticity	-
Initial input power	20 W



PILA LED Wall mounted

Over Time Performance (IEC Compliant)

Lifetime L70B50	35,000 h
-----------------	----------

Application Conditions

Performance ambient temperature Tq	-
------------------------------------	---

Product Data

Full product code	-
Order product name	PILA WL007C LED16S/840 PSU RND WH G2
EAN/UPC - Product	8710163364438
Order code	-
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	911401774762
Net Weight (Piece)	-

Dimensional drawing

