



Get the most out of your time and money

An affordable solution for all of
your floodlighting requirements

DuraForm floodlights meet a broad range of application needs. Configurable and easy to specify, this family offers a wide variety of lumen ranges, optical distributions, mounting options, and controls choices.

Features

- Lumen output ranges from 2,600 – 54,600
- Efficacies up to 138 lumens per watt
- Yoke, Slip Fitter with cord or with wiring through Slip Fitter
- Four distributions: NEMA 3x3, 7x4, 7x5, and 6x5
- Three position terminal block standard
- Tool-less latches or vandal proof access options available
- Field installable shielding options control spill light
- Multiple control options range from simple to advanced

Visor
Top or
Bottom



Glare Shield
Left or Right



Wire Guard



1 Accessory mounting

Shields and Visors easily install in the field

2 LEDs + optics

High performance optics optimized for maximum spacing, target lumens and lighting uniformity

3 Tool-less latches optional

Allows easy access, operable while wearing protective electrical gloves



4 Adjustable aiming

Fully adjustable, durable brackets provide extensive aiming flexibility, integral aiming marks



5 Lens

Tempered glass lens with IK09 impact rating

6 Gasketing

Optical chamber gasketed for IP66 seal

7 Hinged door frame

Allows for easy access to electrical compartment

8 Cast-in alignment guide

For ANSI wattage and source label





Twist-lock receptacle

Optional Twist-lock 7-pin receptacle (TT7)



9 Cast-in sight

Enables easy aiming day or night

10 Driver

Mounted for optimal heat dissipation

11 Surge suppression

10kV/10kA standard, 20kV/10kA optional

12 Field Adjustable Wattage Selector (FAWS)

Optional, allows for output to be reduced in the field

13 Terminal block

Standard on all DuraForm luminaires

14 Tethered door

Tethered door provides additional security

15 IP66 Rated luminaire

Gaskets weatherproof the interior

16 Service Tag

QR code labels allow for ease of maintenance and tracking



FLDS/FLDM/FLDL DuraForm floodlights

Product comparison

Slip Fitter
with external
cord shown




Slip Fitter
with internal
wiring shown



Yoke
Mount
shown




| | FLDS | FLDM | FLDL |
|--|--|----------------|-----------------|
| Lumen Output Range | 2,581 - 12,385 | 8,762 - 26,595 | 15,670 - 54,641 |
| Efficacy | 81 - 131 | 83 - 130 | 85 - 138 |
| HID Replacement | 70W - 200W | 175W - 400W | 250W - 1000W |
| Distribution | A33 Asymmetric (NEMA 6x5), Rectangular Spot (NEMA 3x3), Rectangular Narrow Flood (NEMA 7x5), Rectangular Medium Flood (NEMA 7x4) | | |
| Mounting | Yoke, Slip Fitter with internal wiring, Slip Fitter with external cord | | Yoke |
| Color Temperature | 3000K & 4000K Standard, 2700K & 5000K Available as ETO | | |
| IP Rating | IP66 | | |
| Vibration | Normal (both Slip Fitters), Bridge / Overpass (Yoke) | | |
| DLC Listing | Standard and Premium | | |
| Field Adjustable Wattage Selector (FAWS) | ✓ | ✓ | ✓ |
| DALI Driver | ✓ | ✓ | ✓ |
| SiteWise | ✓ | ✓ | ✓ |
| Limelight by Lutron Capable | ✓ | ✓ | ✓ |
| SiteWise | ✓ | ✓ | ✓ |
| 7-pin Tool-less NEMA Twist-Lock Receptacle | ✓ | ✓ | ✓ |
| Photocontrol Button | ✓ | ✓ | ✓ |
| Surge Protection | 10kV/10kA Standard, 20kV/10kA Optional | | |
| Optional Features | ANSI Label, Tool-less Latches, Vandal Proof Access | | |
| Accessories | Wire Guard, Top or Bottom Visor, Left or Right Glare Shield | | |
| Finish | Black, Bronze, Medium Grey, Optional or Special finishes available | | |
| Temperature Rating | -40°C (-40°F) up to +40°C (+104°F); up to +50°C (+122°F) available - consult factory | | |




A33 Asymmetric 33° Flood
(NEMA 6x5)

30' or 9.14m mounting height, 30° tilt




RSP Rectangular Spot
(NEMA 3x3)

15' or 4.57m setback, 0° tilt



RNF Rectangular Narrow Flood
(NEMA 7x5)

15' or 4.57m setback, 45° tilt



RMF Rectangular Medium Flood
(NEMA 7x4)

10' or 3.05m setback, 30° tilt

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.



© 2019 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. All trademarks are owned by Signify Holding or their respective owners.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008