



**GARDCO**

by **Signify**

**Floodlighting**

**DuraForm LED**

**FLDS/FLDM/FLDL**



## The simple choice for your diverse needs

We get it...you need it all,  
versatility, durability,  
and performance.  
You must deliver on all  
levels. Gardco DuraForm  
floodlight is your solution.

Like all Gardco luminaires, DuraForm gives you peace of mind that you're recommending a quality product that meets all of those requirements. IP66, IK09, and Vibration rated, these floods are rugged enough to function well even in demanding environments, yet sleekly designed with a low profile. As an added bonus, they are backed by our exclusive Service Tag, which includes quick registration, remote monitoring, and spare parts identification, for assistance throughout the life of the product.



# FLDS/FLDM/FLDL DuraForm floodlights




## Benefits


- Three sizes to provide the right light for your needs
- Three mounting options for a variety of applications
- Rugged construction to stand up to harsh environments
- Low profile design blends in with surroundings
- DLC Standard and DLC Premium configurations available

## Features


- Lumen output ranges from 2,600 – 54,600
- Efficacies up to 138 lumens per watt
- Yoke and two Slip Fitter mountings available
- Four distributions range from tight spot to rectangular medium
- Multiple control options range from simple to advanced
- Three standard finish options, with special finishes available




A33 Asymmetric 33° Flood  
(NEMA 6x5)  
30' or 9.14m mounting height, 30° tilt



RSP Rectangular Spot  
(NEMA 3x3)  
15' or 4.57m setback, 0° tilt



RNF Rectangular Narrow Flood  
(NEMA 7x5)  
15' or 4.57m setback, 45° tilt



RMF Rectangular Medium Flood  
(NEMA 7x4)  
10' or 3.05m setback, 30° tilt

The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.

