

Gardco site and area luminaires blend excellent performance with award winning aesthetics. Multiple styles are available for a range of different mounting heights and applications.



Rating	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Best	Best	Best	Best	Best	Best
Product	OptiForm Area Small	OptiForm Area Medium	OptiForm Area Large	EcoForm Area Small	EcoForm Area Large	PowerForm Site and Area	Gullwing Large LED	Form Ten Square Area LED Comfort	Form Ten Square Area LED	Form Ten Round Area LED Comfort	Form Ten Round Area LED	Form Ten Round Area LED	Site and Area Small Round Comfort	Site and Area Small Square Comfort	Site and Area Small Square Precision	PureForm Area Medium Comfort	PureForm Area Medium Precision	PureForm Area Large Precision
Prefix	OPF-S	OPF-M	OPF-L	ECF-S	ECF-L	PFAS	GL18	EH14L-140L	EH14L/EH19L	CA17-140L / MA17-140L	MA17 / MA22L	CA17 / CA22L	P20-C	P15-C	P15-P	P26	P26	P34
Lumen Output Range (4000K, 70CRI)	7,000-22,000	13,500-34,000	34,000-67,000	5713-27,526	29,299-50,641	34,640-103,975	5,710-29,497	2123-9182	5,203- 21,754	1959-9509	5,141-21,852	5,141-21,852	2,100-16,300	2,200-10,800	1,700-16,500	2,200-9,100	6,700-28,900	22,200-50,000
Efficacy (4000K, 70CRI)	140-183	150-190	150-190	113-133	112-128	87-119	87-124	92-108	93-113	84-108	97-113	97-113	97-127	103-126	109-160	92-105	98-152	87-133
Distributions	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 4W 5, 5N, 5W, AFR, BLC, LEED Corner	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5, 5W, AFR	Type 2, 3, 4, 5W, AFR	Type 2, 3, 4, 5	Type 2, 3, 5	Type 2, 3, 4, 5	Type 1, 2, 3, 5	Type 2, 3, 4, 5	Type 2, 3, 4, 5	T1S, T2S, T4S, 4CD, T5S	T1S, T2S, T4S, 4CD, T5S	T2M, T3M, T4S, T5S, BLC	Type 2, 3, 5	Type 2, 3, 4, 5, 5W, AFR, BLC	Type 2, 3, 4, 5, 5W, AFR, BLC
Color Temperatures	2700, 3000, 4000, 5700	2700, 3000, 4000, 5700	2700, 3000, 4000, 5700	3000, 4000, 5000	3000, 4000, 5000	3000, 4000	3000, 4000, 5700	3000, 4000, 5000	3000, 4000, 5700	3000, 4000, 5000	3000, 4000, 5700	3000, 4000, 5700	2700*, 3000, 3500*, 4000, 5000*	2700*, 3000, 3500*, 4000, 5000*	2700*, 3000, 3500*, 4000, 5000*	2700, 3000, 4000, 5000, Amber	2700*, 3000, 4000, 5000, Amber*	2700*, 3000, 4000, 5000, 5000, Amber*
Mounting Height Range	8'-20'	20'-30'	25'-50'	8-40'	8-40'	8-40'	8-40'	8-20'	8-40'	8-20'	8-40'	8-40'	10'-25'	10'-25'	10'-25'	10'-25'	15-35'	30-50'
0 Uplight	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	✓	✓	✓	✓	-	-	-	-	-	-	-	✓	✓	✓	✓	✓	✓
Dual Circuit Control	-	-	-	✓	✓	✓	✓	-	-	-	-	-	-	-	-	-	✓	✓
Auto Profile Dimming	✓	✓	✓	✓	✓	✓	✓	-	-	-	-	-	✓	✓	✓	✓	✓	✓
Motion Response	✓	✓	✓	✓	✓	✓	✓	-	-	✓	-	-	✓	✓	✓	✓	✓	✓
Microwave Hidden Motion Response	-	-	-	-	-	-	-	✓	-	-	-	-	✓	✓	-	-	-	-
Interact Outdoor	✓	✓	✓	✓	✓	✓	✓	-	-	-	-	-	-	-	-	-	-	-
SR Driver with Zhaga Socket	✓	✓	✓	✓	✓	-	-	-	-	-	-	-	✓	✓	✓	-	-	-
Service Tag Standard	✓	✓	✓	✓	✓	✓	-	-	-	✓	-	-	-	-	-	✓	✓	✓
Photocell	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5,TLRD7,TLRPC	Button, TLRD5,TLRD7,TLRPC	Button, TLRD5,TLRD7,TLRPC	Button, TLRD7	TLRD5,TLRPC	TLRD5,TLRPC	TLRD5,TLRPC	TLRD5,TLRPC	TLRD5,TLRPC	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7	Button, TLRD5, TLRD7
Additional Options	Outdoor Multi Sensor, Shielding, Fusing, Increased Surge Protection (20 kA)	Outdoor Multi Sensor, Shielding, Fusing, Increased Surge Protection (20 kA)	Outdoor Multi Sensor, Shielding, Fusing, Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	-	-	-	-	-	-	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)	Increased Surge Protection (20 kA)
Mounting	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Retrofit Arm, Mast Arm, Wall Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Arm Mount, Slip Fitter Mount	Pole Mounted	Arm mounts, Wall mount, Mast Arm Fitter	Arm mounts, Wall mount, Mast Arm Fitter	Arm mounts, Wall mount, Mast Arm Fitter	Arm mounts, Wall mount, Mast Arm Fitter	Arm mounts, Wall mount, Mast Arm Fitter	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount	Standard Arm, Adjustable Slipfitter, Wall Mount, Retrofit Arm Mount
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Natural Aluminium	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze Anodized, Black Anodized, Natural Anodized, Bronze, White, Medium Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP65 Luminaire, IP66 Light Engine	IP65 Luminaire, IP66 Light Engine	IP65 Luminaire, IP66 Light Engine	IP66	IP66	IP66	IP66	Wet Location	Wet Location	Wet Location	Wet Location	Wet Location	IP66	IP65	IP65	IP65	IP65	IP66
Vibration	3G/Level 2 Bridge and Overpass Rated	3G/Level 2 Bridge and Overpass Rated	3G/Level 2 Bridge and Overpass Rated	3G	3G	1.5G	-	-	-	-	-	-	Level 2 (3.8G)	Level 2 (3.8G)	Level 2 (3.8G)	Level 2 (3G)	Level 2 (3G)	Level 1 (1.5G)
DLC Listing	Premium	Premium	Premium	Premium	Premium	Standard	Standard	Standard	Standard	Standard	Standard	Standard	Standard & Premium	Standard & Premium	Standard & Premium	Standard	Premium	Premium
Certifications	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	cULus	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL	UL/cUL
Lifetime	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h	L70 >100,000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link																		