



ReadytoGo Lighting Guide



We couldn't increase
the speed of light,
but we found a way
to get it to you faster.



signify.com/quickship

2023 Q4 Edition

Stock Product

quickship

Choose Signify for great value,
high performance lighting brands
that are ReadytoGo

Introducing our latest **QuickShip ReadytoGo lighting guide**. This new guide has been revamped with an updated product mix that is designed to meet the day-to-day needs of a wide range of lighting projects.

This guide is designed to help support shelf-stocking requirements and discretionary design-build projects with lighting solutions that are ready to ship.

Choose from a wide array of **Stock Ready** products (order to ship in 2-days*) and **Design Ready** products (order to ship in 10 days*) which can help meet those demanding timelines on the job.

For the latest information, visit:

signify.com/quickship

* Service time is calculated from the time the order is entered until it is shipped. See page 5 for full details.



Architectural Lighting	10	Why choose Signify?	4
Office & Industrial Lighting	12	Commitment	5
High Bays	14	Definitions	91
Linear	18	Tools & Resources	92
Grid / Recessed	24		
Indoor Track & Downlighting	32		
Core Downlights	34		
Downlight Kits	42		
Track Lighting	62		
Commercial Outdoor Lighting	70		
Site & Area, Garage & Canopy	72		
Floods & Wall Packs	76		
Special Application	80		
Landscape	81		
Connected Lighting Controls	82		
LED Lamps & Retrofits	84		
LED Electronics	88		



A long history of excellence

As the global leader in lighting for more than 130 years, Signify has the know-how and most comprehensive portfolio to meet any application. We achieved 100% carbon neutrality in 2020. We are number 1 in conventional lamps, LED and Connected lighting. We have over 17,750 patents. We invest 4.8% of total sales in R&D which is two times our nearest competitor! We understand that partnerships are more than sales.

Let's grow together. We are ready to go with you.

Quick and reliable service out of our two distribution centres and two manufacturing facilities.



Find just what you need

Our Stock Ready portfolio makes it easy to find just what you need. Our products are designed for easy ordering through Signify's MyLighting portal. Ready to go products are easy to install with minimal steps, and competitively priced to meet the demands of budget conscious projects focused on cost and energy. Distributors can also benefit from our Stock Ready program which offers deals on freight, guaranteed sales, price change reimbursement, delistment notifications, marketing support, merchandising, and more.

Certifications & labels



Commitment

Our delivery commitment is backed by a significant investment in finished goods and component inventory.

If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs and confirm an acceptable ship date.

In case you have questions, please contact your sales representative or Customer Service.

Order Related Inquiries:
canada.om@signify.com / 1-800-668-9008

General Inquiries: 1-800-555-0050

MyLighting: www.mylighting.signify.com

ReadytoGo	Stock Ready	Design Ready	Spec Ready
Service Offering	Stock & Flow	Design Build	Spec / Bid / Buy
Stock / Order / Sell through Support	•	•	•
Lamps, Ballasts, Luminares	2-Day Order to Delivery	10-Day Order to Delivery	Ships in 4-6 weeks
Filterable on eCatalogue	•	•	•
Returnable	•		

Terms and Conditions

Freight prepaid on all **ReadytoGo** stock orders with combined orders greater than \$3000.

Options available for orders less than \$3000, contact plc-orderentry@signify.com for more information.

Visit www.signify.com/en-ca/support/warranties for details on our standard terms and conditions.

Order Process

Lead time is from the time the order is entered and received by our warehouse. We are committed to entering orders within 24 hours of receipt.

To ensure your order is processed without delay, we recommend you have the following:

- Correct Catalogue Numbers
- Price detail (Deal#, SPA reference)
- Tag "Quick Ship" on your order

Large Orders

To ensure we satisfy all our customers optimally within the committed lead times, maximum order quantities may apply. If the order exceeds the set threshold, Signify will contact you to work out a feasible schedule for your large order. It is always advised to work with your Signify representative to give advance notice of any foreseeable large orders.


Transportation timelines

For **Stock Ready** products, Signify maintains stock levels at our warehouse in Markham, Ontario in order to provide our customers with quick access to the inventory you require. You can calculate when to expect your shipment by adding the following transportation times to the day it leaves our warehouse.

Toronto / Ottawa / Montreal	+1 Day
Windsor	+2 Days
Sudbury / Quebec City	+3 Days
Manitoba / New-Brunswick	+4 Days
Saskatchewan / Nova Scotia / P.E.I.	+5 Days
Alberta	+6 Days
British Columbia / Newfoundland	+7 Days

The right solution for every need.

Signify provides the solution to every lighting need, whether it's lighting and connecting your public spaces, giving your commercial building an energy saving upgrade, or working on a yet to be constructed hospital, we've got you covered.



Ready to Go – Lighting solutions for every need.


Save time and improve efficiencies by consolidating your stock purchases with us! Our Ready to Go portfolio comprised of our 2-day and 10-day quick ship offering makes it easy to find just what you need.

Indoor luminaires

LEDALITE by @ignify Pg 10	ArcForm	VersaForm	PureFX	Vectra	SilkSpace	Shine
ModiFly	FloatPlane	BoldPlay	Sync	Verge	Jump	Sona
SyncLine Linear	Chopstick	TruGroove Suspended	TruGroove Recessed	TruGroove Recessed Micro	TruGroove Perimeter	TruGroove Cove
Lumen Select Switch UN3 Universal 120-347V CCT with Select Switch						
Day-Brite CPI by @ignify	FBY LED High Bay 16	FBZ LED High Bay 16	FCY Value High Bay Selectable 17	HCY Sealed High Bay Selectable 17	FluxStream LED Industrial 20	FluxStream LED Strip EZ 20
FluxStream LED Strip 21	FluxStream LED Wraparound 21	NWL Selectable Wraparound 22	OWL LED Wraparound 22	SDS Strip Dual Select 22	Vaporlume V3W LED 23	Vaportite Dual Select 23
T Series T8 Strip 23	FluxPanel LED Gen. 2 26	Selectable Backlit Panel Dual Select 27	ClearAppeal LED Gen.2 28	FormFlex LED 29	SofTrace LED 30	FluxGrid Recessed LED 31

Indoor luminaires

LIGHTOLIER
by @ignify



Flat Downlight Dual Select
36



Downlight Dual Select
36



Mini Downlight LED
36



Gimbal Dual Select
36



Commercial Retrofit Downlight Dual Select
37



Residential Retrofit Downlight Dual Select
37



CorePro LED
37



Surface Mount Downlight Dual Select
38



SlimSurface LED Round
38



SlimSurface LED Square
41



EasyLyte LED Round
46



LyteProfile LED
48



Calculite LED
51



LyteCaster LED Accent
58



LyteCaster LED
59



LytePoints Conventional
61



Basic Track
64



Alycon Vertical Medium
66



Alycon Vertical LED Large
66



Alycon Recessed Multiples
66



BoldFlood
67



LightFlood
67



OmniSpot
67



OmniSpot Recessed Multiples
68



Conventional Track Heads
69

interact



Interact Scalable System
82

Outdoor luminaires

GARDCO
by @ignify



EcoForm
74

KEENE
by @ignify



Area Light Gen 2 Selectable Wattage
75



Post Top Selectable Wattage
75



Garage & Canopy Dual Select Square
75



Garage & Canopy Dual Select Round
75



Slim Flood Dual Select
78



LWL Wall Light LED
78



SWL Square Wall Light LED
78



Tall Wall Pack LED
78



Wall Pack Dual Select
78



Adjustable Slim Wall Pack Selectable
78



LytePro LED Wall Sconce (S & M & L)
78



RoughLyte LED
80

HABCO
by @ignify



FlexScape MUL4 LED
81



FlexScape BL9 LED
81



Accent Lighting, Line Voltage
81



BL5016 Micro Accent
81

LED Lamps & Retrofits

PHILIPS
LED lamps



EvoKit Click LED Retrofit kits
85



CorePro GU10 & MR16
86



CorePro A-Shape
86



CorePro PAR
86



Reflectors
86




UniversalFit T8
87



MasterClass MainsFit T8 (Type B)
87



CorePro MainsFit T5 & T8 (Type B)
87



MasterClass InstantFit T5 & T8 (Type A/C)
87



CorePro InstantFit T5 & T8 (Type A/C)
87

LED Electronics

ADVANCE
by @ignify



Xtanium LED Driver
89



Centium Ballasts
89



Optanium Ballasts
89



Core & Coil HID Ballasts
89



ModiFly

Architectural Lighting

Ledalite's award-winning, inspiring, and innovative lighting solutions allow specifiers to create a unique vision for a range of interior spaces.

You don't have to sacrifice product quality and performance for critical timing. With the Ledalite QuickShip program, we'll ship your order within 10 working days of order receipt.

This program applies to almost all of our product families, so while we can't increase the speed of light, we did find a way to get you your lighting faster.

Category	Limit per Release
Linear Luminaires	500 linear ft.
Recessed Troffers	100 luminaires

Order limits and exclusions apply. Contact your Signify sales rep for details. For more information please visit [signify.com/en-ca/brands/ledalite/quickship](https://www.signify.com/en-ca/brands/ledalite/quickship)

Recessed



ArcForm



VersaForm



PureFX



Vectra



SilkSpace



Shine

Suspended



ModiFly



FloatPlane



BoldPlay



Sync



Verge



Jump



Sona



SyncLine Linear



Chopstick


TruGroove Family



TruGroove Suspended



TruGroove Recessed




TruGroove Recessed Micro



TruGroove Perimeter




TruGroove Cove



FloatPlane



TruGroove



Selectable Backlit Panel Dual Select (SBP) | Pg. 27




FluxStream LED Strip (FSS) | Pg. 21

Office & Industrial Lighting

Affordable and energy efficient stand-alone and connected lighting solutions for general purpose commercial or industrial projects.

Day-Brite CFI is an industry leader in general purpose and performance lighting systems. With products ranging from high performance recessed ceiling troffers to industrial grade high bay luminaires, Day-Brite CFI's extensive portfolio offers the utmost in quality, performance and efficiency for a variety of applications.



Vaporlume V3W LED | Pg. 23

High Bays 14

LED Quick Selection Guide 15

FBY LED High Bay	16
FBZ LED High Bay	16
FCY Value High Bay Selectable	17
HCY LED High Bay	17

Linear 18

LED Quick Selection Guide 19

FluxStream LED Industrial (FSI)	20
FluxStream LED Strip EZ (FSSEZ)	20
FluxStream LED Strip (FSS)	21
FluxStream LED Wraparound (FSW)	21
NWL Wraparound Selectable	22
OWL LED Wraparound	22
SDS Strip Dual Select.	22
Vaporlume V3W LED	23
Vaportite Dual Select	23
T Series T8 Strip	23


Grid / Recessed 24

LED Quick Selection Guide 25

FluxPanel LED Gen. 2 (FPZ)	26
Selectable Backlit Panel Dual Select (SBP)	27
ClearAppeal LED Gen. 2 (CAX)	28
FormFlex LED (FFX)	29
SofTrace LED (STX)	30
FluxGrid Gen. 2 Recessed LED (FGX)	31

High Bays

High Bays
LED Quick Selection Guide



Ideal illumination
for large industrial
warehouse and
institutional spaces

Choose Day-Brite CFI by Signify for a complete selection
of professional office & industrial lighting products.
Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

FBZ LED High Bay

Day-Brite CFI

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



FBY LED High Bay



FBZ LED High Bay



FCY Value High Bay Selectable



HCY LED High Bay

Product Family	FBY LED High Bay	FBZ LED High Bay	FCY Value High Bay Selectable	HCY LED High Bay
Page Reference	pg. 16	pg. 16	pg. 17	pg. 17
Quick Ship Service	● ■	■	● ■	●
Budget / Grade	Performance / Better	Value / Better		

Features / Performance	Sizes	L=24-1/8" (613mm) × W=11-1/2" (292mm) L=47-7/8" (1216mm) × W=11-1/2" (292mm)	L=23-7/8" (606mm) x W=17-1/4" (438mm) L=27-3/4" (705mm) x W=23-3/8" (594mm)	L=24-7/8" (630mm) × W=11-7/8" (300mm) L=24-7/8" (630mm) × W=14-1/8" (360mm)	Ø 11-3/8" Ø 13-3/4"
	Lumens (lm)	12000-60000	8000-60000	15000 / 22000 / 29000	14000 / 21000 / 28000 / 33000
	Efficacy (lm/W)	up to 148	up to 175	up to 140	up to 144
	Dimming	0-10V	0-10V	0-10V	0-10V
	CCT (K)	3500K* 4000K	3500K* 4000K 5000K	Field Selectable 4000K 5000K	Field Selectable 4000K 5000K
	CRI	80	80	80	80
	Voltage (V)	120-277V / 347V 120V / 208V / 277V / 480V*	120-277V / 347V 120V / 208V / 277V / 480V*	120-277V / 347V	120-347V
	Lens	Clear Acrylic* Frosted Acrylic*	Clear Acrylic* Frosted Acrylic*	Frosted Clear Acrylic	Clear Polycarbonate
Ratings & Certification	Interact Ready	◆	◆		
	IP / Wet Location Rating				IP65
	Other Ratings				NEMA 4X
	cULus Listed			✓	✓
	cETLus Listed	✓	✓		
	DLC	Premium	Standard / Premium	Premium	Premium
	Lifetime (L70)	up to 100,000 hours	up to 100,000 hours	up to 50,000 hours	up to 50,000 hours
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.			

● Stock Ready (2-Day Quick Ship)

■ Design Ready (10-Day Quick Ship)

✓ Standard Feature

* ◆ Spec Ready / Additional Options Available, see spec sheet for details



Product	Description / Features		UPC
FBY LED High Bay			
■ FBY12L835-347	12000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FBY12L835-UNV	12000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	1 90096 18719 5
■ FBY12L840-347	12000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY12L840-UNV	12000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65312 5
■ FBY18L835-347	18000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY18L835-UNV	18000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY18L840-347	18000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY18L840-UNV	18000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65311 8
■ FBY24L835-347	24000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY24L835-UNV	24000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY24L840-347	24000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	7 84197 66555 5
● FBY24L840-UNV	24000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65310 1
● FBY24L840-UNV-WC6	24000lm, 4000K (CRI 80), UNV, Wired 6' 16/3 cord, 0-10V Dimming	PREMIUM	7 84197 66556 2
■ FBY30L835-347	30000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY30L835-UNV	30000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY30L840-347	30000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY30L840-UNV	30000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65309 5
■ FBY36L835-347	36000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY36L835-UNV	36000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY36L840-347	36000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	1 90096 18770 6
■ FBY36L840-UNV	36000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18766 9
FBY LED High Bay (Continued)	L=47-7/8" (1216mm) × W=11-1/2" (292mm)		
■ FBY48L835-347	48000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY48L835-UNV	48000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY48L840-347	48000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY48L840-UNV	48000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18770 6
■ FBY60L840-347	60000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY60L840-UNV	60000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18774 4
Accessories			
● FBY-PENHGR	FBY Pendant hanger (adds 3" to height)		7 84197 66503 6
● FBY-WG	FBY Wire Guard (Order 2 for FBY36, FBY48, & FBY60)		7 84197 66557 9
● HCH5-VHOOK	FBY 5' Cables with V Hook		7 84197 65872 4
● HNH5-VHOOK	FBY 54" Chain with V Hook		7 84197 65876 2
FBZ LED High Bay			
■ FBZ24L840-UNV	FBZ LED High Bay, 24000lm, 4000K (CRI 80), UNV, 0-10V Dimming		7 84197 70797 2
■ FBZ24L840-347	FBZ LED High Bay, 24000lm, 4000K (CRI 80), 347V, 0-10V Dimming		
Accessories			
● FBZ-PENHGR	Pendant hanger kit (pendant supplied by others Accessory)		7 84197 70805 4
● FBZ-WG2	Wire guard for 8000lm to 30000lm Accessory		7 84197 70806 1
● FBZ-WG4	Wire guard for 36000lm to 60000lm Accessory		7 84197 70807 8
● FBZ-SLCA-2N	Clear acrylic snap lens kit for 8000lm to 30000lm Accessory		7 84197 70808 5
● FBZ-SLFA-2N	Frosted acrylic snap lens kit for 8000lm to 30000lm Accessory		7 84197 70809 2
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
FCY Value High Bay Selectable			
■ FCY15L8CST-347-DIM	15000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PLM405XT57ZE	1 90096 18068 4
● FCY15L8CST-UNV-DIM	15000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PLI6CXJN3X6C	1 90096 18065 3
■ FCY22L8CST-347-DIM	22000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PLGRWD3LZYD7	1 90096 18069 1
● FCY22L8CST-UNV-DIM	22000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PL450VSJUE9A	1 90096 18066 0
■ FCY29L8CST-347-DIM	29000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PL5YOSU340LN	1 90096 18070 7
● FCY29L8CST-UNV-DIM	29000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PLS2MUBV8CV	1 90096 18067 7
Accessories			
● FCY-WG	Wire guard for FCY15 and FCY22		1 90096 18072 1
● FCY-WG29	Wire guard for FCY29		1 90096 18074 5
HCY LED High Bay Ø 11-3/8"			
● HCY1421L8CST-UN3-DIM	14,000/21,000lm, 4000/5000K (CRI 80), 120-347V, 0-10V Dimming	PL010HSZT5F0	911401874482
● HCY2833L8CST-UN3-DIM	28,000/33,000lm, 4000/5000K (CRI 80), 120-347V, 0-10V Dimming	PLJXJYXIX60N	911401874582
Accessories			
● HCY2-PRISM	16" Clear polycarbonate reflector for HCY1421L		1 90096 13163 1
● HCY2-PRLG	16" Clear polycarbonate reflector for HCY2833L		1 90096 13162 4
● HCY-REMOTE	Remote hand-held programmer for HCY-SENSOR		1 90096 13114 3
● HCY-SENSOR	Field installed microwave sensor		1 90096 13166 2
● HCY-SURFACE BKT SM	Surface mount bracket for HCY15 and HCY21		1 90096 13117 4
● HCY-SURFACE BKT LG	Surface mount bracket for HCY28 and HCY33		1 90096 13118 1
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			

Versatile surface
mount illumination
for hallways, egress,
and task lighting
applications

Choose Day-Brite CFI by Signify for a complete selection
of professional office & industrial lighting products.
Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

Day-Brite CFI										
Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)										
Product Family										
	FluxStream LED Industrial (FSI)	FluxStream LED Strip EZ (FSSEZ)	FluxStream LED Strip (FSS)	FluxStream LED Wraparound (FSW)	NWL Wraparound Selectable	OWL LED Wraparound	SDS Strip Dual Select	Vaporlume V3W LED	Vaportite Dual Select	
Page Reference	pg. 20	pg. 20	pg. 21	pg. 21	pg. 22	pg. 22	pg. 22	pg. 23	pg. 23	
Quick Ship Service										
Budget / Grade	Budget / Good				Value / Better			Performance / Better		
Spec & Performance	Sizes	4' / 8'	4' / 8'	2' / 3'* 4' / 8'	2'* 4' / 8'	4'	4'	4' / 8'	2'* 4'	2' / 4' / 8'
	Lumens (Max)	4000-14000	4000 / 8000	4000-14000	3000 / 4000	4000	4000 / 5000	Selectable 4850 / 9800	3500-5100	Selectable 8000 / 13000
	Efficacy (lm/W)	up to 134	up to 133	up to 133	up to 122	122	up to 106	up to 139	up to 147	up to 139
	Dimming	0-10V Step* MarkX* DALI*	0-10V	0-10V Step* MarkX* DALI*	0-10V Step* MarkX* DALI*	0-10V	0-10V Step*	0-10V	0-10V Step*	0-10V
	CCT (K)	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	Selectable 3000K 3500K 4000K	4000K	Selectable 3500K 4000K 5000K	3000K* 3500K 4000K 5000K*	Selectable 3500K 4000K 5000K
	CRI	80	80	80	80	80	80	80	80	80
	Voltage (V)	120-277V 347V	120-277V	120-277V 347V	120-277V	120-277V	120-277V 347V	120-347V	120-277V 347V	120-347V
Controls & Options	Construction / Finish	White Metal Matte Black* Satin Aluminum*	White Metal	White Metal Matte Black* Satin Aluminum*	White Metal	White Polycarbonate	White Metal	White Metal	White Fiberglass	White Polycarbonate
	Lens	Frosted Acrylic	Frosted Acrylic	Frosted Acrylic	Frosted Acrylic	Frosted Polycarbonate	Frosted Acrylic	Frosted Polycarbonate	Clear Acrylic Frosted Acrylic* Prismatic*	Frosted Polycarbonate
	Interact Ready									
	Power over Ethernet (PoE)									
Ratings & Certification	Wall Mountable ADA Compliant									
	IP / Wet Location Rating								IP65 IP67*	IP66
	NSF Rating									
	cULus Listed									
	cETLus Listed									
	Other Ratings									NEMA 4X
	DLC	Standard	Standard	Standard	Standard / Premium	Standard	Standard	Standard	Premium	Standard
	Lifetime (L70)	up to 50,000 hours	up to 50,000 hours	up to 100,000 hours	up to 100,000 hours		up to 50,000 hours		up to 100,000 hours	up to 50,000 hours
Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.									

5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



FSI



FSSEZ

Product	Description / Features		UPC
FluxStream LED Industrial (FSI)			
■ FSI440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSI440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	
■ FSI440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	6 22252 78155 3
● FSI440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24554 2
■ FSI455L835-347-DIM	4', 5500lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	6 22252 82034 4
■ FSI455L835-UNV-DIM	4', 5500lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27059 9
■ FSI455L840-347-DIM	4', 5500lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 84197 21300 8
■ FSI455L840-UNV-DIM	4', 5500lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24556 6
■ FSI470L835-347-DIM	4', 7000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSI470L835-UNV-DIM	4', 7000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27073 5
■ FSI470L840-347-DIM	4', 7000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 84197 21301 5
■ FSI470L840-UNV-DIM	4', 7000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24557 3
8'			
■ FSI880L835-347-DIM	8', 8000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSI880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27109 1
■ FSI880L840-347-DIM	8', 8000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	6 22252 78153 9
■ FSI880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24558 0
■ FSI8110L835-347-DIM	8', 11000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSI8110L835-UNV-DIM	8', 11000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27099 5
■ FSI8110L840-347-DIM	8', 11000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	20
■ FSI8110L840-UNV-DIM	8', 11000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24559 7
■ FSI8140L835-347-DIM	8', 14000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSI8140L835-UNV-DIM	8', 14000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	
■ FSI8140L840-347-DIM	8', 14000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSI8140L840-UNV-DIM	8', 14000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24560 3
FluxStream LED Strip EZ (FSSEZ)			
● FSSEZ440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 70650 0
● FSSEZ440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 70017 1
8'			
● FSSEZ880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 70653 1
● FSSEZ880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 70018 8
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



FSS



FSW

Product	Description / Features		UPC
FluxStream LED Strip (FSS)			
■ FSS440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	6 22252 78145 4
● FSS440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27002 5
■ FSS440L835-UNV-DIM-SWZCS	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
● FSS440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 84197 26986 9
● FSS440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 24538 2
■ FSS440L840-UNV-DIM-SWZCS	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
■ FSS440L850-UNV-DIM-SWZCS	4', 4000lm, 5000K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
■ FSS455L835-347-DIM	4', 5500lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSS455L835-UNV-DIM	4', 5500lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27010 0
■ FSS455L840-347-DIM	4', 5500lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	
● FSS455L840-UNV-DIM	4', 5500lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24540 5
■ FSS470L835-347-DIM	4', 7000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSS470L835-UNV-DIM	4', 7000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27018 6
■ FSS470L840-347-DIM	4', 7000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSS470L840-UNV-DIM	4', 7000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24541 2
8'			
■ FSS880L835-347-DIM	8', 8000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	6 22252 78146 1
■ FSS880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27030 8
● FSS880L840-347-DIM	8', 8000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 84197 26990 6
● FSS880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 24542 9
■ FSS8110L835-347-DIM	8', 11000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSS8110L835-UNV-DIM	8', 11000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27025 4
■ FSS8110L840-347-DIM	8', 11000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	
● FSS8110L840-UNV-DIM	8', 11000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24543 6
■ FSS8140L835-347-DIM	8', 14000lm, 3500K (CRI 80), 347V, 0-10V Dimming		6 22252 82032 0
■ FSS8140L835-UNV-DIM	8', 14000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 27028 5
■ FSS8140L840-347-DIM	8', 14000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	
■ FSS8140L840-UNV-DIM	8', 14000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 84197 24544 3
FluxStream LED Wraparound (FSW)			
■ FSW430L835-UNV-DIM-SWZCS	4', 3000lm, 3500K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
■ FSW430L840-UNV-DIM-SWZCS	4', 3000lm, 4000K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
■ FSW440L835-UNV-DIM-SWZCS	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
■ FSW440L840-UNV-DIM-SWZCS	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming, <i>Interact Ready</i>	STANDARD	
FluxStream LED, Accessories			
● FSSWG4	FluxStream Strip, 4' Wire guard (order two for 8' models)		7 84197 29502 8
● FSTH	FluxStream, Sliding Hanger Bracket (Pair)		078197349707
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
NWL Wraparound Selectable			
NWL440L8CST-UNV-DIM-OCC	4' Selectable 3000K, 3500K, 4000K, 80CRI, UNV (120-277V), Occ Sensor	PLTCN60SD433	1 90096 13091 7
OWL LED Wraparound			
OWL440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming		7 81370 62743 0
OWL440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 81370 09721 9
OWL440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 81370 62752 2
OWL440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	STANDARD	7 81370 04900 3
OWL450L835-347-DIM	4', 5000lm, 3500K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 81370 62754 6
OWL450L835-UNV-DIM	4', 5000lm, 3500K (CRI 80), UNV,0-10V Dimming	STANDARD	7 81370 09741 7
OWL450L840-347-DIM	4', 5000lm, 4000K (CRI 80), 347V, 0-10V Dimming	STANDARD	7 81370 62759 1
OWL450L840-UNV-DIM	4', 5000lm, 4000K (CRI 80), UNV,0-10V Dimming	STANDARD	7 81370 04901 0
SDS Strip Dual Select			
SDS21224L8CST-UNV-DIM	2', 1200 / 1800 / 2400lm, 3500K / 4000K / 5000K (CRI 80), UNV 120-277V, Dimmable	PLV59H45ZE1C	1 90096 13156 3
SDS42448L8CST-UN3-DIM	4', 2430 / 3640 / 4850lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	PL330ZYV11GW	1 90096 13160 0
SDS84998L8CST-UN3-DIM	8', 4900 / 7350 / 9800lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	PLB9UEA7HLO5	1 90096 13161 7

Stock Ready (2-Day Quick Ship) Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
Vaporlume V3W LED			
V3W435L835-347-DIM	4', 3500lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
V3W435L835-UNV-DIM	4', 3500lm, 3500K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 62635 8
V3W435L840-347-DIM	4', 3500lm, 4000K (CRI 80), 347, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
V3W435L840-UNV-DIM	4', 3500lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42646 0
V3W443L835-347-DIM	4', 4300lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
V3W443L840-347-DIM	4', 4300lm, 4000K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42656 9
V3W443L840-UNV-DIM	4', 4300lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42655 2
V3W451L835-347-DIM	4', 5100lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
V3W451L840-347-DIM	4', 5100lm, 4000K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
V3W451L840-UNV-DIM	4', 5100lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42653 8
Accessories			
TBK	DWAE Stainless Steel Top Bracket Kit (pair of brackets plus hardware)		7 34340 37459 9
Vaportite Dual Select			
VTS225L840-UN3-DIM	2' 2500lm, 4000K, 120-347V	STANDARD	1 90096 19656 2
VTS22028L8CST-UN3-DIM	2' Dual Select 2000/2400/2800lm, 3500/4000/5000K, 120-347V	S-C761RN	1 90096 19651 7
VTS450L840-UN3-DIM	4' 5000lm, 4000K, 120-347V	STANDARD	1 90096 19652 4
VTS42856L8CST-UN3-DIM	4' Dual Select 2800/4200/5600lm, 3500/4000/5000K, 120-347V	S-XGL7UR	1 90096 19653 1
VTS8100L840-UN3-DIM	8' 1000lm, 4000K, 120-347V	STANDARD	1 90096 19654 8
VTS880130L8CST-UN3-DIM	8' Dual Select 8000/11000/13000lm, 3500/4000/5000K, 120-347V	S-EAOD4I	1 90096 19655 5
T Series T8 Strip			
T232-UNV-1/2-EB	4', 2 Lamp, T8 32W, Electronic Ballast, UNV		7 34340 60832 8
Accessories			
CG-4	T Strip 4' Wire Guard		7 82343 29605 9
FKR-126	Chain hanger set (pair)		7 82343 18410 3

Stock Ready (2-Day Quick Ship) Design Ready (10-Day Quick Ship)

Comfortable
illumination for highly
productive spaces

Choose Day-Brite CFI by Signify for a complete selection of professional office & industrial lighting products. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

Day-Brite CFI							
Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)							
		FluxPanel LED Gen. 2 (FPZ)			FluxGrid Gen2 Recessed LED (FGX)		
		pg. 26			pg. 31		
		● ■			● ■		
Product Family		Selectable Backlit Panel Dual Select (SBP)					
Page Reference		pg. 28			pg. 29		
Quick Ship Service		■			■		
Budget / Grade		Value / Good			Performance / Better		
Spec & Performance	Type	Panel	Recessed Troffer	Panel	Recessed Troffer	Recessed Troffer	Recessed Troffer
	Sizes	1×4', 2×2', 2×4'	1×4', 2×2', 2×4'	1×4', 2×2', 2×4'	1×4', 2×2', 2×4'	1×4', 2×2', 2×4'	1×4', 2×2', 2×4'
	Depth	3"	3-1/8"	1-1/2"	3-15/16"	3-15/16"	3-15/16"
	Lumens (lm)	3000-4800 5400*	9000	Selectable 3400-5800	3000-4800 5400-7400*	3800-4800 5400-7400*	3800-4800 5400-7400*
	Efficacy (lm/W)	up to 132	up to 146	up to 128	up to 130	up to 130	up to 130
	Dimming	0-10V Step* MarkX*	0-10V Step* MarkX phase dimming* Lutron LDE1 1%* DALI*	0-10V	0-10V Step* Lutron LDE5 5%* DALI*	0-10V Step* Lutron LDE5 5%* Lutron LDE1 1%* DALI*	0-10V Step* Lutron LDE5 5%* Lutron LDE1 1%* DALI*
	CCT (K)	3500K 4000K	3000K* 3500K 4000K 5000K*	Selectable 3500K 4000K 5000K	3000K* 3500K 4000K 5000K*	3000K*, 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*
	CRI	80	80 90	80	80 AccuRender 90*	80 AccuRender 90*	80
	Voltage (V)	120-277V 347V	120-277V 347V	120-277V 120-347V	120-277V 347V	120-277V 347V	120-277V 347V
Controls & Options	Lens	Flat opal	Diffuse flat (smooth) Diffuse round (smooth) Diffuse flat (ribbed) Diffuse round (ribbed)	Flat opal	Diffuse (smooth)	Diffuse (smooth) Diffuse perforated* Diffuse opaque* Diffuse linear prism*	Diffuse (smooth)* Diffuse (ribbed)
	Ceiling Types	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*
	Air Function	-	Air Return	-	Air Return Chicago Plenum*	Air Return Chicago Plenum*	Air Return Chicago Plenum*
	Interact Ready	◆	◆		◆	◆	◆
	Power over Ethernet (PoE)		◆		◆	◆	◆
Ratings & Certification	cULus Listed	✓		✓			
	cETLus Listed		✓		✓	✓	✓
	IC Rated	✓	✓		✓	✓	✓
	DLC	Standard / Premium	Standard / Premium	Standard	Standard / Premium	Standard / Premium	Standard / Premium
	Lifetime (L70)	up to 90,000 hours	up to 100,000 hours	up to 67,000 hours	up to 87,000 hours	up to 87,000 hours	up to 87,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.					

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature ◆ Spec Ready / Additional Options Available, see spec sheet for details



Product	Description / Features		UPC
FluxPanel LED Gen. 2 (FPZ)	1×4'		
■ 1FPZ30L835-4-DS-347-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ30L835-4-DS-UNV-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
■ 1FPZ30L840-4-DS-347-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ30L840-4-DS-UNV-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
■ 1FPZ38L835-4-DS-347-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ38L835-4-DS-UNV-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
● 1FPZ38B835-4-DS-UNV-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18001 1
■ 1FPZ38L840-4-DS-347-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ38L840-4-DS-UNV-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
● 1FPZ38B840-4-DS-UNV-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18002 8
■ 1FPZ45L835-4-DS-347-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ45L835-4-DS-UNV-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
■ 1FPZ45L840-4-DS-347-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 1FPZ45L840-4-DS-UNV-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
2×2'			
■ 2FPZ30L835-2-DS-347-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 2FPZ30L835-2-DS-UNV-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ30L840-2-DS-347-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ30L840-2-DS-UNV-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ38L835-2-DS-347-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 2FPZ38L835-2-DS-UNV-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	1 90096 19097 3
■ 2FPZ38L840-2-DS-347-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-2-DS-UNV-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	1 90096 19098 0
● 2FPZ38B835-2-DS-UNV-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18003 5
● 2FPZ38B840-2-DS-UNV-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18004 2
■ 2FPZ45L835-2-DS-347-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 2FPZ45L835-2-DS-UNV-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
■ 2FPZ45L840-2-DS-347-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ45L840-2-DS-UNV-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	1 90096 19100 0
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
FluxPanel LED Gen. 2 (Continued)	2×4'		
■ 2FPZ38L835-4-DS-347-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
■ 2FPZ38L835-4-DS-UNV-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-4-DS-347-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-4-DS-UNV-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
● 2FPZ42B835-4-DS-UNV-DIM	2×4', 4200lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18006 6
● 2FPZ42B840-4-DS-UNV-DIM	2×4', 4200lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	STANDARD	1 90096 18007 3
■ 2FPZ43L835-4-DS-347-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ43L835-4-DS-UNV-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ43L840-4-DS-347-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ43L840-4-DS-UNV-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ48L835-4-DS-347-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ48L835-4-DS-UNV-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	1 90096 19105 5
■ 2FPZ48L840-4-DS-347-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ48L840-4-DS-UNV-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
Selectable Backlit Panel Dual Select (SBP)			
● 1SBP3040L8CS-4-UNV-DIM	1×4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	PLQKCLTPT272	1 90096 13099 3
● 1SBP3040L8CS-4-UN3-DIM	1×4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	PLSPJ8WECQEX	1 90096 13102 0
● 2SBP3040L8CS-2-UNV-DIM	2×2', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	PLKH5HVC3HOT	1 90096 13100 6
● 2SBP3040L8CS-2-UN3-DIM	2×2', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	PLAAFAE505CJ	1 90096 13103 7
● 2SBP3550L8CS-4-UNV-DIM	2×4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	S-3HABOG	1 90096 13101 3
● 2SBP3550L8CS-4-UN3-DIM	2×4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	PLJUM2CXSYNX	1 90096 13104 4
Accessories			
● CFFSF14-PANEL	1×4' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00002 6
● CFFSF22-PANEL	2×2' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00001 9
● CFFSF24-PANEL	2×4' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00003 3
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



CAX

Product	Description / Features		UPC
ClearAppeal LED Gen. 2 (CAX)			
 1CAXG30L835-4-DS-347-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1CAXG30L835-4-DS-UNV-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66954 6
 1CAXG30L840-4-DS-347-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1CAXG30L840-4-DS-UNV-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66962 1
 1CAXG38L835-4-DS-347-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67025 2
 1CAXG38L835-4-DS-UNV-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66955 3
 1CAXG38L840-4-DS-347-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67030 6
 1CAXG38L840-4-DS-UNV-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66963 8
 1CAXG45L835-4-DS-347-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 66957 7
 1CAXG45L835-4-DS-UNV-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66956 0
 1CAXG45L840-4-DS-347-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67033 7
 1CAXG45L840-4-DS-UNV-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66964 5
2×2'			
 2CAXG30L835-2-DS-347-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2CAXG30L835-2-DS-UNV-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66968 3
 2CAXG30L840-2-DS-347-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2CAXG30L840-2-DS-UNV-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66973 7
 2CAXG38L835-2-DS-347-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67659 9
 2CAXG38L835-2-DS-UNV-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66970 6
 2CAXG38L840-2-DS-347-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67076 4
 2CAXG38L840-2-DS-UNV-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66974 4
 2CAXG45L835-2-DS-347-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 66972 0
 2CAXG45L835-2-DS-UNV-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66971 3
 2CAXG45L840-2-DS-347-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 66976 8
 2CAXG45L840-2-DS-UNV-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66975 1
2×4'			
 2CAXG38L835-4-DS-347-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2CAXG38L835-4-DS-UNV-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2CAXG38L840-4-DS-347-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2CAXG38L840-4-DS-UNV-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2CAXG43L835-4-DS-347-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67077 1
 2CAXG43L835-4-DS-UNV-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66981 2
 2CAXG43L840-4-DS-347-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 66986 7
 2CAXG43L840-4-DS-UNV-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 66985 0
 2CAXG48L835-4-DS-347-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67081 8
 2CAXG48L835-4-DS-UNV-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 67080 1
 2CAXG48L840-4-DS-347-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	7 84197 67095 5
 2CAXG48L840-4-DS-UNV-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	7 84197 67094 8

 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)



FFX

Product	Description / Features		UPC
FormFlex LED (FFX)			
 1FFXG30L835-4-DS-347-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG30L835-4-DS-UNV-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 1FFXG30L840-4-DS-347-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG30L840-4-DS-UNV-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 1FFXG38L835-4-DS-347-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG38L835-4-DS-UNV-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 1FFXG38L840-4-DS-347-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG38L840-4-DS-UNV-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 1FFXG45L835-4-DS-347-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG45L835-4-DS-UNV-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 1FFXG45L840-4-DS-347-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 1FFXG45L840-4-DS-UNV-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
2×2'			
 2FFXG30L835-2-DS-347-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG30L835-2-DS-UNV-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2FFXG30L840-2-DS-347-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG30L840-2-DS-UNV-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2FFXG38L835-2-DS-347-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG38L835-2-DS-UNV-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2FFXG38L840-2-DS-347-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG38L840-2-DS-UNV-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2FFXG45L835-2-DS-347-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG45L835-2-DS-UNV-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
 2FFXG45L840-2-DS-347-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	STANDARD	
 2FFXG45L840-2-DS-UNV-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	STANDARD	
2×4'			
 2FFXG38L835-4-DS-347-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG38L835-4-DS-UNV-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
 2FFXG38L840-4-DS-347-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG38L840-4-DS-UNV-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
 2FFXG43L835-4-DS-347-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG43L835-4-DS-UNV-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
 2FFXG43L840-4-DS-347-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG43L840-4-DS-UNV-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
 2FFXG48L835-4-DS-347-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG48L835-4-DS-UNV-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
 2FFXG48L840-4-DS-347-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
 2FFXG48L840-4-DS-UNV-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	

Recessed Luminaire Accessories


 FMA14	1×4' Drywall Flange Kit	7 34340 77548 8
 FMA22	2×2' Drywall Flange Kit	7 34340 77547 1
 FMA24	2×4' Drywall Flange Kit	7 34340 77546 4

 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
SofTrace LED (STX)			
■ 1STXG30L835-4-D-347-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming		
■ 1STXG30L835-4-D-UNV-DIM	1×4', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming		
■ 1STXG30L840-4-D-347-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 1STXG30L840-4-D-UNV-DIM	1×4', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 1STXG38L835-4-D-347-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 1STXG38L835-4-D-UNV-DIM	1×4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67128 0
■ 1STXG38L840-4-D-347-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 1STXG38L840-4-D-UNV-DIM	1×4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67134 1
■ 1STXG45L835-4-D-347-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 1STXG45L835-4-D-UNV-DIM	1×4', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67131 0
■ 1STXG45L840-4-D-347-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 1STXG45L840-4-D-UNV-DIM	1×4', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67137 2
2×2'			
■ 2STXG30L835-2-D-347-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG30L835-2-D-UNV-DIM	2×2', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 2STXG30L840-2-D-347-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG30L840-2-D-UNV-DIM	2×2', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 2STXG38L835-2-D-347-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG38L835-2-D-UNV-DIM	2×2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 2STXG38L840-2-D-347-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG38L840-2-D-UNV-DIM	2×2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67158 7
■ 2STXG45L835-2-D-347-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming		
■ 2STXG45L835-2-D-UNV-DIM	2×2', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming		7 84197 67154 9
■ 2STXG45L840-2-D-347-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG45L840-2-D-UNV-DIM	2×2', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67161 7
2×4'			
■ 2STXG38L835-4-D-347-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG38L835-4-D-UNV-DIM	2×4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 2STXG38L840-4-D-347-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG38L840-4-D-UNV-DIM	2×4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	
■ 2STXG43L835-4-D-347-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG43L835-4-D-UNV-DIM	2×4', 4300lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67176 1
■ 2STXG43L840-4-D-347-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG43L840-4-D-UNV-DIM	2×4', 4300lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67188 4
■ 2STXG48L835-4-D-347-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG48L835-4-D-UNV-DIM	2×4', 4800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	7 84197 67179 2
■ 2STXG48L840-4-D-347-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	STANDARD	
■ 2STXG48L840-4-D-UNV-DIM	2×4', 4800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	STANDARD	

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
FluxGrid Gen.2 Recessed LED (FGX)			
■ 1FGXG42B835-4-FS-UNV-DIM	1×4', 4200, 3500K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70833 7
■ 1FGXG42B835-4-RS-UNV-DIM	1×4', 4200, 3500K (CRI 80), Diffuse (round smooth), UNV, 0-10V Dimming		
■ 1FGXG42B840-4-FS-UNV-DIM	1×4', 4200, 4000K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		
■ 1FGXG42B840-4-RS-UNV-DIM	1×4', 4200, 4000K (CRI 80), Diffuse (round smooth), UNV, 0-10V Dimming		7 84197 70831 3
● 2FGXG38B835-2-FS-UNV-DIM	2×2', 3800, 3500K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70573 2
● 2FGXG38B835-2-RS-UNV-DIM	2×2', 3800, 3500K (CRI 80), Diffuse (round smooth), UNV, 0-10V Dimming		7 84197 70779 8
● 2FGXG38B840-2-FS-UNV-DIM	2×2', 3800, 4000K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70832 0
● 2FGXG38B840-2-RS-UNV-DIM	2×2', 3800, 4000K (CRI 80), Diffuse (round smooth), UNV, 0-10V Dimming		7 84197 70780 4
● 2FGXG42B835-4-FS-UNV-DIM	2×4', 4200, 3500K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70784 2
● 2FGXG42B835-4-RS-UNV-DIM	2×4', 4200, 3500K (CRI 80), Diffuse (round smooth), UNV, 0-10V Dimming		7 84197 70785 9
● 2FGXG42B840-4-FS-UNV-DIM	2×4', 4200, 4000K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70786 6
● 2FGXG42B840-4-RS-UNV-DIM	2×4', 4200, 4000K (CRI 80), Diffuse (flat smooth), UNV, 0-10V Dimming		7 84197 70776 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

Calculite LED 4" Round | Pg. 52

Indoor Track & Downlighting

Environmentally-friendly, efficient indoor track and downlighting solutions that perfectly blend aesthetic and performance. With Lightolier you can confidently find the lighting solution to best suit your application and budget.

Lightolier is a global market leader widely recognized for its innovative LED lighting solutions with an unmatched commitment to technology leadership, reliability, visual appeal and high performance. The Lightolier comprehensive product offering provides you with a quick and easy way to select both downlighting and track lighting solutions that complement every lighting application.

SlimSurface LED Round | Pg. 38

Conventional Track Heads | Pg. 69

Core Downlights 34

LED Quick Selection Guide 35

Flat Downlight Select LED	36	Retrofit Downlight LED	37
Downlight LED.	36	CorePro LED	37
Mini Downlight LED	36	Surface Mount Downlight LED.	38
Gimbal LED	36	SlimSurface LED Round	38
Commercial Retrofit Downlight DualSelect	37	SlimSurface LED Square	41

Downlight Kits 42

LED Quick Selection Guide 43

UniFrame	45	Calculite LED 4" Round.	52
Accessories.	45	Calculite LED 6" Round.	54
EasyLyte LED 4" Round.	46	Calculite LED 6" Square	56
EasyLyte LED 6" Round.	47	Calculite LED 7" Round	56
LyteProfile LED 3" Round	48	LyteCaster LED, 3" Accent	58
LyteProfile LED 3" Square	48	LyteCaster LED 4"	59
LyteProfile LED 4" Round	49	LyteCaster LED 5"	59
LyteProfile LED 6" Round	50	LyteCaster LED 6"	59
LyteProfile LED 6" Square	50	LyteCaster Conventional	60
Calculite LED 3" Round.	51	LytePoints Conventional	61
Calculite LED 3" Square	51		

Track Lighting 62

LED Quick Selection Guide 63

Basic Track	64	LightFlood LED	67
Track Accessories	65	OmniSpot LED Track Heads (06/10)	67
Alcyon LED Vertical Medium Cylinder	66	OmniSpot LED Track Heads (20).	68
Alcyon LED Vertical Large Cylinder	66	OmniSpot LED Recessed Multiple	68
Alcyon LED Recessed Multiples	66	Conventional Track Heads	69
BoldFlood LED	67	LyteSpan Track Head Accessories	69

Downlights that are
easy to install from
below the ceiling

Choose Lightolier by Signify for a complete selection
of professional track and downlighting solutions.
Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

LIGHTOLIER

Click images to
view eCatalogue
(Detailed brochures,
bulletins, spec
sheets, IES files, etc.)

Product Family	Flat Downlight Dual Select LED	Gimbal & Downlight Dual Select LED	Commercial Retrofit Downlight Dual Select	Retrofit Downlight Select LED	CorePro LED	Surface Mount Dual Select LED	SlimSurface LED Round	SlimSurface LED Square
Page Reference	pg. 36	pg. 36	pg. 37	pg. 37	pg. 37	pg. 38	pg. 38	pg. 41
Quick Ship Service	● ■	● ■	●	●	● ■	● ■	● ■	■
Budget / Grade	Budget / Good		Value / Better			Budget / Good	Value / Better	
Applicability	Retail	1 2	3	2	3	1	3	3
	Hospitality	1	2	3	2	2	1	3
	Office	1	1	3	2	2	1	3
	Education	1	1	3	2	3	1	3
	Residential	3	3	2	3	3	3	3

Applicability Scale: 3 High / 2 Medium / 1 Low / - N/A


Trim & Finish	Types	Downlight	Downlight / Gimbal	Downlight	Downlight	Downlight	Downlight	Downlight	Downlight
	Aperture	○ □ 3", 4", 5", 6", 8"	○ 3", 4", 6"	○ 4", 6", 8", 10"	○ 4", 6"	○ 4", 5", 6"	○ □ 5", 7", 9", 11", 14"	○ 5", 7", 10"	□ 4", 6"
	Finish	White Black Trim Fascia*	White Black (Gimbal Only)	White	White	White	White	Aluminum White Black Metal (10" only)*	Aluminum White Black
Spec & Performance	Lumens (lm)	Field Selectable 3": 370/500 4": 540/700 5": 900/1100 6": 900/1100 8": 1100/1300	Field Selectable 3": 370/500 4": 540/700 6": 900/1100	Field Selectable 4": 500-1000 6": 700-1500 8": 1000-2000 10": 2000-3000	4": 700 6": 900	4": 800 5": 950 6": 800 / 1200	5": 540/700 7": 800/1000 9": 900/1200 11": 1200/1500 14": 1600/2000	5": 650 7": 1000 10": 2200	4": 650 6": 1000
	Wattage (W)	8-17	6-15	11-16	9-10	11-16	9-25	9-28	9-28
	Efficacy (lm/W)	up to 82	up to 74	up to 93	up to 96	up to 89	up to 84	up to 94	up to 94
	CCT (K)	Selectable 2700K 3000K 3500K 4000K 5000K	Selectable 2700K 3000K 3500K 4000K 5000K	Selectable 3000K 3500K 4000K	Selectable 2700K 3000K 3500K 4000K 5000K	3000K 4000K	Selectable 2700K 3000K 3500K 4000K 5000K	2700K 3000K 3500K 4000K	2700K 3000K 3500K 4000K
	CRI	90	90	90	90	80 / 90	90	80 / 90	80 / 90
	Dimming	TRIAC, 0-10V	TRIAC, 0-10V	0-10V		TRIAC	TRIAC	0-10V ELV / TRIAC	0-10V ELV / TRIAC
Ratings & Certification	Installations	New Construction Remodeler Wet locations	New Construction Remodeler Wet locations	Wet locations	Wet locations	Wet locations	New Construction Remodeler Wet locations	Wet locations Damp locations (10")	Wet locations Damp locations (10")
	Certification	cULus Listed	cETLus Listed	cULus Listed	cULus Listed	cULus Listed	cETLus Listed	cULus Listed	cULus Listed
	IC Rated	✓	✓	✓	✓	✓	✓		
	Title 24 Rated	✓	✓	✓	✓	✓	✓	✓	✓
	AirSeal IC rated	✓	✓	✓		✓			
	Energy Star	✓	✓	✓	✓	✓	✓	✓	✓
Warranty	Lifetime (L70)	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 42,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.							

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ♦ Spec Ready / Additional Options Available, see spec sheet for details



Product	Description / Features		UPC
Flat Downlight Dual Select LED			
 FD3R4ESCT1W	3" Round 400lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 19616 6
 FD3RSLMZ10SCTUW	3" Round Dual Select 370/500lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 0-10V		1 90096 13167 9
 FD4R7ESCT1W	4" Round 700lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13168 6
 FD4RSLMZ10SCTUW	4" Round Dual Select 540/700lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 0-10V		1 90096 13169 3
 FD5R9ESCT1W	5" Round 900lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 19617 3
 FD5RSLMZ10SCTUW	5" Round Dual Select 900/1100lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 0-10V		1 90096 13170 9
 FD6R11ESCT1W	6" Round 1100lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13171 6
 FD6RSLMZ10SCTUW	6" Round Dual Select 900/1100lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 0-10V		1 90096 13172 3
 FD8R13ESCT1W	8" Round 1300lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 19618 0
 FD8RSLMZ10SCTUW	8" Round Dual Select 1100/1300lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 0-10V		1 90096 13173 0
Accessories			
 FD4NCP	4" New Construction Plate		1 90096 13119 8
 FD6NCP	6" New Construction Plate		1 90096 13120 4
Downlight Dual Select LED			
 DL3R4ESCT1W	Downlight 3" 400lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 19623 4
 DL3RSLMZ10SCTUW	Downlight 3" Dual Select 370/500lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13185 3
 DL4R7EST1W	Downlight 4" 700lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13186 0
 DL4RSLMZ10SCTUW	Downlight 4" Dual Select 540/700lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13187 7
 DL6R11ESCT1W	Downlight 6" 1100lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13188 4
 DL6RSLMZ10SCTUW	Downlight 6" Dual Select 900/1100lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13189 1
Mini Downlight LED			
 MD3R069301FW	3", 550lm, 3000K 90 CRI, 120V, Flood, White		1 90096 01740 9
 MD3R069401FW	3", 550lm, 4000K 90 CRI, 120V, Flood, White		1 90096 01741 6
Gimbal Dual Select LED			
 GB3R4ESCT1W	Gimbal 3" 400lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 19622 7
 GB3RSLMZ10SCTUW	Gimbal 3" Dual Select 370/500lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13190 7
 GB4R7ESCT1W	Gimbal 4" 700lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13191 4
 GB4RSLMZ10SCTUW	Gimbal 4" Dual Select 540/700lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13192 1
 GB6R11ESCT1W	Gimbal 6" 1100lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, TRIAC 5%, 120V		1 90096 13193 8
 GB6RSLMZ10SCTUW	Gimbal 6" Dual Select 900/1100lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13194 5
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
Commercial Retrofit Downlight DualSelect			
 CR4RLMCCT	4" Round Dual Select 500-1000lm, 3000K, 3500K, 4000K, 90CRI, 0-10V		1 90096 13126 6
 CR6RLMCCT	6" Round Dual Select 700-1500lm, 3000K, 3500K, 4000K, 90CRI, 0-10V		1 90096 13127 3
 CR8RLMCCT	8" Round Dual Select 1000-2000lm, 3000K, 3500K, 4000K, 90CRI, 0-10V		1 90096 13128 0
 CR10RLMCCT	10" Round Dual Select 2000-3000lm, 3000K, 3500K, 4000K, 90CRI, 0-10V		1 90096 13129 7
Retrofit Downlight Select LED			
 RD4R79301W	4", Round, 700lm,3000K (CRI 90), 120V		1 90096 13197 6
 RD4R793SCT1W	4" Round, 700lm, Field Selectable (2700K, 3000K, 3500K, 4000K, 5000K), 90CRI, 120V		1 90096 13195 2
 RD5R129301W	5/6" Round, 1200lm, 3000K (CRI 90), 120V		1 90096 01639 6
 RD6R99301W	6", Round, 900lm, 3000K (CRI 90), 120V		1 90096 13198 3
 RD6R99SCT1W	6" Round, 900lm, Field Selectable (2700K, 3000K, 3500K, 4000K, 5000K), 90CRI, 120V		1 90096 13196 9
CorePro LED 4"			
 CP4RR	4" Remodeler Housing, IC c/w LED, Connector		6 62057 93910 0
 CP4RN	4" New Construction Housing, IC c/w LED Connector		6 62057 93909 4
 CP4RB07830W	4", 800lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming		6 62057 93901 8
5"			
 CP5RN	5" New Construction Housing, IC c/w LED, Connector		6 62057 93911 7
 CP5RR	5" Remodeler Housing, IC c/w LED, Connector		6 62057 93912 4
 CP5RB08830W	5", 1000lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming		6 62057 93904 9
 CP5RB08840W	5", 1000lm, 4000K (CRI 80), 120V, White, 10% TRIAC Dimming		6 62057 93905 6
6"			
 CP6RR	6" Remodeler Housing, IC c/w LED, Connector		6 62057 93914 8
 CP6RN	6" New Construction Housing, IC c/w LED Connector		6 62057 93913 1
 CP6RB10830W	6", 1200lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming		6 62057 93907 0
 CP6RB10840W	6", 1250lm, 4000K (CRI 80), 120V, White, 10% TRIAC Dimming		6 62057 93908 7
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
Surface Mount Dual Select LED			
 SD5R7ESCT1W	5" Round 700lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 120V		1 90096 13178 5
 SD5RSLMZ10SCTUW	5" Round Dual Select 540/700lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13179 2
 SD7ROESCT1W	7" Round 1000lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 120V		1 90096 13180 8
 SD7RSLMZ10SCTUW	7" Round Dual Select 800/1000lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13181 5
 SD9R12ESCT1W	9" Round 1200lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 120V		1 90096 19619 7
 SD9RSLMZ10SCTUW	9" Round Dual Select 900/1200lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13182 2
 SD11R15ESCT1W	11" Round 1500lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 120V		1 90096 19620 3
 SD11RSLMZ10SCTUW	11" Round Dual Select 1200/1500lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV)		1 90096 13183 9
 SD14R16ESCT1W	14" Round 1600lm Selectable 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, 120V		1 90096 19621 0
 SD14RSLMZ10SCTUW	14" Round Dual Select 1600/2000lm, 2700K, 3000K, 3500K, 4000K, 5000K, 90CRI, UNV		1 90096 13184 6
SlimSurface LED Round			
5" Round, 650lm, 2700K (CRI 80)			
 S5R827K7AL	5" Round, 650lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98868 9
 S5R827K7ALZ10U	5" Round, 650lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95255 0
 S5R827K7BK	5" Round, 650lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94339 8
 S5R827K7BKZ10U	5" Round, 650lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95256 7
 S5R827K7WZ10U	5" Round, 650lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95254 3
5" Round, 650lm, 2700K (CRI 90)			
 S5R927K7AL	5" Round, 650lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming		6 62057 98871 9
 S5R927K7ALZ10U	5" Round, 650lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming		6 62057 95267 3
 S5R927K7BK	5" Round, 650lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming		6 62057 94353 4
 S5R927K7BKZ10U	5" Round, 650lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming		6 62057 95268 0
 S5R927K7	5" Round, 650lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming		6 62057 98870 2
 S5R927K7WZ10U	5" Round, 650lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming		6 62057 95266 6
5" Round, 650lm, 3000K (CRI 80)			
 S5R830K7AL	5" Round, 650lm, 3000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98869 6
 S5R830K7ALZ10U	5" Round, 650lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95258 1
 S5R830K7BK	5" Round, 650lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94340 4
 S5R830K7BKZ10U	5" Round, 650lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95259 8
 S5R830K7WZ10U	5" Round, 650lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95257 4
 S5R830K7	5" Round, 600lm, 3000K (CRI 80), 120V, White, ELV / Triac (120V) Dimming		6 62057 93605 5
5" Round, 650lm, 3500K (CRI 80)			
 S5R835K7ALZ10U	5" Round, 650lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95261 1
 S5R835K7AL	5" Round, 650lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98549 7
 S5R835K7BKZ10U	5" Round, 650lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95262 8
 S5R835K7BK	5" Round, 650lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94341 1
 S5R835K7WZ10U	5" Round, 650lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95260 4
 S5R835K7	5" Round, 650lm, 3500K (CRI 80), White, ELV / Triac (120V) Dimming		6 62057 98548 0
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
5" Round, 650lm, 4000K (CRI 80)			
 S5R840K7AL	5" Round, 650lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98552 7
 S5R840K7ALZ10U	5" Round, 650lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95264 2
 S5R840K7BK	5" Round, 650lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94342 8
 S5R840K7BKZ10U	5" Round, 650lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95265 9
 S5R840K7	5" Round, 650lm, 4000K (CRI 80), White, ELV / Triac (120V) Dimming		6 62057 98551 0
 S5R840K7WZ10U	5" Round, 650lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95263 5
SlimSurface LED Round			
7" Round, 1000lm, 2700K (CRI 80)			
 S7R827K10ALZ10U	7" Round, 1000lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95285 7
 S7R827K10AL	7" Round, 1000lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98873 3
 S7R827K10BKZ10U	7" Round, 1000lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95286 4
 S7R827K10BK	7" Round, 1000lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94347 3
 S7R827K10WZ10U	7" Round, 1000lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95284 0
 S7R827K10	7" Round, 1000lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming		6 62057 98872 6
7" Round, 1000lm, 2700K (CRI 90)			
 S7R927K10ALZ10U	7" Round, 1000lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming		6 62057 95297 0
 S7R927K10AL	7" Round, 1000lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming		6 62057 98877 1
 S7R927K10BKZ10U	7" Round, 1000lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming		6 62057 95298 7
 S7R927K10BK	7" Round, 1000lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming		6 62057 94355 8
 S7R927K10WZ10U	7" Round, 1000lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming		6 62057 95296 3
 S7R927K10	7" Round, 1000lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming		6 62057 98876 4
7" Round, 1000lm, 3000K (CRI 80)			
 S7R830K10ALZ10U	7" Round, 1000lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95288 8
 S7R830K10BKZ10U	7" Round, 1000lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95289 5
 S7R830K10BK	7" Round, 1000lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 98002 7
 S7R830K10WZ10U	7" Round, 1000lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95287 1
 S7R830K10	7" Round, 1000lm, 3000K (CRI 80), White, ELV / Triac (120V) Dimming		6 62057 98874 0
 S7R930K10	7" Round, 1000lm, 3000K (CRI 90), White, ELV / Triac (120V) Dimming		1 90096 03717 9
7" Round, 1000lm, 3500K (CRI 80)			
 S7R835K10ALZ10U	7" Round, 1000lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming		6 62057 95291 8
 S7R835K10AL	7" Round, 1000lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming		6 62057 98558 9
 S7R835K10BKZ10U	7" Round, 1000lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming		6 62057 95292 5
 S7R835K10BK	7" Round, 1000lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming		6 62057 94348 0
 S7R835K10WZ10U	7" Round, 1000lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming		6 62057 95290 1
 S7R835K10	7" Round, 1000lm, 3500K (CRI 80), White, ELV / Triac (120V) Dimming		6 62057 98557 2

 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
7" Round, 1000lm, 4000K (CRI 80)			
■ S7R840K10ALZ10U	7" Round, 1000lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95294 9
■ S7R840K10AL	7" Round, 1000lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98560 2
■ S7R840K10BKZ10U	7" Round, 1000lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95295 6
■ S7R840K10BK	7" Round, 1000lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94349 7
■ S7R840K10WZ10U	7" Round, 1000lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95293 2
SlimSurface LED Round			
10" Round, 2200lm, 2700K (CRI 80)			
■ S10R827K22WZ10U	10" Round, 2200lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06395 6
■ S10R827K22W	10" Round, 2200lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	1 90096 08736 5
10" Round, 2200lm, 2700K (CRI 90)			
■ S10R927K22WZ10U	10" Round, 2200lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	1 90096 06393 2
■ S10R927K22W	10" Round, 2200lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	1 90096 08740 2
10" Round, 2200lm, 3000K (CRI 80)			
■ S10R830K22WZ10U	10" Round, 2200lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06396 3
10" Round, 2200lm, 3000K (CRI 90)			
■ S10R930K22WZ10U	10" Round, 2200lm, 3000K (CRI 90), White, 0-10V (120-277V) Dimming	★	1 90096 06394 9
■ S10R930K22W	10" Round, 2200lm, 3000K (CRI 90), White, ELV / Triac (120V) Dimming	★	1 90096 08741 9
10" Round, 2200lm, 3500K (CRI 80)			
■ S10R835K22WZ10U	10" Round, 2200lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06397 0

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
SlimSurface LED Square			
4" Square, 650lm, 2700K (CRI 80)			
■ S4S827K7ALZ10U	4" Square, 650lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95240 6
■ S4S827K7AL	4" Square, 650lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98879 5
■ S4S827K7BKZ10U	4" Square, 650lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95241 3
■ S4S827K7BK	4" Square, 650lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94332 9
■ S4S827K7WZ10U	4" Square, 650lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95239 0
■ S4S827K7	4" Square, 650lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98878 8
4" Square, 650lm, 2700K (CRI 90)			
■ S4S927K7ALZ10U	4" Square, 650lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95252 9
■ S4S927K7AL	4" Square, 650lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98883 2
■ S4S927K7BKZ10U	4" Square, 650lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming	★	6 62057 95253 6
■ S4S927K7BK	4" Square, 650lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming	★	6 62057 94352 7
■ S4S927K7WZ10U	4" Square, 650lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	6 62057 95251 2
■ S4S927K7	4" Square, 650lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	6 62057 98882 5
4" Square, 650lm, 3000K (CRI 80)			
■ S4S830K7ALZ10U	4" Square, 650lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95243 7
■ S4S830K7AL	4" Square, 650lm, 3000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98881 8
■ S4S830K7BKZ10U	4" Square, 650lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95244 4
■ S4S830K7BK	4" Square, 650lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94335 0
■ S4S830K7WZ10U	4" Square, 650lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95242 0
■ S4S830K7	4" Square, 650lm, 3000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98880 1
4" Square, 650lm, 3500K (CRI 80)			
■ S4S835K7ALZ10U	4" Square, 650lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95246 8
■ S4S835K7AL	4" Square, 650lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98545 9
■ S4S835K7BKZ10U	4" Square, 650lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95247 5
■ S4S835K7BK	4" Square, 650lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94336 7
■ S4S835K7WZ10U	4" Square, 650lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95245 1
4" Square, 650lm, 4000K (CRI 80)			
■ S4S840K7ALZ10U	4" Square, 650lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95249 9
■ S4S840K7AL	4" Square, 650lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98547 3
■ S4S840K7BKZ10U	4" Square, 650lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95250 5
■ S4S840K7BK	4" Square, 650lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94338 1
■ S4S840K7WZ10U	4" Square, 650lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95248 2

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

Shape lighting
to suit a space

Choose Lightolier by Signify for a complete selection of professional track and downlighting solutions. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

LIGHTOLIER

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)

Product Family		EasyLyte LED	LyteProfile LED Accent	LyteProfile LED	Calculite LED Accent	Calculite LED	LyteCaster LED Accent	LyteCaster LED
Page Reference		pg. 46	pg. 48	pg. 48	pg. 51	pg. 51	pg. 58	pg. 59
Quick Ship Service		■	● ■	● ■	● ■	■	■	■
Budget / Grade		Value / Better					Budget / Good	
Trim & Finish	Aperture	○ 4", 6"	○ □ 3"	○ □ 4", 6"	○ □ 3"	○ □ 4", 6", 7"	○ □ 3"	○ □ 4", 5", 6"
	Reflector Finish	Clear Diffuse Black* White Dark Bronze*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White* Champagne Bronze* Aluminum Diffuse*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White* Champagne Bronze*	Chrome Diffuse White White Baffle Aluminum (Shower Trim Only)	Clear Diffuse White
	Cutoff / Accent Adjustment	70° Direct	Downlight / Wall Wash 60° Direct Adj. Accent 40° Tilt	Downlight / Wall Wash 60° Direct	50° Direct	50° Direct 45° Reflected 45° Tilt	Accent 60° Direct 60° Reflected Adj. Accent 35° Tilt	Downlight 30° Adjustment
Spec & Performance	Lumens (lm)	500-3500	500-1500	500-3500	500-1000	500-6000	800	650-2000
	Efficacy (lm/W)	up to 100	up to 74	up to 100	up to 87	up to 115		up to 90
	Dimming	0-10V 1% ELV Lutron LDE1*	0-10V 1% ELV Lutron PEQ0*	0-10V 1% Lutron LDE1*	0-10V 1% ELV Lutron PEQ0*	0-10V 1% ELV* DALI 0.1%* Lutron LDE1* DMX*	0-10V ELV / TRIAC	0-10V ELV / TRIAC
	CCT (K)	2700K* 3000K 3500K 4000K	2700K* 3000K 3500K 4000K*	2700K* 3000K 3500K 4000K 5000K* Dim to Warm*	2700K* 3000K 3500K 4000K* Dim to Warm	2700K* 3000K 3500K 4000K	2700K 3000K 3500K	2700K 3000K 3500K 4000K
	CRI (SDCM)	80 (3)	90 (3)	80 (3)	90 (2)	90 (2)	80-90 (3)	80-90 (3)
Options	Dim to Warm		◆		■ ◆	◆		
	Interact Ready	◆	◆	◆	◆	◆		◆
	IntelliHue					◆		
Ratings & Certification	POE	◆		◆	◆	◆		
	Frame / Installation (NC - New Construction)	NC (UniFrame) NC AirSeal (IC)* Remodeler*	NC (UniFrame) NC AirSeal (IC)* Remodeler*	NC (UniFrame) NC AirSeal (IC)* Remodeler*	NC (UniFrame) NC (Non-IC) NC (IC)	NC (UniFrame) NC AirSeal (IC)*	NC (non-IC)* NC AirSeal (IC)*	NC AirSeal (IC) Remodeler AirSeal (IC)*
	Ratings	cULus / IC Rated	cULus / IC / Title 24 Rated	cULus / IC Rated	cULus Listed	cULus Listed	cULus Listed	cULus Listed
	Energy Star	✓	✓	✓		✓	✓	✓
	Lifetime	up to 60,000 hours (L70)	up to 60,000 hours (L70)	up to 60,000 hours (L80)	up to 57,000 hours (L70)	up to 60,000 hours (L80)		up to 50,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.						


● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details

One frame for maximum flexibility

The **Lightolier** single frame solution architecture, is adaptable and designed around ever-changing project needs. Three unique downlight families all use this same frame. Your choices and flexibility are now endless.

- **Modular plug-and-play** receptacle enables quick and easy tool-free installation
- **Configurable solutions** mean installation can start sooner and be completed in stages
- **Future-proof** modular design allows easy upgrades without ceiling disturbance
- Unexpected design changes have **minimal schedule impact and waste**

Option available for **Interact Pro wireless control**. For more information visit www.interact-lighting.com/pro



Watch Video

EasyLyte

Light Commercial 2-part system (pg. 46-47)

LyteProfile

Commercial 2-part system (pg. 48-50)

Calculite

Specification 3-part system (pg. 51-56)

Reflector



CL Specular clear

Most specular and therefore most efficient finish, delivers maximum photometric performance but can produce a mirror image effect of the interior space.



CC Comfort clear

Semi-specular finish that softens the light at the source of the reflector and creates a subtle, even luminance from the reflector cone.



CD Comfort clear diffuse

Slightly diffuse clear finish, which eliminates iridescence and reduces the mirror image effect inherent with specular finishes.



CZ Champagne bronze

Semi-specular finish that softens the light at the source of the reflector while providing a warmer reflector appearance (light output is slightly warmer).



WH White (matte)

Brightest aperture when illuminated and provides the smoothest transition to most ceilings when off (white is only available with a white flange).



BK Black (matte)

Specular finish that provides the lowest aperture brightness possible and significantly reduces source identification in a ceiling.

Flange



- White (matte)

Provides the smoothest transition to ceilings when off.



P Polished (matches aperture)

Produces a continuous look throughout the reflector (aperture matching).



F Flangeless (flush-mount)

Creates a flush, virtually seamless transition from aperture to ceiling.

Note: Not all finishes are available for all trims (refer to specification sheet for availability). When handling reflectors, use clean white or plastic film gloves to avoid fingerprints. Specular surfaces can be cleaned by the following methods: Wipe off with soft clean, dry lint-free cloth; or wipe off with a soft cloth dampened in mild detergent solution, rinse, then wipe dry with lint-free cloth or paper towel; or wipe off with clean cloth dampened with a solution of wetting agent and water (such as 2 oz. per gallon "Pluronic L62-LF" by Wynandotte Products or liquid such as Glass Wax) then wipe dry with a lint-free cloth or paper towel. Avoid gritty cleaning agents.

Product	Description / Features		UPC
UniFrame	3"		
■ 3RA	3" Round, AirSeal IC, UNV	★	7 84197 66617 0
■ 3RN	3" Round, New Construction (Non-IC), UNV	★	7 84197 66612 5
■ 3SA	3" Square, AirSeal IC (1000lm max), Standard, UNV	★	7 84197 68678 9
■ 3SAS	3" Square, AirSeal IC (1000lm max), Shallow, UNV	★	7 84197 68679 6
■ 3SN	3" Square, New Construction (Non-IC), UNV	★	7 84197 66618 7
■ 3SNIP	3" Square, New Construction (Non-IC), UNV, Interact Ready	★	7 84197 66619 4
4"			
■ 4RA	4" Round, AirSeal IC, UNV	★	7 84197 24057 8
● 4RN	4" Round, New Construction (Non-IC), UNV	★	7 84197 64192 4
■ 4RN3	4" Round, New Construction (Non-IC), 347V	★	7 84197 21139 4
■ 4RNEM	4" Round, New Construction (Non-IC), Emergency	★	7 84197 64193 1
■ 4RNIP	4" Round, New Construction (Non-IC), UNV, Interact Ready	★	1 90096 01751 5
■ 4RR	4" Round, Remodeler (Non-IC), UNV	★	7 84197 21145 5
■ 4RR3	4" Round, Remodeler (Non-IC), 347V	★	7 84197 21146 2
■ 4SA	4" Square, AirSeal IC, UNV	★	7 84197 24059 2
● 4SN	4" Square, New Construction (Non-IC), UNV	★	7 84197 64195 5
■ 4SN3	4" Square, New Construction (Non-IC), 347V	★	7 84197 21148 6
■ 4SNEM	4" Square, New Construction (Non-IC), Emergency	★	7 84197 64196 2
■ 4SR	4" Square, Remodeler (Non-IC), UNV	★	7 84197 21151 6
■ 4SR3	4" Square, Remodeler (Non-IC), 347V	★	
6"			
■ 6RA	6" Round, AirSeal IC, UNV	★	7 84197 24060 8
● 6RN	6" Round, New Construction (Non-IC), UNV	★	7 84197 64197 9
■ 6RNIP	6" Round, New Construction (Non-IC), UNV, Interact Ready	★	1 90096 01755 3
■ 6RR3	6" Round, Remodeler (Non-IC), 347V	★	7 84197 21164 6
■ 6RN3	6" Round, New Construction (Non-IC), 347V	★	7 84197 21154 7
■ 6RNEM	6" Round, New Construction (Non-IC), Emergency	★	7 84197 64198 6
■ 6RR	6" Round, Remodeler (Non-IC), UNV	★	7 84197 21163 9
■ 6SA	6" Square, AirSeal IC, UNV	★	7 84197 24061 5
● 6SN	6" Square, New Construction (Non-IC), UNV	★	7 84197 64200 6
■ 6SN3	6" Square, New Construction (Non-IC), 347V	★	7 84197 21166 0
■ 6SNEM	6" Square, New Construction (Non-IC), Emergency	★	7 84197 64201 3
■ 6SR	6" Square, Remodeler (Non-IC), UNV	★	
■ 6SR3	6" Square, Remodeler (Non-IC), 347V	★	7 84197 21170 7
7"			
■ 7RN	7" Round, New Construction (Non-IC), UNV	★	7 84197 70574 9
■ 7RN3	7" Round, New Construction (Non-IC), 347V	★	7 84197 70575 6
■ 7RNLC	7" Round, New Construction (Non-IC), Chicago Plenum	★	7 84197 70576 3
■ C7RNEM	7" Round, New Construction (Non-IC), Emergency	★	7 84197 21173 8
Accessories			
● 1950	Mounting Bars 18" Set of (2) (Order in Multiples of 12)		7 84197 14500 2
● 1951	Mounting Bars 27" Set of (2) (Order in Multiples of 12)		7 84197 14503 3
● 1956	Set of 4 Mounting Bar Clips		7 84197 14513 2
■ 7994	Set of 2 Telescoping Mounting Bars-Calculite		7 84197 28904 1
■ CLAEM1520	Calculite LED Field-Wire EM-Pack 1500/2000 Lumen		6 62057 50303 5
● VBE300	Vapor Barrier for 9" IC Box		7 84197 34371 2

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Z4RDL (OCD)



Z4RDL (OWH)



Z4RDL (SWH)

Product	Description / Features		UPC
EasyLyte LED 4" Round	Frames		
See all Lightolier UniFrame options compatible with EasyLyte LED on pg. 45			
1000lm			
■ Z4RDL10835WOCZ10U	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10307 2
■ Z4RDL10835WOCDE1	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10658 5
■ Z4RDL10835WOWHZ10U	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10657 8
■ Z4RDL10840WOCZ10U	4" Round, 1000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10663 9
■ Z4RDL10840WOCDE1	4" Round, 1000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10662 2
1500lm			
■ Z4RDL15830WOCZ10U	4" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10323 2
■ Z4RDL15830WOCDE1	4" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10667 7
■ Z4RDL15835WOCZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10309 6
■ Z4RDL15835WOCDE1	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10308 9
■ Z4RDL15835WOWHZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10669 1
■ Z4RDL15835WOWHE1	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, ELV Dimming, 120V	★	1 90096 10668 4
■ Z4RDL15835WSWHZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10343 0
■ Z4RDL15840WOCZ10U	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10310 2
■ Z4RDL15840WOCDE1	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10675 2
■ Z4RDL15840WOWHZ10U	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10674 5
2000lm			
■ Z4RDL20830WOCZ10U	4" Round, 2000lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10680 6
■ Z4RDL20835WOCDE1	4" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10682 0
■ Z4RDL20835WOWHZ10U	4" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10681 3
■ Z4RDL20840WOCZ10U	4" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10687 5
■ Z4RDL20840WOCDE1	4" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10686 8
2500lm			
■ Z4RDL25835WOCZ10U	4" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10690 5
■ Z4RDL25840WOCZ10U	4" Round, 2500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10692 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Z6RDL (OCD)



Z6RDL (OWH)



Z4RDL (SWH)

Product	Description / Features		UPC
EasyLyte LED 6" Round	Frames		
See all Lightolier UniFrame options compatible with EasyLyte LED on pg. 45			
1000lm			
■ Z6RDL10840WOCZ10U	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10697 4
■ Z6RDL10835WOCDE1	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10695 0
■ Z6RDL10835WOWHZ10U	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10694 3
1500lm			
■ Z6RDL15830WOCZ10U	6" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10700 1
■ Z6RDL15835WOCDE1	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10313 3
■ Z6RDL15835WOWHZ10U	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10328 7
■ Z6RDL15835WSWHZ10U	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10703 2
■ Z6RDL15840WOCDE1	6" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10707 0
■ Z6RDL15840WOWHZ10U	6" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10706 3
2000lm			
■ Z6RDL20830WOCZ10U	6" Round, 2000lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10712 4
■ Z6RDL20835WOCDE1	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10316 4
■ Z6RDL20835WOWHZ10U	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10715 5
■ Z6RDL20835WOWHE1	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, ELV Dimming, 120V	★	1 90096 10714 8
■ Z6RDL20835WSWHZ10U	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10718 6
■ Z6RDL20840WOCZ10U	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10319 5
■ Z6RDL20840WOCDE1	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10721 6
■ Z6RDL20840WOWHZ10U	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10720 9
2500lm			
■ Z6RDL25830WOCZ10U	6" Round, 2500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10728 5
■ Z6RDL25835WOCZ10U	6" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10320 1
■ Z6RDL25835WOWHZ10U	6" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10729 2
3500lm			
■ Z6RDL35830WOCZ10U	6" Round, 3500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10743 8
■ Z6RDL35835WOCZ10U	6" Round, 3500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10322 5
■ Z6RDL35840WOCZ10U	6" Round, 3500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10746 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



P3RDL




P3RA



P3RLW



P3SLW



P3SA



Product	Description / Features	UPC
LyteProfile LED 3" Round		
Frames		
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45		
1000lm		
■ P3RDL10935CCZ10U	3" Round, 1000lm, 3500K (CRI 90), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 66644 6
■ P3RDL10935WHZ10U	3" Round, 1000lm, 3500K (CRI 90), White Reflector, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 69013 7
1500lm		
■ P3RDL15930CCZ10U	3" Round, 1500lm, 3000K (CRI 90), Comfort Clear Finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 66647 7
■ P3RDL15935CCZ10U	3" Round, 1500lm, 3500K (CRI 90), Comfort Clear Finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 66648 4
Adjustable Accent, 1000lm		
■ P3RA10930NFCDPZ10U	3" Round (Adjustable Accent), 1000lm, 3000K (CRI 90), Narrow Flood (21°), Comfort Clear Diffuse Finish, Matching Flange, 0–10V 1% Dimming, UNV	★ 7 84197 69024 3
■ P3RA10930NFCOPZ10U	3" Round (Adjustable Accent), 1000lm, 3000K (CRI 90), Narrow Flood (21°), Comfort Clear Finish, Matching Flange, 0–10V 1% Dimming, UNV	★ 7 84197 69023 6
Wall Wash, 1000lm		
■ P3RLW10930CCZ10U	3" Round (Wall Wash), 1000lm, 3000K (CRI 90), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 66649 1
■ P3RLW10935CCZ10U	3" Round (Wall Wash), 1000lm, 3500K (CRI 90), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 66650 7
LyteProfile LED 3" Square		
Frames		
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45		
1000lm		
■ P3SDL10930CCE1	3" Square, 1000lm, 3000K (CRI 90), Comfort Clear finish, White Flange, ELV Dimming, 120V	★ 7 84197 68713 7
Wall Wash, 1000lm		
■ P3SLW10935CCZ10U	3" Square (Wall Wash), 1000lm, 3500K (CRI 90), Comfort Clear finish, White Flange, 0–10V 1% Dimming, UNV	★ 7 84197 68724 3
Adjustable Accent, 1000lm		
■ P3SA10935NFCCE1	3" Square (Adjustable Accent), 1000lm, 3500K (CRI 90), Narrow Flood (21°), Comfort Clear finish, White Flange, ELV Dimming, 120V	★ 7 84197 68735 9
● Stock Ready (2–Day Quick Ship) ■ Design Ready (10–Day Quick Ship)		



P4RDL (CC)



P4RDL (CD)



P4RLW (CD)



Product	Description / Features	UPC
LyteProfile LED 4" Round		
Frames		
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45		
1000lm		
● P4RDL10830CCZ10U	4" Round, 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10257 0
● P4RDL10835CCZ10U	4" Round, 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10544 1
1500lm		
■ P4RDL15830CCZ10U	4" Round, 1500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10260 0
■ P4RDL15835CCZ10U	4" Round, 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10440 6
■ P4RDL15840CDZ10U	4" Round, 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10559 5
■ P4RDL15840CLZ10U	4" Round, 1500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10558 8
2000lm		
■ P4RDL20830CDZ10U	4" Round, 2000lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10566 3
■ P4RDL20830CCZ10U	4" Round, 2000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10262 4
■ P4RDL20835CCZ10U	4" Round, 2000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10263 1
2500lm		
■ P4RDL25830CCZ10U	4" Round, 2500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10572 4
■ P4RDL25835CCZ10U	4" Round, 2500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 10573 1
Wall Wash, 500lm		
■ P4RLW05830CLZ10U	4" Round (Wall Wash), 500lm, 3000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11251 7
■ P4RLW05835CLZ10U	4" Round (Wall Wash), 500lm, 3500K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11258 6
■ P4RLW05840CLZ10U	4" Round (Wall Wash), 500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11265 4
Wall Wash, 1000lm		
■ P4RLW10830CDZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11353 8
■ P4RLW10830CCZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11349 1
■ P4RLW10830CLZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11351 4
■ P4RLW10835CDZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11360 6
■ P4RLW10835CCZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11356 9
■ P4RLW10835CLZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11358 3
■ P4RLW10840CDZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11367 5
■ P4RLW10840CCZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11363 7
■ P4RLW10840CLZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11365 1
Wall Wash, 1500lm		
■ P4RLW15830CDZ10U	4" Round (Wall Wash), 1500lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11380 4
■ P4RLW15830CLZ10U	4" Round (Wall Wash), 1500lm, 3000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11378 1
■ P4RLW15835CDZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11476 4
■ P4RLW15835CCZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 68174 6
■ P4RLW15835CLZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11474 0
■ P4RLW15840CDZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11482 5
■ P4RLW15840CCZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 7 84197 68175 3
■ P4RLW15840CLZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0–10V 1% Dimming, UNV	★ 1 90096 11480 1
● Stock Ready (2–Day Quick Ship) ■ Design Ready (10–Day Quick Ship)		



P6RDL (CC)



P6RDL (CD)



P6RLW (CD)



P6SDL



Product	Description / Features	UPC
LyteProfile LED 6" Round		
Frames		
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45		
Downlight		
P6RDL10830CCZ10U	6" Round, 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10575 5
P6RDL10835CCZ10U	6" Round, 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 12821 1
P6RDL10840CDZ10U	6" Round, 1000lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10577 9
P6RDL10840CCZ10U	6" Round, 1000lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10576 2
P6RDL15830CCZ10U	6" Round, 1500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10581 6
P6RDL15840CDZ10U	6" Round, 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10584 7
P6RDL15840CCZ10U	6" Round, 1500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10583 0
P6RDL20830CCZ10U	6" Round, 2000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10271 6
P6RDL25830CCZ10U	6" Round, 2500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10589 2
P6RDL25840CCZ10U	6" Round, 2500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10883 1
P6RDL30830CCZ10U	6" Round, 3000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10590 8
Wall Wash		
P6RLW20830CCZ10U	6" Round (Wall Wash), 2000lm, 3000K (CRI 80), Comfort Clear finish	7 84197 68176 0
P6RLW20835CCZ10U	6" Round (Wall Wash), 2000lm, 3500K (CRI 80), Comfort Clear finish	7 84197 68177 7
P6RLW20840CCZ10U	6" Round (Wall Wash), 2000lm, 4000K (CRI 80), Comfort Clear finish	7 84197 68178 4
LyteProfile LED 6" Square		
P6SDL15835CCZ10U	6" Square , 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	1 90096 10623 3
Stock Ready (2-Day Quick Ship) Design Ready (10-Day Quick Ship)		



C3L / C3R



C3L / C3RA



C3L / C3SA



C3L / C3SDL



Product	Description / Features	UPC
Calculite LED 3" Round		
Frames		
See all Lightolier UniFrame options compatible with Calculite LED on pg. 45		
Downlight		
C3L07930ME1R	3", 750lm, 3000K (CRI 90), ELV, 120V, Remodeler	7 84197 68685 7
C3L109D2WWE1	3", 1000lm, 3000K-1800K (CRI 90) Dim to Warm, Wide (62°), ELV Dimming, 120V	7 84197 69009 0
C3L10930MZ10U	3", 1000lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66622 4
C3L10930ME1S	3", 1000lm, 3000K (CRI 90), Medium (55°), ELV Dimming, 120V, Shallow Plenum	7 84197 66630 9
C3L10935MZ10U	3", 1000lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66623 1
C3L10935ME1S	3", 1000lm, 3500K (CRI 90), Medium (55°), ELV Dimming, 120V, Shallow Plenum	7 84197 66631 6
C3L15930MZ10U	3", 1500lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66624 8
C3L15935MZ10U	3", 1500lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66625 5
C3L18935MZ10U	3", 1800lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66627 9
C3L20930MZ10U	3", 2000lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV	7 84197 66626 2
Adjustable		
C3RA15935NFZ10U	3" Round Adjustable, 1500lm, 3500K (CRI 90), Narrow Flood (23°), 0-10V 1% Dimming, UNV	7 84197 68696 3
Trims & Accessories		
C3RACC	3" Trim Round Adjustable, Clear Comfort Reflector, White (matte) Flange	7 84197 68702 1
C3RACCP	3" Trim Round Adjustable, Clear Comfort Reflector, Polished Flange	7 84197 68703 8
C3RDLCC	3" Trim Round Downlight, Clear Comfort Reflector, White (matte) Flange	7 84197 66632 3
C3RDLWH	3" Trim Round Downlight, White (matte) Reflector, White (matte) Flange	7 84197 68999 5
C3RLWCC	3" Trim Round Lensed Wall Wash, Clear Comfort Reflector, White (matte) Flange	7 84197 66635 4
C3RLWWH	3" Trim Round Lensed Wall Wash, White (matte) Reflector, White (matte) Flange	7 84197 69000 7
CA3RAAFT	3", Accessory, Round Mud-in ring for flangeless installs (ordered with a flangeless trim)	1 90096 01794 2
Calculite LED 3" Square		
Frames		
See all Lightolier UniFrame options compatible with Calculite LED on pg. 45		
Downligh		
C3L10935SZ10U	3" Square, 1000lm, 3500K (CRI 90), 0-10V 1% Dimming, UNV	7 84197 69007 6
Trims & Accessories		
C3SACC	3" Trim Square Adjustable , Clear Comfort Reflector, White (matte) Flange	7 84197 68704 5
C3SDLMCC	3" Trim Square Downlight, Medium (59°), Clear Comfort Reflector, White (matte) Flange	7 84197 66633 0
C3SDLWCC	3" Trim Square Downlight, Wide (71°), Clear Comfort Reflector, White (matte) Flange	7 84197 66634 7
C3SDLWDPS	3" Trim Square Downlight, Wide (71°), Aluminum Diffuse Reflector, White Flange (1" regress cast aluminum)	7 84197 66640 8
C3SLWCC	3" Trim Square Lens Wall Washed, Clear Comfort Reflector, White (matte) Flange	7 84197 66636 1
CA3SAAFT	3", Accessory, Square Mud-in ring for flangeless installs (ordered with a flangeless trim)	1 90096 01795 9
Stock Ready (2-Day Quick Ship) Design Ready (10-Day Quick Ship)		



Product	Description / Features		UPC
Calculite LED 4" Round	Frame		
■ C4RA	4" Frame, Round, AirSeal (IC), UNV (120/277V)	★	7 84197 24057 8
	See all Lightolier UniFrame options compatible with Calculite LED on pg. 45		
	LED		
■ C4L05830MZ10U	4", 500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97447 7
■ C4L05830NZ10U	4", 500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97443 9
■ C4L05830WZ10U	4", 500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97451 4
■ C4L05835MZ10U	4", 500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97448 4
■ C4L05835NZ10U	4", 500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97444 6
■ C4L05835WZ10U	4", 500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97452 1
■ C4L05840MZ10U	4", 500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97449 1
■ C4L05840NZ10U	4", 500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97445 3
■ C4L05840WZ10U	4", 500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97453 8
■ C4L10830MZ10U	4", 1000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97483 5
■ C4L10830NZ10U	4", 1000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97479 8
■ C4L10830WZ10U	4", 1000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97487 3
■ C4L10835MZ10U	4", 1000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97484 2
■ C4L10835NZ10U	4", 1000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97480 4
■ C4L10835WZ10U	4", 1000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97488 0
■ C4L10840MZ10U	4", 1000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97485 9
■ C4L10840NZ10U	4", 1000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97481 1
■ C4L10840WZ10U	4", 1000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97489 7
■ C4L15830MZ10U	4", 1500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97534 4
■ C4L15830NZ10U	4", 1500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97530 6
■ C4L15830WZ10U	4", 1500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97538 2
■ C4L15835MZ10U	4", 1500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97535 1
■ C4L15835NZ10U	4", 1500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97531 3
■ C4L15835WZ10U	4", 1500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97539 9
■ C4L15840NZ10U	4", 1500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97532 0
■ C4L15840WZ10U	4", 1500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97540 5
■ C4L20830MZ10U	4", 2000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97582 5
■ C4L20830NZ10U	4", 2000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97578 8
■ C4L20830WZ10U	4", 2000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97586 3
■ C4L20835MZ10U	4", 2000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97583 2
■ C4L20835NZ10U	4", 2000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97579 5
■ C4L20835WZ10U	4", 2000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97587 0
■ C4L20840MZ10U	4", 2000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97584 9
■ C4L20840NZ10U	4", 2000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97580 1
■ C4L20840WZ10U	4", 2000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97588 7
■ C4L25830MZ10U	4", 2500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97660 0
■ C4L25830NZ10U	4", 2500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97656 3
■ C4L25830WZ10U	4", 2500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97664 8

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
Calculite LED 4" Round	LED (Continued)		
■ C4L25835MZ10U	4", 2500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97661 7
■ C4L25835NZ10U	4", 2500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97657 0
■ C4L25835WZ10U	4", 2500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97665 5
■ C4L25840MZ10U	4", 2500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97662 4
■ C4L25840NZ10U	4", 2500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97658 7
■ C4L25840WZ10U	4", 2500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97666 2
■ C4L30830MZ10U	4", 3000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	1 90096 02766 8
■ C4L30830NZ10U	4", 3000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97709 6
■ C4L30830WZ10U	4", 3000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97717 1
■ C4L30835MZ10U	4", 3000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97714 0
■ C4L30835NZ10U	4", 3000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97710 2
■ C4L30835WZ10U	4", 3000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97718 8
■ C4L30840MZ10U	4", 3000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV	★	6 62057 97715 7
■ C4L30840NZ10U	4", 3000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV	★	6 62057 97711 9
■ C4L30840WZ10U	4", 3000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV	★	6 62057 97719 5
	Trims		
■ C4RDLCDF	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Flangeless	★	6 62057 97241 1
■ C4RDLCDP	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Polished Flange	★	6 62057 97236 7
■ C4RDLCD	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, White (matte) Flange	★	6 62057 97230 5
■ C4RDLCCF	4" Trim, Round Downlight, Clear Comfort Reflector, Flangeless	★	6 62057 97239 8
■ C4RDLCCP	4" Trim, Round Downlight, Clear Comfort Reflector, Polished Flange	★	6 62057 97234 3
■ C4RDLCC	4" Trim, Round Downlight, Clear Comfort Reflector, White (matte) Flange	★	6 62057 97200 8
■ C4RDLCLF	4" Trim, Round Downlight, Specular Clear Reflector, Flangeless	★	6 62057 97240 4
■ C4RDLCLP	4" Trim, Round Downlight, Specular Clear Reflector, Polished Flange	★	6 62057 97235 0
■ C4RDLCL	4" Trim, Round Downlight, Specular Clear Reflector, White (matte) Flange	★	6 62057 97229 9
■ C4RDLWHF	4" Trim, Round Downlight, White (matte) Reflector, Flangeless	★	1 90096 02217 5
■ C4RDLWH	4" Trim, Round Downlight, White (matte) Reflector, White (matte) Flange	★	1 90096 02215 1
■ C4RWWCDF	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, Flangeless	★	6 62057 96522 2
■ C4RWWCDP	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, Polished Flange	★	6 62057 96517 8
■ C4RWWCD	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, White (matte) Flange	★	6 62057 96502 4
■ C4RWWCCF	4" Trim, Round Open Wall Wash, Clear Comfort Reflector, Flangeless	★	6 62057 96520 8
■ C4RWWCCP	4" Trim, Round Open Wall Wash, Clear Comfort Reflector, Polished Flange	★	6 62057 96515 4
■ C4RWWCLF	4" Trim, Round Open Wall Wash, Specular Clear Reflector, Flangeless	★	6 62057 96521 5
■ C4RWWCL	4" Trim, Round Open Wall Wash, Specular Clear Reflector, White (matte) Flange	★	6 62057 96501 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
Calculite LED 6" Round	Frame		
■ C6RA	6" Frame, Round, AirSeal (IC), UNV (120/277V)	★	7 84197 24060 8
	See all Lightolier UniFrame options compatible with Calculite LED on pg. 45		
	LED		
■ C6L10830MZ10U	6", 1000lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97761 4
■ C6L10830NZ10U	6", 1000lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97757 7
■ C6L10830WZ10U	6", 1000lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97765 2
■ C6L10835MZ10U	6", 1000lm, 3500K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97762 1
■ C6L10835NZ10U	6", 1000lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97758 4
■ C6L10835WZ10U	6", 1000lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97766 9
■ C6L10840MZ10U	6", 1000lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97763 8
■ C6L10840NZ10U	6", 1000lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97759 1
■ C6L10840WZ10U	6", 1000lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97767 6
■ C6L15830MZ10U	6", 1500lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97809 3
■ C6L15830NZ10U	6", 1500lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97805 5
■ C6L15830WZ10U	6", 1500lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97813 0
■ C6L15835NZ10U	6", 1500lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97806 2
■ C6L15835WZ10U	6", 1500lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97814 7
■ C6L15840MZ10U	6", 1500lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97811 6
■ C6L15840NZ10U	6", 1500lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97807 9
■ C6L15840WZ10U	6", 1500lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97815 4
■ C6L20830MZ10U	6", 2000lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97953 3
■ C6L20830NZ10U	6", 2000lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97908 3
■ C6L20830WZ10U	6", 2000lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97992 2
■ C6L20835NZ10U	6", 2000lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97909 0
■ C6L20835WZ10U	6", 2000lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97993 9
■ C6L20840MZ10U	6", 2000lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 97963 2
■ C6L20840NZ10U	6", 2000lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 97910 6
■ C6L20840WZ10U	6", 2000lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 97997 7
■ C6L25830MZ10U	6", 2500lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98203 8
■ C6L25830NZ10U	6", 2500lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98185 7
■ C6L25830WZ10U	6", 2500lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98218 2
■ C6L25835MZ10U	6", 2500lm, 3500K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98215 1
■ C6L25835NZ10U	6", 2500lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98186 4
■ C6L25835WZ10U	6", 2500lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98220 5
■ C6L25840MZ10U	6", 2500lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98216 8
■ C6L25840NZ10U	6", 2500lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98187 1
■ C6L25840WZ10U	6", 2500lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98221 2
■ C6L35830MZ10U	6", 3500lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98344 8
■ C6L35830NZ10U	6", 3500lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98339 4
■ C6L35830WZ10U	6", 3500lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98375 2

● Stock Ready (2–Day Quick Ship) ■ Design Ready (10–Day Quick Ship)



Product	Description / Features		UPC
Calculite LED 6" Round	LED (Continued)		
■ C6L35835MZ10U	6", 3500lm, 3500K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98345 5
■ C6L35835NZ10U	6", 3500lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98341 7
■ C6L35835WZ10U	6", 3500lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98376 9
■ C6L35840MZ10U	6", 3500lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 98350 9
■ C6L35840NZ10U	6", 3500lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 98342 4
■ C6L35840WZ10U	6", 3500lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	6 62057 98379 0
■ C6L48830MZ10U	6", 4800lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	6 62057 99999 9
■ C6L48830NZ10U	6", 4800lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 99586 1
■ C6L48830WZ10U	6", 4800lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02174 1
■ C6L48835MZ10U	6", 4800lm, 3500K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	1 90096 02002 7
■ C6L48835NZ10U	6", 4800lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 99587 8
■ C6L48835WZ10U	6", 4800lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02175 8
■ C6L48840MZ10U	6", 4800lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	1 90096 02172 7
■ C6L48840NZ10U	6", 4800lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	6 62057 99589 2
■ C6L48840WZ10U	6", 4800lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02177 2
■ C6L60830MZ10U	6", 6000lm, 3000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	1 90096 02196 3
■ C6L60830NZ10U	6", 6000lm, 3000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	1 90096 02192 5
■ C6L60830WZ10U	6", 6000lm, 3000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02200 7
■ C6L60835MZ10U	6", 6000lm, 3500K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	1 90096 02197 0
■ C6L60835NZ10U	6", 6000lm, 3500K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	1 90096 02193 2
■ C6L60835WZ10U	6", 6000lm, 3500K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02201 4
■ C6L60840MZ10U	6", 6000lm, 4000K (CRI 80), Medium (55°), 0–10V 1% Dimming, UNV	★	1 90096 02198 7
■ C6L60840NZ10U	6", 6000lm, 4000K (CRI 80), Narrow (38/40°), 0–10V 1% Dimming, UNV	★	1 90096 02194 9
■ C6L60840WZ10U	6", 6000lm, 4000K (CRI 80), Wide (68/72°), 0–10V 1% Dimming, UNV	★	1 90096 02202 1
	Trims & Accessories		
■ C6RDLCDF	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Flangeless		6 62057 97299 2
■ C6RDLCDP	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Polished Flange		6 62057 97294 7
■ C6RDLCD	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, White (matte) Flange		6 62057 97288 6
■ C6RDLCCF	6" Trim, Round Downlight, Clear Comfort Reflector, Flangeless		6 62057 97297 8
■ C6RDLCCP	6" Trim, Round Downlight, Clear Comfort Reflector, Polished Flange		6 62057 97292 3
■ C6RDLCC	6" Trim, Round Downlight, Clear Comfort Reflector, White (matte) Flange		6 62057 97286 2
■ C6RDLCLF	6" Trim, Round Downlight, Specular Clear Reflector, Flangeless		6 62057 97298 5
■ C6RDLCLP	6" Trim, Round Downlight, Specular Clear Reflector, Polished Flange		6 62057 97293 0
■ C6RDLCL	6" Trim, Round Downlight, Specular Clear Reflector, White (matte) Flange		6 62057 97287 9
■ C6RDLWHF	6" Trim, Round Downlight, White (matte) Reflector, Flangeless		1 90096 02245 8
■ C6RDLWH	6" Trim, Round Downlight, White (matte) Reflector, White (matte) Flange		1 90096 02243 4
■ C6RWWCD	6" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, White (matte) Flange		6 62057 96636 6
■ C6RWWCC	6" Trim, Round Open Wall Wash, Clear Comfort Reflector, White (matte) Flange		6 62057 96634 2
■ C6RWWWHF	6" Trim, Round Open Wall Wash, White (matte) Reflector, Flangeless		1 90096 02248 9
■ C6RWWWH	6" Trim, Round Open Wall Wash, White (matte) Reflector, White (matte) Flange		1 90096 02246 5
■ CA6RFT	6" Round Mud-in ring for use in flangeless trim installations (ordered with a flangeless trim)		1 90096 03031 6

● Stock Ready (2–Day Quick Ship) ■ Design Ready (10–Day Quick Ship)



C6SDL



C7RWWCDP



C7RDLWCL

Product	Description / Features		UPC
Calculite LED 6" Square	Frames See all Lightolier UniFrame options compatible with Calculite LED on pg. 45 Trims		
■ C6SDLNMCC	6" Trim, Square Downlight, Narrow & Medium Beam, Clear Comfort Reflector, White (matte) Flange	★	6 62057 97183 4
■ C6SDLWCC	6" Trim, Square Downlight, Wide Beam, Clear Comfort Reflector, White (matte) Flange	★	6 62057 97315 9
	Accessory		
■ CA6SFT	6" Square Mud-in ring for use in flangeless trim installations (ordered with a flangeless trim)		1 90096 03032 3
Calculite LED 7" Round	Frames See all Lightolier UniFrame options compatible with Calculite LED on pg. 45 Trims		
■ C7RDLNMWH	7" Trim, Round Downlight, Narrow & Medium Beam, White (matte) Reflector, White (matte) Flange	★	1 90096 02275 5
■ C7RDLNMCDP	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Diffuse Reflector, Polished Flange	★	6 62057 97082 0
■ C7RDLNMCD	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Diffuse Reflector, White (matte) Flange	★	6 62057 97076 9
■ C7RDLNMCOP	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Reflector, Polished Flange	★	6 62057 97080 6
■ C7RDLNMCC	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Reflector, White (matte) Flange	★	6 62057 97074 5
■ C7RDLNMCL	7" Trim, Round Downlight, Narrow & Medium Beam, Specular Clear Reflector, White (matte) Flange	★	6 62057 97075 2
■ C7RDLWCD	7" Trim, Round Downlight, Wide Beam, Clear Comfort Diffuse Reflector, White (matte) Flange	★	6 62057 97093 6
■ C7RDLWCC	7" Trim, Round Downlight, Wide Beam, Clear Comfort Reflector, White (matte) Flange	★	6 62057 97091 2
■ C7RDLWCL	7" Trim, Round Downlight, Wide Beam, Specular Clear Reflector, White (matte) Flange	★	6 62057 97092 9

● Stock Ready (2-Day Quick Ship)

■ Design Ready (10-Day Quick Ship)



Discover the full range of specification downlighting products available in the Calculite LED family online at [lightolier.com](#)





Product	Description / Features		UPC
LyteCaster LED, 3" Accent			
Frames			
■ L3AE1	New Construction (Non-IC), ELV/TRIAC, 120V	★	6 62057 99932 6
■ L3NZ10U	New Construction (Non-IC), 0-10V Dimming, 120-277V	★	6 62057 99945 6
LED			
■ L308827F	3" Accent, 800lm, 2700K (CRI 80), Flood (33°)	★	6 62057 99799 5
■ L308827NF	3" Accent, 800lm, 2700K (CRI 80), Narrow Flood (22°)	★	6 62057 99798 8
■ L308927NF	3" Accent, 800lm, 2700K (CRI 90), Narrow Flood (22°)	★	6 62057 99818 3
■ L308830S	3" Accent, 800lm, 3000K (CRI 80), Spot (17°)	★	6 62057 99800 8
■ L308835F	3" Accent, 800lm, 3500K (CRI 80), Flood (33°)	★	6 62057 99813 8
■ L308835NF	3" Accent, 800lm, 3500K (CRI 80), Narrow Flood (22°)	★	6 62057 99812 1
Trims			
■ L3RAPA	3" Accent Trim, Round / Adjustable Pinhole, Aluminum	★	6 62057 99786 5
■ L3RAPW	3" Accent Trim, Round / Adjustable Pinhole, White	★	6 62057 99785 8
■ L3RAD	3" Accent Trim, Round / Adjustable, Diffuse Cone with white flange	★	6 62057 99766 7
■ L3RABW	3" Accent Trim, Round / Baffle Adjustable, White Baffle with white flange	★	6 62057 99764 3
■ L3RGA	3" Accent Trim, Round / Gimbal, Aluminum	★	6 62057 99784 1
■ L3RGB	3" Accent Trim, Round / Gimbal, Black	★	6 62057 99783 4
■ L3RLWC	3" Accent Trim, Round / Lensed Wall Wash, Chrome Cone with white flange	★	6 62057 99770 4
■ L3RLWD	3" Accent Trim, Round / Lensed Wall Wash, Diffuse Cone with white flange	★	6 62057 99771 1
■ L3RLWW	3" Accent Trim, Round / Lensed Wall Wash, White Cone with white flange	★	6 62057 99772 8
■ L3RSA	3" Accent Trim, Round / Shower Light, Aluminum	★	6 62057 99769 8
■ L3SADA	3" Accent Trim, Square / Adjustable, Diffuse Cone with aluminum flange	★	6 62057 99777 3
■ L3SAD	3" Accent Trim, Square / Adjustable, Diffuse Cone with white flange	★	6 62057 99776 6
■ L3SDDA	3" Accent Trim, Square / Downlight, Diffuse Cone with aluminum flange	★	6 62057 99774 2
■ L3SLWA	3" Accent Trim, Square / Lensed Wall Wash, Aluminum	★	6 62057 99779 7
■ L3SLWW	3" Accent Trim, Square / Lensed Wall Wash, White	★	6 62057 99778 0
■ L3SSA	3" Accent Trim, Square / Shower Light, Aluminum	★	6 62057 99781 0
■ L3SSW	3" Accent Trim, Square / Shower Light, White	★	6 62057 99780 3
Accessories			
■ L3SD	3" Accent Accessory, 5° Soft Diffusion Film		1 90096 13525 7
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
LyteCaster LED 4"			
Trims			
● L4RDD	4" Trim, Round / Downlight, Clear diffuse with white flange	★	6 62057 99370 6
● L4RDW	4" Trim, Round / Downlight, White with white flange	★	6 62057 99371 3
■ L4SBW	4" Trim, Square / Baffle Downlight, White with White Flange	★	1 90096 03142 9
■ L4SDD	4" Trim, Square / Downlight, Clear Diffuse with White Flange	★	1 90096 03139 9
LyteCaster LED 5"			
Trims			
■ L5RBW	5" Trim, Round / Downlight, Baffle white with white flange	★	6 62057 99383 6
● L5RDD	5" Trim, Round / Downlight, Clear diffuse with white flange	★	6 62057 99384 3
● L5RDW	5" Trim, Round / Downlight, White with white flange	★	6 62057 99385 0
■ L5SBW	5" Trim, Square / Baffle Downlight, White with White Flange	★	1 90096 03143 6
■ L5SDD	5" Trim, Square / Downlight, Clear Diffuse with White Flange	★	1 90096 03140 5
■ L5SDW	5" Trim, Square / Downlight, White with White Flange	★	1 90096 03137 5
LyteCaster LED 6"			
Trims			
■ L6RBW	6" Trim, Round / Downlight, Baffle white with white flange	★	6 62057 99398 0
● L6RDD	6" Trim, Round / Downlight, Clear diffuse with white flange	★	6 62057 99399 7
● L6RDW	6" Trim, Round / Downlight, White with white flange	★	6 62057 99400 0
■ L6SBW	6" Trim, Square / Baffle Downlight, White with White Flange	★	1 90096 03144 3
■ L6SDD	6" Trim, Square / Downlight, Clear Diffuse with White Flange	★	1 90096 03141 2
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			






Product	Description / Features		UPC
LyteCaster Conventional		3.75"	
■ 2003RS	3.75", Non-IC Remodeler	★	7 84197 17614 3
■ 2076WH	3.75" Trim, Gloss White Baffle, Gloss White Flange	★	6 62057 20608 0
■ L3RPF	3.75" Replacement Optic, Flood	★	6 62057 99822 0
■ L3RPNF	3.75" Replacement Optic, Narrow Flood	★	6 62057 99821 3
■ L3RPS	3.75" Replacement Optic, Spot	★	6 62057 99820 6
■ L3AHB	3.75" Accent Accessory Holder, Black	★	6 62057 99788 9
■ L3AHW	3.75" Accent Accessory Holder, White	★	6 62057 99787 2
● 0089L	New Construction Plate, 3" Round (Long)	★	6 24563 16007 2
● 0089S	New Construction Plate, 3" Round (Short)	★	6 24563 10769 5
		4"	
● 0092L	New Construction Plate, 4" Round (Long)	★	6 24563 15997 7
● 0092S	New Construction Plate, 4" Round (Short)	★	6 24563 10770 1
		5"	
■ 1000IC	5" IC Frame	★	7 84197 11995 9
■ 1004ICNS	5" Lytening IC Frame with Integral Nails	★	7 84197 48773 7
■ 1004SICR	5" Lytening IC Frame / Non-IC Shallow	★	7 84197 19853 4
■ 1004ICXS	5" Lytening IC Frame (High Watt) with Integral Screws	★	7 84197 21984 0
■ 1005WHS	5" Trim, White Step Baffle Reflector	★	7 84197 51354 2
■ 1013WH	5" Trim, White Cone	★	7 84197 10130 5
● 1076CH	5" Trim, Basic Specular Cone Chrome Reflector	★	6 62057 67212 0
● 1076WH	5" Trim, Basic White Baffle	★	7 84197 10760 4
		6.75"	
■ 1100IC	6.75" IC Frame	★	7 84197 11023 9
■ 1104SIC	6.75" Lytening IC Frame / Non-IC Shallow	★	7 84197 19849 7
■ 1104SICR	6.75" Lytening Remodeler IC Frame / Non-IC Shallow	★	7 84197 19854 1
● 1105CL	6.75" Trim, Reflector Alzak Cone Clear	★	6 62057 67977 8
■ 1105WH	6.75" Trim, Step Baffle Reflector, Matte White	★	7 84197 11070 3
■ 1113CD	6.75" Trim, Cone Reflector, Clear Diffuse, White Flange	★	7 84197 35971 3
■ 1113WH	6.75" Trim, Cone Reflector, Matte White	★	7 84197 01113 0
● 1176WH	6.75" Trim, Basic Baffle White	★	7 84197 00351 7
■ 1176WHSNEW	6.75" Trim, Baffle Reflector, White Baffle, White Flange	★	7 84197 12036 8
		Accessories	
■ LAS56	Lytening AirSeal Gasket		7 84197 36723 7
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
LytePoints Conventional		3.75"	
■ 394CHX	3.75" Trim, MR16 Basic Cone Chrome	★	6 24563 15413 2
		4.25"	
■ 502AICSX	4.25" PAR20 Frame-In Kit IC/AirSeal	★	6 24563 21722 6
■ 502X	4.25" V-Frame, Frame-In Kit Non-IC	★	6 24563 08840 6
■ 513WHX	4.25" Trim, Residence PAR20 White	★	6 24563 08854 3
■ 516WHX	4.25" Trim, Contour PAR20 White	★	6 24563 08855 0
■ 575WHX	4.25" Trim, Adjustable Step Baffle PAR20 White	★	6 24563 08845 1
■ 594CHX	4.25" Trim, Adjustable Alzak Cone PAR20 Chrome	★	6 24563 11675 8
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Flexible lighting that
can evolve with your
spaces

Choose Lightolier by Signify for a complete selection
of professional track and downlighting solutions.
Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

LIGHTOLIER

Click images to
view eCatalogue
(Detailed brochures,
bulletins, spec
sheets, IES files, etc.)

Product Family		Basic Track	BoldFlood	LightFlood	Alcyon Vertical	Alcyon Recessed Multiples	OmniSpot	OmniSpot Recessed Multiples
Page Reference		pg. 64	pg. 67	pg. 67	pg. 66	pg. 66	pg. 67	pg. 68
Quick Ship Service								
Budget / Grade		Value / Good	Performance / Better		Spec / Best			
Trim & Finish	Finishes	Aluminum* White Black*	Aluminum* White Black*	Aluminum White* Black*	Aluminum* White Black	White Black*	Aluminum* White Black	White Black*
	Optics		Integrated	Integrated	Modular	Modular	Modular	Modular
	Narrow Spot				✓	✓	✓	✓
	Spot			✓	✓	✓	✓	✓
	Narrow Flood			✓	✓	✓	✓	✓
	Flood		✓	✓	✓	✓	✓	✓
	Beams		95° W x 90° L	100°	10° to 36° (4 beams)	10° to 36° (4 beams)	11° to 36° (4 beams)	11° to 36° (4 beams)
Spec & Performance	Lumens		2000 4000	2000 4000*	600, 1000, 2000, 3000	600, 1300, 2000	600, 1000, 2000	600 1000
	Wattage (W)		23-41W	23W	10-34W	10-34W	6-25W	6-12W
	Efficacy (lm/W)		up to 100	up to 100	up to 93	up to 60	up to 108	up to 83
	CCT (K)		2700K* 3000K 3500K 4000K*	2700K* 3000K 4000K*	2700K* 3000K 3500K* 4000K*	2700K* 3000K 4000K*	2700K* 3000K 4000K*	2700K* 3000K 3500K* 4000K*
	CRI		90	80	80 / 90	80	80 / 90	80, 90
	CrispWhite			■ ◆	■ ◆		■ ◆	■ ◆
	CBCP		up to 1,808cd	up to 900cd	up to 46,000cd	up to 14,400cd	up to 30,000cd	up to 8,700cd
Accessories	Dimming		ELV	ELV / TRIAC	ELV	0-10V	ELV	0-10V
	Adapters	Lightolier Halo* Juno*	Lightolier Halo* Juno*	Lightolier Halo* Juno* GES* GTEK* HTEK*	Lightolier Halo* Juno* Prospec*	-	Lightolier Juno Halo* Capri* GTEK* Prospec*	-
	Accessory Holder Snoot				✓	✓	✓	✓
	Diffusion Filters & Films				✓	✓	✓	✓
	Colour Filters							
Ratings & Certification	Hex Cell Louvers		✓		✓	✓	✓	✓
	cULus listed	✓	✓	✓	✓	✓	✓	✓
	Energy Star		✓		✓	✓	✓	✓
	Lifetime (L70)		up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours
Warranty			5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.					

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



Basic Track (60)



Product	Description / Features		UPC
Basic Track			
■ 6002DWH	Gen 2, 2' Individual Track with Dead End, White	★	1 90096 19174 1
■ 6002DBK	Gen 2, 2' Individual Track with Dead End, Black	★	1 90096 19175 8
■ 6002DAL	Gen 2, 2' Individual Track with Dead End, Aluminum	★	1 90096 19176 5
■ 6004DWH	Gen 2, 4' Individual Track with Dead End, White	★	1 90096 19177 2
■ 6004DBK	Gen 2, 4' Individual Track with Dead End, Black	★	1 90096 19178 9
■ 6004DAL	Gen 2, 4' Individual Track with Dead End, Aluminum	★	1 90096 19179 6
■ 6008DWH	Gen 2, 8' Individual Track with Dead End, White	★	1 90096 19180 2
■ 6008DBK	Gen 2, 8' Individual Track with Dead End, Black	★	1 90096 19181 9
■ 6008DAL	Gen 2, 8' Individual Track with Dead End, Aluminum	★	1 90096 19182 6
LyteSpan Basic Track			
■ 6000NBK	2' Individual Track with Live End Feed Connector, Black	★	7 84197 59418 3
■ 6000NWH	2' Individual Track with Live End Feed Connector, White	★	7 84197 59419 0
■ 6002NAL	8' Individual Track with Live End Feed Connector, Aluminum	★	7 84197 53980 1
■ 6003NBK	8' Joiner Track with Mini Coupler, Black	★	7 84197 59424 4
■ 6004NAL	4' Plain Track with Dead End, Aluminum	★	7 84197 53977 1
■ 6008NAL	8' Plain Track with Dead End, Aluminum	★	7 84197 53973 3
Basic Connectors			
■ 6046NBK	Basic Power Extension Connector, Black	★	7 84197 59454 1
■ 6046NWH	Basic Power Extension Connector, White	★	7 84197 59455 8
■ 6048NAL	Basic Live End, Aluminum	★	7 84197 53975 7
● 6048NBK	Basic Live End, Black	★	7 84197 59458 9
● 6048NWH	Basic Live End, White	★	7 84197 59459 6
■ 6049NAL	Basic Mini Coupler, Aluminum	★	7 84197 53947 4
● 6049NBK	Basic Mini Coupler, Black	★	7 84197 59456 5
● 6049NWH	Basic Mini Coupler, White	★	7 84197 59457 2
■ 6050NBK	Basic "L" Connector, Black	★	7 84197 59446 6
● 6050NWH	Basic "L" Connector, White		7 84197 59447 3
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



"T" Connector



"X" Connector



In-Line Connector



End Feed Canopy Kit



Saddle Canopy Kit Power Feed



Product	Description / Features		UPC
LyteSpan Basic Track		Basic Connectors (Continued)	
■ 6051NBK	Basic "T" Connector, Black	★	7 84197 59448 0
■ 6051NWH	Basic "T" Connector, White	★	7 84197 59449 7
■ 6052NBK	Basic "X" Connector, Black	★	7 84197 59450 3
■ 6054NBK	Basic In-Line Connector, Black	★	7 84197 59432 9
■ 6054NWH	Basic In-Line Connector, White	★	7 84197 59435 0
■ 6099BK	Basic PowerTrip, Live End Canopy, Black	★	7 84197 46993 1
■ 6099WH	Basic PowerTrip, Live End Canopy, White	★	7 84197 46992 4
LyteSpan Track Accessories			
■ 6060BK	End Feed Canopy Kit Black		7 84197 60601 5
■ 6060NAL	End Feed Canopy Kit Aluminum		7 84197 59474 9
■ 6060WH	End Feed Canopy Kit White		7 84197 60600 8
■ 6061BK	Floating Canopy Kit Black		7 84197 60611 4
■ 6063BK	Saddle Canopy Kit Power Feed Black		7 84197 60631 2
■ 6063WH	Saddle Canopy Kit Power Feed White		7 84197 60630 5
■ 6074WH	Extension Wand 18" White		7 84197 60740 1
■ 6087	Regressed Edge Panel & T Bar Clips (9Clip/Box)		7 84197 02006 4
■ 6089	Regressed Edge Panel & Slotted Grid Runner Clips (9Clip/Box)		7 84197 60890 3
■ 7584	18" Stem Mounting Kit for Basic & Advent Track White		7 84197 27426 9
■ 7586	48" Stem Mounting Kit for Basic & Advent Track White		7 84197 27432 0
■ 7681	48" Stem Mounting Kit for Basic & Advent Track Black		7 84197 27711 6
■ 7589BK	Track Attachment Fitting, Matte Black		7 84197 75890 5
■ 7596	Track/Surface Raceway Adapter for Basic Track		7 84197 27462 7
■ 7599	Track Pendant Adapter, White		7 84197 00230 5
PowerTrip Plug-In Breaker			
■ PLD120BK	120W (1.0A), Black		7 84197 53136 2
■ PLD120WH	120W (1.0A), White		7 84197 53137 9
■ PLD360BK	360W (3.0A), Black		7 84197 53152 2
■ PLD600BK	600W (5.0A), Black		7 84197 53157 7
■ PLD600WH	600W (5.0A), White		7 84197 53158 4
■ PLD900BK	900W (7.5A), Black		1 90096 13592 9
■ PLD900WH	900W (7.5A), White		1 90096 13593 6
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Clips



Raceway Adapter



PowerTrip Plug-In Breaker



LLAV11 (Medium)



LLAV20 (Medium)



LLAV (Large)

Product	Description / Features		UPC
Alcyon LED Vertical Medium Cylinder			
■ LLAV1130BK	1300lm, 3000K (CRI 80), Black	★	6 62057 54204 1
■ LLAV1130WH	1300lm, 3000K (CRI 80), White	★	6 62057 54203 4
■ LLAV2030BK	2000lm, 3000K (CRI 80), Black	★	6 62057 94974 1
■ LLAV2030WH	2000lm, 3000K (CRI 80), White	★	6 62057 94973 4
■ LLAV20930WHCW	2000lm, 3000K (CRI 90) Crisp White, White	★	6 62057 94982 6
Accessories			
■ LLAV11AHAL	Accessory holder, Aluminum		6 62057 89826 1
■ LLAV11AHWH	Accessory holder, White		6 62057 89824 7
■ LLAV11FR	Diffusion Film, Frosted Etched		6 62057 89858 2
■ LLAV11LS	Diffusion Film, Linear Spread		6 62057 89852 0
■ LLAV11SF	Diffusion Film, Soft Focus		6 62057 89856 8
■ LLAV11SY	Diffusion Film, Symmetrical Spread		6 62057 89854 4
■ LLAV11RNS	Reflector, Narrow Spot (11°)		6 62057 89679 3
Alcyon LED Vertical Large Cylinder			
■ LLAV3030BK	3000lm, 3000K (CRI 90) Crisp White, White	★	1 90096 01950 2
Accessories			
■ LLAV12RF	Reflector, Flood (36°)		6 62057 89677 9
■ LLAV12RNS	Reflector, Narrow Spot (11°)		6 62057 89678 6
■ LLAV12RS	Reflector, Spot (17°)		6 62057 89675 5
Alcyon LED Recessed Multiples			
1 Head Frame & Fixture			
■ LLAVRM11H1120	Frame, 1 Head, 120V	★	6 62057 91343 8
2 Head Frame & Fixture			
■ LLAVRM11H2120	Frame, 2 Head, 120V	★	6 62057 91345 2
■ LLAVRM12H2120	Frame, 2 Head (2000lm), 120V	★	6 62057 91356 8
■ LLAVRM11H2277	Frame, 2 Head, 277V	★	6 62057 91347 6
■ LLAVRMWH1130H2	Fixture, 2 Head, 1300lm, 3000K (CRI 80), White	★	6 62057 91294 3
3 Head Frame & Fixture			
■ LLAVRM11H3120	Frame, 3 Head, 120V	★	6 62057 91349 0
■ LLAVRM12H3120	Frame, 3 Head (2000lm), 120V	★	6 62057 91358 2
■ LLAVRM11H3277	Frame, 3 Head, 277V	★	6 62057 91350 6
■ LLAVRMWH1130H3	Fixture, 3 Head, 1300lm, 3000K (CRI 80), White	★	6 62057 91296 7
4 Head Frame & Fixture			
■ LLAVRM12H4120	Frame, 4 Head (2000lm), 120V	★	6 62057 91360 5
■ LLAVRM11H4277	Frame, 4 Head, 277V	★	6 62057 91353 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



LLAVRM (1 Head)



LLAVRM (2 Head)



LLAVRM (3 Head)



LLAVRM (4 Head)



BoldFlood LED



LightFlood LED



OmniSpot LED



OmniSpot LED

Product	Description / Features		UPC
BoldFlood LED			
■ LWW20930WH	2000lm, 3000K (CRI 90), White (matte)	★	1 90096 13639 1
■ LWW20935WH	2000lm, 3500K (CRI 90), White (matte)	★	1 90096 13640 7
■ LWW40930WH	4000lm, 3000K (CRI 90), White (matte)	★	1 90096 13641 4
■ LWW40935WH	4000lm, 3500K (CRI 90), White (matte)	★	1 90096 13642 1
LightFlood LED			
■ LLF230AL	2000lm, 3000K (CRI 80), Aluminum	★	6 62057 75883 1
OmniSpot LED Track Heads (06/10)			
Track Head with Lightolier Adapter			
■ LC06830BKTE	600lm, 3000K (CRI 80), Matte Black, ELV Dimming	★	1 90096 03678 3
■ LC06830WTE	600lm, 3000K (CRI 80), Matte White, ELV Dimming	★	1 90096 03762 9
■ LC10830BKTE	1000lm, 3000K (CRI 80), Matte Black, ELV Dimming	★	1 90096 03679 0
■ LC10930WTECW	1000lm, 3000K (CRI 90) Crisp White, Matte White, ELV Dimming	★	1 90096 03763 6
■ LC10930BKTE	1000lm, 3000K (CRI 90), Matte Black, ELV Dimming	★	1 90096 03166 5
■ LC10930WTE	1000lm, 3000K (CRI 90), Matte White, ELV Dimming	★	1 90096 03165 8
Track Head with Juno Adapter			
■ LCJ10830BKTE	1000lm, 3000K (CRI 80), Matte Black	★	1 90906 02098 8
■ LCJ10830WTE	1000lm, 3000K (CRI 80), Matte White	★	1 90906 02097 1
■ LCJ10930BKTECW	1000lm, 3000K (CRI 90) Crisp White, Matte Black	★	1 90906 02112 1
■ LCJ10930WTECW	1000lm, 3000K (CRI 90) Crisp White, Matte White	★	1 90906 02111 4
■ LCJ10930BKTE	1000lm, 3000K (CRI 90), Matte Black	★	1 90096 03379 9
■ LCJ10930WTE	1000lm, 3000K (CRI 90), Matte White	★	1 90096 03378 2
Accessories			
■ LC10AHBK	Accessory holder, Matte Black		1 90096 02886 3
■ LC10FR	Diffusion Film, Frosted Etched		1 90096 02901 3
■ LC10LS	Diffusion Film, Linear Spread		1 90096 02902 0
■ LC10SY	Diffusion Film, Symmetrical Spread		1 90096 02899 3
■ LC10SNBK	Snoot, Matte Black		1 90096 01474 3
■ LC10SNWH	Snoot, Matte White		1 90096 01473 6
■ LLMRF	Reflector, Flood (36°)		1 90096 02884 9
■ LLMRNS	Reflector, Narrow Spot (11°/12°)		1 90096 02881 8
■ LLMRS	Reflector, Spot (18°)		1 90096 02882 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Diffusion Film



LC10SNBK



LC10SNWH



LLMRS



Product	Description / Features		UPC
OmniSpot LED Track Heads (20)		Track Head with Lightolier Adapter	
■ LC20830BKTE	2000lm, 3000K (CRI 80), Matte Black, ELV Dimming	★	6 62057 97052 3
■ LC20930BKTECW	2000lm, 3000K (CRI 90) Crisp White, Matte Black, ELV Dimming	★	1 90096 04111 4
■ LC20930WTECW	2000lm, 3000K (CRI 90) Crisp White, Matte White, ELV Dimming	★	1 90096 03764 3
■ LC20930BKTE	2000lm, 3000K (CRI 90), Matte Black, ELV Dimming	★	1 90096 03189 4
■ LC20930WTE	2000lm, 3000K (CRI 90), Matte White, ELV Dimming	★	1 90096 02815 3
Track Head with Juno Adapter			
■ LCJ20830BKTE	2000lm, 3000K (CRI 80), Matte Black	★	1 90906 02118 3
■ LCJ20830WTE	2000lm, 3000K (CRI 80), Matte White	★	1 90906 02117 6
■ LCJ20930BKTECW	2000lm, 3000K (CRI 90) Crisp White, Matte Black	★	1 90906 02130 5
■ LCJ20930WTECW	2000lm, 3000K (CRI 90) Crisp White, Matte White	★	1 90906 02129 9
■ LCJ20930BKTE	2000lm, 3000K (CRI 90), Matte Black	★	1 90096 03384 3
■ LCJ20930WTE	2000lm, 3000K (CRI 90), Matte White	★	1 90096 03383 6
Accessories			
■ LC20AHBK	Accessory holder, Matte Black		1 90096 02889 4
■ LC20AHWH	Accessory holder, Matte White		1 90096 02888 7
■ LC20FR	Diffusion Film, Frosted Etched		1 90096 02905 1
■ LC20LS	Diffusion Film, Linear Spread		1 90096 02906 8
■ LC20SF	Diffusion Film, Soft Focus		1 90096 02904 4
■ LC20SY	Diffusion Film, Symmetrical Spread		1 90096 02903 7
■ LC20SNBK	Snoot, Matte Black		1 90096 01477 4
■ LC20SNWH	Snoot, Matte White		1 90096 01476 7
OmniSpot LED Recessed Multiple		2 Head Frame & Fixture	
■ LCRM10H2	Frame, 2 Head (2" Cylinders)	★	1 90096 07211 8
■ LCRM10830H2WHZ10U	Fixture, 2 Head (2" Cylinders), 1000lm, 3000K (CRI 80), Flange, 0-10V 1% Dimming, 120/277V	★	1 90096 07388 7
■ LCRM10930CWH2WHZ10U	Fixture, 2 Head (2" Cylinders), 1000lm, 3000K (CRI 90) Crisp White, Flange, 0-10V 1% Dimming, 120/277V	★	1 90096 07441 9
3 Head Frame & Fixture			
■ LCRM10H3	Frame, 3 Head (2" Cylinders)	★	1 90096 07212 5
■ LCRM10830H3WHZ10U	Fixture, 3 Head (2" Cylinders), 1000lm, 3000K (CRI 80), Flange, 0-10V 1% Dimming, 120/277V	★	1 90096 07389 4
■ LCRM10930CWH3WHZ10U	Fixture, 3 Head (2" Cylinders), 1000lm, 3000K (CRI 90) Crisp White, Flange, 0-10V 1% Dimming, 120/277V	★	1 90096 07442 6
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
Conventional Track Heads		Basic Track Head	
● 6320WH	Basic Track Head Universal Lytespot White	★	6 24563 01997 4
PAR Ring			
● 6278WH	50W PAR20 White	★	7 84197 62780 5
● 6282WH	75W PAR30S White	★	6 24563 06025 9
■ 6284	250W PAR38 Max White	★	7 84197 76284 1
● 9030NBK	PAR30 Black	★	6 62057 90590 7
● 9030NWH	PAR30 White	★	6 62057 90591 4
● 9038NBK	PAR38 Black	★	6 62057 90593 8
● 9038NWH	PAR38 White	★	6 62057 90594 5
● 55215WH	250W PAR38 White	★	6 24563 06024 2
● 55241WH	75W PAR30S Front Relamp White	★	6 24563 03005 4
● 55242WH	250W PAR38 Front Relamp White	★	6 24563 03007 8
LyteSpan Track Head Accessories			
■ AL2HC	2" Hex Cell Louver		7 84197 11611 8
■ AL25HC	2.5" Hex Cell Louver		7 84197 16269 6
■ AL3HC	3.75" Hex Cell Louver		7 84197 16293 1
■ AL4HC	6" & 7" Hex Cell Louver for Adjustable Track Head		7 84197 11606 4
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			






Garage & Canopy LED Dual Select | Pg. 75

Commercial Outdoor Lighting

Outdoor general purpose lighting

The brands feature contractor-friendly outdoor lighting solutions that help make the most of your time and budget. Readily available and dependable luminaires suitable for a range of commercial application types.



LWL Wall Light LED



SlimFlood Dual Select

Site & Area, Garage & Canopy 72

LED Quick Selection Guide	73
EcoForm Small	74
Area Light Gen. 2 Selectable Wattage	75
Post Top Selectable Wattage	75
Garage & Canopy Dual Select	75

Floods & Wall Packs 76

LED Quick Selection Guide	77
SlimFlood Dual Select	78
LWL Wall Light LED	78
SWL Square Wall Light LED.	78
Tall Wall Pack LED	78
Wall Pack Dual Select.	78
Adjustable Slim Wall Pack Selectable	78
LytePro LED Wall Sconce	78

Special Application 80


RoughLyte LED	80
-------------------------	----

Landscape 81

FlexScape BL9 LED	81
FlexScape IL9 LED	81
FlexScape MUL4 LED	81
FlexScape Low Voltage Transformer	81
BL5016 Micro Accent.	81

Site & Area Garage & Canopy

Site & Area, Garage & Canopy LED Quick Selection Guide



Illuminate parking lots and canopies

Choose Keene by Signify for a complete selection
of commercial outdoor lighting products.
Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.



KEENE

Click images to
view eCatalogue
(Detailed brochures,
bulletins, spec
sheets, IES files, etc.)



	Gardco EcoForm Small	Area Light Gen. 2 Selectable Wattage	Post Top Selectable Wattage	Garage & Canopy LED Dual Select	
Product Family					
Page Reference	pg. 74	pg. 75	pg. 75	pg. 75	
Quick Ship Service	■	●	●	●	
Budget / Grade	Performance / Better	Value / Good	Value / Good	Value / Good	
Finish / Spec & Performance	Finish	Black / Bronze / Medium Grey	Bronze	Black	
	Wattage	106W / 159W / 206W	Field Adjustable Wattage Selector (FAWS) 46-71W / 96-142W	Field Adjustable Wattage Selector (FAWS) 20-53W	Field Adjustable Wattage Selector (FAWS) 28-60W / 70-90W
	Lumen Output Range	13,388-27,526	7,609-22,590	2,047-6,308	4,100-12,400
	Efficacy	up to 136	up to 172	up to 129	up to 150
	Distribution	Type 3, 4, 5	Type 3, 4	Type 3, 5	Type 5 Symmetric
	Color Temperature	4000K	4000K	3000K / 4000K	Selectable 3000K / 4000K / 5000K
	CRI	70	70	70	70
Voltage	120-277V	120-277V / 347-480V	120-347V	120-347V	
Ratings & Certification	IP Rating	IP65	IP65	IP65	
	DLC Listing	Premium	Premium	Standard	Premium
	cULus Listed	✓	✓	✓	✓
	Lifetime (L70)	up to 100,000 hours	up to 100,000 hours	up to 54,000 hours	up to 60,000 hours
Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.				

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

✓ Standard Feature * ♦ Spec Ready / Additional Options Available, see spec sheet for details



Product	Description / Features		UPC
EcoForm Small			
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18811 6
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01806 2
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01807 9
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18812 3
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01808 6
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01809 3
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18784 3
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01810 9
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01811 6
159W, 48 LED			
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18783 6
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01812 3
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01813 0
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18440 8
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01814 7
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01815 4
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18458 3
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01816 1
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01817 8
206W, 64 LED			
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18377 7
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01818 5
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01819 2
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18378 4
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01820 8
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01821 5
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18550 4
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01822 2
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01823 9
Internal House Side shield			
■ HIS-32-H	Internal House Side shield (Standard optic orientation) for 32 LEDs (2 modules)		1 90096 15919 4
■ HIS-48-H	Internal House Side shield (Standard optic orientation) for 48 LEDs (2 modules)		1 90096 15920 0
■ HIS-64-H	Internal House Side shield (Standard optic orientation) for 64 LEDs (2 modules)		1 90096 15921 7
Retrofit Arm mount kit			
■ RS-ECF-RAM-G2-BK	Retrofit Arm mount kit, Black		1 90096 19133 8
■ RS-ECF-RAM-G2-BZ	Retrofit Arm mount kit, Bronze		1 90096 19132 1
■ RS-ECF-RAM-G2-DGY	Retrofit Arm mount kit, Dark Grey		1 90096 15908 8
■ RS-ECF-RAM-G2-MGY	Retrofit Arm mount kit, Medium Grey		1 90096 15509 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
Area Light Gen. 2 Selectable Wattage			
● AL70-NW-G2-AR-3-8-FAWS-BZ	4000K, Type 3, Field-adjustable wattage, 50-57-65-72W, 120-277V	S-ZLIVG8	1 90096 18055 4
● AL70-NW-G2-AR-3-6-FAWS-BZ	4000K, Type 3, Field-adjustable wattage, 50-57-65-72W, 347-480V	PLZABA9BN8X7	1 90096 18057 8
● AL70-NW-G2-AR-4-8-FAWS-BZ	4000K, Type 4, Field-adjustable wattage, 50-57-65-72W, 120-277V	S-RGNVW4	1 90096 18059 2
● AL70-NW-G2-AR-4-6-FAWS-BZ	4000K, Type 4, Field-adjustable wattage, 50-57-65-72W, 347-480V	PL0D6LZUHINA	1 90096 18061 5
96-142W Field Adjustable Wattage Selector (FAWS)			
● AL150-NW-G2-AR-3-8-FAWS-BZ	4000K, Type 3, Field-adjustable wattage, 95-115-130-145W, 120-277V	S-6BUKAR	1 90096 18056 1
● AL150-NW-G2-AR-3-6-FAWS-BZ	4000K, Type 3, Field-adjustable wattage, 95-115-130-145W, 347-480V	PLSOLWJ3RNVN	1 90096 18058 5
● AL150-NW-G2-AR-4-8-FAWS-BZ	4000K, Type 4, Field-adjustable wattage, 95-115-130-145W, 120-277V	S-26RBEY	1 90096 18060 8
● AL150-NW-G2-AR-4-6-FAWS-BZ	4000K, Type 4, Field-adjustable wattage, 95-115-130-145W, 347-480V	PL38DXHUB7V	1 90096 18062 2
Accessory			
● AL-SF-G2-BZ	Area Light Slip Fitter Mounting Accessory		1 90096 18063 9
● AL-RP-G2-BZ	Area Light Slip Fitter Mounting Accessory		1 90096 18200 8
Post Top Selectable Wattage			
● PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK	3000K, Type 3, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	PL93CH3J24MU	7 83352 02606 4
● PT50-WW-G1-T2-5-HV3-FAWS-TLRPC-BK	3000K, Type 5, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	PL3KYCJH4R0Z	7 83352 02607 1
● PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK	4000K, Type 3, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	PL15T6Z3FCOE	7 83352 02608 8
● PT50-NW-G1-T2-5-HV3-FAWS-TLRPC-BK	4000K, Type 5, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	PL0ASEYVWBL1	7 83352 02609 5
Garage & Canopy LED Dual Select			
● GC60-SCT-G2-SM-5-10-BZ	Garage & Canopy Square Selectable Wattage and CCT 28-40-60W / 3000K, 4000K, 5000K	PLVXWEOIQDCS	1 90096 13131 0
● GC90-SCT-G2-SM-5-10-BZ	Garage & Canopy Square Selectable Wattage and CCT 70-80-90W / 3000K, 4000K, 5000K	PLWNEI9VD4T5	1 90096 13132 7
● GCR60-SCT-G1-SM-5-10-BZ	Garage & Canopy Round Selectable Wattage and CCT 28-40-60W / 3000K, 4000K, 5000K	PL29WAS5ASGM	1 90096 18195 7
● GCR90-SCT-G1-SM-5-10-BZ	Garage & Canopy Round Selectable Wattage and CCT, 70-80-90W / 3000K, 4000K, 5000K	PLFS8QAG3NGG	1 90096 18196 4
Accessory			
● GC60/90-MH10	Garage & Canopy Dual Select Controller		1 90096 13159 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

Create safe and functional outdoor spaces

Choose Keene by Signify for a complete selection of commercial outdoor lighting products. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

KEENE

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)

Product Family

Page Reference

Quick Ship Service

Budget / Grade

Finish / Spec & Performance	Finish	Bronze	Bronze	Bronze	Bronze	Bronze	Brown Grey	Bronze, Dark Grey White*		
	Wattage	Field Adjustable Wattage Selector (FAWS) 15W 15-25-35W 15-35-60W 60-80-100W 100-120-150W 120-150-205W 205-255-300W	12W	13W	20W	Field Adjustable Wattage Selector (FAWS) 28-60, 70-100W	Field Adjustable Wattage Selector (FAWS) 15-20-25W 45-60-75W	10W	30W	70W
	Lumens (lm)	2,175-43,500	1,104	1,178	2,277	3,860-12,800	1800-9000	1,050	2,065-4,629	6,472-9,637
	Efficacy (lm/W)	up to 145	up to 90	up to 93	up to 120	up to 145	upto 120	up to 108	up to 104	up to 114
	Distribution	-	-	-	Type 4	-		Type 2	Type 3, 4	Type 3, 4
	Color Temperature	Selectable 3000K 4000K 5000K	3000K	3000K	4000K	Selectable 3000 4000 5000K	Selectable 3000 4000 5000K	3000K 4000K	3000K 4000K	3000K 4000K
	CRI	70	80	80	70	70	70	70	70	70
	Voltage	120-347V	120V	120V	120-277V 347V	120-347V	120-347V	120-277V	120-277V 347-480V	120-277V 347-480V
Technology / Certification	Photocell	✓	✓	✓	✓	✓		✓	✓	✓
	IP Rating	IP65			IP65/IP66	IP65	IP65	IP65	IP65	IP65
	DLC Listing	Premium			Standard	Standard	Premium	Standard	Standard	Standard
	cULus Listed		✓	✓	✓	✓				
	cETLus Listed	✓					✓	✓	✓	✓
	Lifetime (L70)	up to 50,000 hours	up to 48,000 hours	up to 48,000 hours	up to 102,000 hours	up to 54,000 hours	up to 50,000 hours	up to 60,000 hours	up to 54,000 hours	up to 54,000 hours
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.								

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ♦ Spec Ready / Additional Options Available, see spec sheet for details



Product	Description / Features		UPC
SlimFlood Dual Select			
 SF15-SCT-K-G2-10-BZ	15W, 3000K / 4000K / ~5000K, 120-347V, Knukle Mount	S-XDAS9R	1 90096 19600 5
 SF15-SCT-Y-G2-10-BZ	15W, 3000K / 4000K / ~5000K, 120-347, Yoke Mount	S-XDAS9R	1 90096 19601 2
 SF35-SCT-K-G2-10-PCB-BZ	15-25-35W, 3000K / 4000K / 5000K, 120-347V, Knukle Mount, Photocell	S-1T286U	1 90096 19602 9
 SF35-SCT-Y-G2-10-PCB-BZ	15-25-35W, 3000K / 4000K / 5000K, 120-347V, Yoke Mount, Photocell	S-1T286U	1 90096 19603 6
 SF60-SCT-K-G2-10-PCB-BZ	15-35-60W, 3000K / 4000K / 5000K, 120-347V, Knukle Mount, Photocell	S-746YXP	1 90096 19604 3
 SF60-SCT-Y-G2-10-PCB-BZ	15-35-60W, 3000K / 4000K / 5000K, 120-347V, Yoke Mount, Photocell	S-746YXP	1 90096 19605 0
 SF100-SCT-S-G2-10-PCB-BZ	60-80-100W, 3000K / 4000K / 5000K, 120-347V, Slipfitter, Photocell	S-RENDJO	1 90096 19606 7
 SF100-SCT-T-G2-10-PCB-BZ	60-80-100W, 3000K / 4000K / 5000K, 120-347V, Trunnion Mount, Photocell	S-RENDJO	1 90096 19607 4
 SF150-SCT-S-G2-10-PCB-BZ	100-120-150W, 3000K / 4000K / 5000K, 120-347V, Slipfitter, Photocell	S-M8YAEV	1 90096 19608 1
 SF150-SCT-T-G2-10-PCB-BZ	100-120-150W, 3000K / 4000K / 5000K, 120-347V, Trunnion Mount, Photocell	S-M8YAEV	1 90096 19609 8
 SF205-SCT-S-G2-10-BZ	120-150-205W, 3000K / 4000K / 5000K, 120-347V, Slipfitter	S-DT894A	1 90096 19610 4
 SF205-SCT-T-G2-10-BZ	120-150-205W, 3000K / 4000K / 5000K, 120-347V, Trunnion Mount	S-DT894A	1 90096 19611 1
 SF300-SCT-S-G2-10-BZ	205-255-300W, 3000K / 4000K / 5000K, 120-347V, Slipfitter	S-F10Y78	1 90096 19612 8
 SF300-SCT-T-G2-10-BZ	205-255-300W, 3000K / 4000K / 5000K, 120-347V, Trunnion Mount	S-F10Y78	1 90096 19613 5
Accessory			
 SF205-300-PCB	120-150-205-255-300W, Photocell		1 90096 1914 2
LWL Wall Light LED			
 LWL-WW-G2-PCB-1-BZ	12W, 3000K (CRI 80), 120V, Bronze, Button Photocell installed		7 83352 02576 0
SWL Square Wall Light LED			
 SWL-WW-G1-PCB-1-BZ	13W, 3000K (CRI 80), 120V, Bronze, Button Photocell installed		7 83352 02577 7
Tall Wall Pack LED			
 TW20-NW-G1-8-BZ	20W, 4000K (CRI 70), 120-277V, Bronze	STANDARD	7 83352 02405 3
 TW20-NW-G1-PCB-1-BZ	20W, 4000K (CRI 70), 120, Bronze, Button Photocell installed	STANDARD	6 24563 34013 9
Wall Pack Dual Select			
 WP60-SCT-G2-10-BZ	70W/80W/90W/100W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	PLS3A95FM210	1 90096 13133 4
 WP100-SCT-G2-10-BZ	28W/40W/60W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	PLDEKXDYR83Y	1 90096 13134 1
Adjustable Slim Wall Pack Selectable			
 ASW25-SCT-G1-10-BW	15W/20W/25W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	S-L10Z13	1 90096 18205 3
 ASW75-SCT-G1-10-BW	45W/60W/75W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	S-W278UM	1 90096 18206 0
LytePro LED Wall Sconce			
7 LED Small Wall Sconce, 10W			
 LPW7-G3-8-BZ	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Bronze	STANDARD	6 22252 81385 8
 LPW7-G3-8-DGY	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Dark Gray	STANDARD	6 22252 81384 1
 LPW7-10-NW-G3-2-UNV-BK	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Black	STANDARD	1 90096 11725 3
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
16 LED Medium Wall Sconce, 30W			
 LPW16-G3-8-BZ	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Bronze	STANDARD	6 22252 81387 2
 LPW16-G3-8-DGY	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Dark Gray	STANDARD	6 22252 81386 5
 LPW16-30-NW-G3-3-UNV-BK	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Black	STANDARD	1 90096 11838 0
 LPW16-30-NW-G3-3-HVU-BK	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Black	STANDARD	
 LPW16-30-NW-G3-3-HVU-BZ	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Bronze	STANDARD	
 LPW16-30-NW-G3-3-HVU-DGY	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Dark Grey	STANDARD	1 90096 11841 0
32 LED Large Wall Sconce, 70W			
 LPW32-G3-8-BZ	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Bronze	STANDARD	6 22252 81389 6
 LPW32-G3-8-DGY	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Dark Grey	STANDARD	6 22252 81388 9
 LPW32-70-NW-G3-3-UNV-BK	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Black	STANDARD	1 90096 11878 6
 LPW32-70-NW-G3-3-HVU-BK	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Black	STANDARD	1 90096 11883 0
 LPW32-70-NW-G3-3-HVU-BZ	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Bronze	STANDARD	
 LPW32-70-NW-G3-3-HVU-DGY	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Dark Grey	STANDARD	1 90096 11881 6
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
RoughLyte LED			
 VCXL-14-NW-G1-8	RoughLyte LED, Ceiling 4" box mounted, 14W, 4000K (CRI 70), 120-277V	STANDARD	7 83352 02477 0
 VWXL-14-NW-G1-8	RoughLyte LED, Wall 4" box mounted, 14W, 4000K (CRI 70), 120-277V	STANDARD	7 83352 02478 7
Photocontrols			
 P105A	120V Button Photocell	STANDARD	1 90096 00183 5
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)			



Product	Description / Features	UPC
FlexScape BL9 LED		
 BL9DW-AS7	Low Voltage 9W Bullet Lighting, 3000K, Black, Stake Mount	7 83352 02080 2
 BL9DW-HS7	Low Voltage 9W Bullet Lighting, 3000K, Bronze, Stake Mount	7 83352 02081 9
FlexScape IL9 LED		
 IL9DW-A	Low Voltage 9W In-ground Lighting, 3000K, Black	7 83352 02158 8
FlexScape MUL4 LED		
 MUL4-AS7LED2W	Low Voltage 2W Path Lighting, 3000K, 12V, Black, Stake Mount	7 83352 02046 8
 MUL4-HS7LED2W	Low Voltage 2W Path Lighting, 3000K, 12V, Bronze, Stake Mount	7 83352 02048 2
FlexScape Low Voltage Transformer		
 TC152-12TP	Voltage Control Switch (Low =11.5V, High=12.5V), Line voltage amperage draw: 150VA = 0.9 AMP, integral timer and photocell, 50/60Hz input	7 83352 01504 4
BL5016 Micro Accent		
 BL5016-AS7	50W MR16, 3000K, 12V, Black, Stake Mount	7 83352 00415 4
 BL5016-HS7	50W MR16, 3000K, 12V, Bronze, Stake Mount	7 83352 00426 0
 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)		





Connected Lighting Controls

Make the leap from smart lighting to super smart lighting with the Interact scalable system with integrated wireless sensors that make connectivity simple.

Connectivity is everywhere, and it is the future and key to unlock your smart building potential. It is unknown territory for some though and can often be perceived as complex.

- No restrictions on light points or building size
- Just add a gateway anytime and unlock more capabilities, no need to change or swap sensors
- Future proof your design and lay the right foundation
- Easy point-2-point commissioning sequence enables the installer to be more in control

- You can start simple and lay the right foundation and scale up to the next tier to access more benefits by adding a gateway
- Unlock super savings and occupant comfort through adaptive dimming and dwell time features
- Get a complete view of the 3 tiers and compatible products at: www.interact-lighting.com

Interact scalable controls: Smart wireless devices for code and rebate compliancy and to help maximize energy savings

- UID8465/10 Scene Selector and Zigbee Green Power Switch
- SWS 200 wireless scene selector to recall custom scenes
- System Bridge Accessory (SBA) for 0-10V and phase dimming integration
- RFSR20 wireless switch relay, ideal to control plug loads or integrate with 0-10V fixtures
- Optional IRT9015 handheld remote to help fastrack the commissioning process and minimize on-site setup time.



FluxStream LED Strip (FSS) | Pg. 21



UniFrame | Pg. 45



FluxPanel LED Gen. 2 (FPZ) | Pg. 26



Philips EvoKit Click | Pg. 85



MasterConnect PAR Lamps | Pg. 86



MasterConnect InstantFit LEDtube | Pg. 87

Product	Description / Features		UPC
Interact			
● SWS200	Philips Smart Wireless Wall Scene Switch (4 button)	NLC	046677559144
● RFSR20	Interact Ready RF Switch Relay		046677584559
● UID8465/10	Zigbee Green Power Switch and Scene Selector		
● SBAZ10-CS	Interact System Bridge 0-10V Control Module	NLC	
● IRT9015	Interact Retrofit Commissioning Device (Remote)	NLC	87 18696 82759 8
● LCN1840/05	Interact Wireless Gateway (North America)	NLC	046677476335
● OCC SENSOR IA CM WH 10/1	Philips Smart Wireless Sensor, OCC SENSOR IA CM IP42 WH 10/1	NLC	046677476182
● LCN3120/05	Philips Smart Wireless Sensor, OCC-DL Sensor IA CM IP65 WH (presence + daylight detection)	NLC	046677558895
● LCN3110/05	Philips Smart Wireless Sensor, OCC Sensor IA CM IP65 WH		046677558888
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



SWS 200



UID8465/10



SBAZ10-CS



IRT9015



LCN1840/05



Occupancy Sensor



LCN3120/05

MasterConnect InstantFit LEDtube | Pg. 87

Philips EvoKit Click

LED Lamps & Retrofits

Philips MasterClass and CorePro tiers are designed to help professional lighting customers more quickly and easily identify the right product to fit any project or budget.

Philips MasterClass

For every project where exceptional, high quality lighting is required. The MasterClass line of LEDs meets or exceeds applicable industry energy efficiency requirements, featuring improved lifespan over traditional incandescent bulbs and warranties with broad product ranges.

Philips CorePro

For every job requiring efficiency, value and uncompromising quality, these LED lamps are perfect for basic lighting needs across a wide range of applications. The CorePro line of LEDs meet industry efficiency standards and minimize maintenance costs for quick payback.

Product	Product Name	Description / Features	UPC
Philips EvoKit Click			
◆ 114157	EvoKit CLKE 2x2 32L 24W 835 UNV SWZCS P1	2×2', 3200lm, 3500K (CRI 80), UNV, Interact Ready	781087167816
◆ 114140	EvoKit CLKE 2x2 32L 24W 840 UNV SWZCS P4	2×2', 3200lm, 4000K (CRI 80), UNV, Interact Ready	781087167809
◆ 121400	EvoKit CLKE 2x4 42L 29W 835 UNV SWZCS P1	2×4', 4200lm, 3500K (CRI 80), UNV, Interact Ready	781087167847
◆ 121392	EvoKit CLKE 2x4 42L 29W 840 UNV SWZCS P4	2×4', 4200lm, 4000K (CRI 80), UNV, Interact Ready	781087167830
Philips EvoKit High Efficiency G5			
◆ 113977	EvoKit HE 2x2 31L 20W 835 UNV SWZCS G5	2×2', 3100lm, 3500K (CRI 80), UNV, Interact Ready	781087167649
◆ 113985	EvoKit HE 2x2 31L 20W 840 UNV SWZCS G5	2×2', 3100lm, 4000K (CRI 80), UNV, Interact Ready	781087167656
◆ 113993	EvoKit HE 2x4 42L 26W 835 UNV SWZCS G5	2×4', 4200lm, 3500K (CRI 80), UNV, Interact Ready	781087167663
◆ 114009	EvoKit HE 2x4 42L 26W 840 UNV SWZCS G5	2×4', 4200lm, 4000K (CRI 80), UNV, Interact Ready	781087167670

● Stock Ready (2-Day Quick Ship)

■ Design Ready (10-Day Quick Ship)

◆ Spec Ready (Ships in 4-6 weeks)



EvoKit Click



EvoKit G5



Product	Product Name	Description / Features		UPC
MasterConnect PAR Lamps				
● 570663	4.4PAR16S/PER/930/F40/DIM/G/T20 4/1PF	PAR16L, 4.4W, 400lm, 3000K (CRI 90), 40°, 120V, Dimming		046677570668
● 568089	5.5PAR20/LED/F40/930/DIM/G/T20 6/1FB	PAR20, 5.5W, 500lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677568085
● 568097	5.5PAR20/LED/F40/940/DIM/G/T20 6/1FB	PAR20, 5.5W, 500lm, 4000K (CRI 80), 40°, 120V, Dimming	★	046677568092
● 567981	8.5PAR30L/LED/930/F40/DIM/GULW/T20 6/1FB	PAR30L, 8.5W, 850lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677567989
● 567999	8.5PAR30L/LED/940/F40/DIM/GULW/T20 6/1FB	PAR30L, 8.5W, 850lm, 4000K (CRI 80), 40°, 120V, Dimming	★	046677567996
● 553602	8PAR30L/MC/930/F25/IA/120V 6/1FB	PAR30L, 850lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677553609
● 553636	8PAR30L/MC/930/F40/IA/120V 6/1FB	PAR30L, 850lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677553630
● 553669	8PAR30S/MC/930/F25/IA/120V 6/1FB	PAR30S, 850lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677553661
● 553693	8PAR30S/MC/930/F40/IA/120V 6/1FB	PAR30S, 850lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677553692
● 567909	10PAR38/LED/930/F40/DIM/GULW/T20 6/1FB	PAR38, 10W, 900lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677567903
● 567917	10PAR38/LED/940/F40/DIM/GULW/T20 6/1FB	PAR38, 10W, 900lm, 4000K (CRI 80), 40°, 120V, Dimming	★	046677567910
● 555789	13PAR38/MC/930/F25/IA/120V 6/1FB	PAR38, 13W, 1200lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677555788
● 555813	13PAR38/MC/930/F40/IA/120V 6/1FB	PAR38, 13W, 1200lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, <i>Interact Ready</i>	★	046677555818
CorePro LED Lamps				
● 550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	A19, 8.8W, 800lm, 2700K (CRI 90), Dimming, Plastic, Frosted	★	046677550431
● 561019	16A19/PER/950/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 5000K (CRI 90), Dimming, Plastic, Frosted	★	046677561017
● 545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	A19, 8.8W, 800lm, 4000K (CRI 90), Dimming, Plastic, Frosted	★	046677545895
● 561068	16A19/PER/927/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 2700K (CRI 90), Dimming, Plastic, Frosted	★	046677561062
● 561076	16A19/PER/930/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 3000K (CRI 90), Dimming, Plastic, Frosted	★	046677561079
● 561456	16A19/PER/940/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 4000K (CRI 90), Dimming, Plastic, Frosted	★	046677561451
● 545905	7.2BR30/PER/930/P/E26/DIM 6/1FB T20	BR30, 7.2W, 650lm, 3000K (CRI 90), Dimming	★	046677545901
● 553909	8.8BR40/PER/927/P/E26/DIM 6/1FB T20	BR40, 8.8W, 800lm, 2700K (CRI 90), Dimming	★	046677553906
● 468140	4GU10/LED/930/F35/DIM/G/120V T20 10/1	GU10, 4W, 380lm, 3000K (CRI 90), 35°, 120V, Dimming	★	046677468149
● 573899	7MR16/LED/830/F35/DIM 12V 10/1FB	MR16, 7W, 515lm, 3000K (CRI 82), 35°, 120V, Dimming	★	046677573898
Ceramalux High Pressure Sodium (HPS) Lamps				
● 467241	SON 100W E39 ED75 CL SL/12	Mogul Base (E39), 9400lm, 2100K, 12pk		046677467241
● 467233	SON 150W E39 ED75 CL SL/12	Mogul Base (E39), 15800lm, 2100K, 12pk		046677467234
● 467217	SON 250W E39 ED58 CL SL/12	Mogul Base (E39), 27000lm, 2100K, 12pk		046677467210
● 467373	SON 400W E39 ED58 CL SL/12	Mogul Base (E39), 50000lm, 2100K, 12pk		046677467371
● 368837	C1000S52/ALTO	Mogul Base (E39), 130000lm, 2100K, 6pk		046677368838
Metal Halide (MH) Lamps				
● 287334	MH175/U 12PK	Mogul Base (E39), 14000lm, 4300K, 12pk		046677287337
● 274845	MH250/U 12PK	Mogul Base (E39), 21000lm, 4000K, 12pk		046677274849
● 426023	MH400/U/ED28 12PK	Mogul Base (E39), 36000lm, 4000K, 12pk		046677426026
● 274498	MH400/U 6PK	Mogul Base (E39), 39000lm, 3900K, 6pk		046677274498
● 415224	MH1000/U 6PK	Mogul Base (E39), 110000lm, 4000K, 6pk		046677415228

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship) ◆ Spec Ready (Ships in 4-6 weeks)



Product	Product Name	Description / Features		UPC
MasterConnect InstantFit LEDtube				
■ 547299	14T8/48-835/IF20/MC IA 10/1	T8, 14W, 4', 2000lm, 3500K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677547295
■ 547307	14T8/48-840/IF21/MC IA 10/1	T8, 14W, 4', 2100lm, 4000K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677547301
■ 547315	14T8/48-850/IF21/MC IA 10/1	T8, 14W, 4', 2100lm, 5000K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677547318
● 562736	14.5T8/48-835/MF20/MC IA 10/1	T8, 14.5W, 4', 2000lm, 3500K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677562731
● 562744	14.5T8/48-840/MF21/MC IA 10/1	T8, 14.5W, 4', 2100lm, 4000K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677562748
● 562751	14.5T8/48-850/MF21/MC IA 10/1	T8, 14.5W, 4', 2100lm, 5000K (CRI 83), Wireless Dimming, <i>Interact Ready</i>	DLC	046677562755
MasterClass InstantFit LEDtube				
● 467142	24T5HO/46-840/IF35/P/DIM 10/1	T5HO, 24W, 4', 3500lm, 4000K (CRI 82)	DLC	046677467142
● 467159	24T5HO/46-850/IF35/P/DIM 10/1	T5HO, 24W, 4', 3500lm, 5000K (CRI 82)	DLC	046677467159
● 541821	7T8/MAS/24-835/IF10/P 10/1	T8, 7W, 2', 1050lm, 3500K (CRI 82)	DLC	046677541828
● 541839	7T8/MAS/24-840/IF11/P 10/1	T8, 7W, 2', 1150lm, 4000K (CRI 82)	DLC	046677541835
● 541847	7T8/MAS/24-850/IF11/P 10/1	T8, 7W, 2', 1150lm, 5000K (CRI 82)	DLC	046677541822
● 539866	8.5T8/MAS/36-835/IF13/P/DIM 10/1	T8, 8.5W, 3', 1300lm, 3500K (CRI 82)	DLC	046677539863
● 539874	8.5T8/MAS/36-840/IF14/P 10/1	T8, 8.5W, 3', 1400lm, 4000K (CRI 82)	DLC	046677539870
● 539882	8.5T8/MAS/36-850/IF14/P/DIM 10/1	T8, 8.5W, 3', 1400lm, 5000K (CRI 82)	DLC	046677539887
MasterClass InstantFit Energy Advantage				
● 565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	T8, 8.9W, 4', 1500lm, 3500K (CRI 80)	DLC	0 46677 56559 6
● 565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	T8, 8.9W, 4', 1600lm, 4000K (CRI 80)	DLC	0 46677 56560 2
● 565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	T8, 8.9W, 4', 1600lm, 5000K (CRI 80)	DLC	0 46677 56561 9
CorePro InstantFit LEDtube				
● 553222	10T8/COR/48-835/IF15/G 10/1	T8, 10W, 4', 1500lm, 3500K (CRI 80)	DLC	046677553227
● 553230	10T8/COR/48-840/IF16/G/DIM 10/1	T8, 10W, 4', 1600lm, 4000K (CRI 80)	DLC	046677553234
● 553248	10T8/COR/48-850/IF16/G/DIM 10/1	T8, 10W, 4', 1600lm, 5000K (CRI 80)	DLC	046677553241
● 470104	14T8/COR/48-835/IF20/G 10/1	T8, 14W, 4', 2000lm, 3500K (CRI 82)	DLC	046677452759
● 470112	14T8/COR/48-840/IF21/G 10/1	T8, 14W, 4', 2100lm, 4000K (CRI 82)	DLC	046677453251
● 470120	14T8/COR/48-850/IF21/G 10/1	T8, 14W, 4', 2100lm, 5000K (CRI 82)	DLC	046677452483
CorePro UniversalFit LEDtube				
● 539972	16T8/LED/48-840/UF18/G 10/1	T8, 16W, 4', 1800lm, 4000K (CRI 80)		046677539979
Basic CorePro LEDtube MainsFit				
● 577775	14.5T8/BCP/48-840/MF18/G 25/1	T8, 14.5W, 4', 1800lm, 4000K (CRI 80), UL Type B		046677577773
● 577783	14.5T8/BCP/48-850/MF18/G 25/1	T8, 14.5W, 4', 1800lm, 5000K (CRI 80), UL Type B		046677577780
Linear Fluorescent Lamps				
● 135103	F54T5/850/HO/ALTO 40PK	T5 (Medium Bipin), 54W, 5000lm, 5000K (CRI 80), 40 Pack		046677135102
● 290833	54W/840 Min Bipin T5 HO ALTO UNP	T5 (Miniature Bipin), 54W, 5000lm, 4000K (CRI 80), 40 Pack		046677290832
● 479626	F32T8/TL941/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 4100K (CRI 90), 30 Pack		046677479626
● 479634	F32T8/TL950/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 5000K (CRI 90), 30 Pack		046677479633
● 479642	F32T8/TL965/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 6500K (CRI 90), 30 Pack		046677479640
● 479600	F32T8/TL935/ALTO 30PK	T8 (Medium Bipin), 32W, 2625lm, 3500K (CRI 90), 30 Pack		046677479602
● 281675	F32T8/TL835 PLUS ALTO 30PK	T8 (Medium Bipin), 32W, 2950lm, 3500K (CRI 85), 30 Pack		046677281670
● 281790	F32T8/TL841 PLUS ALTO HV 30PK	T8 (Medium Bipin), 32W, 2950lm, 4100K (CRI 85), 30 Pack		046677281793
● 281816	F32T8/TL850 PLUS ALTO HV 30PK	T8 (Medium Bipin), 32W, 2950lm, 5000K (CRI 82), 30 Pack		046677281816
● 423889	F40T12/CWSupreme/ALTO	T12 (Medium Bipin), 2600lm, 4100K, 30 Pack		046677423889
● 423194	F96T12/CW Supreme/ALTO 15PK	T12 (Single Pin), 5000lm, 4100K, 15 Pack		046677423193

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship) ◆ Spec Ready (Ships in 4-6 weeks)



LED Electronics

Advance has a long standing tradition of being the name in quality and reliable lighting components. With drivers, modules, and ballasts all under the same brand, Advance offers the latest in lighting innovations to give you the features you are looking for. We invite you to learn more about what sets us apart and why we continue to be a leader in lighting components.

Advance Express

Advance Express is more than just LED Drivers. It is a program for our distributor partners to help their customers address luminaire component failure in the field by providing an LED driver programming service.

Learn more online:
signify.com/AdvanceExpressCA



Xitanium (Indoor)



Xitanium (Outdoor)



Centium



Optanium



Core & Coil

Product	Product Name	Description / Features	UPC
Xitanium LED Driver		Indoor Linear Driver	
● 513051	XI020C056V054BST2M	XITANIUM 20W 0.1-0.56A 54V 0-10V INT-T	781087143186
● 528711	XI036C140V054BSM2	XITANIUM 36W G2 1.4A 54V 0-10V SSET 1%BE	781087166475
● 524199	XI050C140V054BST1M	XITANIUM 50W 1.4A 54V 0-10V 120-277V	781087155264
● 513168	XI075C200V054BST1M	XITANIUM 75W 0.1-2.0A 54V 0-10V INT-T	781087143223
		Outdoor and High Bay Driver	
● 514786	XI180C125V200BSF1M	XITANIUM 180W 0.1-1.25A 200V SS INT -F	781087142455
● 517714	XI095C275V054BSF1M	XITANIUM 95W 0.1-2.75A 54V SS INT -F 6KV	781087148167
		Outdoor Driver	
● 518241	XI055C180V054BSJ1M	XITANIUM 55W 0.1-1.8A SS 120-277V J 6KV	781087150474
		TLED Driver	
● 518712	IZT2P16TLEDSC35M	TLED 14 & 16.5W 120-277V	781087148631
● 518720	IZT4P16TLEDSC35M	TLED 14 & 16.5W 120-277V	781087148662
Centium Ballasts		T8 Instant Start	
● 196873	ICN2P32N35M	CENTIUM ELE BALLAST (2) F32T8 120-277V	781087069127
● 109140	ICN4P32N35M	CENTIUM ELE BALLAST (4) F32T8 120-277V	781087091517
		T5HO	
● 498394	ICN2S5490CN35M	CENTIUM ELE BALLAST (2) F54/T5HO 120-277V	781087124857
● 197871	HCN2S5490CWL35M	CENTIUM ELE BALLAST (2) F54T5/HO 347-480V	781087030660
● 119560	HCN4S5490C2LSG35M	CENTIUM ELE BALLAST (4) F54T5/HO 347-480V	781087047880
● 119404	ICN4S5490C2LSG35M	CENTIUM ELE BALLAST (4) F54T5HO 120-277V	781087047866
		T12 Slimline	
● 503144	ICN2P60N35M	CENTIUM ELE BALLAST (2) F96T12 120-277V	781087135556
		T12HO	
● 107136	ICN2S110SC35M	CENTIUM ELE BALLAST (2) F96T12/HO 120-277V	781087085288
Optanium Ballasts		T8 Instant Start	
● 107847	IOPA2P32N35M	OPTANIUM ELE BALLAST (2) F32T8 120-277V	781087086834
● 510644	GOPA2P32N35M	OPTANIUM ELE BALLAST (2) F32T8 347V	781087142394
● 498956	IOPA4P32N35M	OPTANIUM ELE BALLAST (4) F32T8 120-277V	781087115244
● 197970	GOPA4P32SC35M	OPTANIUM ELE BALLAST (4) F32T8 347V	781087073926
Core & Coil HID Ballasts		HPS	
● 192039	71A87A3001	CORE & COIL HID HPS BAL 1000W S52 120/277/347V KIT	781087037485
● 192005	71A82A1001D	CORE & COIL HID HPS BAL 250W S50 120/277/347V KIT	781087031230
● 192013	71A84A3001D	CORE & COIL HID HPS BAL 400W S51 120/277/347V KIT	781087034316
		MH	
● 192831	71A52A2001D	CORE & COIL HID MH BAL 70W M98/143 120/277/347V KIT	781087078150
● 192930	71A53A0001D	CORE & COIL HID MH BAL 100W M90/140 120/277/347V KIT	781087078167
● 191866	71A55A0001D	CORE & COIL HID MH BAL 175W M57 120/277/347V KIT	781087096543
● 191874	71A57A0001D	CORE & COIL HID MH BAL 250W M58 120/277/347V KIT	781087098233
● 191890	71A60A1001D	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	781087096659
● 191916	71A65A2001	CORE & COIL HID MH BAL 1000W M47 120/277/347V KIT	781087021958

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

Brand Line Card

Signify proudly markets the best lighting brands in the world.

IoT Platform	Lamps & Controls	Electronics	Specialty
			
A secure IoT platform with software applications that deliver benefits to professional customers across a variety of business verticals.	Global lighting leader in LED and conventional lamps for every application.	Offering a full range of reliable and robust ballasts, LED drivers and lighting components for the electrical wholesaler and OEM channels.	Innovative emergency lighting components / unit equipment designed for safety.
interact-lighting.com	lighting.philips.ca	signify.com/advance	bodine.com


Luminaires	Indoor	Day-Brite		
				
Genlyte Solutions is a collection of industry-leading luminaire brands within Signify North America. These brands include Lightolier, Day-Brite CFI, Ledalite, Lumec, Hadco, Gardco, Keene and Alkco.	Germicidal UV luminaires with UV-C lamp systems have the power to neutralize harmful micro-organisms that might be present.	Versatile commercial and industrial indoor lighting solutions built for functionality and dependable performance throughout the product life cycle.	Strikingly aesthetic, unique and bold indoor lighting to make a rich statement in professional, commercial and institutional spaces.	Impactful, reliable track and downlighting solutions with uncompromising quality for professional and commercial spaces.
genlytesolutions.ca	alkco.com	cfi-lighting.com	ledalite.com	lightolier.com

Outdoor				
				
Architecturally relevant, configurable and functional lighting solutions that enhance and complement outdoor spaces.	Pedestrian and Landscape lighting solutions that blend craftsmanship with optical performance to provide a sense of security and beauty in parks and other public or residential settings.	Contractor-friendly outdoor lighting solutions that help make the most of your time and budget.	Contemporary outdoor lighting that blends modern and traditional style with leading-edge engineering to provide functional elegance for urban and roadway spaces.	
gardcolighting.com	hadco.com	keene-lighting.com	lumec.com	

Learn more about the vast array of lighting solutions available from Signify. Visit www.signify.com/en-ca/brands

Definitions

Some lighting knowledge.



Lumens (lm)

The measurement total light output by a light regardless of direction. Icon to the right denotes products with **field selectable lumen output OR field adjustable wattage selector (FAWS for outdoor)**.

Colour Temperature (CCT)

The colour of light output by a source is referenced as correlated colour temperature (CCT) measured in Kelvins (K). Icon to the right denotes products with **field selectable colour temperature switch**.

Colour Rendering Index (CRI)

The effect a light source has on colour appearance is expressed as CRI, on a scale of 0-100. Natural outdoor light is used as a standard with a CRI of 100. Icon to the right denotes products with options of **CRI of 90 and higher**.

Ratings & Certifications

 Protected from total dust ingress. Protected from low pressure water jets from any direction.	 Protected from total dust ingress. Protected from high pressure water jets from any direction.	 Protected from total dust ingress. Protected from immersion between 15 centimeters and 1 meter in depth.	 Protected from total dust ingress. Protected from long term immersion up to a specified pressure.	 Products with icon above denote products with voltage sensing drivers (120-347V)*
 The ENERGY STAR® symbol is the internationally recognized and trusted mark of high efficiency. Products meet strict technical specifications for energy performance—tested and certified against a number of standards.	 A wet location is one where water may drip, splash, or flow on or against electrical equipment. Fixtures rated for this have been engineered so that water cannot enter or accumulate in the wireway, lampholders or other electrical parts.	 NSF International is an accredited, independent third-party certification body that tests and certifies products to verify they meet these public health and safety standards.	 National Electrical Manufacturers Association (NEMA) classification for weather tight enclosures constructed with corrosion-resistant materials.	Standard Universal Voltage (UNV) = 120-277V. *Unless otherwise stated. See specification sheets for up-to-date information.
 The DesignLights Consortium® (DLC) promotes high-quality, energy-efficient lighting products in collaboration with utilities and energy efficiency program members, manufacturers, lighting designers, and federal, state, and local entities.	 DLC Premium is a higher-performance classification for luminaires and retrofit kits where products meet higher efficacy and lumen maintenance requirements.	The DesignLights Consortium® (DLC) promotes high-quality, energy-efficient lighting products in collaboration with utilities and energy efficiency program members, manufacturers, lighting designers, and federal, state, and local entities.	devices, allowing for application of multiple control strategies, programmability, building- or enterprise-level control, zoning and rezoning using software, and measuring and monitoring. They can save 35% or more of lighting energy use in commercial buildings while providing a host of additional capabilities and benefits.	
A Network Lighting Controls (NLC) consists of an intelligent network of individually addressable luminaires and control				

Tools & Resources

Bringing us closer together with meaningful digital tools. Additional resources available, contact your Signify representative for details.

Signify professional lighting catalogue mobile app for iOS and Android





Stock Ready Preferred Partner Program



Lamps eCatalogue



Interact IoT Smart Lighting Platform



Learning Center signify.com/canadalearning




Rebate Finder Tool briteswitch.com/signify-ca



NatureConnect


Bright ideas

Notes, drawings, and more!



Bright ideas

Notes, drawings, and more!



Signify Lighting
Limited Warranties





© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America
Corporation 400 Crossing
Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.