



QuickShip Ready to Go

Field selectable product price guide

Q3 2023



Lumen
Select Switch



CCT with
Select Switch

LIGHTOLIER

Day-Brite
CFI

KEENE



A long history of excellence

As the global leader in lighting for more than 130 years, Signify has the know-how and most comprehensive portfolio to meet any application. We achieved 100% carbon neutrality in 2020. We are number 1 in conventional lamps, LED and Connected lighting. We have over 17,750 patents. We invest 4.8% of total sales in R&D which is two times our nearest competitor! We understand that partnerships are more than sales.

Let's grow together. We are ready to go with you.

Quick and reliable service out of our two distribution centres and two manufacturing facilities.



Find just what you need

Our Stock Ready portfolio makes it easy to find just what you need. Our products are designed for easy ordering through Signify's MyLighting portal. Ready to go products are easy to install with minimal steps, and competitively priced to meet the demands of budget conscious projects focused on cost and energy. Distributors can also benefit from our Stock Ready program which offers deals on freight, guaranteed sales, price change reimbursement, delistment notifications, marketing support, merchandising, and more.

Certifications & labels




Field Selectable Products

With the unique convenience of adjustable color temperatures and/or lumen outputs, our new field selectable product line makes it easy to always have the right product for the job.

Field Selectable products give you the added benefit of carrying one SKU versus multiple SKUs, keeping your inventory low and turns high. These field selectable products are priced right and are all part of our Ready to go offering!

Learn more about additional Ready to go offerings at www.signify.com/readytogo

LIGHTOLIER
by @ignify



Flat Downlight
Dual Select



Commercial Retrofit Downlight
Dual Select



Residential Retrofit Downlight
Selectable



Downlight & Gimbal
Dual Select



Surface Mount Downlight
Dual Select

**Day-Brite
CFI**
by @ignify



SDS Strip
Dual Select



NWL Selectable Wraparound



FCY Value High Bay
Selectable



HCY Sealed High Bay
Selectable



Selectable Backlit Panel
Dual Select



Vaportite Dual Select

KEENE
by @ignify



Wall Pack
Dual Select



Slim Flood Dual Select




Garage & Canopy Dual Select
Square



Garage & Canopy Dual Select
Round



Adjustable Slim Wall Pack
Selectable




Post Top Selectable
Wattage



Area Light Gen 2
Selectable Wattage

Selectable Backlit Panel Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Selectable Backlit Panel 1'x4'					
1SBP3040L8CS-4-UN3-DIM	190096131020	1x4' Dual Select 3500K, 4000K, 5000K, 80CRI, UN3 (120-347V)	4/48	PLSPJ8WECQEX	\$
1SBP3040L8CS-4-UNV-DIM	190096130993	1x4' Dual Select 3500K, 4000K, 5000K, 80CRI, UNV (120-277)	4/48	PLQKCLTPT272	\$
Selectable Backlit Panel 2'x2'					
2SBP3040L8CS-2-UN3-DIM	190096131037	2x2' Dual Select 3500K, 4000K, 5000K, 80CRI, UNV (120-277)	4/40	PLAFAE505CJ	\$
2SBP3040L8CS-2-UNV-DIM	190096131006	2x2' Dual Select 3500K, 4000K, 5000K, 80CRI, UN3 (120-347V)	4/40	PLKH5HVC3HOT	\$
Selectable Backlit Panel 2'x4'					
2SBP3550L8CS-4-UN3-DIM	190096131044	2x4' Dual Select 3500K, 4000K, 5000K, 80CRI, UN3 (120-347V)	4/20	PLIJM2CXSYNX	\$
2SBP3550L8CS-4-UNV-DIM	190096131013	2x4' Dual Select 3500K, 4000K, 5000K, 80CRI, UNV (120-277)	4/20	S-3HABOG	\$
Accessories					
CFFSF14-PANEL	626772000026	1x4' Surface mount field assembly kit for Selectable Backlit Panel (SBP)	10/80	N/A	\$
CFFSF22-PANEL	626772000019	2x2' Surface mount field assembly kit for Selectable Backlit Panel (SBP)	10/40	N/A	\$
CFFSF24-PANEL	626772000033	2x4' Surface mount field assembly kit for Selectable Backlit Panel (SBP)	10/240	N/A	\$

NWL Wraparound Selectable



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
NWL Selectable Wraparound					
NWL440L8CST-UNV-DIM-OCC	190096130917	4' Selectable 3000K, 3500K, 4000K, 80CRI, UNV (120-277V), Occ Sensor	4/32	PLTCN6OSD433	\$

FCY Value High Bay Selectable



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
FCY Value High Bay Selectable					
FCY15L8CST-UNV-DIM	190096180653	15,000lm Selectable 4000K, 5000K, 80CRI, UNV (120-277V)	1/27	PLI6CXJN3X6C	\$
FCY22L8CST-UNV-DIM	190096180660	22,000lm Selectable 4000K, 5000K, 80CRI, UNV (120-277V)	1/27	PL450VSJUE9A	\$
FCY29L8CST-UNV-DIM	190096180677	29,000lm Selectable 4000K, 5000K, 80CRI, UNV (120-277V)	1/36	PLS2MUBV8ECV	\$
FCY15L8CST-347-DIM	190096180684	15,000lm Selectable 4000K, 5000K, 80CRI, (347V)	1/27	PLM405XT57ZE	\$
FCY22L8CST-347-DIM	190096180691	22,000lm Selectable 4000K, 5000K, 80CRI, (347V)	1/27	PLGRWD3LZYD7	\$
FCY29L8CST-347-DIM	190096180707	29,000lm Selectable 4000K, 5000K, 80CRI, (347V)	1/24	PL5YOSU340LN	\$
FCY-WG	190096180721	Wire guard for FCY15 and FCY22	10/600		\$
FCY-WG29	190096180745	Wire guard for FCY29	10/600		\$

Vaportite Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Vaportite					
VTS22028L8CSTUN3-DIM	190096196517	2' Dual Select 2000/2400/2800lm, 3500/4000/5000K, 120-347V	6/144	S-C761RN	\$
VTS42856L8CSTUN3-DIM	190096196531	4' Dual Select 2800/4200/5600lm, 3500/4000/5000K, 120-347V	4/64	S-XGL7UR	\$
VTS880130L8CSTUN3-DIM	190096196555	8' Dual Select 8000/11000/13000lm, 3500/4000/5000K, 120-347V	2/64	S-EAOD4I	\$

SDS Strip Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
SDS Strip Dual Select					
SDS21224L8CST-UNV-DIM	190096131563	2' Dual Select Strip 2430/3640/4850lm, 3500K, 4000K, 5000K, 80CRI, UNV (120-277V)	9/450	PLV59H45ZE1C	\$
SDS42448L8CST-UN3-DIM	190096131600	4' Dual Select Strip 2430/3640/4850lm, 3500K, 4000K, 5000K, 80CRI, UN3 (120-347V)	9/144	PL33OZYV11GW	\$
SDS84998L8CST-UN3-DIM	190096131617	8' Dual Select Strip 4900/7350/9800lm, 3500K, 4000K, 5000K, 80CRI, UN3 (120-347V)	6/180	PLB9UEA7HLO5	\$

HCY Sealed High Bay Selectable



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
HCY Sealed High Bay Selectable					
HCY1421L8CST-UN3-DIM	190096131648	14,000lm, Selectable 4000K/5000K (CRI 80), 0-10V UNV, 120-347V	1/36	PL010HSZT5F0	\$
HCY2833L8CST-UN3-DIM	190096131655	33,000lm, Selectable 4000K/5000K (CRI 80), 0-10V UNV, 120-347V	1/24	PLJXJYXIX60N	\$
Accessories					
HCY2-PRSM	190096131631	16" Clear Polycarbonate Reflector for HCY14L and HCY21L	10/80	N/A	\$
HCY2-PRLG	190096131624	16" Clear Polycarbonate Reflector for HCY28L and HCY33L	10/40	N/A	\$
HCY-SURFACE BKT SM	190096131174	Surface Mount Bracket for HCY14L and HCY21L	10/240	N/A	\$
HCY-SURFACE BKT LG	190096131181	Surface Mount Bracket for HCY28L and HCY33L	10/180	N/A	\$
HCY-REMOTE	190096131143	Remote hand-held programmer for HCY-SENSOR	20/4800	N/A	\$
HCY-SENSOR	190096131662	Field installed microwave sensor	50/4500	N/A	\$

Wall Pack

Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Wall Pack dual select					
WP100-SCT-G2-10-BZ	190096131341	28W/40W/60W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	2/24	PLDEKDYR83Y	\$
WP60-SCT-G2-10-BZ	190096131334	70W/80W/90W/100W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	2/24	PLS3A95FM210	\$

Adjustable Slim Wall Pack

Selectable



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Adjustable Slim Wall Pack Selectable					
ASW25-SCT-G1-10-BW	190096182053	15W/20W/25W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	4/144	S-L10ZI3	\$
ASW75-SCT-G1-10-BW	190096182060	45W/60W/75W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V	4/120	S-W278UM	\$

SlimFlood

Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
SlimFlood Dual Select 15W/25/35W					
SF15-SCT-K-G2-10-BZ	190096196005	15W Selectable 3000K, 4000K, 5000K, 70CRI, 120-347V - Knuckle Mt.	180	S-XDAS9R	\$
SF15-SCT-Y-G2-10-BZ	190096196012	15W Selectable 3000K, 4000K, 5000K, 70CRI, 120-347V - Yoke Mt.	300	S-XDAS9R	\$
SF35-SCT-K-G2-10-PCB-BZ	190096196029	15W/25W/35W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Knuckle Mt, Photocell	180	S-17Z86U	\$
SF35-SCT-Y-G2-10-PCB-BZ	190096196036	15W/25W/35W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Yoke Mt, Photocell	240	S-17Z86U	\$
SlimFlood Dual Select 15W/35/60W					
SF60-SCT-K-G2-10-PCB-BZ	190096196043	15W/35W/60W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Knuckle Mt, Photocell	120	S-746YXP	\$
SF60-SCT-Y-G2-10-PCB-BZ	190096196050	15W/35W/60W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Yoke Mt, Photocell	120	S-746YXP	\$
SlimFlood Dual Select 60W/80/100W					
SF100-SCT-S-G2-10-PCB-BZ	190096196067	60W/80W/100W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - SlipFitter Mt, Photocell	60	S-RENDJO	\$
SF100-SCT-T-G2-10-PCB-BZ	190096196074	60W/80W/100W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Trunnion Mt, Photocell	90	S-RENDJO	\$
SlimFlood Dual Select 100W/120/150W					
SF150-SCT-S-G2-10-PCB-BZ	190096196081	100W/120W/150W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - SlipFitter Mt, Photocell	40	S-M8YAEV	\$
SF150-SCT-T-G2-10-PCB-BZ	190096196098	100W/120W/150W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Trunnion Mt, Photocell	40	S-M8YAEV	\$
SlimFlood Dual Select 120W/150/205W					
SF205-SCT-S-G2-10-BZ	190096196104	120W/150W/205W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - SlipFitter Mt.	24	S-DT894A	\$
SF205-SCT-T-G2-10-BZ	190096196111	120W/150W/205W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Trunnion Mt.	24	S-DT894A	\$
SlimFlood Dual Select 205W/225/300W					
SF300-SCT-S-G2-10-BZ	190096196128	205W/255W/300W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - SlipFitter Mt.	20	S-F1OY78	\$
SF300-SCT-T-G2-10-BZ	190096196135	205W/255W/300W Dual Select 3000K, 4000K, 5000K, 70CRI, 120-347V - Trunnion Mt.	20	S-F1OY78	\$
Accessory for SF205 & SF300					
SF205-300-PCB	190096196142	Slim Flood 120-150-205-255-300W Photocell.	1440	N/A	\$

Garage & Canopy

Dual Select



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Garage & Canopy Dual Select					
GC60-SCT-G2-SM-5-10-BZ	190096131310	Garage & Canopy Square Selectable Wattage and CCT 28-40-60W / 3000K, 4000K, 5000K	2/24	PLVXWEOIQDC5	\$
GC90-SCT-G2-SM-5-10-BZ	190096131327	Garage & Canopy Square Selectable Wattage and CCT 70-80-90W / 3000K, 4000K, 5000K	2/24	PLWNEI9VD4T5	\$
GCR60-SCT-G1-SM-5-10-BZ	190096181957	Garage & Canopy Round Selectable Wattage and CCT 28-40-60W / 3000K, 4000K, 5000K		PL29WA55ASGM	\$
GCR90-SCT-G1-SM-5-10-BZ	190096181964	Garage & Canopy Round Selectable Wattage and CCT, 70-80-90W / 3000K, 4000K, 5000K		PLFS6QA93NGG	\$
Accessories					
GC60/90-MH10	190096131556	Garage & Canopy Dual Select Controller		N/A	\$

Post Top

Selectable Wattage



Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Site & Area Post Top Type 3					
PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK	783352026064	3000K, Type 3, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	1	PL93CH3J24MU	\$
PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK	783352026088	4000K, Type 3, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	1	PL15T6Z3FCOE	\$
Site & Area Post Top Type 5					
PT50-WW-G1-T2-5-HV3-FAWS-TLRPC-BK	783352026071	3000K, Type 5, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	1	PL3KYCJH4R02	\$
PT50-NW-G1-T2-5-HV3-FAWS-TLRPC-BK	783352026095	4000K, Type 5, 120-347V, Field-adjustable wattage, twist-lock recept, w/short cap	1	PLQASEYVWBL1	\$

Area Light Gen 2

Selectable Wattage




Catalog Number	UPC Code	Product Description	Case/Pallet Qty	DLC#	Price
Area Light Gen 2 Type 3					
AL150-NW-G2-AR-3-8-FAWS-BZ	190096180585	4000K, Type 3, Field-adjustable wattage, 95-115-130-145W, 120-277V	15	S-6BUKAR	\$
AL70-NW-G2-AR-3-8-FAWS-BZ	190096180578	4000K, Type 3, Field-adjustable wattage, 50-57-65-72W, 120-277V	15	S-ZLIVG8	\$
AL150-NW-G2-AR-3-6-FAWS-BZ	190096180585	4000K, Type 3, Field-adjustable wattage, 95-115-130-145W, 347-480V	15	PLSOUWJ3RNNW	\$
AL70-NW-G2-AR-3-6-FAWS-BZ	190096180578	4000K, Type 3, Field-adjustable wattage, 50-57-65-72W, 347-480V	15	PLZABA9BN8X7	\$
Area Light Gen 2 Type 4					
AL150-NW-G2-AR-4-8-FAWS-BZ	190096180622	4000K, Type 4, Field-adjustable wattage, 95-115-130-145W, 120-277V	15	S-26RB EY	\$
AL70-NW-G2-AR-4-8-FAWS-BZ	190096180615	4000K, Type 4, Field-adjustable wattage, 50-57-65-72W, 120-277V	15	S-RGNVW4	\$
AL150-NW-G2-AR-4-6-FAWS-BZ	190096180622	4000K, Type 4, Field-adjustable wattage, 95-115-130-145W, 347-480V	15	PL38DXHUBY7V	\$
AL70-NW-G2-AR-4-6-FAWS-BZ	190096180615	4000K, Type 4, Field-adjustable wattage, 50-57-65-72W, 347-480V	15	PL06LZUHINA	\$
Accessories					
AL-SF-G2-BZ	190096180639	Slip Fitter Mounting Accessory		N/A	\$
AL-RP-G2-BZ	190096182008	Round Pole Adapter Accessory		N/A	\$



Bright ideas

Notes, drawings, and more!



Insert Agency Logo Here



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.