



Quick Ship Lighting Guide

Lighting that's Ready to **Go** when you are

The most complete stock
offering in the industry.

signify.com/quickship



2022 Q1

if you want hard days to feel a little easier

Choose Signify for great value,
high performance lighting brands
that are ReadytoGo

Introducing our latest **ReadytoGo: Quick Ship Lighting Guide**. This new guide has been revamped with an updated product mix that is designed to meet the day-to-day needs of a wide range of lighting projects.

This guide is designed to help support shelf-stocking requirements and discretionary design-build projects with lighting solutions that are ready to ship.

Choose from a wide array of **Stock Ready** products (order to ship in 2-days*) and **Design Ready** products (order to ship in 10 days*) which can help meet those demanding timelines on the job.

For the latest information, visit:

signify.com/quickship

* Service time is calculated from the time the order is entered until it is shipped. See page 5 for full details.



ReadytoGo



Architectural Lighting

8

Office & Industrial Lighting

10

High Bays

12

Linear

16

Grid / Recessed

22

Indoor Track & Downlighting

32

Core Downlights

34

Downlight Kits

42

Track Lighting

64

Commercial Outdoor Lighting

74

Site & Area

76

Floods & Wall Packs

80

Special Application

84

Low Voltage

85

Connect Lighting Controls

86

LED Lamps & Retrofits

88

Ballasts & Electronics

92

Budget LED

94

Why choose Signify?

4

Commitment

5

Definitions

97

Tools & Resources

98

Why choose Signify?

Quick, reliable service out of our distribution center.

Find just what you need

Our **ReadytoGo** program makes it easy to find just what you need with the most comprehensive stocking portfolio in the industry.

● **Stock Ready** (2-Day Quick Ship)

■ **Design Ready** (10-Day Quick Ship)

ReadytoGo products are designed for easy ordering through Signify's **MyLighting portal**, easy to install with minimal steps, and competitively priced to meet the demands of budget conscious projects focused on cost and energy.

Distributors can benefit from our **Stock Ready program** which provides our key partners with preferred service and delivery support, marketing support, merchandising, and more.

Your one-stop shop for any lighting need

Signify offers the most complete stock offering in the industry. We provide conventional and LED lamps, ballasts, drivers, retrofit kits, and indoor and outdoor stock luminaires. Save time and improve efficiencies by consolidating your stock purchases with Signify.

As the global leader in lighting for more than 125 years, Signify has the know-how and most comprehensive portfolio to meet any application. Signify achieved 100% Carbon Neutrality in 2020. We are #1 in conventional lamps, LED and connected lighting. With over 17,750 patents, Signify invests 4.8% of total sales in R&D which is two times our nearest competitor!

125+

Years in business as a global leader in lighting

100%

Carbon neutral in 2020

#1

Connected lighting, conventional lamps, & LED lamps

\$7.3B

Sales (~75%) in professional lighting & connected solutions

100+

University partnerships

64M+

Connected light points

17K+

Patents

4.8%

Total sales invested in R&D
—2X our nearest competitor

Commitment

Our delivery commitment is backed by a significant investment in finished goods and component inventory.

If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs and confirm an acceptable ship date.

In case you have questions, please contact your sales representative or Customer Service.

Order Related Inquiries:

canada.om@signify.com / 1-800-668-9008

General Inquiries: 1-800-555-0050

MyLighting: www.mylighting.signify.com

ReadytoGo

Service Offering

Stock / Order / Sell through Support

Lamps, Ballasts, Luminaires

Filterable on eCatalogue

Returnable

● Stock Ready	■ Design Ready	◆ Spec Ready
Stock & Flow	Design Build	Spec / Bid / Buy
•	•	•
2-Day Order to Delivery	10-Day Order to Delivery	Ships in 4–6 weeks
•	•	•
•		

Terms and Conditions

Freight prepaid on all **ReadytoGo** stock orders with combined orders greater than \$1500.

Options available for orders less than \$1500, contact plc-orderentry@signify.com for more information.

Visit www.signify.com/en-ca/support/warranties for details on our standard terms and conditions.

Order Process

Lead time is from the time the order is entered and received by our warehouse. We are committed to entering orders within 24 hours of receipt.

To ensure your order is processed without delay, we recommend you have the following:

- Correct Catalogue Numbers
- Price detail (Deal#, SPA reference)
- Tag "Quick Ship" on your order

Large Orders

To ensure we satisfy all our customers optimally within the committed lead times, maximum order quantities may apply. If the order exceeds the set threshold, Signify will contact you to work out a feasible schedule for your large order. It is always advised to work with your Signify representative to give advance notice of any foreseeable large orders.

Transportation timelines

For **Stock Ready** products, Signify maintains stock levels at our warehouse in Markham, Ontario in order to provide our customers with quick access to the inventory you require. You can calculate when to expect your shipment by adding the following transportation times to the day it leaves our warehouse.

Toronto / Ottawa / Montreal	+1 Day
Windsor	+2 Days
Sudbury / Quebec City	+3 Days
Manitoba / New-Brunswick	+4 Days
Saskatchewan / Nova Scotia / P.E.I.	+5 Days
Alberta	+6 Days
British Columbia / Newfoundland	+7 Days

The right solution for every need.


Signify provides the solution to every lighting need, whether it's lighting and connecting your public spaces, giving your commercial building an energy saving upgrade, or working on a yet to be constructed hospital, we've got you covered.



Cities / Public Spaces

Residential

Landmarks



Retail / Hospitality

Offices / Education

Warehouse / Industry

Stock up on our new Field Selectable product line.

With the convenience of adjustable colour temperatures and lumen outputs, our comprehensive Field Selectable product solutions make it easy to always have the right product for the job.



FCY LED High Bay | Pg. 15



HCY LED High Bay | Pg. 15



Flat Downlight Select LED | Pg. 36



Retrofit Downlight DualSelect | Pg. 37



NWL LED Wraparound | Pg. 20



SDS Selectable Strip | Pg. 20



Area Light LED Gen. 2 | Pg. 79 (AL70)



Area Light LED Gen. 2 | Pg. 79 (AL150)



Selectable Backlit Panel (SBP) | Pg. 26



Post Top LED | Pg. 79



Garage & Canopy LED DualSelect | Pg. 79



Wall Pack LED DualSelect | Pg. 83



ModiFly

Architectural Lighting


Ledalite's award-winning, inspiring, and innovative lighting solutions allow specifiers to create a unique vision for a range of interior spaces.





You don't have to sacrifice product quality and performance for critical timing. With the Ledalite QuickShip program, we'll ship your order within 10 working days of order receipt.

This program applies to almost all of our product families, so while we can't increase the speed of light, we did find a way to get you your lighting faster.

Category	Limit per Release
Recessed LED	100 units
Linear LED	500 linear ft.
TruGroove Family	

Order limits and exclusions apply. Contact your Signify sales rep for details. For more information please visit signify.com/en-ca/brands/ledalite/quickship





Day-Brite

CFI

by Signify

Selectable Backlit Panel (SBP) | Pg. 26

Office & Industrial Lighting

Affordable and energy efficient stand-alone and connected lighting solutions for general purpose commercial or industrial projects.

Day-Brite CFI is an industry leader in general purpose and performance lighting systems. With products ranging from high performance recessed ceiling troffers to industrial grade high bay luminaires, Day-Brite CFI's extensive portfolio offers the utmost in quality, performance and efficiency for a variety of applications.



FluxStream LED Strip (FSS) | Pg. 19



Vaporlume V3W LED | Pg. 21

High Bays

12

LED Quick Selection Guide

13

APX LED High Bay	14
FBX LED High Bay	14
FBY LED High Bay	14
FCX LED High Bay	15
FCY LED High Bay	15
HCY LED High Bay	15
SHE High Bay	15

Linear

16

LED Quick Selection Guide

17

FluxStream LED Industrial (FSI)	18
FluxStream LED Strip EZ (FSSEZ)	18
FluxStream LED Strip (FSS)	19
FluxStream LED Wraparound (FSW)	19
NWL LED Wraparound	20
OWL LED Wraparound	20
SCD LED Wide Strip	20
SDS Selectable Strip	20
SLS Linkable LED Strip	20
Vaporlume V3W LED	21
VTC Sealed Strip LED	21
BVL Vaporlume	21
CFW Wraparound	21
T Series T8 Strip	21

Grid / Recessed

22

LED Quick Selection Guide

23

SlimLux Surface LED	24
FluxPanel LED Gen. 2 (FPZ)	25
Selectable Backlit Panel (SBP)	26
ClearAppeal LED Gen. 2 (CAX)	27
FluxGrid LED (FGG)	28
FormFlex LED (FFX)	30
SofTrace LED (STX)	31
TG8 Recessed Lensed	31

Day-Brite

CFI

by Signify

High Bays

if

you need ideal
illumination for large
industrial warehouses
and institutional
spaces

Choose Day-Brite CFI by Signify for a complete selection of professional office & industrial lighting products. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.


Day-Brite CFI

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		APX LED High Bay	FBX LED High Bay	FBY LED High Bay	FCX LED High Bay	FCY LED High Bay	HCY LED High Bay
Page Reference		pg. 14	pg. 14	pg. 14	pg. 15	pg. 15	pg. 15
Quick Ship Service		● ■	● ■	● ■	● ■	● ■	● ■
Budget / Grade		Spec / Best	Performance / Better		Value / Good		
Features / Performance	Sizes	L=51.91" (1318.5mm) W=14.61" (371mm)	L=23-7/8" (606mm) × W=14-3/4" (375mm) L=23-7/8" (606mm) × W=24" (610mm)	L=24-1/8" (613mm) × W=11-1/2" (292mm) L=47-7/8" (1216mm) × W=11-1/2" (292mm)	L=24.6" (624.6mm) × W=12.6" (320mm)	L=24-7/8" (630mm) × W=11-7/8" (300mm) L=24-7/8" (630mm) × W=14-1/8" (360mm)	Ø 11-3/8" Ø 13-3/4"
	Lumens (lm)	12000 / 24000 8000 / 16000 / 20000*	8000-24000 30000-72000*	12000-60000	15000 22000*	15000 / 22000 / 29000	14000 / 21000 / 28000 / 33000
	Efficacy (lm/W)	up to 129	up to 146	up to 148	up to 148	up to 140	up to 144
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V
	CCT (K)	3500K* 4000K	3500K* 4000K 5000K*	3500K 4000K	4000K	Field Selectable 4000K 5000K	Field Selectable 4000K 5000K
	CRI	80	80	80	80	80	80
	Voltage (V)	120-277V / 347V	120-277V / 347V 120V / 208V / 277V / 480V*	120-277V / 347V 120V / 208V / 277V / 480V*	120-277V* / 347V	120-277V / 347V	120-347V
	Lens	Clear Acrylic Frosted Acrylic* Clear Polycarbonate* Frosted Polycarbonate*	Clear Acrylic* Frosted Acrylic* Clear Ribbed* Frosted Ribbed* Clear Polycarbonate*	Clear Acrylic* Frosted Acrylic*	No Lens	Frosted Clear Acrylic	Clear Polycarbonate
Ratings & Certification	Interact Ready	◆	◆	◆			
	SpaceWise	◆	◆	◆			
	IP / Wet Location Rating	IP65 / IP67					IP65
	Other Ratings	NSF / NEMA 4X					NEMA 4X
	cULus Listed				✓	✓	✓
	cETLus Listed	✓	✓	✓			
	DLC	Standard	Standard / Premium	Premium	Premium	Premium	Premium
	Lifetime (L70)	up to 100,000 hours	up to 100,000 hours	up to 100,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.					

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
 ✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



APX



FBX



FBY

Product	Description / Features		UPC
APX LED High Bay L=51.91" (1318.5mm) × W=14.61" (371mm)			
■ APX12LL40-347	12000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ APX12LL40-UNV	12000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	
■ APX16LL40-347	16000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ APX16LL40-UNV	16000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	
■ APX20LL40-347	20000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ APX20LL40-UNV	20000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	
■ APX24LL40-347	24000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
● APX24LL40-UNV	24000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 05652 0
FBX LED High Bay L=23-7/8" (606mm) × W=14-3/4" (375mm)			
■ FBX08LL40-347	8000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FBX08LL40-UNV	8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBX12LL40-347	12000lm, 4000K (CRI 80), 347, 0-10V Dimming	DLC	
■ FBX12LL40-UNV	12000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 81370 29992 7
L=23-7/8" (606mm) × W=24" (610mm)			
■ FBX16LL40-347	16000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FBX16LL40-UNV	16000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 81370 00994 6
■ FBX20LL40-347	20000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FBX20LL40-UNV	20000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FBX24LL40-347	24000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FBX24LL40-UNV	24000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 82343 06687 4
FBY LED High Bay L=24-1/8" (613mm) × W=11-1/2" (292mm)			
■ FBY12L835-347	12000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FBY12L835-UNV	12000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FBY12L840-347	12000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY12L840-UNV	12000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65312 5
■ FBY18L835-347	18000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY18L835-UNV	18000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY18L840-347	18000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY18L840-UNV	18000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65311 8
■ FBY24L835-347	24000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY24L835-UNV	24000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY24L840-347	24000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	7 84197 66555 5
● FBY24L840-UNV	24000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65310 1
● FBY24L840-UNV-WC6	24000lm, 4000K (CRI 80), UNV, Wired 6' 16/3 cord, 0-10V Dimming	PREMIUM	7 84197 66556 2
■ FBY30L835-347	30000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY30L835-UNV	30000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY30L840-347	30000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY30L840-UNV	30000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 65309 5
L=47-7/8" (1216mm) × W=11-1/2" (292mm)			
■ FBY36L835-347	36000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY36L835-UNV	36000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY36L840-347	36000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY36L840-UNV	36000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features	DLC	UPC
FBY LED High Bay (Continued) L=47-7/8" (1216mm) × W=11-1/2" (292mm)			
■ FBY48L835-347	48000lm, 3500K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY48L835-UNV	48000lm, 3500K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY48L840-347	48000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY48L840-UNV	48000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
■ FBY60L840-347	60000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
■ FBY60L840-UNV	60000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	
Accessories			
● FBY-PENHGR	FBY Pendant hanger (adds 3" to height)		7 84197 66503 6
● FBY-WG	FBY Wire Guard (Order 2 for FBY36, FBY48, & FBY60)		7 84197 66557 9
● HCH5-VHOOK	FBY 5' Cables with V Hook		7 84197 65872 4
● HNH5-VHOOK	FBY 54" Chain with V Hook		7 84197 65876 2
FCX LED High Bay L=24.6" (624.6mm) × W=12.6" (320mm)			
● FCX15L840-347-DIM	15000lm, 4000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
FCY LED High Bay L=24-7/8" (630mm) × W=11-7/8" (300mm)			
■ FCY15L8CST-347-DIM	15000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
● FCY15L8CST-UNV-DIM	15000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18065 3
■ FCY22L8CST-347-DIM	22000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
● FCY22L8CST-UNV-DIM	22000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18066 0
L=24-7/8" (630mm) × W=14-1/8" (360mm)			
■ FCY29L8CST-347-DIM	29000lm, 4000K / 5000K (CRI 80), 347V, 0-10V Dimming	PREMIUM	
● FCY29L8CST-UNV-DIM	29000lm, 4000K / 5000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	1 90096 18067 7
Accessories			
● FCY-WG	Wire guard for FCY15 and FCY22		1 90096 18072 1
HCY LED High Bay Ø 11-3/8"			
● HCY14L8CST-UN3-DIM	Round, 14000lm, 4000K / 5000K (CRI 80), 120-347V, 0-10V Dimming	PREMIUM	1 90096 13109 9
● HCY21L8CST-UN3-DIM	Round, 21000lm, 4000K / 5000K (CRI 80), 120-347V, 0-10V Dimming	PREMIUM	1 90096 13110 5
Ø 13-3/4"			
● HCY28L8CST-UN3-DIM	Round, 28000lm, 4000K / 5000K (CRI 80), 120-347V, 0-10V Dimming	PREMIUM	1 90096 13111 2
● HCY33L8CST-UN3-DIM	Round, 33000lm, 4000K / 5000K (CRI 80), 120-347V, 0-10V Dimming	PREMIUM	1 90096 13112 9
Accessories			
● HCY-PRSM	16" Clear polycarbonate reflector for HCY14 and HCY21		1 90096 13115 0
● HCY-PRLG	16" Clear polycarbonate reflector for HCY28 and HCY33		1 90096 13116 7
● HCY-SURFACE BKT SM	Surface mount bracket for HCY15 and HCY21		1 90096 13117 4
● HCY-SURFACE BKT LG	Surface mount bracket for HCY28 and HCY33		1 90096 13118 1
SHE High Bay L=48-1/8" (1222mm) × W=11-1/8" (283mm)			
● SHE454HO-347-1/4EB-GENRS-CORD	T5HO 54W (4 lamps), 347V, 6' Cord (no plug)		7 73849 34995 0
● SHE454HO-UNV-1/4EB-GENRS-CORD	T5HO 54W (4 lamps), UNV, 6' Cord (no plug)		7 73849 34994 3
L=48-1/8" (1222mm) × W=16-1/8" (409.6mm)			
● SHE654HO-347-1/42EB-GENRS-CORD	T5HO 54W (6 lamps), 347V, 6' Cord (no plug)		7 73849 34993 6
● SHE654HO-UNV-1/42EB-GENRS-CORD	T5HO 54W (6 lamps), UNV, 6' Cord (no plug)		7 73849 34992 9
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			

Day-Brite

CFI

by Signify

Linear

if
you need versatile
surface mount
illumination for
hallways, egress,
and task lighting
applications

Choose Day-Brite CFI by Signify for a complete selection of professional office & industrial lighting products. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

Day-Brite CFI

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		FluxStream LED Industrial (FSI)	FluxStream LED Strip EZ (FSSEZ)	FluxStream LED Strip (FSS)	FluxStream LED Wraparound (FSW)	NWL LED Wraparound	OWL LED Wraparound	SCD LED Wide Strip	SDS Selectable Strip	SLS Linkable LED Strip	Vaporlume V3W LED	VTC Sealed Strip LED
Page Reference		pg. 18	pg. 18	pg. 19	pg. 19	pg. 20	pg. 20	pg. 20	pg. 20	pg. 20	pg. 21	pg. 21
Quick Ship Service		● ■	● ■	● ■	● ■	● ■	● ■	●	●	● ■	● ■	● ■
Budget / Grade		Performance / Better				Value / Good					Performance / Better	
Spec & Performance	Sizes	4' / 8'	4' / 8'	2' / 3' / 4' / 8'	2' / 4' / 8'	4'	4'	2' / 3' / 4'	4' / 8'	2' / 4'	2' / 4'	4'
	Lumens (Max)	4000-14000	4000 / 8000	4000-14000	3000 / 4000	4000	4000 / 5000	2000 / 5000	Selectable 4850 / 9800	1600 / 3200	3500-5100	3600
	Efficacy (lm/W)	up to 134	up to 133	up to 133	up to 122	122	up to 106	up to 119	up to 139	up to 104	up to 147	up to 104
	Dimming	0-10V Step* MarkX* DALI*	0-10V	0-10V Step* MarkX* DALI*	0-10V Step* MarkX* DALI*	0-10V	0-10V Step*		0-10V		0-10V Step*	
	CCT (K)	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	Selectable 3000K 3500K 4000K	4000K	4000K	Selectable 3500K 4000K 5000K	3500K 4000K	3000K* 3500K 4000K 5000K*	4000K
	CRI	80	80	80	80	80	80	80	80	80	80	80
	Voltage (V)	120-277V 347V	120-277V	120-277V 347V	120-277V	120-277V	120-277V 347V	120-277V	120-347V	120-277V	120-277V 347V	120-277V
Controls & Options	Construction / Finish	White Metal Matte Black* Satin Aluminum*	White Metal	White Metal Matte Black* Satin Aluminum*	White Metal	White Polycarbonate	White Metal	White Metal	White Metal	White Metal	White Fiberglass	Grey Polycarbonate
	Lens	Frosted Acrylic	Frosted Acrylic	Frosted Acrylic	Frosted Acrylic	Frosted Polycarbonate	Frosted Acrylic	Frosted Acrylic	Frosted Polycarbonate	Frosted Acrylic	Clear Acrylic Frosted Acrylic* Prismatic*	Frosted Acrylic Clear Acrylic*
	Interact Ready	◆	◆	■ ◆	■ ◆						◆	
	SpaceWise	◆	◆	◆							◆	
	Power over Ethernet (PoE)			◆								
Ratings & Certification	Wall Mountable ADA Compliant	✓	✓	✓	✓							
	IP / Wet Location Rating										IP65 IP67*	IP65
	NSF Rating										◆	
	cULus Listed							✓	✓	✓		
	cETLus Listed	✓	✓	✓	✓	✓	✓					
	DLC	Standard	Standard	Standard	Standard / Premium	Standard	Standard	Standard	Standard	Standard	Premium	Standard
	Lifetime (L70)	up to 50,000 hours	up to 50,000 hours	up to 100,000 hours	up to 100,000 hours		up to 50,000 hours				up to 100,000 hours	
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.										

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



FSI



FSSEZ

Product	Description / Features		UPC
FluxStream LED Industrial (FSI)			
4'			
■ FSI440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSI440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
● FSI440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24554 2
■ FSI455L835-347-DIM	4', 5500lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI455L835-UNV-DIM	4', 5500lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI455L840-347-DIM	4', 5500lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI455L840-UNV-DIM	4', 5500lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24556 6
■ FSI470L835-347-DIM	4', 7000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI470L835-UNV-DIM	4', 7000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI470L840-347-DIM	4', 7000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI470L840-UNV-DIM	4', 7000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24557 3
8'			
■ FSI880L835-347-DIM	8', 8000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSI880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI880L840-347-DIM	8', 8000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24558 0
■ FSI8110L835-347-DIM	8', 11000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI8110L835-UNV-DIM	8', 11000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI8110L840-347-DIM	8', 11000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI8110L840-UNV-DIM	8', 11000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24559 7
■ FSI8140L835-347-DIM	8', 14000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI8140L835-UNV-DIM	8', 14000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSI8140L840-347-DIM	8', 14000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSI8140L840-UNV-DIM	8', 14000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24560 3
FluxStream LED Strip EZ (FSSEZ)			
4'			
● FSSEZ440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 70650 0
● FSSEZ440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 70017 1
8'			
● FSSEZ880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 70653 1
● FSSEZ880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 70018 8

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



FSS



FSW

Product	Description / Features		UPC
FluxStream LED Strip (FSS)			
4'			
■ FSS440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
● FSS440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 27002 5
■ FSS440L835-UNV-DIM-SWZCS	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
● FSS440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	7 84197 26986 9
● FSS440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 24538 2
■ FSS440L840-UNV-DIM-SWZCS	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
■ FSS440L850-UNV-DIM-SWZCS	4', 4000lm, 5000K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
■ FSS455L835-347-DIM	4', 5500lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSS455L835-UNV-DIM	4', 5500lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 27010 0
■ FSS455L840-347-DIM	4', 5500lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
● FSS455L840-UNV-DIM	4', 5500lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24540 5
■ FSS470L835-347-DIM	4', 7000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSS470L835-UNV-DIM	4', 7000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSS470L840-347-DIM	4', 7000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSS470L840-UNV-DIM	4', 7000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24541 2
8'			
■ FSS880L835-347-DIM	8', 8000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSS880L835-UNV-DIM	8', 8000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 27030 8
● FSS880L840-347-DIM	8', 8000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	7 84197 26990 6
● FSS880L840-UNV-DIM	8', 8000lm, 4000K (CRI 80), UNV, 0-10V Dimming	PREMIUM	7 84197 24542 9
■ FSS8110L835-347-DIM	8', 11000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSS8110L835-UNV-DIM	8', 11000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 27025 4
■ FSS8110L840-347-DIM	8', 11000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
● FSS8110L840-UNV-DIM	8', 11000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 84197 24543 6
■ FSS8140L835-347-DIM	8', 14000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
■ FSS8140L835-UNV-DIM	8', 14000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	
■ FSS8140L840-347-DIM	8', 14000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
■ FSS8140L840-UNV-DIM	8', 14000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	
FluxStream LED Wraparound (FSW)			
■ FSW430L835-UNV-DIM-SWZCS	4', 3000lm, 3500K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
■ FSW430L840-UNV-DIM-SWZCS	4', 3000lm, 4000K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
■ FSW440L835-UNV-DIM-SWZCS	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
■ FSW440L840-UNV-DIM-SWZCS	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming, Interact Ready	DLC	
FluxStream LED, Accessories			
● FSSWG4	FluxStream Strip, 4' Wire guard (order two for 8' models)		7 84197 29502 8
● FSTH	FluxStream, Sliding Hanger Bracket (Pair)		078197349707
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
NWL LED Wraparound			
 NWL440L8CST-UNV-DIM-OCC	4', 4000lm, 3000K / 3500K / 4000K (CRI 80), UNV, 0-10V Dimming, Occupancy Sensor	DLC	1 90096 13091 7
OWL LED Wraparound			
 OWL440L835-347-DIM	4', 4000lm, 3500K (CRI 80), 347V, 0-10V Dimming		
 OWL440L835-UNV-DIM	4', 4000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 81370 09721 9
 OWL440L840-347-DIM	4', 4000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
 OWL440L840-UNV-DIM	4', 4000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 81370 04900 3
 OWL450L835-347-DIM	4', 5000lm, 3500K (CRI 80), 347V, 0-10V Dimming	DLC	
 OWL450L835-UNV-DIM	4', 5000lm, 3500K (CRI 80), UNV, 0-10V Dimming	DLC	7 81370 09741 7
 OWL450L840-347-DIM	4', 5000lm, 4000K (CRI 80), 347V, 0-10V Dimming	DLC	
 OWL450L840-UNV-DIM	4', 5000lm, 4000K (CRI 80), UNV, 0-10V Dimming	DLC	7 81370 04901 0
SCD LED Wide Strip			
 SCD220L840-UNV	2', 2000lm, 4000K (CRI 80), UNV, Non-Dimmable		1 90096 13014 6
 SCD330L840-UNV	3', 3000lm, 4000K (CRI 80), UNV, Non-Dimmable		1 90096 13015 3
 SCD428L840-UNV	4', 2800lm, 4000K (CRI 80), UNV, Non-Dimmable	DLC	1 90096 13016 0
 SCD450L840-UNV	4', 5000lm, 4000K (CRI 80), UNV, Non-Dimmable		1 90096 13017 7
SDS Selectable Strip			
 SDS42448L8CST-UN3-DIM	4', 2430 / 3640 / 4850lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	DLC	1 90096 13160 0
 SDS84998L8CST-UN3-DIM	8', 4900 / 7350 / 9800lm, 3500K / 4000K / 5000K (CRI 80), UN3 120-347V, Dimmable	DLC	1 90096 13161 7
SLS Linkable LED Strip			
 SLS216L840-UNV	2', 1600lm, 4000K (CRI 80), UNV, Non-dimmable		1 90096 13019 1
 SLS432L840-UNV	4', 3200lm, 4000K (CRI 80), UNV, Non-dimmable		1 90096 13020 7

 Stock Ready (2-Day Quick Ship)  Design Ready (10-Day Quick Ship)



V3W



VTC



BVL



CFW



T Series

Product	Description / Features		UPC
Vaporlume V3W LED			
■ V3W435L835-347-DIM	4', 3500lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
■ V3W435L835-UNV-DIM	4', 3500lm, 3500K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 62635 8
■ V3W435L840-347-DIM	4', 3500lm, 4000K (CRI 80), 347, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
● V3W435L840-UNV-DIM	4', 3500lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42646 0
■ V3W443L835-347-DIM	4', 4300lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
■ V3W443L835-UNV-DIM	4', 4300lm, 3500K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 62636 5
■ V3W443L840-347-DIM	4', 4300lm, 4000K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
● V3W443L840-UNV-DIM	4', 4300lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42655 2
■ V3W451L835-347-DIM	4', 5100lm, 3500K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
■ V3W451L835-UNV-DIM	4', 5100lm, 3500K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 62637 2
■ V3W451L840-347-DIM	4', 5100lm, 4000K (CRI 80), 347V, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	
■ V3W451L840-UNV-DIM	4', 5100lm, 4000K (CRI 80), UNV, 0-10V Dimming, Clear Acrylic Lens	PREMIUM	7 84197 42653 8
Accessories			
● TBK	DWAE Stainless Steel Top Bracket Kit (pair of brackets plus hardware)		7 34340 37459 9
VTC Sealed Strip LED			
● VTC436L840-UNV	4', 3600lm, 4000K (CRI 80), UNV, Non-dimmable		1 90096 13028 3
BVL Vaporlume			
● BVL254HO-UNV-1/2EB-GENRS-SS	4', T5HO 54W (2 lamps), UNV, Wet Location, Polycarbonate Lens		7 73849 36268 3
CFW Wraparound			
● CFW232-120-1/2EB-GENIS	4', 2 Lamp, T8 32W, 120V, Electronic ballast, Acrylic lens		7 73849 35503 6
T Series T8 Strip			
● T232-UNV-1/2-EB	4', 2 Lamp, T8 32W, Electronic Ballast, UNV		7 34340 60832 8
● TT232-UNV-1/4-EB	8', 4 Lamp, T8 32W, Electronic Ballast, UNV		7 34340 60834 2
Accessories			
● CG-4	T Strip 4' Wire Guard		7 82343 29605 9
● FKR-126	Chain hanger set (pair)		7 82343 18410 3
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			

Day-Brite

CFI

by Signify

Grid / Recessed

if

you need comfortable
illumination for highly
productive spaces

Choose Day-Brite CFI by Signify for a complete selection
of professional office & industrial lighting products.

Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

Day-Brite CFI

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		SlimLux Surface LED	FluxPanel LED Gen. 2 (FPZ)	Selectable Backlit Panel (SBP)	ClearAppeal LED Gen. 2 (CAX)	FluxGrid LED (FGG)	FormFlex LED (FFX)	SofTrace LED (STX)
Page Reference		pg. 24	pg. 25	pg. 26	pg. 27	pg. 28	pg. 30	pg. 31
Quick Ship Service								
Budget / Grade		Value / Good	Value / Good		Performance / Better			
Spec & Performance	Type	T-Grid Mount	Panel	Panel	Recessed Troffer	Recessed Troffer	Recessed Troffer	Recessed Troffer
	Sizes	2', 4'	1x4', 2x2', 2x4'	1x4', 2x2', 2x4'	1x4', 2x2', 2x4'	1x4', 2x2', 2x4'	1x4', 2x2', 2x4'	1x4', 2x2', 2x4'
	Depth	1-9/16" (Driver Box)	3"	1-1/2"	3-15/16"	3"	3-15/16"	3-15/16"
	Lumens (lm)	3000-3800 lm/4'	3000-4800 5400*	Selectable 3400-5800	3000-4800 5400-7400*	3000-4800 5400-9000*	3800-4800 5400-7400*	3800-4800 5400-7400*
	Efficacy (lm/W)	up to 124 (AC) up to 142 (DC)	up to 132	up to 128	up to 130	up to 125	up to 130	up to 130
	Dimming	0-10V Step* Lutron LDE5 5%* Lutron LDE1 1%*	0-10V Step* MarkX*	0-10V	0-10V Step* Lutron LDE5 5%* DALI*	0-10V Step* Lutron LDE5 5%* DALI*	0-10V Step* Lutron LDE5 5%* Lutron LDE1 1%* DALI*	0-10V Step* Lutron LDE5 5%* Lutron LDE1 1%* DALI*
	CCT (K)	3500K 4000K	3500K 4000K	Selectable 3500K 4000K 5000K	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*	3000K* 3500K 4000K 5000K*
	CRI	80	80	80	80 AccuRender 90*	80	80 AccuRender 90*	80
	Voltage (V)	120-277V 347V*	120-277V 347V	120-277V 120-347V	120-277V 347V	120-277V 347V	120-277V 347V	120-277V 347V
Controls & Options	Lens	Asymmetric reflection/refraction	Flat opal	Flat opal	Diffuse (smooth)	Diffuse (ribbed) Diffuse (smooth)	Diffuse (smooth) Diffuse perforated* Diffuse opaque* Diffuse linear prism*	Diffuse (smooth)* Diffuse (ribbed)
	Ceiling Types	NEMA G	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*	NEMA G NEMA NFG and F*	NEMA G and NFG NEMA F*	NEMA G and NFG NEMA F*
	Air Function	Chicago Plenum*	-	-	Air Return Chicago Plenum*	Air Return* Chicago Plenum*	Air Return Chicago Plenum*	Air Return Chicago Plenum*
	Interact Ready							
	SpaceWise							
	Power over Ethernet (PoE)							
Ratings & Certification	cULus Listed							
	cETLus Listed							
	IC Rated	Driver Pods with 1 and 4 lightbars only						
	DLC	Standard / Premium	Standard / Premium	Standard	Standard / Premium	Standard	Standard / Premium	Standard / Premium
	Lifetime (L70)	up to 70,000 hours	up to 90,000 hours	up to 67,000 hours	up to 87,000 hours	up to 85,000 hours	up to 87,000 hours	up to 87,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.						


Stock Ready (2-Day Quick Ship) Design Ready (10-Day Quick Ship)
 Standard Feature * Spec Ready / Additional Options Available, see spec sheet for details



SlimLux

Product	Description / Features		UPC
SlimLux Surface LED	Driver Pod		
● SL04SG38LUNVDIM1	SlimLux Surface LED Driver Pod for 1: 4' Lightbar, 3800lm/4ft, UNV DIM		7 84197 65602 7
● SL04QG38LUNVDIM1	SlimLux Surface LED Driver Pod for 4: 4' Lightbars, 3800lm/4ft, UNV DIM		7 84197 65601 0
● SL04MG38LUNVDIM1	SlimLux Surface LED Driver Pod for 8: 4' Lightbars, 3800lm/4ft, UNV DIM		7 84197 65603 4
	Lightbar		
● SL1P02835NGW	SlimLux Surface LED Lightbar, 2', 3500K (CRI 80), White		1 90096 13006 1
● SL1P02840NGW	SlimLux Surface LED Lightbar, 2', 4000K (CRI 80), White	DLC	1 90096 13004 7
● SL1P04835NGW	SlimLux Surface LED Lightbar, 4', 3500K (CRI 80), White	DLC	1 90096 13002 3
● SL1P04840NGW	SlimLux Surface LED Lightbar, 4', 4000K (CRI 80), White	DLC	1 90096 13000 9


● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Driver pods include integral clips for mounting to T-bar above the ceiling



Quick Connects to Light Bar



Quick Connect to building mains

- 1 Note that each Driver Pod is designed for the exact amount of lightbars. For example: Q pod must be installed and operated with 4 lightbars.
- 2 Single (S) driver pod is direct wire to lightbar. Quad (Q) and Oct (M) driver pods include two-port push in wire connections.
- 3 Oct (M) driver pod includes four connection ports on each side of splice box.

[Watch Video](#)




FPZ

Product	Description / Features		UPC
FluxPanel LED Gen. 2 (FPZ)			
1x4'			
■ 1FPZ30L835-4-DS-347-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ30L835-4-DS-UNV-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FPZ30L840-4-DS-347-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ30L840-4-DS-UNV-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FPZ38L835-4-DS-347-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ38L835-4-DS-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
● 1FPZ38B835-4-DS-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18001 1
■ 1FPZ38L840-4-DS-347-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ38L840-4-DS-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
● 1FPZ38B840-4-DS-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18002 8
■ 1FPZ45L835-4-DS-347-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ45L835-4-DS-UNV-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FPZ45L840-4-DS-347-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FPZ45L840-4-DS-UNV-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
2x2'			
■ 2FPZ30L835-2-DS-347-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FPZ30L835-2-DS-UNV-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ30L840-2-DS-347-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ30L840-2-DS-UNV-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ38L835-2-DS-347-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FPZ38L835-2-DS-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FPZ38L840-2-DS-347-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-2-DS-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
● 2FPZ38B835-2-DS-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18003 5
● 2FPZ38B840-2-DS-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18004 2
■ 2FPZ45L835-2-DS-347-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FPZ45L835-2-DS-UNV-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FPZ45L840-2-DS-347-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ45L840-2-DS-UNV-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



FPZ




SBP

Product	Description / Features		UPC
FluxPanel LED Gen. 2 (Continued)			
■ 2FPZ38L835-4-DS-347-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FPZ38L835-4-DS-UNV-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-4-DS-347-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ38L840-4-DS-UNV-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
● 2FPZ42B835-4-DS-UNV-DIM	2x4', 4200lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18006 6
● 2FPZ42B840-4-DS-UNV-DIM	2x4', 4200lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming (Base Configuration)	DLC	1 90096 18007 3
■ 2FPZ43L835-4-DS-347-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ43L835-4-DS-UNV-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ43L840-4-DS-347-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ43L840-4-DS-UNV-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ48L835-4-DS-347-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ48L835-4-DS-UNV-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
■ 2FPZ48L840-4-DS-347-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM	
■ 2FPZ48L840-4-DS-UNV-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM	
Selectable Backlit Panel (SBP)			
● 1SBP3040L8CS-4-UN3-DIM	1x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC	1 90096 13102 0
● 2SBP3040L8CS-2-UNV-DIM	2x2', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	DLC	1 90096 13100 6
● 2SBP3040L8CS-2-UN3-DIM	2x2', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC	1 90096 13104 4
● 2SBP350L8CS-4-UNV-DIM	2x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UNV (120-277V), 0-10V Dimming	DLC	1 90096 13101 3
● 2SBP350L8CS-4-UN3-DIM	2x4', Lumen Selectable, 3500K / 4000K / 5000K (CRI 80), UN3 (120-347V), 0-10V Dimming	DLC	1 90096 13103 7
Accessories			
● CFFSF14-PANEL	1x4' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00002 6
● CFFSF22-PANEL	2x2' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00001 9
● CFFSF24-PANEL	2x4' Surface mount field assembly kit for Select Backlit Panel (SBP)		6 26772 00003 3
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features		UPC
ClearAppeal LED Gen. 2 (CAX)			
1x4'			
■ 1CAXG30L835-4-DS-347-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG30L835-4-DS-UNV-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66954 6
■ 1CAXG30L840-4-DS-347-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG30L840-4-DS-UNV-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66962 1
■ 1CAXG38L835-4-DS-347-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG38L835-4-DS-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66955 3
■ 1CAXG38L840-4-DS-347-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG38L840-4-DS-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66963 8
■ 1CAXG45L835-4-DS-347-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG45L835-4-DS-UNV-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66956 0
■ 1CAXG45L840-4-DS-347-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1CAXG45L840-4-DS-UNV-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66964 5
2x2'			
■ 2CAXG30L835-2-DS-347-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG30L835-2-DS-UNV-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66968 3
■ 2CAXG30L840-2-DS-347-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG30L840-2-DS-UNV-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66973 7
■ 2CAXG38L835-2-DS-347-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG38L835-2-DS-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2CAXG38L840-2-DS-347-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG38L840-2-DS-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66974 4
■ 2CAXG45L835-2-DS-347-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG45L835-2-DS-UNV-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66971 3
■ 2CAXG45L840-2-DS-347-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG45L840-2-DS-UNV-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66975 1
2x4'			
■ 2CAXG38L835-4-DS-347-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG38L835-4-DS-UNV-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2CAXG38L840-4-DS-347-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG38L840-4-DS-UNV-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2CAXG43L835-4-DS-347-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG43L835-4-DS-UNV-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66981 2
■ 2CAXG43L840-4-DS-347-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG43L840-4-DS-UNV-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 66985 0
■ 2CAXG48L835-4-DS-347-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG48L835-4-DS-UNV-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2CAXG48L840-4-DS-347-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2CAXG48L840-4-DS-UNV-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	


● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



FGG

Product	Description / Features		UPC
FluxGrid LED (FGG)			
1x4'			
■ 1FGG30L835-4-DS-347-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG30L835-4-DS-UNV-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FGG30L840-4-DS-347-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG30L840-4-DS-UNV-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FGG38L835-4-DS-347-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG38L835-4-DS-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FGG38L840-4-DS-347-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG38L840-4-DS-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
● 1FGG41B835-4-D-UNV-DIM	1x4', 4100lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 20363 4
● 1FGG41B840-4-D-UNV-DIM	1x4', 4100lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 24228 2
■ 1FGG45L835-4-DS-347-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG45L835-4-DS-UNV-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 1FGG45L840-4-DS-347-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 1FGG45L840-4-DS-UNV-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
2x2'			
■ 2FGG30L835-2-DS-347-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG30L835-2-DS-UNV-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG30L835-2-D-UNV-DIM-SWZCS	2x2', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
■ 2FGG30L840-2-DS-347-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG30L840-2-DS-UNV-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG30L840-2-D-UNV-DIM-SWZCS	2x2', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
● 2FGG38B835-2-D-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 20364 1
■ 2FGG38L835-2-DS-347-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming		
■ 2FGG38L835-2-DS-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming		
■ 2FGG38L835-2-D-UNV-DIM-SWZCS	2x2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
● 2FGG38B840-2-D-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 24226 8
■ 2FGG38L840-2-DS-347-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG38L840-2-DS-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG38L840-2-D-UNV-DIM-SWZCS	2x2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
■ 2FGG45L835-2-DS-347-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming		
■ 2FGG45L835-2-DS-UNV-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming		
■ 2FGG45L840-2-DS-347-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG45L840-2-DS-UNV-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



FGG

Product	Description / Features		UPC
FluxGrid LED (FGG) (Continued)	2x4'		
■ 2FGG38L835-4-DS-347-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG38L835-4-DS-UNV-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG38L835-4-D-UNV-DIM-SWZCS	2x4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
■ 2FGG38L840-4-DS-347-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG38L840-4-DS-UNV-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG38L840-4-D-UNV-DIM-SWZCS	2x4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
● 2FGG42B835-4-D-UNV-DIM	2x4', 4200lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 20365 8
● 2FGG42B840-4-D-UNV-DIM	2x4', 4200lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming (Base Configuration)	DLC	7 84197 24223 7
■ 2FGG43L835-4-DS-347-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG43L835-4-DS-UNV-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG43L835-4-D-UNV-DIM-SWZCS	2x4', 4300lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
■ 2FGG43L840-4-DS-347-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG43L840-4-DS-UNV-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG43L840-4-D-UNV-DIM-SWZCS	2x4', 4300lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming, Interact Ready	DLC	
■ 2FGG48L835-4-DS-347-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming		
■ 2FGG48L835-4-DS-UNV-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	
■ 2FGG48L840-4-DS-347-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC	
■ 2FGG48L840-4-DS-UNV-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC	7 84197 28412 1
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



Product	Description / Features	 UPC
FormFlex LED (FFX)		
1x4'		
■ 1FFXG30L835-4-DS-347-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG30L835-4-DS-UNV-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 1FFXG30L840-4-DS-347-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG30L840-4-DS-UNV-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 1FFXG38L835-4-DS-347-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG38L835-4-DS-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 1FFXG38L840-4-DS-347-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG38L840-4-DS-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 1FFXG45L835-4-DS-347-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG45L835-4-DS-UNV-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 1FFXG45L840-4-DS-347-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 1FFXG45L840-4-DS-UNV-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
2x2'		
■ 2FFXG30L835-2-DS-347-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG30L835-2-DS-UNV-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 2FFXG30L840-2-DS-347-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG30L840-2-DS-UNV-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 2FFXG38L835-2-DS-347-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG38L835-2-DS-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 2FFXG38L840-2-DS-347-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG38L840-2-DS-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 2FFXG45L835-2-DS-347-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG45L835-2-DS-UNV-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
■ 2FFXG45L840-2-DS-347-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	DLC
■ 2FFXG45L840-2-DS-UNV-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	DLC
2x4'		
■ 2FFXG38L835-4-DS-347-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG38L835-4-DS-UNV-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
■ 2FFXG38L840-4-DS-347-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG38L840-4-DS-UNV-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
■ 2FFXG43L835-4-DS-347-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG43L835-4-DS-UNV-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
■ 2FFXG43L840-4-DS-347-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG43L840-4-DS-UNV-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
■ 2FFXG48L835-4-DS-347-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG48L835-4-DS-UNV-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
■ 2FFXG48L840-4-DS-347-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), 347V, 0-10V Dimming	PREMIUM
■ 2FFXG48L840-4-DS-UNV-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Smooth), UNV, 0-10V Dimming	PREMIUM
Recessed Luminaire Accessories		
● FMA14	1x4' Drywall Flange Kit	7 34340 77548 8
● FMA22	2x2' Drywall Flange Kit	7 34340 77547 1
● FMA24	2x4' Drywall Flange Kit	7 34340 77546 4

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



STX




TG8

Product	Description / Features		UPC
SofTrace LED (STX)			
1x4'			
■ 1STXG30L835-4-D-347-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming		
■ 1STXG30L835-4-D-UNV-DIM	1x4', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming		
■ 1STXG30L840-4-D-347-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 1STXG30L840-4-D-UNV-DIM	1x4', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 1STXG38L835-4-D-347-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 1STXG38L835-4-D-UNV-DIM	1x4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 1STXG38L840-4-D-347-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 1STXG38L840-4-D-UNV-DIM	1x4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 1STXG45L835-4-D-347-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 1STXG45L835-4-D-UNV-DIM	1x4', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 1STXG45L840-4-D-347-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 1STXG45L840-4-D-UNV-DIM	1x4', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
2x2'			
■ 2STXG30L835-2-D-347-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG30L835-2-D-UNV-DIM	2x2', 3000lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG30L840-2-D-347-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG30L840-2-D-UNV-DIM	2x2', 3000lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG38L835-2-D-347-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG38L835-2-D-UNV-DIM	2x2', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG38L840-2-D-347-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG38L840-2-D-UNV-DIM	2x2', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG45L835-2-D-347-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming		
■ 2STXG45L835-2-D-UNV-DIM	2x2', 4500lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming		
■ 2STXG45L840-2-D-347-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG45L840-2-D-UNV-DIM	2x2', 4500lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
2x4'			
■ 2STXG38L835-4-D-347-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG38L835-4-D-UNV-DIM	2x4', 3800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG38L840-4-D-347-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG38L840-4-D-UNV-DIM	2x4', 3800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG43L835-4-D-347-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG43L835-4-D-UNV-DIM	2x4', 4300lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG43L840-4-D-347-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG43L840-4-D-UNV-DIM	2x4', 4300lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG48L835-4-D-347-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG48L835-4-D-UNV-DIM	2x4', 4800lm, 3500K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
■ 2STXG48L840-4-D-347-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Ribbed), 347V, 0-10V Dimming	DLC	
■ 2STXG48L840-4-D-UNV-DIM	2x4', 4800lm, 4000K (CRI 80), Diffuse (Ribbed), UNV, 0-10V Dimming	DLC	
TG8 Recessed Lensed			
● 2TG8432-01-UNV-1/4-EB	TG8 Recessed Lensed, 2x4', 4 Lamp, T8 32W, UNV, Electronic Ballast, FS, Pattern 12 Prismatic		7 34340 97659 5
● Stock Ready (2-Day Quick Ship)	■ Design Ready (10-Day Quick Ship)		

Indoor Track & Downlighting

Environmentally-friendly, efficient indoor track and downlighting solutions that perfectly blend aesthetic and performance. With Lightolier you can confidently find the lighting solution to best suit your application and budget.

Lightolier is a global market leader widely recognized for its innovative LED lighting solutions with an unmatched commitment to technology leadership, reliability, visual appeal and high performance. The Lightolier comprehensive product offering provides you with a quick and easy way to select both downlighting and track lighting solutions that complement every lighting application.



SlimSurface LED
Round | Pg. 38

Track Head LED
| Pg. 72

Core Downlights 34

LED Quick Selection Guide 35

Flat Downlight Select LED	36
Mini Downlight LED	36
Mini Gimbal LED	36
Commercial Retrofit Downlight DualSelect	37
Retrofit Downlight LED	37

CorePro LED	37
Surface Mount Downlight LED	38
SlimSurface LED Round	38
SlimSurface LED Square	40

Downlight Kits 42

LED Quick Selection Guide 43

UniFrame	45
Accessories	45
EasyLyte LED 4" Round	46
EasyLyte LED 6" Round	47
LyteProfile LED 3" Round	48
LyteProfile LED 3" Square	48
LyteProfile LED 4" Round	49
LyteProfile LED 6" Round	50
LyteProfile LED 6" Square	50
Calculite LED 1.75" Micro	50
Calculite LED 3" Round	51
Calculite LED 3" Square	51

Calculite LED 4" Round	52
Calculite LED 4" Round Adjustable	53
Calculite LED 6" Round	54
Calculite LED 6" Square	56
Calculite LED 7" Round	56
LyteCaster LED, 3" Accent	57
LyteCaster LED 4"	58
LyteCaster LED 5"	59
LyteCaster LED 6"	60
LyteCaster Conventional	62
LytePoints Conventional	63

Track Lighting 64

LED Quick Selection Guide 65

LyteSpan Advent Track	66
LyteSpan Basic Track	66
LyteSpan Track Accessories	67
Alcyon LED Horizontal Medium Cylinder	68
Alcyon LED Vertical Medium Cylinder	68
Alcyon LED Vertical Large Cylinder	68
Alcyon LED Recessed Multiples	69
BoldFlood LED	70
CorePro LED Mini Cylinder	70

LightFlood LED	70
OmniSpot LED Track Heads (06/10)	70
OmniSpot LED Track Heads (20)	71
OmniSpot LED Recessed Multiple	71
Spot LED	72
Track Head LED	72
Conventional Track Heads	73
LyteSpan Track Head Accessories	73

LIGHTOLIER

by @signify

Core Downlights

if
you need downlights
that are easy to install
from below the ceiling

Choose Lightolier by Signify for a complete selection
of professional track and downlighting solutions.

Visit signify.com/quickship to learn more.

LIGHTOLIER

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		Flat Downlight Select LED	Mini Downlight LED & Mini Gimbal LED	Retrofit Downlight DualSelect	Retrofit Downlight LED	CorePro LED	Surface Mount Downlight LED	SlimSurface LED Round	SlimSurface LED Square
Page Reference		pg. 36	pg. 36	pg. 37	pg. 37	pg. 37	pg. 38	pg. 38	pg. 40
Quick Ship Service									
Budget / Grade		Budget / Good			Value / Better			Budget / Good	Value / Better
Applicability	Retail	1	2	3	2	3	1	3	3
	Hospitality	1	2	3	2	2	1	3	3
	Office	1	1	3	2	2	1	3	3
	Education	1	1	3	2	3	1	3	3
	Residential	3	3	2	3	3	3	3	3

Applicability Scale: 3 High / 2 Medium / 1 Low / - N/A

Trim & Finish	Types	Downlight	Downlight / Gimbal	Downlight	Downlight	Downlight	Downlight	Downlight	Downlight
	Aperture	○ 4", 6"	○ 3"	○ 4", 6", 8", 10"	○ 4", 5/6"	○ 4", 5", 6"	○ 5", 7"	○ 5", 7", 10"	□ 4", 6"
	Finish	White Black Trim Fascia* Brushed Nickel Fascia*	White Black (Gimbal Only) Brushed Nickel (Gimbal Only)*	White	White	White	White	Aluminum White Black Metal (10" only)*	Aluminum White Black
Spec & Performance	Lumens (lm)	4": 700 6": 900	550	Field Selectable 4": 500-1000lm 6": 700-1500lm 8": 1000-2000lm 10": 2000-3000lm	4": 800 5/6": 1200	4": 800 5": 950 6": 800 / 1200	5": 700 7": 1000	5": 650 7": 1000 10": 2200	4": 650 6": 1000
	Wattage (W)	12-15	8	11-16	13-18.5	11-16	10-15	9-28	9-28
	Efficacy (lm/W)	up to 70	up to 69	up to 93	up to 76	up to 89	up to 69	up to 94	up to 94
	CCT (K)	Selectable 2700K 3000K 4000K 5000K	3000K 4000K	Selectable 3000K 3500K 4000K	3000K	3000K 4000K	3000K	2700K 3000K 3500K 4000K	2700K 3000K 3500K 4000K
	CRI	90	90	90	90	80 / 90	90	80 / 90	80 / 90
	Dimming	0-10V	TRIAC	0-10V		TRIAC	TRIAC	0-10V ELV / TRIAC	0-10V ELV / TRIAC
Ratings & Certification	Installations	New Construction Remodeler Wet locations	New Construction Remodeler Wet locations	Wet locations	Wet locations	Wet locations	New Construction Remodeler Wet locations	Wet locations Damp locations (10")	Wet locations Damp locations (10")
	Certification	cULus Listed	cETLus Listed	cULus Listed	cULus Listed	cULus Listed	cETLus Listed	cULus Listed	cULus Listed
	IC Rated	✓	✓	✓	✓	✓	✓		
	Title 24 Rated	✓	✓	✓	✓	✓	✓	✓	✓
	AirSeal IC rated	✓	✓	✓		✓			
	Energy Star	✓	✓	✓	✓	✓	✓	✓	✓
	Lifetime (L70)	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 42,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.							

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



FD



MD



MG

Product	Description / Features		UPC
Fiat Downlight Select LED			
● FD4R4CCT	4" Round, 700lm, 2700K / 3000K / 4000K / 5000K (CRI 90), 120V, White	★	7 84197 68127 2
● FD6R4CCT	6" Round, 900lm, 2700K / 3000K / 4000K / 5000K (CRI 90), 120V, White	★	7 84197 68128 9
Accessories			
● FD10EC	10' Extension Cord		1 90096 13121 1
● FD4NCP	4" New Construction Plate		1 90096 13119 8
● FD4TBK	4" Trim Black		1 90096 13122 8
● FD4TBN	4" Trim Brushed Nickel		1 90096 13124 2
● FD6NCP	6" New Construction Plate		1 90096 13120 4
● FD6TBK	6" Trim Black		1 90096 13123 5
● FD6TBN	6" Trim Brushed Nickel		1 90096 13125 9
Mini Downlight LED			
● MD3R069301FW	3", 550lm, 3000K (CRI 90), Flood, White	★	1 90096 01740 9
● MD3R069401FW	3", 550lm, 4000K (CRI 90), Flood, White	★	1 90096 01741 6
Mini Gimbal LED			
● MG3R06930NF1W	3", 550lm, 3000K (CRI 90), Narrow Flood, White	★	1 90096 01727 0
● MG3R06940NF1W	3", 550lm, 4000K (CRI 90), Narrow Flood, White	★	1 90096 01730 0
Accessories			
● MDRN	Mini Downlight / Mini Gimbal New Construction Plate, 3" Round		1 90096 01735 5
● MD20C	Mini Downlight / Mini Gimbal 20' Extension Cord	★	1 90096 01734 8
● MD06C	Mini Downlight / Mini Gimbal 6' Extension Cord	★	1 90096 01733 1
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



CR



RD



CP4R

Product	Description / Features		UPC
Commercial Retrofit Downlight DualSelect			
● CR4RLMCCT	4" Round, 500-1000lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	★	1 90096 13126 6
● CR6RLMCCT	6" Round, 700-1500lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	★	1 90096 13127 3
● CR8RLMCCT	8" Round, 1000-2000lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	★	1 90096 13128 0
● CR10RLMCCT	9.5" Round, 2000-3000lm, 3000K / 3500K / 4000K (CRI 90), 120-347V	★	1 90096 13129 7
Retrofit Downlight LED			
● RD4R089301W	4" Round, 800lm, 3000K (CRI 90), 120V	★	1 90096 01638 9
● RD5R129301W	5/6" Round, 1200lm, 3000K (CRI 90), 120V	★	1 90096 01639 6
CorePro LED 4"			
● CP4RR	4" Remodeler Housing, IC c/w LED, Connector	★	6 62057 93910 0
● CP4RN	4" New Construction Housing, IC c/w LED Connector	★	6 62057 93909 4
● CP4RB07830W	4", 800lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93901 8
■ CP4RB07930W	4", 800lm, 3000K (CRI 90), 120V, White, 10% TRIAC Dimming		6 62057 93900 1
● CP4RB07840W	4", 800lm, 4000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93902 5
5"			
● CP5RN	5" New Construction Housing, IC c/w LED, Connector	★	6 62057 93911 7
● CP5RR	5" Remodeler Housing, IC c/w LED, Connector	★	6 62057 93912 4
● CP5RB07830W	5", 1000lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93904 9
■ CP5RB08930W	5", 1000lm, 3000K (CRI 90), 120V, White, 10% TRIAC Dimming		6 62057 93903 2
● CP5RB08840W	5", 1000lm, 4000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93905 6
6"			
● CP6RR	6" Remodeler Housing, IC c/w LED, Connector	★	6 62057 93914 8
● CP6RN	6" New Construction Housing, IC c/w LED Connector	★	6 62057 93913 1
● CP6RB10830W	6", 1200lm, 3000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93907 0
● CP6RB10840W	6", 1250lm, 4000K (CRI 80), 120V, White, 10% TRIAC Dimming	★	6 62057 93908 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



SD



S5R (Aluminum)



S5R (Black)



S5R (White)



S7R (White)

Product	Description / Features		UPC
Surface Mount Downlight LED			
● SD5R079301W	5" Round, 700lm, 3000K (CRI 90), 120V	★	1 90096 01642 6
● SD7R099301W	7" Round, 1000lm, 3000K (CRI 90), 120V	★	1 90096 01643 3
SlimSurface LED Round			
5" Round, 650lm, 2700K (CRI 80)			
■ S5R827K7AL	5" Round, 650lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98868 9
■ S5R827K7ALZ10U	5" Round, 650lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95255 0
■ S5R827K7BK	5" Round, 650lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94339 8
■ S5R827K7BKZ10U	5" Round, 650lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95256 7
■ S5R827K7WZ10U	5" Round, 650lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95254 3
5" Round, 650lm, 2700K (CRI 90)			
■ S5R927K7AL	5" Round, 650lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98871 9
■ S5R927K7ALZ10U	5" Round, 650lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95267 3
■ S5R927K7BK	5" Round, 650lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming	★	6 62057 94353 4
■ S5R927K7BKZ10U	5" Round, 650lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming	★	6 62057 95268 0
■ S5R927K7	5" Round, 650lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	6 62057 98870 2
■ S5R927K7WZ10U	5" Round, 650lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	6 62057 95266 6
5" Round, 650lm, 3000K (CRI 80)			
■ S5R830K7AL	5" Round, 650lm, 3000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98869 6
■ S5R830K7ALZ10U	5" Round, 650lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95258 1
■ S5R830K7BK	5" Round, 650lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94340 4
■ S5R830K7BKZ10U	5" Round, 650lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95259 8
■ S5R830K7WZ10U	5" Round, 650lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95257 4
● S5R830K7	5" Round, 600lm, 3000K (CRI 80), 120V, White, ELV / Triac (120V) Dimming	★	6 62057 93605 5
5" Round, 650lm, 3500K (CRI 80)			
■ S5R835K7ALZ10U	5" Round, 650lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95261 1
■ S5R835K7AL	5" Round, 650lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98549 7
■ S5R835K7BKZ10U	5" Round, 650lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95262 8
■ S5R835K7BK	5" Round, 650lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94341 1
■ S5R835K7WZ10U	5" Round, 650lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95260 4
● S5R835K7	5" Round, 650lm, 3500K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98548 0
5" Round, 650lm, 4000K (CRI 80)			
■ S5R840K7AL	5" Round, 650lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98552 7
■ S5R840K7ALZ10U	5" Round, 650lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95264 2
■ S5R840K7BK	5" Round, 650lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94342 8
■ S5R840K7BKZ10U	5" Round, 650lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95265 9
● S5R840K7	5" Round, 650lm, 4000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98551 0
■ S5R840K7WZ10U	5" Round, 650lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95263 5
SlimSurface LED Round			
7" Round, 1000lm, 2700K (CRI 80)			
■ S7R827K10ALZ10U	7" Round, 1000lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95285 7
■ S7R827K10AL	7" Round, 1000lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98873 3
■ S7R827K10BKZ10U	7" Round, 1000lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95286 4
■ S7R827K10BK	7" Round, 1000lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94347 3
■ S7R827K10WZ10U	7" Round, 1000lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95284 0
■ S7R827K10	7" Round, 1000lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98872 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



S7R (White)



S10R (White)

Product	Description / Features		UPC
7" Round, 1000lm, 2700K (CRI 90)			
■ S7R927K10ALZ10U	7" Round, 1000lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95297 0
■ S7R927K10AL	7" Round, 1000lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98877 1
■ S7R927K10BKZ10U	7" Round, 1000lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming	★	6 62057 95298 7
■ S7R927K10BK	7" Round, 1000lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming	★	6 62057 94355 8
■ S7R927K10WZ10U	7" Round, 1000lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	6 62057 95296 3
■ S7R927K10	7" Round, 1000lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	6 62057 98876 4
7" Round, 1000lm, 3000K (CRI 80)			
■ S7R830K10ALZ10U	7" Round, 1000lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95288 8
■ S7R830K10BKZ10U	7" Round, 1000lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95289 5
■ S7R830K10BK	7" Round, 1000lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 98002 7
■ S7R830K10WZ10U	7" Round, 1000lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95287 1
● S7R830K10	7" Round, 1000lm, 3000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98874 0
■ S7R930K10	7" Round, 1000lm, 3000K (CRI 90), White, ELV / Triac (120V) Dimming	★	1 90096 03717 9
7" Round, 1000lm, 3500K (CRI 80)			
■ S7R835K10ALZ10U	7" Round, 1000lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95291 8
■ S7R835K10AL	7" Round, 1000lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98558 9
■ S7R835K10BKZ10U	7" Round, 1000lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95292 5
■ S7R835K10BK	7" Round, 1000lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94348 0
■ S7R835K10WZ10U	7" Round, 1000lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95290 1
■ S7R835K10	7" Round, 1000lm, 3500K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98557 2
7" Round, 1000lm, 4000K (CRI 80)			
■ S7R840K10ALZ10U	7" Round, 1000lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95294 9
■ S7R840K10AL	7" Round, 1000lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98560 2
■ S7R840K10BKZ10U	7" Round, 1000lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95295 6
■ S7R840K10BK	7" Round, 1000lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94349 7
■ S7R840K10WZ10U	7" Round, 1000lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95293 2
SlimSurface LED Round			
10" Round, 2200lm, 2700K (CRI 80)			
■ S10R827K22WZ10U	10" Round, 2200lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06395 6
■ S10R827K22W	10" Round, 2200lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	1 90096 08736 5
10" Round, 2200lm, 2700K (CRI 90)			
■ S10R927K22WZ10U	10" Round, 2200lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	1 90096 06393 2
■ S10R927K22W	10" Round, 2200lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	1 90096 08740 2
10" Round, 2200lm, 3000K (CRI 80)			
■ S10R830K22WZ10U	10" Round, 2200lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06396 3
10" Round, 2200lm, 3000K (CRI 90)			
■ S10R930K22WZ10U	10" Round, 2200lm, 3000K (CRI 90), White, 0-10V (120-277V) Dimming	★	1 90096 06394 9
■ S10R930K22W	10" Round, 2200lm, 3000K (CRI 90), White, ELV / Triac (120V) Dimming	★	1 90096 08741 9
10" Round, 2200lm, 3500K (CRI 80)			
■ S10R835K22WZ10U	10" Round, 2200lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	1 90096 06397 0

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



S4S (Aluminum)



S4S (Black)



S4S (White)

Product	Description / Features		UPC
SlimSurface LED Square	4" Square, 650lm, 2700K (CRI 80)		
■ S4S827K7ALZ10U	4" Square, 650lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95240 6
■ S4S827K7AL	4" Square, 650lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98879 5
■ S4S827K7BKZ10U	4" Square, 650lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95241 3
■ S4S827K7BK	4" Square, 650lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94332 9
■ S4S827K7WZ10U	4" Square, 650lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95239 0
■ S4S827K7	4" Square, 650lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98878 8
	4" Square, 650lm, 2700K (CRI 90)		
■ S4S927K7ALZ10U	4" Square, 650lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95252 9
■ S4S927K7AL	4" Square, 650lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98883 2
■ S4S927K7BKZ10U	4" Square, 650lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming	★	6 62057 95253 6
■ S4S927K7BK	4" Square, 650lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming	★	6 62057 94352 7
■ S4S927K7WZ10U	4" Square, 650lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	6 62057 95251 2
■ S4S927K7	4" Square, 650lm, 2700K (CRI 90), White, ELV / Triac (120V) Dimming	★	6 62057 98882 5
	4" Square, 650lm, 3000K (CRI 80)		
■ S4S830K7ALZ10U	4" Square, 650lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95243 7
■ S4S830K7AL	4" Square, 650lm, 3000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98881 8
■ S4S830K7BKZ10U	4" Square, 650lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95244 4
■ S4S830K7BK	4" Square, 650lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94335 0
■ S4S830K7WZ10U	4" Square, 650lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95242 0
■ S4S830K7	4" Square, 650lm, 3000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98880 1
	4" Square, 650lm, 3500K (CRI 80)		
■ S4S835K7ALZ10U	4" Square, 650lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95246 8
■ S4S835K7AL	4" Square, 650lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98545 9
■ S4S835K7BKZ10U	4" Square, 650lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95247 5
■ S4S835K7BK	4" Square, 650lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94336 7
■ S4S835K7WZ10U	4" Square, 650lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95245 1
	4" Square, 650lm, 4000K (CRI 80)		
■ S4S840K7ALZ10U	4" Square, 650lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95249 9
■ S4S840K7AL	4" Square, 650lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98547 3
■ S4S840K7BKZ10U	4" Square, 650lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95250 5
■ S4S840K7BK	4" Square, 650lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94338 1
■ S4S840K7WZ10U	4" Square, 650lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95248 2

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



S6S (Aluminum)



S6S (Black)



S6S (White)

Product	Description / Features		UPC
SlimSurface LED Square			
6" Square, 1000lm, 2700K (CRI 80)			
■ S6S827K10ALZ10U	6" Square, 1000lm, 2700K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95270 3
■ S6S827K10AL	6" Square, 1000lm, 2700K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98885 6
■ S6S827K10BKZ10U	6" Square, 1000lm, 2700K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95271 0
■ S6S827K10BK	6" Square, 1000lm, 2700K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94343 5
■ S6S827K10WZ10U	6" Square, 1000lm, 2700K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95269 7
■ S6S827K10	6" Square, 1000lm, 2700K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98884 9
6" Square, 1000lm, 2700K (CRI 90)			
■ S6S927K10ALZ10U	6" Square, 1000lm, 2700K (CRI 90), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95282 6
■ S6S927K10AL	6" Square, 1000lm, 2700K (CRI 90), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98889 4
■ S6S927K10BKZ10U	6" Square, 1000lm, 2700K (CRI 90), Black, 0-10V (120-277V) Dimming	★	6 62057 95283 3
■ S6S927K10BK	6" Square, 1000lm, 2700K (CRI 90), Black, ELV / Triac (120V) Dimming	★	6 62057 94354 1
■ S6S927K10WZ10U	6" Square, 1000lm, 2700K (CRI 90), White, 0-10V (120-277V) Dimming	★	6 62057 95281 9
6" Square, 1000lm, 3000K (CRI 80)			
■ S6S830K10ALZ10U	6" Square, 1000lm, 3000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95273 4
■ S6S830K10AL	6" Square, 1000lm, 3000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98887 0
■ S6S830K10BKZ10U	6" Square, 1000lm, 3000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95274 1
■ S6S830K10BK	6" Square, 1000lm, 3000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94344 2
■ S6S830K10WZ10U	6" Square, 1000lm, 3000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95272 7
■ S6S830K10	6" Square, 1000lm, 3000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98886 3
6" Square, 1000lm, 3500K (CRI 80)			
■ S6S835K10ALZ10U	6" Square, 1000lm, 3500K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95276 5
■ S6S835K10AL	6" Square, 1000lm, 3500K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98554 1
■ S6S835K10BKZ10U	6" Square, 1000lm, 3500K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95277 2
■ S6S835K10BK	6" Square, 1000lm, 3500K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94345 9
■ S6S835K10WZ10U	6" Square, 1000lm, 3500K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95275 8
■ S6S835K10	6" Square, 1000lm, 3500K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98553 4
6" Square, 1000lm, 4000K (CRI 80)			
■ S6S840K10ALZ10U	6" Square, 1000lm, 4000K (CRI 80), Aluminum, 0-10V (120-277V) Dimming	★	6 62057 95279 6
■ S6S840K10AL	6" Square, 1000lm, 4000K (CRI 80), Aluminum, ELV / Triac (120V) Dimming	★	6 62057 98556 5
■ S6S840K10BKZ10U	6" Square, 1000lm, 4000K (CRI 80), Black, 0-10V (120-277V) Dimming	★	6 62057 95280 2
■ S6S840K10BK	6" Square, 1000lm, 4000K (CRI 80), Black, ELV / Triac (120V) Dimming	★	6 62057 94346 6
■ S6S840K10WZ10U	6" Square, 1000lm, 4000K (CRI 80), White, 0-10V (120-277V) Dimming	★	6 62057 95278 9
■ S6S840K10	6" Square, 1000lm, 4000K (CRI 80), White, ELV / Triac (120V) Dimming	★	6 62057 98555 8

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

LIGHTOLIER

by **Signify**

Downlight Kits

if
you want to
shape lighting
to suit a space

Choose Lightolier by Signify for a complete selection of professional track and downlighting solutions. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

LyteProfile LED 3" Square | Pg. 48

LIGHTOLIER

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)

       								
Product Family	EasyLyte LED	LyteProfile LED Accent	LyteProfile LED	Calculite LED Micro	Calculite LED Accent	Calculite LED	LyteCaster LED Accent	LyteCaster LED
Page Reference	pg. 46	pg. 48	pg. 49	pg. 50	pg. 50	pg. 52	pg. 58	pg. 59
Quick Ship Service	■	● ■	● ■	● ■	● ■	■	■	■
Budget / Grade	Value / Better			Spec / Best			Budget / Good	
Aperture	○ 4", 6"	○ □ 3"	○ □ 4", 6"	○ □ 1.75"	○ □ 3"	○ □ 4", 6", 7"	○ □ 3"	○ □ 4", 5", 6"
Reflector Finish	Clear Diffuse Black* White Dark Bronze*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White*	Comfort Clear Diffuse Black* White* Champagne Bronze*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White* Champagne Bronze* Aluminum Diffuse* Bronze*	Specular Clear Comfort Clear Comfort Clear Diffuse Black* White* Champagne Bronze*	Chrome Diffuse White White Baffle Aluminum (Shower Trim Only)	Clear Diffuse White
Cutoff / Accent Adjustment	70° Direct	Downlight / Wall Wash 60° Direct Adj. Accent 40° Tilt	Downlight / Wall Wash 60° Direct	50° Direct 75° Direct*	50° Direct	50° Direct 45° Reflected 45° Tilt	Accent 60° Direct 60° Reflected Adj. Accent 35° Tilt	Downlight 30° Adjustment
Lumens (lm)	500-3500	500-1500	500-3500	900	500-1000	500-6000	800	650-2000
Efficacy (lm/W)	up to 100	up to 74	up to 100	up to 85	up to 87	up to 115		up to 90
Dimming	0-10V 1% ELV Lutron LDE1*	0-10V 1% ELV Lutron PEQ0*	0-10V 1% Lutron LDE1*	0-10V 1% ELV	0-10V 1% ELV Lutron PEQ0*	0-10V 1% ELV* DALI 0.1%* Lutron LDE1* DMX*	0-10V ELV / TRIAC	0-10V ELV / TRIAC
CCT (K)	2700K* 3000K 3500K 4000K	2700K* 3000K 3500K 4000K*	2700K* 3000K 3500K 4000K 5000K* Dim to Warm*	2700K 3000K 3500K* 4000K*	2700K* 3000K 3500K 4000K* Dim to Warm	2700K* 3000K 3500K 4000K	2700K 3000K 3500K	2700K 3000K 3500K 4000K
CRI (SDCM)	80 (3)	90 (3)	80 (3)	90 (2)	90 (2)	90 (2)	80-90 (3)	80-90 (3)
Dim to Warm		◆			■ ◆	◆		
Interact Ready	◆	◆	◆		◆	◆		◆
SpaceWise	◆	◆	◆		◆	◆		
IntelliHue						◆		
POE	◆		◆		◆	◆		
Frame / Installation (NC - New Construction)	NC (UniFrame) NC AirSeal (IC)* Remodeler*	NC (UniFrame) NC AirSeal (IC)* Remodeler*	NC (UniFrame) NC AirSeal (IC)* Remodeler*	Integral NC Frame (Non-IC) NC (IC)	NC (UniFrame) NC (Non-IC) NC (IC)	NC (UniFrame) NC AirSeal (IC)*	NC (non-IC)* NC AirSeal (IC)*	NC AirSeal (IC) Remodeler AirSeal (IC)*
Ratings	cULus / IC Rated	cULus / IC / Title 24 Rated	cULus / IC Rated		cULus Listed	cULus Listed	cULus Listed	cULus Listed
Energy Star	✓	✓	✓			✓	✓	✓
Lifetime	up to 60,000 hours (L70)	up to 60,000 hours (L70)	up to 60,000 hours (L80)	up to 90,700 hours (L90)	up to 57,000 hours (L70)	up to 60,000 hours (L80)		up to 50,000 hours
Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.							


● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)
✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details

One frame for maximum flexibility

The **Lightolier** single frame solution architecture, is adaptable and designed around ever-changing project needs. Three unique downlight families all use this same frame. Your choices and flexibility are now endless.

- **Modular plug-and-play** receptacle enables quick and easy tool-free installation
- **Configurable solutions** mean installation can start sooner and be completed in stages
- **Future-proof** modular design allows easy upgrades without ceiling disturbance
- Unexpected design changes have **minimal schedule impact and waste**

Option available for **Interact Pro** wireless control.
For more information visit www.interact-lighting.com/pro


[Watch Video](#)


EasyLyte

Light Commercial
2-part system
(pg. 46-46)



LyteProfile

Commercial
2-part system
(pg. 48-50)



Calculite

Specification
3-part system
(pg. 50-56)

Reflector



CL Specular clear

Most specular and therefore most efficient finish, delivers maximum photometric performance but can produce a mirror image effect of the interior space.



CC Comfort clear

Semi-specular finish that softens the light at the source of the reflector and creates a subtle, even luminance from the reflector cone.



CD Comfort clear diffuse

Slightly diffuse clear finish, which eliminates iridescence and reduces the mirror image effect inherent with specular finishes.



CZ Champagne bronze

Semi-specular finish that softens the light at the source of the reflector while providing a warmer reflector appearance (light output is slightly warmer).



WH White (matte)

Brightest aperture when illuminated and provides the smoothest transition to most ceilings when off (white is only available with a white flange).



BK Black (matte)

Specular finish that provides the lowest aperture brightness possible and significantly reduces source identification in a ceiling.

Flange



- White (matte)

Provides the smoothest transition to ceilings when off.



P Polished (matches aperture)

Produces a continuous look throughout the reflector (aperture matching).



F Flangeless (flush-mount)

Creates a flush, virtually seamless transition from aperture to ceiling.

Note: Not all finishes are available for all trims (refer to specification sheet for availability). When handling reflectors, use clean white or plastic film gloves to avoid fingerprints. Specular surfaces can be cleaned by the following methods: Wipe off with soft clean, dry lint-free cloth; or wipe off with a soft cloth dampened in mild detergent solution, rinse, then wipe dry with lint-free cloth or paper towel; or wipe off with clean cloth dampened with a solution of wetting agent and water (such as 2 oz. per gallon "Pluronic L62-LF" by Wynandotte Products or liquid such as Glass Wax) then wipe dry with a lint-free cloth or paper towel. Avoid gritty cleaning agents.

Product	Description / Features	ENERGY STAR	UPC
UniFrame	3"		
■ 3RA	3" Round, AirSeal IC, UNV		7 84197 66617 0
■ 3RN	3" Round, New Construction (Non-IC), UNV	★	7 84197 66612 5
■ 3RNIP	3" Round, New Construction (Non-IC), UNV, Interact Ready	★	7 84197 66613 2
■ 3SA	3" Square, AirSeal IC (1000lm max), Standard, UNV	★	7 84197 68678 9
■ 3SAS	3" Square, AirSeal IC (1000lm max), Shallow, UNV	★	7 84197 68679 6
■ 3SN	3" Square, New Construction (Non-IC), UNV	★	7 84197 66618 7
■ 3SNIP	3" Square, New Construction (Non-IC), UNV, Interact Ready		7 84197 66619 4
4"			
■ 4RA	4" Round, AirSeal IC, UNV		7 84197 24057 8
● 4RN	4" Round, New Construction (Non-IC), UNV	★	7 84197 64192 4
■ 4RN3	4" Round, New Construction (Non-IC), 347V		7 84197 21139 4
■ 4RNEM	4" Round, New Construction (Non-IC), Emergency		7 84197 64193 1
■ 4RNIP	4" Round, New Construction (Non-IC), UNV, Interact Ready	★	1 90096 01751 5
■ 4RR	4" Round, Remodeler (Non-IC), UNV		7 84197 21145 5
■ 4RR3	4" Round, Remodeler (Non-IC), 347V	★	7 84197 21146 2
■ 4SA	4" Square, AirSeal IC, UNV		7 84197 24059 2
● 4SN	4" Square, New Construction (Non-IC), UNV	★	7 84197 64195 5
■ 4SN3	4" Square, New Construction (Non-IC), 347V		7 84197 21148 6
■ 4SNEM	4" Square, New Construction (Non-IC), Emergency		7 84197 64196 2
■ 4SR	4" Square, Remodeler (Non-IC), UNV		7 84197 21151 6
■ 4SR3	4" Square, Remodeler (Non-IC), 347V		
6"			
■ 6RA	6" Round, AirSeal IC, UNV		7 84197 24060 8
● 6RN	6" Round, New Construction (Non-IC), UNV	★	7 84197 64197 9
■ 6RNIP	6" Round, New Construction (Non-IC), UNV, Interact Ready	★	1 90096 01755 3
■ 6RR3	6" Round, Remodeler (Non-IC), 347V	★	7 84197 21164 6
■ 6RN3	6" Round, New Construction (Non-IC), 347V		7 84197 21154 7
■ 6RNEM	6" Round, New Construction (Non-IC), Emergency		7 84197 64198 6
■ 6RR	6" Round, Remodeler (Non-IC), UNV		7 84197 21163 9
■ 6SA	6" Square, AirSeal IC, UNV		7 84197 24061 5
● 6SN	6" Square, New Construction (Non-IC), UNV	★	7 84197 64200 6
■ 6SN3	6" Square, New Construction (Non-IC), 347V		7 84197 21166 0
■ 6SNEM	6" Square, New Construction (Non-IC), Emergency		7 84197 64201 3
■ 6SR	6" Square, Remodeler (Non-IC), UNV		
■ 6SR3	6" Square, Remodeler (Non-IC), 347V		7 84197 21170 7
7"			
■ 7RN	7" Round, New Construction (Non-IC), UNV		7 84197 70574 9
■ 7RN3	7" Round, New Construction (Non-IC), 347V		7 84197 70575 6
■ 7RNLC	7" Round, New Construction (Non-IC), Chicago Plenum		7 84197 70576 3
■ C7RNEM	7" Round, New Construction (Non-IC), Emergency		7 84197 21173 8
Accessories			
● 1950	Mounting Bars 18" Set of (2) (Order in Multiples of 12)		7 84197 14500 2
● 1951	Mounting Bars 27" Set of (2) (Order in Multiples of 12)		7 84197 14503 3
● 1956	Set of 4 Mounting Bar Clips		7 84197 14513 2
■ 7994	Set of 2 Telescoping Mounting Bars-Calculite		7 84197 28904 1
■ CLAEM1520	Calculite LED Field-Wire EM-Pack 1500/2000 Lumen		6 62057 50303 5
● VBE300	Vapor Barrier for 9" IC Box		7 84197 34371 2
● Stock Ready (2-Day Quick Ship)	■ Design Ready (10-Day Quick Ship)		



Z4RDL (OCD)



Z4RDL (OWH)



Z4RDL (SWH)

Product	Description / Features	ENERGY STAR	UPC
EasyLyte LED 4" Round	Frames		
See all Lightolier UniFrame options compatible with EasyLyte LED on pg. 45			
1000lm			
■ Z4RDL10835WOCZ10U	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10307 2
■ Z4RDL10835WOCDE1	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10658 5
■ Z4RDL10835WOWHZ10U	4" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10657 8
■ Z4RDL10840WOCZ10U	4" Round, 1000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10663 9
■ Z4RDL10840WOCDE1	4" Round, 1000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10662 2
1500lm			
■ Z4RDL15830WOCZ10U	4" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10323 2
■ Z4RDL15830WOCDE1	4" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10667 7
■ Z4RDL15835WOCZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10309 6
■ Z4RDL15835WOCDE1	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10308 9
■ Z4RDL15835WOWHZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10669 1
■ Z4RDL15835WOWHE1	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, ELV Dimming, 120V	★	1 90096 10668 4
■ Z4RDL15835WSWHZ10U	4" Round, 1500lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10343 0
■ Z4RDL15840WOCZ10U	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10310 2
■ Z4RDL15840WOCDE1	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10675 2
■ Z4RDL15840WOWHZ10U	4" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10674 5
2000lm			
■ Z4RDL20830WOCZ10U	4" Round, 2000lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10680 6
■ Z4RDL20835WOCDE1	4" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10682 0
■ Z4RDL20835WOWHZ10U	4" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10681 3
■ Z4RDL20840WOCZ10U	4" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10687 5
■ Z4RDL20840WOCDE1	4" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10686 8
2500lm			
■ Z4RDL25835WOCZ10U	4" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10690 5
■ Z4RDL25840WOCZ10U	4" Round, 2500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10692 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Z6RDL (OCD)



Z6RDL (OWH)



Z4RDL (SWH)

Product	Description / Features	ENERGY STAR	UPC
EasyLyte LED 6" Round	Frames		
See all Lightolier UniFrame options compatible with EasyLyte LED on pg. 45			
1000lm			
■ Z6RDL10840WOCDDZ10U	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10697 4
■ Z6RDL10835WOCDE1	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10695 0
■ Z6RDL10835WOWHZ10U	6" Round, 1000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10694 3
1500lm			
■ Z6RDL15830WOCDDZ10U	6" Round, 1500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10700 1
■ Z6RDL15835WOCDE1	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10313 3
■ Z6RDL15835WOWHZ10U	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10328 7
■ Z6RDL15835WSWHZ10U	6" Round, 1500lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10703 2
■ Z6RDL15840WOCDE1	6" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10707 0
■ Z6RDL15840WOWHZ10U	6" Round, 1500lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10706 3
2000lm			
■ Z6RDL20830WOCDDZ10U	6" Round, 2000lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10712 4
■ Z6RDL20830WOCDE1	6" Round, 2000lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10711 7
■ Z6RDL20835WOCDE1	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10316 4
■ Z6RDL20835WOWHZ10U	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10715 5
■ Z6RDL20835WOWHE1	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, ELV Dimming, 120V	★	1 90096 10714 8
■ Z6RDL20835WSWHZ10U	6" Round, 2000lm, 3500K (CRI 80), Wide Beam, Step Baffle, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10718 6
■ Z6RDL20840WOCDDZ10U	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open downlight, Clear diffuse finish, 0-10V 1% Dimming, UNV	★	1 90096 10319 5
■ Z6RDL20840WOCDE1	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, ELV Dimming, 120V	★	1 90096 10721 6
■ Z6RDL20840WOWHZ10U	6" Round, 2000lm, 4000K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10720 9
2500lm			
■ Z6RDL25830WOCDDZ10U	6" Round, 2500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10728 5
■ Z6RDL25835WOCDDZ10U	6" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10320 1
■ Z6RDL25835WOWHZ10U	6" Round, 2500lm, 3500K (CRI 80), Wide Beam, Open, Matte White Reflector, 0-10V 1% Dimming, UNV	★	1 90096 10729 2
3500lm			
■ Z6RDL35830WOCDDZ10U	6" Round, 3500lm, 3000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10743 8
■ Z6RDL35835WOCDDZ10U	6" Round, 3500lm, 3500K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10322 5
■ Z6RDL35840WOCDDZ10U	6" Round, 3500lm, 4000K (CRI 80), Wide Beam, Open, Clear Diffuse, 0-10V 1% Dimming, UNV	★	1 90096 10746 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



P3RDL



P3RA



P3RLW



P3SLW



P3SA

Product	Description / Features	ENERGY STAR	UPC
LyteProfile LED 3" Round			
Frames			
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45			
1000lm			
■ P3RDL10935CCZ10U	3" Round, 1000lm, 3500K (CRI 90), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		7 84197 66644 6
■ P3RDL10935WHZ10U	3" Round, 1000lm, 3500K (CRI 90), White Reflector, White flange, 0-10V 1% Dimming, UNV		7 84197 69013 7
1500lm			
■ P3RDL15930CCZ10U	3" Round, 1500lm, 3000K (CRI 90), Comfort Clear Finish, White flange, 0-10V 1% Dimming, UNV		7 84197 66647 7
■ P3RDL15935CCZ10U	3" Round, 1500lm, 3500K (CRI 90), Comfort Clear Finish, White flange, 0-10V 1% Dimming, UNV		7 84197 66648 4
Adjustable Accent, 1000lm			
■ P3RA10930NFCDPZ10U	3" Round (Adjustable Accent), 1000lm, 3000K (CRI 90), Narrow Flood (21°), Comfort Clear Diffuse Finish, Matching Flange, 0-10V 1% Dimming, UNV		7 84197 69024 3
■ P3RA10930NFCPPZ10U	3" Round (Adjustable Accent), 1000lm, 3000K (CRI 90), Narrow Flood (21°), Comfort Clear Finish, Matching Flange, 0-10V 1% Dimming, UNV		7 84197 69023 6
Wall Wash, 1000lm			
■ P3RLW10930CCZ10U	3" Round (Wall Wash), 1000lm, 3000K (CRI 90), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		7 84197 66649 1
■ P3RLW10935CCZ10U	3" Round (Wall Wash), 1000lm, 3500K (CRI 90), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		7 84197 66650 7
LyteProfile LED 3" Square			
Frames			
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45			
1000lm			
■ P3SDL10930CCE1	3" Square, 1000lm, 3000K (CRI 90), Comfort Clear finish, White Flange, ELV Dimming, 120V		7 84197 68713 7
Wall Wash, 1000lm			
■ P3SLW10935CCZ10U	3" Square (Wall Wash), 1000lm, 3500K (CRI 90), Comfort Clear finish, White Flange, 0-10V 1% Dimming, UNV		7 84197 68724 3
Adjustable Accent, 1000lm			
■ P3SA10935NFCCE1	3" Square (Adjustable Accent), 1000lm, 3500K (CRI 90), Narrow Flood (21°), Comfort Clear finish, White Flange, ELV Dimming, 120V		7 84197 68735 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



P4RDL (CC)



P4RDL (CD)



P4RLW (CD)

Product	Description / Features	ENERGY STAR	UPC
LyteProfile LED 4" Round	Frames		
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45			
1000lm			
● P4RDL10830CCZ10U	4" Round, 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10257 0
● P4RDL10835CCZ10U	4" Round, 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10544 1
1500lm			
■ P4RDL15830CCZ10U	4" Round, 1500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10260 0
■ P4RDL15835CCZ10U	4" Round, 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10440 6
■ P4RDL15840CDZ10U	4" Round, 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10559 5
■ P4RDL15840CLZ10U	4" Round, 1500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10558 8
2000lm			
■ P4RDL20830CDZ10U	4" Round, 2000lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10566 3
■ P4RDL20830CCZ10U	4" Round, 2000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10262 4
■ P4RDL20835CCZ10U	4" Round, 2000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10263 1
2500lm			
■ P4RDL25830CCZ10U	4" Round, 2500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10572 4
■ P4RDL25835CCZ10U	4" Round, 2500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10573 1
Wall Wash, 500lm			
■ P4RLW05830CLZ10U	4" Round (Wall Wash), 500lm, 3000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11251 7
■ P4RLW05835CLZ10U	4" Round (Wall Wash), 500lm, 3500K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11258 6
■ P4RLW05840CLZ10U	4" Round (Wall Wash), 500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11265 4
Wall Wash, 1000lm			
■ P4RLW10830CDZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11353 8
■ P4RLW10830CCZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11349 1
■ P4RLW10830CLZ10U	4" Round (Wall Wash), 1000lm, 3000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11351 4
■ P4RLW10835CDZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11360 6
■ P4RLW10835CCZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11356 9
■ P4RLW10835CLZ10U	4" Round (Wall Wash), 1000lm, 3500K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11358 3
■ P4RLW10840CDZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11367 5
■ P4RLW10840CCZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11363 7
■ P4RLW10840CLZ10U	4" Round (Wall Wash), 1000lm, 4000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11365 1
Wall Wash, 1500lm			
■ P4RLW15830CDZ10U	4" Round (Wall Wash), 1500lm, 3000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11380 4
■ P4RLW15830CLZ10U	4" Round (Wall Wash), 1500lm, 3000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11378 1
■ P4RLW15835CDZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11476 4
■ P4RLW15835CCZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		7 84197 68174 6
■ P4RLW15835CLZ10U	4" Round (Wall Wash), 1500lm, 3500K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11474 0
■ P4RLW15840CDZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11482 5
■ P4RLW15840CCZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		7 84197 68175 3
■ P4RLW15840CLZ10U	4" Round (Wall Wash), 1500lm, 4000K (CRI 80), Specular Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 11480 1

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



P6RDL (CC)



P6RDL (CD)



P6RLW (CD)



P6SDL



C2L



Product	Description / Features		UPC
LyteProfile LED 6" Round			
Frames			
See all Lightolier UniFrame options compatible with LyteProfile LED on pg. 45			
Downlight			
● P6RDL10830CCZ10U	6" Round, 1000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10575 5
● P6RDL10835CCZ10U	6" Round, 1000lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 12821 1
■ P6RDL10840CDZ10U	6" Round, 1000lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10577 9
■ P6RDL10840CCZ10U	6" Round, 1000lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10576 2
■ P6RDL15830CCZ10U	6" Round, 1500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10581 6
■ P6RDL15840CDZ10U	6" Round, 1500lm, 4000K (CRI 80), Comfort Clear Diffuse finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10584 7
■ P6RDL15840CCZ10U	6" Round, 1500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10583 0
■ P6RDL20830CCZ10U	6" Round, 2000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV	★	1 90096 10271 6
■ P6RDL25830CCZ10U	6" Round, 2500lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10589 2
■ P6RDL25840CCZ10U	6" Round, 2500lm, 4000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10883 1
■ P6RDL30830CCZ10U	6" Round, 3000lm, 3000K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10590 8
Wall Wash			
■ P6RLW20830CCZ10U	6" Round (Wall Wash), 2000lm, 3000K (CRI 80), Comfort Clear finish		7 84197 68176 0
■ P6RLW20835CCZ10U	6" Round (Wall Wash), 2000lm, 3500K (CRI 80), Comfort Clear finish		7 84197 68177 7
■ P6RLW20840CCZ10U	6" Round (Wall Wash), 2000lm, 4000K (CRI 80), Comfort Clear finish		7 84197 68178 4
LyteProfile LED 6" Square			
■ P6SDL15835CCZ10U	6" Square, 1500lm, 3500K (CRI 80), Comfort Clear finish, White flange, 0-10V 1% Dimming, UNV		1 90096 10623 3
Calculite LED 1.75" Micro			
Frame			
■ C2LIC	1.75" Micro Frame, IC Frame (new construction)		6 62057 63446 3
■ C2L04DL30K25R1	1.75" Micro Frame, 400lm, Downlight Flanged, 3000K, 25° Beam Spread, Remodeler, 120V		6 62057 57451 6
■ C2L04DL30K25RUZ10V	1.75" Micro Frame, 400lm, Downlight Flanged, 3000K, 25° Beam Spread, Remodeler, 0-10V 1% Dimming		6 62057 74181 9
LED			
■ C2L09DL927RZ10U	1.75" Micro, 900lm, Flanged, 2700K (CRI 90), Remodeler, 0-10V 1% Dimming, UNV		1 90096 01711 9
■ C2L09DL927RE1	1.75" Micro, 900lm, Flanged, 2700K (CRI 90), Remodeler, ELV Dimming, 120V		1 90096 01715 7
● C2L09DL930RZ10U	1.75" Micro, 900lm, Flanged, 3000K (CRI 90), Remodeler, 0-10V 1% Dimming, UNV		190096017126
■ C2L09DL930RE1	1.75" Micro, 900lm, Flanged, 3000K (CRI 90), Remodeler, ELV Dimming, 120V	★	1 90096 01716 4
Trims & Accessories			
■ C2LDLCCDP	1.75" Micro Trim, Downlight (50° Cutoff), Comfort Clear Diffuse Reflector, Polished Flange		6 62057 57477 6
■ CA2FMR	1.75" Micro Accessory, Round aperture flush-mount mud-in ring		6 62057 56997 0
■ CA2X2FMR	1.75" Micro Accessory, Square aperture flush-mount mud-in ring		6 62057 62549 2
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



C3L / C3R



C3L / C3RA



C3L / C3SA



C3L / C3SDL



Product	Description / Features	ENERGY STAR	UPC
Calculite LED 3" Round			
Frames			
See all Lightolier UniFrame options compatible with Calculite LED on pg. 45			
Downlight			
■ C3LO7930ME1R	3", 750lm, 3000K (CRI 90), ELV, 120V, Remodeler		7 84197 68685 7
■ C3L109D2WWE1	3", 1000lm, 3000K-1800K (CRI 90) Dim to Warm, Wide (62°), ELV Dimming, 120V		7 84197 69009 0
■ C3L10930MZ10U	3", 1000lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66622 4
■ C3L10930ME1S	3", 1000lm, 3000K (CRI 90), Medium (55°), ELV Dimming, 120V, Shallow Plenum		7 84197 66630 9
■ C3L10935MZ10U	3", 1000lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66623 1
■ C3L10935ME1S	3", 1000lm, 3500K (CRI 90), Medium (55°), ELV Dimming, 120V, Shallow Plenum		7 84197 66631 6
■ C3L15930MZ10U	3", 1500lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66624 8
■ C3L15935MZ10U	3", 1500lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66625 5
■ C3L18935MZ10U	3", 1800lm, 3500K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66627 9
■ C3L20930MZ10U	3", 2000lm, 3000K (CRI 90), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 66626 2
Adjustable			
■ C3RA15935NFZ10U	3" Round Adjustable, 1500lm, 3500K (CRI 90), Narrow Flood (23°), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 68696 3
Trims & Accessories			
■ C3RACC	3" Trim Round Adjustable, Clear Comfort Reflector, White (matte) Flange		7 84197 68702 1
■ C3RACCP	3" Trim Round Adjustable, Clear Comfort Reflector, Polished Flange		7 84197 68703 8
■ C3RDLCC	3" Trim Round Downlight, Clear Comfort Reflector, White (matte) Flange		7 84197 66632 3
■ C3RDLWH	3" Trim Round Downlight, White (matte) Reflector, White (matte) Flange		7 84197 68999 5
■ C3RLWCC	3" Trim Round Lensed Wall Wash, Clear Comfort Reflector, White (matte) Flange		7 84197 66635 4
■ C3RLWWH	3" Trim Round Lensed Wall Wash, White (matte) Reflector, White (matte) Flange		7 84197 69000 7
■ CA3RAAFT	3", Accessory, Round Mud-in ring for flangeless installs (ordered with a flangeless trim)		1 90096 01794 2
Calculite LED 3" Square			
Frames			
See all Lightolier UniFrame options compatible with Calculite LED on pg. 45			
Downlight			
■ C3L10935SZ10U	3" Square, 1000lm, 3500K (CRI 90), 0-10V 1% Dimming, UNV (120/277/347V)		7 84197 69007 6
Trims & Accessories			
● C3SACC	3" Trim Square Adjustable, Clear Comfort Reflector, White (matte) Flange		7 84197 68704 5
■ C3SDLMCC	3" Trim Square Downlight, Medium (59°), Clear Comfort Reflector, White (matte) Flange		7 84197 66633 0
■ C3SDLWCC	3" Trim Square Downlight, Wide (71°), Clear Comfort Reflector, White (matte) Flange		7 84197 66634 7
■ C3SDLWDPS	3" Trim Square Downlight, Wide (71°), Aluminum Diffuse Reflector, White Flange (1" regress cast aluminum)		7 84197 66640 8
■ C3SLWCC	3" Trim Square Lens Wall Washed, Clear Comfort Reflector, White (matte) Flange		7 84197 66636 1
■ CA3SAAFT	3", Accessory, Square Mud-in ring for flangeless installs (ordered with a flangeless trim)		1 90096 01795 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



C4RA



C4L

Product	Description / Features	UPC
Calculite LED 4" Round	Frame	
■ C4RA	4" Frame, Round, AirSeal (IC), UNV (120/277V)	7 84197 24057 8
	See all Lightolier UniFrame options compatible with Calculite LED on pg. 45	
	LED	
■ C4L05830MZ10U	4", 500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97447 7
■ C4L05830NZ10U	4", 500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97443 9
■ C4L05830WZ10U	4", 500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97451 4
■ C4L05835MZ10U	4", 500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97448 4
■ C4L05835NZ10U	4", 500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97444 6
■ C4L05835WZ10U	4", 500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97452 1
■ C4L05840MZ10U	4", 500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97449 1
■ C4L05840NZ10U	4", 500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97445 3
■ C4L05840WZ10U	4", 500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97453 8
■ C4L10830MZ10U	4", 1000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97483 5
■ C4L10830NZ10U	4", 1000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97479 8
■ C4L10830WZ10U	4", 1000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97487 3
■ C4L10835MZ10U	4", 1000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97484 2
■ C4L10835NZ10U	4", 1000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97480 4
■ C4L10835WZ10U	4", 1000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97488 0
■ C4L10840MZ10U	4", 1000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97485 9
■ C4L10840NZ10U	4", 1000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97481 1
■ C4L10840WZ10U	4", 1000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97489 7
■ C4L15830MZ10U	4", 1500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97534 4
■ C4L15830NZ10U	4", 1500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97530 6
■ C4L15830WZ10U	4", 1500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97538 2
■ C4L15835MZ10U	4", 1500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97535 1
■ C4L15835NZ10U	4", 1500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97531 3
■ C4L15835WZ10U	4", 1500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97539 9
■ C4L15840NZ10U	4", 1500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97532 0
■ C4L15840WZ10U	4", 1500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97540 5
■ C4L20830MZ10U	4", 2000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97582 5
■ C4L20830NZ10U	4", 2000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97578 8
■ C4L20830WZ10U	4", 2000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97586 3
■ C4L20835MZ10U	4", 2000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97583 2
■ C4L20835NZ10U	4", 2000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97579 5
■ C4L20835WZ10U	4", 2000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97587 0
■ C4L20840MZ10U	4", 2000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97584 9
■ C4L20840NZ10U	4", 2000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97580 1
■ C4L20840WZ10U	4", 2000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97588 7
■ C4L25830MZ10U	4", 2500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97660 0
■ C4L25830NZ10U	4", 2500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97656 3
■ C4L25830WZ10U	4", 2500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97664 8

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



C4L



C4RDLCDP



C4RDLWHF



C4RWWCDP

Product	Description / Features	ENERGY STAR	UPC
Calulite LED 4" Round			
LED (Continued)			
■ C4L25835MZ10U	4", 2500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97661 7
■ C4L25835NZ10U	4", 2500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97657 0
■ C4L25835WZ10U	4", 2500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97665 5
■ C4L25840MZ10U	4", 2500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97662 4
■ C4L25840NZ10U	4", 2500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97658 7
■ C4L25840WZ10U	4", 2500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97666 2
■ C4L30830MZ10U	4", 3000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		1 90096 02766 8
■ C4L30830NZ10U	4", 3000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97709 6
■ C4L30830WZ10U	4", 3000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97717 1
■ C4L30835MZ10U	4", 3000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97714 0
■ C4L30835NZ10U	4", 3000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97710 2
■ C4L30835WZ10U	4", 3000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97718 8
■ C4L30840MZ10U	4", 3000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97715 7
■ C4L30840NZ10U	4", 3000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97711 9
■ C4L30840WZ10U	4", 3000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)		6 62057 97719 5
Trims			
■ C4RDLCDF	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Flangeless		6 62057 97241 1
■ C4RDLCDP	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Polished Flange		6 62057 97236 7
■ C4RDLCD	4" Trim, Round Downlight, Clear Comfort Diffuse Reflector, White (matte) Flange		6 62057 97230 5
■ C4RDLCCF	4" Trim, Round Downlight, Clear Comfort Reflector, Flangeless		6 62057 97239 8
■ C4RDLCCP	4" Trim, Round Downlight, Clear Comfort Reflector, Polished Flange		6 62057 97234 3
■ C4RDLCC	4" Trim, Round Downlight, Clear Comfort Reflector, White (matte) Flange		6 62057 97200 8
■ C4RDLCLF	4" Trim, Round Downlight, Specular Clear Reflector, Flangeless		6 62057 97240 4
■ C4RDLCLP	4" Trim, Round Downlight, Specular Clear Reflector, Polished Flange		6 62057 97235 0
■ C4RDLCL	4" Trim, Round Downlight, Specular Clear Reflector, White (matte) Flange		6 62057 97229 9
■ C4RDLWHF	4" Trim, Round Downlight, White (matte) Reflector, Flangeless		1 90096 02217 5
■ C4RDLWH	4" Trim, Round Downlight, White (matte) Reflector, White (matte) Flange		1 90096 02215 1
■ C4RWWCDF	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, Flangeless		6 62057 96522 2
■ C4RWWCDP	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, Polished Flange		6 62057 96517 8
■ C4RWWCD	4" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, White (matte) Flange		6 62057 96502 4
■ C4RWWCCF	4" Trim, Round Open Wall Wash, Clear Comfort Reflector, Flangeless		6 62057 96520 8
■ C4RWWCCP	4" Trim, Round Open Wall Wash, Clear Comfort Reflector, Polished Flange		6 62057 96515 4
■ C4RWWCLF	4" Trim, Round Open Wall Wash, Specular Clear Reflector, Flangeless		6 62057 96521 5
■ C4RWWCL	4" Trim, Round Open Wall Wash, Specular Clear Reflector, White (matte) Flange		6 62057 96501 7
Calulite LED 4" Round Adjustable			
■ C4LA15NUZ10V	4" Adjustable Accent Frame (1500lm), New Construction (Non-IC), UNV (120/277V), 0-10V 1% Dimming		6 62057 91441 1
LED			
■ C4L15A35K8FL	4" Adjustable Accent, 1500lm, 3500K (CRI 80), Flood (29°)		6 62057 91420 6
Trim			
■ C4LACCLW	4" Adjustable Accent, Comfort Clear Reflector, White (Matte) Flange		6 62057 91404 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



C4RA



C6L

Product	Description / Features	UPC
		
Calculate LED 6" Round	Frame	
■ C6RA	6" Frame, Round, AirSeal (IC), UNV (120/277V)	7 84197 24060 8
See all Lightolier UniFrame options compatible with Calculate LED on pg. 45		
LED		
■ C6L10830MZ10U	6", 1000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97761 4
■ C6L10830NZ10U	6", 1000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97757 7
■ C6L10830WZ10U	6", 1000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97765 2
■ C6L10835MZ10U	6", 1000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97762 1
■ C6L10835NZ10U	6", 1000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97758 4
■ C6L10835WZ10U	6", 1000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97766 9
■ C6L10840MZ10U	6", 1000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97763 8
■ C6L10840NZ10U	6", 1000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97759 1
■ C6L10840WZ10U	6", 1000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97767 6
■ C6L15830MZ10U	6", 1500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97809 3
■ C6L15830NZ10U	6", 1500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97805 5
■ C6L15830WZ10U	6", 1500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97813 0
■ C6L15835NZ10U	6", 1500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97806 2
■ C6L15835WZ10U	6", 1500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97814 7
■ C6L15840MZ10U	6", 1500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97811 6
■ C6L15840NZ10U	6", 1500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97807 9
■ C6L15840WZ10U	6", 1500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97815 4
■ C6L20830MZ10U	6", 2000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97953 3
■ C6L20830NZ10U	6", 2000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97908 3
■ C6L20830WZ10U	6", 2000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97992 2
■ C6L20835NZ10U	6", 2000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97909 0
■ C6L20835WZ10U	6", 2000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97993 9
■ C6L20840MZ10U	6", 2000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97963 2
■ C6L20840NZ10U	6", 2000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97910 6
■ C6L20840WZ10U	6", 2000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 97997 7
■ C6L25830MZ10U	6", 2500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98203 8
■ C6L25830NZ10U	6", 2500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98185 7
■ C6L25830WZ10U	6", 2500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98218 2
■ C6L25835MZ10U	6", 2500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98215 1
■ C6L25835NZ10U	6", 2500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98186 4
■ C6L25835WZ10U	6", 2500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98220 5
■ C6L25840MZ10U	6", 2500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98216 8
■ C6L25840NZ10U	6", 2500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98187 1
■ C6L25840WZ10U	6", 2500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98221 2
■ C6L35830MZ10U	6", 3500lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98344 8
■ C6L35830NZ10U	6", 3500lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98339 4
■ C6L35830WZ10U	6", 3500lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98375 2

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



C6L



C6RDLCDP



C6RDLWHF



C6RWWCDP

Product	Description / Features	UPC
		
Calculate LED 6" Round	LED (Continued)	
■ C6L35835MZ10U	6", 3500lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98345 5
■ C6L35835NZ10U	6", 3500lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98341 7
■ C6L35835WZ10U	6", 3500lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98376 9
■ C6L35840MZ10U	6", 3500lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98350 9
■ C6L35840NZ10U	6", 3500lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98342 4
■ C6L35840WZ10U	6", 3500lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 98379 0
■ C6L48830MZ10U	6", 4800lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 99999 9
■ C6L48830NZ10U	6", 4800lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 99586 1
■ C6L48830WZ10U	6", 4800lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02174 1
■ C6L48835MZ10U	6", 4800lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02002 7
■ C6L48835NZ10U	6", 4800lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 99587 8
■ C6L48835WZ10U	6", 4800lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02175 8
■ C6L48840MZ10U	6", 4800lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02172 7
■ C6L48840NZ10U	6", 4800lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	6 62057 99589 2
■ C6L48840WZ10U	6", 4800lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02177 2
■ C6L60830MZ10U	6", 6000lm, 3000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02196 3
■ C6L60830NZ10U	6", 6000lm, 3000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02192 5
■ C6L60830WZ10U	6", 6000lm, 3000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02200 7
■ C6L60835MZ10U	6", 6000lm, 3500K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02197 0
■ C6L60835NZ10U	6", 6000lm, 3500K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02193 2
■ C6L60835WZ10U	6", 6000lm, 3500K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02201 4
■ C6L60840MZ10U	6", 6000lm, 4000K (CRI 80), Medium (55°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02198 7
■ C6L60840NZ10U	6", 6000lm, 4000K (CRI 80), Narrow (38/40°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02194 9
■ C6L60840WZ10U	6", 6000lm, 4000K (CRI 80), Wide (68/72°), 0-10V 1% Dimming, UNV (120/277/347V)	1 90096 02202 1
Trims & Accessories		
■ C6RDLCDF	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Flangeless	6 62057 97299 2
■ C6RDLCDP	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, Polished Flange	6 62057 97294 7
■ C6RDLCD	6" Trim, Round Downlight, Clear Comfort Diffuse Reflector, White (matte) Flange	6 62057 97288 6
■ C6RDLCCF	6" Trim, Round Downlight, Clear Comfort Reflector, Flangeless	6 62057 97297 8
■ C6RDLCCP	6" Trim, Round Downlight, Clear Comfort Reflector, Polished Flange	6 62057 97292 3
■ C6RDLCC	6" Trim, Round Downlight, Clear Comfort Reflector, White (matte) Flange	6 62057 97286 2
■ C6RDLCLF	6" Trim, Round Downlight, Specular Clear Reflector, Flangeless	6 62057 97298 5
■ C6RDLCLP	6" Trim, Round Downlight, Specular Clear Reflector, Polished Flange	6 62057 97293 0
■ C6RDLCL	6" Trim, Round Downlight, Specular Clear Reflector, White (matte) Flange	6 62057 97287 9
■ C6RDLWHF	6" Trim, Round Downlight, White (matte) Reflector, Flangeless	1 90096 02245 8
■ C6RDLWH	6" Trim, Round Downlight, White (matte) Reflector, White (matte) Flange	1 90096 02243 4
■ C6RWWCD	6" Trim, Round Open Wall Wash, Clear Comfort Diffuse Reflector, White (matte) Flange	6 62057 96636 6
■ C6RWWCC	6" Trim, Round Open Wall Wash, Clear Comfort Reflector, White (matte) Flange	6 62057 96634 2
■ C6RWWWHF	6" Trim, Round Open Wall Wash, White (matte) Reflector, Flangeless	1 90096 02248 9
■ C6RWWWH	6" Trim, Round Open Wall Wash, White (matte) Reflector, White (matte) Flange	1 90096 02246 5
■ CA6RFT	6" Round Mud-in ring for use in flangeless trim installations (ordered with a flangeless trim)	1 90096 03031 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



C6SDL



C7RWWC DP



C7RDLWCL

Product	Description / Features	UPC
		
Calculite LED 6" Square	Frames	
	See all Lightolier UniFrame options compatible with Calculite LED on pg. 45	
	Trims	
■ C6SDLNMCC	6" Trim, Square Downlight, Narrow & Medium Beam, Clear Comfort Reflector, White (matte) Flange	6 62057 97183 4
■ C6SDLWCC	6" Trim, Square Downlight, Wide Beam, Clear Comfort Reflector, White (matte) Flange	6 62057 97315 9
	Accessory	
■ CA6SFT	6" Square Mud-in ring for use in flangeless trim installations (ordered with a flangeless trim)	1 90096 03032 3
Calculite LED 7" Round	Frames	
	See all Lightolier UniFrame options compatible with Calculite LED on pg. 45	
	Trims	
■ C7RDLNMWH	7" Trim, Round Downlight, Narrow & Medium Beam, White (matte) Reflector, White (matte) Flange	1 90096 02275 5
■ C7RDLNMCDP	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Diffuse Reflector, Polished Flange	6 62057 97082 0
■ C7RDLNMCD	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Diffuse Reflector, White (matte) Flange	6 62057 97076 9
■ C7RDLNMCCP	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Reflector, Polished Flange	6 62057 97080 6
■ C7RDLNMCC	7" Trim, Round Downlight, Narrow & Medium Beam, Clear Comfort Reflector, White (matte) Flange	6 62057 97074 5
■ C7RDLNMCL	7" Trim, Round Downlight, Narrow & Medium Beam, Specular Clear Reflector, White (matte) Flange	6 62057 97075 2
■ C7RDLWCD	7" Trim, Round Downlight, Wide Beam, Clear Comfort Diffuse Reflector, White (matte) Flange	6 62057 97093 6
■ C7RDLWCC	7" Trim, Round Downlight, Wide Beam, Clear Comfort Reflector, White (matte) Flange	6 62057 97091 2
■ C7RDLWCL	7" Trim, Round Downlight, Wide Beam, Specular Clear Reflector, White (matte) Flange	6 62057 97092 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Discover the full range of specification downlighting products available in the Calculite LED family online at lightolier.com





L3AE1



Light Engine

Product	Description / Features	ENERGY STAR	UPC
LyteCaster LED, 3" Accent			
Frames			
■ L3AE1	New Construction (Non-IC), ELV/TRIAC, 120V		6 62057 99932 6
■ L3NZ10U	New Construction (Non-IC), 0-10V Dimming, 120-277V		6 62057 99945 6
LED			
■ L308827F	3" Accent, 800lm, 2700K (CRI 80), Flood (33°)		6 62057 99799 5
■ L308827NF	3" Accent, 800lm, 2700K (CRI 80), Narrow Flood (22°)		6 62057 99798 8
■ L308927NF	3" Accent, 800lm, 2700K (CRI 90), Narrow Flood (22°)		6 62057 99818 3
■ L308830S	3" Accent, 800lm, 3000K (CRI 80), Spot (17°)		6 62057 99800 8
■ L308835F	3" Accent, 800lm, 3500K (CRI 80), Flood (33°)	★	6 62057 99813 8
■ L308835NF	3" Accent, 800lm, 3500K (CRI 80), Narrow Flood (22°)	★	6 62057 99812 1
Trims			
■ L3RAPA	3" Accent Trim, Round / Adjustable Pinhole, Aluminum		6 62057 99786 5
■ L3RAPW	3" Accent Trim, Round / Adjustable Pinhole, White		6 62057 99785 8
■ L3RAD	3" Accent Trim, Round / Adjustable, Diffuse Cone with white flange		6 62057 99766 7
■ L3RABW	3" Accent Trim, Round / Baffle Adjustable, White Baffle with white flange		6 62057 99764 3
■ L3RGA	3" Accent Trim, Round / Gimbal, Aluminum		6 62057 99784 1
■ L3RGB	3" Accent Trim, Round / Gimbal, Black		6 62057 99783 4
■ L3RLWC	3" Accent Trim, Round / Lensed Wall Wash, Chrome Cone with white flange		6 62057 99770 4
■ L3RLWD	3" Accent Trim, Round / Lensed Wall Wash, Diffuse Cone with white flange		6 62057 99771 1
■ L3RLWW	3" Accent Trim, Round / Lensed Wall Wash, White Cone with white flange		6 62057 99772 8
■ L3RSA	3" Accent Trim, Round / Shower Light, Aluminum		6 62057 99769 8
■ L3SADA	3" Accent Trim, Square / Adjustable, Diffuse Cone with aluminum flange		6 62057 99777 3
■ L3SAD	3" Accent Trim, Square / Adjustable, Diffuse Cone with white flange		6 62057 99776 6
■ L3SDDA	3" Accent Trim, Square / Downlight, Diffuse Cone with aluminum flange		6 62057 99774 2
■ L3SLWA	3" Accent Trim, Square / Lensed Wall Wash, Aluminum		6 62057 99779 7
■ L3SLWW	3" Accent Trim, Square / Lensed Wall Wash, White		6 62057 99778 0
■ L3SSA	3" Accent Trim, Square / Shower Light, Aluminum		6 62057 99781 0
■ L3SSW	3" Accent Trim, Square / Shower Light, White		6 62057 99780 3
Accessories			
■ L3SD	3" Accent Accessory, 5° Soft Diffusion Film		1 90096 13525 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Adjustable Trim



Downlight Trim



Gimbal Trim



Lensed Wall Wash



Shower Light, Aluminum



Housing



Remodeler



LED



LED Adjustable

Product	Description / Features	ENERGY STAR	UPC
LyteCaster LED 4"			
■ L4RANZ10UVA	4" Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV, Version A	★	6 62057 94176 9
■ L4RANE1VA	4" Housing, New construction with nails (AirSeal IC), ELV, 120V, Version A	★	6 62057 94165 3
■ L4R10ANZ10UVA	4" (1000lm) Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV 120-277V, Version A		6 62057 95206 2
■ L4R10RE1VA	4" (1000lm) Housing, Remodeler, ELV Dimming, 120V, Version A		1 90096 01960 1
LED			
■ L4R06827VA	4", 650lm, 2700K (CRI 80), Version A		6 62057 99871 8
■ L4R06835VA	4", 650lm, 3500K (CRI 80), Version A	★	6 62057 99874 9
■ L4R06840VA	4", 650lm, 4000K (CRI 80), Version A		6 62057 99938 8
■ L4R10927VA	4", 1000lm, 2700K (CRI 90), Version A		6 62057 95091 4
■ L4R10835VA	4", 1000lm, 3500K (CRI 80), Version A		6 62057 95089 1
■ L4R10840VA	4", 1000lm, 4000K (CRI 80), Version A		6 62057 95090 7
LED Adjustable			
■ L4RA06830WVA	4" Adjustable, 650lm, 3000K (CRI 80), White with white flange, Version A		6 62057 94105 9
■ L4RA06840WVA	4" Adjustable, 650lm, 4000K (CRI 80), White with white flange, Version A		6 62057 94107 3
LyteCaster LED 4"			
LED Adjustable (Continued)			
■ L4RA10827WVA	4" Adjustable, 1000lm, 2700K (CRI 80), White with white flange, Version A		6 62057 95190 4
■ L4RA10927WVA	4" Adjustable, 1000lm, 2700K (CRI 90), White with white flange, Version A		6 62057 95194 2
■ L4RA10830WVA	4" Adjustable, 1000lm, 3000K (CRI 80), White with white flange, Version A		6 62057 95191 1
■ L4RA10835WVA	4" Adjustable, 1000lm, 3500K (CRI 80), White with white flange, Version A		6 62057 95192 8
■ L4RA10840WVA	4" Adjustable, 1000lm, 4000K (CRI 80), White with white flange, Version A		6 62057 95193 5
Trims			
● L4RDD	4" Trim, Round / Downlight, Clear diffuse with white flange		6 62057 99370 6
● L4RDW	4" Trim, Round / Downlight, White with white flange		6 62057 99371 3
■ L4SBW	4" Trim, Square / Baffle Downlight, White with White Flange		1 90096 03142 9
■ L4SDD	4" Trim, Square / Downlight, Clear Diffuse with White Flange		1 90096 03139 9

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



L4RDD



L4RDW



L4SDD



Housing



Remodeler



LED



LED Adjustable

Product	Description / Features	ENERGY STAR	UPC
LyteCaster LED 5"			
■ L5RANZ10UVA	5" Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV, Version A	★	6 62057 94171 4
■ L5RANE1VA	5" Housing, New construction with nails (AirSeal IC), ELV, 120V, Version A	★	6 62057 94170 7
■ L5R10RE1VA	5" (1000lm) Housing, Remodeler, ELV Dimming, 120V, Version A		1 90096 01956 4
■ L5R15ANZ10UVA	5" (1500lm) Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV 120-277V, Version A		6 62057 95210 9
LED			
■ L5R10827VA	5", 1000lm, 2700K (CRI 80), Version A		6 62057 94109 7
● L5R10830VA	5", 1000lm, 3000K (CRI 80), Version A	★	6 62057 94110 3
● L5R10835VA	5", 1000lm, 3500K (CRI 80), Version A	★	6 62057 94111 0
■ L5R10840VA	5", 1000lm, 4000K (CRI 80), Version A		6 62057 94112 7
■ L5R15827VA	5", 1500lm, 2700K (CRI 80), Version A		6 62057 95092 1
■ L5R15927VA	5", 1500lm, 2700K (CRI 90), Version A		6 62057 95096 9
■ L5R15840VA	5", 1500lm, 4000K (CRI 80), Version A		6 62057 95095 2
LED Adjustable			
■ L5RA10927WVA	5" Adjustable, 1000lm, 2700K (CRI 90), White with white flange, Version A		6 62057 94118 9
■ L5RA10830WVA	5" Adjustable, 1000lm, 3000K (CRI 80), White with white flange, Version A		6 62057 94115 8
■ L5RA10835WVA	5" Adjustable, 1000lm, 3500K (CRI 80), White with white flange, Version A		6 62057 94116 5
■ L5RA10840WVA	5" Adjustable, 1000lm, 4000K (CRI 80), White with white flange, Version A		6 62057 94117 2
■ L5RA15827WVA	5" Adjustable, 1500lm, 2700K (CRI 80), White with white flange, Version A		6 62057 95195 9
■ L5RA15927WVA	5" Adjustable, 1500lm, 2700K (CRI 90), White with white flange, Version A		6 62057 95199 7
■ L5RA15830WVA	5" Adjustable, 1500lm, 3000K (CRI 80), White with white flange, Version A		6 62057 95196 6
■ L5RA15835WVA	5" Adjustable, 1500lm, 3500K (CRI 80), White with white flange, Version A		6 62057 95197 3
■ L5RA15840WVA	5" Adjustable, 1500lm, 4000K (CRI 80), White with white flange, Version A		6 62057 95198 0
Trims			
■ L5RBW	5" Trim, Round / Downlight, Baffle white with white flange		6 62057 99383 6
● L5RDD	5" Trim, Round / Downlight, Clear diffuse with white flange		6 62057 99384 3
● L5RDW	5" Trim, Round / Downlight, White with white flange		6 62057 99385 0
■ L5SBW	5" Trim, Square / Baffle Downlight, White with White Flange		1 90096 03143 6
■ L5SDD	5" Trim, Square / Downlight, Clear Diffuse with White Flange		1 90096 03140 5
■ L5SDW	5" Trim, Square / Downlight, White with White Flange		1 90096 03137 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



L5RBW



L5RDD



L6RDW



L5SDD



Housing



LED



LED Adjustable

Product	Description / Features	ENERGY STAR	UPC
LyteCaster LED 6"			
■ L6RANZ10UVA	6" (1500lm) Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV 120-277V, Version A		6 62057 99970 8
■ L6R20ANZ10UVA	6" (2000lm) Housing, New construction with nails (AirSeal IC), 0-10V Dimming, UNV 120-277V, Version A		6 62057 95214 7
LED			
■ L6R15827VA	6", 1500lm, 2700K (CRI 80), Version A		6 62057 94119 6
■ L6R15835VA	6", 1500lm, 3500K (CRI 80), Version A	★	6 62057 94121 9
■ L6R15840VA	6", 1500lm, 4000K (CRI 80), Version A		6 62057 94122 6
■ L6R20827VA	6", 2000lm, 2700K (CRI 80), Version A		6 62057 95097 6
■ L6R20927VA	6", 2000lm, 2700K (CRI 90), Version A		6 62057 95101 0
■ L6R20840VA	6", 2000lm, 4000K (CRI 80), Version A		6 62057 95100 3
LED Adjustable			
■ L6RA15927WVA	6" Adjustable, 1500lm, 2700K (CRI 90), White with white flange, Version A		6 62057 94128 8
■ L6RA15830WVA	6" Adjustable, 1500lm, 3000K (CRI 80), White with white flange, Version A		6 62057 94125 7
■ L6RA15840WVA	6" Adjustable, 1500lm, 4000K (CRI 80), White with white flange, Version A		6 62057 94127 1
■ L6RA20827WVA	6" Adjustable, 2000lm, 2700K (CRI 80), White with white flange, Version A		6 62057 95200 0
■ L6RA20927WVA	6" Adjustable, 2000lm, 2700K (CRI 90), White with white flange, Version A		6 62057 95204 8
■ L6RA20830WVA	6" Adjustable, 2000lm, 3000K (CRI 80), White with white flange, Version A		6 62057 95201 7
■ L6RA20835WVA	6" Adjustable, 2000lm, 3500K (CRI 80), White with white flange, Version A		6 62057 95202 4
■ L6RA20840WVA	6" Adjustable, 2000lm, 4000K (CRI 80), White with white flange, Version A		6 62057 95203 1
Trims			
■ L6RBW	6" Trim, Round / Downlight, Baffle white with white flange		6 62057 99398 0
● L6RDD	6" Trim, Round / Downlight, Clear diffuse with white flange		6 62057 99399 7
● L6RDW	6" Trim, Round / Downlight, White with white flange		6 62057 99400 0
■ L6SBW	6" Trim, Square / Baffle Downlight, White with White Flange		1 90096 03144 3
■ L6SDD	6" Trim, Square / Downlight, Clear Diffuse with White Flange		1 90096 03141 2

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



L6RBW



L6RDD



L6RDW



L6SDD



2003RS




L3RPF / L3RPNF / L3RPS



L3AHW



0089L / 0092L




0089S / 0092S

Product	Description / Features	ENERGY STAR	UPC
LyteCaster Conventional			
■ 2003RS	3.75", Non-IC Remodeler		7 84197 17614 3
■ 2076WH	3.75" Trim, Gloss White Baffle, Gloss White Flange		6 62057 20608 0
■ L3RPF	3.75" Replacement Optic, Flood		6 62057 99822 0
■ L3RPNF	3.75" Replacement Optic, Narrow Flood		6 62057 99821 3
■ L3RPS	3.75" Replacement Optic, Spot		6 62057 99820 6
■ L3LS	3.75" Accent Linear Spread Film		1 90096 13516 5
■ L3AHB	3.75" Accent Accessory Holder, Black		6 62057 99788 9
■ L3AHW	3.75" Accent Accessory Holder, White		6 62057 99787 2
● 0089L	New Construction Plate, 3" Round (Long)		6 24563 16007 2
● 0089S	New Construction Plate, 3" Round (Short)		6 24563 10769 5
4"			
● 0092L	New Construction Plate, 4" Round (Long)		6 24563 15997 7
● 0092S	New Construction Plate, 4" Round (Short)		6 24563 10770 1
5"			
■ 1000IC	5" IC Frame		7 84197 11995 9
■ 1004ICNS	5" Lytensing IC Frame with Integral Nails		7 84197 48773 7
■ 1004SICR	5" Lytensing IC Frame / Non-IC Shallow		7 84197 19853 4
■ 1004ICXN	5" Lytensing IC Frame (High Watt) with Integral Nails		7 84197 23900 8
■ 1004ICXS	5" Lytensing IC Frame (High Watt) with Integral Screws		7 84197 21984 0
■ 1005WHS	5" Trim, White Step Baffle Reflector		7 84197 51354 2
■ 1013WH	5" Trim, White Cone		7 84197 10130 5
● 1076CH	5" Trim, Basic Specular Cone Chrome Reflector		6 62057 67212 0
● 1076WH	5" Trim, Basic White Baffle		7 84197 10760 4
6.75"			
■ 1100IC	6.75" IC Frame		7 84197 11023 9
■ 1104SIC	6.75" Lytensing IC Frame / Non-IC Shallow		7 84197 19849 7
■ 1104SICR	6.75" Lytensing Remodeler IC Frame / Non-IC Shallow		7 84197 19854 1
● 1105CL	6.75" Trim, Reflector Alzak Cone Clear		6 62057 67977 8
■ 1105WH	6.75" Trim, Step Baffle Reflector, Matte White		7 84197 11070 3
■ 1113CD	6.75" Trim, Cone Reflector, Clear Diffuse, White Flange		7 84197 35971 3
■ 1113WH	6.75" Trim, Cone Reflector, Matte White		7 84197 01113 0
● 1176WH	6.75" Trim, Basic Baffle White		7 84197 00351 7
■ 1176WHSNEW	6.75" Trim, Baffle Reflector, White Baffle, White Flange		7 84197 12036 8
Accessories			
■ LAS56	Lytensing AirSeal Gasket		7 84197 36723 7

● Stock Ready (2-Day Quick Ship)

■ Design Ready (10-Day Quick Ship)



1000IC



1004ICNS



1004ICR



1004ICXN



313WHX



502X



575WHX

Product	Description / Features	ENERGY STAR	UPC
LytePoints Conventional			
3.75"			
■ 305WHWX	3.75" Trim, MR16 Adjustable Baffle White		6 24563 08331 9
● 313STX	3.75" Trim, MR16 Adjustable Gimbal Brushed Steel		7 84197 43570 7
● 313WHX	3.75" Trim, MR16 Adjustable Gimbal White		7 84197 43571 4
● 394CHX	3.75" Trim, MR16 Basic Cone Chrome		6 24563 15413 2
4.25"			
● 502AICSX	4.25" PAR20 Frame-In Kit IC/AirSeal		6 24563 21722 6
● 502X	4.25" V-Frame, Frame-In Kit Non-IC		6 24563 08840 6
● 513WHX	4.25" Trim, Residence PAR20 White		6 24563 08854 3
● 516WHX	4.25" Trim, Contour PAR20 White		6 24563 08855 0
● 575WHX	4.25" Trim, Adjustable Step Baffle PAR20 White		6 24563 08845 1
● 594CHX	4.25" Trim, Adjustable Alzak Cone PAR20 Chrome		6 24563 11675 8
● Stock Ready (2-Day Quick Ship)	■ Design Ready (10-Day Quick Ship)		

LIGHTOLIER

by **Signify**

Track Lighting

if
you want flexible
lighting that can
evolve with your
spaces

Choose Lightolier by Signify for a complete selection of professional track and downlighting solutions. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.

LIGHTOLIER

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		CorePro LED	Track Head	BoldFlood	LightFlood	SpotLED	Alcyon Horizontal	Alcyon Vertical	Alcyon Recessed Multiples	OmniSpot	OmniSpot Recessed Multiples
Page Reference		pg. 70	pg. 72	pg. 70	pg. 70	pg. 72	pg. 68	pg. 68	pg. 69	pg. 70	pg. 71
Quick Ship Service		● ■	● ■	● ■	● ■	● ■	● ■	● ■	● ■	● ■	● ■
Budget / Grade		Value / Good		Performance / Better			Spec / Best				
Spec & Performance	Finishes	Aluminum* White Black*	White Black	Aluminum* White Black*	Aluminum* White* Black*	Aluminum* White Black	Aluminum* White Black*	Aluminum* White Black	White Black*	Aluminum* White Black	White Black*
	Optics	Integrated	Integrated	Integrated	Integrated	Integrated	Modular	Modular	Modular	Modular	Modular
	Narrow Spot	✓	✓					✓	✓	✓	✓
	Spot		✓		✓	✓	✓	✓	✓	✓	✓
	Narrow Flood		✓		✓	✓	✓	✓	✓	✓	✓
	Flood	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Beams	23° to 35° (2 beams)	15° to 36° (4 beams)	95° W x 90° L	100°	8° to 40° (3 beams)	13° to 28° (3 beams)	10° to 36° (4 beams)	10° to 36° (4 beams)	11° to 36° (4 beams)	11° to 36° (4 beams)
Spec & Performance	Lumens	600 1000, 2000*	600 1000	2000 4000	2000 4000*	600, 1000, 2000, 3000	1200	600, 1000, 2000, 3000	600, 1300, 2000	600, 1000, 2000	600 1000
	Wattage (W)	6-12W	6-12W	23-41W	23W	10-39W	15W	10-34W	10-34W	6-25W	6-12W
	Efficacy (lm/W)	up to 107	up to 90	up to 100	up to 100	up to 78	up to 78	up to 93	up to 60	up to 108	up to 83
	CCT (K)	2700* 3000	3000K	2700K* 3000K 3500K 4000K*	2700K* 3000K 4000K*	2700K* 3000K 4000K*	2700K* 3000K 3500K 4000K*	2700K* 3000K 3500K* 4000K*	2700K* 3000K 4000K*	2700K* 3000K 4000K*	2700K* 3000K 3500K* 4000K*
	CRI	80 / 90	90	90	80	80, 85	80 / 90	80 / 90	80	80 / 90	80, 90
	CrispWhite	◆			■ ◆		■ ◆	■ ◆		■ ◆	■ ◆
	CBCP	up to 2,900cd	up to 12,300cd	up to 1,808cd	up to 900cd	up to 70,000cd	up to 11,700cd	up to 46,000cd	up to 14,400cd	up to 30,000cd	up to 8,700cd
Accessories	Dimming	ELV	0-10V	ELV	ELV / TRIAC	ELV	ELV / TRIAC	ELV	0-10V	ELV	0-10V
	Adapters	Lightolier Halo* Juno*	Lightolier Juno	Lightolier Halo* Juno*	Lightolier Halo* Juno* GES* GTEK* HTEK*	Lightolier Halo* Juno* GES* GTEK* HTEK*	Lightolier	Lightolier Halo* Juno* Prospec*	-	Lightolier Juno Halo* Capri* GTEK* Prospec*	-
	Accessory Holder Snoot		✓			✓	✓	✓	✓	✓	✓
	Diffusion Filters & Films		✓			✓	✓	✓	✓	✓	✓
	Colour Filters		✓			✓					
	Hex Cell Louvers		✓	✓		✓	✓	✓	✓	✓	✓
	cULus listed	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Ratings & Certification	Energy Star	✓	✓	✓		✓	✓	✓	✓	✓	✓
	Lifetime (L70)	up to 50,000 hours	up to 60,000 hours	up to 50,000 hours	up to 50,000 hours	up to 54,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours	up to 50,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.									

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

✓ Standard Feature * ◆ Spec Ready / Additional Options Available, see spec sheet for details



Advent Track (61)



Basic Track (60)



Mini Coupler



"L" Connector



Variable Angle Connector

Product	Description / Features	UPC
LyteSpan Advent Track		
■ 6101NBK	4' Individual Advent Track Black	7 84197 57286 0
■ 6101NWH	4' Individual Advent Track White	7 84197 57287 7
■ 6102NBK	8' Individual Advent Track Black	7 84197 57289 1
■ 6103NBK	8' Joiner Track with Mini Coupler, Black	7 84197 57292 1
■ 6104NBK	4' Plain Track with Dead End, Black	7 84197 57295 2
■ 6104NWH	4' Plain Track with Dead End, White	7 84197 57296 9
■ 6108NBK	8' Plain Track with Dead End, Black	7 84197 57298 3
Connectors		
■ 6146NBK	Advent Power Extension Connector Kit Black	7 84197 57319 5
■ 6146NWH	Advent Power Extension Connector Kit White	7 84197 57320 1
■ 6148NBK	Advent Live End Black	7 84197 57362 1
■ 6149NBK	Advent Mini Coupler Black	7 84197 57322 5
■ 6149NWH	Advent Mini Coupler White	7 84197 57323 2
■ 6150NBK	Advent "L" Connector Black	7 84197 57308 9
■ 6150NWH	Advent "L" Connector White	7 84197 57309 6
■ 6151NWH	Advent "T" Connector White	7 84197 57312 6
■ 6153NWH	Advent Variable Angle Connector White	7 84197 57317 1
■ 6154NBK	Advent In-Line Connector Black	7 84197 57305 8
■ 6154NWH	Advent In-Line Connector White	7 84197 57306 5
LyteSpan Basic Track		
■ 6000NBK	2' Individual Track with Live End Feed Connector, Black	7 84197 59418 3
■ 6000NWH	2' Individual Track with Live End Feed Connector, White	7 84197 59419 0
■ 6002NAL	8' Individual Track with Live End Feed Connector, Aluminum	7 84197 53980 1
■ 6003NBK	8' Joiner Track with Mini Coupler, Black	7 84197 59424 4
■ 6004NAL	4' Plain Track with Dead End, Aluminum	7 84197 53977 1
● 6004NBK	4' Plain Track with Dead End, Black	7 84197 59426 8
● 6004NWH	4' Plain Track with Dead End, White	7 84197 59427 5
■ 6008NAL	8' Plain Track with Dead End, Aluminum	7 84197 53973 3
● 6008NBK	8' Plain Track with Dead End, Black	7 84197 59428 2
● 6008NWH	8' Plain Track with Dead End, White	7 84197 59429 9
● 6012NWH	12' Plain Track with Dead End, White	7 84197 59431 2
Basic Connectors		
■ 6046NBK	Basic Power Extension Connector, Black	7 84197 59454 1
■ 6046NWH	Basic Power Extension Connector, White	7 84197 59455 8
■ 6048NAL	Basic Live End, Aluminum	7 84197 53975 7
● 6048NBK	Basic Live End, Black	7 84197 59458 9
● 6048NWH	Basic Live End, White	7 84197 59459 6
■ 6049NAL	Basic Mini Coupler, Aluminum	7 84197 53947 4
● 6049NBK	Basic Mini Coupler, Black	7 84197 59456 5
● 6049NWH	Basic Mini Coupler, White	7 84197 59457 2
■ 6050NBK	Basic "L" Connector, Black	7 84197 59446 6
● 6050NWH	Basic "L" Connector, White	7 84197 59447 3
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)		



"T" Connector



"X" Connector



In-Line Connector



End Feed Canopy Kit



Saddle Canopy Kit Power Feed

Product	Description / Features	UPC
LyteSpan Basic Track		
Basic Connectors (Continued)		
■ 6051NBK	Basic "T" Connector, Black	7 84197 59448 0
■ 6051NWH	Basic "T" Connector, White	7 84197 59449 7
■ 6052NBK	Basic "X" Connector, Black	7 84197 59450 3
■ 6054NBK	Basic In-Line Connector, Black	7 84197 59432 9
■ 6054NWH	Basic In-Line Connector, White	7 84197 59435 0
■ 6099BK	Basic PowerTrip, Live End Canopy, Black	7 84197 46993 1
■ 6099WH	Basic PowerTrip, Live End Canopy, White	7 84197 46992 4
LyteSpan Track Accessories		
■ 6060BK	End Feed Canopy Kit Black	7 84197 60601 5
■ 6060NAL	End Feed Canopy Kit Aluminum	7 84197 59474 9
■ 6060WH	End Feed Canopy Kit White	7 84197 60600 8
■ 6061BK	Floating Canopy Kit Black	7 84197 60611 4
■ 6061WH	Floating Canopy Kit White	7 84197 60610 7
■ 6063BK	Saddle Canopy Kit Power Feed Black	7 84197 60631 2
■ 6063WH	Saddle Canopy Kit Power Feed White	7 84197 60630 5
■ 6074WH	Extension Wand 18" White	7 84197 60740 1
■ 6087	Regressed Edge Panel & T Bar Clips (9Clip/Box)	7 84197 02006 4
■ 6089	Regressed Edge Panel & Slotted Grid Runner Clips (9Clip/Box)	7 84197 60890 3
■ 6170BK	Rectangular Monopoint, Matte Black	7 84197 51555 3
■ 6170WH	Rectangular Monopoint, Matte White	7 84197 51554 6
■ 7515	4' Recessed Housing for Basic and Advent Track White	7 84197 27219 7
■ 7517	4' Recessed Housing Splice Box/End	7 84197 27225 8
■ 7584	18" Stem Mounting Kit for Basic & Advent Track White	7 84197 27426 9
■ 7586	48" Stem Mounting Kit for Basic & Advent Track White	7 84197 27432 0
■ 7681	48" Stem Mounting Kit for Basic & Advent Track Black	7 84197 27711 6
■ 7589BK	Track Attachment Fitting, Matte Black	7 84197 75890 5
■ 7596	Track/Surface Raceway Adapter for Basic Track	7 84197 27462 7
■ 7599	Track Pendant Adapter, White	7 84197 00230 5
PowerTrip Plug-In Breaker		
■ PLD120BK	120W (1.0A), Black	7 84197 53136 2
■ PLD120WH	120W (1.0A), White	7 84197 53137 9
■ PLD360BK	360W (3.0A), Black	7 84197 53152 2
■ PLD600BK	600W (5.0A), Black	7 84197 53157 7
■ PLD600WH	600W (5.0A), White	7 84197 53158 4
■ PLD900BK	900W (7.5A), Black	1 90096 13592 9
■ PLD900WH	900W (7.5A), White	1 90096 13593 6
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)		



Clips



Rectangular Monopoint



Recessed Housing



Raceway Adapter



PowerTrip Plug-In Breaker



LLAH (Medium)



LLAV11 (Medium)



LLAV20 (Medium)



LLAV (Large)

Product	Description / Features	ENERGY STAR	UPC
Alcyon LED Horizontal Medium Cylinder			
■ LLAH1183OWTE	1200lm, 3000K (CRI 80), White, Triac / ELV Dimming		6 62057 98357 8
■ LLAH11835WTE	1200lm, 3500K (CRI 80), White, Triac / ELV Dimming		6 62057 98360 8
■ LLAH1193OWTECW	1200lm, 3500K (CRI 90) Crisp White, White, Triac / ELV Dimming		6 62057 98371 4
Accessories			
■ LLA11SNBK	Snoot, Black		6 62057 28773 7
■ LLA11SNWH	Snoot, White		6 62057 28772 0
■ LLAHCA11	Hex Cell Louver		6 62057 28781 2
■ LLRF	Reflector, Flood (29°)		1 90096 13559 2
■ LLRNF	Reflector, Narrow Flood (23°)		1 90096 13560 8
Alcyon LED Vertical Medium Cylinder			
■ LLAV1130BK	1300lm, 3000K (CRI 80), Black		6 62057 54204 1
■ LLAV1130WH	1300lm, 3000K (CRI 80), White		6 62057 54203 4
■ LLAV2030BK	2000lm, 3000K (CRI 80), Black		6 62057 94974 1
■ LLAV2030WH	2000lm, 3000K (CRI 80), White		6 62057 94973 4
■ LLAV20930WHCW	2000lm, 3000K (CRI 90) Crisp White, White		6 62057 94982 6
Accessories			
■ LLAV11AHAL	Accessory holder, Aluminum		6 62057 89826 1
■ LLAV11AHWH	Accessory holder, White		6 62057 89824 7
■ LLAV11FR	Diffusion Film, Frosted Etched		6 62057 89858 2
■ LLAV11LS	Diffusion Film, Linear Spread		6 62057 89852 0
■ LLAV11SF	Diffusion Film, Soft Focus		6 62057 89856 8
■ LLAV11SY	Diffusion Film, Symmetrical Spread		6 62057 89854 4
■ LLAV11RNS	Reflector, Narrow Spot (11°)		6 62057 89679 3
Alcyon LED Vertical Large Cylinder			
■ LLAV3030BK	3000lm, 3000K (CRI 90) Crisp White, White		1 90096 01950 2
Accessories			
■ LLAV12RF	Reflector, Flood (36°)		6 62057 89677 9
■ LLAV12RNS	Reflector, Narrow Spot (11°)		6 62057 89678 6
■ LLAV12RS	Reflector, Spot (17°)		6 62057 89675 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



LLAVRM (1 Head)



LLAVRM (2 Head)



LLAVRM (3 Head)



LLAVRM (4 Head)

Product	Description / Features	ENERGY STAR	UPC
Alcyon LED Recessed Multiples			
1 Head Frame & Fixture			
■ LLAVRM11H1120	Frame, 1 Head, 120V		6 62057 91343 8
2 Head Frame & Fixture			
■ LLAVRM11H2120	Frame, 2 Head, 120V		6 62057 91345 2
■ LLAVRM12H2120	Frame, 2 Head (2000lm), 120V		6 62057 91356 8
■ LLAVRM11H2277	Frame, 2 Head, 277V		6 62057 91347 6
■ LLAVRMWH1130H2	Fixture, 2 Head, 1300lm, 3000K (CRI 80), White		6 62057 91294 3
3 Head Frame & Fixture			
■ LLAVRM11H3120	Frame, 3 Head, 120V		6 62057 91349 0
■ LLAVRM12H3120	Frame, 3 Head (2000lm), 120V		6 62057 91358 2
■ LLAVRM11H3277	Frame, 3 Head, 277V		6 62057 91350 6
■ LLAVRMWH1130H3	Fixture, 3 Head, 1300lm, 3000K (CRI 80), White		6 62057 91296 7
4 Head Frame & Fixture			
■ LLAVRM12H4120	Frame, 4 Head (2000lm), 120V		6 62057 91360 5
■ LLAVRM11H4277	Frame, 4 Head, 277V		6 62057 91353 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



BoldFlood LED



CorePro LED Mini Cylinder



LightFlood LED



LC10 (Black)



LC10 (White)

Product	Description / Features	ENERGY STAR	UPC
BoldFlood LED			
■ LWW20930WH	2000lm, 3000K (CRI 90), White (matte)		1 90096 13639 1
■ LWW20935WH	2000lm, 3500K (CRI 90), White (matte)		1 90096 13640 7
■ LWW40930WH	4000lm, 3000K (CRI 90), White (matte)		1 90096 13641 4
■ LWW40935WH	4000lm, 3500K (CRI 90), White (matte)		1 90096 13642 1
CorePro LED Mini Cylinder			
● LTO8RWF830BKVA	900lm, Wide Flood (35°), 3000K (CRI 80), Black, ELV Dimming	★	1 90096 04192 3
● LTO8RWF830WHVA	900lm, Wide Flood (35°), 3000K (CRI 80), White, ELV Dimming	★	1 90096 04191 6
LightFlood LED			
■ LLF230AL	2000lm, 3000K (CRI 80), Aluminum		6 62057 75883 1
OmniSpot LED Track Heads (06/10) Track Head with Lightolier Adapter			
■ LC06830BKTE	600lm, 3000K (CRI 80), Matte Black, ELV Dimming		1 90096 03678 3
■ LC06830WTE	600lm, 3000K (CRI 80), Matte White, ELV Dimming		1 90096 03762 9
■ LC10830BKTE	1000lm, 3000K (CRI 80), Matte Black, ELV Dimming		1 90096 03679 0
■ LC10930WTECW	1000lm, 3000K (CRI 90) Crisp White, Matte White, ELV Dimming		1 90096 03763 6
■ LC10930BKTE	1000lm, 3000K (CRI 90), Matte Black, ELV Dimming		1 90096 03166 5
■ LC10930WTE	1000lm, 3000K (CRI 90), Matte White, ELV Dimming		1 90096 03165 8
Track Head with Juno Adapter			
■ LCJ10830BKTE	1000lm, 3000K (CRI 80), Matte Black		1 90906 02098 8
■ LCJ10830WTE	1000lm, 3000K (CRI 80), Matte White		1 90906 02097 1
■ LCJ10930BKTECW	1000lm, 3000K (CRI 90) Crisp White, Matte Black		1 90906 02112 1
■ LCJ10930WTECW	1000lm, 3000K (CRI 90) Crisp White, Matte White		1 90906 02111 4
■ LCJ10930BKTE	1000lm, 3000K (CRI 90), Matte Black		1 90096 03379 9
■ LCJ10930WTE	1000lm, 3000K (CRI 90), Matte White		1 90096 03378 2
Accessories			
■ LC10AHBK	Accessory holder, Matte Black		1 90096 02886 3
■ LC10AHWH	Accessory holder, Matte White		1 90096 02885 6
■ LC10FR	Diffusion Film, Frosted Etched		1 90096 02901 3
■ LC10LS	Diffusion Film, Linear Spread		1 90096 02902 0
■ LC10SY	Diffusion Film, Symmetrical Spread		1 90096 02899 3
■ LC10SNBK	Snoot, Matte Black		1 90096 01474 3
■ LC10SNWH	Snoot, Matte White		1 90096 01473 6
■ LLMRF	Reflector, Flood (36°)		1 90096 02884 9
■ LLMRNS	Reflector, Narrow Spot (11°/12°)		1 90096 02881 8
■ LLMRS	Reflector, Spot (18°)		1 90096 02882 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Diffusion Film



LC10SNBK



LC10SNWH



LLMRS



LC20 (Black)



LC20 (White)



LC20AHBK



LC20AHWH



LC20SNBK

Product	Description / Features	ENERGY STAR	UPC
OmniSpot LED Track Heads (20)			
Track Head with Lightolier Adapter			
■ LC20830BKTE	2000lm, 3000K (CRI 80), Matte Black, ELV Dimming		6 62057 97052 3
■ LC20930BKTECW	2000lm, 3000K (CRI 90) Crisp White, Matte Black, ELV Dimming		1 90096 04111 4
■ LC20930WTECW	2000lm, 3000K (CRI 90) Crisp White, Matte White, ELV Dimming		1 90096 03764 3
■ LC20930BKTE	2000lm, 3000K (CRI 90), Matte Black, ELV Dimming		1 90096 03189 4
■ LC20930WTE	2000lm, 3000K (CRI 90), Matte White, ELV Dimming		1 90096 02815 3
Track Head with Juno Adapter			
■ LCJ20830BKTE	2000lm, 3000K (CRI 80), Matte Black		1 90906 02118 3
■ LCJ20830WTE	2000lm, 3000K (CRI 80), Matte White		1 90906 02117 6
■ LCJ20930BKTECW	2000lm, 3000K (CRI 90) Crisp White, Matte Black		1 90906 02130 5
■ LCJ20930WTECW	2000lm, 3000K (CRI 90) Crisp White, Matte White		1 90906 02129 9
■ LCJ20930BKTE	2000lm, 3000K (CRI 90), Matte Black		1 90096 03384 3
■ LCJ20930WTE	2000lm, 3000K (CRI 90), Matte White		1 90096 03383 6
Accessories			
■ LC20AHBK	Accessory holder, Matte Black		1 90096 02889 4
■ LC20AHWH	Accessory holder, Matte White		1 90096 02888 7
■ LC20FR	Diffusion Film, Frosted Etched		1 90096 02905 1
■ LC20LS	Diffusion Film, Linear Spread		1 90096 02906 8
■ LC20SF	Diffusion Film, Soft Focus		1 90096 02904 4
■ LC20SY	Diffusion Film, Symmetrical Spread		1 90096 02903 7
■ LC20SNBK	Snoot, Matte Black		1 90096 01477 4
■ LC20SNWH	Snoot, Matte White		1 90096 01476 7
OmniSpot LED Recessed Multiple			
2 Head Frame & Fixture			
■ LCRM10H2	Frame, 2 Head (2" Cylinders)		1 90096 07211 8
■ LCRM10830H2WHZ10U	Fixture, 2 Head (2" Cylinders), 1000lm, 3000K (CRI 80), Flange, 0-10V 1% Dimming, 120/277V		1 90096 07388 7
■ LCRM10930CWH2WHZ10U	Fixture, 2 Head (2" Cylinders), 1000lm, 3000K (CRI 90) Crisp White, Flange, 0-10V 1% Dimming, 120/277V		1 90096 07441 9
3 Head Frame & Fixture			
■ LCRM10H3	Frame, 3 Head (2" Cylinders)		1 90096 07212 5
■ LCRM10830H3WHZ10U	Fixture, 3 Head (2" Cylinders), 1000lm, 3000K (CRI 80), Flange, 0-10V 1% Dimming, 120/277V		1 90096 07389 4
■ LCRM10930CWH3WHZ10U	Fixture, 3 Head (2" Cylinders), 1000lm, 3000K (CRI 90) Crisp White, Flange, 0-10V 1% Dimming, 120/277V		1 90096 07442 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



OmniSpot LED (2 Head)



OmniSpot LED (3 Head)



LLABS / LLAB0



LLAB1



LLAB3



TH10



TH30



Product	Description / Features		UPC
Spot LED			
10W / 600lm			
■ LLABS30RNBK	600lm, 3000K (CRI 85), Narrow Flood (20°), Black	★	6 62057 65103 3
12W / 1000lm			
■ LLAB030RFBKVA	1000lm, 3000K (CRI 85), Flood (39°), Black, Version A	★	6 62057 95584 1
■ LLAB030RFBHVA	1000lm, 3000K (CRI 85), Flood (39°), White, Version A	★	6 62057 95581 0
■ LLAB030RSHVA	1000lm, 3000K (CRI 85), Spot (11°), White, Version A	★	6 62057 95565 0
28W / 2000lm			
■ LLAB130RFBKVA	2000lm, 3000K (CRI 85), Flood (38°), Black, Version A	★	6 62057 94703 7
■ LLAB130RFBHVA	2000lm, 3000K (CRI 85), Flood (38°), White, Version A	★	6 62057 94699 3
■ LLAB130RNBHVA	2000lm, 3000K (CRI 85), Narrow Flood (20°), White, Version A	★	6 62057 94690 0
■ LLAB130RSHVA	2000lm, 3000K (CRI 85), Spot (8°), White, Version A	★	6 62057 94682 5
39W / 3000lm			
■ LLAB330RNBKVA	3000lm, 3000K (CRI 80), Narrow Flood (20°), Black, Version A	★	6 62057 95837 8
■ LLAB330RNBHVA	3000lm, 3000K (CRI 80), Narrow Flood (20°), White, Version A	★	6 62057 95827 9
■ LLAB330RSBKVA	3000lm, 3000K (CRI 80), Spot (8°), Black, Version A	★	6 62057 95821 7
■ LLAB330RSHVA	3000lm, 3000K (CRI 80), Spot (8°), White, Version A	★	6 62057 95818 7
Accessories			
■ LLAB1AHBK	Large Accessory holder, Black		6 62057 65493 5
■ LLAB1AHWH	Large Accessory holder, White		6 62057 65708 0
■ LLABSAHBK	Small Accessory holder, Black		6 62057 64919 1
■ LLABSAHWH	Small Accessory holder, White		6 62057 88717 3
Track Head LED			
Track Head with Lightolier Adapter			
● TH10930NF1B	1100lm, 3000K (CRI 90), Narrow Flood (30°), 120V, Black	★	1 90096 01649 5
● TH10930NF1W	1100lm, 3000K (CRI 90), Narrow Flood (30°), 120V, White	★	1 90096 01648 8
■ TH10930S1B	1100lm, 3000K (CRI 90), Spot (15°), 120V, Black	★	1 90096 01647 1
■ TH10930S1W	1100lm, 3000K (CRI 90), Spot (15°), 120V, White	★	1 90096 01646 4
■ TH30930F1B	3000lm, 3000K (CRI 90), Flood (36°), 120V, Black	★	1 90096 01651 8
■ TH30930F1W	3000lm, 3000K (CRI 90), Flood (36°), 120V, White	★	1 90096 01650 1
■ TH30930NF1B	3000lm, 3000K (CRI 90), Narrow Flood (22°), 120V, Black	★	1 90096 01653 2
■ TH30930NF1W	3000lm, 3000K (CRI 90), Narrow Flood (22°), 120V, White	★	1 90096 01652 5
Track Head with Juno Adapter			
■ THJ10930NF1B	1100lm, 3000K (CRI 90), Narrow Flood (30°), 120V, Black	★	1 90096 01722 5
■ THJ10930NF1W	1100lm, 3000K (CRI 90), Narrow Flood (30°), 120V, White	★	1 90096 01721 8
■ THJ10930S1B	1100lm, 3000K (CRI 90), Spot (15°), 120V, Black	★	1 90096 01720 1
■ THJ10930S1W	1100lm, 3000K (CRI 90), Spot (15°), 120V, White	★	1 90096 01719 5
■ THJ30930F1B	3000lm, 3000K (CRI 90), Flood (36°), 120V, Black	★	1 90096 01724 9
■ THJ30930F1W	3000lm, 3000K (CRI 90), Flood (36°), 120V, White	★	1 90096 01723 2
■ THJ30930NF1B	3000lm, 3000K (CRI 90), Narrow Flood (22°), 120V, Black	★	1 90096 01726 3
■ THJ30930NF1W	3000lm, 3000K (CRI 90), Narrow Flood (22°), 120V, White	★	1 90096 01725 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



6320WH



6278WH



6284



9030NWH



55215WH

Product	Description / Features	ENERGY STAR	UPC
Conventional Track Heads			
● 6320WH	Basic Track Head Universal Lytespot White		6 24563 01997 4
PAR Ring			
● 6278WH	50W PAR20 White		7 84197 62780 5
● 6282WH	75W PAR30S White		6 24563 06025 9
■ 6284	250W PAR38 Max White		7 84197 76284 1
● 9030NBK	PAR30 Black		6 62057 90590 7
● 9030NWH	PAR30 White		6 62057 90591 4
● 9038NBK	PAR38 Black		6 62057 90593 8
● 9038NWH	PAR38 White		6 62057 90594 5
● 55215WH	250W PAR38 White		6 24563 06024 2
● 55241WH	75W PAR30S Front Relamp White		6 24563 03005 4
● 55242WH	250W PAR38 Front Relamp White		6 24563 03007 8
Mini			
■ 81LV4BK	Mini HID 20W CMH BT PGJ5 Wall Washer, Vertical Blade Louver		6 62057 22660 6
■ 81VZ4BK	Mini HID 20W CMH BT PGJ5 Wall Washer, Visor Black		6 62057 22658 3
■ 81VZ4WH	Mini HID 20W CMH BT PGJ5 Wall Washer, Visor White		1 90096 19068 3
■ 9021AL	Mini Universal Metallic Aluminum, 250W Max		7 84197 20733 5
■ 9173BBK	MiniForms, Matte Black, All Lytespan Track Systems, MR16 50W Max.		7 84197 91714 2
■ 9175NWH	MiniForms, Matte White, All Lytespan Track Systems, MR16 50W Max.		7 84197 25109 3
Par-Tech			
■ 8201BK	Par-Tech, Bezel 20 Shade, Matter Black		7 84197 82011 4
■ 8227WH	Par-Tech, Bezel 20 Shade, Matter White		7 84197 82270 5
Sof-Tech Spot			
■ 6276BBK	Sof-Tech Spot, MR16, Matte Black		7 84197 52631 3
■ 6276BWH	Sof-Tech Spot, MR16, Matte White		7 84197 52630 6
■ 8420WH	Sof-Tech Spot, PAR20, Matte Black		7 84197 84200 0
■ 8430WH	Sof-Tech Spot, PAR30, Matte White		7 84197 84300 7
LyteSpan Track Head Accessories			
■ AF2FR	2" Frosted Softening Lens		7 84197 47799 8
■ AF2SY	2" 55° Symmetrical Spread Lens		7 84197 11616 3
■ AF2AS	2" Beam Elongator Lens		7 84197 11617 0
■ AF4AS	4.75" Beam Elongator Lens		7 84197 11597 5
■ AL2HC	2" Hex Cell Louver		7 84197 11611 8
■ AL25HC	2.5" Hex Cell Louver		7 84197 16269 6
■ AL3HC	3.75" Hex Cell Louver		7 84197 16293 1
■ AL4HC	6" & 7" Hex Cell Louver for Adjustable Track Head		7 84197 11606 4
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



55241WH



8227WH



6276BBK



Beam Elongator Lens



Hex Cell Louver

KEENE

by Signify



Garage & Canopy LED DualSelect | Pg. 79

Commercial Outdoor Lighting

Outdoor general purpose lighting

The Keene brand features contractor-friendly outdoor lighting solutions that help make the most of your time and budget. Readily available and dependable luminaires suitable for a range of commercial application types.



LWL Wall Light LED | Pg. 82

Dusk to Dawn LED | Pg. 84

Site & Area 76

LED Quick Selection Guide 77

EcoForm Small	78
Area Light LED Gen. 2	79
Post Top LED	79
Garage & Canopy LED DualSelect	79

Floods & Wall Packs 80

LED Quick Selection Guide 81

General Purpose Flood LED	82
Slim Flood LED	82
LWL Wall Light LED	82
SWL Square Wall Light LED.	82
Low Profile Wall LED	83
Tall Wall Pack LED	83
Wall Pack LED DualSelect	83
LytePro LED Wall Sconce	83

Special Application 84

Dusk to Dawn LED	84
LED Commercial Bollard	84
RoughLyte LED	84

Low Voltage 85

FlexScape BL9 LED	85
FlexScape IL9 LED	85
FlexScape MUL4 LED	85
FlexScape Low Voltage Transformer	85
BL5016 Micro Accent.	85

KEENE

by @signify

Site & Area



if
you need to illuminate
parking lots and
canopies

Choose Keene by Signify for a complete selection of commercial outdoor lighting products. Visit [signify.com/quickship](https://www.signify.com/quickship) to learn more.



KEENE

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Gardco EcoForm Small



Area Light LED Gen. 2



Post Top LED



Garage & Canopy LED DualSelect

Product Family

Page Reference

Quick Ship Service

Budget / Grade

Finish / Spec & Performance	Finish	Black / Bronze / Medium Grey	Bronze	Black	Bronze
	Wattage	106W / 159W / 206W	Field Adjustable Wattage Selector (FAWS) 46-71W / 96-142W	Field Adjustable Wattage Selector (FAWS) 20-53W	Field Adjustable Wattage Selector (FAWS) 28-60W / 70-90W
	Lumen Output Range	13,388-27,526	7,609-22,590	2,047-6,308	4,100-12,400
	Efficacy	up to 136	up to 172	up to 129	up to 150
	Distribution	Type 3, 4, 5	Type 3, 4	Type 3, 5	Type 5 Symmetric
	Color Temperature	4000K	4000K	3000K / 4000K	Selectable 3000K / 4000K / 5000K
	CRI	70	70	70	70
	Voltage	120-277V	120-277V / 347-480V	120-347V	120-347V
	IP Rating	IP65	IP65	IP65	IP65
Ratings & Certification	DLC Listing	Premium	Premium	Standard	Standard
	cULus Listed	✓	✓	✓	✓
	Lifetime (L70)	up to 100,000 hours	up to 100,000 hours	up to 54,000 hours	up to 60,000 hours
	Warranty	5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.			

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

✓ Standard Feature * ♦ Spec Ready / Additional Options Available, see spec sheet for details



RS-ECF-S

Product	Description / Features		UPC
EcoForm Small	106W, 32 LED		
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18811 6
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01806 2
■ RS-ECF-S-32L-1A-NW-G2-AR-3-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01807 9
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18812 3
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01808 6
■ RS-ECF-S-32L-1A-NW-G2-AR-4-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01809 3
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-BK	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18784 3
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-BZ	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01810 9
■ RS-ECF-S-32L-1A-NW-G2-AR-5-UNV-MGY	106W, 32 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01811 6
159W, 48 LED			
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18783 6
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01812 3
■ RS-ECF-S-48L-1A-NW-G2-AR-3-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01813 0
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18440 8
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01814 7
■ RS-ECF-S-48L-1A-NW-G2-AR-4-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01815 4
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-BK	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18458 3
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-BZ	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01816 1
■ RS-ECF-S-48L-1A-NW-G2-AR-5-UNV-MGY	159W, 48 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01817 8
206W, 64 LED			
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Black	PREMIUM	1 90096 18377 7
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 01818 5
■ RS-ECF-S-64L-1A-NW-G2-AR-3-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 3, 120-277V, Medium Grey	PREMIUM	1 90096 01819 2
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Black	PREMIUM	1 90096 18378 4
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 01820 8
■ RS-ECF-S-64L-1A-NW-G2-AR-4-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 4, 120-277V, Medium Grey	PREMIUM	1 90096 01821 5
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-BK	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Black	PREMIUM	1 90096 18550 4
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-BZ	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Bronze	PREMIUM	1 90096 01822 2
■ RS-ECF-S-64L-1A-NW-G2-AR-5-UNV-MGY	206W, 64 LED, 4000K (CRI 70), Arm Mount, Type 5, 120-277V, Medium Grey	PREMIUM	1 90096 01823 9
Internal House Side shield			
■ HIS-32-H	Internal House Side shield (Standard optic orientation) for 32 LEDs (2 modules)		1 90096 15919 4
■ HIS-48-H	Internal House Side shield (Standard optic orientation) for 48 LEDs (2 modules)		1 90096 15920 0
■ HIS-64-H	Internal House Side shield (Standard optic orientation) for 64 LEDs (2 modules)		1 90096 15921 7
Retrofit Arm mount kit			
■ RS-ECF-RAM-G2-BK	Retrofit Arm mount kit, Black		1 90096 19133 8
■ RS-ECF-RAM-G2-BZ	Retrofit Arm mount kit, Bronze		1 90096 19132 1
■ RS-ECF-RAM-G2-DGY	Retrofit Arm mount kit, Dark Grey		1 90096 15908 8
■ RS-ECF-RAM-G2-MGY	Retrofit Arm mount kit, Medium Grey		1 90096 15509 5

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Product	Description / Features		UPC
Area Light LED Gen. 2			
46-71W Field Adjustable Wattage Selector (FAWS)			
● AL70-NW-G2-AR-3-8-FAWS-BZ	46-71W, 4000K (CRI 70), Arm mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 18055 4
● AL70-NW-G2-AR-3-6-FAWS-BZ	46-71W, 4000K (CRI 70), Arm mount, Type 3, 347-480V, Bronze	PREMIUM	1 90096 18057 8
● AL70-NW-G2-AR-4-8-FAWS-BZ	46-71W, 4000K (CRI 70), Arm mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 18059 2
● AL70-NW-G2-AR-4-6-FAWS-BZ	46-71W, 4000K (CRI 70), Arm mount, Type 4, 347-480V, Bronze	PREMIUM	1 90096 18061 5
96-142W Field Adjustable Wattage Selector (FAWS)			
● AL150-NW-G2-AR-3-8-FAWS-BZ	96-142W, 4000K (CRI 70), Arm mount, Type 3, 120-277V, Bronze	PREMIUM	1 90096 18056 1
● AL150-NW-G2-AR-3-6-FAWS-BZ	96-142W, 4000K (CRI 70), Arm mount, Type 3, 347-480V, Bronze	PREMIUM	1 90096 18058 5
● AL150-NW-G2-AR-4-8-FAWS-BZ	96-142W, 4000K (CRI 70), Arm mount, Type 4, 120-277V, Bronze	PREMIUM	1 90096 18060 8
● AL150-NW-G2-AR-4-6-FAWS-BZ	96-142W, 4000K (CRI 70), Arm mount, Type 4, 347-480V, Bronze	PREMIUM	1 90096 18062 2
Accessory			
● AL-SF-G2-BZ	Area Light Slip Fitter Mounting Accessory		1 90096 18063 9
Post Top LED			
20-53W Field Adjustable Wattage Selector (FAWS)			
● PT50-WW-G1-T2-3-HV3-FAWS-TLRPC-BK	20-53W, 3000K (CRI 70), Type 3, 120-347V, Black, Twist Lock Receptacle w/ Shorting Cap		7 83352 02606 4
● PT50-WW-G1-T2-5-HV3-FAWS-TLRPC-BK	20-53W, 3000K (CRI 70), Type 5, 120-347V, Black, Twist Lock Receptacle w/ Shorting Cap	DLC	7 83352 02607 1
● PT50-NW-G1-T2-3-HV3-FAWS-TLRPC-BK	20-53W, 4000K (CRI 70), Type 3, 120-347V, Black, Twist Lock Receptacle w/ Shorting Cap		7 83352 02608 8
● PT50-NW-G1-T2-5-HV3-FAWS-TLRPC-BK	20-53W, 4000K (CRI 70), Type 5, 120-347V, Black, Twist Lock Receptacle w/ Shorting Cap		7 83352 02609 5
Garage & Canopy LED DualSelect			
Field Adjustable Wattage and CCT Selector (FAWS)			
● GC60-SCT-G2-SM-5-10-BZ	28-60W, 3000K / 4000K / 5000K (CRI 70), Type 5 Symmetric, 120-347V, Bronze, Integrated Motion and Daylight Sensor	DLC	1 90096 13131 0
● GC90-SCT-G2-SM-5-10-BZ	70-90W, 3000K / 4000K / 5000K (CRI 70), Type 5 Symmetric, 120-347V, Bronze, Integrated Motion and Daylight Sensor	DLC	1 90096 13132 7
Accessory			
● GC60/90-MH10	Garage & Canopy DualSelect Controller		1 90096 13159 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

KEENE

by @signify

Floods & Wall Packs

if

you need create
safe and functional
outdoor spaces

Choose Keene by Signify for a complete selection
of commercial outdoor lighting products.
Visit signify.com/quickship to learn more.

KEENE

Click images to view eCatalogue (Detailed brochures, bulletins, spec sheets, IES files, etc.)



Product Family		LED General Purpose Flood	Slim Flood LED	LWL Wall Light LED	SWL Square Wall Light LED	Low Profile Wall LED	Tall Wall Pack LED	Wall Pack LED Dual Select	LytePro LED Wall Sconce (Small)	LytePro LED Wall Sconce (Medium)	LytePro LED Wall Sconce (Large)
Page Reference		pg. 82	pg. 82	pg. 82	pg. 82	pg. 83	pg. 83	pg. 83	pg. 83	pg. 83	pg. 83
Quick Ship Service		●	●	●	●	●	●	●	● ■	● ■	● ■
Budget / Grade		Value / Good		Value / Good					Performance / Better		
Finish / Spec & Performance	Finish	Bronze	Bronze	Bronze	Bronze	Bronze	Bronze	Bronze	Bronze, Dark Grey White*		
	Wattage	150, 300W	10, 30, 50, 100, 150, 200W	12W	13W	15, 30, 50, 80W	20W	Field Adjustable Wattage Selector (FAWS) 28-60, 70-100W	10W	30W	70W
	Lumens (lm)	16,325-34,025	1,089-24,987	1,104	1,178	1,656-5,114	2,277	3,860-12,800	1,050	2,065-4,629	6,472-9,637
	Efficacy (lm/W)	up to 113	up to 126	up to 90	up to 93	up to 110	up to 120	up to 145	up to 108	up to 104	up to 114
	Distribution	-	-	-	-	Type 2	Type 4	-	Type 2	Type 3, 4	Type 3, 4
	Color Temperature	4000K	4000K	3000K	3000K	4000K	4000K	Selectable 3000 4000 5000K	3000K 4000K	3000K 4000K	3000K 4000K
	CRI	70	80	80	80	80	70	70	70	70	70
	Voltage	120-277V 347V	120-277V	120V	120V	120-277V	120-277V 347V	120-347V	120-277V	120-277V 347-480V	120-277V 347-480V
Technology / Certification	Photocell			✓	✓		✓	✓	✓	✓	✓
	IP Rating	IP66	IP65			IP65	IP65/IP66	IP65	IP65	IP65	IP65
	DLC Listing	Standard	Standard			Standard	Standard	Standard	Standard	Standard	Standard
	cULus Listed	✓		✓	✓	✓	✓	✓			
	cETLus Listed		✓						✓	✓	✓
	Lifetime (L70)	up to 54,000 hours	up to 76,000 hours	up to 48,000 hours	up to 48,000 hours	up to 54,000 hours	up to 102,000 hours	up to 54,000 hours	up to 60,000 hours	up to 54,000 hours	up to 54,000 hours
Warranty		5 year manufacturer's limited warranty. Visit www.signify.com/warranties for complete warranty information.									

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)

✓ Standard Feature * ♦ Spec Ready / Additional Options Available, see spec sheet for details



FL



TF



BT10



LWL



SWL

Product	Description / Features		UPC
General Purpose Flood LED			
● FL150-NW-G1-T-FL-6-BZ	150W, 4000K (CRI 70), Yoke mount, 347V, Bronze	DLC	7 83352 02423 7
● FL300-NW-G1-S-FL-8-BZ	300W, 4000K (CRI 70), Slip Fitter Mount, 120-277V, Bronze	DLC	7 83352 02519 7
● FL300-NW-G1-S-FL-6-BZ	300W, 4000K (CRI 70), Slip Fitter Mount, 347V, Bronze	DLC	6 24563 34052 8
● FL300-NW-G1-T-FL-8-BZ	300W, 4000K (CRI 70), Yoke mount, 120-277V, Bronze	DLC	7 83352 02419 0
● FL300-NW-G1-T-FL-6-BZ	300W, 4000K (CRI 70), Yoke mount, 347V, Bronze	DLC	7 83352 02424 4
Slim Flood LED			
● TF10-NW-G1-K-FL-8-BZ	10W, 4000K (CRI 80), Yoke/Knuckle Mount, 120-277V, Bronze	DLC	7 83352 02594 4
● TF30-NW-G1-K-FL-8-BZ	30W, 4000K (CRI 80), Yoke/Knuckle Mount, 120-277V, Bronze	DLC	7 83352 02595 1
● TF50-NW-G1-K-FL-8-BZ	50W, 4000K (CRI 80), Yoke/Knuckle Mount, 120-277V, Bronze	DLC	7 83352 02596 8
● TF100-NW-G1-Y-FL-8-BZ	100W, 4000K (CRI 80), Yoke Mount, 120-277V, Bronze	DLC	7 83352 02597 5
● TF150-NW-G1-Y-FL-8-BZ	150W, 4000K (CRI 80), Yoke Mount, 120-277V, Bronze	DLC	7 83352 02598 2
● TF200-NW-G1-Y-FL-8-BZ	200W, 4000K (CRI 80), Yoke Mount, 120-277V, Bronze	DLC	7 83352 02599 9
Accessory			
● BT10	Universal slipfitter, converts yoke mount flood to tenon mount (fits 23/8" O.D. tenon), bronze finish		6 24290 37773 6
LWL Wall Light LED			
● LWL-WW-G2-PCB-1-BZ	12W, 3000K (CRI 80), 120V, Bronze, Button Photocell installed		7 83352 02576 0
SWL Square Wall Light LED			
● SWL-WW-G1-PCB-1-BZ	13W, 3000K (CRI 80), 120V, Bronze, Button Photocell installed		7 83352 02577 7

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



PW



TW20



WP

Product	Description / Features		UPC
Low Profile Wall LED			
15W			
● PW15-NW-G1-8-BZ	15W, 4000K (CRI 80), 120-277V, Bronze	DLC	7 83352 02429 9
● PW15-NW-G1-6-BZ	15W, 4000K (CRI 80), 347V, Bronze		7 83352 02432 9
30W			
● PW30-NW-G1-8-BZ	30W, 4000K (CRI 80), 120-277V, Bronze		7 83352 02430 5
● PW30-NW-G1-6-BZ	30W, 4000K (CRI 80), 347V, Bronze		7 83352 02433 6
50W			
● PW50-NW-G1-8-BZ	50W, 4000K (CRI 80), 120-277V, Bronze		7 83352 02431 2
● PW50-NW-G1-6-BZ	50W, 4000K (CRI 80), 347V, Bronze		7 83352 02434 3
80W			
● PW80-NW-G1-8-BZ	80W, 4000K (CRI 80), 120-277V, Bronze	DLC	6 24563 34014 6
● PW80-NW-G1-6-BZ	80W, 4000K (CRI 80), 347V, Bronze		6 24563 34015 3
Tall Wall Pack LED			
● TW20-NW-G1-8-BZ	20W, 4000K (CRI 70), 120-277V, Bronze	DLC	7 83352 02405 3
● TW20-NW-G1-PCB-1-BZ	20W, 4000K (CRI 70), 120, Bronze, Button Photocell installed	DLC	6 24563 34013 9
Wall Pack LED DualSelect			
● WP60-SCT-G2-10-BZ	28-60W, 3000K / 4000K / 5000K (CRI 70), Integrated Daylight Sensor, 120-347V, Bronze	DLC	1 90096 13133 4
● WP100-SCT-G2-10-BZ	70-100W, 3000K / 4000K / 5000K (CRI 70), Integrated Daylight Sensor, 120-347V, Bronze	DLC	1 90096 13134 1
LytePro LED Wall Sconce			
7 LED Small Wall Sconce, 10W			
■ LPW7-10-NW-G3-2-UNV-BK	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Black	DLC	1 90096 11725 3
● LPW7-G3-8-BZ	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Bronze		6 22252 81385 8
● LPW7-G3-8-DGY	7 LED Small Wall Sconce, 10W, 4000K (CRI 70), Type 2, 120-277V, Dark Gray		6 22252 81384 1
16 LED Medium Wall Sconce, 30W			
■ LPW16-30-NW-G3-3-UNV-BK	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Black		1 90096 11838 0
● LPW16-G3-8-BZ	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Bronze		6 22252 81387 2
● LPW16-G3-8-DGY	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 120-277V, Dark Gray		6 22252 81386 5
■ LPW16-30-NW-G3-3-HVU-BK	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Black		
■ LPW16-30-NW-G3-3-HVU-BZ	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Bronze		
■ LPW16-30-NW-G3-3-HVU-DGY	16 LED Medium Wall Sconce, 30W, 4000K (CRI 70), Type 3, 347-480V, Dark Grey		1 90096 11841 0
32 LED Large Wall Sconce, 70W			
■ LPW32-70-NW-G3-3-UNV-BK	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Black	DLC	1 90096 11878 6
● LPW32-G3-8-BZ	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Bronze		6 22252 81389 6
● LPW32-G3-8-DGY	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 120-277V, Dark Grey		6 22252 81388 9
■ LPW32-70-NW-G3-3-HVU-BK	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Black	DLC	1 90096 11883 0
■ LPW32-70-NW-G3-3-HVU-BZ	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Bronze	DLC	
■ LPW32-70-NW-G3-3-HVU-DGY	32 LED Large Wall Sconce, 70W, 4000K (CRI 70), Type 3, 347-480V, Dark Grey	DLC	1 90096 11881 6

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



LPW7



LPW16



LPW32



LED Commercial Bollard

Product	Description / Features		UPC
Dusk to Dawn LED			
● DTD40-NW-G3-AR-5-TLRPC-1-GY3S	Dusk to Dawn LED, 40W, 4000K (CRI 70), Arm mount, Type 5, 120V, Twist lock receptacle + Photocell, Grey	DLC	6 24563 33983 6
● DTDARMGY3S	Dusk to Dawn LED, Mounting arm with hardware, Ø1.5" steel, gray finish		7 83352 02414 5
LED Commercial Bollard			
● BL25-NW-G1-5-8-BZ	LED Commercial Bollard, 25W, 4000K (CRI 70), Type 5 Symmetrical, 120-277V, Bronze finish		6 24563 34030 6
RoughLyte LED			
● VCXL-14-NW-G1-8	RoughLyte LED, Ceiling 4" box mounted, 14W, 4000K (CRI 70), 120-277V		7 83352 02477 0
● VWXL-14-NW-G1-8	RoughLyte LED, Wall 4" box mounted, 14W, 4000K (CRI 70), 120-277V		7 83352 02478 7
Photocontrols			
● P105A	120V Button Photocell		1 90096 00183 5
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



DTD40




BL25



VCXL



VWXL



P105A



FlexScape BL9 LED

Product	Description / Features	UPC
FlexScape BL9 LED		
■ BL9DW-AS7	Low Voltage 9W Bullet Lighting, 3000K, Black, Stake Mount	7 83352 02080 2
■ BL9DW-HS7	Low Voltage 9W Bullet Lighting, 3000K, Bronze, Stake Mount	7 83352 02081 9
FlexScape IL9 LED		
■ IL9DW-A	Low Voltage 9W In-ground Lighting, 3000K, Black	7 83352 02158 8
FlexScape MUL4 LED		
■ MUL4-AS7LED2W	Low Voltage 2W Path Lighting, 3000K, 12V, Black, Stake Mount	7 83352 02046 8
■ MUL4-HS7LED2W	Low Voltage 2W Path Lighting, 3000K, 12V, Bronze, Stake Mount	7 83352 02048 2
FlexScape Low Voltage Transformer		
■ TC152-12TP	Voltage Control Switch (Low =11.5V, High=12.5V), Line voltage amperage draw: 150VA = 0.9 AMP, integral timer and photocell, 50/60Hz input	7 83352 01504 4
BL5016 Micro Accent		
■ BL5016-AS7	50W MR16, 3000K, 12V, Black, Stake Mount	7 83352 00415 4
■ BL5016-HS7	50W MR16, 3000K, 12V, Bronze, Stake Mount	7 83352 00426 0

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



BL9DW



IL9DW-A



MUL4



TC152-12TP



BL5016



Connected Lighting Controls

Make the leap from smart lighting to super smart lighting with the Interact Pro scalable system with integrated wireless sensors that make connectivity simple.

Connectivity is everywhere, and it is the future and key to unlock your smart building potential. It is unknown territory for some though and can often be perceived as complex.

- No restrictions on light points or building size
- Just add a gateway anytime and unlock more capabilities, no need to change or swap sensors
- Future proof your design and lay the right foundation
- Easy point-2-point commissioning sequence enables the installer to be more in control
- With its 3 tier approach Foundation → Advanced → Enterprise, you can start simple and lay the right foundation and scale up to the next tier to access more benefits by adding a gateway
- Unlock super savings and occupant comfort through adaptive dimming and dwell time features
- Get a complete view of the 3 tiers and compatible products at:
interact-lighting.com/interactproscalablesystem

Interact Pro scalable controls: Smart wireless devices for code and rebate compliancy and to help maximize energy savings

- UID8451/10 wireless On/Off & dimmer switch
- SWS200 wireless scene selector to recall custom scenes
- System Bridge Accessory (SBA) for 0-10V and phase dimming integration
- RFSR10 wireless switch relay, ideal to control plug loads or integrate with 0-10V fixtures
- Optional IRT9015 handheld remote to help fastrack the commissioning process and minimize on-site setup time.



FluxStream LED Strip (FSS) | Pg. 19



UniFrame | Pg. 45



FluxGrid LED (FGG) | Pg. 28



Philips EvoKit Click | Pg. 89



MasterConnect PAR Lamps | Pg. 90



MasterConnect InstantFit LEDtube | Pg. 91


Product	Description / Features		UPC
Interact Pro Foundation Components			
● SWS 200	Philips Smart Wireless Wall Scene Switch (4 button)	NLC	046677559144
● UID8451/10	Philips Smart Wireless Wall Switch, On/Off/Dim Switch (2 button)	NLC	046677455439
● SBAZ10-CS	Interact System Bridge 0-10V Control Module	NLC	
● IRT9015	Interact Retrofit Commissioning Device (Remote)	NLC	87 18696 82759 8
Advanced Components			
● LCN1840/05	Interact Wireless Gateway (North America)	NLC	046677476335
● OCC-DL SENSOR IA CM WH 10/1	Philips Smart Wireless Sensor, OCC-DL Sensor IA CM IP42 WH (presence + daylight detection)	NLC	046677476199
● LCN3120/05	Philips Smart Wireless Sensor, OCC-DL Sensor IA CM IP65 WH (presence + daylight detection)	NLC	046677558895
● RFSR10	Philips Interact Ready RF Switch Relay	NLC	046677571849
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)			



SWS 200



UID8451/10



SBAZ10-CS



IRT9015



LCN1840/05



Occupancy Multi Sensor



LCN3120/05



RFSR10

LED Lamps & Retrofits

Philips MasterClass and CorePro tiers are designed to help professional lighting customers more quickly and easily identify the right product to fit any project or budget.

Philips MasterClass

For every project where exceptional, high quality lighting is required. The MasterClass line of LEDs meets or exceeds applicable industry energy efficiency requirements, featuring improved lifespan over traditional incandescent bulbs and warranties with broad product ranges.

Philips CorePro

For every job requiring efficiency, value and uncompromising quality, these LED lamps are perfect for basic lighting needs across a wide range of applications. The CorePro line of LEDs meet industry efficiency standards and minimize maintenance costs for quick payback.

Philips EvoKit Click

Product	Product Name	Description / Features	UPC
Philips EvoKit Click			
◆ 114157	EvoKit CLKE 2x2 32L 24W 835 UNV SWZCS P1	2x2', 3200lm, 3500K (CRI 80), UNV, Interact Ready	
◆ 114140	EvoKit CLKE 2x2 32L 24W 840 UNV SWZCS P4	2x2', 3200lm, 4000K (CRI 80), UNV, Interact Ready , 4 pack	
◆ 121400	EvoKit CLKE 2x4 42L 29W 835 UNV SWZCS P1	2x4', 4200lm, 3500K (CRI 80), UNV, Interact Ready	
◆ 121392	EvoKit CLKE 2x4 42L 29W 840 UNV SWZCS P4	2x4', 4200lm, 4000K (CRI 80), UNV, Interact Ready , 4 pack	
Philips EvoKit High Efficiency G5			
◆ 113977	EvoKit HE 2x2 31L 20W 835 UNV SWZCS G5	2x2', 3100lm, 3500K (CRI 80), UNV	
◆ 113985	EvoKit HE 2x2 31L 20W 840 UNV SWZCS G5	2x2', 3100lm, 4000K (CRI 80), UNV	
◆ 113993	EvoKit HE 2x4 42L 26W 835 UNV SWZCS G5	2x4', 4200lm, 3500K (CRI 80), UNV	
◆ 114009	EvoKit HE 2x4 42L 26W 840 UNV SWZCS G5	2x4', 4200lm, 4000K (CRI 80), UNV	

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship) ◆ Spec Ready (Ships in 4–6 weeks)



EvoKit Click



EvoKit G5



A19



BR30



GU10



MR16



PAR16

Product	Product Name	Description / Features		UPC
MasterConnect PAR Lamps				
● 553602	8PAR30L/MC/930/F25/IA/120V 6/1FB	PAR30L, 8W, 850lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, Interact Ready	★	046677553609
● 553636	8PAR30L/MC/930/F40/IA/120V 6/1FB	PAR30L, 8W, 850lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, Interact Ready	★	046677553630
● 553669	8PAR30S/MC/930/F25/IA/120V 6/1FB	PAR30S, 8W, 850lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, Interact Ready	★	046677553661
● 553693	8PAR30S/MC/930/F40/IA/120V 6/1FB	PAR30S, 8W, 850lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, Interact Ready	★	046677553692
● 555789	13PAR38/MC/930/F25/IA/120V 6/1FB	PAR38, 13W, 1200lm, 3000K (CRI 90), 25°, 120V, Wireless Dimming, Interact Ready	★	046677555788
● 555813	13PAR38/MC/930/F40/IA/120V 6/1FB	PAR38, 13W, 1200lm, 3000K (CRI 90), 40°, 120V, Wireless Dimming, Interact Ready	★	046677555818
CorePro LED Lamps				
● 550434	8.8A19/PER/927/P/E26/DIM 6/1FB T20	A19, 8.8W, 800lm, 2700K (CRI 90), Dimming, Plastic, Frosted	★	046677550431
● 545897	8.8A19/PER/940/P/E26/DIM 6/1FB T20	A19, 8.8W, 800lm, 4000K (CRI 90), Dimming, Plastic, Frosted	★	046677545895
● 561068	16A19/PER/927/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 2700K (CRI 90), Dimming, Plastic, Frosted	★	046677561062
● 561076	16A19/PER/930/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 3000K (CRI 90), Dimming, Plastic, Frosted	★	046677561079
● 561456	16A19/PER/940/P/E26/DIM 6/1FB T20	A19, 16W, 1600lm, 4000K (CRI 90), Dimming, Plastic, Frosted	★	046677561451
● 545905	7.2BR30/PER/930/P/E26/DIM 6/1FB T20	BR30, 7.2W, 650lm, 3000K (CRI 90), Dimming	★	046677545901
● 457051	9BR30/PER/827-22/P/E26/WG 4/1BC	BR30, 7.2W, 650lm, 2700K (CRI 80), Warm Glow Dimming		
● 457010	8.8BR40/PER/927-22/P/E26/WG 6/1FB T20	BR30, 7.2W, 650lm, 2700K (CRI 90), Warm Glow Dimming		046677457013
● 468140	4GU10/LED/930/F35/DIM/G/120V T20 10/1	GU10, 4W, 380lm, 3000K (CRI 90), 35°, 120V, Dimming	★	046677468149
● 533158	7.3MR16/LED/830/F35/DIM 12V 10/1FB	MR16, 7.3W, 515lm, 3000K (CRI 82), 35°, 120V, Dimming	★	046677533151
● 469998	4.4PAR16S/LED/930/F40/DIM/G/120V 4/1BC	PAR16, 4.4W, 800lm, 2700K (CRI 90), 40°, 120V, Dimming	★	046677469993
● 471144	7PAR20/LED/F40/830/E26/GL/DIM 120V	PAR20, 7W, 500lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677471149
● 529743	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	PAR30L, 10W, 850lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677529741
● 529594	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	PAR38, 12W, 900lm, 3000K (CRI 80), 40°, 120V, Dimming	★	046677529598
Ceramelux High Pressure Sodium (HPS) Lamps				
● 467241	SON 100W E39 ED75 CL SL/12	Mogul Base (E39), 9400lm, 2100K, 12pk / 960 pallet		046677467241
● 467233	SON 150W E39 ED75 CL SL/12	Mogul Base (E39), 15800lm, 2100K, 12pk / 960 pallet		046677467234
● 467217	SON 250W E39 ED58 CL SL/12	Mogul Base (E39), 27000lm, 2100K, 12pk / 432 pallet		046677467210
● 467373	SON 400W E39 ED58 CL SL/12	Mogul Base (E39), 50000lm, 2100K, 12pk / 432 pallet		046677467371
● 368837	C1000S52/ALTO	Mogul Base (E39), 130000lm, 2100K, 6pk / 240 pallet		046677368838
Metal Halide (MH) Lamps				
● 287334	MH175/U 12PK	Mogul Base (E39), 14000lm, 4300K, 12pk / 480 pallet		046677287337
● 274845	MH250/U 12PK	Mogul Base (E39), 21000lm, 4000K, 12pk / 480 pallet		046677274849
● 426023	MH400/U/ED28 12PK	Mogul Base (E39), 36000lm, 4000K, 12pk / 384 pallet		046677426026
● 274498	MH400/U 6PK	Mogul Base (E39), 39000lm, 3900K, 6pk / 144 pallet		046677274498
● 415224	MH1000/U 6PK	Mogul Base (E39), 110000lm, 4000K, 6pk / 90 pallet		046677415228

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship) ◆ Spec Ready (Ships in 4–6 weeks)



PAR20



PAR30L (MasterConnect)



PAR38 (MasterConnect)



HPS



MH





MasterConnect InstantFit T8

InstantFit T5

InstantFit T8

MainsFit

UniversalFit

Product	Product Name	Description / Features		UPC
MasterConnect InstantFit LEDtube				
■ 547299	14T8/48-835/IF20/MC IA 10/1	T8, 14W, 4', 2000lm, 3500K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677547295
■ 547307	14T8/48-840/IF21/MC IA 10/1	T8, 14W, 4', 2100lm, 4000K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677547301
■ 547315	14T8/48-850/IF21/MC IA 10/1	T8, 14W, 4', 2100lm, 5000K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677547318
■ 562736	14.5T8/48-835/MF20/MC IA 10/1	T8, 14.5W, 4', 2000lm, 3500K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677562731
■ 562744	14.5T8/48-840/MF21/MC IA 10/1	T8, 14.5W, 4', 2100lm, 4000K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677562748
■ 562751	14.5T8/48-850/MF21/MC IA 10/1	T8, 14.5W, 4', 2100lm, 5000K (CRI 83), Wireless Dimming, Interact Ready	DLC	046677562755
MasterClass InstantFit LEDtube				
● 467142	24T5HO/46-840/IF35/P/DIM 10/1	T5HO, 24W, 4', 3500lm, 4000K (CRI 82)	DLC	046677467142
● 467159	24T5HO/46-850/IF35/P/DIM 10/1	T5HO, 24W, 4', 3500lm, 5000K (CRI 82)	DLC	046677467159
● 541839	7T8/MAS/24-840/IF11/P 10/1	T8, 7W, 2', 1150lm, 4000K (CRI 82)	DLC	046677541835
● 539874	8.5T8/MAS/36-840/IF14/P 10/1	T8, 8.5W, 3', 1400lm, 4000K (CRI 82)	DLC	046677539870
● 473982	9.5T8/MAS/48-835/IF15/P 10/1	T8, 9.5W, 4', 1500lm, 3500K (CRI 82)		046677473983
● 473990	9.5T8/MAS/48-840/IF16/P 10/1	T8, 9.5W, 4', 1600lm, 4000K (CRI 82)	DLC	046677473990
● 474007	9.5T8/MAS/48-850/IF16/P 10/1	T8, 9.5W, 4', 1600lm, 5000K (CRI 82)	DLC	046677474003
MasterClass InstantFit Energy Advantage				
● 565580	8.9T8/MAS/48-830/IF15/P/DIM 10/1	T8, 8.9W, 4', 1500lm, 3000K (CRI 80)	DLC	0 46677 56558 9
● 565598	8.9T8/MAS/48-835/IF15/P/DIM 10/1	T8, 8.9W, 4', 1500lm, 3500K (CRI 80)	DLC	0 46677 56559 6
● 565606	8.9T8/MAS/48-840/IF16/P/DIM 10/1	T8, 8.9W, 4', 1600lm, 4000K (CRI 80)	DLC	0 46677 56560 2
● 565614	8.9T8/MAS/48-850/IF16/P/DIM 10/1	T8, 8.9W, 4', 1600lm, 5000K (CRI 80)	DLC	0 46677 56561 9
CorePro InstantFit LEDtube				
● 553222	10T8/COR/48-835/IF15/G 10/1	T8, 10W, 4', 1500lm, 3500K (CRI 80)	DLC	046677553227
● 541986	10T8/COR/48-840/IF16/G 25/1	T8, 10W, 4', 1600lm, 4000K (CRI 80)	DLC	046677541989
● 541994	10T8/COR/48-850/IF16/G 25/1	T8, 10W, 4', 1600lm, 5000K (CRI 80)	DLC	046677541996
● 470104	14T8/COR/48-835/IF20/G 10/1	T8, 14W, 4', 2000lm, 3500K (CRI 82)	DLC	046677452759
● 470112	14T8/COR/48-840/IF21/G 10/1	T8, 14W, 4', 2100lm, 4000K (CRI 82)	DLC	046677453251
● 470120	14T8/COR/48-850/IF21/G 10/1	T8, 14W, 4', 2100lm, 5000K (CRI 82)	DLC	046677452483
CorePro MainsFit LEDtube				
● 477331	12.5T8/COR/48-840/MF18/G 10/1	T8, 12.5W, 4', 1800lm, 4000K (CRI 80), UL Type B	DLC	046677477332
CorePro UniversalFit LEDtube				
● 539972	16T8/LED/48-840/UF18/G 10/1	T8, 16W, 4', 1800lm, 4000K (CRI 80)		046677539979
Linear Fluorescent Lamps				
● 135103	F54T5/850/HO/ALTO 40PK	T5 (Medium Bipin), 54W, 5000lm, 5000K (CRI 80), 40 Pack		046677135102
● 290833	54W/840 Min Bipin T5 HO ALTO UNP	T5 (Miniature Bipin), 54W, 5000lm, 4000K (CRI 80), 40 Pack		046677290832
● 479626	F32T8/TL941/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 4100K (CRI 90), 30 Pack		046677479626
● 479634	F32T8/TL950/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 5000K (CRI 90), 30 Pack		046677479633
● 479642	F32T8/TL965/ALTO 30PK	T8 (Medium Bipin), 32W, 2600lm, 6500K (CRI 90), 30 Pack		046677479640
● 479600	F32T8/TL935/ALTO 30PK	T8 (Medium Bipin), 32W, 2625lm, 3500K (CRI 90), 30 Pack		046677479602
● 281675	F32T8/TL835 PLUS ALTO 30PK	T8 (Medium Bipin), 32W, 2950lm, 3500K (CRI 85), 30 Pack		046677281670
● 281790	F32T8/TL841 PLUS ALTO HV 30PK	T8 (Medium Bipin), 32W, 2950lm, 4100K (CRI 85), 30 Pack		046677281793
● 281816	F32T8/TL850 PLUS ALTO HV 30PK	T8 (Medium Bipin), 32W, 2950lm, 5000K (CRI 82), 30 Pack		046677281816
● 423889	F40T12/CWSupreme/ALTO	T12 (Medium Bipin), 2600lm, 4100K, 30 Pack		046677423889
● 423194	F96T12/CW Supreme/ALTO 15PK	T12 (Single Pin), 5000lm, 4100K, 15 Pack		046677423193

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship) ◆ Spec Ready (Ships in 4–6 weeks)

ADVANCE

by @signify



Ballasts & Electronics

Advance has a long standing tradition of being the name in quality and reliable lighting components. With drivers, modules, and ballasts all under the same brand, Advance offers the latest in lighting innovations to give you the features you are looking for. We invite you to learn more about what sets us apart and why we continue to be a leader in lighting components.

Advance Express

Advance Express is more than just LED Drivers. It is a program for our distributor partners to help their customers address luminaire component failure in the field by providing an LED driver programming service.

Learn more online:
signify.com/AdvanceExpressCA





Xitanium (Indoor)



Xitanium (Outdoor)



Centium



Optanium



Core & Coil

Product	Product Name	Description / Features	UPC
Xitanium LED Driver		Indoor Linear Driver	
● 513051	XI020C056V054BST2M	XITANIUM 20W 0.1-0.56A 54V 0-10V INT-T	
● 513127	XI054C150V054BST1M	XITANIUM 54W 0.1-1.5A 54V 0-10V INT-T	
● 513168	XI075C200V054BST1M	XITANIUM 75W 0.1-2.0A 54V 0-10V INT-T	
		Indoor Point Driver	
● 512475	XI036C100V054DSM1M	XITANIUM 36W 1.0A 54V 0-10V SSET 1% BE	7 81087 14207 3
		Outdoor and High Bay Driver	
● 514786	XI180C125V200BSF1M	XITANIUM 180W 0.1-1.25A 200V SS INT -F	
● 517714	XI095C275V054BSF1M	XITANIUM 95W 0.1-2.75A 54V SS INT -F 6KV	
		Outdoor Driver	
● 518241	XI055C180V054BSJ1M	XITANIUM 55W 0.1-1.8A SS 120-277V J 6KV	
		TLED Driver	
● 518712	IZT2P16TLEDSC35M		
● 518720	IZT4P16TLEDSC35M		
Centium Ballasts		T8 Instant Start	
● 196873	ICN2P32N35M	CENTIUM ELE BALLAST (2) F32T8 120-277V	7 81087 06912 7
● 109140	ICN4P32N35M	CENTIUM ELE BALLAST (4) F32T8 120-277V	7 81087 09151 7
		T5HO	
● 498394	ICN2S5490CN35M	CENTIUM ELE BALLAST (2) F54/T5HO 120-277V	7 81087 12485 7
● 197871	HCN2S5490CWL35M	CENTIUM ELE BALLAST (2) F54T5/HO 347-480V	7 81087 03066 0
● 119560	HCN4S5490C2LSG35M	CENTIUM ELE BALLAST (4) F54T5/HO 347-480V	7 81087 04788 0
● 119404	ICN4S5490C2LSG35M	CENTIUM ELE BALLAST (4) F54T5HO 120-277V	7 81087 04786 6
		T12 Slimline	
● 503144	ICN2P60N35M	CENTIUM ELE BALLAST (2) F96T12 120-277V	7 81087 13555 6
		T12HO	
● 107136	ICN2S110SC35M	CENTIUM ELE BALLAST (2) F96T12/HO 120-277V	7 81087 08528 8
Optanium Ballasts		T8 Instant Start	
● 107847	IOPA2P32N35M	OPTANIUM ELE BALLAST (2) F32T8 120-277V	7 81087 08683 4
● 510644	GOPA2P32N35M	OPTANIUM ELE BALLAST (2) F32T8 347V	7 81087 14239 4
● 498956	IOPA4P32N35M	OPTANIUM ELE BALLAST (4) F32T8 120-277V	7 81087 11524 4
● 197970	GOPA4P32SC35M	OPTANIUM ELE BALLAST (4) F32T8 347V	7 81087 07392 6
Core & Coil HID Ballasts		HPS	
● 192039	71A87A3001	CORE & COIL HID HPS BAL 1000W S52 120/277/347V KIT	7 81087 03748 5
● 192005	71A82A1001D	CORE & COIL HID HPS BAL 250W S50 120/277/347V KIT	7 81087 03123 0
● 192013	71A84A3001D	CORE & COIL HID HPS BAL 400W S51 120/277/347V KIT	7 81087 03431 6
		MH	
● 192831	71A52A2001D	CORE & COIL HID MH BAL 70W M98/143 120/277/347V KIT	7 81087 07815 0
● 192930	71A53A0001D	CORE & COIL HID MH BAL 100W M90/140 120/277/347V KIT	7 81087 07816 7
● 191866	71A55A0001D	CORE & COIL HID MH BAL 175W M57 120/277/347V KIT	7 81087 09654 3
● 191874	71A57A0001D	CORE & COIL HID MH BAL 250W M58 120/277/347V KIT	7 81087 09823 3
● 191890	71A60A1001D	CORE & COIL HID MH BAL 400W M59 120/277/347V KIT	7 81087 09665 9
● 191916	71A65A2001	CORE & COIL HID MH BAL 1000W M47 120/277/347V KIT	7 81087 02195 8

● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)



Budget LED

Solid lighting, saving energy

PILA offers an essential selection of lighting products. By keeping our range simple and focused on popular applications, we ensure you get lighting of the highest possible quality at a competitive price. Our LED lamps and luminaires are an excellent choice for replacing their conventional equivalents.



Product	Description / Features	UPC
PILA Disk		
● PILADISC4R30K	Disk 4" Round, 700lm, 3000K (CRI 80), 120V, Dimmable, 4-Pack	0 46677 60004 4
● PILADISC6R30K	Disk 6" Round, 900lm, 3000K (CRI 80), 120V, Dimmable, 4-Pack	0 46677 60005 1
PILA Retrofit Downlight		
● PILARETR4R30K	Retrofit Downlight 4" Round, 600lm, 3000K (CRI 80), 120V, Dimmable, 6-Pack	0 46677 60006 8
● PILARETR5R30K	Retrofit Downlight 5" Round, 650lm, 3000K (CRI 80), 120V, Dimmable, 6-Pack	0 46677 60007 5
PILA Linear High bay		
● LH24L40KU	Linear High bay, 183W, 24000lm, 4000K (CRI80), UNV	1 90096 13108 2
PILA Round High bay		
● RH24L40KU	Round High bay, 183W, 24000lm, 4000K (CRI80), UNV	1 90096 13107 5
PILA Shop Light		
● SH45L40K1	4' Shop Light, 45W, 4500lm, 4000K (CRI 80), 120V, White	1 90096 13071 9
PILA Strip		
● ST422L40KU	4' Strip, 20W, 2200lm, 4000K (CRI 80), UNV	1 90096 13086 3
PILA Wraparound		
● WP440L40KU	4' Wraparound, 48W, 4000lm, 4000K (CRI 80), UNV	1 90096 13092 4
PILA Panel		
● BP2230L35KU	2x2' Panel, 30W, 3000lm, 3500K (CRI 80), UNV, 0-10V Dimmable	1 90096 13078 8
● BP2230L40KU	2x2' Panel, 30W, 3000lm, 4000K (CRI 80), UNV, 0-10V Dimmable	1 90096 13080 1
● BP2448L35KU	2x4' Panel, 30W, 4800lm, 3500K (CRI 80), UNV, 0-10V Dimmable	1 90096 13079 5
● BP2448L40KU	2x4' Panel, 30W, 4800lm, 4000K (CRI 80), UNV, 0-10V Dimmable	1 90096 13081 8
PILA Flood Light		
● FL10W40K1	Flood light, 10W, 850lm, 4000K (CRI 80), 120V, Black	1 90096 13072 6
● FL30W40K1	Flood light, 30W, 2550lm, 4000K (CRI 80), 120V, Black	1 90096 13074 0
● FL50W40K1	Flood light, 50W, 4250lm, 4000K (CRI 80), 120V, Black	1 90096 13075 7
● FL70W40K1	Flood light, 70W, 5950lm, 4000K (CRI 80), 120V, Black	1 90096 13076 4
PILA Wall Pack LED		
● TWP20W40K1	Wall Pack, 20W, 4000K (CRI 70), 120-277V, Bronze, Includes Photocontrol	1 90096 13077 1
● Stock Ready (2-Day Quick Ship) ■ Design Ready (10-Day Quick Ship)		



Brand Line Card

Signify proudly markets the best lighting brands in the world.

IoT Platform

interact

A secure IoT platform with software applications that deliver benefits to professional customers across a variety of business verticals.

interact-lighting.com

Lamps & Controls

PHILIPS

Global lighting leader in LED and conventional lamps for every application.

lighting.philips.ca

Electronics

ADVANCE
by @signify

Offering a full range of reliable and robust ballasts, LED drivers and lighting components for the electrical wholesaler and OEM channels.

signify.com/advance

Specialty

COLOR KINETICS

Dynamic and intelligent lighting for architectural indoor, outdoor and entertainment spaces.

colorkinetics.com

Luminaires

GENLYTE SOLUTIONS

Genlyte Solutions is a collection of industry-leading luminaire brands within Signify North America. These brands include Lightolier, Day-Brite CFI, Ledalite, Lumec, Hadco, Gardco, Keene and Alkco.

genlytesolutions.ca

Indoor

ALKCO

Germicidal UV luminaires with UV-C lamp systems have the power to neutralize harmful micro-organisms that might be present.

Day-Brite

CFI
by @signify

Versatile commercial and industrial indoor lighting solutions built for functionality and dependable performance throughout the product life cycle.

cfi-lighting.com

LEDALITE
by @signify

Strikingly aesthetic, unique and bold indoor lighting to make a rich statement in professional, commercial and institutional spaces.

ledalite.com

LIGHTOLIER
by @signify

Impactful, reliable track and downlighting solutions with uncompromising quality for professional and commercial spaces.

lightolier.com

Outdoor

GARDCO
by @signify

Architecturally relevant, configurable and functional lighting solutions that enhance and complement outdoor spaces.

gardcolighting.com

HADCO
by @signify

Pedestrian and Landscape lighting solutions that blend craftsmanship with optical performance to provide a sense of security and beauty in parks and other public or residential settings.

hadco.com

KEENE
by @signify

Contractor-friendly outdoor lighting solutions that help make the most of your time and budget.

keene-lighting.com

LUMEC
by @signify


Contemporary outdoor lighting that blends modern and traditional style with leading-edge engineering to provide functional elegance for urban and roadway spaces.

lumec.com

Learn more about the vast array of lighting solutions available from Signify. Visit www.signify.com/en-ca/brands

Definitions

Some lighting knowledge.



Lumens (lm)

The measurement total light output by a light regardless of direction. Icon to the right denotes products with **field selectable lumen output OR field adjustable wattage selector (FAWS for outdoor)**.



Colour Temperature (CCT)

The colour of light output by a source is referenced as correlated colour temperature (CCT) measured in Kelvins (K). Icon to the right denotes products with **field selectable colour temperature switch**.



Colour Rendering Index (CRI)

The effect a light source has on colour appearance is expressed as CRI, on a scale of 0–100. Natural outdoor light is used as a standard with a CRI of 100. Icon to the right denotes products with options of **CRI of 90 and higher**.



Ratings & Certifications



Protected from total dust ingress. Protected from low pressure water jets from any direction.



Protected from total dust ingress. Protected from high pressure water jets from any direction.



Protected from total dust ingress. Protected from immersion between 15 centimeters and 1 meter in depth.



Protected from total dust ingress. Protected from long term immersion up to a specified pressure.



Products with icon above denote products with **voltage sensing drivers (120–347V)***



The **ENERGY STAR**® symbol is the internationally recognized and trusted mark of high efficiency. Products meet strict technical specifications for energy performance—tested and certified against a number of standards.



A **wet location** is one where water may drip, splash, or flow on or against electrical equipment. Fixtures rated for this have been engineered so that water cannot enter or accumulate in the wireway, lampholders or other electrical parts.



NSF International is an accredited, independent third-party certification body that tests and certifies products to verify they meet these public health and safety standards.



National Electrical Manufacturers Association (NEMA) classification for weather tight enclosures constructed with corrosion-resistant materials.

Standard Universal Voltage (UNV) = 120–277V.

*Unless otherwise stated. See specification sheets for up-to-date information.



The **DesignLights Consortium® (DLC)** promotes high-quality, energy-efficient lighting products in collaboration with utilities and energy efficiency program members, manufacturers, lighting designers, and federal, state, and local entities.




DLC Premium is a higher-performance classification for luminaires and retrofit kits where products meet higher efficacy and lumen maintenance requirements.

A **Network Lighting Controls (NLC)** consists of an intelligent network of individually addressable luminaires and control

devices, allowing for application of multiple control strategies, programmability, building- or enterprise-level control, zoning and rezoning using software, and measuring and monitoring. They can save 35% or more of lighting energy use in commercial buildings while providing a host of additional capabilities and benefits.

Tools & Resources

Bringing us closer together with meaningful digital tools. Additional resources available, contact your Signify representative for details.



Bright ideas

Notes, drawings, and more!

