


Signify  
NatureConnect

NatureConnect Sky  
LP902P NC Sky W60L60



220 V  
240 V

50Hz  
60Hz




IP20




IK02



	Power (W)	Dimensions LxWxH (mm)	EU Energy class of the light source	kg
Sky W60L60	60	598 x 598 x 141	C	13



Installation in NatureConnect island





1


For more detailed mounting instruction, please consult your Signify representative for the NatureConnect system installation manual.



## Installation to ceiling



4x





2 nuts + threaded rod (M6 class 8.8),  
NOT INCLUDED


1



## Connection to mains



connector GST18i5  
5 pole, male




! Cable inspection


1



Always use gloves when installing luminaire.



## Inrush current



### Electrical characteristics

I max (A)	16
T ref (Us)	175
MCB	Max n. of lumin.
B-10 A	26
B-16 A	42
C-10 A	28
C-16 A	44



ATTENTION  
OBSERVE PRECAUTIONS  
FOR HANDLING  
ELECTROSTATIC  
SENSITIVE  
DEVICES

- The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations or the national requirements.
- The light source and/or the external flexible cable contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
- During installation or maintaining the luminaire please use gloves to avoid spots on the cover.
- To remove dust and spots use the following:
  - Dust: use micro fiber cloths only
  - Fingerprints, etc.: use a cleaner for synthetic materials with antistatic properties.
- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked.
- If the above advice is not taken and the luminaires are subject to water ingress, Signify cannot guarantee safe failure & product warranty will become void.