

NatureConnect sky

As part of NatureConnect islands, Sky is the element that provides a view to the sky to create a feeling of spaciousness and connection with nature. It can also be installed separately, recessed in ceilings, always combined with a white light.

Operating and Electrical

Input voltage	220–240 V
Input frequency	50 to 60 Hz
Input current	0.3 A
Inrush current	16 A
Inrush time	175 us
Products per MCB (type B 16A)	42
Power factor (min)	0.9
Surge Protection	1 kV DM and 2 kV CM

Controls and User Interface

Lighting control	Compatible with NatureConnect control system
------------------	--

Mechanical and Housing

Dimensions (LxWxH)	598 x 598 x 140.4 mm
Housing material	Steel
Housing color	White RAL9003
Optical cover/lens type	Polycarbonate
Optical cover/lens finish	Transparent (Sky); Opal (Sun)
Net weight product	13 kg

Product Data

822274820223	LP902P NC Sky W60L60
--------------	----------------------


General Information

Light source	Non-replaceable LED module
Driver included	Yes
Driver/power unit/transformer	PSD (Power supply unit with DALI interface)
Maximum electrical power	60 W
Average electrical power	32 W (typical use case)
Luminaire beam angle	120 °
Lifetime	50 khrs B50L80
Control interface	DALI
Connector	GST18i5 male
Protection class IEC	Safety class I
Ambient temperature range	+10 to +35 °C
Performance ambient temp. Tq	25 °C
Storage temperature	–20 to +60 °C
Ingress protection code	IP20
Mech. impact protection code	IK02
Glow-wire test	650 °C
CE mark	Yes
ENEC mark	–
UL mark	–
Warranty period	5 years

	Sky	Sun rim
Light source colour	Tunable white&blue	Tunable white
Light output	2600 lm	1600 lm
CCT	6500 K to Blue	2700 K to 6500 K
Colour point SDCM	3	4
CRI	80	80
Constant light output (CLO)	No	

NatureConnect sky

Dimensional drawing



Dimensions in mm