



MultiOne


by **signify**

Release notes

MultiOne

Online Configuration tooling

MultiOne Web 1.12



Release Notes August 2025

MultiOne Web URL:

<https://www.multione.signify.com/>

Support:

multione@signify.com

Technical documentation

EU and Global MyLighting portal – [MyLighting: Log On](#)

NAM users portal – [Login | Signify My Technology Portal NAM](#)

For supported devices (see Supported Device List document)

What's new:

- Bug fixes.
- Luminaire Info update.
 - DALI 251 format 4&5

NOTE: it is advised to first clear the cache of the browser before starting to use the new version of MultiOne Web.

Overview of supported features:

AOC (Adjustable Output Current)	CLO & CLOlite (Constant Light Output)
ALO (Adjustable Light Output)	Dynadimmer
DALI PSU (DALI Power Supply Unit)	Line Switch
Min dim level	Dimming Interface
Touch & Dim	Corridor
MTP (Module Temperature Protection)	DTL – Driver Temperature Protection
AST (Adjustable Start-up Time)	DALI 253M
Coded Mains	DC Emergency
Luminaire info – format 0, 3, 4 & 5	Amp Dim
ZTV (0-10V/1-10V) – <i>Partial implementation only. Consists of parameters: curve selection and min dim level</i>	Retrieve production date info of the driver
SR bridge lite device – <i>Partial implementation only. Consists of features: LIP (Luminaire Input Power), RSO (Relay Switched Output), and ZTV (0-10V/1-10V) Output</i>	Box configuration
FlexTune, multi-config mode, Dynadimmer (10 steps with CCT) – relevant only for 929002827206Xi SR 75W 2:0.3-1.0A SNEMPF C170 sXt	FlexTune for indoor and outdoor
Dynadimmer 10 steps – relevant only for 92900387698, Xi LP 200W 0.3-1.05A S1 WL I165	0-10V/1-10V
OWP	