

## NatureConnect daylight W60L180 driver island

NatureConnect daylight W60L180 driver island is the driver for the NatureConnect daylight W60L180 LED panel.

### Controls and User Interface

Lighting control	Compatible with NatureConnect control system
------------------	--


Number of DALI addresses 2

### Mechanical and Housing

Dimensions (LxWxH)	361.1 x 214.8 x 40.7 mm
Gear tray material	Steel
Net weight product	1.5 kg
Net weight product	1.5 kg

### Product data

822274820226	Daylight W60L180 Driver Island
--------------	--------------------------------



### General information

Type of driver	PSD (Power supply unit with DALI interface)
Maximum electrical power	110 W
Control interface	DALI
Connector	GST18i5 male
Protection class IEC	Safety class I
Ambient temperature range	+10 to +35 °C
Performance ambient temp. Tq	25 °C
Storage temperature	-20 to +60 °C
Ingress protection code	IP20
Mech. impact protection code	IK02
Glow-wire test	650 °C
CE mark	Yes
Warranty period	5 years
ENEC mark	-
UL mark	-
Constant light output (CLO)	No

### Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Input current	0.5 A
Inrush current	55 A
Inrush time	290 us
Products per MCB (type B 16A)	8
Power factor (min)	0.9
Surge Protection	1 kV DM and 2 kV CM