Signify NatureConnect



NatureConnect daylight W60L60 driver

NatureConnect daylight W60L60 driver is the driver for the NatureConnect daylight W60L60 LED panel.

Controls and User Interface

Lighting control	81 x 81 x 142 mm
Number of DALI addresses	2

Mechanical and Housing

Dimensions (LxWxH)	595 x 114 x 72 mm
Gear tray material	Steel
Net weight product	1.5 kg


Product data

910505103363

General information

Type of driver	PSD (Power supply unit with DALI interface)
Maximum electrical power	33 W
Control interface	DALI
Protection class IEC	Safety class I
Ambient temperature range	+10 to +35 °C
Performance ambient temp. Tq	25 °C
Storage temperature	-20 to +60 °C
Ingress protection code	IP20
Mech. impact protection code	IKO2
Glow-wire test	650 °C
CE mark	Yes
Warranty period	5 years
ENEC mark	-
UL mark	-
Constant light output (CLO)	No

Dimensional drawing





Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Input current	0.16 A
Inrush current	8 A
Inrush time	175 us
Products per MCB (type B 16A)	40
Power factor (min)	0.9
Surge Protection	1 kV DM and 2 kV CM

Signify NatureConnect | daylight W60L60 driver | Specsheet July, 2025

Specified data are subject to change

