

NatureConnect small island

NatureConnect small island combines Sky and Daylight panels for a fully immersive natural experience.


Controls and User Interface

Lighting control	Compatible with NatureConnect link/ Scene set
Number of DALI addresses	16

Product Data

		q.ty
822274820223	Sky W60L60	3
822274820224	Daylight W60L180 (double panel)	1
822274820226	Daylight W60L180 Driver Island	4
822274820232	Island Gear tray	1
822274820222	Small frame (for suspended installations)	1
822274820716	Cable set (for recessed installations)	1

Dimensional drawing



General Information

Power-on electrical power	125 W
Power-on light output	10 600 lm
Typical electrical power	165 W (Day Rhythtm)
Typical light output	14 300 lm (Day Rhythm)
Maximum electrical power	220 W (Energize)
Maximum light output	20 000 lm (Energize)
Control interface	DALI
Power connector	GST18i5 male
DALI connector	BST14i2 male
Warranty period	5 years

Operating and Electrical

Input voltage	220-240 V
Input frequency	50 to 60 Hz
Input current	2 A
Inrush current	19 A
Inrush time	1000 us
Products per MCB (type B 16A)	6
Power factor (min)	0.9

Mechanical and Housing

Dimensions (LxWxH)	1838 x 1838 x 141 mm
Frame material	Steel
Frame color	Dark grey RAL7043
Luminaire color	White RAL9003
Net weight product	90 kg