

Slim design. All-in flexibility.

The new CoreLine slim wall-mounted



The
professional's
choice

PHILIPS

Philips CoreLine slim wall-mounted brings a sleek, super-slim look to contemporary indoor spaces, making it ideal for decorative applications where appearance matters. With All-in flexibility, uniform light distribution and high energy efficiency, it offers an easy-to-select and easy-to-install solution for renovations and new builds alike.

Slim, unobtrusive design

- Flat diffuser with a modern look
- Product height of only 57 mm
- Suitable for many decorative indoor applications, such as entrance areas, break-out rooms and general areas

Flexible and durable

- 3 diameters: 220 mm, 300 mm, 400 mm
- All-in: Up to 4 lumen outputs and 2 color temperatures in one luminaire
- Flexible control options, including DALI dimming with DC-compatible power supply
- Dust and moisture protected (IP54) and impact resistant (IK08)

Install smarter. Finish sooner.

- Push-in connectors
- Loop-in/loop-out wiring possibility
- Screwless opening and closing
- Suitable for mounting over a junction box

Sustainable choice

- High energy efficiency: 125-142 lm/W
- Long lifetime: 50.000 hours (L90)
- Optional motion detection with daylight sensing, step dimming and wireless grouping function for additional energy savings

Emergency kit available


- Easily transform CoreLine slim wall-mounted luminaires into emergency lighting¹






Dimensions (mm)


D220



D300



D400



Ordering information

Product description	CRI	Power	Lumen output ¹ (switchable with All-in)	Efficacy ¹	CCT (switchable with All-in)	Protection rating	EOC
CoreLine slim wall-mounted		W	lm	lm/W	K		
WL200V 5_8_14_18S/830_840 PSU D220	≥80	4-13	550/850/1400/1850	137-142	3000/4000	IP54/IK08	911401853588
WL200V 11_17_28_34S/830_840 PSU D300		8-24	1150/1700/2800/3400	141-143			911401853688
WL200V 14_21_34_42S/830_840 PSU D400		10-30	1400/2100/3400/4200	140-141			911401853788
WL200V 5_8_14_18S/830_840 PSR MDU D220		5-13	550/850/1400/1850	108-138			911401853888
WL200V 11_17_28_34S/830_840 PSR MDU D300		8-24	1150/1700/2800/3400	138-142			911401853988
WL200V 14_21_34_42S/830_840 PSR MDU D400		11-30	1400/2100/3400/4200	133-140			911401854088
WL200V 18S/830_840 PSED D220		13	1700	130			911401854188
WL200V 33S/830_840 PSED D300		24	3200	133			911401854288
WL200V 42S/830_840 PSED D400		30	4200	140			911401854388

¹ With 4000K PSU

Get all product info and
configuration options in the
[online catalog](#)



© 2026 Koninklijke Philips N.V. All rights reserved.
www.philips.com

a lighting brand of Signify