

Clean look. Flexible light. Ledinaire All-in floodlights



PHILIPS

Philips Ledinaire All-in floodlights combine a clean modern housing with Multi ColorTemp All-in flexibility. With three selectable color temperatures, it is easy to adapt the light on site for a wide range of outdoor applications — from building facades and urban spaces to industrial, logistics, infrastructure, and security areas.

Ready for every job

- White housing for a clean, versatile look across outdoor applications
- All-in: 3 selectable color temperatures in one floodlight (3000K/4000K/6500K)
- Choice of lumen outputs: 2,400 lm, 3,600 lm, 6,000 lm, 12,000 lm
- 4 wattages available: 20 W, 30 W, 50 W, 100 W

Efficient and reliable


- High efficacy: up to 120 lm/W at 4000K
- Long lifetime: 50,000 hours (L80)
- 5-year warranty

Dependable outdoor performance

- Dust and water protection (IP65)
- Impact resistance (IK07/IK08)
- Symmetric light distribution for broad and even illumination




a lighting brand of ©signify




Dimensions (mm)


BVP167 LED24




BVP167 LED36



BVP167 LED60



BVP169 LED120



Ordering information

Product description	Power	Lumen output	Efficacy	CCT (switchable with All-in)	Protection rating	CRI	EOC
Ledinaire All-in floodlights	W	lm	lm/W	K			
BVP167 LED24/830_40_65 PSU 20W SWB WH	20	2,400	120	3000/ 4000/ 6500	IP65 / IK07	80	872110334218899
BVP167 LED36/830_40_65 PSU 30W SWB WH	30	3,600					872110334219599
BVP167 LED60/830_40_65 PSU 50W SWB WH	50	6,000					872110334220199
BVP169 LED120/830_40_65 PSU 100W SWB WH	100	12,000			IP65 / IK08		872110334221899

Proven quality. Effortless installation. Every time.
Philips Ledinaire: Your dependable and affordable choice for every job.



Get all product info and
configuration options in the
[online catalog](#)



© 2026 Koninklijke Philips N.V. All rights reserved.
www.philips.com

a lighting brand of signify