




Fortimo

LED

LED Panel Accessories



Datasheet

LED Panel Accessories

To enable Fortimo and Certaflux LED panels to be used in a wider variety of indoor applications, a wide range of accessories can be used. By selecting these accessories the panels can be used as a pendant or surface mounted luminaire, or in different types of ceilings like plaster ceilings. The accessories can be used for both the Fortimo and Certaflux ranges.

Key features and benefits

- Pendant cable set for suspension applications
- Surface mounted kit and Surface mounted kit basic for surface mounted applications
- Recessed frame and recessed clips to be used in recessed applications like plaster ceilings
- Accessories can be used on both Fortimo and Certaflux LED panels
- See the application matrix to see which accessory can be used with which panel



Ordering data

Commercial product name	EOC	12NC	Box quantity
LED Panel pendant cable accessory set	8710163 615417 00	9290 028 69806	50
LED Panel surface mounted kit basic 6060	8710163 615462 00	9290 028 69906	9
LED Panel surface mounted kit basic 6262	8710163 615493 00	9290 028 70006	9
LED Panel surface mounted kit basic 30120	8710163 615523 00	9290 028 70106	9
LED Panel surface mounted kit basic 60120	8710163 615554 00	9290 028 70206	9
LED Panel surface mounted kit 6060	8710163 615585 00	9290 028 70306	3
LED Panel surface mounted kit 6262	8710163 615615 00	9290 028 70406	3
LED Panel surface mounted kit 30120	8710163 615646 00	9290 028 70506	4
LED Panel surface mounted kit 60120	8710163 615677 00	9290 028 70606	2
LED Panel recessed mounted frame 6060	8710163 615707 00	9290 028 70706	2
LED Panel recessed mounted frame 6262	8710163 615738 00	9290 028 70806	2
LED Panel recessed mounted clips	8710163 615769 00	9290 028 70906	40
LED Panel DC female cable	618647 00	9290 048 49301	100
LED Panel SR female cable	618654 00	9290 048 53001	200


Compatibility table

Product Name	12NC	LED Panel pendant cable accessory set 929002869806	LED Panel surface mounted kit basic 6060 929002869906	LED Panel surface mounted kit basic 6262 929002870006	LED Panel surface mounted kit basic 30120 929002870106	LED Panel surface mounted kit basic 60120 929002870206	LED Panel surface mounted kit 6060 929002870306	LED Panel surface mounted kit 6262 929002870406	LED Panel surface mounted kit 30120 929002870506	LED Panel surface mounted kit 60120 929002870606	LED Panel recessed mounted frame 6060 929002870706	LED Panel recessed mounted frame 6262 929002870806	LED Panel recessed mounted clips 929002870906	DC female cable 929004849301	SR female cable 929004853001
Fortimo LED Panel 6060 830 MD3	929003431506	●	●				●				●		●	●	
Fortimo LED Panel 6060 840 MD3	929003431606	●	●				●				●		●	●	
Fortimo LED Panel 6060 830 TPA MD3	929003431706	●	●				●				●		●	●	
Fortimo LED Panel 6060 840 TPA MD3	929003431806	●	●				●				●		●	●	
Fortimo LED Panel 6262 830 MD3	929003431906	●		●				●				●	●	●	
Fortimo LED Panel 6262 840 MD3	929003432006	●		●				●				●	●	●	
Fortimo LED Panel 30120 830 MD3	929003432106	●			●				●				●	●	
Fortimo LED Panel 30120 835 MD3	929003432206	●			●				●				●	●	
Fortimo LED Panel 30120 840 MD3	929003432306	●			●				●				●	●	
Fortimo LED Panel 30120 830 TPA MD3	929003432406	●			●				●				●	●	
Fortimo LED Panel 30120 840 TPA MD3	929003432506	●			●				●				●	●	
Fortimo LED Panel 60120 830 MD3	929003432606	●				●				●			●	●	
Fortimo LED Panel 60120 840 MD3	929003432706	●				●				●			●	●	
Fortimo HE BL Panel 6060 830/840 MD3	929003432806	●	●				●				●		●	●	
Fortimo HE BL Panel 6060 835/865 MD3	929003432906	●	●				●				●		●	●	
Fortimo HE BL Panel 6262 830/840 MD3	929003433006	●		●				●				●	●	●	
Fortimo HE BL Panel 6060 830-865 TW MD3	929003433306	●	●				●				●		●	●	
Fortimo HE BL Panel 6262 830-865 TW MD3	929003433406	●		●				●				●	●	●	
Fortimo HE BL Panel 6060 840 MC MD3	929003433506	●	●				●				●		●	●	●
Fortimo HE BL Panel 6262 840 MC MD3	929003433606	●		●				●				●	●	●	●
Fortimo HE BL Panel 6262 930/940 MD3	929003457706	●		●				●				●	●	●	
Fortimo HE BL Panel 6060 930/940 MD3	929003457806	●	●				●				●		●	●	
Fortimo HE BL Panel 6060 830/840 MC MD3	929003936901	●	●				●				●		●	●	●
Fortimo HE BL Panel 6060 830/840 SNS MD3	929003937301	●	●				●				●		●	●	●

Mechanical characteristics


LED Panel pendant cable accessory set

Parameter	Min	Typ	Max	Unit
Length	590	600	610	mm
Height	1490	1500	1510	mm
Product mass		120		gram




LED Panel surface mounted kit basic 6060

Parameter	Min	Typ	Max	Unit
Length	612	613	614	mm
Width	612	613	614	mm
Height	71.9	72.4	72.9	mm
Product mass		1200		gram




LED Panel surface mounted kit basic 6262

Parameter	Min	Typ	Max	Unit
Length	637	638	639	mm
Width	637	638	639	mm
Height	71.9	72.4	72.9	mm
Product mass		1250		gram




LED Panel surface mounted kit basic 30120

Parameter	Min	Typ	Max	Unit
Length	1212	1213	1214	mm
Width	312	313	314	mm
Height	71.9	72.4	72.9	mm
Product mass		1650		gram




LED Panel surface mounted kit basic 60120

Parameter	Min	Typ	Max	Unit
Length	1212	1213	1214	mm
Width	612	613	614	mm
Height	71.9	72.4	72.9	mm
Product mass		1900		gram




LED Panel surface mounted kit 6060

Parameter	Min	Typ	Max	Unit
Length	599.5	600.5	601.5	mm
Width	599.5	600.5	601.5	mm
Height	75	76	77	mm
Product mass		1600		gram




LED Panel surface mounted kit 6262

Parameter	Min	Typ	Max	Unit
Length	624.5	625.5	626.5	mm
Width	624.5	625.5	626.5	mm
Height	75	76	77	mm
Product mass		1650		gram




LED Panel surface mounted kit 30120

Parameter	Min	Typ	Max	Unit
Length	1199.5	1200.5	1201.5	mm
Width	299.5	300.5	301.5	mm
Height	75	76	77	mm
Product mass		1950		gram




LED Panel surface mounted kit 60120

Parameter	Min	Typ	Max	Unit
Length	1199.5	1200.5	1201.5	mm
Width	599.5	600.5	601.5	mm
Height	75	76	77	mm
Product mass		3100		gram




LED Panel recessed mounted frame 6060

Parameter	Min	Typ	Max	Unit
Length	645	648	651	mm
Width	623	625	627	mm
Height	75	76	77	mm
Product mass		1160		gram




LED Panel recessed mounted frame 6262

Parameter	Min	Typ	Max	Unit
Length	661	664	667	mm
Width	648	650	652	mm
Height	75	76	77	mm
Product mass		1200		gram




LED Panel recessed mounted clips

Parameter	Min	Typ	Max	Unit
Length	33.5	34	34.5	mm
Width	27.5	28.5	29.5	mm
Height	33	33	34	mm
Product mass		100		gram



LED Panel DC female cable

Parameter	Min	Typ	Max	Unit
Length	145	155	165	mm
Wire strip length	7	8	9	mm
Wire cross section		0.5		mm2
Product mass		10.6		gram
Working voltage			60	Vdc



LED Panel SR female cable

Parameter	Min	Typ	Max	Unit
Length	110	115	120	mm
Wire strip length	8	9	10	mm
Wire cross section		0.3		mm ²
Product mass		5.6		gram
Working voltage			60	Vdc

