



by Signify

Architectural Linear

Suspended, Surface,  
and Wall

Product Selection Guide

Explore Ledalite's comprehensive offering of award winning families and inspiring lighting solutions. Ledalite innovations support design flexibility, allowing specifiers to create their unique vision without compromise.

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable

		Good	Good	Better	Better	Better	Better	Better	Better	Better	Best	Best	Best	Best	Best
Applications	Model	FloatPlane	Sona	Jump	Sync	Verge	ChopStick	BoldPlay	TruGroove suspended/surface/wall (definition 3")	TruGroove suspended/surface/wall micro (performance 1.75")	TruGroove suspended/surface/wall (performance 3")	TruGroove suspended/surface/wall micro (performance 1.75")	TruGroove shapes	ModiFY	EyeLine
	Education	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Office	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Healthcare	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Fashion and Retail	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	QuickShip 10 day	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide	QuickShip Guide
	Standalone Sizes*	4', 6', 8'	4', 8'	4', 8'	4', 8'	4', 8'	4', 6', 8'	4', 8'	2', 3', 4', 5', 6', 8'	2', 2 1/2', 3', 3 1/2', 4', 5', 6', 8'	2', 3', 4', 5', 6', 8'	2', 2 1/2', 3', 3 1/2', 4', 5', 6', 8'	Square: 1'x1', 2'x2' Cross: 2'x2', 4'x4' Rectangle: 1'x4', 2'x4'	2', 3', 4', 5', 6', 8'	4'
Features and Specifications	Continuous Run Increments	4'	4'	4'	4'	4'	2'	4'	1'	6"	1'	6"	-	1'	4'
	Watts (Max/4ft)	65.5	63.7	45.8	56.9	56.9	57.8	56.9	63.9	98.7	63.9	100.4	208	35.4	53.4
	lm/W (Max/4ft)	146.9	150.7	120.6	124.1	124.1	124.7	124.1	129.7	140.5	127.9	140.5	139	140.3	124.9
	Lumens (Max/4ft)	7602	8410	5012	6636	6636	6697	6636	7451	11542	7261	11328	17500	4438	6498
	Lumen Maintenance L80 (l0k) > 60,000h	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Optics	Acrylic diffuser w/optional Down Kits	Acrylic diffuser/Louvers	Symmetric & Asymmetric	Micro-structured light guide w/MesoOptics	Micro-structured light guide w/MesoOptics	Micro-structured light guide w/MesoOptics	Micro-structured light guide w/MesoOptics	Definition Symmetric	Definition Symmetric	Performance Symmetric & Asymmetric	Performance Symmetric & Asymmetric	Definition Symmetric down, Performance Symmetric up	Micro-structured light guide	Micro-structured light guide
	Lens	Fully luminous Silk lens	Fully luminous Silk lens or White louver	Ribbed MesoOptics DX Lens	Fully luminous MesoOptics lens	Fully luminous MesoOptics lens	Fully luminous MesoOptics lens	Fully luminous MesoOptics lens	Fully luminous Silk Lens down, freeform elliptical lens up	Fully luminous Silk Lens down, freeform elliptical lens up	Fully luminous MesoOptic Lens down, freeform elliptical lens up	Fully luminous MesoOptic Lens or QuadOptic louver down, freeform elliptical lens up	Fully luminous silk lens down, freeform elliptical lens up	Fully luminous light guide panel	Fully luminous MesoOptics lens
	Spacing ratio	1.28/1.26	1.25/1.28	1.12/1.56	1.62/1.79	1.62/1.79	-	1.62/1.79	1.23/1.21	1.23/1.22	1.66/1.34	1.44/1.23	1.23/1.23	1.49/1.18	1.29/1.54
	CCT	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K	Static: 2700, 3000, 3500, 4000, 5000K Tunable White: 2700-6500K
	CRI	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80	Static: ≥90 (AccuRender) Tunable White: ≥80
	MDER, w/AccuRender @5000K 0.8 (Daylight is 1.0)	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Mounting Types	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Suspended with variable sling mount aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.	Wall mount or suspended via aircraft cable & tamper-resistant gripper from flat or sloped Drywall, Open Structure or T-Grid ceilings. Standard canopy finish is white. Canopy types 1 & 3 can be finished to match fixture color.
	Related families	Suspended and wall	Suspended and wall	Suspended and wall	Suspended and wall	Suspended and wall	Suspended and wall	Suspended and wall	TruGroove recessed, cove, perimeter, suspended, surface, wall	TruGroove recessed, cove, perimeter, suspended, surface, wall	TruGroove recessed, cove, perimeter, suspended, surface, wall	TruGroove recessed, cove, perimeter, suspended, surface, wall	TruGroove recessed, perimeter, cove, suspended, surface, wall	Suspended and wall	Suspended and wall
	Suspension lengths up to 240"	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Straight runs and/or patterns possible	Straight runs	Straight runs	Straight runs	Straight runs	Straight runs	Straight runs	Straight runs	Straight runs & Patterns	Straight runs & Patterns	Straight runs & Patterns	Straight runs & Patterns	-	Straight runs & (wall to suspended) Patterns	Straight runs & Patterns
	Finish: standard and custom colors	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Factory: Prewired with Self aligning quick connect	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Drivers*	Emergency	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.	Available with factory installed UL924 certified Emergency circuit. Battery pack, Generator transfer device or Sensor bypass relay with power sensing or power interrupt detection.
	UL Dry & Damp location rating	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Advance Xitanium 0-10V (1% Dim)	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
	Advance Xitanium DALI (5% Dim)	✓	✓*	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓	✓
	Lutron EcoSystem LDE1 (<1% Dim, Fade-to-Black)	✓	✓*	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓	✓
	Advance Sensor Ready (1% Dim)	✓	✓	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓	✓
Systems/Controls*	PoE	✓	✓	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓	✓*
	Sensor location	✓ (Integral)	✓ (Integral)	✓ (Remote or Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Integral)	✓ (Remote)	✓ (Integral)	✓ (Remote)
	Interact Pro Wireless Radio (RA)	✓	✓	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓	✓*	✓	✓
	Interact Pro Foundation/Advanced Wireless (CS)	✓	✓	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓	✓*	✓	✓
	Interact Pro Enterprise Wireless Sensor Bundle (SB)	✓	✓*	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓*	✓*
	Interact Office Wired (IO)	✓	✓	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓	✓*	✓*	✓*
Link	Interact Office Advanced Wired Sensor Bundle (SB)	✓	✓*	✓*	✓*	✓*	✓*	✓*	✓	✓	✓	✓	✓*	✓*	✓*
	DLC	Standard and Premium	Standard and Premium	Standard	Standard	Standard	-	-	Standard	Standard	Standard	Standard	-	Standard and Premium	Standard and Premium
Link	Link	Suspended Wall	Suspended Wall	Suspended/Surface Wall/Cantilever	Suspended Wall	Suspended Wall	Suspended Wall	Suspended Wall	Suspended Surface Wall	Coming soon	Suspended Surface Wall	Coming soon		Suspended Wall	Suspended Wall

\*Custom options available on request, please enquire with Ledalite