

Day-Brite



by Signify

Commercial Linear

Strips

Product Selection Guide

Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable



		Good	Good	Better	Best	Best	Best
		SLS Linkable Strip	SCD LED Wide Strip	FluxStream EZ LED Strip	FluxStream Strip	FluxStream Industrial	5F LED Industrial
Applications	Model	SLS Linkable Strip	SCD LED Wide Strip	FluxStream EZ LED Strip	FluxStream Strip	FluxStream Industrial	5F LED Industrial
	Education	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Office	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Healthcare	-	-	★ ★ ★	★ ★ ★	★ ★ ★	★ ★
	Retail	★ ★	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Industrial	★ ★	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Residential	★ ★	★ ★	★ ★	★ ★	★	-
Sizes	2', 4'	2', 3', 4'	4'	2', 4', 8'	2', 4', 8'	4', 8'	
Features and Specifications	Lumen Output	1.6K/3.2K	2K/2.8K/3K/5K	4K/8K	2K/3K/4K/5.5K/6K/7K/ 8K/11K/14K	2K/3K/4K/5.5K/6K/7K/8K/11K/14K	4K/5.5K/7K/8K/11K/14K
	Max. Efficacy	104 lm/W	119 lm/W	104 lm/W	133 lm/W	133 lm/W	159 lm/W
	Color Temperature	4000K	4000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3500/4000/5000K
	Color Rendering	80	80	80	80	80	80
	Lifetime	-	-	L ₇₀ 50,000 hrs	L ₇₀ 100,000 hrs	L ₇₀ 100,000 hrs	L ₇₀ 100,000 hrs
	Ambient Temperature	-10 to +35°C	-10 to +35°C	-10 to +25°C	-20 to +40°C	-20 to +40°C	-20 to +40°C
	Dimming	-	-	0-10V	0-10V	0-10V	0-10V
	Emergency	-	-	✓	✓	✓	✓
	Electro-Connect Modular v Wiring Capability	✓ ¹	✓ ¹	✓ ¹	✓ ¹	✓ ¹	✓ ¹
	DLC	-	Standard	Standard	Standard/Premium	Standard/Premium	Standard/Premium
Warranty	5 years	5 years	5 years	5 years	5 years	5 years	
Integrated Controls	Occupancy Sensor	-	-	✓	✓	✓	✓
	SpaceWise	-	-	-	✓	✓	✓
	Interact	-	-	-	✓	✓	-
	Link						

1. See Electro Connect product specifications for complete details.