

Day-Brite



by Signify

Industrial

Vaportight

Product Selection Guide

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable



		Good	Better	Better	Better	Best
Applications	Model	VTC LED Sealed Strip	Fluxstream Sealed Strip	DW Vaporlume LED	V2 Specification Vaporlume LED	V3W Vaporlume LED
	Big Box Retail	-	-	-	-	-
	Sports/Recreation	★	★	★	★	★
	Warehouse	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Manufacturing	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Cold Storage	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Large Indoor	-	-	-	-	-
Features and Specifications	Complex Environments	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Size(s)	4'	4', 8'	2', 4', 8'	2', 4', 8'	2', 4'
	Lumen Output	3.6K	4K/6K/8K/12K	2.7K/3.5K/4.3K/5.1K/ 7K/10.2K/14K	7K/10.2K/14K	2.7K/3.5K/4.3K/5.1K/ 7K/8K/10K
	Max. Efficacy	104 lm/W	122 lm/W	121 lm/W	122 lm/W	147 lm/W
	Color Temperature	4000K	3000/3500/ 4000/5000K	3000/3500/ 4000/5000K	3000/3500/ 4000/5000K	3000/3500/ 4000/5000K
	Color Rendering	80	80	80	80	80
	Light Distributions	-	-	-	-	-
	Lifetime	L ₇₀ 50,000 hrs	L ₇₀ 100,000 hrs	Up to L ₇₀ 100,000 hrs	Up to L ₇₀ 100,000 hrs	L ₇₀ 100,000 hrs
	Ambient Temperature	-10 to +40°C	-20 to +40°C	-20 to +40°C	-20 to +40°C	-20 to +40°C
	Ingress Protection	IP65	Wet location listed (IP6 optional)	IP65/IP67/NSF	IP65/IP67/NSF	IP65/IP67/NEMA 4X/ NSF
	Dimming	-	0-10V	0-10V	0-10V	0-10V
	Emergency	-	✓	✓	✓	✓
	DLC	-	Standard	Standard	Standard	Standard/Premium
	Other	-	-	-	Stainless steel latches/Top & end hubs	-
Warranty	5 years	5 years	5 years	5 years	5 years	
Integrated Controls	Occupancy Sensor	-	✓ (factory installed)	✓ (factory or field installed)	✓ (factory or field installed)	✓ (factory or field installed)
	SpaceWise	-	✓	✓	✓	✓
	Interact	-	✓	✓	✓	✓
	Link					



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.