



	Good	Good	Good	Good
Prefix	SSS	SRS	GTS	TRS
Description	Straight Square Steel	Straight Round Steel	Tapered Square Steel	Tapered Round Steel
Nominal Height (ft)	10, 12, 14, 15, 18, 20, 25, 30, 35, 40	10, 14, 16, 20, 25, 30	20, 25, 30, 35, 39	20, 25, 30, 35, 39
Diameter (inches)	4 5 6	3 4 5	3.05 x 5.25 3.25 x 6.00 3.11 x 6.41 2.96 x 6.81 2.92 x 7.18 2.87 x 7.13	3.1 x 5.9 3.7 x 6.5 2.4 x 5.9 3.5 x 7.0 2.4 x 6.6 3.8 x 8.0 2.4 x 7.3 3.6 x 8.5 2.4 x 7.8 3.6 x 9.0
Wall Thickness / Gauge	.125", .188" 11 ga., 7 ga.	.125", .188" 11 ga., 7 ga.	.125", .188" 11 ga., 7 ga.	.125" 11 ga.
Base	Cast Base			
Bolt Circle (inches)	8.5, 11, 12 (+/- 0.5)	8.5 (+/- 0.5)	10.75, 12, 12.5, 13, 13.5	9, 9.5, 10, 10.5, 11, 11.5, 12.5
EPA 80 MPH	4.7 - 30.6	2.8 - 19.1	8.6 - 18.0	10.7 - 24.2
EPA 90 MPH	2.0 - 23.9	1.9 - 15.0	5.4 - 13.8	8.5 - 19.3
EPA 100 MPH	n/a - 18.9	1.3 - 12.2	3.0 - 10.7	6.6 - 15.6
EPA 110 MPH	n/a - 14.5	-	n/a - 8.4	5.5 - 13.0
EPA 120 MPH	n/a - 12.0	-	n/a - 6.5	4.5 - 11.0
EPA 130 MPH	n/a - 9.9	-	n/a - 5.1	3.5 - 9.3
Options	Festoon Outlet, Vibration Dampener, Additional Hand Hole, Couplings (Internal Thread), Nipples (External Thread)			
Finish	Bronze, Black, White, Medium Grey, Dark Grey, Galvanized, Finish over Galvanized, Optional (e.g. RAL code), Special (custom color chip)			
Limited Warranty	1 Year			
Link	https://www.signify.com/api/assets/v1/file/content/85dc a31da39e457fab43ab0400f 877a1/08-SSS_Spec_Sheet.pdf	https://www.signify.com/api/assets/v1/file/content/0f68ab0340ac4e3d91b9ab 0400f8ef27/10-SRS_Spec_Sheet.pdf	https://www.signify.com/api/assets/v1/file/content/31716 6b55632497d9b50ab0400f 89cfe/10-GTS_Spec_Sheet.pdf	https://www.signify.com/api/assets/v1/file/content/456 e9b15d2b64faa8c3fab0400f 922f8/10-TRS_Spec_Sheet.pdf

Continued on next page.

Outdoor Site & Area Poles



	Good	Good	Good
Prefix	SSA	RA	TRA
Description	Straight Square Aluminum	Straight Round Aluminum	Tapered Round Aluminum
Nominal Height (ft)	8, 10, 12, 15, 16, 18, 20	8, 10, 12, 15, 18, 20	8, 10, 12, 14, 16, 20, 25, 28, 30, 35, 39
"Diameter (inches)"	4 4.5 5 6	4 4.5 5	3 x 4 3 x 5 4 x 6 4 x 7 4.5 x 8 6 x 10
Wall Thickness / Gauge	.125", .156", .188", .250" 11 ga., 9 ga., 7 ga., 3 ga.	.125", .156", .188" 11 ga., 9 ga., 7 ga.	.125", .156", .188", .250" 11 ga., 9 ga., 7 ga., 3 ga.
Base	"Cast Base Steel Tenon Base Hinged Base"	Cast Base Steel Tenon Base Hinged Base	Cast Base
Bolt Circle (inches)	7, 9, 10, 11, 12	6.5 - 10 (varies)	6.5 - 14.5 (varies)
EPA 80 MPH	2.2 - 42.5	1.2 - 20.2	5.8 - 16.9
EPA 90 MPH	n/a - 32.7	n/a - 15.7	4.0 - 12.9
EPA 100 MPH	n/a - 25.8	n/a - 12.6	2.8 - 10.1
EPA 110 MPH	-	-	-
EPA 120 MPH	-	-	-
EPA 130 MPH	-	-	-
Options	Duplex Receptacle, Ground Fault Receptacle, Vibration Dampener, Additional Hand Hole, Couplings (Internal Thread), Nipples (External Thread)		
Finish	Bronze, Black, White, Medium Grey, Dark Grey, Bronze Anodized, Black Anodized, Medium Grey Anodized, Optional (e.g. RAL code), Special (custom color chip)		
Limited Warranty	1 Year		
Link	https://www.signify.com/api/assets/v1/file/content/c006cadefe634c4b9492ab0400f90d5f/10-SSA-HB_Spec_Sheet.pdf	https://www.signify.com/api/assets/v1/file/content/e63236d5f24b41448df2ab0400f8c5ea/10-RA-HB_Spec_Sheet.pdf	https://www.signify.com/api/assets/v1/file/content/60db5233b8354dc59688ab0400f88a55/08-TRA_Spec_Sheet.pdf



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.