

Day-Brite



by Signify

Commercial Linear

Strips

Product Selection Guide

Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable



		Good	Good	Better	Better	Best
Applications	Model	SDS LED Selectable Strip	FluxStream EZ LED Strip	FluxStream Strip	FluxStream Industrial	5F LED Industrial
	Education	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Office	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Healthcare	-	★ ★ ★	★ ★ ★	★ ★ ★	★ ★
	Retail	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Industrial	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Residential	★ ★	★ ★	★ ★	★	-
	Sizes	2', 4', 8'	4'	2', 4', 8'	2', 4', 8'	4', 8'
Features and Specifications	Lumen Output	1.2K/1.8K/2.4K/3.6K/4.8K/7.3K/9.8K	4K/8K	2K/3K/4K/5.5K/6K/7K/8K/11K/14K	2K/3K/4K/5.5K/6K/7K/8K/11K/14K	4K/5.5K/7K/8K/11K/14K
	Max. Efficacy	119 lm/W	104 lm/W	133 lm/W	133 lm/W	159 lm/W
	Color Temperature	3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3500/4000/5000K
	Color Rendering	80	80	80	80	80
	Lifetime	L70 50,000 hrs	L ₇₀ 50,000 hrs	L70 100,000 hrs	L70 100,000 hrs	L70 100,000 hrs
	Ambient Temperature	-20 to +40°C	-10 to +25°C	-20 to +40°C	-20 to +40°C	-20 to +40°C
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V
	Emergency	✓ (field installed)	✓	✓	✓	✓
	DLC	Standard	Standard	Standard/Premium	Standard/Premium	Standard/Premium
	Warranty	5 years	5 years	5 years	5 years	5 years
Integrated Controls	Occupancy Sensor	-	✓	✓	✓	✓
	SpaceWise	-	-	✓	✓	✓
	Interact	-	-	✓	✓	-
	Link					