

Gardco wall sconce luminaires blend excellent performance with aesthetics. Multiple shapes are available to blend with architecture or make a statement.



Rating	Better	Better	Better	Better	Better	Better	Better	Best	Best
Product	121 LED	111 Mini Sconce	101 LED	104 LED	102 LED	106 LED	161 LED	PureForm Sconce Comfort	PureForm Sconce
Prefix	121	111L	101L	104L	102L	106L	161	PWS	PWS
Lumen Output Range	1,391-12,421	1,400-4,700	1,429-12,045	2,687-9,800	2,687-9,800	2,687-9,800	10,245-27,300	2,448-10,698	6,298-21,800
Efficacy	93-140	115-134	98-136	81-110	81-110	81-110	102-121	102-116	120-137
Distribution	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4	Type 2, 3, 4, BLC
Color Temperature	2700, 3000, 3500, 4000, 5000, Amber	3000, 4000, 5700	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	3000, 4000, 5000	2700, 3000, 3500, 4000, 5000, Amber	2700, 3000, 3500, 4000, 5000, Amber
Mounting Height	8-20'	8-12'	8-20'	8-20'	8-20'	8-20'	15-25'	8-20'	15-25'
0 Uplight	✓	✓	✓	✓	✓	✓	✓	✓	✓
Emergency Battery Backup (0°C to 40°C)	-	-	-	-	-	-	-	✓	-
Emergency Cold Pack (-20°C to 40°C)	✓	-	✓	✓	✓	✓	-	✓	✓
Field Adjustable Wattage Selector (FAWS)	✓	-	-	-	-	-	-	✓	✓
Dual Circuit Control (DCC)	✓	-	✓	✓	✓	✓	✓	-	✓
Auto Profile Dimming	✓	-	✓	✓	✓	✓	✓	✓	✓
Motion Response	✓	-	✓	✓	✓	✓	✓	✓	✓
Wireless Controls	✓	-	✓	✓	✓	✓	-	✓	✓
Photocell	Button	Button	Button, TLRD5,TLRD7,TLRPC	Button	Button	Button	Button	Button	Button
Additional Options	-	Diffusing lens	-	-	-	-	-	-	-
Finish	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey	Bronze, Black, White, Medium Grey, Dark Grey
IP Rating	IP66 LED Light Engine	IP66	IP66 LED Light Engine	IP66 LED Light Engine	IP66 LED Light Engine	IP66 LED Light Engine	IP66	IP65	IP65 housing/ IP66 LED Light Engine
DLC Listing	Premium, Standard	-	Standard	Standard	Standard	Standard	Standard	Premium	Premium
Certifications	Title 24, cULus	Title 24, cULus	Title 24, cULus	Title 24, cULus	Title 24, cULus	Title 24, cULus	cULus	UL/cUL	UL/cUL
Lifetime	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h	L70-100,000h
Limited Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Link									