

Lumec offers a wide range of post top luminaires that are great for urban projects. These timeless luminaires are made from high-quality materials, easy to maintain, and add a distinctive decorative aspect to any contemporary environment. In addition, they offers a variety of optical distributions suitable for several applications, including streets, walkways, and public spaces.

																																			
	Good	Good	Good	Good	Good	Good	Good	Good	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	Better	
Category	Transitional	Transitional	Contemporary	Contemporary	Historical	Historical	Historical	Historical	Historical	Historical	Transitional	Transitional	Transitional	Transitional	Historical	Transitional	Transitional	Historical	Historical	Historical	Historical	Historical	Modern	Historical	Historical	Historical	Historical	Modern	Modern	Modern	Historical	Contemporary	Contemporary		
Style	Nautical	Caged Globe	Sphere	Sphere	Caged Globe	Caged Globe	Caged Globe	Caged Globe	Caged Acorn	Open	Caged Globe	Caged Globe	Caged Globe	Open	Square Lantern	Open	Open	Caged Globe	Open	Caged Globe	Caged Acorn	Caged Acorn	Caged Globe	Square Lantern	Square Lantern	Square Lantern	Square Lantern	Caged Globe	Caged Globe	Caged Globe	Caged Globe	Open	Open		
Product	Candela	LP20	New Westminster Small	New Westminster	Zenith	Zenith	Zenith	Zenith	Ancestra	Ancestra - Comfort	ClassicStyle	Contemporary Lantern	Domus Large	Domus Large - Comfort	L40U	MetroScape	MetroScape - Comfort	Optima	Optima - Comfort	Optima	Serenade DSX	Serenade DSX	SleekVison	Square Lantern	Square Lantern - Comfort	Square Lantern	Square Lantern - Comfort	TownGuide	TownGuide	TownGuide	Transit	UrbanScape	UrbanScape - Comfort		
Prefix	CAND2	LP20	NWS	NWS601	Z12, Z12A	Z14	Z40	Z47A	AT10-C, AT20-C, AT30-C, AT40-C		VLR	L80/L81	DMS60	DMS60-C	L40U	MPTR	MPTR-C	OT10, OT20	OT10-C, OT20-C	XL10	S55, S55C1-C2	S56, S56C1-C2	VLC	S26A, S26N	S26A-C, S26N-C	S40, S41	S40-C, S41-C	PBDP102	DBDP103	PBDP100	TR10	MPTC	MPTC-C		
Light Engine	EcoSwap	LED Lamp Included	Rotomatic (Vertical)	LED Lamp Included	EcoSwap	EcoSwap	EcoSwap	EcoSwap	LEDgine	Comfort	ClearGuide	LEDgine	LEDgine	Comfort	LEDgine	LEDgine	Comfort	LEDgine	LEDgine	LEDgine	LEDgine	LEDgine	ClearGuide	LEDgine	Comfort	LEDgine	Comfort	Mid-Power LEDs	Mid-Power LEDs	Mid-Power LEDs	LEDgine	LEDgine	Comfort		
Lumen Output Range	Up to 5,960	Up to 4,958	Up to 6,555	Up to 5,492	Up to 6,974	Up to 6,425	Up to 6,425	Up to 6,974	Up to 9,412	Up to 7,840	Up to 7,796	Up to 7,644	Up to 9,309	Up to 8,137	Up to 12,184	Up to 15,270	Up to 7,724	Up to 10,591	Up to 7,840	Up to 10,591	Up to 13,036	Up to 13,036	Up to 8,152	Up to 11,674	Up to 8,382	Up to 11,674	Up to 7,382	Up to 10,422	Up to 9,900	Up to 9,235	Up to 9,117	Up to 15,270	Up to 7,724		
Efficacy	Up to 87 LPW	Up to 95 LPW	Up to 93 LPW	Up to 105 LPW	Up to 107 LPW	Up to 99 LPW	Up to 99 LPW	Up to 107 LPW	Up to 122 LPW	Up to 122 LPW	Up to 109 LPW	Up to 104 LPW	Up to 122 LPW	Up to 94 LPW	Up to 101 LPW	Up to 122 LPW	Up to 140 LPW	Up to 94 LPW	Up to 140 LPW	Up to 140 LPW	Up to 130 LPW	Up to 130 LPW	Up to 114 LPW	Up to 117 LPW	Up to 94 LPW	Up to 92 LPW	Up to 109 LPW	Up to 99 LPW	Up to 92 LPW	Up to 120 LPW	Up to 121 LPW	Up to 90 LPW			
Distribution	Type III, V	Type V	Type III, V	Type V	Type III, V	Type III, V	Type III, V	Type III, V	Type II, III, IV, V	Type I, II, III, IV, V	Type III, V	Type II, III, IV, V	Type II, III, IV, V	Type I, II, III, IV, V	Type II, III, IV, V	Type I, II, III, IV, V	Type II, III, IV, V	Type I, II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type III, V	Type I, II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type II, III, IV, V	Type I, II, III, IV, V	Type I, II, III, IV, V		
Color Temperature	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	3000K, 4000K	
Globe/Panels	Clear, Satin	Satin Clear	Acrylic, Polycarbonate Clear, Satin Clear	Acrylic, Polycarbonate Opalin, Satin Clear	Acrylic, Polycarbonate	Acrylic, Polycarbonate	Acrylic, Polycarbonate	Acrylic, Polycarbonate	Acrylic Globe, Flat Glass, Sag Glass	Open	Acrylic, Polycarbonate	PC	Acrylic Globe, Flat Glass, Sag Glass	Open	Clear Acrylic, Polycarbonate	Flat Glass Lens, Open	Open	Acrylic Globe, Flat Glass, Sag Glass	Open	Acrylic, Glass	Acrylic, Glass	Acrylic, Polycarbonate	Clear, Satin Clear	Clear	Clear, Satin Clear	Clear	Clear	Clear, Frosted	Clear	Clear, Frosted	Clear	Acrylic Globe, Flat Glass, Sag Glass	Flat Glass Lens, Open	Open	
Fitter/POD	Standard	SF1, SF2, SF70, SFO, SFS	Standard	Standard	SF24	SF24	SF24	SF24	Standard	Standard	Standard	SF2, SF3, SF70, SF71, SF72, SF73, SF80, SFO, SFS	Standard	Standard	Standard	Multiple Sizes	Multiple Sizes	Multiple Adapters	Multiple Adapters	Multiple Adapters	Oak Lead, Standard	Oak Lead, Standard	Standard	Multiple Adapters	Multiple Adapters	SFR, SF41	Multiple Adapters	Standard	Standard	Standard	Multiple Adapters	Multiple Sizes	Multiple Sizes		
Roof	-	Spun Aluminum	-	-	Spun Aluminum	Spun Aluminum	Spun Aluminum	Spun Aluminum	Copper Cupola	Copper Cupola	Metal Hood	Cast Aluminum	Spun Aluminum	Spun Aluminum	Square	Cast Aluminum	Cast Aluminum	Spun Aluminum	Spun Aluminum	Spun Aluminum	Spun Aluminum	Spun Aluminum	Aluminum	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Spun Aluminum	Cast Aluminum	Cast Aluminum	
Cage/Band	-	Guard	Die Cast Guard	Die Cast Guard	Cast Aluminum	Cast Aluminum	Cast Aluminum	Cast Aluminum	DA, DC, DFN10, DFN20	DA, DC, DFN10	Brim Optional	Standard	Standard	Standard	Standard	Cast Aluminum	Cast Aluminum	DA, DC, DFN10, DFN20	DA, DC, DFN10, DFN20	Copper Cupola	Cast Aluminum	Cast Aluminum	Optional	-	-	-	-	-	-	-	-	-	Cast Aluminum	Cast Aluminum	
Finalal	-	-	-	-	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FNC	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FNC	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FNC	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FNC	FN1, FN2, FN3, FN5, FN6, FN8, FN9, FN10, FNC	FN1, FN2, FN3, FN5, FN6, FN8, FN9, WC, FNC,	FN1, FN2, FN3, FN5, FN6, FN8, FN9, FN10, FN11	FN1, FN2, FN3, FN5, FN6, FN8, FN9, FN10, FN11	FN2, FN3, FN4, FN6, FN8, FN9	FN2, FN3, FN4, FN6, FN8, FN9	Cupola	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FN11	FN1, FN2, FN3, FN4, FN8, FN9, FN10, FN11	FN1, FN2, FN3, FN5, FN6, FN8, NF9, FN10, FNC	FN2, FN3, FN5, FN6, FN8, FN9, FNC	FN1, FN2, FN3, FN5, FN6, FN8, FN9, FN10, FNC	FN2, FN3, FN4, FN8, FN9, FN10, FN11, FNC	FN2, FN3, FN4, FN8, FN9, FN10, FN11, FNC	FN1, FN2, FN3, FN5, FN6, FN8, FN9, FN10, FN11	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Die Cast	Cupola	-	-	
Mounting Height Range	15' - 25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' - 25'	15' -30'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' - 25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -25'	15' -30'	15' -25'	
0 Uplight	-	-	-	-	-	-	-	-	Flat Lens	✓	-	-	Flat Lens	✓	-	✓	✓	Flat Lens	✓	Flat Lens	-	-	-	-	-	-	-	-	-	-	-	Flat Lens	✓	✓	
DALI	-	-	-	-	-	-	-	-	✓	-	✓	✓	✓	-	-	✓	-	-	-	✓	✓	-	-	-	-	-	-	-	-	-	-	-	✓	✓	
Sensor Ready Driver	-	-	-	-	-	-	-	-	✓	✓	✓	✓	✓	-	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓	✓
Service Tag	✓	-	-	-	-	-	-	-	-	-	✓	-	✓	-	-	✓	✓	-	-	-	✓	✓	✓	-	-	-	-	-	✓	✓	✓	-	✓	✓	
Photocell	PH7	-	-	-	PH7	PH7	PH7	PH7	PH8, PHXL	PH8, PHXL	PH8, PH8/347, PH8/480, PHXL	PH8, PHXL	PH7, PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH8, PHXL	PH7, PH8, PHXL	PH7, PH8, PHXL	PH8, PH8/347, PH8/480, PHXL	PH7	PH7	PH7	PH7	PH7	PH8	PH8	PH8	PH8, PHXL	PH8, PHXL	PH8, PHXL	
Receptacle	7 Pin	-	7 Pin	-	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	7 Pin	
Shielding	HS	-	HS	-	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS	HS						