



Outdoor

Parking Garage & Canopy

Product Selection Guide

Gardco and Stonco garage and canopy luminaires provide a high quality solution specifically designed to meet the unique challenges of these applications. Whether you are seeking energy savings or require an enhanced sense of security and optimal light levels, our portfolio has you covered.



Stonco



Stonco



GARDCO



GARDCO



GARDCO



GARDCO

| | Good | Good | Better | Best | Best | Best |
|-----------------------|---|--|--|--|---|---|
| | Garage and Canopy Dual Select | Garage and Canopy Round Dual Select | G3 | SoftView | SlenderForm Canopy | SlenderForm Canopy Recessed |
| Prefix | GC | GC | G3 | SVPG | SFC | SFRC |
| Lumen Output Range | 4100-12400 | 4100-12400 | 2,750-13,200 | 2,030-17,900 | 4,630-14,700 | 4,630-14,700 |
| Efficacy | 125-150 | 125-150 | 104-148 | 83-148 | 107-125 | 107-125 |
| Distribution | Type 5 Symmetric | Type 5 Symmetric | Type 5 Square, Concentrated Downlight, Type 1R, Type 3 | Type 1R, 3, 5, Concentrated Downlight | Type 3, 5 Rectangular, 5 Wide, Concentrated Downlight | Type 3, 5 Rectangular, 5 Wide, Concentrated Downlight |
| Color Temperature | 3000, 4000, 5000K (Field Selectable) | 3000, 4000, 5000K (Field Selectable) | 3000, 4000, 5000 | 3000, 4000, 5000 | 3000, 4000, 5000 | 3000, 4000, 5000 |
| Uplight | - | - | - | ✓ | - | - |
| Motion Response | ✓ | ✓ | ✓ | ✓ | ✓ | - |
| Wireless Controls | - | - | ✓ | ✓ | - | - |
| Photocell | ✓ | ✓ | Button | - | Button | - |
| Additional Options | - | - | Bird Guard, Balanced offset j-box for pendant | Shielding, various Bird Guards, Wire Guard | Diffuse lens, Bird Guard | Diffuse lens, Bird Guard |
| Mounting | Surface Mount | Surface Mount | Surface Mount | Surface Mount, Pendant Mount, Trunnion Mount, Wall Mount | Surface Mount | Recessed |
| Vibration | - | - | Bridge/Overpass option | Normal or Bridge/Overpass | - | - |
| Finish | Bronze | Bronze | Bronze, White, Black, Medium Grey | Bronze, White, Medium Grey | Medium Grey | Medium Grey |
| IP Rating | IP65 | IP65 | IP66 | IP66 | IP66 | IP66 |
| IK Rating | - | - | - | IK10 | - | - |
| Surge Protection | - | - | 10kV/20kA | 10kV/10kA | 20kV/10kA option | 10kV/10kA |
| DLC Listing | Standard | Standard | Standard and Premium | Standard and Premium | Standard | Standard |
| Certifications | cULus | cULus | cULus | cULus | cULus | cULus |
| Lifetime | L70-60,000h | L70-60,000h | L70-100,000h | L70-100,000h | L70-100,000h | L70-100,000h |
| Luminaire Useful Life | 100,000+ hours accounting for LED life, driver life, etc. - see specification sheet for details | | | | | |
| Limited Warranty | 5 years | 5 years | 5 years | 5 years | 5 years | 5 years |
| Link | | | | | | |

