



Top Selling Stock Ready Luminaires

2023 Q2 Select Edition

CHLORIDE

LIGHTOLIER

Day-Brite

Stonco

Top Stock Ready Items

**Stock, Sell, and Restock with
Signify's best movers!**

Save time and improve efficiencies by consolidating your stock purchases with Signify's top stocking product families which includes a wide range of unique adjustable color temperature and/or lumen outputs field selectable product lines. These products are priced right and ready to go!

For the full portfolio of Stock Ready items,
visit www.signify.com/stockready for the full catalog




A long history of excellence

As the global leader in lighting for more than 130 years, Signify has the know-how and most comprehensive portfolio to meet any application. We achieved 100% Carbon Neutrality in 2020. We are number 1 in conventional lamps, LED and Connected lighting. We have over 17,750 patents. We invest 4.8% of total sales in R&D which is two times our nearest competitor! Partnership is more than sales.

Let's grow together. We are ready to go with you.

Quick and reliable service out of our distribution centers.



Find just what you need

Our Stock Ready portfolio makes it easy to find just what you need. Our products are designed for easy ordering through Signify's MyLighting portal, easy to install with minimal steps, and competitively priced to meet the demands of budget conscious projects focused on cost and energy. Distributors can also benefit from our Stock Ready program which offers deals on freight, guaranteed sales, price change reimbursement, delistment notifications, marketing support, merchandising, and more.



Certifications & labels




interact
ready.

The right solution


Signify provides the solution to every lighting need whether it's lighting and connecting your public spaces, giving your commercial building an energy saving upgrade, or working on a yet to be constructed hospital, we've got you covered.




Government



Cities



Offices



Industry



Education



Retail

Stock up on our new field selectable products

With the unique convenience of adjustable color temperatures and/or lumen outputs, our new Field Selectable product lines make it easy to always have the right product for the job. Field Selectable products give you the added benefit of carrying one SKU versus multiple SKUs, keeping your inventory low and turns high. These product lines are priced right as part of our Ready-to-go offering.



Lumen
Select Switch



CCT with
Select Switch

LIGHTOLIER

Day-Brite

Stonco



Flat Downlight
LED dual select



Commercial Retrofit Downlight
LED dual select



Residential Retrofit Downlight
LED select



Gimbal & Downlight
LED dual select



Surface Mount Downlight
LED dual select



SDS Selectable Strip
LED dual select



NWL Wraparound
LED select



FCY Value High Bay
LED dual select



Selectable Backlit Panel
LED select



Slim Flood
LED dual select



Wall Pack
LED dual select



Adjustable Slim Wall Pack
LED dual select


Indoor luminaires



Residential Retrofit Downlight 2




Commercial Retrofit Downlight 3




Flat Downlight 4




Surface Mount Downlight 5




Downlight & Gimbal 6



Select Backlit Panel 7



FPEM 8



FlatPanel Gen2 9



SDS Selectable Strip 10



FCY Value High Bay 11



NWL Wraparound 12



Exit signs 13



Value+ Family 14

Outdoor luminaires



Slim Flood LED dual select 15



Wall Pack LED dual select 16



Adj. Slim Wall Pack LED dual select 17

Indoor & Outdoor luminaires



Residential Retrofit Downlight

An LED retrofit as
easy as snap and click

Hassle-free install will save you time and frustration on the job site. You may not even need to open your toolbox.

**Top selling
residential
product**

Residential Retrofit Downlight 5/6"

Residential Retrofit Downlight 4"



Why choose Retrofit Downlight?

- Adjustable color temperature switch allows you to make choices while your install or afterward
- Utilizes existing frames to make replacing old downlighting and upgrading to LED a truly easy task
- Flexible springs allow for installation without tools
- Quick-connect plug and medium-based socket adapter means no extra accessories to purchase



Residential Retrofit Downlight LED select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|---|--------------|--------------|--------------------------------------|-------------|-----------------|---------------------|
| Residential Retrofit Downlight - 4" Round | | | | | | |
| RD4R79301W | 190096131976 | 911401868184 | 4" Round, 700 lumen 90CRI 3000K 120V | Energy Star | 16/560 | PA TN CA |
| RD4R79SCT1W | 190096131952 | 911401867984 | 4" Round, 700 lumen 90CRI 5CCT 120V | Energy Star | 12/300 | PA TN CA |
| Residential Retrofit Downlight - 5/6" Round | | | | | | |
| RD6R99301W | 190096131983 | 911401868284 | 6" Round, 900 lumen 90CRI 3000K 120V | Energy Star | 16/560 | PA TN CA |
| RD6R99SCT1W | 190096131969 | 911401868084 | 6" Round, 900 lumen 90CRI 5CCT 120V | Energy Star | 12/300 | PA TN CA |





Commercial Retrofit Downlight

Bright, brighter, **brightest**

Will reduce onsite time and headaches for busy installers with its adjustable lumen and color output switch.




Why choose Commercial Retrofit Downlight?

- Adjustable lumen output and color temperature switch allows you to make choices while you install or afterward
- Great for different ceiling heights and different light level needs
- Sturdy metal clips provide a solid fit and easy installation
- Out-of-the-box pre-wired with flexible metal conduit
- 50,000 hour rated life (L70)


Commercial Retrofit Downlight LED dual select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|--|--------------|--------------|---|-------------|-----------------|---------------------|
| Commercial Retrofit Downlight – 6" Round | | | | | | |
| CR6RLMCCT | 190096131273 | 911401870181 | 6" Round, 700-1500 lumen 90CRI 3000K-3500K-4000K White Finish 120-347V | Energy Star | 120 | CA, TN, PA |
| Commercial Retrofit Downlight – 8" Round | | | | | | |
| CR8RLMCCT | 190096131280 | 911401870281 | 8" Round, 1000-2000 lumen 90CRI 3000K-3500K-4000K White Finish 120-347V | Energy Star | 288 | CA, TN, PA |



Flat Downlight

Make your next lighting project faster and easier, with a product from a name you can trust.




Why choose Flat Downlight?

- FD dual select: 5 field selectable CCT and multiple lumen selection options
- Quick and easy installation without frame or reflector
- Junction box clips to luminaire meeting National Electric Code (NEC)
- Dimmable to 10%
- Lifetime >50,000 hours (L70)
- IC-rated for insulation direct contact
- UL1598 wet location rated



Flat Downlight LED dual select


| Catalog Number | UPC Code | Model Number | Product Description | Compliance | C/P Qty | Dist. Center |
|---------------------------------|--------------|--------------|--|-------------|---------|--------------|
| Flat Downlight Round | | | | | | |
| FD3R7ESCT1W | 190096196166 | 911401883584 | 3" Round, 480lm 2700K-3000K-3500K-4000K-5000K White Finish 120V | Energy Star | 12/384 | PA TN CA |
| FD3RSLMZ10SCTUW | 190096131679 | 911401825284 | 3" Round, 370lm/500lm 90CRI 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 12/288 | PA TN CA |
| FD4R7ESCT1W | 190096131686 | 911401825384 | 4" Round, 700lm 2700K-3000K-3500K-4000K-5000K White Finish 120V | Energy Star | 20/360 | PA TN CA |
| FD4RSLMZ10SCTUW | 190096131693 | 911401825484 | 4" Round, 540lm/700lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 12/216 | PA TN CA |
| FD5R9ESCT1W | 190096196173 | 911401883684 | 5" Round, 900lm 2700K-3000K-3500K-4000K-5000K White Finish 120V | Energy Star | 6/270 | PA TN CA |
| FD5RSLMZ10SCTUW | 190096131709 | 911401825584 | 5" Round, 900lm/1100lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 6/180 | PA TN CA |
| FD6R11ESCT1W | 190096131716 | 911401825684 | 6" Round, 1100lm 2700K-3000K-3500K-4000K-5000K White Finish 120V | Energy Star | 10/300 | PA TN CA |
| FD6RSLMZ10SCTUW | 190096131723 | 911401825784 | 6" Round, 900lm/1100lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 6/180 | PA TN CA |
| FD8R13ESCT1W | 190096196180 | 911401883784 | 8" Round, 1300lm 2700K-3000K-3500K-4000K-5000K White Finish 120V | Energy Star | 6/144 | PA TN CA |
| FD8RSLMZ10SCTUW | 190096131730 | 911401825884 | 8" Round, 1100lm/1300lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 6/144 | PA TN CA |
| Flat Downlight Square | | | | | | |
| FD3SSLMZ10SCTUW | 190096131747 | 911401825984 | 3" Square, 370lm/500lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 12/288 | PA TN CA |
| FD4SSLMZ10SCTUW | 190096131754 | 911401826084 | 4" Square, 540lm/700lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 12/216 | PA TN CA |
| FD6SSLMZ10SCTUW | 190096131761 | 911401826184 | 6" Square, 900lm/1100lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 6/180 | PA TN CA |
| FD8SSLMZ10SCTUW | 190096131778 | 911401826284 | 8" Square, 1100lm/1300lm 2700K-3000K-3500K-4000K-5000K White Finish UNV | Energy Star | 6/144 | PA TN CA |
| Flat Downlight Accessory | | | | | | |
| FD4NCP | 190096131198 | 911401865081 | 4" New Construction Plate | — | 40/2800 | Factory |
| FD6NCP | 190096131204 | 911401865181 | 6" New Construction Plate | — | 40/2000 | Factory |



Surface Mount Downlight

The shallow ceiling **problem solver**

Ideal when faced with a challenging ceiling, but you still want a good-looking downlight.




Why choose Surface Mount Downlight?

- Adjustable lumen output and color temperature switch allows you to make choices while you install or afterward
- Easy to install on standard J-boxes
- Surface mount downlight solves the problem of limited plenum space
- Glare controlling lens for comfortable light distribution
- Affordable alternative to Air-Seal IC recessed housings
- Support wire attached for easy installation


Surface Mount Downlight LED dual select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|--|--------------|--------------|--|-------------|-----------------|---------------------|
| Surface Mount Downlight 5" Round | | | | | | |
| SD5R7ESCT1W | 190096131785 | 911401836484 | 5" Round, 700lm 90CRI 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/672 | PA TN CA |
| SD5RSLMZ10SCTUW | 190096131792 | 911401836584 | 5" Round, 540lm/700lm 90CRI 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/672 | PA TN CA |
| Surface Mount Downlight 7" Round | | | | | | |
| SD7R10ESCT1W | 190096131808 | 911401836684 | 7" Round, 1000lm 90CRI 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/360 | PA TN CA |
| SD7RSLMZ10SCTUW | 190096131815 | 911401836784 | 7" Round, 800lm/1000lm 90CRI 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/360 | PA TN CA |
| Surface Mount Downlight 9" Round | | | | | | |
| SD9RSLMZ10SCTUW | 190096131822 | 911401836884 | 9" Round, 900lm/1200lm 90CRI 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/192 | PA TN CA |
| SD9R12ESCT1W | 190096196197 | 911401883884 | 9" Round, 1200lm 90CRI 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/192 | PA TN CA |
| Surface Mount Downlight 11" Round | | | | | | |
| SD11RSLMZ10SCTUW | 190096131839 | 911401836984 | 11" Round, 1200lm/1500lm 90CRI 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 6/162 | PA TN CA |
| SD11R15ESCT1W | 190096196203 | 911401883984 | 11" Round, 1500lm 90CRI 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 6/162 | PA TN CA |
| Surface Mount Downlight 14" Round | | | | | | |
| SD14RSLMZ10SCTUW | 190096131846 | 911401837084 | 14" Round, 1600lm/2000lm 90CRI 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 6/90 | PA TN CA |
| SD14R16ESCT1W | 190096196210 | 911401884084 | 14" Round, 2000lm 90CRI 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 5/90 | PA TN CA |



Downlight and Gimbal

Provides an
easy install solution




Why choose Downlight and Gimbal?


- Adjustable lumen output and color temperature switch allows you to make choices while your install or afterward
- Sizes: 3, 4, and 6 inch round
- Dimming: TRIAC down to 10%
- Installation: Easy to adjust at the time of installation
- Lifetime: L70 at 50,000 hours
- Listings: ENERGY STAR®, Title 24 (JA8-2016), damp location, ETL listed. Airseal IC.



Downlight and Gimbal LED dual select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Dist. Center |
|---------------------------|--------------|--------------|--|-------------|-----------------|--------------|
| Downlight 3" Round | | | | | | |
| DL3RSLMZ10SCTUW | 190096131853 | 911401837684 | 3" Round, Downlight 370lm/500lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/320 | PA TN CA |
| DL3R4ESCT1W | 190096196234 | 911401884284 | 3" Round, Downlight 500lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/384 | PA TN CA |
| Downlight 4" Round | | | | | | |
| DL4RSLMZ10SCTUW | 190096131877 | 911401837884 | 4" Round, Downlight 540lm/700lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/240 | PA TN CA |
| DL4R7ESCT1W | 190096131860 | 911401837784 | 4" Round, Downlight 700lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 20/640 | PA TN CA |
| Downlight 6" Round | | | | | | |
| DL6RSLMZ10SCTUW | 190096131891 | 911401838084 | 6" Round, Downlight 900lm/1100lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/160 | PA TN CA |
| DL6R11ESCT1W | 190096131884 | 911401837984 | 6" Round, Downlight 1100lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 10/300 | PA TN CA |
| Gimbal 3" Round | | | | | | |
| GB3RSLMZ10SCTUW | 190096131907 | 911401837184 | 3" Round, Gimbal 370lm/500lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/320 | PA TN CA |
| GB3R4ESCT1W | 190096196227 | 911401884184 | 3" Round, Gimbal 500lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/384 | PA TN CA |
| Gimbal 4" Round | | | | | | |
| GB4RSLMZ10SCTUW | 190096131921 | 911401837384 | 4" Round, Gimbal 540lm/700lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/240 | PA TN CA |
| GB4R7ESCT1W | 190096131914 | 911401837284 | 4" Round, Gimbal 700lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 8/480 | PA TN CA |
| Gimbal 6" Round | | | | | | |
| GB6RSLMZ10SCTUW | 190096131945 | 911401837584 | 6" Round, Gimbal 900lm/1100lm 2700K-3000K-3500K-4000K-5000K UNV | Energy Star | 8/160 | PA TN CA |
| GB6R11ESCT1W | 190096131938 | 911401837484 | 6" Round, Gimbal 1100lm 2700K-3000K-3500K-4000K-5000K 120V | Energy Star | 6/240 | PA TN CA |





Selectable Backlit Panel

Make the **easy selection** and carry less stock with more options.



Why choose Selectable Backlit Panel?


- 3 color temperature selections, 3 wattage choices, and 3 sizes available
- Numerous options for your customers, while keeping inventory levels and SKU count low
- Available for use in recessed, suspended and surface mount applications

Selectable Backlit Panel

| Catalog Number | UPC Code | Model No. | Product Description | Compliance | C/P Qty | Dist. Center |
|--------------------------|--------------|--------------|--|--------------|---------|---------------------|
| Selectable Backlit Panel | | | | | | |
| 2SBP3040L8CS-2-UNV-DIM | 190096131006 | 911401837781 | 2x2, Lumens Select, 80CRI, Color Select 3500K/4000K/5000K, UNV 120-277V, 0-10V (30W/34W/39W) | DLC Standard | 4/40 | CA, TN, PA, IL, GA* |
| 2SBP3550L8CS-4-UNV-DIM | 190096131013 | 911401837881 | 2x4, Lumens Select, 80CRI, Color Select 3500K/4000K/5000K, UNV 120-277V, 0-10V (35W/38W/50W) | DLC Standard | 4/20 | CA, TN, PA, IL, GA* |

FPEM

Ideal for renovations and new construction opportunities where remote mounting is a necessity.



Why choose FPEM?





- A simple, time saving solution for emergency remote mounting applications
- Designed for use with several configurations of panels, wraps, and strips product families
- Operates an LED load of up to 10.4 W at nominal battery voltage for a minimum of 90 minutes
- Indicator test switch and plate mounting compatibility with grid ceiling, drywall, or open ceiling application



FluxPanel

| Catalog Number | UPC Code | Model Number | Product Description | Case/Pallet Qty | Distribution Center |
|-----------------------|--------------|--------------|---|-----------------|---------------------|
| FluxPanel Gen2 | | | | | |
| FPEMLED10RM | 784197707941 | 912401608930 | Emergency LED driver, Class 2, 10W, compatible with Selectable Panel / NWL Wrap / SDS Strip / FCY | 1/120 | CA, TN, PA |

Product families compatible with the FPEM

| FluxPanel SBP | FluxPanel FPZ | NWL Wraparound | SDS LED |
|---|---|--|---|
| FluxPanel Selectable LED flat panel | FluxPanel Gen2 LED flat panel | NWL Wraparound LED | SDS LED Selectable Strip |
|  |  |  |  |



FluxPanel gen 2

Uniform surface of light
provides low glare, flicker free
lighting at an affordable price.



Why choose FluxPanel Gen2?

- DLC standard and premium options to assure performance and maximum ROI
- Tested TM21 prediction L70 up to 90,000 hrs and warranted for 5 years¹
- Install the remote mount sensor accessory to capture maximum savings now and expand the network for add on sales and value in the future
- Flexible wiring options
- Available with factory installed BSL10LST self test 10W and BSL6LST self test 6W ...more lumen output for 1 watt less

FluxPanel

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|-------------------------|--------------|--------------|---|--------------|-----------------|---------------------|
| FluxPanel Gen2 | | | | | | |
| 2FPZ38B835-2-DS-UNV-DIM | 190096180035 | 912401609018 | 2x2, 3800 lumen, 80CRI, 3500K, Smooth Diffuser, UNV 120-277V, 0-10V | DLC Standard | 1/40 | CA, TN, PA |
| 2FPZ38B840-2-DS-UNV-DIM | 190096180042 | 912401609019 | 2x2, 3800 lumen, 80CRI, 4000K, Smooth Diffuser, UNV 120-277V, 0-10V | DLC Standard | 1/40 | CA, TN, PA, IL |
| 2FPZ42B835-4-DS-UNV-DIM | 190096180066 | 912401609021 | 2x4, 4200 lumen, 80CRI, 3500K, Smooth Diffuser, UNV 120-277V, 0-10V | DLC Standard | 1/20 | CA, TN, PA |
| 2FPZ42B840-4-DS-UNV-DIM | 190096180073 | 912401609022 | 2x4, 4200 lumen, 80CRI, 4000K, Smooth Diffuser, UNV 120-277V, 0-10V | DLC Standard | 1/20 | CA, TN, PA, IL |

1. Visit signify.com/warranties for full warranty information.

SDS Selectable Strip

Economical luminaire
delivering the right light



SDS
(Selectable Strip)

Why choose SDS Selectable LED Strip?

- Simple form
- Convenient specification
- Ease of installation
- Ease of maintenance
- Durable construction
- Simple mounting method
- Frosted glare-free lens
- CCT & Lumen selectability



SDS Selectable Strip

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Dist. Center |
|-------------------------|--------------|--------------|---|--------------|-----------------|----------------|
| Linear Strip SDS | | | | | | |
| SDS21224L8CST-UNV-DIM | 190096131563 | 911401870782 | 2', 1200/1800/2400 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable | DLC Standard | 288 | PA, CA, TN, IL |
| SDS42448L8CST-UNV-DIM | 190096131570 | 911401870882 | 4', 2430/3640/4850 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable | DLC Standard | 144 | PA, CA, TN, IL |
| SDS84998L8CST-UNV-DIM | 190096131587 | 911401870982 | 8', 4900/7350/9800 lumen, 3500K/4000K/5000K (CRI 80), UNV, Dimmable | DLC Standard | 36 | PA, CA, TN, IL |



Field CCT selectable 4000K or 5000K

FCY Value High Bay

Update and upgrade for **real savings**

Low profile and durable design, efficiency and great price – FCX value high bay has it all.



Why choose FCY Value High Bay?

- Die formed sheet metal housing and end plates
- Corrosion resistant gloss white paint after fabrication
- V-hooks and 48" chains supplied (set of 2) for installation
- Lumen maintenance up to 70% (L70) at 50,000 hours
- Access plate located on top of housing for easy wiring
- cULus listed for use in damp locations, -20°C to 45°C ambient

FCY Value High Bay

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|--------------------|--------------|--------------|--|-------------|-----------------|---------------------|
| FCY Value High Bay | | | | | | |
| FCY15L8CST-UNV-DIM | 190096180653 | 912401590942 | 15,000 lumen, 80CRI, Color Select 4000K/5000K, 0-10V, UNV 120-347V | DLC Premium | 1/27 | IL, TN, PA, CA, GA |
| FCY22L8CST-UNV-DIM | 190096180660 | 912401590943 | 22,000 lumen, 80CRI, Color Select 4000K/5000K, 0-10V, UNV 120-347V | DLC Premium | 1/27 | IL, TN, PA, CA, GA |

NWL Selectable Wraparound

Achieve a balance of
performance and appeal



NWL
(Wraparound)
with field on/off
occupancy sensor

Why choose NWL Selectable Wraparound?

- White polycarbonate housing for durability
- Frosted polycarbonate lens for even, low glare lighting
- Hardware for surface mounting included
- Field CCT selectable for 3000K, 3500K or 4000K
- cETLus listed to meet UL 1598 standards for -10°C to 35°C ambient
- Suitable for damp locations



NWL Selectable Wraparound

| Catalog Number | UPC Code | Model No. | Product Description | Compliance | C/P Qty | Dist. Center |
|---------------------------|--------------|--------------|--|--------------|---------|---------------------|
| NWL Selectable Wraparound | | | | | | |
| NWL440L8CST-UNV-DIM-OCC | 190096130917 | 911401803581 | 4000 lumen, 80CRI, Color Select 3000K-3500K-4000K, UNV 120-277V, 0-10V, Occupancy sensor | DLC Standard | 4/32 | CA, TN, PA, IL, GA* |



Value+ LED Exit Signs

Basic exit that offers a low profile design, giving it stylish appeal suitable for any general purpose application.



Why choose Value+ Family?

- Thermoplastic (off white) ABS housing
- Low profile, snap together quick mount design
- Universal wall/ceiling/end mounting
- UL damp location listed
- Pop out chevron directional indicators are easily removed when required
- Extra stencil faceplate for double face sign applications
- 6V maintenance free nickel cadmium battery

Value+ LED Exit Signs

| Catalog Number | UPC Code | Model Number | Product Description | Case Qty | Pallet Qty | Distribution Center |
|-------------------|--------------|--------------|--|----------|------------|---------------------|
| Value+ Exit Signs | | | | | | |
| VEGW | 782343263020 | 912400348806 | Value+ Economy Grade Thermoplastic Exit, Green Letters, White Housing | 12 | 144 | CA |
| VEGWEM | 782343263044 | 912400348808 | Value+ Economy Grade Thermoplastic Exit, Green Letters, White Housing, Emergency (Nicad battery) | 12 | 288 | CA, TN, PA |
| VERW | 782343263006 | 912400348805 | Value+ Economy Grade Thermoplastic Exit, Red Letters, White Housing | 12 | 384 | CA, TN |
| VERWEM | 782343263037 | 912400348807 | Value+ Economy Grade Thermoplastic Exit, Red Letters, White Housing, Emergency (Nicad battery) | 12 | 288 | CA, TN, PA, IL, GA* |

Value+ LED Emergency Units

General purpose emergency product that features a low profile design giving it a stylish appeal suitable for any general purpose application.



Why choose Value+ Family?

- Wall, ceiling and surface mounting provisions
- Long life LED lamps
- 3.6V maintenance free nickel cadmium battery
- UL damp location listed



Value+ LED Emergency Units

| Cat. No. | UPC Code | Model Number | Product Description | Case Qty | Pallet Qty | Dist. Center |
|-----------------------|--------------|--------------|---|----------|------------|---------------------|
| Value+ Emergency Unit | | | | | | |
| VLLU | 784197038342 | 912401289498 | Value + Economy Grade 3.6V LED Emergency white and (2) 1 watt LED lamps | 12 | 96 | CA, TN, PA, IL, GA* |
| VLLU2 | 784197043858 | 912401289502 | Value + Economy Grade 3.6V LED Emergency white and (2) 2 watt LED lamps | 12 | 96 | CA, TN, PA |



All sizes arrive fully assembled and ready to install

Slim Flood LED dual select

Fade-resistant, textured bronze finish with tempered glass lens that is heat and impact resistant

Why choose Slim Flood dual select?

- Complete family of LED floodlights ideal for illuminating signs, building facades or other dark areas
- Can be mounted on the ground, wall, or pole mounted
- Field selectable CCT of 3000–5000K
- Field selectable wattages 10–300W with 7 housing sizes & 4 mountings
- Photo Cell included 35–150W, Photo Cell option 205 & 300W
- IP65 rated, 5-year limited warranty¹



Slim Flood LED dual select

| Catalog Number | UPC Code | Model No. | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|--------------------------|--------------|--------------|--|-------------|-----------------|---------------------|
| Slim Flood dual select | | | | | | |
| SF15-SCT-K-G2-10-BZ | 190096196005 | 911401874384 | Slim Flood Dual Select 15W Max, 3CCT, UNV, Knuckle, Bronze | DLC Premium | 1/180 | TN, CA, PA |
| SF15-SCT-Y-G2-10-BZ | 190096196012 | 911401874484 | Slim Flood Dual Select 15W Max, 3CCT, UNV, Yoke, Bronze | DLC Premium | 1/300 | TN, CA, PA |
| SF35-SCT-K-G2-10-PCB-BZ | 190096196029 | 911401874584 | Slim Flood Dual Select 35W Max, 3CCT, UNV, Knuckle, Bronze | DLC Premium | 1/180 | TN, CA, PA |
| SF35-SCT-Y-G2-10-PCB-BZ | 190096196036 | 911401874684 | Slim Flood Dual Select 35W Max, 3CCT, UNV, Yoke, Bronze | DLC Premium | 1/240 | TN, CA, PA |
| SF60-SCT-K-G2-10-PCB-BZ | 190096196043 | 911401874784 | Slim Flood Dual Select 60W Max, 3CCT, UNV, Knuckle, Bronze | DLC Premium | 1/120 | TN, CA, PA |
| SF60-SCT-Y-G2-10-PCB-BZ | 190096196050 | 911401874884 | Slim Flood Dual Select 60W Max, 3CCT, UNV, Yoke, Bronze | DLC Premium | 1/120 | TN, CA, PA |
| SF100-SCT-S-G2-10-PCB-BZ | 190096196067 | 911401874984 | Slim Flood Dual Select 100W Max, 3CCT, UNV, Slip Fitter, PCB, Bronze | DLC Premium | 1/60 | TN, CA, PA |
| SF100-SCT-T-G2-10-PCB-BZ | 190096196074 | 911401875084 | Slim Flood Dual Select 100W Max, 3CCT, UNV, Trunion, PCB, Bronze | DLC Premium | 1/90 | TN, CA, PA |
| SF150-SCT-S-G2-10-PCB-BZ | 190096196081 | 911401875184 | Slim Flood Dual Select 150W Max, 3CCT, UNV, Slip Fitter, PCB, Bronze | DLC Premium | 1/40 | TN, CA, PA |
| SF150-SCT-T-G2-10-PCB-BZ | 190096196098 | 911401875284 | Slim Flood Dual Select 150W Max, 3CCT, UNV, Trunion, PCB, Bronze | DLC Premium | 1/40 | TN, CA, PA |
| SF205-SCT-S-G2-10-BZ | 190096196104 | 911401875384 | Slim Flood Dual Select 205W Max, 3CCT, UNV, Slip Fitter, PCB, Bronze | DLC Premium | 1/24 | TN, CA, PA |
| SF205-SCT-T-G2-10-BZ | 190096196111 | 911401875484 | Slim Flood Dual Select 205W Max, 3CCT, UNV, Trunion, PCB, Bronze | DLC Premium | 1/24 | TN, CA, PA |
| SF300-SCT-S-G2-10-BZ | 190096196128 | 911401875584 | Slim Flood Dual Select 300W Max, 3CCT, UNV, Slip Fitter, PCB, Bronze | DLC Premium | 1/20 | TN, CA, PA |
| SF300-SCT-T-G2-10-BZ | 190096196135 | 911401875684 | Slim Flood Dual Select 300W Max, 3CCT, UNV, Trunion, PCB, Bronze | DLC Premium | 1/20 | TN, CA, PA |
| SF205-300-PCB | 190096196142 | 911401875784 | Slim Flood, 120–150–205W PCB Accessory | DLC Premium | — | TN, CA, PA |

1. See www.signify.com/warranties for details.

Wall Pack LED dual select

Classic design meets LED technology

The new Wall Pack dual select helps you upgrade from costly HID fixtures with confidence.



Why choose Wall Pack?

- An easy switch from costly HID fixture
- Field selectable wattage and color temperature
- Flexible options, built-in photocell, and field enable or disable
- Glass refractor lens design cuts down on glare



Wall Pack LED dual select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|-----------------------|--------------|--------------|---|-------------|-----------------|---------------------|
| Wall Pack dual select | | | | | | |
| WP100-SCT-G2-10-BZ | 190096131341 | 911401872481 | Selectable Wattage and CCT 80-100W / 30K-40K-50K, Bronze Finish | DLC Premium | 2/24 | CA, TN, PA, IL, GA* |
| WP60-SCT-G2-10-BZ | 190096131334 | 911401872381 | Selectable Wattage and CCT 28-40-60W / 30K-40K-50K, Bronze Finish | DLC Premium | 2/24 | CA, TN, PA, IL, GA* |



Adj. Slim Wall Pack LED dual select

Slim, low profile LED design

Features a discreet design that will complement any building exterior. Two sizes are available, with three wattage and three CCT selectable options each.



Why choose Adjustable Slim Wall Pack?

- Wall, surface, low level mounting
- Die-cast aluminum, hinged
- Simplified solution – dual select
- 2 housing sizes (25W & 75W)
 - 25W (15/20/25W & 1800/2400/3000 lms)
 - 75W (45/60/75W & 5400/7200/9000 lms)
- CCT Selectable (3K/4K/5K) & 120-277V
- IP65 / IK07 Rated / DLC 5.1
- Button Photocontrol w/0-90° tilt option

Adjustable Slim Wall Pack LED dual select

| Catalog Number | UPC Code | Model Number | Product Description | Compliance | Case/Pallet Qty | Distribution Center |
|---------------------------|--------------|--------------|---|-------------|-----------------|---------------------|
| Adjustable Slim Wall Pack | | | | | | |
| ASW25-SCT-G1-8-PCB-BW | 190096182039 | 912401591885 | Adj Slim WP DS 15-25W/30-40-50K/UNV/PCB | DLC Premium | 4/144 | TN,CA,PA |
| ASW75-SCT-G1-8-PCB-BW | 190096182046 | 912401591886 | Adj Slim WP DS 45-75W/30-40-50K/UNV/PCB | DLC Premium | 4/120 | TN,CA,PA |



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.