

LUMEC

by  Signify

Urban

OmniScape

Post Top & Arm Mount



A vision of versatility

Lumec OmniScape LED Post Top & Arm Mount luminaires offer a clean and modern aesthetic while providing a foundation to build your vision and enhance any outdoor space. Along with providing uniquely customizable design flexibility and personalization, these luminaires deliver industry leading performance. This new family also allows for the integration of connected ready controls and technology.

Modularity

Custom combinations

- Contemporary style
- Transitional style
- Historical style
- Post top mount
- Arm mount
- Skirt option & finial options
- LEDgine/ComfortEdge™ light engines
- 2700, 3000, 4000K CCT in 70/80 CRI
- Multiple distributions available

Performance

(LEDgine) 4000K, 70CRI

- Post top: Up to 18,000lm (169 LPW)
- Arm mount: Up to 21,000lm (198 LPW)

ComfortEdge

- Post top: Up to 16,000lm (132 LPW)
- Arm mount: Up to 18,000lm (152 LPW)

Connectivity

Connected ready options/controls

- Zhaga certified driver (zD4i)
- Digitally addressable lighting interface driver (DALI)
- Sensor Ready driver (SR)
- 7-pin receptacle (TRLD7)
- Zhaga socket (TLRSR)
- Outdoor Multi-Sensor (OMS)
- Microwave Motion Sensors (MW)
- Field Adjustable Watt Selector (FAWS)
- Photoelectric Cell controls (PH)

OSA/OSP OmniScape

LED Post Top & Arm Mount



S-OSPCCC

Contemporary



S-OSPTTT

Transitional



S-OSPHHH
with Skirt

Historical

Mix components to create your own personal style and accentuate any outdoor space. OmniScape is designed to meet a broad range of Contemporary, Transitional or Historical lighting applications in a single family.



Contemporary

Boasting a modern and refined aesthetic, the Contemporary style incorporates a minimalist design language and soft volume transitions. Luminaire arms create an overall conical form, featuring gentle radii transitions and generous chamfers, adding character, and creating a sense of unity. This style is distinctively modern and aimed at contemporary architectural spaces, yet its minimalist appearance makes it suitable for a variety of outdoor areas.

Transitional

A harmonious fusion of classic and modern elements, the Transitional style creates a sophisticated and elegant look. The smooth fitter and curved arms are inspired by the natural beauty of the calla lily, and flow seamlessly from the base to the light source. The open frame design is a stylish feature that also pays homage to the historic luminaire that once illuminated the most renowned parks in North America. The transitional design is adaptable and timeless, complementing any architectural style or outdoor setting.

Historical

The Historical style draws inspiration from the past while incorporating seamlessly into the present, featuring a sleek acorn-shaped body that evokes the classic style of historical luminaires without the need for a globe. The double arched arms connect the fitter to the roof, creating a smooth and elegant classic silhouette. The top section combines dome and cornice forms to add character and familiarity to the design. The design is suitable for both historical and modern settings, as it blends the past and the present in a refined and versatile way.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.