

# Day-Brite CFI

## Commercial Linear

### Strips

#### Product Selection Guide

Real convenience for your operation's success. Tough and dependable luminaires designed for ease of handling and flexibility.

Reference	
★ ★ ★	High applicability
★ ★	Medium applicability
★	Low applicability
-	Non-applicable



		Good	Better	Better	Better	Best	Best	Best	Best
Applications	Model	SDS LED Selectable Strip	FluxStream EZ LED Strip	FluxStream Strip	FluxStream Industrial	FluxSpace Round Lens	FluxSpace Square Lens/No Lens	FluxSpace Uplight	5F LED Industrial
	Education	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Office	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Healthcare	-	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★
	Retail	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Industrial	★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★	★ ★ ★
	Residential	★ ★	★ ★	★ ★	★	★	★	★	-
	Sizes	2', 4', 8'	4', 8'	2', 3', 4', 8'	4', 8'	2', 3', 4', 8'	2', 3', 4', 8'	2', 3', 4', 8'	4', 8'
Features and Specifications	Lumen Output	1.2K/1.8K/2.4K/3.6K/4.8K/7.3K/9.8K	4K/8K	2K/3K/4K/5.5K/6K/7K/8K/11K/14K	2K/3K/4K/5.5K/6K/7K/8K/11K/14K	2K/3K/4K/4.5K/5K/6K/7K/8K/9K/10K/12K/14K/16K/18K/20K/24K	2K/3K/4K/4.5K/5K/6K/7K/8K/9K/10K/12K/14K/16K/18K/20K/24K	2K/3K/4K/4.5K/5K/6K/7K/8K/9K/10K/12K/14K/16K/18K/20K/24K	4K/5.5K/7K/8K/11K/14K
	Max. Efficacy	119 lm/W	104 lm/W	133 lm/W	133 lm/W	160 lm/W	159 lm/W, 170 lm/W (no lens)	161 lm/W	159 lm/W
	Efficacy	Standard	Standard	Standard	Standard	Standard/High	Standard/High	Standard/High	-
	Lens Optics	-	-	-	-	-	Narrow, Wide, Aisle	-	-
	Color Temperature	3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K	3000/3500/4000/5000K/2700-6500 TW	3000/3500/4000/5000K/2700-6500 TW	3000/3500/4000/5000K/2700-6500 TW	3500/4000/5000K
	Color Rendering	80	80	80	80	80/90	80/90	80/90	80
	Lifetime	L70 50,000 hrs	L70 50,000 hrs	L70 100,000 hrs	L70 100,000 hrs	L70 100,000 hrs	L70 100,000 hrs	L70 100,000 hrs	L70 100,000 hrs
	Ambient Temperature	-20 to +40°C	-10 to +25°C	-20 to +40°C	-20 to +40°C	-20 to +50°C	-20 to +50°C	-20 to +50°C	-20 to +40°C
	Dimming	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V	0-10V
	Emergency	✓ (field installed)	✓	✓	✓	✓	✓	✓	✓
	Electro-Connect Modular Wiring Capability	-	✓	✓	✓	✓	✓	✓	-
	DLC	Standard	Standard	Standard/Premium	Standard/Premium	Standard/Premium	Standard/Premium	Standard/Premium	Standard/Premium
	Warranty	5 years	5 years	5 years	5 years	5 years	5 years	5 years	5 years
Integrated Controls	Occupancy Sensor	-	✓	✓	✓	✓	✓	✓	✓
	SpaceWise	-	-	✓	✓	✓	✓	✓	✓
	Interact	-	-	✓	✓	✓	✓	✓	-
	Link					Coming soon	Coming soon	Coming soon	