

PD Cylinder Pendants



Classic Fixture for Modern Needs

This stylish lighting solution combines high efficiency with stunning design, offering a wide range of brightness to suit any setting. Perfect for offices, retail, and hospitality, it comes in universal colors with flexible mounting options.

Made sustainably from recycled materials, it's also easy to maintain with versatile lamp choices. Plus, it's Buy American (BAA) compliant.

Configuration

Downloads

Application Imagery



Key specifications

- Classic form factor compatible with PAR38 Lamps
- Printed from sustainably sourced, recyclable materials
- Canopy or track mounted
- 3 colors and 2 texture options
- Printed and Assembled in Littlestown PA
- Buy American Act (BAA) Compliant

Operational & certifications

Protection Class	IP20
Ambient Range	0 to +25C
Certifications	RoHS
Warranty	5 Years

Electrical

Dimming: Lamp Dependant

Input Voltage: 120V – 277V

Frequency: 50/60Hz

Power Factor: Lamp Dependant

Configuration

Downloads

3D printing Brochure

Spec Sheet

Photometrics – 16" Low Bay – BAL Series

Photometrics – 12" Low Bay – BAL S Series

Mounting instruction

Interested?

Learn more about possibilities offered by 3D-printed luminaries.

Sustainability



Co-Creation



Our Products



Applications



LIGHTOLIER