

# Stonco KEENE

Outdoor

Wall Mount

Product Selection Guide

Stonco features a variety of wall packs to suit a range of building types. Stonco wall mount luminaires are readily available and easy to install, making them a great choice for any project.



|  | Good                  | Good                      | Good                  | Better  | Better  | Better                                       |
|--|-----------------------|---------------------------|-----------------------|---|---|--|
|  | Wall Pack Dual Select | Adjustable Slim Wall Pack | Residential Wall Pack | LytePro Wall Small                            | LytePro Wall Medium                           | LytePro Wall Large                           |
| Prefix                                   | WP                    | ASW                       | RWP                   | LPW7  | LPW16   | LPW32  |
| Lumen Output Range                       | 3860-12800            | 1800-9000                 | 2600-4100             | 1050  | 2065-4629                                     | 6472-9637                                    |
| Efficacy                                 | 128-145               | 120+                      | 120                   | 108   | 87-104  | 95-114                                       |
| Distribution                             | -                     | -                         | -                     | Type 2  | Type 3, 4                                     | Type 3, 4                                    |
| Color Temperature                        | 3000K, 4000K, 5000K   | 3000K, 4000K, 5000K       | 3000K, 4000K, 5000K   | 3000K, 4000K                                  | 3000K, 4000K                                  | 3000K, 4000K                                 |
| Mounting Height                          | 10-25                 | -                         | 7-10                  | 7-10  | 10-15   | 15-25  |
| 0 Uplight                                | -                     | -                         | -                     | ✓   | ✓   | ✓  |
| Emergency (0°C to 40°C)                  | -                     | -                         | -                     | -   | -   | ✓  |
| Field Adjustable Wattage Selector (FAWS) | ✓                     | ✓                         | ✓                     | -   | -   | ✓  |
| Motion Response                          | -                     | -                         | -                     | -   | -   | ✓  |
| Photocell                                | ✓                     | ✓                         | Button                | Button  | Button  | Button                                       |
| Finish                                   | Bronze, White         | Bronze                    | Bronze                | Black, Bright, Bronze, Dark Grey, Medium Grey | Black, Bright, Bronze, Dark Grey, Medium Grey | Black, White, Bronze, Dark Grey, Medium Grey |
| IP Rating                                | IP65                  | IP65                      | IP65                  | IP65  | IP65  | IP65   |
| DLC Listing                              | Standard              | DLC 5.1 Premium           | DLC 5.1 Premium       | Standard                                      | Standard                                      | Standard                                     |
| Certifications                           | cULus                 | cULus                     | cULus                 | cETLus  | cETLus  | cETLus                                       |
| Lifetime                                 | L70-54000h            | L70-54,000h               | L70                   | L70-60,000h                                   | L70-54,000h                                   | L70-54000h                                   |
| Limited Warranty                         | 5 years               | 5 years                   | 5 years               | 5 years                                       | 5 years                                       | 5 years                                      |
| Link                                     |                       |                           |                       |   |   |  |