

PHILIPS

Compact fluorescent
Spiral bulb

Spiral

18 W (75 W)

GU24 base

Soft White

046677454203



Spend a little, save a lot

Philips Twister Mini energy-saving bulbs provide instant brightness and make colors appear more vivid. Due to its compact design, this low-consumption spiral bulb is ideal for narrow luminaires, saving energy and money for up to 10 years.

Sustainable choice

- Lasts up to 9 years
- Very low energy consumption; saving at least 77%

Energy efficiency

- An energy saving twister lamp, it can last up to 10,000 hrs

Similar to Incandescent

- Similar to Incandescent

Bring your room to life

- This twister bulb creates a soft, warm light

Highlights

Lifetime 9 years

With a lifetime of up to 10,000 hours, this Philips CFL lamp will ensure your desired atmosphere for up to 9 years*.

Saving up to 77%

By replacing traditional light bulbs with a Philips CFL alternative, you will gain immediate, significant, energy savings while contributing to a sustainable planet.

Energy efficient lamp

This bulb saves up to \$62.70 in energy costs when you replace a 75 Watt incandescent with this 18 Watt compact fluorescent light bulb**.

Similar to Incandescent

This CFL lamp is an easy retrofit for GU24 lamps and fixtures.

Soft White 2700K

Light can have different colour temperatures, indicated in units called Kelvin (K). Bulbs with a low value produce a warm, more cozy light, while those with a high Kelvin value, create a cool, more energizing light.

Specifications

Bulb characteristics

- Shape: Spiral
- Socket: GU24
- Lamp shape code: GU24
- Dimmable: No

Bulb dimensions

- Height: 117 mm
- Width: 139 mm

Durability

- Average life (at 2.7 hrs/day): 9 year(s)
- Number of switch cycles: 5,000
- Nominal lifetime: 10,000

Light characteristics

- Application: Soft light
- Color rendering index (CRI): 80
- Color temperature: 2700 K
- Light Color Category: Soft White
- Nominal luminous flux: 1250 lm
- Correlated Color Temperature (Nom): 2700 K
- Luminous Flux: 1,250 lm
- Luminous Efficacy (rated) (Nom): 67

Power

- Power Factor (Fraction): 0.55

Power consumption

- Wattage equivalent: 75 W
- Power: 18.0 W
- Energy Consumption kWh/1000 h: 18

Rated values

- Rated lifetime: 10,000
- Rated luminous flux: 1250 lm

Technical specifications

- Chromaticity Coordinate Y: 412
- Chromaticity Coordinate X: 459
- Dimmable: No
- Line Frequency: 50 or 60
- Cap-Base: GU24

Packaging dimensions and weight

- EAN/UPC - product: 046677454203
- Net weight: 0.07 kg
- Gross weight: 0.1 kg
- Height: 11.6 cm
- Length: 6 cm
- Width: 6 cm



Issue date: 2026-02-07
Version: 0.614

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com