

PHILIPS

LEDtube Type A T8

LED

600mm

4000K

G13

046677469443



Simple T8 LED replacement for fluorescent tubes

Philips InstantFit LED tubes easily replace fluorescent T8 tubes operated on instant-start electronic ballasts, no rewiring needed. This glass LED linear bulb looks and feels like fluorescent and has a cool white light and long lifetime.

High quality light

- Cool, white light

Instant on

- Instant light when switched on

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.

Highlights

Cool, white light



This bulb has a color temperature of 4000K providing you with an extra cool, fresh and crisp light.

Instant On



No need to wait: Philips LED light bulbs provide their full level of brightness immediately when they are switched on. Just by flipping the switch, your

room is at full brightness. There is no slow starting or waiting.

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: T8
- Socket: G13
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 70,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 180
- Color rendering index (CRI): 80
- Color temperature: 4000 K
- Nominal luminous flux: 1200 lm
- Warm-up time to 60% light: 0.5
- Color Code: 840 | CCT of 4000K
- Luminous Efficacy (rated) (Nom): 171

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 046677469443
- EOC: 469445
- Product title: 7T8/LED/24-840/IF11/P 10/1 FB

Power consumption

- Power factor: 0.9
- Voltage: 120-277, 347 V
- Wattage equivalent: 17
- Power: 7

Product dimensions and weight

- Overall height: 602.8 mm
- Overall length: 602.8 mm
- Overall width: 26.3 mm

Technical specifications

- Frequency: 20-120
- Bulb technology: LED

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677469443
- Net weight: 0.09 kg
- Gross weight: 0.12 kg
- Height: 61 cm
- Length: 2.8 cm
- Width: 2.8 cm



Issue date: 2026-04-15
Version: 0.623

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com