

PHILIPS

Reflector 90W
PAR38 E26

LED

3000K

900lm

15000h

046677544720



One bulb, four light settings

With Philips SceneSwitch color change LED PAR bulbs, you can have white light for everyday use or colored light for special occasions. Flip your existing switch to toggle between white, red, green, or blue.

Light beyond illumination

- Restore the lamp to the default factory setting
- No dimmer or additional installation needed
- Instant on

Highlights

Reset (Sceneswitch)



If multiple lamps are used and they are no longer synchronized, simply toggle

the switch (turn it on and off again within 1 second) to restore the lamps to the default factory setting.

Instant on

Plug and play



Does not require any additional installation or a dimmer switch. This bulb is not suitable for use with dimmers. If used on a dimmer set the dimmer setting to 100% brightness.

Specifications

Bulb characteristics

- Lamp shape: Directional reflector
- Socket: E26
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Color rendering index (CRI): 80
- Nominal luminous flux: 900 lm

Other characteristics

- Efficacy: 90 lm/W

Power consumption

- Power factor: 0.6

Product dimensions and weight

- Length: 13.4 cm

Rated values

- Rated peak intensity: 2300 cd

Technical specifications

- Frequency: 50-60

Packaging dimensions and weight [10PAR38/LED/830-R-G-B/F35/ SSCC/G 4/1FBWS]

- EAN/UPC - product: 046677544720
- Net weight: 0.39 kg
- Gross weight: 0.48 kg
- Height: 13.7 cm
- Length: 12.5 cm
- Width: 12.5 cm

046677544720

Packaging dimensions and weight
[10PAR38/LED/830-R-G-B/F35/
SSCC/G 4/1FB]

- EAN/UPC - product: 046677544720
- Net weight: 0.39 kg

- Gross weight: 0.48 kg
- Height: 13.7 cm
- Length: 12.5 cm
- Width: 12.5 cm



Issue date: 2025-11-01
Version: 0.341

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com