

PHILIPS

Bulb 65W BR30 E26
x4

LED

5000K

650lm

11000h

04667755399



Bright LED lighting with excellent light quality

Philips LED light bulbs provide a cool white light, an exceptionally long life, and immediate, significant energy savings. With a pure and elegant design, this bulb is the perfect replacement for your matted traditional bulbs.

Choose for a sustainable solution

- Saves up to 80% Energy

Light beyond illumination

- A simple LED for everyday use
- Instant on

High quality LED light that lasts for decades

- Designed for the comfort of your eyes

Highlights

Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

A simple LED for everyday use



The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from LED at an affordable price.

Instant on Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional reflector
- Socket: E26
- Bulb Finish: Frosted
- Dimmable: No

Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 11,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 110
- Color rendering index (CRI): 80
- Color temperature: 5000 K
- Nominal luminous flux: 650 lm
- Warm-up time to 60% light: 0.5
- Luminous Efficacy (rated) (Nom): 72

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 046677555399
- EOC: 555391
- Product title: 9BR30/LED/850/FR/P/ND 2/4FB

Power consumption

- Power factor: >0.5
- Voltage: 120 V
- Wattage equivalent: 65
- Power: 9

Product dimensions and weight

- Overall height: 130 mm
- Overall length: 130 mm
- Overall width: 95 mm

Technical specifications

- Frequency: 60
- Bulb technology: LED

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 046677555399
- Net weight: 0.38 kg
- Gross weight: 0.52 kg
- Height: 15.1 cm
- Length: 16.8 cm
- Width: 16.8 cm



Issue date: 2026-05-13
Version: 0.99

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com