



Filament Globe clear 3.8W (Eq.40W) G25 E26

Enjoy more convenience in everyday life with this smart WiZ LED G25 vintage globe-shape bulb. This bulb gives soft white light that dims to your desired brightness level via app or voice. You can set schedule to turn lights on and off according to your daily or weekly routines, and have remote access to your lights even when you're away. WiZ lights connect to your existing Wi-Fi, no additional hardware is needed.

PRODUCT HIGHLIGHTS

- Soft white
- Glass
- Easy plug and play
- Control with WiZ app or voice



Easy plug and play. Works with your existing Wi-Fi.

WIZ works with your existing Wi-Fi router, no additional gateway is needed. Simply plug in your new light, download the WIZ app and you're ready to go!

Automate your light with schedules

Automate the lights to fit your daily or weekly routines. Schedule your light to turn on before you arrive home and keep it off when not needed.

Control anywhere with your smartphone.

Control your WIZ lights wherever you are with smartphone. No need to worry if you've left your lights on before leaving home. WIZ app is available for iOS and Android.

Energy monitoring

The WIZ app keeps records of the energy consumption of your lights. View your weekly or daily report and plan your lighting wisely for an optimized energy consumption at home.

Smart dimming via app, voice or dimmer

Dim your lights to your desired brightness level via your smartphone, the WIZmote or your voice. No need to install an expensive dimmer.

Customize Scenes with preset dynamic light modes.

Mix different color and white lights modes to create the perfect light ambience for your daily moment. Save it and call it out anytime with app, WIZmote or voice.



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor/Outdoor
Lamp shape: G25
Socket: E26
Technology: Smart Wi-Fi
Type of glass: Clear
Dimmable: Yes

BULB DIMENSIONS

Height: 11.9 cm
Weight: 0.05 kg
Width: 8 cm

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s)
Lumen maintenance factor: 70%
Number of switch cycles: 20,000
Nominal lifetime: 15,000

EXTRA FEATURE/ACCESSORY INCL.

LED integrated: Yes
Solar Energy: No
Warm glow dimmable light: No

LIGHT CHARACTERISTICS

Color consistency: 4 SDCM
Color rendering index (CRI): 90
Color temperature: 2700 K
Light Color Category: Soft White
Nominal luminous flux: 350 lm
Starting time: <1 s
Warm-up time to 60% light: instant
full light

OTHER CHARACTERISTICS

Lamp current: 45 mA
Efficacy: 92 lm/W

PACKAGING INFORMATION

EAN: 046677556068
EOC: 556068
Product title: 3.8G25/WiFi
DIM/927/CL 4/1FB

POWER CONSUMPTION

Power factor: 0.7
Voltage: 120 V
Wattage: 3.8 W
Wattage equivalent: 40 W

PRODUCT DIMENSIONS AND WEIGHT

Length: 11.9 cm

RATED VALUES

Rated lifetime: 15,000
Rated luminous flux: 350 lm
Rated power: 3.8 W

SERVICE

Warranty: 3 year(s)

TECHNICAL SPECIFICATIONS

Frequency: 60
Bulb technology: LED

THE BULB

Software upgradable: Yes

WHAT'S SUPPORTED

Compatible with Effects: Yes
WiFi: 802.11b/g/n
Defined support period: Minimum of 60 months after introduction date
Max. number of accessories: 9999
Compatible operating systems: iOS
Android
Communication protocol: Bluetooth
WiFi (2.4GHz)
Compatibility with 3rd party systems:
Alexa Enki Google Home Homey
IFTTT Matter Samsung Smartthings
Siri Shortcuts
Matter functionality: Via 3rd party hubs (Wi-Fi)

PACKAGING DIMENSIONS AND WEIGHT

EAN/UPC - product: 046677556068
Net weight: 0.05 kg
Gross weight: 0.13 kg
Height: 14.5 cm
Length: 9.2 cm
Width: 10.9 cm



© 2026 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.